

# BURNDY® TOOLS

PATRIOT®  
PATCUT1500  
SERIES



# BURNDY® PATRIOT® PATCUT1500 SERIES

## FEATURES & BENEFITS




## MODELS, SPECIFICATIONS & CAPACITIES

MODELS	
PATCUT1500LI	Tool, 3Ah, 120V AC
PATCUT1500L5	Tool, 5Ah, 120V AC
PATCUT1500LCB	Tool, No Charger/Batteries

SPECIFICATIONS	
Tool Weight	8.1 lbs with battery
Length	15.5"
Operating Voltage	18 V-DC Lithium-ion
Recharge Time	30 minutes (3.0Ah)
	45 minutes (5.0Ah)
Warranty	3 year limited warranty (excluding blades)
	3 years on battery and charger

CUTTING CAPACITIES	
Aluminum	up to 1500 kcmil
Copper Flex	up to 1250 kcmil
Copper (soft drawn)	up to 1000 kcmil
Copper (hard drawn)	up to 750 kcmil
Do Not Cut Steel or ACSR	



**TRUST THE BURNDY ENGINEERED SYSTEM**



**WHEN FACING THE UNPREDICTABLE,  
YOU'RE NOT ALONE...**

** BURNDY HAS YOUR BACK!**

**PROFESSIONAL GRADE  
TOOLS YOU KNOW  
TOOLS YOU TRUST**



Customer Service Department  
7 Aviation Park Drive  
Londonderry, NH 03053  
1-800-346-4175  
1-800-451-4956 (Technical Services)  
1-603-647-5299 (International)

Canada  
1-800-361-6975 (Quebec)  
1-800-387-6487 (All other provinces)

Mexico  
011-52-722-265-4400

Brazil  
011-55-11-5515-7225

Tool Service Center  
Littleton Industrial Park  
Littleton, NH 03561  
1-800-426-8720

[www.burndy.com](http://www.burndy.com) | 1-800-346-4175

** BURNDY**

**Connecting Power to Your World®**

