

Smaller Package - Better Balance

Compact Size, Robust Jaw Design, Interchangeable!

Newly redesigned PATRIOT® IN-LINE® tool platform:

PATMD-LW Series of Tools



The BURNDY® PATRIOT® IN-LINE® tool platform has been redesigned to meet the growing market need for a smaller, lighter, and more ergonomic IN-LINE tool.

The PATMD-LW series weighs just 6.7 lbs. and is only 18.70" in height. This represents a 14% reduction in weight and an 11% overall length reduction compared to the current PATMD series; offering unrivaled ergonomics and comfort. Newly redesigned, robust jaws featuring proprietary locking tabs and a spring release pin, simplify the jaw change out process. An added layer of safety, as the jaws stay retained in the tool when the release pin is activated. The crimp jaws accept standard BURNDY® "W" and "X" style crimping dies.

A 350° rotatable head allows the tool to be used in hard to reach areas and an LED has been added to assist in lighting up the work area. Featuring the robust and reliable INFINITY DRIVE® transmission, a patented high-speed hydraulic pump system, and newly designed and protected electronic circuitry, the PATMD-LW retains the industry-leading performance, speed, and dependability expected from the PATRIOT line of rugged and reliable tools. Large on/off triggers and hand grip area enhance the user experience, with or without gloves. To prevent accidental operation of the tool, a safety switch is integrated into the trigger.

The PATMD-LW is powered by Makita Li-ion batteries for long-lasting power and will accept multiple Makita battery platforms (2.0Ah through 5.0Ah). It will be offered with a choice of either 3.0Ah or 5.0Ah batteries.

A lifetime warranty on the INFINITY DRIVE is offered along with a 5-year limited warranty (excluding blades) for the tool and a 3-year limited warranty on the batteries and charger.

Customer Service 1-800-346-4175 | Tool Service Center 1-800-426-8720 | Technical Services 1-800-451-4956 | www.burndy.com



Connecting Power to Your World®



Smaller Package - Better Balance

Compact Size, Robust Jaw Design, Interchangeable!

Features & Benefits

- **Compact Size** — Reduced weight and length; 14% lighter and 11% shorter for unmatched ergonomics and comfort
- **Robust Jaw Design** — Improves tool balance and user experience
- **Scissor-Action Interchangeable Jaws** — Simplifies the crimping and cutting processes
- **Locking Tabs** — Retain the jaws in place when the change-out pin is released for quick jaw changeover and user safety
- **LED Worklight** — Lights up the work area
- **Coated PCB** — Protects the electronics from dust, dirt, and humidity
- **350° Rotatable Head** — Allows the tool to be used in multiple positions for hard to reach areas
- **Large Triggers and Hand Grip Area** — Allows for easy operation and comfort while wearing work gloves
- **Trigger Lock Safety Switch** — Prevents accidental operation of the tool
- **Manual Drain Trigger** — Provides total control of the crimping process
- **Quick-Release Actuated Blade Guide** — Automatically closes to isolate cables for easy positioning and guides the blades through the cutting cycle
- **Makita Battery and Charger** — For long lasting power
- **Lifetime Warranty** on INFINITY DRIVE® Transmission

Interchangeable Jaws



BG / D3 Groove
(shown on tool)



O / D3 Groove



D3 Groove Only
Snub-Nose



Cutting Jaw



Customer Service 1-800-346-4175 | Tool Service Center 1-800-426-8720 | Technical Services 1-800-451-4956 | www.burndy.com