

NEW 444S REMOTE SERIES

VERSATILE 11-TON DIELESS REMOTE C-HEAD

Features & Benefits




- New C-Head Style for easy access and increased flexibility
- Dieless System with Range Taking Capability
- For Use On:
 - #4AWG-1000kcmil Copper&Aluminum
 - #4 AWG - 556.6 kcmil ACSR, AAC, AAAC, ACAR (Full Tension Overhead Splices)
- Operates on 10,000 psi pressure
- Includes remote head tool and canvas carry bag

Connections are UL Listed to UL 486A-486B on Copper & Aluminum terminals and splices;

Also, comply with ANSI C119.4 on YDS-RL and the New YDS-RLNI Splices (ACSR, AAC, AAAC, ACAR)

Other BURNDY splice families coming soon!



Unique 444S Crimp Embossment

Customer Service 1-800-346-4175 | Tool Service Center 1-800-426-8720 | Technical Services 1-800-451-4956 | www.burndy.com