



- Glass fiber Reinforced Plastic laminate construction
- Suitable for use with GAI-Tronics telephones and Page Party equipment
- 23dB Mean noise reduction
- Polypropylene interior
- 2" acoustic lining panels
- Internal gear plate for ease of equipment mounting
- Up to 132lbs (60kgs) of equipment can be carried
- Detachable internal shelf
- External mounting straps
- Fire retardant

TECHNICAL SPECIFICATION

Body Material

Main Body and Detachable Shelf:

General purpose resin continuous filament MAT

Acoustic Damping:

Insulation - Rockwool RW3, Density 60kg/m3 (50mm)

Acoustic Facing:

Internal Lining - White perforated PPC, 3mm thickness.

Fire Resistance:

BS476 Part 7 Fire Retardant Class 2

Telephone Mounting Plate:

988-60-0002-20* - 316 (Marine) Grade Stainless Steel

Mounting Straps:

988-60-0002-20* - 316 Stainless Steel

Colour:

Yellow or red as standard. Other options available

Weight:

Approx 55lbs (25 kg)

DIMENSIONS

- **H 36 ¼" x W 27" x D 23 ½"**
(H 920mm x W 690mm x D 600mm)
- **Fixing: W 29 ¼" x H 22 ½"**
(W 740mm x H 575mm)

ORDER INFORMATION

	Mounting Plate: Stainless Steel (316)	Mounting Straps: Stainless Steel (316)	Internal Shelf
988-60-0002-20*	✓	✓	✓
Larger gear plate: To be used with Drillers Intercom stations (DEX), Ex PageParty® and SmartSeries™ stations, and Elemecplus external access panels.			
988-60-0002-50*	✓	✓	✓

*color	yellow	red
	1	2

Gear / Mounting Plates

