

## Features

- **16 - Frequency / Function Control**
- **Programmable Quick Pages, Aliases, and Group Paging**
- **2-Line Adjustable LCD Display**
- **4 Programmable Input / Outputs**
- **Parallel Status Updating**
- **Multiple Parallel Deskset Support**
- **Line Operated Transmit Light (LOTL)**
- **Programmable Voice Delay**
- **Full Duplex Capability 2 or 4-Wire**
- **Parallel Transmit Audio**
- **Line Receive and Transmit Compression**
- **Adjustable Receive Input Sensitivity and Transmit Output Level**
- **Monitor and Intercom**
- **MDC1200 Operation with Printer Output**
- **DTMF Encode**
- **PC Programmable**
- **External Connection for Accessory Microphone**



## Applications

- **Police, Fire, Ambulance**
- **Utilities, Taxis, Airlines**
- **Forestry, Parks, Recreation**
- **Industries, Municipalities, Construction**
- **Security and Public Safety**

The **L3149B Advanced Tone Remote Deskset** offers console-style alternatives to conventional base station control. Used with GAI-Tronics model ITA2000A Tone Remote Adapter, the L3149B provides users the flexibility needed for cost-effective, reliable dispatch.

Key features include 16-frequency control, 2-line display, function aliases, intercom, parallel status updating, programmable voice delay, and multiple deskset support. Each of the four programmable pushbuttons can be programmed with two functions. Additionally, there are four inputs and outputs that can be programmed for various uses. With the use of the Relay Control Option (XRC0001A), outputs can be configured for On-Air Light, General Purpose Control "On-Off", PTT, Vox Detect, Data Enable, and Guard Tone Detect. Inputs can be configured for Button Remap, E-Lead, for E&M, Output Link, and Link to Page. Additional capabilities include DTMF, 2-Tone,

Plectron, 5-Tone, 1500, 2805, and custom 2-Tone paging formats. Pushbuttons can be configured for both preset and stack paging. Utilizing the Relay Control Option, the L3149B is capable of local or E&M with tone control.

Each unit also includes a plug-in power supply, handset, built-in microphone and speaker. Front-mounted controls and adjustments allow for easy installation and operation.

The L3149B can be programmed for MDC1200 functionality, providing the following feature operations:


- |               |               |                 |
|---------------|---------------|-----------------|
| • Emergency   | • Radio Check | • Message       |
| • Call Alert  | • PTT ID      | • Radio Enable  |
| • Rapid Call  | • Post PTT ID | • Radio Disable |
| • Select Call | • Status      |                 |

## Specifications for L3149B

Color ..... Black  
 Dimensions ..... 7.6" W x 8.9" L x 4.7" H  
 Weight ..... 3.2 lbs. min.  
 Temperature ..... -35° to +70°C  
 Humidity ..... 95% at 50°C non-condensing  
 Power Input ..... 10.5-16 VDC 400 mA maximum  
 Frequency Response ..... ±3 dB from 300-3000 Hz  
 (except notch filter)  
 Hum and Noise ..... Less than -45 dB below rated outputs  
 Audio Output to Speakers ..... 1 watt minimum with level in  
 compression range  
 Audio Distortion ..... Less than 3% THD  
 Transmit Audio ..... -14 dBm to +12 dBm adjustable  
 Maximum Number of Remotes ..... Per System Limitations  
 Microphone Connections ..... 8-pin modular

**Control Functions** (Tones Standard as Shipped):  
 Guard Tone ..... 2175 Hz, programmable  
 F1-F16 ..... Each can be programmed from 550-2050 Hz  
 in 100 Hz increments  
 Monitor ..... 2050 Hz, programmable  
 Safety ..... Class III SELV-powered  
 equipment. Powered by UL-listed (E104603) and  
 CSA certified (LR67888) ac adapter  
 Emissions ..... USA: FCC Part 15, Sub. B-Verification  
 Canada: ICES-003  
 Line Interface ..... USA: FCC Part 68 Exempt (Category II Tariff  
 #260 service for private/leased line applications) Canada:  
 Designed to meet IC CS03-8  
 Paging Encoder ..... DTMF, Plecton, 2-Tone,  
 5-Tone, 1500, 2805, Custom 2-Tone

## System Diagram



## Accessories & Options

ITA2000A	Tone Remote Adapter	XAAB002A	Audio Accessory Box
XAC4000B	Programming Bundle Flash Drive	XDM004A	Desk Microphone
XAC0004A	Programming Cable	XFS002A	Dual PTT & Monitor Footswitch
XRC0001A	Relay Control Field Install Kit	XDM005A	Desktop Gooseneck Microphone
XAC0100A	Mounting Kit for Relay Kit	XHS003C / XCC004B / 25815-003:	Headset, Adapter Cable, and line cord
40419-008	Replacement Power Supply		

- Note: 1. An XAC0100A Mounting Kit must be procured with the XRC0001A Relay Control Kit  
 2. Use of the Relay Control Option may eliminate the need for a remote adapter. In this case, the controller can be connected directly to the radio, if desired (max. distance of 1,000 feet)  
 3. **Note: Models XHS003C, XFS002A, and XDM005A Require XAAB002A Audio Accessory Box.**

Call Customer Service (1-800-492-1212) For Application Assistance and Pricing. Specifications Subject To Change Without Notice.



Toll Free: 1 (800) 492-1212 Tel: (610) 777-1374  
 Fax: (610) 796-5954 www.gai-tronics.com



Quality Management System Certified by DNV-GL - ISO 9001:2008. The policy of GAI-Tronics is one of continuous improvement; therefore the company reserves the right to change specifications without notice.



Pub. 070301 Rev. 5/2015