

COMPACT CORD REELS

INDOOR MODEL

SPECIFICATIONS

Heavy gauge steel housing with white polyester baked-on finish, hardware for wall or ceiling mounting, positive ratchet lock and cord stop, designed for indoor use. 24 inch (610mm) pigtail, included. Plugs into standard outlet. Also available with bare wire.



CORD INCLUDED

CONVENIENT WALL OR CEILING MOUNTING

Compact cord reels on this page come with hardware for wall mounting (180° swing) or ceiling mounting (swivel).

NEW!




Model GLED-1840

Reel w/ LED light

Two four-watt, high output LEDs. Provides 5,000K-color bright white light lasting up to 50,000 hrs. Comes with one-watt LED flashlight at the end of the fixture. Covered ON/OFF switch.


NOTE: ETL listed. Not UL listed.



Model GL-1630

*Reel w/ Incandescent Lamp**


Metal Guard/Reflector, Convenience Receptacle in Handle (10 Amp, ground pin), Switch



Model GP-1630

Reel w/ Triple Receptacle on extendible cord, plug on pigtail.


10 Amp Rating



Model GF-1820 or GF-1840

Reel w/ Fluorescent Tube

Twin Lamp (13 watt), Switch



Model GN-1820

Reel w/ Bare cord ends for hard wiring or attachment of custom receptacles or lamps

NOTE: Not UL listed.

*Lamp included in box for user attachment.

Selection Chart for Reels shown on this page

FITTING INCLUDED	CORD TYPE (2)	*CORD LENGTH ft. (m)	MAX AMPS	PIGTAIL LENGTH in. (mm)	PIGTAIL PLUG	REEL DESIGN	REEL SIZE l x h x w in. (mm)	WEIGHT lbs. (kg)	MODEL NUMBER
Incandescent (1)	16/3 SJT	30 (9.0)	10	24 (610)	Yes	Compact	10 x 10 x 3 (254 x 254 x 76)	8.75 (3.9)	GL-1630
Triple Outlet	16/3 SJT	30 (9.0)	10	24 (610)	Yes	Compact	10 x 10 x 3 (254 x 254 x 76)	8.50 (3.8)	GP-1630
Fluorescent	18/2 SVT	20 (6.0)	-	24 (610)	Yes	Compact	7 x 7 x 2 (178 x 178 x 51)	5.50 (2.5)	GF-1820
Fluorescent	18/2 SJTOW-A	40 (12.0)	-	24 (610)	Yes	Compact	10 x 10 x 3 (254 x 254 x 76)	9.50 (4.3)	GF-1840
LED	18/2 SJTOW	40 (12.0)	.065	24 (610)	Yes	Compact	10 x 10 x 3 (254 x 254 x 76)	10.0 (4.5)	GLED-1840
None (4)	18/3 SVT	20 (6.0)	7	24 (610)	No	Compact	7 x 7 x 2 (178 x 178 x 51)	3.00 (1.4)	GN-1820

NOTES: (1) Convenience receptacle in handle. Incandescent bulb (75 watt max.) NOT included.

(2) Cord stop included.

(3) Single female receptacle on pigtail. Molded male plug on free cord. Not UL listed.

(4) Because cord ends are not terminated, these reels are not UL listed.