

HUBBELL INDUSTRIAL DUTY CORD REELS

Open Spool Cord reels with fluorescent or incandescent lamp, single or dual outlet or bare cord. Also available with bare cord end. All reels include automatic spring rewind, a multi-position four roller cord guide & a 48" pigtail with three prong plug. Ideal for a wide variety of industrial applications mounted from wall, ceiling or under work bench. Cord lengths from 25' to 70'. All reels include adjustable cord stop, spring rewind and ratchet lock. Operator simply pulls cord off spool. Ratchet lock maintains desired cable length and, when task is completed, a slight pull releases the ratchet allowing the spring motor to rewind the cord. Reels feature heavy steel frame with baked-on polyester finish. Fully gasketed steel Slip-ring housing. Both hand lamps include on-off switch. Fluorescent lamp features directed light, polycarbonate outer tube and integral ballast. Twenty amp duplex box includes ground fault circuit interrupter (GFCI). **Consult factory if installation height is greater than 16'.**



Reel with
FLUORESCENT or LED LAMP



Reel with
SINGLE OUTLET



Reel with
DUPLEX OUTLET BOX




Reel with
INCANDESCENT LAMP





MODEL LIST-CORD REELS

Accessory	Amps	CORD TYPE S/JOW-A/SJO			Weight lbs. (kg)	Model
		AWG	Cond	Length ft (m)		
Incandescent	15	16	3	25 (8)	23.3 (10.6)	GCA16325-HL
Incandescent	10	16	3	35 (11)	24.2 (11.0)	GCA16335-HL
Incandescent	10	16	3	50 (15)	25.6 (11.6)	GCA16350-HL
Incandescent	10	16	3	70 (21)	40.0 (18.2)	GCC16370-HL
Fluorescent	13 W	16	3	25 (8)	23.8 (10.8)	GCA16325-FL
Fluorescent	13 W	16	3	35 (11)	24.7 (11.2)	GCA16335-FL
Fluorescent	13 W	16	3	50 (15)	26.0 (11.8)	GCA16350-FL
Fluorescent	13 W	16	3	70 (21)	40.5 (18.4)	GCC16370-FL
LED	13 W	16	3	50 (15)	26.0 (11.8)	GCA16350-LED
LED	13 W	16	3	70 (21)	40.5 (18.4)	GCC16370-LED
Single Recept	10	16	3	25 (8)	22.8 (10.4)	GCA16325-SR
Single Recept	10	16	3	35 (11)	23.7 (10.8)	GCA16335-SR
Single Recept	10	16	3	50 (15)	25.0 (11.4)	GCA16350-SR
Single Recept	10	16	3	70 (21)	35.3 (16.1)	GCC16370-SR
Single Recept	15	14	3	25 (8)	24.5 (11.1)	GCA14325-SR
Single Recept	15	14	3	35 (11)	26.1 (11.8)	GCA14335-SR
Single Recept	15	14	3	50 (15)	28.5 (12.9)	GCA14350-SR
Single Recept	15	14	3	70 (21)	36.6 (16.6)	GCC14370-SR
Single Recept	20	12	3	25 (8)	23.7 (10.8)	GCA12325-SR
Single Recept	20	12	3	35 (11)	25.0 (11.4)	GCA12335-SR
Single Recept	20	12	3	45 (14)	26.9 (12.3)	GCA12345-SR
Single Recept	15	12	3	50 (15)	42.7 (19.4)	GCC12350-SR
Single Recept	15	12	3	70 (21)	47.6 (21.6)	GCC12370-SR
Dual Recept	20	12	3	25 (8)	23.4 (10.6)	GCA12325-DR
Dual Recept	20	12	3	35 (11)	24.7 (11.2)	GCA12335-DR
Dual Recept	20	12	3	45 (14)	26.0 (11.8)	GCA12345-DR
Dual Recept	15	12	3	50 (15)	44.2 (20.1)	GCC12350-DR
Dual Recept	15	12	3	70 (21)	49.1 (22.3)	GCC12370-DR
None	10	16	3	25 (8)	21.7 (9.9)	GCA16325-BC
None	10	16	3	35 (11)	22.4 (10.2)	GCA16335-BC
None	10	16	3	50 (15)	23.4 (10.6)	GCA16350-BC
None	10	16	3	70 (21)	34.8 (18.8)	GCC16370-BC
None	15	14	3	25 (8)	22.2 (10.1)	GCA14325-BC
None	15	14	3	35 (11)	23.1 (10.5)	GCA14335-BC
None	15	14	3	50 (15)	24.4 (11.1)	GCA14350-BC
None	15	14	3	70 (21)	36.2 (16.4)	GCC14370-BC
None	20	12	3	25 (8)	23.2 (10.6)	GCA12325-BC
None	20	12	3	35 (11)	24.5 (11.1)	GCA12335-BC
None	20	12	3	45 (14)	25.8 (11.7)	GCA12345-BC
None	15	12	3	50 (15)	42.2 (19.2)	GCC12350-BC
None	15	12	3	70 (21)	47.1 (21.4)	GCC12370-BC

CORD REEL DIMENSIONS—inches (mm)
Reel size "A" (third letter in model number)



CORD REEL DIMENSIONS—inches (mm)
Reel size "C" (third letter in model number)



Optional 340° Pivot Base
Model RC-PB-B (left, above)

Reel follows activity for smoother operation, reduced cord wear.

Optional Wall Mounted Pivot Base
Model RC-WP (right, above)

Provides 180° pivot.

NOTE: Either base fits all reel sizes.