

GROUNDING and BONDING CABLES

Antistatic Cables prevent sparks from static electricity generated by movement and flow of flammable liquids. **Bonding between containers during liquid transfer and connecting drums to an earth ground are required by Federal and local codes.** Various clamps and terminals allow a wide variety of uses. All cables are 7 x 19 stranded steel. Insulated cables have Safety Orange jacket.

- Available in several lengths, insulated or non-insulated
- Five types of end connectors available on all cables lengths and types
- For longer reach or "Y", connect several cables with 1/4" terminal ends
- Stranded cable for maximum flexibility and conductivity

Alligator Clip & C-Clamp

Model No.	Cable Description
GCSP-AC-03	3' Flexible Steel
GCSP-AC-05	5' Flexible Steel
GCSP-AC-10	10' Flexible Steel
GCSI-AC-03	3' Insulated Steel
GCSI-AC-05	5' Insulated Steel
GCSI-AC-10	10' Insulated Steel



Hand Clamp & Alligator Clip

Model No.	Cable Description
GCSP-AH-03	3' Flexible Steel
GCSP-AH-05	5' Flexible Steel
GCSP-AH-10	10' Flexible Steel
GCSI-AH-03	3' Insulated Steel
GCSI-AH-05	5' Insulated Steel
GCSI-AH-10	10' Insulated Steel



Hand Clamp & C-Clamp

Model No.	Cable Description
GCSP-HC-03	3' Flexible Steel
GCSP-HC-05	5' Flexible Steel
GCSP-HC-10	10' Flexible Steel
GCSI-HC-03	3' Insulated Steel
GCSI-HC-05	5' Insulated Steel
GCSI-HC-10	10' Insulated Steel



Two Hand Clamps

Model No.	Cable Description
GCSP-HH-03	3' Flexible Steel
GCSP-HH-05	5' Flexible Steel
GCSP-HH-10	10' Flexible Steel
GCSI-HH-03	3' Insulated Steel
GCSI-HH-05	5' Insulated Steel
GCSI-HH-10	10' Insulated Steel



Two Alligator Clips

Model No.	Cable Description
GCSP-AA-03	3' Flexible Steel
GCSP-AA-05	5' Flexible Steel
GCSP-AA-10	10' Flexible Steel
GCSI-AA-03	3' Insulated Steel
GCSI-AA-05	5' Insulated Steel
GCSI-AA-10	10' Insulated Steel



Hand Clamp & 1/4" Terminal

Model No.	Cable Description
GCSP-HE-03	3' Flexible Steel
GCSP-HE-05	5' Flexible Steel
GCSP-HE-10	10' Flexible Steel
GCSI-HE-03	3' Insulated Steel
GCSI-HE-05	5' Insulated Steel
GCSI-HE-10	10' Insulated Steel



Two 1/4" Terminals

Model No.	Cable Description
GCSP-EE03	3' Flexible Steel
GCSP-EE-05	5' Flexible Steel
GCSP-EE-10	10' Flexible Steel
GCSI-EE-03	3' Insulated Steel
GCSI-EE-05	5' Insulated Steel
GCSI-EE-10	10' Insulated Steel



Individual Connectors & Accessories



Ground Clamp -- .5"-1.0"
Model No. GC-CL

UL & CSA Listed, RoHS Compliant



C-Clamp
Model No. GC-CEE



100 Amp Alligator Clip
Model No. GC-ALG

FEDERAL SPEC: CID AA59466-010



Hand Clamp
Model No. GC-PLR



Aircraft Clamp
Model No. AGC-MOD

MIL-SPEC: M83413/7-1



Round Grounding Plug
Model No. AGP-01

MIL-SPEC: M83413/4-1



STUDBUG™ Grounding Stud
Model No. SDS-STD

Bulk Wire Rope - Galvanized

Model No.	Cable Description
GCB-NY-050	50' 1/8" OD Clear
GCB-NY-075	75' 1/8" OD Clear
GCB-NY-100	100' 1/8" OD Clear
GCB-PL-050	50' 3/32" OD Plain
GCB-PL-075	75' 3/32" OD Plain
GCB-PL-100	100' 3/32" OD Plain

Bulk Wire Rope - Stainless Steel

Model No.	Cable Description
GCB-OR-050	50' 1/8" OD Orange
GCB-OR-075	75' 1/8" OD Orange
GCB-OR-100	100' 1/8" OD Orange
GCB-YL-050	50' 5/32" OD Yellow
GCB-YL-075	75' 5/32" OD Yellow
GCB-YL-100	100' 5/32" OD Yellow

STATIC DISCHARGE REELS

Ideal for a wide variety of grounding applications. Available with your choice of cable length and connector, Open Spool Reels include spring rewind, centrifugal brake and ratchet lock (permanent ratchet lock, no on/off switch). **Cable is 7 x 7 stranded stainless steel with yellow polyester elastomer cover, 5/32" OD. Reel has safety orange baked polyester finish.

Heavy-duty Open Spool Series 'OSD'

- Open Spool Design
- Cable Lengths to 100 Ft.
- Spring Rewind with Centrifugal Brake
- Rugged Steel Construction
- Choice of Grounding Clamps and Plugs



Static Discharge Reel with **HAND CLAMP**




Static Discharge Reel with 100 amp **ALLIGATOR CLIP**



Static Discharge Reel with ***ROUND GROUNDING PLUG**
*MIL-SPEC: M83413/4-1

Unpainted surfaces on mounting plate used for grounding.



Series "OSD"

**Includes Cable Installed on Reel

Cable Length	Connector	Model Number
50'	Hand Clamp	OSD050-SS-YL-SG-C1
50'	Aircraft Clamp	OSD050-SS-YL-SG-C2
50'	Alligator Clip	OSD050-SS-YL-SG-AL
50'	Round Grounding Plug	OSD050-SS-YL-SG-P1
75'	Hand Clamp	OSD075-SS-YL-SG-C1
75'	Aircraft Clamp	OSD075-SS-YL-SG-C2
75'	Alligator Clip	OSD075-SS-YL-SG-AL
75'	Round Grounding Plug	OSD075-SS-YL-SG-P1
100'	Hand Clamp	OSD100-SS-YL-SG-C1
100'	Aircraft Clamp	OSD100-SS-YL-SG-C2
100'	Alligator Clip	OSD100-SS-YL-SG-AL
100'	Round Grounding Plug	OSD100-SS-YL-SG-P1


**Meets Federal Grounding Spec: RR-W-410.

STATIC DISCHARGE REELS

Ideal for a wide variety of grounding applications. Reel has enclosed spool and safety orange baked polyester finish. See table for various cable and connector options.

Enclosed Spool Series 'SD'

- Automatic **E-Z PULL™** Rewinding
- Rugged Steel Construction
- Compact Enclosed Design
- Positive Ratchet Lock with On/Off Switch
- Steel Cable Installed
- Safety Orange Polyester Baked-On Finish



Series 'SD'

Includes Cable Installed on Reel

Model No.	Cable Length ft.	Cable Material	Cable Cover	End Options
SD-2030 ¹	30	Galvanized	none	Alligator Clip
SD-2030-C1	30	Galvanized	none	Hand Clamp
SD-2030-C2	30	Galvanized	none	Aircraft Clamp
SD-2030-P1	30	Galvanized	none	Aircraft Plug, Rnd
SD-2050 ¹	50	Galvanized	none	Alligator Clip
SD-2050-C1	50	Galvanized	none	Hand Clamp
SD-2050-C2	50	Galvanized	none	Aircraft Clamp
SD-2050-P1	50	Galvanized	none	Aircraft Plug, Rnd
SD-2050-OS ³	50	Stainless	Orange	Alligator Clip
SD-2050-OS-C1 ³	50	Stainless	Orange	Hand Clamp
SD-2050-OS-C2 ³	50	Stainless	Orange	Aircraft Clamp
SD-2050-OS-P1 ³	50	Stainless	Orange	Aircraft Plug, Rnd
SD-2050N ²	50	Galvanized	Clear	Alligator Clip
SD-2050N-C1	50	Galvanized	Clear	Hand Clamp
SD-2050N-C2	50	Galvanized	Clear	Aircraft Clamp
SD-2050N-P1	50	Galvanized	Clear	Aircraft Plug, Rnd
SD-2050Y ¹	50+	Galvanized	none	Alligator Clip
SD-2050-YL-AL	50	Stainless	Yellow	Alligator Clip
SD-2050-YL-C1	50	Stainless	Yellow	Hand Clamp
SD-2050-YL-C2	50	Stainless	Yellow	Aircraft Clamp
SD-2050-YL-P1	50	Stainless	Yellow	Aircraft Plug, Rnd

End Options:

Aircraft Plug, Round



Aircraft Clamp



Hand Clamp



Alligator Clip



¹ Static discharge reels are supplied complete with 3/32" OD steel aircraft cable. The electrical resistance between the end effector and the mounting surface shall not exceed 10-Ohms.

² Nylon covered cable (1/8" OD) is an optional extra. The electrical resistance between the end effector and the mounting surface shall not exceed 10-Ohms.

³ Stainless Steel cable covered with Orange or Yellow Nylon jacket to 1/8" OD. The electrical resistance between the end effector and the mounting surface shall not exceed 10-Ohms.

Unpainted surfaces on mounting plate used for grounding.