

	Rating Color Coded by Voltage	15 Ampere		20 Ampere		30 Ampere	
		Receptacle / Conn. Body	Plug / Inlet	Receptacle / Conn. Body	Plug / Inlet	Receptacle / Conn. Body	Plug / Inlet
2 Pole / 2 Wire	125V	L1 B-11 L1-15R	B-11 L1-15P				
	250V	L2		B-19 L2-20R	B-19 L2-20P		
2 Pole / 3 Wire Grounding	125V	L5 B-13 C-7 AA-34 L5-15R	B-12 C-7 AA-34 L5-15P	B-21 C-7 AA-36 L5-20R	B-20 C-7 AA-36 L5-20P	B-29 C-8 L5-30R	B-28 C-8 L5-30P
	250V	L6 B-13 C-7 L6-15R	B-12 C-7 L6-15P	B-21 C-7 L6-20R	B-20 C-7 L6-20P	B-29 C-8 L6-30R	B-28 C-8 L6-30P
	277V AC	L7 B-13 C-7 L7-15R	B-12 C-7 L7-15P	B-21 C-7 L7-20R	B-20 C-7 L7-20P	B-29 C-8 L7-30R	B-28 C-8 L7-30P
	480V AC	L8		B-24 L8-20R	B-24 L8-20P	B-37 L8-30R	B-37 L8-30P
	600V AC	L9		B-24 L9-20R	B-24 L9-20P	B-37 L9-30R	B-37 L9-30P
3 Pole / 3 Wire	125/250V AC	L10		B-24 L10-20R	B-24 L10-20P	B-31 L10-30R	B-30 L10-30P
	125/250V AC	L14		B-23 C-8 L14-20R	B-22 C-8 L14-20P	B-31 C-9 L14-30R	B-30 C-9 L14-30P
	3Ø 250V AC	L15		B-23 C-8 L15-20R	B-22 C-8 L15-20P	B-31 C-9 L15-30R	B-30 C-9 L15-30P
	3Ø 480V AC	L16		B-23 C-8 L16-20R	B-22 C-8 L16-20P	B-33 C-9 L16-30R	B-32 C-9 L16-30P
	3Ø 600V AC	L17				B-33 C-9 L17-30R	B-32 C-9 L17-30P
	3ØY 120/208V AC	L18		B-25 L18-20R	B-25 L18-20P	B-36 C-9 L18-30R	B-36 C-9 L18-30P
	3ØY 277/480V AC	L19		B-25 L19-20R	B-25 L19-20P	B-36 L19-30R	B-36 L19-30P
4 Pole / 4 Wire	3ØY 347/600V AC	L20		B-25 L20-20R	B-25 L20-20P	B-36 L20-30R	B-36 L20-30P
	3ØY 120/208V AC	L21		B-27 L21-20R	B-26 L21-20P	B-35 L21-30R	B-34 L21-30P
	3ØY 277/480V AC	L22		B-27 L22-20R	B-26 L22-20P	B-35 L22-30R	B-34 L22-30P
	3ØY 347/600V AC	L23		B-27 L23-20R	B-26 L23-20P	B-35 L23-30R	B-34 L23-30P
	347V AC	L24		B-24 L24-20R	B-24 L24-20P		
2P / 3W	240V AC	L25				B-37 L25-30R	B-37 L25-30P
	3ØY 240/415V AC	L26				B-35 L26-30R	B-34 L26-30P

MIDGET TWIST-LOCK® DEVICES		
Rating	Receptacle	Plug
2P / 2W 15A 125V	B-7 ML-1R	B-6 ML-1P
2P / 3W Gr 15A 125V	B-7 ML-2R	B-6 ML-2P
3P / 3W 15A 125/250V AC	B-7 ML-3R	B-6 ML-3P

50A TWIST-LOCK® DEVICES			
Rating	Receptacle	Plug	
2 Pole / 3 Wire Grounding	50A 125V Corrosion Resistant ANSI C73-110 / NEMA SS1-50 Marine Products	AA-14 AA-15 AA-15	AA-14 AA-15 AA-15
	50A 125V	B-56 	B-56
	50A 250V	B-56 	B-56
	50A 480V AC	B-56 	B-56
	50A 125/250V Corrosion Resistant ANSI C73-111 / NEMA SS2-50 Marine Products	AA-16 AA-17 AA-17	AA-16 AA-17 AA-17
3 Pole / 4 Wire Grounding	50A 125/250V AC	B-57 	B-57
	50A 3Ø 250V AC	B-57 	B-57
	50A 3Ø 480V AC	B-57 	B-57
		B-57 	B-57

NON-NEMA TWIST-LOCK® DEVICES			
Rating	Receptacle	Plug	
3 Pole / 3 Wire	20A 125/250V	B-45 C-8 C-8	B-44 C-8 C-8
	30A 125/250V	B-48 C-9 C-9	B-47 C-9 C-9
4 Pole / 4 Wire	20A 3ØY 120/208V AC	B-45 	B-44
	30A 3ØY 120/208V AC	B-48 C-9 C-9	B-47 C-9 C-9
4P/5W Gr	20A 250V 10A 600V AC	B-46 	B-46