

PRODUCT SOLUTIONS FOR ELECTRICAL PREFABRICATION

SAVE TIME, MATERIAL, AND MONEY

YOUR ONE SOURCE FOR ELECTRICAL PREFAB SOLUTIONS

The commercial construction industry is moving to pre-fabrication or “prefab.” Electrical contractors are setting up their own prefab shops to pre-assemble electrical components before sending them to jobsites. No further prep needed on site. It’s an opportunity to save time, materials, and money.

Assembling components under controlled conditions helps you ensure quality control. Shipping assemblies to the jobsite reduces labor costs for both rough-in and trim-out stages of a project.

SINGLE SOURCE SOLUTION

It’s easy to start. You need a workbench and basic tools in the shop, along with components shipped direct to you. Hubbell Wiring-Device Kellems now provides you one source electrical prefab components. This not only streamlines the process for you, it also eliminates errors when ordering:

- Electrical boxes
- Devices (receptacles and switches)
- Mounting brackets
- Cable management
- Mud rings

BENEFIT WITH HUBBELL PREFAB PRODUCTS

- Lower material and jobsite labor costs
- Pre-wiring devices off-site maintains quality control
- Finish the rough-in phase of the job faster
- Hubbell SNAPConnect® devices reduce trim-out time
- Minimizes jobsite packaging waste and scrap, clean up time, and theft

Additionally, our prefab line includes innovative products that save even more time in the shop or on the jobsite. Discover them on the following pages.



TABLE OF CONTENTS

4 ¹ / ₁₆ " SQUARE BOXES	4	GANGABLE AV WALLBOXES	8
4" SQUARE BOXES	5	LARGE CAPACITY WALLBOXES	9
4" & 4 ¹ / ₁₆ " BOX ACCESSORIES	6	SNAPCONNECT® DEVICES & ACCESSORIES	10
GRAND SLAM JUNCTION BOXES	7		

Hubbell's prefab components save time with unique installation efficiency features. Increase productivity during assembly in the shop and during installation on the jobsite. Perfect for construction projects that require repetitive wiring installs.

Choose from a variety of the 4¹/₁₆" and 4" square boxes for a wide variety of applications. Integrated STAB-iT® connectors for terminating MC cable reduce installation cost. Grand Slam boxes offer a clean solution for home run circuits. Adjustable, hinged and stud-mount mud rings provide installation versatility. Finally, inventory our SNAPConnect® device line to speed up trim out with standard or controlled duplex, StyleLine Decorator, USB, or GFCI receptacles.



STAB-IT CONNECTORS

- Install **3 TIMES FASTER**
- Designed for quick installation of MC, AC, and HCF Cable
- 14/2 to 10/3 for most cable types
- UL listed for use without a plastic anti-short bushing (except for AC Cable)



BOXES

- Available with built-in cable clamps
- With built-in box mounting brackets for steel or wood stud mounting
- Some boxes include far-side support
- Boxes include ground wires



ADJUSTABLE MUD RINGS

- Adjustable post installation
- 1 and 2 Gang with 1/2" to 1-3/4" Adjustability
- Ring adjusting screws are covered, protecting wires within the box



HINGED MUD RINGS

- Hinged mud rings for easy wiring access
- Available for 4" Square Boxes in 1 and 2-Gangs
- 5/8" Depth
- Can be used with Box Mounting Brackets



STUD MOUNT MUD RINGS

- Available for 4-11/16" and 4" Square Boxes
- For use with power or low voltage
- 1 and 2 Gangs



GRAND SLAM BOXES

- Easy homerun wiring
- Includes STAB-IT Connectors
- Includes raised grounding bars
- With or without concentric knock-outs



SNAPCONNECT CONNECTORS

- Rough-in right angle pig tail connectors
- Ships in protective packaging
- Clear terminal housing for easy inspection of contacts
- Connector allows for safe circuit testing



SNAPCONNECT RECEPTACLES

- No terminal screws means no terminal screw torque requirements
- Save one minute per device
- One connector fits the whole SNAPConnect receptacle product line

4¹/₁₆" SQUARE BOXES



Featuring STAB-IT® connectors

Integrated into the box, our exclusive connectors are field proven to terminate MC cable up to 3 times faster than traditional cable clamps. It's easy: remove the pry-out, prep the cable, insert cable, done! These welded large boxes provide more room for wiring and include connectors for three or six cables, plus a knockout on the same side as the connectors. Available mounting brackets and cable management offer the first means of support.

- 3-cable STAB-IT connectors install 3 times faster than traditional connectors
- Designed for quick installation of flex, MC, MCI, MCI-A, MC-PCS, AC, and HCF Cable
- HBL252MSCM & HBL252MS include far-side support on back
- Includes ground wires, box mounting brackets and cable clamps
- Easier installation for labor savings



Boxes

Boxes are 4¹/₁₆" square, 2¹/₈" deep. They are constructed with welded steel and have raised grounds. The boxes have 42 in.³ capacity.

Box Description	Side Knock Outs		Back Knock Outs		Catalog Number
	TKO	Cable Pry-outs	Concentric	TKO	
Standard	(12) 1/2"-3/4"		(1) 1/2"	(3) 1/2"-3/4"	HBL257*
(1) STAB-IT Connector and 8" Solid #12 Ground Pigtail	(10) 1/2"-3/4"	3	(1) 1/2"	(1) 1/2"-3/4"	HBL252S
(1) STAB-IT Connector, 8" Solid #12 Ground Pigtail and (1) Cable Management Clamp	(10) 1/2"-3/4"	3	(1) 1/2"	(1) 1/2"-3/4"	HBL252SCM
(1) STAB-IT Connector, 8" Solid #12 Ground Pigtail and (1) Mounting Bracket	(10) 1/2"-3/4"	3	(1) 1/2"	(1) 1/2"-3/4"	HBL252MS
(1) STAB-IT Connector, 8" Solid #12 Ground Pigtail, (2) Mounting Brackets and (1) Cable Management Clamp	(10) 1/2"-3/4" (1) 3/4"-1"	3	(1) 1/2"	(1) 1/2"-3/4"	HBL252MSCM
(2) STAB-IT Connectors and 8" Solid #12 Ground Pigtail	(8) 1/2"-3/4"	6	(1) 1/2"		HBL254S
(2) STAB-IT Connectors, 8" Solid #12 Ground Pigtail, and (2) Cable Management Clamps	(8) 1/2"-3/4"	6	(1) 1/2"		HBL254SCM

*UL Listed Only




4" SQUARE BOXES



Regular or STAB-IT® boxes

These popular boxes are available with our unique connectors built into the box. Terminate MC cable in one third the time of other clamps. Models are available with connectors for two or four cables. Available mounting brackets and cable management offer the first means of support.

- 2-cable STAB-IT connectors install 3 times faster than traditional connectors
- Designed for quick installation of flex, MC, MCI, MCI-A, MC-PCS, AC, and HCF Cable
- HBL232MSCM & HBL232MS includes far-side support on back
- Includes ground wires, box mounting brackets and cable clamps
- Easier installation for labor savings



Boxes

Boxes are 4" square, 2-1/8" deep. They are constructed with welded steel and have raised grounds. The boxes have 30.3 in.³ capacity.

Box Description	Side Knock Outs			Back Knock Outs		
	Concentric	TKO	Cable Pry-outs	Concentric	TKO	Catalog Number
Standard	(8) 1/2"	(4) 1/2"-3/4"		(2) 1/2"	(2) 1/2"-3/4"	HBL232
10" Solid #12 Ground Pigtail	(8) 1/2"	(4) 1/2"-3/4"		(2) 1/2"	(2) 1/2"-3/4"	HBL232SM
(1) STAB-IT Connector, 8" Solid #12 Ground Pigtail	(6) 1/2"	(3) 1/2"-3/4"	2	(1) 1/2"	(1) 1/2"-3/4"	HBL232S
(1) STAB-IT Connector, 8" Solid #12 Ground Pigtail, Back- Far Side Support, and (2) Mounting Brackets	(6) 1/2"	(3) 1/2"-3/4"	2	(1) 1/2"	(1) 1/2"-3/4"	HBL232MS
(1) STAB-IT Connector, 8" Solid #12 Ground Pigtail, and (1) Cable Management Clamp	(6) 1/2"	(3) 1/2"-3/4"	2	(1) 1/2"	(1) 1/2"-3/4"	HBL232SCM
(1) STAB-IT Connector, 8" Solid #12 Ground Pigtail, Back- Far Side Support, (1) Cable Management Clamp, and (2) Mounting Brackets	(6) 1/2"	(3) 1/2"-3/4"	2	(1) 1/2"	(1) 1/2"-3/4"	HBL232MSCM
(2) STAB-IT Connectors, 8" Solid #12 Ground Pigtail, Back- Far Side Support, (2) Cable Management Clamp, and (2) Mounting Brackets	(6) 1/2"	(3) 1/2"-3/4"	4	(1) 1/2"	(1) 1/2"-3/4"	HBL244MSCM
(2) STAB-IT Connectors, 8" Solid #12 Ground Pigtail	(4) 1/2"	(2) 1/2"-3/4"	4	(1) 1/2"		HBL248S



Boxes

Boxes are 4" square, 1 1/2" deep, and have 21 in.³ capacity. Use with standard cable connectors.

Box Description	Side Knock Outs		Back Knock Outs		Catalog Number
	Concentric	TKO	Concentric	TKO	
Welded Steel, Raised Ground, 8" Solid #12 Ground Pigtail	(8) 1/2"	(4) 1/2"-3/4"	(2) 1/2"	(2) 1/2"-3/4"	HBL189F
Welded Steel, Raised Ground, 10" Solid #12 Ground Pigtail	(8) 1/2"	(4) 1/2"-3/4"	(2) 1/2"	(2) 1/2"-3/4"	HBL189SM*
Welded Steel, Long Side Mounting Brackets	(8) 1/2"	(4) 1/2"-3/4"	(3) 1/2"	(2) 1/2"-3/4"	HBL196
Welded Steel, Raised Ground, 10" Solid #12 Ground Pigtail	(8) 1/2", (4) 3/4"		(2) 1/2", (2) 3/4"		HBL232SCM

*cULus



4" & 4¹/₁₆" BOX ACCESSORIES

Mud rings, covers, supports

Steel adjustable mud rings provide flexibility after installation to match the drywall depth. Hinged mud rings allow devices to be installed during pre-assembly, then swing out of the way for final wiring on site. Protector plates can be attached during prefab to protect devices during drywall install, then removed during trim out.

- 1 & 2-Gang adjustable mud rings
- Standard 1 & 2-gang mud rings
- Adjustable open box mounting brackets
- Floor mounted box support includes fold back stabilizer prevents bracket from being pushed back in wall cavity during drywall installation



Mud Rings

For use with	Type	Raised Height	Capacity (In. ³)	Listing	Catalog Number	
4 ¹ / ₁₆ " boxes	1-Gang, Adjustable	½" to 1⅜"	4 to 9.5	UL Listed	HBL868AMR HBL869AMR	
	2-Gang, Adjustable		8 to 15.5			
	1-Gang	⅝"	4.5	cULus	HBL843 HBL842	
		1¼"	9.5			
	4" boxes	2-Gang	½"	5.5	cULus	HBL841 HBL818 HBL840 HBL819 HBL820
			⅝"	7.3		
¾"		8.8				
1"		12.0				
1¼"		15.0				
1-Gang, Adjustable		½" to 1⅜"	4 to 9.5	UL Listed		
2-Gang, Adjustable	8 to 15.5					
4" boxes	1-Gang	⅝"	4.5	UL Listed	HBL768	
	1-Gang, Stud Mount	⅝"	4.5	UL Listed	HBL768B	
	1-Gang, Hinged	⅝"	5.5	UL Listed	HBL768H	
	1-Gang	1¼"	9.5	cULus	HBL775	
	2-Gang	⅝"	7.3	cULus	HBL769	
	2-Gang, Stud Mount	⅝"	7.3	UL Listed	HBL769B	
	2-Gang, Hinged	⅝"	8.3	UL Listed	HBL769H	
	2-Gang	1¼"	15	cULus	HBL781	



Square Metallic Covers for Exposed Work

For use with	1 Decorator	1 Duplex	2 Decorator	2 Duplex	1 Duplex, 1 Decorator
4" boxes, UL Listed	HBL808C	HBL902C	HBL809C	HBL907C	HBL915C

Metallic Box Brackets and Supports

For use with	Type	Box Mounting	Catalog Number
4 ¹ / ₁₆ " and 4" boxes, cULus	Open Wall Adjustable Box Bracket	16" to 24"	HBL9020R
	Floor Mounted Box Support	12" 18"	HBL9009 HBL9010

Plates

Description	For use with	Height	1-Gang	2-Gang
Reusable metallic mud ring cable protector plate	4 ¹ / ₁₆ " and 4" boxes	Flush ¾"	HBL701F HBL701R	HBL702F HBL702R
Metallic flush-fit devices levelling plate	4 ¹ / ₁₆ " and 4" boxes	-	HBL999	-

GRAND SLAM JUNCTION BOXES



Large capacity home run boxes

Terminate home runs in commercial applications with the Grand Slam box. It offers both flexibility and space. Features built-in STAB-iT® connectors for jobsite labor savings as well as included ground bar.

- With STAB-IT® clamps, has been tested at over 3X faster than traditional connectors
- Surface mount cover and ground bar included
- Two raised grounds for installation flexibility
- Available with concentric knockouts on side and back
- UL Listed



Grand Slam Junction Boxes


Box, surface covers and ground bar included.

Dimensions	Concentric Knock Outs	STAB-IT Clamps	Capacity (In. ³)	Catalog Number
8" X 8" X 3"	(12) 1/2" & 3/4" (5) 3/4" & 1"	(4) 14/2 to 10/3 Up to 8 Cables	179	HBLSC080803STRC
8" X 8" X 3"	NA	(4) 14/2 to 10/3 Up to 8 Cables	179	HBLSC080803NKSTRC
12" X 12" X 4"	(12) 1/2" & 3/4" (9) 3/4" & 1" (8) 1" & 1 1/4"	(6) 14/2 to 10/3 Up to 12 Cables	546	HBLSC121204STRC
12" X 12" X 4"	NA	(6) 14/2 to 10/3 Up to 12 Cables	546	HBLSC121204NKSTRC



Grand Slam Junction Box Accessories

Description	For Use With	Dimensions	Catalog Number
Flush Style Cover	8" X 8" Boxes 12" X 12" Boxes	10" x 10" 14" x 14"	HBLSCF0808RC HBLSCF1212RC
STAB-IT® Connector (accepts 2 cables)	All Grand Slam boxes	1.032" x 1.75" x 0.983"	HBL989ST



AV WALL BOXES



Gangable boxes

Deliver data, AV, and power side-by-side with these oversized in-wall boxes. Designed to install independently or ganged together for multiple devices. Perfect for Cat6 and 6A fiber optic cables that require a larger bend radius.

- 4" depth accepts any device
- Knockouts from 1/2" up to 2"
- Accepts low voltage partition
- NEMA spaced device mounting, accepts industry standard wallplates
- Adjustable stud mounting brackets and far side support
- Suitable for masonry application



Gangable AV Wall Boxes

Box Description	Knockouts			Catalog Number
	Top	Bottom	Back	
2-Gang, 2 in. KO, 54 in ³ capacity, 4.21" X 4.06" X 4"	(2) 1/2" (2) 1/2" - 3/4" TKO	(1) 1", 1 1/4", 1 1/2", 2"	(2) 1/2"-3/4"	HBL985
3-Gang, 2 in. KO, 79 in ³ capacity, 4.21" X 5.87" X 4"	(3) 1/2" (3) 1/2" - 3/4" TKO	(1) 1/2" (1) 1/2" - 3/4" TKO (1) 1", 1 1/4", 1 1/2", 2"	(3) 1/2"-3/4"	HBL986
4-Gang, 2 in. KO, 104 in ³ capacity, 4.21" X 7.69" X 4"	(4) 1/2" (4) 1/2" - 3/4" TKO	(1) 1/2" (1) 1/2" - 3/4" TKO (2) 1", 1 1/4", 1 1/2", 2"	(4) 1/2"-3/4"	HBL987
6-Gang, 2 in. KO, 154 in ³ capacity, 4.21" X 11.31" X 4"	(6) 1/2" (6) 1/2" - 3/4" TKO	(1) 1/2" (1) 1/2" - 3/4" TKO (2) 1", 1 1/4", 1 1/2", 2"	(6) 1/2"-3/4"	HBL988



Low Voltage AV Wallbox Partition

For use with	Type	Catalog Number
HBL985, HBL986, HBL987 and HBL988	Solid divider With pass-thru capability	HBL989 HBL989AVD



LARGE CAPACITY WALL BOXES



One, two or three gang boxes

Oversized two or three gang boxes and mud rings are perfect for AV, data and power applications. Extra-large knockouts for pulling pre-terminated cables.

- Designed to deliver power and low voltage in the same box
- Use standard mud rings and wallplates
- Two inch knockout feed-thru
- 3 ¼ Inch depth accommodates large cables and bend radii



2-Gang Large Capacity Wall Boxes

Boxes are 4 1/16" square, 3 1/4" deep. The boxes have 66.7 in.³ capacity. Use with industry standard 4 1/16" square mud rings for 1- or 2-gang applications

Box Description	Side Knock Outs		Back Knock Outs	Catalog Number
	Concentric	TKO	TKO	
Standard	(2) 1"-2"	(2) 3/4"-1" (2) 1"-1 1/4"	(2) 3/4"-1" (2) 1 1/2"	HBL260
With mounting brackets	(2) 1"-2"	(2) 3/4"-1" (2) 1"-1 1/4"	(2) 3/4"-1" (2) 1 1/2"	HBL260H



3-Gang Large Capacity Wall Box

Boxes are 4 1/16"H, 7 3/4"W, 3 1/4" deep. The boxes have 113.3 in.³ capacity. Use with industry standard 4" square mud rings for 1- or 2-gang applications

Box Description	Side Knock Outs		Back Knock Outs	Catalog Number
	Concentric	TKO	TKO	
Square 2- or 3-gang wall box	(2) 1"-2"	(4) 1/2"-3/4" (4) 3/4"-1" (2) 1"-1 1/4"	(2) 1/2"-3/4" (2) 3/4"-1" (2) 1"-1 1/4"	HBL263



Mud Rings

Description	For use with	Height	Capacity (In. ³)	Catalog Number
2-gang mud rings	HBL260	5/8"	7.3	HBL818
		3/4"	8.8	HBL840
		1"	12.0	HBL819
		1 1/4"	15.0	HBL820
3-gang mud rings	HBL263	1/2"	10.1	HBL792
		5/8"	12.3	HBL793
		1 1/4"	24.3	HBL794



Low Voltage Partition

For use with	Mud Ring Depth	Type	Catalog Number
HBL260 and HBL263	1/2", 3/4" and 1 1/4"	Solid divider With pass-thru capability	HBL981 HBL981AVD



SNAPCONNECT® DEVICES & ACCESSORIES



Modular wiring system

Our labor-saving receptacles and switches save up to 5 minutes per device. Perfect for prefab applications. The SNAPConnect terminal can be part of the pre-assembly. The device can be snapped in during pre-assembly or during trim out. Secure and fast, these products eliminate exposed live terminals.

- **Modular wiring system eliminates screw terminals and NEC® torque requirements, speeding installation and trim-out**
- **Clear polycarbonate terminal connector housing to inspect contacts**
- **Receptacles available in standard, tamper-resistant and power indicating LED versions**
- **Abuse resistant nylon for extra heavy use applications**
- **Stainless steel autoground**
- **Simplifies device change out for end users**



SNAPConnect® Right Angle Pigtailed Connectors for Receptacles

Description	Solid	Stranded
6 inch wire connector	SNAP1RNA	SNAP2RNA
6 inch wire with push-wire terminals	SNAP1RNAM2	SNAP2RNAM2



Hospital Grade SNAPConnect® Extra Heavy Duty Duplex Receptacles

Description	Style	Color	15A 125A	20A 125V
Standard	Duplex StyleLine Decorator	White	SNAP8200WNA SNAP2172WNA	SNAP8300WNA SNAP2182WNA
Standard with Finder Groove	Duplex	White	SNAP8200WA	SNAP8300WA
Tamper-Resistant	Duplex StyleLine Decorator	White	SNAP8200WTRA SNAP2172WTRA	SNAP8300WTRA SNAP2182WTRA
Tamper-Resistant with Split Circuit	Duplex StyleLine Decorator	White	SNAP8200WSCTRA SNAP2172WSCTRA	SNAP8300WSCTRA SNAP2182WSCTRA
Standard with Power Indicating (LED)	Duplex StyleLine Decorator	White	SNAP8200WL SNAP2172WL	SNAP8300WL SNAP2182WL
Tamper-Resistant with Power Indicating (LED)	Duplex StyleLine Decorator	White	SNAP8200WLTRA SNAP2172WLTRA	SNAP8300WLTRA SNAP2182WLTRA



Specification Grade SNAPConnect® Extra Heavy Duty Duplex Receptacles

Description	Style	Color	15A 125A	20A 125V
Standard	Duplex StyleLine Decorator	White	SNAP5262WNA SNAP2152WNA	SNAP5362WNA SNAP2162WNA
Standard with Finder Groove	Duplex	White	SNAP5262WA	SNAP5362WA
Tamper-Resistant	Duplex StyleLine Decorator	White	SNAP5262WTRA SNAP2152WTRA	SNAP5362WTRA SNAP2162WTRA
Tamper-Resistant with Split Circuit	Duplex StyleLine Decorator	White	SNAP5262WSCTRA SNAP2152WSCTRA	SNAP5362WSCTRA SNAP2162WSCTRA
Standard with Power Indicating (LED)	Duplex StyleLine Decorator	White	SNAP5262WL SNAP2152WL	SNAP5362WL SNAP2162WL
Tamper-Resistant with Power Indicating (LED)	Duplex StyleLine Decorator	White	SNAP5262WLTRA SNAP2152WLTRA	SNAP5362WLTRA SNAP2162WLTRA





SNAPConnect® Permanently Marked Controlled Duplex Receptacles

Description	Color	Standard		Tamper-Resistant	
		15A 125V	20A 125V	15A 125V	20A 125V
Duplex One Face Controlled Split Circuit Snap	White	SNAP5262C1W	SNAP5362C1W	SNAP5262C1WTRA	SNAP5362C1WTRA
Duplex Both faces Controlled	White	SNAP5262C2W	SNAP5362C2W	SNAP5262C2WTRA	SNAP5362C2WTRA
StyleLine Decorator One Face Controlled Split Circuit	White	SNAP2152C1W	SNAP2162C1W	SNAP2152C1WTRA	SNAP2162C1WTRA
StyleLine Decorator Both faces Controlled	White	SNAP2152C2W	SNAP2162C2W	SNAP2152C2WTRA	SNAP2162C2WTRA



SNAPConnect® Protection Receptacles

Description	Color	Hospital Grade		Specification Grade	
		15A 125V	20A 125V	15A 125V	20A 125V
Heavy Duty Commercial Ground Fault	White	GFRST82SNAPW	GFRST83SNAPW	GFRST15SNAPW	GFRST20SNAPW
Heavy Duty Commercial Ground Fault Tamper-Resistant Weather-Resistant	White	GFTWRST82SNAPW	GFTWRST83SNAPW	GFTWRST15SNAPW	GFTWRST20SNAPW
Surge Protection Tamper resistant with Power Indicating (LED)	White	SNAP8262WS	SNAP8362WS	SNAP5262WA	SNAP5362WS
USB Charger Duplex, one USB Type A and one Type-C port, 3 Amp up to 9 Volt USB output	White	SNAP8200UACW	SNAP8300UACW	SNAP15UACW	SNAP20UACW



SNAPConnect® Right Angle Pigtailed Connectors for Switches

Description		Solid	Stranded
		single pole single pole, with push-in terminals	SNAPSP1NA SNAPSP1NAM2
6 inch wire connector for use with	single pole pilot light single pole pilot light, with push-wire terminals	SNAPSP1NA SNAPSP1NAM2	SNAPSP2NA SNAPSP2NAM2
	3-way pilot light 3-way pilot light, with push-wire terminals	SNAP3W1NA SNAP3W1NAM2	SNAP3W2NA SNAP3W2NAM2



SNAPConnect® White Specification Grade Switches

Description	Style	15A, 120-277V AC		20A, 120-277V AC	
		Single Pole	Three Way	Single Pole	Three Way
Standard	Toggle Decorator	SNAP1201WNA SNAP2101WNA	SNAP1203WNA SNAP2103WNA	SNAP1221WNA SNAP2121WNA	SNAP1223WNA SNAP2123WNA
Illuminated blue LED, light ON with load OFF	Toggle Decorator	SNAP1201ILWNA SNAP2101ILWNA	SNAP1203ILWNA SNAP2103ILWNA	SNAP1221ILWNA SNAP2121ILWNA	SNAP1223ILWNA SNAP2123ILWNA
Pilot red LED, light ON with load OFF	Toggle Decorator	SNAP1201PLWNA SNAP2101PLWNA	—	SNAP1221PLWNA SNAP2121PLWNA	—



SNAPConnect® Testers

Description	Catalog Number
Circuit Tester for SNAPConnect® receptacle terminals, GFCI and standard receptacles	SNAPCTG
Switch jumper/tester, single pole, illuminated	SANPSWJUMP
Switch jumper/tester, 3-way, illuminated	SNAP3WJUMP



Polycarbonate Wallplates

Description	Standard		Mid-Size	
	1-Gang	2-Gang	1-Gang	2-Gang
StyleLine Decorator, white	P26W	P262W	PJ26W	PJ262W
Duplex, white	P8W	P82W	PJ8W	PJ82W
Toggle, white	PTW	P2W	PJ1W	PJ2W
Combination 1-Toggle and 1-Duplex, white	-	P18W	-	PJ18W
Combination 1-Duplex and 1-StyleLine Decorator, white	-	P826W	-	PJ826W
Combination 1-Toggle and 1-StyleLine Decorator, white	-	P126W	-	PJ126W



Hubbell Delivery Systems



INSTALLATION EFFICIENCY ETOUR

This interactive, 360-degree Installation Efficiency eTour walks users through ten different environments and identifies how and where Hubbell solutions can be used to efficiently deliver power, data, and AV—all while supporting fast installation.

Visit www.hubbell.com/wiringdevice-kellems > Resources to take the tour.



University



Library



Product Page

ONLINE RESOURCES


The Hubbell Wiring Device-Kellems website offers fast and convenient information through our online catalog, technical support, videos and more.

Visit www.hubbell.com/wiringdevice-kellems.

CONTACT US

Count on Hubbell Wiring Device-Kellems for the most reliable and innovative wiring device product line in North America.

 custserv@hubbell.com

 (800) 288-6000


 Find your local representative at www.hubbell.com/wiringdevice-kellems

LITERATURE SUPPORT

Hubbell offers an extensive literature library for product support. Downloadable PDFs are available online.



Hubbell SystemOne Recessed Floor Boxes



Pre-Wired Raceway Product Guide



Trench, Wall and Underfloor Duct Products



Cable Tray Systems



Aluminum Service Poles

HUBBELL[®]
Wiring Device-Kellems

www.hubbell.com/wiringdevice-kellems

