

⚡ DIMMER SWITCH

Transform any standard light switch into a connected dimmer switch and customize lighting from anywhere.



DIMMER SWITCH KEY FEATURES



Works With Most Dimmable Bulbs



Remote Access



Standard Installation



Voice Control



LED Night Light



No Hub Required



Two-Year Warranty


ACCESSORIES TO CONTROL WITH DIMMER SWITCH



Chandeliers



Track Lighting



Recessed Lighting




Hanging Fixtures



Bathroom Lighting



Pendant Lighting



Under-Cabinet Lighting

COMPATIBLE PLATFORMS



SPECIAL ORDER CUSTOM COLORS AVAILABLE



DIMMER SWITCH FEATURES AND RATINGS

- Fits any standard gang box
- Supports single pole, 3- and 4-way operation
- No hub or running additional wires
- Compatible with any dimmable bulb
- Standard rocker switch with double tap and brightness memory features
- In-app setup creates min/max dim levels, preventing bulb flicker
- Works with any standard rocker faceplate
- Pull-out HomeKit™ pairing tab
- Customizable LED night light
- Input: 120VAC, 60Hz
- Output: 120VAC, 60Hz
- CFL/LED: 150W — supports forward-phase dimming only
- Incandescent/halogen: 400W

CONNECTED APP

The iDevices Connected app allows you to control and schedule all your iDevices products from anywhere, with your iOS or Android™ device.

App Features:

- Voice control with Siri®, Alexa and the Google Assistant
- Access from anywhere, no hub required
- Set schedules, scenes, and control multiple homes
- Compatible with other HomeKit™ products
- Customize with pictures of your home
- Over-the-air software updates



SHIPPING SPECIFICATIONS

	Shipping Specs	Product Dimensions	Carton Dimensions
Product Number	IDEV0009		
UPC#	852931005650		
Cube (FT3)	0.17		
Carton UPC#	10852931005657		
Height		4.35"	5.00"
Width		2.00"	5.50"
Depth		2.50"	10.50"
GW		6.94 oz	4.62 lbs
NW			4.34 lbs
Pack Quantity			10

STANDARDS & CERTIFICATIONS: UL compliant, FCC compliant, RoHS compliant, CSA compliant, IC compliant, Wi-Fi CERTIFIED™ Bluetooth®

