



PROGRESS LIGHTING
DESIGN+SERIES™

2020



*INTRODUCING STATEMENT-
MAKING PIECES FROM OUR
DESIGN SERIES COLLECTION.*

Our Design Series fixtures feature artistic influence, fashion forward elements and details to contribute to affordable luxury for the home.

The fixtures found throughout the Design Series become the statement, the art piece and the focal point – and contribute to an overall luxurious experience in the home. They don't blend in. They stand out.



TABLE OF CONTENTS


4 Pictorial Index
22 Guest Designer: Jeffrey Alan Marks
50 Design Series™ Inspiration
94 Point Dume™ Collection



118 Fixture Collections



236 Pendants



268 Sconces



278 Bath Collections



320 Outdoor
364 Index

To explore more of the Design Series™ visit us online:



- @ProgressLtg
- @ProgressLtg
- @ProgressLtg
- Progress Lighting
- @ProgressLighting
- Progress-Lighting

POINT DUME™ COLLECTION

POINT DUME™ COLLECTION

CHANDELIERS AND PENDANTS

WANDERMERE
Brushed Brass p.95



MOONRISE
Antique Nickel p.102



ONSHORE
Brushed Nickel p.99



ONSHORE
Brushed Brass p.98



ROCKDANCE
Antique Nickel p.109



ROCKDANCE
Aged Brass p.109



ROCKDANCE
Brushed Nickel p.108



ROCKDANCE
Aged Brass p.109



SANDBAR
Brushed Brass p.100



SANDBAR
Brushed Brass p.101



SEQUIT POINT
Antique Nickel p.111



SEQUIT POINT
Brushed Brass p.110



SHEARWATER
White p.106



SHEARWATER
Antique Nickel p.107



SHEARWATER
Aged Brass p.107



SURFRIDER
Galvanized p.97



POINT DUME™ COLLECTION

PENDANTS

SURFRIDER Malibue p.97 *SURFRIDER* Galvanized p.97 *SURFRIDER* Malibue p.96 *TAPIA TRAIL* Brushed Nickel p.114



TAPIA TRAIL Aged Brass p.115 *WINDBLUFF* Brushed Brass p.116 *YERBA* Silver Ridge p.104 *YERBA* Silver Ridge p.105



CLOSE TO CEILING

ROCKDANCE Antique Nickel p.109 *ROCKDANCE* Aged Brass p.109 *SANDBAR* Brushed Brass p.101 *SEQUIT POINT* Antique Nickel p.111



SEQUIT POINT Brushed Brass p.110 *TAPIA TRAIL* Brushed Nickel p.114 *TAPIA TRAIL* Aged Brass p.115 *YERBA* Silver Ridge p.105



POINT DUME™ COLLECTION

SCONCES / WALL BRACKETS

LATIGO BAY Brushed Nickel p.112 *LATIGO BAY* Antique Bronze p.113 *LOOKOUT* Brushed Nickel p.103 *ONSHORE* Brushed Brass p.99



SHEARWATER Antique Nickel p.107 *SHEARWATER* Aged Brass p.107 *SURFRIDER* Antique Bronze p.97 *SURFRIDER* White p.97



SURFRIDER Galvanized p.97 *SANDBAR* Brushed Brass p.101 *YERBA* Silver Ridge p.105



COLLECTIONS

ADAGIO
Black p.124



ADAGIO
Black p.125



ALLAIRE
Antique Bronze p.224



ASSEMBLY HALL
Brushed Nickel p.231



CALDER
Brushed Nickel p.158



CALDER
Graphite p.159



CARRIAGE HILL
Brushed Nickel p.153



CARRIAGE HILL
Brushed Bronze p.152



ASSEMBLY HALL
Antique Bronze p.230



ASTRA
Brushed Nickel p.156



ASTRA
Antique Bronze p.157




BERGAMO
Forged Bronze p.222



CELESTE
Polished Nickel p.214



CINQ
Brushed Nickel p.235



CINQ
Antique Bronze p.234




CORDIN
Brushed Nickel p.142



BLAKELY
Graphite p.130



BLAKELY
Graphite p.131



BLAKELY
Graphite p.132



BONITA
Satin Brass p.216



CUMBERLAND
Matte Black p.120



DEBUT
Brushed Nickel p.178



DEBUT
Graphite p.180



DESIREE
Silver Ridge p.211



BONITA
Matte Black p.217



BONITA
Brushed Nickel p.219



BONITA
Polished Chrome p.218



CAHILL
Brushed Bronze p.144



DESIREE
Silver Ridge p.210



ELEVATE
Matte Black p.134



ELEVATE
Polished Chrome p.136



ELEVATE
Brushed Bronze p.138



COLLECTIONS

EVOKE
Antique Bronze p.192



EVOKE
Polished Nickel p.194



FONTAYNE
Brushed Nickel p.186



FONTAYNE
Antique Bronze p.184



HANGAR
Antique Bronze p.168




HANGAR
Antique Bronze p.169



ION
Polished Nickel p.161



ION
Brushed Bronze p.160



FONTAYNE
Brushed Nickel p.187



FONTAYNE
Antique Bronze p.185



GLAYSE
Brushed Nickel p.146



GLAYSE
Antique Bronze p.148



LOOKING GLASS
Antique Bronze p.176



MARCHÉ
Polished Nickel p.212



MARQUE
Graphite p.232



MOD
Polished Chrome p.162



GLIMMER
Antique Bronze p.204



GLIMMER
Silver Ridge p.204



GLIMMER
Antique Bronze p.206



GLIMMER
Silver Ridge p.206



NOMA
Antique Bronze p.196



NOMA
Polished Nickel p.198



ORRIZO
Black p.140



PALACIO
Vintage Gold p.150



GRESHAM
Graphite p.172



GRESHAM
Graphite p.174



HANGAR
Brushed Nickel p.166



HANGAR
Brushed Nickel p.167



RAE
Brushed Bronze p.122



RATIO
Brushed Nickel p.127



RATIO
Antique Bronze p.126



REMIX
Graphite p.182



COLLECTIONS

REMIX
Graphite p.183



RIGSBY
Vintage Gold p.154



SAVOR
Silver Ridge p.220



SPATIAL
Black p.164



SPATIAL
Black p.165



SPICEWOOD
Gilded Iron p.190



STRATHAM
Brushed Nickel p.208



TORRES
Matte Black p.128



TORRES
Matte Black p.129



TURNBURY
Galvanized Finish p.188



UNION SQUARE
Stainless Steel p.170



UNION SQUARE
Stainless Steel p.171



WESTFALL
Antique Bronze p.229



WESTFALL
Graphite p.228



WEST VILLAGE
Brushed Nickel p.202



WEST VILLAGE
Antique Bronze p.200



PENDANTS

ADAGIO
Black p.125



ALLAIRE
Antique Bronze p.227



ASSEMBLY HALL
Brushed Nickel p.231



ASSEMBLY HALL
Brushed Nickel p.230



BEAKER
Polished Chrome p.256



BEAKER
Antique Bronze p.257



BERGAMO
Forged Bronze p.223



BLAKELY
Graphite p.131



BONITA
Brushed Nickel p.217



BONITA
Satin Brass p.217



BONITA
Matte Black p.217



BONITA
Polished Nickel p.219



CAHILL
Brushed Bronze p.145



CAHILL
Brushed Bronze p.145



CARBON
Polished Nickel p.267



CARBON
Graphite p.266



CARRIAGE HILL
Brushed Nickel p.153



CARRIAGE HILL
Brushed Bronze p.153



CELESTE
Polished Nickel p.215



CHRONICLE
Antique Bronze p.248



CINQ
Brushed Nickel p.235



CINQ
Antique Bronze p.235



CORDIN
Brushed Nickel p.143



CUMBERLAND
Matte Black p.121



DESIREE
Silver Ridge p.211



DESIREE
Silver Ridge p.211



ELEVATE
Matte Black p.135



ELEVATE
Polished Chrome p.137



ELEVATE
Brushed Bronze p.139




ELLYSON
Polished Chrome p.244



PENDANTS (CONT'D)

ELLYSON Brushed Bronze p.245
ERA Matte Black p.254
FERMI Brushed Nickel p.264
FINN Matte Black p.261
FINN Metallic Silver p.260



FONTAYNE Antique Bronze p.184
FONTAYNE Brushed Nickel p.186
GALLEY Antique Bronze p.242
GALLEY Polished Nickel p.243
GLAYSE Antique Bronze p.149



GLAYSE Brushed Nickel p.147
GLIMMER Antique Bronze p.206
GLIMMER Silver Ridge p.206
GLIMMER Antique Bronze p.207
GLIMMER Silver Ridge p.207



GRESHAM Graphite p.175
GRESHAM Graphite p.175
HANGAR Antique Bronze p.169
HANGAR Brushed Nickel p.167
HANGAR Antique Bronze p.169



HANGAR Brushed Nickel p.167
LOOKING GLASS Antique Bronze p.177
MALBEC Brushed Nickel p.252
MALBEC Antique Bronze p.253
MALBEC Graphite p.253



MARCHÉ Polished Nickel p.213
MARQUE Graphite p.233
MAULDIN Brushed Nickel p.238
MAULDIN Matte Black p.239
MESH Antique Bronze p.258



MODERNA Brushed Nickel p.265
NOMA Polished Nickel p.199
NOMA Antique Bronze p.197
NOMA Polished Nickel p.199
NOMA Antique Bronze p.197



PALACIO Vintage Gold p.151
PALACIO Vintage Gold p.151
RATIO Brushed Nickel p.127
RATIO Antique Bronze p.126
RE-BAR Polished Chrome p.262



REMIX Graphite p.182
RIGSBY Vintage Gold p.154
SAVOR Silver Ridge p.221
SINCLAIRE Black p.240
SPATIAL Black p.165



SPATIAL Black p.164
SPICEWOOD Gilded Iron p.191
STAUNTON Brushed Nickel p.247
STAUNTON Antique Bronze p.246
STAUNTON Graphite p.247



TORRES Matte Black p.129
TURNBURY Galvanized Finish p.189
WESTFALL Antique Bronze p.229
WESTFALL Graphite p.229
WEST VILLAGE Antique Bronze p.201



WEST VILLAGE Brushed Nickel p.203
ZIN Brushed Nickel p.251
ZIN Antique Bronze p.251
ZIN Graphite p.250



SCONCES / WALL BRACKETS

ADAGIO Black p.125 *ALLAIRE* Antique Bronze p.226 *ASTRA* Brushed Nickel p.157 *ASTRA* Antique Bronze p.157 *AVANA* Brushed Nickel p.272



AVANA Polished Nickel p.273 *BERGAMO* Forged Bronze p.223 *BLAKELY* Graphite p.133 *BONITA* Antique Bronze p.275 *BONITA* Satin Brass p.275



BONITA Matte Black p.275 *BONITA* Brushed Nickel p.275 *BONITA* Polished Chrome p.275 *CAHILL* Brushed Bronze p.145 *CARLYN* Antique Bronze p.303



CARLYN Polished Nickel p.303 *CORDIN* Brushed Nickel p.143 *CUMBERLAND* Matte Black p.121 *DEBUT* Brushed Nickel p.179 *DEBUT* Graphite p.179



DESIREE Silver Ridge p.211 *ELEVATE* Matte Black p.135 *ELEVATE* Polished Chrome p.137 *ELEVATE* Brushed Bronze p.139 *GLAYSE* Brushed Nickel p.147



GLAYSE Antique Bronze p.149 *GLIMMER* Antique Bronze p.207 *GLIMMER* Silver Ridge p.207 *GRESHAM* Graphite p.175 *HANGAR* Brushed Nickel p.167



HANGAR Antique Bronze p.169 *HOBBS* Brushed Nickel p.276 *HOBBS* Polished Chrome p.277 *HOBBS* Antique Bronze p.277 *LOOKING GLASS* Antique Bronze p.177



MARCHÉ Polished Nickel p.213 *METRO* Polished Chrome p.271 *METRO* Brushed Nickel p.271 *METRO* Antique Bronze p.270 *MOD* Polished Chrome p.163



NOMA Antique Bronze p.197 *NOMA* Polished Nickel p.199 *ORRIZO* Black p.141 *PALACIO* Vintage Gold p.151 *RAE* Brushed Bronze p.123



RIGSBY Vintage Gold p.155 *SAVOR* Silver Ridge p.221 *STRATHAM* Brushed Nickel p.209 *TORRES* Matte Black p.129 *UNION SQUARE* Stainless Steel p.171



WEST VILLAGE Brushed Nickel p.203 *WEST VILLAGE* Antique Bronze p.201 *ZURA* Brushed Nickel p.319 *ZURA* Polished Chrome p.319 *ZURA* Matte Black p.319



BATH COLLECTIONS

CAHILL
Brushed Bronze p.294



CARLYN
Antique Bronze p.302



CARLYN
Polished Nickel p.303



DEBUT
Brushed Nickel p.297



DEBUT
Graphite p.296



METRIC
Polished Chrome p.315



MOD
Polished Chrome p.288



SPATIAL
Black p.290



UNION SQUARE
Stainless Steel p.282



VOLO
Brushed Nickel p.316



ELEVATE
Matte Black p.284



ELEVATE
Polished Chrome p.287



ELEVATE
Brushed Bronze p.286



FLIGHT
Brushed Nickel p.298



FLIGHT
Polished Chrome p.299



WANDER
Brushed Nickel p.310



WANDER
Polished Chrome p.312



WANDER
Venetian Bronze p.313



WEST VILLAGE
Brushed Nickel p.301



WEST VILLAGE
Antique Bronze p.300



GLANCE
Polished Chrome p.304



GLANCE
Antique Bronze p.305



GLAYSE
Brushed Nickel p.280



GLAYSE
Antique Bronze p.281



GLIDE
Brushed Nickel p.306



ZURA
Brushed Nickel p.318



ZURA
Polished Chrome p.319



ZURA
Matte Black p.319



GLIDE
Polished Chrome p.308



GLIDE
Oil Rubbed Bronze p.309



LISBON
Matte Black p.293



LISBON
Polished Nickel p.292



METRIC
Brushed Nickel p.314



OUTDOOR

CADENCE
Oil Rubbed Bronze p.326



CADENCE
Textured Black p.328



CHATSWORTH
Textured Black p.322



CREIGHTON
Antique Bronze p.338



CREIGHTON
Textured Black p.338



MORRISON
Antique Bronze p.324



MORRISON
Antique Pewter p.325



NORTHHAMPTON LED
Architectural Bronze p.363



NORTHHAMPTON LED
Black p.362



PATEWOOD
Black p.354



CULLMAN
Antique Bronze p.358



DEVEREUX
Antique Bronze p.348



GIBBES STREET
Antique Bronze p.332



GIBBES STREET
Textured Black p.334



HERMOSA
Textured Black p.342



SANTEE
Antique Bronze p.336



SANTEE
Matte Black p.337



TWAIN
Antique Bronze p.360



UNION SQUARE
Stainless Steel p.356



VERDAE
Antique Bronze p.350



JANSSEN
Oil Rubbed Bronze p.352



KIAWAH
Textured Black p.340



LEAWOOD LED
White p.345



LEAWOOD LED
Textured Black p.344



MAISON
Textured Black p.330



VERDAE
Textured Black p.351



WHITACRE
Antique Bronze p.346






JEFFREY ALAN MARKS

PROGRESS LIGHTING
DESIGN+SERIES™

A fitting collaboration between dreamer and maker.



DREAMER

Jeffrey's purposeful and authentic spaces beg to be lived in rather than existing only to be stylish. Today this Elle Décor A-List designer's spirited aesthetic is realized beyond his fortunate clients through licensing partnerships and a broader audience can look forward to homes that are more genuine, more personal and more engaging.

JEFFREY ALAN MARKS





Photo by Lisa Romerein

“I believe that lighting has a higher purpose, to be at once illuminating and decorative, purposeful and beautiful. Lighting is the ultimate marriage of form and function and the most transformative element in a design project. The very nature of light itself is inspirational.”

JEFFREY ALAN MARKS



Jeffrey's Point Dume™ lighting collection celebrates a curated mix of yesterday and today, distilling both industrial and artisanal influences. At home in a range of lifestyles from coastal to urban, the Collection is inspired by one of his favorite places, Point Dume, California, with

exceptional combinations of materials woven throughout. Emulating both the raw strength and the captivating honesty of the landscape, Jeffrey intuitively elevates lighting to a more authentic art form as he marries craftsmanship and style with some of his favorite materials and memories.



MAKER

In the eclectic Point Dume™ Collection, the dreamer and the maker are united by the desire to provide an elevated level of home fashion to an enthusiastic design-savvy consumer. As the inaugural guest designer of Progress' Design Series brand, Jeffrey's design goals are in sync with the Design Series

philosophy — to offer sophisticated styling at an accessible price. Together they are on a journey to inspire individuals to update the favorite spaces in their homes through fixtures that highlight artistic influence, rich finishes and fashion-forward elements.

POINT DUME™ COLLECTION







Featuring Point Dume™ Surfrider

Photo by Lisa Romerein



Featuring Point Dume™ Shearwater / Photo by Lisa Romerein



Featuring Point Dume™ Wandermere



Featuring Point Dume™ Wandermere





Featuring Point Dume™ Onshore



Featuring Point Dume™ Windbluff and Point Dume™ Sandbar



Featuring Point Dume™ Rockdance / Photo by Lisa Romerein



Photo by Lisa Romerein

Featuring Point Dume™ Yerba






Featuring Point Dume™ Latigo Bay / Photo by Lisa Romerein



Photo by Lisa Romerein

Featuring Point Dume™ Surfrider



“Beautiful lighting can appeal to both one’s pragmatic nature and one’s artistic spirit. For me, there is no better reward than to create well-loved spaces where life can be enjoyed fully and lived beautifully.”

JEFFREY ALAN MARKS



GOOD DESIGN HAS NO LIMITS

Test interior design limits by taking the chandelier out of the dining room and into the living room. Placed over a sofa in a richly layered and beautifully realized living room décor, it makes an artistic silhouette that punctuates a room and adds life to a tonal palette. The Rae chandelier doubles as a work of art, with its blend of geometric shapes and a sculpted, handcrafted frame finished in a glowing golden finish.

PLAYING WITH ANGLES

Basic geometry is anything but boring when you add shapely influences to your home for a unique touch of style. This foyer sets the stage for the first steps into your home as it plays up the geometric trend to the hilt with abstract artwork, a clean-lined X base console table, and a dramatic lighting fixture. Your guests will do a double-take as they gaze up at Cumberland, a unique geometric pendant finished in matte black frames and accented with circular seed glass panes. Its artistic "X" and "O" tic-tac-toe pattern echoes the geometry of the hall table for a design scheme that's sure to draw compliments.



Featuring Cumberland



Featuring Chatsworth

FIRST IMPRESSIONS COUNT

It only takes seven seconds to make a first impression, so make it count with your front entryway. Here, classic architectural style gets a modern vibe with an unadorned column and the elongated shape of the Chatsworth lantern.

*CLASSIC +
MODERN PLAY
WELL TOGETHER*

Exaggerated color and playful silhouettes abound in this living room that is a unique juxtaposition of modern and traditional styling. Traditional highboy and side table furnishings meld with the contemporary use of two circular stools as a coffee table. The simply charming Maudlin pendant at either end of an emerald couch adds symmetry and balances the bright color. Maudlin's geometric frames and clear seeded glass panes play off the diamond-patterned rug and showcase a modern twist on age-old classics.





SHADES OF BLACK AND GRAY

Turn the shiplap trend on its head by installing it vertically on the wall and painting it an accent color. The black vanity placed against the gray wall adds a moody, comforting tone to a serene bathroom. A pair of Bonita wall sconces flank an oversized mirror, adding understated elegance to the vignette. Contemporary ladder shelving displays bath necessities against an adjoining wall for additional visual flair.

MODERN LUXURY

Celebrate geometric forms and alluring intrigue. Create grand gestures and sweeping statements with a mixture of lighting fixtures that glimmer and shine. Metal accents, airy designs and artful arrangements are featured in collections, such as Orrizo, Adagio, Sinclair and Blakely. These fixtures all pair together perfectly because of the clean lines and fashion-forward designs featured in each.



EVOKE STYLISH STORYBOOK CHARM

This space charms all five senses through soft color palettes, vintage pieces of furniture and floral accents. The beautiful detail of Hermosa's Mediterranean-style lanterns contribute visual interest while bringing traditional exterior fixtures indoors. Bergamo's two-toned frame and tassel accents enhance the textured ceilings, walls and accessories.

A rustic mountain home interior featuring a stone fireplace, leather sofa, and dining area. The room has a high ceiling with exposed wooden beams and a large stone fireplace in the center. A brown leather sofa is positioned in front of a large window with sheer curtains. A wooden coffee table with metal legs sits in front of the sofa. To the right, a white tufted armchair and a brown leather ottoman are visible. In the background, a dining table with wooden chairs is set up. A large chandelier hangs from the ceiling, and a framed picture is mounted on the stone fireplace mantel.

RUSTIC MOUNTAIN HOME

Set the mood with a display of substantial style, Gresham's frame was inspired by the elegance of traditional iron structures. Specific attention to forging details creates a distinctive collection to highlight rustic-inspired spaces. Morrison and Fontayne complete the lighting design with complementary forms.



EARTH TONES TRENDING

Earthy granites and similar tones can make a big statement within a room. Additionally, Walnut is making a comeback because of the popularity of the mid-century modern design.

Featuring Morrison



Featuring Lisbon

TRADITIONAL LUXURY

Enjoy high status with sparkle and shine. Relax and unwind in this bath and vanity area full of femininity, sparkle and shine. The highly polished design style of Lisbon complements both Modern and Luxe interiors – and can be mounted up or down.

TRADITIONAL LUXURY

Enhance any space with artful angles and opulent accents. Soft metal tones, fabric shades and a soothing color palette create an oasis from everyday stress and responsibilities in this traditional luxury bath area. With a glamorous and modern appeal, Carriage Hill's hexagonal shape complements Stratham's signature string of alternating beads. Large in scale, this space showcases a stunning display of attention to detail.

SWEET, SERENE & SOPHISTICATED

Celebrate a new addition's grand entrance with a nursery to match! Designers today are incorporating sophisticated and simple elements to create magical settings for children.

The furniture selection carries a monochromatic color scheme, while floral accents and textured accessories add character to the space shown. Marché collection pairs perfectly with Carlyn's luxurious pattern and glass accents to create a gorgeous nursery with a touch of glam.



COMPLEMENT CLASSIC DESIGNS

Classic forms, geometric patterns and mixed metal finishes work together to define this stunning living area, while also enhancing the soothing color palette. Westfall's dramatic soaring frame and candelabra cluster complement Soiree's tall candles and clear seeded glass, creating an overall inviting atmosphere.



Featuring Westfall and Soiree



Featuring Glimmer chandelier and Bonita wall sconce.

EMBRACE ELEGANCE & SPARKLE

To contrast the gray color scheme, rich furniture and sleek hardware, we chose lighting fixtures with glass accents, metal finishes and architecturally styled frames to bring intrigue and a sophisticated sparkle to the room.

*A SERIES OF
STATEMENT-
MAKING FIXTURES*

Bold geometric patterns and Glayse's unbounded beveled glass adds a quirky flair to the clean lines and functionality of this design.

Additionally, the use of glass creates a sense of connection to nature and the outdoors. Hangar's unique form and Astra's organic design serve as statement pieces to complete the look.





MIXED METALS ARE HOT!

Not only are finishes “heating up” but the freedom to mix metals is growing in popularity. Much like combining gold and silver jewelry, there isn’t a rule that commits you to one finish from room to room. How you curate and combine metal accents will enhance a luxurious setting.



*PAIR SCULPTURAL
DESIGNS WITH
FARMHOUSE DÉCOR*

With a little country flair and an inviting atmosphere, this clean and simple design style is surging in popularity in homes across the nation. Rich tones and antique décor pair perfectly with the sculptural details featured in our Fermi and Re-Bar pendants. The lighting design also features a wall sconce and chandelier from our Cordin collection, which provides a playful contrast and creates a unique visual statement within the space.



UNWIND IN A ROMANTIC SETTING

This spa-inspired sanctuary encourages rest and relaxation. Romantic rose tones, plush furniture and natural light work to create the perfect environment to escape from the daily to-do list. Our Savor chandelier and sconce contribute an essence of craftsmanship with contemporized wrought iron details and a sweeping profile.

Featuring Savor

BRING THE OUTDOORS IN

Size matters! When it comes to selecting fixtures for a particular room, oversized or exaggerated frames are on trend in a big way.

In lieu of table lamps, we've chosen sconces from our Union Square outdoor lantern collection - a unique way of bringing the "outdoors" inside! Finally, our oversized Turnbury chandelier creates a dramatic focal point for this luxurious bedroom.



*SWOON OVER
MID-CENTURY
MODERN DESIGN*

Our designers selected a series of statement fixtures, where each complements the next, to highlight this great room that features a variety of shapes and pops of color.

Hangar's light and airy form adds visual interest, while also providing a unique contrast to Astra's asymmetrical design. Inspired by the art of engineering, Spatial's geometric frame balances and completes the design scheme.





THE KEY TO COORDINATING

The key to coordinating lighting throughout the home is finding a good balance. Try to avoid choosing every light fixture from one particular collection.

Instead, select fixtures that feature similar metal profiles or design styles. While the Era pendant and Looking Glass chandelier are from different families, each contains elements with an overall vintage feel. Iron accents, hints of brass and mechanical details all work together to create a unique statement.

LAYER LIGHTING WITH GEOMETRIC ACCENTS

Circular elements featured in the mirror and Debut chandelier work together to provide dramatic focal points to this living space. Additionally, the Squire outdoor wall lantern was incorporated in a clever way in this interior setting to create a rich layer of light to contribute to the room's décor.



Featuring Debut and Squire



Featuring Ion chandelier.

PERSONALIZE TRENDS TO MAKE IT YOUR OWN

Keep in mind, a light fixture is not going to define your style. It's all about how your light fixture fits into your personalized living space. You can make a home feel more luxurious because of the product you are putting into it so get creative and design with what you like.



Featuring Zura

SLEEK AND SOPHISTICATED

One of the most important things to remember when illuminating your bathroom is to provide shadow-free lighting at the mirror. This bath area benefits from a generous amount of natural light, while our sleek and sophisticated Zura sconces placed on either side of the bathroom mirror work to further reduce shadows on the side of the face.



*EARTH TONES
TRENDING*

Earthy granites and similar tones can make a big statement within a room. Additionally, Walnut is making a comeback because of the popularity of the mid-century modern design.

Featuring Cinq

*ALL THAT
GLITTERS FOR
A GLAMOROUS
DESIGN*

When friends and family walk into this glamorous foyer, they will instantly fall in love with the lighting design presented.

This grouping of pendants from the Desiree collection features luxury materials and details reminiscent of Hollywood's "Golden Era." A Silver Ridge finish and clear crystal strands cascade in a waterfall effect to convey the glitz and glamour from an iconic time that is making a modern comeback.

*MARBLE, GLASS &
GOLD – OH MY!*

Everyone deserves a little bit of luxe in his or her home. Sleek design, nature-inspired elements and ornate details make a statement within this lavishly designed setting. Our Palacio fixtures pair a Vintage Gold finish with faux white marble accents that complement the sophisticated glass spheres found in the Ellyson pendants.

POINT DUME™ COLLECTION



POINT DUME™ / WANDERMERE

With elegant out-stretched arms and the grace of a Calder mobile, the Wandermere chandelier is “modern symmetry in balance.” Available in Brushed Brass with curved metal shades, the Wandermere is an architectural presence for any space.

*FINISH*

● Brushed Brass - 160

EIGHT LIGHT CHANDELIER

P400192-160 Brushed Brass with white
40" dia., 28-1/4" ht.
Overall ht. w/chain 103-1/2", wire 15'.
Eight candelabra base lamps,
each 60w max.

POINT DUME™ / SURFRIDER

Rows of lapping wave-like metal are combined with beautifully braided cords, and suspension hooks for an ageless “industrial meets the modern minded” point of view. The inspired Surfrider pendant is offered in a Galvanized finish and a refreshing “Maliblu” finish. To round out the versatile group, the Surfrider collection also includes complementary sconces available in Galvanized, Antique Bronze or White.



P500200-162



P500199-141



P500199-162



P500200-141



P500200-162



P710064-030



P710064-020



P710064-141

FINISHES

- Antique Bronze - 020
- White - 030
- Galvanized - 141
- Maliblu - 162

ONE-LIGHT PENDANT

P500199-141 Galvanized with white
P500199-162 Maliblu with white
 13-7/8" dia., 12-3/8" ht.
 Overall ht. w/hooks & chain 96-1/2",
 wire 15'.
 One medium base lamp,
 75w max.

THREE-LIGHT PENDANT

P500200-141 Galvanized with white
P500200-162 Maliblu with white
 24-7/8" dia., 17-1/2" ht.
 Overall ht. w/hooks & chain 103-1/2",
 wire 15'.
 Three medium base lamps,
 each 75w max.

WALL SCONCE

P710064-020 Antique Bronze
P710064-030 White
P710064-141 Galvanized
 9" W., 11-1/8" ht.
 Extends 3-7/8". H/CTR 6".
 Two candelabra base lamps,
 each 60w max.
 ADA

POINT DUME™ / ONSHORE

Continuing Jeffrey's modern take on light and movement, the Onshore series combines some of his favorite materials and finishes. Offered as a White and Brushed Brass pendant, or a "Maliblu" and Brushed Nickel option, the Onshore group is a fresh and uplifting choice for casual living. The Onshore swing arm wall sconce in Brushed Brass has a three-tiered white enamel shade that complements this lifestyle.



P500194-160



P500194-009



P500194-160

FINISHES

- Brushed Nickel - 009
- Brushed Brass - 160

ONE LIGHT PENDANT

P500194-009 Brushed Nickel with white and Maliblu
P500194-160 Brushed Brass with white
 8" dia., 13" ht.
 Overall ht. w/stem 79", wire 10'.
 One medium base lamp,
 100w max.

WALL BRACKET

P710070-160 Brushed Brass with white
 8-7/8" dia., 1-3/4" ht.
 Extends 22-1/2". H/CTR 4".
 One medium base lamp,
 60w max.



P710070-160

POINT DUME™ / SANDBAR

Ageless Brushed Brass is layered in modern tiers for the Sandbar ceiling fixture, sconce and pendant light. The addition of Jeffrey's tailormade leather details, brass hooks, milk glass and cables make for memorable, luxury lighting with infinite design applications.



P500198-160



P350141-160



P350141-160
shown as semi-flush



P710068-160



P500198-160

FINISH

● Brushed Brass - 160

SEMI-FLUSH CONVERTIBLE

P350141-160 Brushed Brass with milk glass Hanging and ceiling mount hardware included. 15-1/8" dia., 14-7/8" ht. Overall ht. w/stem 76", wire 10'. Three medium base lamps, each 100w max.

THREE LIGHT PENDANT


P500198-160 Brushed Brass with milk glass and beige leather 21-1/4" dia., 14-7/8" ht. Overall ht. w/hook & chain 93-1/2", wire 15'. Three medium base lamps, each 100w max.

WALL SCONCE

P710068-160 Brushed Brass with milk glass 8-7/8" W., 12" ht. Extends 4-1/2". H/CTR 6". One candelabra base lamp, 60w max.

POINT DUME™ / MOONRISE

Quintessential JAM, Moonrise is an ethereal globe fashioned of Antique Nickel and marbled white glass. With a nod to its vintage ancestry, this simple style statement manages to defy time and live quite happily in the present. Jeffrey recommends the simplicity of Moonrise's round silhouette the perfect choice when the design calls for multiples.



FINISH

● Antique Nickel - 081

THREE LIGHT PENDANT

P500204-081 Antique Nickel
with marble glass
18-1/2" dia., 19-1/4" ht.
Overall ht. w/chain 94", wire 15".
Three medium base lamps,
each 100w max.

POINT DUME™ / LOOKOUT

The Lookout wall sconce is a modern classic that combines Brushed Nickel, clear seeded glass and handsome leather accents. Perfectly at home in so many locations and lifestyles, the Lookout sconce is ideal to use when multiples are a must. The Lookout wall sconce has the enduring sensibility that adds an uncomplicated elegance to any interior.



FINISH

● Brushed Nickel - 009

ONE LIGHT WALL BRACKET

P710069-009 Brushed Nickel
with brown leather
6" W., 12-7/8" ht.
Extends 7-3/8". H/CTR 7-3/4"
One medium base lamp,
60w max

POINT DUME™ / YERBA

The Yerba group marries a modernized Moroccan shape with Mid-Century geometric detail. Crafted of pierced metal in a Silver Ridge finish, the Yerba collection offers an inverted pendant, a dome shaped pendant, ceiling mounted fixture and wall sconce, each casting dramatic dappled light throughout a space.



P500197-134



P500201-134



P710067-134



P350140-134



P500197-134

FINISH

● Silver Ridge - 134

THREE LIGHT SEMI-FLUSH

P350140-134 Silver Ridge
17-3/8" dia., 12-3/8" ht.
Three candelabra base lamps,
each 60w max.

FOUR LIGHT PENDANT

P500197-134 Silver Ridge
21-5/8" dia., 24" ht.
Overall ht. w/stem 90", wire 15'.
Four medium base lamps,
each 60w max.

ONE LIGHT PENDANT

P500201-134 Silver Ridge
12" dia., 8-1/4" ht.
Overall ht. w/stem 74-1/2", wire 10'.
One medium base lamp,
100w max.

ONE LIGHT WALL SCONCE

P710067-134 Silver Ridge
8-1/4" W., 12-1/2" ht.
Extends 3-7/8". H/CTR 6-1/4".
One candelabra base lamp,
60w max.
ADA

POINT DUME™ / SHEARWATER

The Shearwater hanging lanterns and wall sconces embody Jeffrey's love of easy coastal living. His lighter lantern and sconce option combine Antique Nickel with clear glass and a soft-beige stitched leather handle, while the more traditional version combines Aged Brass, clear glass, and a handsome brown stitched leather handle. For a more California look, Jeffrey offers a White or Antique Nickel lantern with clear glass and his signature Maliblu accent as a pop of color in the roof of the fixture.



P500196-161



P500196-030



P500196-081



P500196-161



P710066-081



P710066-161

FINISHES

- White - 030
- Antique Nickel - 081
- Aged Brass - 161

FOUR LIGHT PENDANT

P500196-030 White with Maliblu and Brown Leather
P500196-081 Antique Nickel with Maliblu and Beige Leather
P500196-161 Aged Brass and Brown Leather
 16-1/4" dia., 32" ht.
 Overall ht. w/chain 109", wire 15'.
 Four candelabra base lamps, each 60w max.

ONE LIGHT WALL SCONCE

P710066-081 Antique Nickel with Beige Leather
P710066-161 Aged Brass with Brown Leather
 8" W., 15-7/8" ht.
 Extends 3-7/8. H/CTR 7-7/8".
 One candelabra base lamp, 60w max.
 ADA

POINT DUME™ / ROCKDANCE

The Rockdance Lighting series is a graceful series fashioned from unique glass, hook elements, and handsome stitched leather strapping. With the signatures of a bespoke handbag or boot, the surprising design elements that punctuate this exciting group are certain to become design favorites for generations. Available in Brushed Nickel or Antique Nickel with clear seeded glass or Aged Brass with mercury glass.



P500195-009



P500195-009



P500195-161



P500202-081



P500202-161



P350143-081



P350143-161

FINISHES

- Brushed Nickel - 009
- Aged Brass - 161
- Antique Nickel - 081

FOUR LIGHT SEMI-FLUSH

P350143-081 Antique Nickel with seeded glass with beige leather
P350143-161 Aged Brass with mercury glass and brown leather
 14-3/8" dia., 10-1/4" ht.
 Four candelabra base lamps, each 60w max.

ONE LIGHT PENDANT

P500195-009 Brushed Nickel with seeded glass and beige leather
P500195-161 Aged Brass with mercury glass and brown leather
 15-3/4" dia., 10-1/8" ht.
 Overall ht. w/hooks & chain 85-1/2", wire 10'.
 One medium base lamp, 100w max.

ONE LIGHT PENDANT

P500202-081 Antique Nickel with beige leather and seeded glass
P500202-161 Aged Brass with brown leather and mercury glass
 9-1/2" dia., 17-1/2" ht.
 Overall ht. w/hooks & chain 92-1/2", wire 10'.
 One medium base lamp, 100w max.

POINT DUME™ / SEQUIT POINT

The romance and architectural presence of a lighthouse is expressed in the Sequit Point group. In the same way strips of glass increased the effectiveness of lighthouse beacons, the modern Sequit Point series benefits from a similar ingenuity. Mercury glass sleeves stand in tandem with clear glass rods to provide a familiar glow for the convertible ceiling fixture/pendant. Available in Antique Nickel and Brushed Brass.



P350142-160



P350142-081



P350142-160



P350142-081
shown as semi-flush



P350142-160
shown as semi-flush

FINISHES

- Antique Nickel - 081
- Brushed Brass - 160

SEMI-FLUSH CONVERTIBLE

P350142-081 Antique Nickel with mercury glass
P350142-160 Brushed Brass with mercury glass
 Hanging and ceiling mount hardware included.
 14" dia., 9-5/8" ht.
 Overall ht. w/stem 78", wire 10'.
 Three candelabra base lamps, each 60w max.

POINT DUME™ / LATIGO BAY

The timeless Latigo Bay wall sconce hugs the wall with a simple lined Mercury glass back and an articulated curved metal shade. Predicted to be a classic go-to for a variety of easy interior updates, this slim vertical sconce is available in Antique Bronze and Brushed Nickel.



P710065-009



P710065-009



P710065-020

FINISHES

- Brushed Nickel - 009
- Antique Bronze - 020

WALL SCONCE

P710065-009 Brushed Nickel with mercury glass
P710065-020 Antique Bronze with mercury glass
 7" W., 11" ht.
 Extends 4". H/CTR 5-1/2".
 One medium base lamp, 60w max.
 ADA

POINT DUME™ / TAPIA TRAIL

Jeffrey creates two distinctive looks when combining first Aged Brass and milk glass and then timeless Brushed Nickel and seeded glass. Both versions of the Tapia Trail fixture are defined by rivet details and remind us of their industrial origins — part Nautical, part Farmhouse, all American.



P350139-009



P350139-009
shown as semi-flush



P350139-161
shown as semi-flush

FINISHES

- Brushed Nickel - 009
- Aged Brass - 161

SEMI-FLUSH CONVERTIBLE

P350139-009 Brushed Nickel with seeded glass
P350139-161 Aged Brass with milk glass
 Hanging and ceiling mount hardware included.
 11-3/4" dia., 12-7/8" ht.
 Overall ht. w/stem 77-1/2", wire 10'.
 One medium base lamp, 100w max.

POINT DUME™ / WINDBLUFF

With sophisticated effortlessness, the Windbluff pendant was inspired by breezy shoreline living and incorporates Brushed Brass and natural linen. This transitional pendant, perfect for both modern and traditional interiors, is suspended by decorative brass hooks and thoughtfully has a white diffuser to create that perfect glow.



FINISH

● Brushed Brass - 160

THREE LIGHT PENDANT

P500203-160 Brushed Brass
with linen shade
20" dia., 16-1/2" ht.
Overall ht. w/hook & chain 91-1/2",
wire 15'.
Three medium base lamps,
each 100w max.

DESIGN+SERIES™
COLLECTIONS



COLLECTIONS

CUMBERLAND NEW

Experience the sense of shelter, warmth, and protection offered by the Modern Mountain glow of the Cumberland collection. Let wandering eyes hungry for a satisfying lighting experience satiate their appetites as their gaze feasts upon the artistic “X” and “O” tic-tac-toe pattern intricately weaved into Matte Black frames. Signature circular seeded glass panes foster a gazing window design on each fixture in the collection to give Cumberland that rustic, modern cabin vibe.



P500233-031



P500232-031



P500233-031



P350159-031



P710076-031

COLLECTIONS

FINISH

- Matte Black - 031

PAIR WITH

Looking Glass
Foster

TWO-LIGHT FLUSH MOUNT

P350159-031 Matte Black
13" sq., 5-1/2" ht.
Two medium base lamps,
each 60w max.

EIGHT-LIGHT FOYER

P500232-031 Matte Black
16-7/8" sq., 27-5/8" ht.
Overall ht. w/stem 94", wire 15'.
Eight candelabra base lamps,
each 60w max.

FIVE-LIGHT PENDANT

P500233-031 Matte Black
16-1/8" sq., 17-1/8" ht.
Overall ht. w/stem 83", wire 15'.
Five candelabra base lamps,
each 60w max.

WALL SCONCE

P710076-031 Matte Black
5-1/8" W., 14-5/8" ht.
Extends 4". H/CTR 7-1/4".
One candelabra base lamp,
60w max.



RAE NEW

Execute bold visions and design statements with the Rae Collection. A blend of geometric shapes and a sculpted, hand artisan frame with a golden finish bring this modern collection to life for an awe-inspiring lighting experience guaranteed to spark conversation amongst your gazing guests.



P400216-109



P400217-109



P710078-109



P350158-109



P350158-109
shown as semi-flush

COLLECTIONS

FINISH

● Brushed Bronze - 109

PAIR WITH

Palacio
Evoke

SEMI-FLUSH CONVERTIBLE

P350158-109 Brushed Bronze
18" dia., 8-1/2" ht.
Hanging and ceiling mount
hardware included.
Overall ht. w/chain 73-1/2", wire 10'.
3 candelabra base lamps,
each 60w max.

SIX-LIGHT CHANDELIER

P400216-109 Brushed Bronze
26-7/8" dia., 14" ht.
Overall ht. w/chain 80", wire 15'.
Six candelabra base lamps,
each 60w max.

NINE-LIGHT CHANDELIER

P400217-109 Brushed Bronze
30-1/2" dia., 21-5/8" ht.
Overall ht. w/chain 87-1/2", wire 15'.
Nine candelabra base lamps,
each 60w max.

WALL SCONCE

P710078-109 Brushed Bronze
5-1/2" W., 15" ht.
Extends 3-3/4". H/CTR 7-1/2".
Two candelabra base lamps,
each 60w max.



ADAGIO

An array of geometric patterns in Adagio is a nod to the musical description of a tender and melodic tone. The modern design features lights that are distributed around a circular band. Mixed metal elements, which are present in Brushed Silver and Brushed Gold accents, can complement monochromatic color palettes that are popular in homes today. Each fixture in the Adagio collection creates a focal point and is ideal for Luxe and Modern interiors.



P500174-031



P400170-031



P710057-031



P500173-031

COLLECTIONS

FINISH

● Black - 031

PAIR WITH

Orrizo
Glaysé

SIX-LIGHT ISLAND

P400170-031 Black
38" W., 16-3/8" ht., 7" d.
Overall ht. w/stem 82-1/2", wire 15'.
Six candelabra base lamps,
each 60w max.

MINI-PENDANT

P500173-031 Black
12" dia., 14-5/8" ht.
Overall ht. w/stem 80", wire 10'.
One medium base lamp,
75w max.

SIX-LIGHT PENDANT

P500174-031 Black
24" dia., 26" ht.
Overall ht. w/stem 87-1/2", wire 15'.
Six candelabra base lamps,
each 60w max.

TWO-LIGHT WALL SCONCE

P710057-031 Black
11" W., 15-1/2" ht.
Extends 6". H/CTR 7-3/4".
Two G16.5 candelabra base lamps,
each 60w max.

RATIO

A sleek metal frame supports a low-slung shade to create Ratio's casual modern style. The frame's proportion to the white linen drum shade evokes a perfect ratio for lighting. All fixtures include a polished glass diffuser that offers an elegant appeal.



P5015-20



P3604-09
shown as
pendant



P5015-09



P3604-20



P3604-09
shown as semi-flush



P5021-09



P5021-20

COLLECTIONS

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20

PAIR WITH

- Metric
- Finn
- Glaysé

SEMI-FLUSH CONVERTIBLE

P3604-09 Brushed Nickel
P3604-20 Antique Bronze
 Hanging and ceiling mount hardware included.
 16" dia., 11-1/2" ht.
 Overall ht. w/stem 77-1/2", wire 10'.
 Three medium base lamps, each 75w max.

FOUR-LIGHT PENDANT

P5015-09 Brushed Nickel
P5015-20 Antique Bronze
 Hanging and ceiling mount hardware included.
 24" dia., 15-7/8" ht.
 Overall ht. w/stem 82", wire 10'.
 Four medium base lamps, each 75w max.

SIX-LIGHT PENDANT


P5021-09 Brushed Nickel
P5021-20 Antique Bronze
 Hanging and ceiling mount hardware included.
 30" dia., 19-1/8" ht.
 Overall ht. w/stem 85", wire 10'.
 Six medium base lamps, each 75w max.

TORRES NEW

Elevate your Modern Mountain home décor by incorporating ravishing rustic design in the heart of your home with the Torres Collection. Handcrafted spires reminiscent of rugged forest surroundings coalesce in cultivated masterpieces of rustic sophistication. Beautiful black, blunt edges crisscross in open-cage designs for an organic interpretation of the popular tic-tac-toe pattern.



P400213-031



P400215-031



P710077-031



P500248-031

FINISH
● Black - 031

PAIR WITH
Looking Glass
Spicewood

FOUR-LIGHT CHANDELIER
P400213-031 Black
18" dia., 11-5/8" ht.
Overall ht. w/stem 77-1/2", wire 15'.
Four candelabra base lamps,
each 60w max.

FIVE-LIGHT ISLAND
P400215-031 Black
40" W., 11-3/8" ht., 14" d.
Overall ht. w/stem 77-1/2", wire 15'.
Five candelabra base lamps,
each 60w max.

FOUR-LIGHT FOYER
P500248-031 Black
16" dia., 22" ht.
Overall ht. w/stem 88", wire 15'.
Four candelabra base lamps,
each 60w max.

WALL SCONCE
P710077-031 Black
8" W., 22" ht.
Extends 3-7/8". H/CTR 11".
Two candelabra base lamps,
each 60w max.



BLAKELY

The Blakely collection has two unique and fashion-forward design styles. Choose between a rectangular frame or an open linear form. Both styles celebrate geometric interplay with clean, straight lines. Finished in Graphite with satin brass accents, the Blakely collection is ideal for Modern and Traditional interiors.



P500168-143



P350120-143



P350120-143
shown as semi-flush



P500168-143



P400086-143

FINISH

● Graphite - 143

PAIR WITH

Rae
Rainey

SEMI-FLUSH CONVERTIBLE

P350120-143 Graphite
Hanging and ceiling mount hardware included.
17-1/4" W., 9-3/8" ht.
Overall ht. w/chain 74-1/2", wire 10'.
Two medium base lamps, each 60w max.

FOUR-LIGHT ISLAND

P400086-143 Graphite
40-7/8" W., 17-1/4" ht., 11" depth.
Overall ht. w/stem 82-1/2", wire 15'.
Four medium base lamps, each 60w max.

FOUR-LIGHT PENDANT

P500168-143 Graphite
23-1/4" W., 25-3/4" ht.
Overall ht. w/stem 91-1/2", wire 15'.
Four medium base lamps, each 60w max.

BLAKELY

FINISHES

- Brushed Nickel - 009
- Polished Nickel - 104
- Brushed Bronze - 109
- Graphite - 143

TWO-LIGHT WALL BRACKET

P300214-143 Graphite
 8-1/4" W., 9-3/8" ht.
 Extends 4-7/8". H/CTR 5-5/8".
 Two candelabra base lamps,
 each 60w max.

TWO-LIGHT FLUSH MOUNT

P350121-009 Brushed Nickel
P350121-104 Polished Nickel
P350121-109 Brushed Bronze
 13-5/8" dia., 5-3/4" ht.
 Two medium base lamps,
 each 60w max.

FOUR-LIGHT CHANDELIER

P400179-143 Graphite
 20" W., 15-5/8" ht.
 Overall ht. w/stem 82", wire 15'.
 Four candelabra base lamps,
 each 60w max.

SIX-LIGHT CHANDELIER

P400113-143 Graphite
 28" W., 15-5/8" ht.
 Overall ht. w/stems 82", wire 15'.
 Six candelabra base lamps,
 each 60w max.

SIX-LIGHT ISLAND

P400114-143 Graphite
 40" W., 15-5/8" ht., 15" d.
 Overall ht. w/stems 82", wire 15'.
 Six candelabra base lamps,
 each 60w max.



P350121-009



P350121-104



P350121-109



P300214-143

P400113-143

ELEVATE

Achieve a sleek and modern look with Elevate. Etched glass white shades paired with a Matte Black, Brushed Bronze or Polished Chrome frame provide an elegant contrast for Modern interior design settings.

ALSO AVAILABLE IN
Bath, page 282



P400022-031



P350040-031



P300020-031



P500151-031



P400021-031



P400022-031



P400023-031

COLLECTIONS

FINISH

● Matte Black - 031

PAIR WITH

Penn
Ratio
Mod

THREE-LIGHT FLUSH MOUNT

P350040-031 Matte Black
11-3/4" dia., 9-7/8" ht.
Three medium base lamps,
each 75w max.

THREE-LIGHT CHANDELIER

P400021-031 Matte Black
21-3/4" dia., 23" ht.
Overall ht. w/stem 89", wire 15'.
Three medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER

P400022-031 Matte Black
27-3/8" dia., 23" ht.
Overall ht. w/stem 89", wire 15'.
Five medium base lamps,
each 100w max.

SEVEN-LIGHT CHANDELIER

P400023-031 Matte Black
32-5/8" dia., 22-7/8" ht.
Overall ht. w/stem 89", wire 15'.
Seven medium base lamps,
each 100w max.

MINI-PENDANT

P500151-031 Matte Black
3-7/8" dia., 7" ht.
Overall ht. w/stem 73", wire 10'.
One medium base lamp,
100w max.

ELEVATE

FINISH

● Polished Chrome - 015

ONE-LIGHT WALL BRACKET

P300020-015 Polished Chrome
5" W., 8" ht.
Extends 7". H/CTR 4".
One medium base lamp,
100w max.

THREE-LIGHT SEMI-FLUSH

P350040-015 Polished Chrome
11-3/4" dia., 9-7/8" ht.
Three medium base lamps,
each 75w max.

ONE-LIGHT FLUSH MOUNT

P350105-015-30 Polished Chrome
13" dia., 5-1/4" ht.
One 17W LED module, 3000K,
90 CRI, 1452 source lumens.



THREE-LIGHT CHANDELIER

P400021-015 Polished Chrome
21-3/4" dia., 23" ht.
Overall ht. w/stem 89"; wire 15'.
Three medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER

P400022-015 Polished Chrome
27-3/8" dia., 23" ht.
Overall ht. w/stem 89"; wire 15'.
Five medium base lamps,
each 100w max.

SEVEN-LIGHT CHANDELIER

P400023-015 Polished Chrome
32-5/8" dia., 22-7/8" ht.
Overall ht. w/stem 89"; wire 15'.
Seven medium base lamps,
each 100w max.

MINI-PENDANT

P500151-015 Polished Chrome
3-7/8" dia., 7" ht.
Overall ht. w/stem 73"; wire 10'.
One medium base lamp,
100w max.



P400022-015



P350040-015



P350105-015-30



P300020-015



P500151-015



P400021-015



P400022-015



P400023-015

ELEVATE

FINISH

● Brushed Bronze - 109

ONE-LIGHT WALL BRACKET

P300020-109 Brushed Bronze
5" W., 8" ht.
Extends 7". H/CTR 4".
One medium base lamp,
100w max.

THREE-LIGHT SEMI-FLUSH

P350040-109 Brushed Bronze
11-3/4" dia., 9-7/8" ht.
Three medium base lamps,
each 75w max.

ONE-LIGHT FLUSH MOUNT

P350105-109-30 Brushed Bronze
13" dia., 5-1/4" ht.
One 17W LED module, 3000K,
90 CRI, 1452 source lumens.



THREE-LIGHT CHANDELIER

P400021-109 Brushed Bronze
21-3/4" dia., 23" ht.
Overall ht. w/stem 89"; wire 15'.
Three medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER

P400022-109 Brushed Bronze
27-3/8" dia., 23" ht.
Overall ht. w/stem 89"; wire 15'.
Five medium base lamps,
each 100w max.

SEVEN-LIGHT CHANDELIER

P400023-109 Brushed Bronze
32-5/8" dia., 22-7/8" ht.
Overall ht. w/stem 89"; wire 15'.
Seven medium base lamps,
each 100w max.

MINI-PENDANT

P500151-109 Brushed Bronze
3-7/8" dia., 7" ht.
Overall ht. w/stem 73", wire 10'.
One medium base lamp,
100w max.



P350040-109



P350105-109-30



P300020-109



P500151-109



P400021-109



P400022-109



P400023-109

P400022-109

ORRIZO

Suitable for sleek and sophisticated interiors, Orrizo presents an artful arrangement of clear glass and golden metal rods that adorn a Black band. Geometric and artisan design influences complement both Modern and Luxe settings. Common applications for these statement-making fixtures include dining rooms and bedrooms and foyers. Six-light chandelier may be staggered in a cluster or grouping for large entryway settings.



P400176-031



P400176-031

FINISH
● Black - 031

PAIR WITH
Adagio
Sinclair

SIX-LIGHT CHANDELIER
P400176-031 Black
24" dia., 19-3/8" ht.
Overall ht. w/stem 84", wire 15'.
Six candelabra base lamps,
each 60w max.

TWO-LIGHT WALL SCONCE
P710063-031 Black
6-3/8" W., 23" ht.
Extends 5". H/CTR 10-1/2".
Two medium base lamps,
each 60w max.



P710063-031

CORDIN

Featuring a striking combination of traditional and modern design, classic styling in the Cordin collection highlights a distinctive look for a variety of interiors. Elegant linear arms and a double-lined linen shade create a softer feel when combined with the vintage mechanical details and dual-tone frame. A Brushed Nickel finish with natural brass accents are incorporated in all fixtures in the Cordin family, including chandeliers, semi-flush, mini-pendant, island and swing arm options.



P400090-009



P710034-009



P400089-009



P500101-009



P400092-009



P350095-009



P400091-009

COLLECTIONS

FINISH

● Brushed Nickel - 009

PAIR WITH

Hangar
Bonn
Hansford

SEMI-FLUSH CONVERTIBLE

P350095-009 Brushed Nickel
Hanging and ceiling mount hardware included.
16" dia., 12-1/2" ht.
Overall ht. w/stem 78", wire 10'.
Three medium base lamps, each 60w max.

THREE-LIGHT CHANDELIER

P400089-009 Brushed Nickel
25" dia., 19" ht.
Overall ht. w/stem 85", wire 15'.
Three medium base lamps, each 75w max.

FIVE-LIGHT CHANDELIER

P400090-009 Brushed Nickel
30" dia., 20" ht.
Overall ht. w/stem 86", wire 15'.
Five medium base lamps, each 75w max.

NINE-LIGHT CHANDELIER

P400091-009 Brushed Nickel
38" dia., 26" ht.
Overall ht. w/stem 92", wire 15'.
Nine medium base lamps, each 75w max.

THREE-LIGHT LINEAR CHANDELIER

P400092-009 Brushed Nickel
38" W., 10" L., 21" ht.
Overall ht. w/stem 87", wire 15'.
Three medium base lamps, each 75w max.

MINI-PENDANT

P500101-009 Brushed Nickel
10" dia., 8" ht.
Overall ht. w/stem 74", wire 10'.
One medium base lamp, 75w max.

WALL BRACKET


P710034-009 Brushed Nickel
10" W., 17-1/2" ht.
Extends 13-1/2". H/CTR 13-1/8".
Arm pivots 120°
One medium base lamp, 75w max.

CAHILL

A stylish Brushed Bronze finish frames brilliant clear beveled glass panels in the Cahill collection. Ideal for Luxe or Mid-Century Modern interiors, the visual interest provides a reinvention of the popular glass design.

ALSO AVAILABLE IN

Bath, page 292



P400071-109



P500075-109



P500076-109



P500077-109



P300108-109



P400071-109



P400072-109

COLLECTIONS

FINISH

● Brushed Bronze - 109

PAIR WITH

Rainey
Elevate
Orrizo

ONE-LIGHT BATH

P300108-109 Brushed Bronze
4-1/2" W., 19-3/4" ht.
Extends 7-1/2".
One candelabra base lamp,
60w max.

FIVE-LIGHT CHANDELIER

P400071-109 Brushed Bronze
25-5/8" dia., 13" ht.
Overall ht. w/chain 70", wire 15'.
Five candelabra base lamps,
each 60w max.

EIGHT-LIGHT CHANDELIER

P400072-109 Brushed Bronze
31-3/8" dia., 13-5/8" ht.
Overall ht. w/chain 69-1/2", wire 15'.
Eight candelabra base lamps,
each 60w max.

MINI-PENDANT

P500075-109 Brushed Bronze
7-3/4" dia., 17-5/8" ht.
Overall ht. w/chain 75", wire 10'.
One medium base lamp,
60w max.

FOUR-LIGHT FOYER

P500076-109 Brushed Bronze
15-3/4" dia., 19-3/4" ht.
Overall ht. w/chain 78-1/2", wire 10'.
Four candelabra base lamps,
each 60w max.

SIX-LIGHT FOYER

P500077-109 Brushed Bronze
18" dia., 24-1/2" ht.
Overall ht. w/chain 81", wire 10'.
Six candelabra base lamps,
each 60w max.

All fixtures shown with P7826-01
vintage lamps, not included.

GLAYSE

Inspired by modern architecture, Glayse features handsome details for variety of interior design styles. The frameless unbounded beveled glass creates beautiful light and reflection. The structure of Glayse is the focal point of the design, where form follows function.

ALSO AVAILABLE IN

Bath, page 280



P500095-009



P350090-009



P500073-009



P500074-009



P500095-009



P400116-009



P300105-009

COLLECTIONS

FINISH

● Brushed Nickel - 009

PAIR WITH

Ratio
Calder

WALL SCONCE

P300105-009 Brushed Nickel
7" W., 8-3/8" ht.
Extends 5-1/2". H/CTR 5-3/8".
One medium base lamp,
60w max.

SEMI-FLUSH CONVERTIBLE

P350090-009 Brushed Nickel
Hanging and ceiling mount
hardware included.
16-3/4" Sq., 14-3/4" ht.
Overall ht. w/chain 80", wire 10'.
Four medium base lamps,
each 60w max.

FIVE-LIGHT LINEAR CHANDELIER

P400116-009 Brushed Nickel
36-3/4" W., 10" L., 15-3/4" ht.
Overall ht. w/stem 82", wire 15'.
Five medium base lamps,
each 60w max.

MINI-PENDANT

P500073-009 Brushed Nickel
6-1/2" Sq., 11-7/8" ht.
Overall ht. w/stem 77", wire 10'.
One medium base lamp,
60w max.

FIVE-LIGHT PENDANT

P500074-009 Brushed Nickel
22-3/4" Sq., 13-3/4" ht.
Overall ht. w/chain 80, wire 15'.
Five medium base lamps,
each 60w max.

FOUR-LIGHT FOYER

P500095-009 Brushed Nickel
14-3/4" W., 28-3/8" ht.
Overall ht. w/stem 94-1/2", wire 15'.
Four medium base lamps,
each 60w max.

All fixtures shown with P7825-01
vintage lamps, not included.

GLAYSE

FINISH

- Antique Bronze - 020

WALL SCONCE

P300105-020 Antique Bronze
7" W., 8-3/8" ht.
Extends 5-1/2". H/CTR 5-3/8".
One medium base lamp,
60w max.

SEMI-FLUSH CONVERTIBLE

P350090-020 Antique Bronze
Hanging and ceiling mount
hardware included.
16-3/4" Sq., 14-3/4" ht.
Overall ht. w/chain 80", wire 10'.
Four medium base lamps,
each 60w max.

FIVE-LIGHT LINEAR CHANDELIER

P400116-020 Antique Bronze
36-3/4" W., 10" L., 15-3/4" ht.
Overall ht. w/stem 82", wire 15'.
Five medium base lamps,
each 60w max.

MINI-PENDANT

P500073-020 Antique Bronze
6-1/2" Sq., 11-7/8" ht.
Overall ht. w/stem 77", wire 10'.
One medium base lamp,
60w max.

FIVE-LIGHT PENDANT

P500074-020 Antique Bronze
22-3/4" Sq., 13-3/4" ht.
Overall ht. w/chain 80, wire 15'.
Five medium base lamps,
each 60w max.

FOUR-LIGHT FOYER

P500095-020 Antique Bronze
14-3/4" W., 28-3/8" ht.
Overall ht. w/stem 94-1/2", wire 15'.
Four medium base lamps,
each 60w max.

All fixtures shown with P7825-01 vintage lamps, not included.



P500095-020



P350090-020



P500073-020



P500074-020



P500095-020



P400116-020



P300105-020

PALACIO

An intriguing fashion-forward lighting collection, Palacio pairs a Vintage Gold finish with faux white marble accents for a stunningly elegant design. White silk shades complement gold accents to create a statement-making style. Ideal for a variety of interiors.



P400098-078



P500108-078

P500105-078

P400098-078

P500106-078

P400099-078

P500107-078

COLLECTIONS

FINISH
● Vintage Gold - 078

PAIR WITH
Cahill
Rae

FIVE-LIGHT CHANDELIER
P400098-078 Vintage Gold
27" dia., 21-1/2" ht.
Overall ht. w/chain 96-1/2", wire 15'.
Five medium base lamps,
each 75w max.

NINE-LIGHT CHANDELIER
P400099-078 Vintage Gold
36" dia., 25" ht.
Overall ht. w/chain 148", wire 15'.
Nine medium base lamps,
each 75w max.

FOUR-LIGHT FOYER
P500105-078 Vintage Gold
15" Sq., 26-1/2" ht.
Overall ht. w/chain 110", wire 15'.
Four candelabra base lamps,
each 60w max.

EIGHT-LIGHT FOYER
P500106-078 Vintage Gold
20" dia., 30-1/2" ht.
Overall ht. w/chain 113-1/2", wire 15'.
Eight candelabra base lamps,
each 60w max.

MINI-PENDANT
P500107-078 Vintage Gold
8" dia., 17" ht.
Overall ht. w/stem 83", wire 10'.
One medium base lamp, 75w max.

FOUR-LIGHT PENDANT
P500108-078 Vintage Gold
22" dia., 9-5/8" ht.
Overall ht. w/stem 73", wire 10'.
Four candelabra base lamps,
each 60w max.

WALL BRACKET
P710037-078 Vintage Gold
6" W., 17" ht.
Extends 7-1/2". H/CTR 9".
One medium base lamp, 75w max.

P710037-078

CARRIAGE HILL

Featuring artful angles and soft metal tones, Carriage Hill offers a sophisticated pendant design for Traditional interiors. A crisp ecru fabric shade forms a hexagonal shape to surround an interior candelabra cluster. Available in Brushed Bronze and Brushed Nickel finishes. Pendants can be displayed individually or in groupings of two or more in kitchens, entryways and foyers.



P500166-109



P500166-009



P500166-109

FINISHES

- Brushed Nickel - 009
- Brushed Bronze - 109

PAIR WITH

Tinsley
Stratham

THREE-LIGHT PENDANT

P500166-009 Brushed Nickel
P500166-109 Brushed Bronze
20-3/4" dia., 24-1/2" ht.
Overall ht. w/chain 99 1/2", wire 15'.
Three candelabra base lamps,
each 60w max.

SIX-LIGHT PENDANT

P500167-009 Brushed Nickel
P500167-109 Brushed Bronze
28-7/8" dia., 28-7/8" ht.
Overall ht. w/chain 104", wire 15'.
Six candelabra base lamps,
each 60w max.



P500167-009



P500167-109

RIGSBY

The use of mixed media highlights a variety of elegant details featured in Rigsby. A hint of faux marble appears in the horizontal cross bars, while Vintage Gold and Chrome accents create a dual toned finish. Decorated white gloss hardback shades – lined with burnished gold foil – complete the fixture. Inspired by mid-century design influences, this distinct and classic collection is suitable for Modern and Luxe interiors.



P500175-078



P350128-078



P500175-078



P350128-078
shown as semi-flush



P400172-078



P300201-078



P400173-078

COLLECTIONS

FINISH

● Vintage Gold - 078

PAIR WITH

Rae
Ion

WALL BRACKET

P300201-078 Vintage Gold
6" W., 13-1/4" ht.
Extends 9-5/8". H/CTR 7-1/2".
One medium base lamp,
60w max.

SEMI-FLUSH CONVERTIBLE

P350128-078 Vintage Gold
Hanging and ceiling mount
hardware included.
18" dia., 11-3/4" ht.
Overall ht. w/chain 52", wire 10'.
Three medium base lamps,
each 60w max.

FIVE-LIGHT CHANDELIER

P400172-078 Vintage Gold
32" dia., 16-3/4" ht.
Overall ht. w/chain 92", wire 15".
Five medium base lamps,
each 60w max.

NINE-LIGHT CHANDELIER

P400173-078 Vintage Gold
Two-tier.
36" dia. 26-1/4"
Overall ht. w/chain 149-1/2", wire 15'.
Nine medium base lamps,
each 60w max.

FOUR-LIGHT PENDANT

P500175-078 Vintage Gold
22" dia., 12-1/4" ht.
Overall ht. w/chain 81", wire 10'.
Four medium base lamps,
each 60w max.

ASTRA

An iconic fixture, Astra features an organic, asymmetrical design. Ideal for dining room settings or entryways, these classic Mid-Century inspired pieces are so versatile they can be incorporated into a variety of interiors.



P400108-009



P710027-009



P710027-020



P400108-009



P400108-020



P400109-009



P400109-020

COLLECTIONS

FINISHES

- Brushed Nickel - 009
- Antique Bronze - 020

PAIR WITH

Hangar
Glaysé

SIX-LIGHT CHANDELIER

P400108-009 Brushed Nickel
P400108-020 Antique Bronze
22-5/8" dia., 10-1/2" ht.
Overall ht. w/stem 72", wire 15'.
Six medium base lamps,
each 60w max.

EIGHT-LIGHT CHANDELIER

P400109-009 Brushed Nickel
P400109-020 Antique Bronze
42-3/8" dia., 19-5/8" ht.
Overall ht. w/stem 77", wire 15'.
Eight medium base lamps,
each 60w max.

WALL BRACKET

P710027-009 Brushed Nickel
P710027-020 Antique Bronze
7-1/4" W., 17-3/4" ht.
Extends 3-7/8". H/CTR 7".
Two medium base lamps,
each 60w max.

*Fixture dimension does not
include lamps.*

*All fixtures shown with P7826-01
vintage lamps, not included.*

CALDER

Calder celebrates the elegance of movement with a graceful articulating center column. Pivoting arms provide a nearly endless array of configurations to complement the asymmetric design. Larger scale design is suitable for open floor plans, great rooms or anywhere a dramatic focal piece is needed to make a bold statement. The minimal form provides a perfect showcase for vintage or globe style light bulbs. Available in either Brushed Nickel or Graphite finish.



P400144-009



P400143-143



P400143-009



P400144-143



P400144-009

COLLECTIONS

FINISHES

- Brushed Nickel - 009
- Graphite - 143

PAIR WITH

Hangar
Cirro

SIX-LIGHT CHANDELIER

P400143-009 Brushed Nickel
P400143-143 Graphite
30-1/2" dia., 12-5/8" ht.
Overall ht. w/stem 70", wire 10'.
Six medium base lamps,
each 60w max.

TEN-LIGHT CHANDELIER

P400144-009 Brushed Nickel
P400144-143 Graphite
38-1/2" dia., 19-3/8" ht.
Overall ht. w/stem 76-1/2", wire 10'.
Ten medium base lamps,
each 60w max.

*Fixture dimension does not
include lamps.*

*All fixtures shown with
P860028-001 or G30 Globe
lamps, not included.*

ION

Featuring a Polished Nickel or Brushed Bronze finish, these Space-Age inspired chandeliers boast either twelve or sixteen lights, each extending to support a single candelabra base lamp. Additionally, Ion chandeliers pair with Progress Lighting's Elevate collection for stunning Mid-Century inspired interiors.



P400040-109




P400041-104



P400040-104



P400041-109



P400040-109

COLLECTIONS

FINISHES

- Polished Nickel - 104
- Brushed Bronze - 109

PAIR WITH

- Cahill
- Orrizo
- Glaysé

TWELVE-LIGHT CHANDELIER

P400040-104 Polished Nickel
P400040-109 Brushed Bronze
 14-1/8" dia.,
 Overall ht. w/stem 76"; wire 15'.
 Twelve candelabra base lamps,
 each 25w max.

SIXTEEN-LIGHT CHANDELIER

P400041-104 Polished Nickel
P400041-109 Brushed Bronze
 24" dia.,
 Overall ht. w/stem 79-1/2"; wire 15'.
 Sixteen candelabra base lamps,
 each 25w max.

Fixture dimension does not include lamps.

All fixtures shown with P7826-01 or G16.5 crown reflector lamps, not included.

MOD

Giving a nod to the space age with mid-century modern appeal, Mod features a sleek linear frame in a Polished Chrome finish. Clear, spherical glass shades offer the perfect focal point for vintage bulbs or reflector-style globes.

ALSO AVAILABLE IN
Bath, page 288



P4755-15



P2850-15



P4755-15



P4756-15

COLLECTIONS

FINISH

● Polished Chrome - 15

PAIR WITH

Ion

WALL BRACKET

P2850-15 Polished Chrome
5-7/8" W., 7-3/4" ht.
Extends 7-3/8". H/CTR 3-7/8".
One candelabra base lamp,
60w max.

FIVE-LIGHT CHANDELIER

P4755-15 Polished Chrome
28-7/8" dia., 19-7/8" ht.
Overall ht. w/stem 86", wire 15'.
Five candelabra base lamps
each, 60w max.

SIX-LIGHT CHANDELIER

P4756-15 Polished Chrome
34" dia., 24-7/8" ht.
Overall ht. w/stem 91", wire 15'.
Six candelabra base lamps
each, 60w max.

All fixtures shown with P7827-01
vintage lamps, not included.

SPATIAL

Spatial showcases a modern form that complements Urban Industrial, Mid-Century Modern and Bohemian styles. Overscale geometric frames feature designs inspired by metal trusses and the art of engineering. Matte Black finish is highlighted by clear globe shades or open candles. Chandelier and pendant options are ideal for foyers and entryways, while vanity fixtures complement modern spa-like bath suites.



ALSO AVAILABLE IN
Bath, page 290



P500083-031



P500082-031



P500083-031



P500084-031



P400077-031



P500096-031



P400084-031

COLLECTIONS

FINISH
● Black - 031

PAIR WITH
Remix
Finn

SEMI-FLUSH CONVERTIBLE
P400077-031 Black
Hanging and ceiling mount hardware included.
19-5/8" dia., 14" ht.
Overall ht. w/chain 52", wire 10'.
Three candelabra base lamps, each 60w max.

SIX-LIGHT CHANDELIER
P400084-031 Black
26" dia., 32" ht.
Overall ht. w/chain 101", wire 15'.
Six medium base lamps, each 60w max.

MINI-PENDANT
P500082-031 Black
12" dia., 11-1/4" ht.
Overall ht. w/chain 85", wire 10'.
One medium base lamp, 100w max.

FOUR-LIGHT PENDANT
P500083-031 Black
23-1/2" dia., 19" ht.
Overall ht. w/chain 93-1/2", wire 15'.
Four candelabra base lamps, each 60w max.


SIX-LIGHT PENDANT
P500084-031 Black
28" dia., 26" ht.
Overall ht. w/chain 101", wire 15'.
Six candelabra base lamps, each 60w max.

THREE-LIGHT FOYER
P500096-031 Black
23-3/4" dia., 25-1/2" ht.
Overall ht. w/chain 100-1/2", wire 15'.
Three candelabra base lamps, each 60w max.

All fixtures shown with P7826-01 or G16.5 lamps, not included.

HANGAR

Fixtures in the Hangar collection are fun, light and airy pieces – perfect for both casual and modern homes. A sophisticated, statement-making frame occupies a large visual space. Modern wire basket forms are finished in Brushed Nickel with graphite accents or Antique Bronze and natural brass accents to complete the design.



P500117-009



P500115-009



P400105-009



P400106-009



P710043-009



P350102-009



P500116-009

COLLECTIONS

FINISH

● Brushed Nickel - 009

PAIR WITH

Astra
Zag

SEMI-FLUSH CONVERTIBLE

P350102-009 Brushed Nickel
Hanging and ceiling mount hardware included. Vintage Linen Shade. 16" dia., 13-1/4" ht. Overall ht. w/stem 78-1/2", wire 10'. Two medium base lamps, each 60w max.

FIVE-LIGHT CHANDELIER

P400105-009 Brushed Nickel
30" dia., 19-3/4" ht.* Overall ht. w/stem 77", wire 15'. Five medium base lamps, each 60w max.

EIGHT-LIGHT CHANDELIER

P400106-009 Brushed Nickel
40" dia., 24-7/8" ht.* Overall ht. w/stem 91-1/2", wire 15'. Eight medium base lamps, each 60w max.

MINI-PENDANT

P500115-009 Brushed Nickel
13" dia., 9-5/8" ht. Overall ht. w/stem 76-1/2", wire 10'. One medium base lamp, 60w max.

ONE-LIGHT PENDANT

P500116-009 Brushed Nickel
Vintage Linen Shade. 20" dia., 26" ht. Overall ht. w/stem 92", wire 15'. One medium base lamp, 100w max.

THREE-LIGHT PENDANT

P500117-009 Brushed Nickel
Vintage Linen Shade. 24" dia., 24-1/4" ht. Overall ht. w/stem 90", wire 15'. Three medium base lamps, each 75w max.

WALL BRACKET

P710043-009 Brushed Nickel
5" W., 8-3/4" ht.* Extends 4-1/2". H/CTR 4". One medium base lamp, 60w max.

*Fixture dimension does not include lamps.

All fixtures shown with P7825-01 or P7827-01 lamps, not included.

HANGAR

FINISH

- Antique Bronze - 020

SEMI-FLUSH CONVERTIBLE

P350102-020 Brushed Nickel
Hanging and ceiling mount hardware included. Vintage Linen Shade. 16" dia., 13-1/4" ht.
Overall ht. w/stem 78-1/2", wire 10'.
Two medium base lamps, each 60w max.



P710043-020

FIVE-LIGHT CHANDELIER

P400105-020 Antique Bronze
30" dia., 19-3/4" ht.*
Overall ht. w/stem 77", wire 15'.
Five medium base lamps, each 60w max.



P400105-020

EIGHT-LIGHT CHANDELIER

P400106-020 Antique Bronze
40" dia., 24-7/8" ht.*
Overall ht. w/stem 91-1/2", wire 15'.
Eight medium base lamps, each 60w max.



P400106-020

MINI-PENDANT

P500115-020 Antique Bronze
13" dia., 9-5/8" ht.
Overall ht. w/stem 76-1/2", wire 10'.
One medium base lamp, 60w max.



P350102-020

ONE-LIGHT PENDANT

P500116-020 Antique Bronze
Vintage Linen Shade.
20" dia., 26" ht.
Overall ht. w/stem 92", wire 15'.
One medium base lamp, 100w max.



P500116-020

THREE-LIGHT PENDANT

P500117-020 Antique Bronze
Vintage Linen Shade.
24" dia., 24-1/4" ht.
Overall ht. w/stem 90", wire 15'.
Three medium base lamps, each 75w max.

WALL BRACKET

P710043-020 Antique Bronze
5" W., 8-3/4" ht.*
Extends 4-1/2". H/CTR 4".
One medium base lamp, 60w max.

*Fixture dimension does not include lamps.

All fixtures shown with P7825-01 or P7827-01 lamps, not included.



P500117-020

UNION SQUARE

Originally inspired by historical reproduction gas lanterns, Union Square now offers a four-light chandelier and five-light linear island fixture. The simple geometric form features a Stainless Steel frame that is paired with vintage-style light bulbs. Mechanical details such as exaggerated knobs provide character to the form.

ALSO AVAILABLE IN

Bath, page 282
Outdoor, page 356



P400112-135



P400112-135

FINISH
● Stainless Steel - 135

PAIR WITH
Remix
Turnbury

FOUR-LIGHT CHANDELIER
P400112-135 Stainless Steel
20" W., 9-3/4" ht.
Overall ht. w/stems 76-1/2", wire 15'.
Four medium base lamps,
each 60w max.

FIVE-LIGHT ISLAND
P400145-135 Stainless Steel
38" W., 9-3/4" ht., 8-1/2" d.
Overall ht. w/stems 76", wire 15'.
Five medium base lamps,
each 60w max.

ONE-LIGHT BRACKET
P710038-135 Stainless Steel
5-1/4" W., 12" ht.
Extends 5". H/CTR 6".
One medium base lamp,
60w max.

*All fixtures shown with
P7825-01 lamps, not included.*



P400145-135



P710038-135
shown with P7825-01
vintage lamp



P710038-135
shown with P7827-01
vintage lamp

GRESHAM

A display of substantial style, Gresham's frame was inspired by the elegance of traditional iron structures. Specific attention to forging details creates a distinctive collection for Transitional and Farmhouse interior spaces. Seeded glass shades and a Graphite finish pair together to complete the look.



P400164-143



P400164-143



P400165-143



P400166-143

FINISH

● Graphite - 143

PAIR WITH

Debut
Spicewood

SIX-LIGHT CHANDELIER

P400164-143 Graphite
28" dia., 22-1/2" ht.
Overall ht. w/chain 96-1/2", wire 15'.
Six candelabra base lamps,
each 60w max.

NINE-LIGHT CHANDELIER

P400165-143 Graphite
36" dia., 24-7/8" ht.
Overall ht. w/chain 99", wire 15'.
Nine candelabra base lamps,
each 60w max.

FIFTEEN-LIGHT CHANDELIER

P400166-143 Graphite
Two-tier.
47-1/8" dia., 40-3/8" ht.
Overall ht. w/chain 163", wire 15'.
Fifteen candelabra base lamps,
each 60w max.

GRESHAM

FINISH

- Graphite - 143

SEMI-FLUSH CONVERTIBLE

P350119-143 Graphite
Hanging and ceiling mount hardware included.
17-3/4" dia., 12" ht.
Overall ht. w/chain 50", wire 10'.
Three medium base lamps, each 60w max.

FOUR-LIGHT FOYER

P500164-143 Graphite
20" dia., 26-1/4" ht.
Overall ht. w/chain 100", wire 15'.
Four candelabra base lamps, each 60w max.

EIGHT-LIGHT FOYER

P500165-143 Graphite
24" dia., 41-3/8" ht.
Overall ht. w/chain 115-1/2", wire 15'.
Eight candelabra base lamps, each 60w max.

EIGHT-LIGHT LINEAR CHANDELIER

P400180-143 Graphite
38" W., 17-1/2" ht., 13-7/8" d.
Overall ht. w/chain 91-1/2", wire 15'.
Eight candelabra base lamps, each 60w max.

ONE-LIGHT WALL BRACKET

P710055-143 Graphite
4-3/4" W., 15" ht.
Extends 5-3/4". H/CTR 10".
One candelabra base lamp, 60w max.



P500165-143



P350119-143



P350119-143
shown as semi-flush



P500164-143



P500165-143



P710055-143



P400180-143

LOOKING GLASS

Whether for a mountain cabin or an urban retreat, the rustic charm of the Looking Glass collection is an artful display of romantic vintage lighting. Inspired by a timber frame farmhouse, Looking Glass features iron elements that support clear seeded glass reflectors. Hints of brass accentuate the mechanical details to enhance a vintage feel.



P400002-020



P400002-020



P400003-020



P500042-020



P710002-020

COLLECTIONS

FINISH

- Antique Bronze - 020

PAIR WITH

Torres
Cumberland

FOUR-LIGHT CHANDELIER

P400002-020 Antique Bronze
25-3/8" W., 18-1/4" ht.
Overall ht. w/stem 84", wire 15'.
Four medium base lamps,
each 60w max.

SIX-LIGHT CHANDELIER

P400003-020 Antique Bronze
19" W., 36-3/4" L., 18-1/4" ht.
Overall ht. w/stem 84", wire 15'.
Six medium base lamps,
each 60w max.

MINI-PENDANT

P500042-020 Antique Bronze
9" dia., 14 3/4" ht.
Overall ht. w/stem 81", wire 10'.
One medium base lamp,
100w max.

WALL SCONCE

P710002-020 Antique Bronze
9" W., 17-7/8" ht.
Extends 7-5/8". H/CTR 11-3/8".
One medium base lamp,
60w max.

*All fixtures shown with P7825-01
vintage lamps, not included.*

DEBUT

Debut provides a fitting stage to feature nostalgic, vintage lamps. Glass accessory shades in clear or frosted seeded finishes are available to complement traditional incandescent or energy efficient lamps.

ALSO AVAILABLE IN

Bath, page 296



P400015-009



P350036-009



P400015-009
shown with
P860003-001 shade



P400017-009
shown with
P860002-001 shade



P300008-009

P300008-009
shown with
P860002-001 shade



P860002-001

P860003-001



P400016-009

COLLECTIONS

FINISH

● Brushed Nickel -009

PAIR WITH

Remix
Staunton

WALL BRACKET

P300008-009 Brushed Nickel
4-1/2" W., 8-1/2" ht.
Extends 5-7/8". H/CTR 5".
One medium base lamp,
60w max.

SEMI-FLUSH CONVERTIBLE

P350036-009 Brushed Nickel
Hanging and ceiling mount
hardware included.
19-7/8" dia., 15" ht.
Overall ht. w/chain 52"; wire 10'.
Three medium base lamps,
each 60w max.

SIX-LIGHT CHANDELIER

P400015-009 Brushed Nickel
28" dia., 27-1/2" ht.
Overall ht. w/chain 102-1/2"; wire 15'.
Six medium base lamps,
each 60w max.

NINE-LIGHT CHANDELIER

P400016-009 Brushed Nickel
36" dia., 34-1/2" ht.
Overall ht. w/chain 109-1/2"; wire 15'.
Nine medium base lamps,
each 60w max.

FIFTEEN-LIGHT CHANDELIER

P400017-009 Brushed Nickel
36" dia., 41-5/8" ht.
Overall ht. w/chain 164-1/2"; wire 15'.
Fifteen medium base lamps,
each 60w max.

ACCESSORY SHADE

P860002-001 Frosted
seeded glass shade.
4-1/4" dia., 5-7/8" ht.

ACCESSORY SHADE

P860003-001 Clear
seeded glass shade.
4-1/4" dia., 5-7/8" ht.

All fixtures shown with P7825-01
vintage lamps, not included.

DEBUT

FINISH

● Graphite - 143

WALL BRACKET

P300008-143 Graphite
4-1/2" W., 8-1/2" ht.
Extends 5-7/8". H/CTR 5".
One medium base lamp,
60w max.

SEMI-FLUSH CONVERTIBLE

P350036-143 Graphite
Hanging and ceiling mount
hardware included.
19-7/8" dia., 15" ht.
Overall ht. w/chain 52"; wire 10'.
Three medium base lamps,
each 60w max.

SIX-LIGHT CHANDELIER

P400015-143 Graphite
28" dia., 27-1/2" ht.
Overall ht. w/chain 102-1/2"; wire 15'.
Six medium base lamps,
each 60w max.

NINE-LIGHT CHANDELIER

P400016-143 Graphite
36" dia., 34-1/2" ht.
Overall ht. w/chain 109-1/2"; wire 15'.
Nine medium base lamps,
each 60w max.

FIFTEEN-LIGHT CHANDELIER

P400017-143 Graphite
36" dia., 41-5/8" ht.
Overall ht. w/chain 164-1/2"; wire 15'.
Fifteen medium base lamps,
each 60w max.

ACCESSORY SHADE

P860002-001 Frosted
seeded glass shade.
4-1/4" dia., 5-7/8" ht.

ACCESSORY SHADE

P860003-001 Clear
seeded glass shade.
4-1/4" dia., 5-7/8" ht.

*All fixtures shown with P7825-01
vintage lamps, not included.*



P400015-143

P350036-143
shown with
P860002-001 shade



P400015-143



P400017-143
shown with
P860003-001 shade



P300008-143



P300008-143
shown with
P860003-001 shade



P860002-001




P860003-001



P400016-143

REMIX

Remix features industrial-inspired pendant options. A Graphite frame is comprised of straps that weave together to create an open cage design. Brushed Nickel accents on the inside add a touch of mixed metal accents.



P500012-143



P500010-143



P400051-143



P500011-143



P500012-143

COLLECTIONS

FINISH
● Graphite - 143

PAIR WITH
Spicewood
West Village

FIVE-LIGHT CHANDELIER
P400051-143 Graphite
26" dia., 20" ht.
Overall ht. w/stem 86", wire 15'.
Five medium base lamps,
each 60w max.

MINI-PENDANT
P500010-143 Graphite
10" dia., 9-1/4" ht.
Overall ht. w/stem 75-1/2"; wire 10'.
One medium base lamp,
60w max.

THREE-LIGHT PENDANT
P500011-143 Graphite
16" dia., 15" ht.
Overall ht. w/stem 81"; wire 15'.
Three medium base lamps,
each 60w max.

FOUR-LIGHT PENDANT
P500012-143 Graphite
22" dia., 15" ht.
Overall ht. w/stem 81"; wire 15'.
Four medium base lamps,
each 60w max.

*All fixtures shown with P7825-01
vintage lamps, not included.*

FONTAYNE

With updated designs that honor the charm of early American styling, Fontayne provides a timeless elegance to Rustic Farmhouse, Modern Farmhouse and Urban Industrial spaces. Impressive graphic elements take center stage, while candelabra lights highlight subtle curves. Dual tone finish combinations include Antique Bronze with faux oak accents or Brushed Nickel with weathered gray accents.



P400080-020



P400080-020



P500088-020



P400081-020



P500089-020



P400083-020



P400082-020

COLLECTIONS

FINISH

● Antique Bronze - 020

PAIR WITH

Galley
Conestee
Hansford

FOUR-LIGHT CHANDELIER

P400080-020 Antique Bronze
15-3/4" dia., 30" ht.
Overall ht. w/stem 105", wire 15'.
Four candelabra base lamps,
each 60w max.

SIX-LIGHT CHANDELIER

P400081-020 Antique Bronze
22" dia., 24-3/4" ht.
Overall ht. w/stem 111-1/2", wire 15'.
Six candelabra base lamps,
each 60w max.

SIX-LIGHT LINEAR CHANDELIER

P400082-020 Antique Bronze
36" W., 22" d., 15-3/4" ht.
Overall ht. w/stems 103-1/2", wire 15'.
Six candelabra base lamps,
each 60w max.

TWELVE-LIGHT CHANDELIER

P400083-020 Antique Bronze
32" dia., 28-3/4" ht.
Overall ht. w/stem 107", wire 15'.
Twelve candelabra base lamps,
each 60w max.

FOUR-LIGHT PENDANT

P500088-020 Antique Bronze
14" Sq., 25" ht.
Overall ht. w/chain 99", wire 15'.
Four candelabra base lamps,
each 60w max.

SIX-LIGHT PENDANT

P500089-020 Antique Bronze
20" Sq., 32" ht.
Overall ht. w/chain 107-1/2", wire 15'.
Six candelabra base lamps,
each 60w max.

All fixtures shown with P7826-01 vintage lamps, not included.

FONTAYNE

FINISH

● Brushed Nickel - 009

FOUR-LIGHT CHANDELIER

P400080-009 Brushed Nickel
15-3/4" dia., 30" ht.
Overall ht. w/stem 105", wire 15'.
Four candelabra base lamps,
each 60w max.

SIX-LIGHT CHANDELIER

P400081-009 Brushed Nickel
22" dia., 24-3/4" ht.
Overall ht. w/stem 111-1/2", wire 15'.
Six candelabra base lamps,
each 60w max.

SIX-LIGHT LINEAR CHANDELIER

P400082-009 Brushed Nickel
36" W., 22" d., 15-3/4" ht.
Overall ht. w/stems 103-1/2", wire 15'.
Six candelabra base lamps,
each 60w max.

TWELVE-LIGHT CHANDELIER

P400083-009 Brushed Nickel
32" dia., 28-3/4" ht.
Overall ht. w/stem 107", wire 15'.
Twelve candelabra base lamps,
each 60w max.

FOUR-LIGHT PENDANT

P500088-009 Brushed Nickel
14" Sq., 25" ht.
Overall ht. w/chain 99", wire 15'.
Four candelabra base lamps,
each 60w max.

SIX-LIGHT PENDANT

P500089-009 Brushed Nickel
20" Sq., 32" ht.
Overall ht. w/chain 107-1/2", wire 15'.
Six candelabra base lamps,
each 60w max.

All fixtures shown with P7826-01 vintage lamps, not included.



P400080-009



P400080-009



P500088-009



P400081-009



P500089-009



P400083-009



P400082-009

TURNBURY

Coastal-inspired pieces are popular in a variety of today's home designs. Turnbury pendants feature a solid wood frame surround with hand-painted, galvanized metal fittings. The distressed pine frame finish is reminiscent of driftwood that has been weathered in the sun.



P4761-141



P5317-141
Shown with
P7825-01
vintage lamps



P4760-141



P4763-141

COLLECTIONS

FINISH

- Galvanized Finish - 141

PAIR WITH

- Fontayne
- Zin
- Union Square

FOUR-LIGHT CHANDELIER

P4760-141 Galvanized Finish
16" dia., 18-3/4" ht.
Overall ht. w/chain 93-1/2", wire 15'.
Four candelabra base lamps
each, 60w max.

SIX-LIGHT CHANDELIER

P4761-141 Galvanized Finish
26" dia., 28-3/4" ht.
Overall ht. w/chain 103-1/2", wire 15'.
Six candelabra base lamps
each, 60w max.

EIGHT-LIGHT CHANDELIER

P4763-141 Galvanized Finish
Two tier
36" W., 39" ht.
Overall ht. w/chain 162", wire 15'.
Eight candelabra base lamps,
each 60w max.

MINI-PENDANT

P5317-141 Galvanized Finish
10" dia., 12-1/4" ht.
Overall ht. w/chain 87", wire 10'.
One medium base lamp,
100w max.

*Fixtures shown with P7826-01
vintage lamps, not included.*

SPICEWOOD

The statement-making Spicewood pendants feature a rich, solid wood surround in a classic quatrefoil pattern. Wrought iron metal fittings in a Gilded Iron finish are paired with a distressed pine frame to complement rustic and reclaimed design styles.



P4766-71



P5318-71
shown with
P7825-01
vintage lamp



P4766-71



P4767-71

FINISH

● Gilded Iron - 71

PAIR WITH

Fontayne
Gresham
Malbec

FOUR-LIGHT CHANDELIER

P4766-71 Gilded Iron
22" dia., 24-1/2" ht.
Overall ht. w/chain 99-1/2", wire 15'.
Four candelabra base lamps
each, 60w max.

SIX-LIGHT CHANDELIER

P4767-71 Gilded Iron
30" dia., 32-1/2" ht.
Overall ht. w/chain 107-1/2", wire 15'.
Six candelabra base lamps
each, 60w max.

MINI-PENDANT

P5318-71 Gilded Iron
10" dia., 11" ht.
Overall ht. w/stem 77", wire 10'.
One medium base lamp,
100w max.

*Fixtures shown with P7826-01
vintage lamps, not included.*

EVOKE

Evoke features an elliptical frame that gracefully supports a candelabra with clear glass shade. Mixed finishes highlight the unique shape and provide a hint of livable luxury to your home. Three-, five- and six-light options available.



P400117-020



P400024-020



P400026-020



P400025-020



P400117-020

COLLECTIONS

FINISH

● Antique Bronze - 020

PAIR WITH

Noma
Marche

THREE-LIGHT CHANDELIER

P400024-020 Antique Bronze
17-5/8" dia., 28-1/2" ht.
Overall ht. w/chain 103-1/2"; wire 15'.
Three candelabra base lamps,
each 60w max.

FIVE-LIGHT CHANDELIER

P400025-020 Antique Bronze
24-5/8" dia., 35-3/8" ht.
Overall ht. w/chain 110-1/2"; wire 15'.
Five candelabra base lamps,
each 60w max.

SIX-LIGHT CHANDELIER

P400026-020 Antique Bronze
28-1/2" dia., 39-1/2" ht.
Overall ht. w/chain 114-1/2"; wire 15'.
Six candelabra base lamps,
each 60w max.

FIVE-LIGHT CHANDELIER

P400117-020 Antique Bronze
33-3/4" dia., 27-7/8" ht.
Overall ht. w/chain 103", wire 15'.
Five candelabra base lamps,
each 60w max.

*All fixtures shown with P7826-01
vintage lamps, not included.*

EVOKE

FINISH

- Polished Nickel - 104

THREE-LIGHT CHANDELIER

P400024-104 Polished Nickel
17-5/8" dia., 28-1/2" ht.
Overall ht. w/chain 103-1/2"; wire 15'.
Three candelabra base lamps,
each 60w max.

FIVE-LIGHT CHANDELIER

P400025-104 Polished Nickel
24-5/8" dia., 35-3/8" ht.
Overall ht. w/chain 110-1/2"; wire 15'.
Five candelabra base lamps,
each 60w max.

SIX-LIGHT CHANDELIER

P400026-104 Polished Nickel
28-1/2" dia., 39-1/2" ht.
Overall ht. w/chain 114-1/2"; wire 15'.
Six candelabra base lamps,
each 60w max.

FIVE-LIGHT CHANDELIER

P400117-104 Polished Nickel
33-3/4" dia., 27-7/8" ht.
Overall ht. w/chain 103"; wire 15'.
Five candelabra base lamps,
each 60w max.

*All fixtures shown with P7826-01
vintage lamps, not included.*



P400117-104



P400024-104



P400026-104




P400025-104



P400117-104

NOMA

Mixed finishes, such as Polished Nickel with silver ridge accents and Antique Bronze with champagne accents are highlighted in Noma. Soft angles and curving lines created from flat metal straps elegantly frame etched white glass shades.



P400012-020



P350034-020



P400011-020



P400014-020



P400013-020



P500007-020



P350035-020

P710005-020

COLLECTIONS

FINISH

- Antique Bronze - 020

PAIR WITH

- Ratio
- Evolve

SEMI-FLUSH CONVERTIBLE

P350034-020 Antique Bronze Hanging and ceiling mount hardware included. 15-5/8" dia., 12-1/2" ht. Overall ht. w/chain 51-1/2"; wire 10'. Two medium base lamps, each 100w max.

THREE-LIGHT CHANDELIER

P400011-020 Antique Bronze 23" dia., 17-7/8" ht. Overall ht. w/chain 92-1/2"; wire 15'. Three medium base lamps, each 100w max.

FIVE-LIGHT CHANDELIER

P400012-020 Antique Bronze 28-1/2" dia., 26" ht. Overall ht. w/chain 101"; wire 15'. Five medium base lamps, each 100w max.

NINE-LIGHT CHANDELIER

P400013-020 Antique Bronze Two-tier. 34" dia., 32" ht. Overall ht. w/chain 155"; wire 15'. Nine medium base lamps, each 100w max.

FOUR-LIGHT FOYER PENDANT

P400014-020 Antique Bronze 16" dia., 29-1/4" ht. Overall ht. w/chain 104"; wire 15'. Four candelabra base lamps, each 60w max.

MINI-PENDANT

P500007-020 Antique Bronze 7-3/8" dia., 6-1/2" ht. Overall ht. w/stem 72-1/2"; wire 10'. One medium base lamp, 100w max.

WALL BRACKET

P710005-020 Antique Bronze 7-3/8" W., 18-5/8" ht. Extends 8-3/8". H/CTR 6-3/4". One medium base lamp, 100w max.

TWO-LIGHT FLUSH MOUNT

P350035-020 Antique Bronze 14-7/8" dia., 7-3/4" ht. Two medium base lamps, each 60w max.

NOMA

FINISH

● Polished Nickel - 104

SEMI-FLUSH CONVERTIBLE

P350034-104 Polished Nickel
Hanging and ceiling mount hardware included.
15-5/8" dia., 12-1/2" ht.
Overall ht. w/chain 51-1/2"; wire 10'.
Two medium base lamps, each 100w max.

THREE-LIGHT CHANDELIER

P400011-104 Polished Nickel
23" dia., 17-7/8" ht.
Overall ht. w/chain 92-1/2"; wire 15'.
Three medium base lamps, each 100w max.

FIVE-LIGHT CHANDELIER

P400012-104 Polished Nickel
28-1/2" dia., 26" ht.
Overall ht. w/chain 101"; wire 15'.
Five medium base lamps, each 100w max.

NINE-LIGHT CHANDELIER

P400013-104 Polished Nickel
Two-tier.
34" dia., 32" ht.
Overall ht. w/chain 155"; wire 15'.
Nine medium base lamps, each 100w max.

FOUR-LIGHT FOYER PENDANT

P400014-104 Polished Nickel
16" dia., 29-1/4" ht.
Overall ht. w/chain 104"; wire 15'.
Four candelabra base lamps, each 60w max.

MINI-PENDANT

P500007-104 Polished Nickel
7-3/8" dia., 6-1/2" ht.
Overall ht. w/stem 72-1/2"; wire 10'.
One medium base lamp, 100w max.

WALL BRACKET

P710005-104 Polished Nickel
7-3/8" W., 18-5/8" ht.
Extends 8-3/8". H/CTR 6-3/4".
One medium base lamp, 100w max.

TWO-LIGHT FLUSH MOUNT

P350035-104 Polished Nickel
14-7/8" dia., 7-3/4" ht.
Two medium base lamps, each 60w max.



P400012-104



P350034-104



P400011-104



P400014-104



P400013-104



P500007-104



P350035-104

P710005-104

WEST VILLAGE

A modern form with industrial-inspired accents are featured in West Village. Double prismatic glass shades provide a beautiful illumination effect. Visual interest continues with a three-spoke frame that holds each glass shade. Antique Bronze with antique brass accents or Brushed Nickel with chrome accents provide touches of mixed metal in all fixtures within the collection.



ALSO AVAILABLE IN
Bath, page 300



P400009-020



P400008-020



P500006-020



P400010-020



P300004-020



P350032-020



P350032-020

COLLECTIONS

FINISH

● Antique Bronze - 020

PAIR WITH

Union Square
Remix

WALL BRACKET

P300004-020 Antique Bronze
5-1/8" W., 8-1/8" ht.
Extends 7". H/CTR 4-1/8".
One medium base lamp,
100w max.

SEMI-FLUSH CONVERTIBLE

P350032-020 Antique Bronze
Hanging and ceiling mount
hardware included.
13-1/2" dia., 9-1/4" ht.
Overall ht. w/stem 75"; wire 15'.
One medium base lamp,
100w max.

THREE-LIGHT CHANDELIER

P400008-020 Antique Bronze
20" dia., 16-1/8" ht.
Overall ht. w/stem 82-1/2"; wire 15'.
Three medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER

P400009-020 Antique Bronze
25" dia., 20-1/8" ht.
Overall ht. w/stem 86-1/2"; wire 15'.
Five medium base lamps,
each 100w max.

NINE-LIGHT CHANDELIER

P400010-020 Antique Bronze
31-1/4" dia., 20-3/8" ht.
Overall ht. w/stem 86-1/2"; wire 15'.
Nine medium base lamps,
each 100w max.

MINI-PENDANT

P500006-020 Antique Bronze
5-1/8" dia., 7-5/8" ht.
Overall ht. w/stem 74"; wire 10'.
One medium base lamp,
100w max.

WEST VILLAGE

FINISH

● Brushed Nickel - 009

WALL BRACKET

P300004-009 Brushed Nickel
5-1/8" W., 8-1/8" ht.
Extends 7". H/CTR 4-1/8".
One medium base lamp,
100w max.

SEMI-FLUSH CONVERTIBLE

P350032-009 Brushed Nickel
Hanging and ceiling mount
hardware included.
13-1/2" dia., 9-1/4" ht.
Overall ht. w/stem 75"; wire 15'.
One medium base lamp,
100w max.

THREE-LIGHT CHANDELIER

P400008-009 Brushed Nickel
20" dia., 16-1/8" ht.
Overall ht. w/stem 82-1/2"; wire 15'.
Three medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER

P400009-009 Brushed Nickel
25" dia., 20-1/8" ht.
Overall ht. w/stem 86-1/2"; wire 15'.
Five medium base lamps,
each 100w max.

NINE-LIGHT CHANDELIER

P400010-009 Brushed Nickel
31-1/4" dia., 20-3/8" ht.
Overall ht. w/stem 86-1/2"; wire 15'.
Nine medium base lamps,
each 100w max.

MINI-PENDANT

P500006-009 Brushed Nickel
5-1/8" dia., 7-5/8" ht.
Overall ht. w/stem 74"; wire 10'.
One medium base lamp,
100w max.



P400009-009



P400008-009



P500006-009



P400010-009



P300004-009



P350032-009



P350032-009

GLIMMER

Elements that sparkle create an instant statement within the home - Glimmer fits the definition of livable luxury. Prismatic glass pendants are supported by an architecturally styled frame in Silver Ridge or Antique Bronze finishes.



P5321-134



P2326-134



P2326-20



P5321-134



P5321-20



P5346-134



P5346-20

COLLECTIONS

FINISHES

- Antique Bronze - 20
- Silver Ridge - 134

PAIR WITH

- Equinox
- Desiree
- Anjoux

SEMI-FLUSH CONVERTIBLE

P2326-20 Antique Bronze
P2326-134 Silver Ridge
 Hanging and ceiling mount hardware included.
 16-1/4" dia., 19" ht.
 Overall ht. w/chain 96-1/2", wire 10'.
 Three candelabra base lamps, each 60w max.

FIVE-LIGHT PENDANT

P5321-20 Antique Bronze
P5321-134 Silver Ridge
 22-1/4" dia., 23-7/8" ht.
 Overall ht. w/chain 99", wire 10'.
 Five candelabra base lamps, each 60w max.

SIX-LIGHT PENDANT

P5346-134 Silver Ridge
P5346-20 Antique Bronze
 28" dia., 29-1/4" ht.
 Overall ht. w/chain 104-1/2", wire 10'.
 Six candelabra base lamps, each 60w max.

GLIMMER

FINISHES

- Antique Bronze - 020
- Silver Ridge - 134

SEMI-FLUSH CONVERTIBLE

P350058-020 Antique Bronze
P350058-134 Silver Ridge
 Hanging and ceiling mount hardware included.
 13-5/8" Sq., 11-1/8" ht.
 Overall ht. w/stem 49-1/2", wire 10'.
 Two medium base lamps, each 60w max.

FOUR-LIGHT LINEAR CHANDELIER

P400101-020 Antique Bronze
P400101-134 Silver Ridge
 33-7/8" W., 11-1/2" L. 11" ht.
 Overall ht. w/stem 76", wire 15'.
 Four medium base lamps, each 60w max.

FOUR-LIGHT PENDANT

P500109-020 Antique Bronze
P500109-134 Silver Ridge
 20-1/8" Sq., 11" ht.
 Overall ht. w/stem 77", wire 10'.
 Four medium base lamps, each 60w max.



P350058-020



P350058-134



P500109-020



P500109-134



P400101-020



P400101-134



P5320-134



P5320-20



P2325-134



P2325-20



P2325-134



P2325-20



P7198-134



P7198-20

GLIMMER

FINISHES

- Antique Bronze - 20
- Silver Ridge - 134

SEMI-FLUSH CONVERTIBLE

P2325-20 Antique Bronze
P2325-134 Silver Ridge
 Hanging and ceiling mount hardware included.
 13-1/8" dia., 15-1/2" ht.
 Overall ht. w/chain 94", wire 10'.
 Three candelabra base lamps, each 60w max.

MINI-PENDANT

P5320-20 Antique Bronze
P5320-134 Silver Ridge
 6" dia., 11-1/4" ht.
 Overall ht. w/stem 77-1/2", wire 10'.
 One medium base lamp, 100w max.

WALL SCONCE

P7198-134 Silver Ridge
P7198-20 Antique Bronze
 8" W., 10" ht.
 Extends 4-3/4". H/CTR 3-1/2".
 Two candelabra base lamps, each 60w max.

STRATHAM

Stratham's signature focal point features a sparkly string of alternating drops of cylindrical and crystal orb beads. Large in scale, while delicate in details, the chandelier and semi-flush options showcase a stunning, faceted K9 glass column. Upward arching candelabra arms feature a soft Brushed Nickel finish and add visual interest for a variety of applications. Off white silk shades available separately for chandelier and semi-flush fixtures.



P400160-009
shown w/ P8704-01



P350118-009
shown as semi-flush



P350118-009



P710053-009



P400160-009



P400161-009

COLLECTIONS

FINISH

● Brushed Nickel - 009

PAIR WITH

Carriage Hill
Glimmer
Celeste

SEMI-FLUSH CONVERTIBLE

P350118-009 Brushed Nickel
Hanging and ceiling mount
hardware included.
19" dia., 16-3/4" ht.
Overall ht. w/chain 56", wire 10'.
Four candelabra base lamps,
each 60w max.

FIVE-LIGHT CHANDELIER

P400160-009 Brushed Nickel
27-1/4" dia., 25-1/2" ht.
Overall ht. w/chain 101", wire 15'.
Five candelabra base lamps,
each 60w max.

NINE-LIGHT CHANDELIER

P400161-009 Brushed Nickel
Two-tier.
35-1/8" dia., 42" ht.
Overall ht. w/chain 164-1/2", wire 15'.
Nine candelabra base lamps,
each 60w max.

WALL BRACKET

P710053-009 Brushed Nickel
4-1/2" W., 14-1/8" ht.
Extends 5-3/4". H/CTR 6-3/4".
One candelabra base lamp,
60w max.

ACCESSORY SHADE

P8704-01 White Fabric
1" uno-style fitter.
5-1/2" dia., 4-3/4" ht.



P8704-01

DESIREE

The Desiree collection features luxury materials and details reminiscent of Hollywood's Regency period. A Silver Ridge finish and clear crystal strands cascade in a waterfall effect to convey the glitz and glamour from an iconic time that is making a modern comeback.



P400079-134



P350106-134



P400078-134



P400100-134



P500085-134



P500086-134



P710030-134

COLLECTIONS

FINISH

- Silver Ridge - 134

PAIR WITH

- Landree
- Celeste

SEMI-FLUSH CONVERTIBLE

P350106-134 Silver Ridge
Hanging and ceiling mount hardware included.
15-7/8" dia., 14" ht.
Overall ht. w/chain 53", wire 10'.
Three candelabra base lamps, each 60w max.

FIVE-LIGHT CHANDELIER

P400078-134 Silver Ridge
28" dia., 24" ht.
Overall ht. w/chain 99", wire 15'.
Five candelabra base lamps, each 60w max.

SIX-LIGHT LINEAR CHANDELIER

P400079-134 Silver Ridge
38" W., 13-3/4" ht., 12" d.
Overall ht. w/chain 103-3/4", wire 15'.
Six candelabra base lamps, each 60w max.

EIGHT-LIGHT CHANDELIER

P400100-134 Silver Ridge
36" dia., 30-3/4" ht.
Overall ht. w/chain 106", wire 15'.
Eight candelabra base lamps, each 60w max.

THREE-LIGHT FOYER

P500085-134 Silver Ridge
13-7/8" dia., 19-3/8" ht.
Overall ht. w/chain 94-1/2", wire 15'.
Three candelabra base lamps, each 60w max.

SIX-LIGHT FOYER

P500086-134 Silver Ridge
17-7/8" dia., 29" ht.
Overall ht. w/chain 104", wire 15'.
Six candelabra base lamps, each 60w max.

WALL SCONCE

P710030-134 Silver Ridge
8-1/4" W., 13-5/8" ht.
Extends 5-3/8". H/CTR 6-3/4".
One candelabra base lamp, 60w max.

MARCHÉ

Marché is an eclectic arrangement of gleaming metal turnings, which recreates the vintage styles found in Parisian neighborhood markets. Polished Nickel elements are combined with a luxurious sheer silver organza shade and clear K9 glass elements. Coordinate with Nissé or Caress collections to create a truly distinctive addition to your home.



P400049-104



P400049-104



P500043-104



P710013-104



P350029-104

COLLECTIONS

FINISH

- Polished Nickel - 104

PAIR WITH

- Glimmer
- Glaysé

SEMI-FLUSH CONVERTIBLE

P350029-104 Polished Nickel Hanging and ceiling mount hardware included. 18" dia., 14" ht. Overall ht. w/chain 55", wire 10'. Three candelabra base lamps, each 60w max.

FIVE-LIGHT CHANDELIER

P400049-104 Polished Nickel 28" dia., 25-1/8" ht. Overall ht. w/chain 100", wire 15'. Five candelabra base lamps, each 60w max.

FOUR-LIGHT PENDANT

P500043-104 Polished Nickel 22" dia., 20" ht. Overall ht. w/chain 95", wire 15'. Four candelabra base lamps, each 60w max.

WALL BRACKET

P710013-104 Polished Nickel 6-7/8" W., 12-1/4" ht. Extends 10-1/2". H/CTR 6-5/8". One candelabra base lamp, 60w max.

CELESTE

Celeste features elegant modern design for an updated traditional appeal. The frame is composed of opposing arched forms to create a beautiful asymmetrical design from any vantage point. Etched opal glass shades add a classic detail to the open frame, while a brilliant Polished Nickel finish completes the design. A perfect choice for Luxe and Mid-Century Modern interiors.



P500124-104



P500123-104



P500124-104

FINISH

- Polished Nickel - 104

PAIR WITH

Tinsley
Landree

MINI-PENDANT

P500123-104 Polished Nickel
10" sq., 14-3/8" ht.
Overall ht. w/stem 80-1/2", wire 10'.
One medium base lamp,
100w max.

FOUR-LIGHT PENDANT

P500124-104 Polished Nickel
15-1/8" sq., 23-5/8" ht.
Overall ht. w/stem 89-1/2", wire 15'.
Four candelabra base lamps,
each 60w max.

BONITA NEW

Inspired at its roots by an understated beauty and a breathtaking formal elegance, the Bonita collection makes a stunning addition to any luxurious living space. This gaze-grabbing modern collection grants a slight nod to antique candle-like fixtures with graceful, arrow drum shades held in place by light bases supported by elegantly curved arms. Bonita's signature elegant design is ideal for illuminating family meals at your dining table or around a kitchen island.



P400227-012



P400227-012



P400227-031



P500285-012



P500285-031



P710018-012

P710019-012



P710018-031

P710019-031

COLLECTIONS

FINISHES

- Satin Brass - 012
- Matte Black - 031

PAIR WITH

Celeste
Carriage Hill

SIX-LIGHT CHANDELIER

P400227-012 Satin Brass
P400227-031 Matte Black
30-1/2" dia., 24" ht.
Overall ht. w/stem 90", wire 15'.
Six candelabra base lamps,
each 40w max.

FOUR-LIGHT FOYER

P500285-012 Satin Brass
P500285-031 Matte Black
23" dia., 25-7/8" ht.
Overall ht. w/stem 92", wire 15'.
Four candelabra base lamps,
each 40w max.

WALL BRACKET

P710018-012 Satin Brass
P710018-031 Matte Black
4-1/2" W., 17-1/8" ht.
Extends 6-7/8". H/CTR 13-5/8".
One candelabra base lamp,
40w max.

WALL BRACKET

P710019-012 Satin Brass
P710019-031 Matte Black
13-5/8" W., 17-1/4" ht.
Extends 6-7/8". H/CTR 13-5/8".
Two candelabra base lamps,
each 40w max.

BONITA



P400227-015 **N**



P400227-009 **N**



P500285-015 **N**



P500285-009 **N**



P710018-015 P710019-015



P710018-009 P710019-009



P710018-020 P710019-020

FINISHES

- Brushed Nickel - 009
- Polished Chrome - 015
- Antique Bronze - 20

SIX-LIGHT CHANDELIER

P400227-009 Brushed Nickel
P400227-015 Polished Chrome
 30-1/2" dia., 24" ht.
 Overall ht. w/stem 90", wire 15'.
 Six candelabra base lamps,
 each 40w max.

FOUR-LIGHT FOYER

P500285-009 Brushed Nickel
P500285-015 Polished Chrome
 23" dia., 25-7/8" ht.
 Overall ht. w/stem 92", wire 15'.
 Four candelabra base lamps,
 each 40w max.

WALL SCONCE

P710018-009 Brushed Nickel
P710018-015 Polished Chrome
P710018-020 Antique Bronze
 4-1/2" W., 17-1/8" ht.
 Extends 6-7/8". H/CTR 13-5/8".
 One candelabra base lamp,
 40w max.

WALL SCONCE

P710019-009 Brushed Nickel
P710019-015 Polished Chrome
P710019-020 Antique Bronze
 13-5/8" W., 17-1/4" ht.
 Extends 6-7/8". H/CTR 13-5/8".
 Two candelabra base lamps,
 each 40w max.

N New Product

SAVOR

Savor is a soft blend of sweeping details and contemporized wrought iron craftsmanship making it suitable for a wide variety of home décor styles. Sheer sailcloth textured shades are integral to the design.



P400075-134



P350092-134



P500080-134



P500081-134



P400076-134



P710029-134



P400076-134

COLLECTIONS

FINISH

- Silver Ridge - 134

PAIR WITH

- Glimmer
- Desiree

SEMI-FLUSH CONVERTIBLE

P350092-134 Silver Ridge
Hanging and ceiling mount hardware included.
17" dia., 15-1/2" ht.
Overall ht. w/chain 56-1/2", wire 10'.
Four candelabra base lamps, each 60w max.

SIX-LIGHT CHANDELIER

P400075-134 Silver Ridge
33" dia., 27-1/2" ht.
Overall ht. w/chain 102-1/2", wire 15'.
Six candelabra base lamps, each 60w max.

TEN-LIGHT CHANDELIER

P400076-134 Silver Ridge
38" dia., 35-3/4" ht.
Overall ht. w/chain 159", wire 15'.
Ten candelabra base lamps, each 60w max.

MINI-PENDANT

P500080-134 Silver Ridge
10" dia., 14-1/2" ht.
Overall ht. w/stem 80-1/2", wire 10'.
One medium base lamp, 100w max.

SIX-LIGHT PENDANT

P500081-134 Silver Ridge
24" dia., 25-1/4" ht.
Overall ht. w/chain 100-1/2", wire 15'.
Six candelabra base lamps, each 60w max.

WALL BRACKET

P710029-134 Silver Ridge
6-5/8" W., 18" ht.
Extends 8". H/CTR 9-3/4".
One candelabra base lamp, 60w max.

BERGAMO

Bergamo features an elegant wispieness within a two-toned frame. Weathered stone accents and tassel details create a relaxed, rustic casual collection. These versatile pieces can be incorporated over a dining room table in a Rustic Farmhouse setting or in a Transitional open living space. Wall bracket, chandelier and foyer fixture options are available.



P400068-077



P400068-077



P400069-077



P400070-077



P710032-077



P500091-077

COLLECTIONS

FINISH

● Forged Bronze - 077

PAIR WITH

Bowman
Gresham

FIVE-LIGHT CHANDELIER

P400068-077 Forged Bronze
26" dia., 27-7/8" ht.
Overall ht. w/chain 103", wire 15'.
Five candelabra base lamps,
each 60w max.

SIX-LIGHT CHANDELIER

P400069-077 Forged Bronze
32" dia., 33-3/8" ht.
Overall ht. w/chain 108-1/2", wire 15'.
Six candelabra base lamps,
each 60w max.

TWELVE-LIGHT CHANDELIER

P400070-077 Forged Bronze
42-1/8" dia., 46-7/8" ht.
Overall ht. w/chain 170", wire 15'.
Twelve candelabra base lamps,
each 60w max.

FOUR-LIGHT FOYER

P500091-077 Forged Bronze
18-3/4" dia., 42-1/8" ht.
Overall ht. w/chain 117-1/2", wire 15'.
Four candelabra base lamps,
each 60w max.

WALL BRACKET

P710032-077 Forged Bronze
6" W., 17-1/4" ht.
Extends 7-5/8". H/CTR 6".
One candelabra base lamp,
60w max.

ALLAIRE

Alternating oval and round vintage beads create beautiful strands that are completed by a large faceted glass pendalog. Champagne candles and an Antique Bronze finish add to the sophisticated design details. Two shade styles, both featuring a rich Espresso trim, are available as accessories.



P400004-020 with
P860000-001 shade



P400004-020



P400004-020
shown with
P860001-001 shade



P400004-020
shown with
P860000-001 shade

COLLECTIONS

FINISH

● Antique Bronze - 020

PAIR WITH

Evoke
Noma

FIVE-LIGHT CHANDELIER

P400004-020 Antique Bronze
26" dia., 30-3/4" ht.
Overall ht. w/chain 108-1/2"; wire 15'.
Five candelabra base lamps,
each 60w max.

ACCESSORY SHADE

P860000-001 Champagne
silk with espresso trim.
1" uno-style candle fitter.
5" dia., 5" ht.

ACCESSORY SHADE

P860001-001 Champagne
organza with espresso trim.
1" uno-style candle fitter.
5" dia., 5" ht.



P860001-001



P860000-001

ALLAIRE

FINISH

● Antique Bronze - 020

SEMI-FLUSH CONVERTIBLE

P350030-020 Antique Bronze
Hanging and ceiling mount hardware included. Accessory shades do not fit fixture.
16" dia., 12-7/8" ht.
Overall ht. w/chain 52"; wire 10'.
Three candelabra base lamps, each 40w max.

EIGHT-LIGHT CHANDELIER

P400005-020 Antique Bronze
32" dia., 31" ht.
Overall ht. w/chain 108-1/2"; wire 15'.
Eight candelabra base lamps, each 60w max.

NINE-LIGHT CHANDELIER

P400006-020 Antique Bronze
32" dia., 35" ht.
Overall ht. w/chain 160"; wire 15'.
Nine candelabra base lamps, each 60w max.

WALL BRACKET

P710003-020 Antique Bronze
5-1/8" W., 20-5/8" ht.
Extends 6-3/4". H/CTR 12".
One candelabra base lamp, 60w max.



P710003-020



P710003-020
shown with
P860000-001 shade



P710003-020
shown with
P860001-001 shade



P400005-020



P400005-020
shown with
P860001-001 shade



P400006-020



P400006-020
shown with
P860000-001 shade



P350030-020



P350030-020
shown as semi-flush

WESTFALL

Westfall is a combination of arching elements that create a dramatic soaring frame. A dual-tone finish highlights the distinctive form. Metal fittings add a touch of elegance and dimension to further enhance the classic architectural form.



P500040-143



P500038-020



P500038-143



P500039-020
Shown with
Antique Bronze
candle covers



P500039-143



P500040-020



P500040-143

COLLECTIONS

FINISHES

- Antique Bronze - 020
- Graphite - 143

PAIR WITH

Noma
Allaire

FOUR-LIGHT FOYER

P500038-020 Antique Bronze
P500038-143 Graphite
10-1/8" sq., 19-5/8" ht.
Overall ht. w/chain 94-1/2", wire 15'.
Four candelabra base lamps,
each 60w max.

FOUR-LIGHT FOYER

P500039-020 Antique Bronze
P500039-143 Graphite
13-7/8" sq., 25-1/8" ht.
Overall ht. w/chain 100", wire 15'.
Four candelabra base lamps,
each 60w max.

EIGHT-LIGHT FOYER

P500040-020 Antique Bronze
P500040-143 Graphite
19-3/4" sq., 33-1/8" ht.
Overall ht. w/chain 156", wire 15'.
Eight candelabra base lamps,
each 60w max.

Note: Antique Bronze fixtures include Vintage Brass and Antique Bronze candle covers for additional customization.

All fixtures shown with P7826-01 vintage lamps, not included.

ASSEMBLY HALL

Assembly Hall provides a formal and classic open caged pendant for a variety of traditional and transitional interiors. Available in two sizes, arching frames are great in scale and surround a candelabra with matching candles – Antique Bronze fixtures also include vintage brass candles for additional customization.



P500036-020



P500036-009



P500036-020
Shown with
Antique Bronze
candle covers



P500037-009



P500037-020

COLLECTIONS

FINISHES

- Brushed Nickel - 009
- Antique Bronze - 020

PAIR WITH
Bergamo
Durrell

FOUR-LIGHT FOYER

P500036-009 Brushed Nickel
P500036-020 Antique Bronze
15" sq., 26" ht.
Overall ht. w/chain 100"; wire 15'.
Four candelabra base lamps,
each 60w max.

SIX-LIGHT FOYER

P500037-009 Brushed Nickel
P500037-020 Antique Bronze
20" sq., 32-3/4" ht.
Overall ht. w/chain 106-1/2"; wire 15'.
Six candelabra base lamps,
each 60w max.

*Note: Antique Bronze fixtures
include Vintage Brass and
Antique Bronze candle covers
for additional customization.*

*All fixtures shown with P7826-01
vintage lamps, not included.*

MARQUE

With clear seeded glass in the Graphite finish, this vintage pendant family can be used as a sleek substitute for chandeliers in a variety of living spaces, including foyers and hallways.



P3598-143



P3601-143



P5073-143



P3598-143

COLLECTIONS

FINISH

- Graphite - 143

PAIR WITH

Remix

ONE-LIGHT FOYER

P3598-143 Graphite
12" dia., 19-3/4" ht.
Overall ht. w/stem 86"; wire 15'.
One medium base lamp,
100w max.

THREE-LIGHT FOYER

P3601-143 Graphite
18" dia., 28-3/4" ht.
Overall ht. w/stem 95"; wire 15'.
Three medium base lamps,
each 100w max.

MINI-PENDANT

P5073-143 Graphite
7-3/4" dia., 9-1/4" ht.
Overall ht. w/stem 75-1/4"; wire 10'.
One medium base lamp,
100w max.

*All fixtures shown with P7825-01
vintage lamps, not included.*

CINQ NEW

Cinq finds inspiration from modern geometric designs and the beauty of contrasting elements. Five-sided bottom panels are outlined in an Antique Bronze finish with antique mirrored glass or Brushed Nickel finish with clear seeded glass lower panels, while the upper panels are comprised of clear glass.



P5322-20



P5322-20



P5322-09 N



P5319-20



P5319-09 N



P3868-20



P3868-09 N

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20

PAIR WITH
Draper

ONE-LIGHT PENDANT

P5319-09 Brushed Nickel
P5319-20 Antique Bronze
12" dia., 18-1/2" ht.
Overall ht. w/stem 84-1/2", wire 10'
One medium base lamp,
100w max.

THREE-LIGHT PENDANT

P5322-09 Brushed Nickel
P5322-20 Antique Bronze
19" dia., 25-7/8" ht.
Overall ht. w/stem 92", wire 10'.
Three medium base lamps,
each 100w max.

ONE-LIGHT FLUSH MOUNT

P3868-09 Brushed Nickel
P3868-20 Antique Bronze
12" dia., 9-1/4" ht.
One medium base lamp,
100w max.

*All fixtures shown with P7825-01
vintage lamps, not included.*

N New Product



PENDANTS

MAULDIN NEW

Enjoy the generous, antique glow of the simply charming Maudlin Collection. Geometric frames and clear seeded glass panes foster a soft, vintage demeanor and recall memories of raindrops clinging to windows during a summer evening thunderstorm.



P500221-009



P500221-031



P500221-009

PENDANTS

FINISHES

- Brushed Nickel - 009
- Black - 031

ONE-LIGHT PENDANT

P500221-009 Brushed Nickel
P500221-031 Black
 12" sq., 19-7/8" ht.
 Overall ht. w/chain 82", wire 10".
 One medium base lamp,
 100w max.

THREE-LIGHT PENDANT

P500222-009 Brushed Nickel
P500222-031 Black
 17" sq., 27-1/4" ht.
 Overall ht. w/chain 89-1/2", wire 10".
 Three medium base lamps,
 each 60w max.



P500222-031



P500222-009

SINCLAIRE

Sinclair features a tapered frame and airy design complemented by a Gold Leaf and Black finish. While Sinclair pendants are suitable in Modern and Luxe environments, the elegant details are comprised of elements that be found in popular outdoor markets showcasing vintage and antique treasures. Available in two sizes.



P500163-031



P500161-031



P500163-031

FINISH

● Black - 031

ONE-LIGHT PENDANT

P500161-031 Black
14" dia., 14" ht.
Overall ht. w/chain 88", wire 10'.
One medium base lamp,
75w max.

ONE-LIGHT PENDANT

P500163-031 Black
20" dia., 23" ht.
Overall ht. w/chain 97", wire 10'.
One medium base lamp,
75w max.

GALLEY

Galley is a simple modern form that complements both coastal décor and commercial style kitchens. The arched supporting frame features overscale metal turnings for an enhanced sense of architectural styling. The linen shades are comprised of rich, satin lining for the feel of a tailored fit and finish to complement the multi-light cluster.



P500047-020



P500046-020



P500046-104



P500047-020



P500047-104

PENDANTS

FINISHES

- Antique Bronze - 020
- Polished Nickel - 104

TWO-LIGHT PENDANT

P500046-020 Antique Bronze
P500046-104 Polished Nickel
 15" dia., 18" ht.
 Overall ht. w/stem 84", wire 10'.
 Two medium base lamps,
 each 75w max.

THREE-LIGHT PENDANT

P500047-020 Antique Bronze
P500047-104 Polished Nickel
 21" dia., 24-1/2" ht.
 Overall ht. w/stem 90-1/2", wire 10'.
 Three medium base lamps,
 each 75w max.

ELLYSON

Clear prismatic glass creates a sophisticated, spherical globe in Ellyson. Influenced by mid century aesthetics, the glass is highlighted by simple accents finished in Polished Chrome or Brushed Bronze. From Mid-Century Modern to Luxe and Vintage Electric to Coastal, these pendants enhance a variety of design styles and can be displayed singularly or in groupings of two or more.



P500118-015



P500118-015



P500118-109

PENDANTS

FINISHES

- Polished Chrome - 015
- Brushed Bronze - 109

ONE-LIGHT PENDANT

P500118-015 Polished Chrome
P500118-109 Brushed Bronze
18-3/8" dia., 24" ht.
Overall ht. w/stem 90", wire 10'.
One medium base lamp,
100w max.

STAUNTON

Inspired by the stacked modern elements of items found in Parisian boutiques, Staunton's chess piece silhouette offers a signature focal point. Available in three shapes and color variations – they can be grouped as a single style or mixed and matched to offer a more eclectic look. All pendants feature a vintage, woven cloth cord.



P5332-20



P5332-09



P5332-20



P5332-143



P5333-09



P5333-20



P5333-143



P5334-09



P5334-20



P5334-143

PENDANTS

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20
- Graphite - 143

ONE-LIGHT PENDANT

P5332-09 Brushed Nickel with clear glass
P5332-20 Antique Bronze with champagne glass
P5332-143 Graphite with smoked glass
 12" dia., 11-1/4" ht.
 Overall ht. w/cord 125-1/2"; cord 10'.
 One medium base lamp, 75w max.

ONE-LIGHT PENDANT

P5333-09 Brushed Nickel with clear glass
P5333-20 Antique Bronze with champagne glass
P5333-143 Graphite with smoked glass
 9" dia., 16-1/2" ht.
 Overall ht. w/cord 124"; cord 10'.
 One medium base lamp, 75w max.

ONE-LIGHT PENDANT

P5334-09 Brushed Nickel with clear glass
P5334-20 Antique Bronze with champagne glass
P5334-143 Graphite with smoked glass
 8 1/2" dia., 12-3/4" ht.
 Overall ht. w/cord 126-1/2"; cord 10'.
 One medium base lamp, 75w max.

CHRONICLE

Chronicle pendants add visual interest and are ideal for commercial-style home kitchens or vintage dining areas. A metal accent ring adds a finishing touch on the glass globe. Clear seeded glass with an Antique Bronze frame.



P5311-20



P5309-20



P5311-20

PENDANTS

FINISH

- Antique Bronze - 20

ONE-LIGHT MINI-PENDANT

P5309-20 Antique Bronze
8" dia., 9" ht.
Overall ht. w/stem 75"; wire 10'.
One medium base lamp,
100w max.

ONE-LIGHT PENDANT

P5311-20 Antique Bronze
12" dia., 13" ht.
Overall ht. w/stem 79"; wire 10'.
One medium base lamp,
100w max.

*All fixtures shown with P7825-01
vintage lamp, not included.*

ZIN

Inspired by a beautiful wine cask design, the Zin pendants are artfully formed from one large piece of glass. Create a customized look for Rustic Farmhouse and Modern Farmhouse to Urban Industrial settings by grouping several pendants together in a kitchen, entryway or living room setting. Perfectly imperfect, the design offers dimension and visual texture.



P500064-143



P500064-009



P500064-020

PENDANTS

FINISHES

- Brushed Nickel - 009
- Antique Bronze - 020
- Graphite - 143

ONE-LIGHT PENDANT


P500064-009 Brushed Nickel with clear glass
P500064-020 Antique Bronze with light blue glass
P500064-143 Graphite with smoked glass
13" dia., 20-3/8" ht.
Overall ht. w/chain 95-1/2", wire 10'.
One medium base lamp, 100w max.



P500064-143

MALBEC

Artisanal glass and high quality craftsmanship offers a signature focal point in the Malbec pendants. Create a customized look suitable for designs from Bohemian to Coastal by grouping several pendants together in a kitchen, entryway or living room setting. Perfectly imperfect, the design offers dimension and visual interest.



P500063-009



P500063-009



P500063-020



P500063-143

PENDANTS

FINISHES

- Brushed Nickel - 009
- Antique Bronze - 020
- Graphite - 143

ONE-LIGHT PENDANT

P500063-009 Brushed Nickel with clear glass

P500063-020 Antique Bronze with light blue glass

P500063-143 Graphite with smoked glass

11-3/4" dia., 14" ht.

Overall ht. w/chain 89", wire 10'.

One medium base lamp, 100w max.

ERA

Achieve a vintage feel with Era's carefully crafted details and special eclectic accents. One light pendant or mini pendant options are available in Matte Black with gold leaf accents.



P500033-031



P500098-031



P500032-031



P500033-031

PENDANTS

FINISH

- Matte Black - 031

MINI-PENDANT

P500032-031 Matte Black
6-3/8" dia., 11-3/4" ht.
Overall ht. w/cord 78"; cord 10'.
One medium base lamp,
60w max.

ONE-LIGHT PENDANT

P500033-031 Matte Black
8-3/8" dia., 16-3/4" ht.
Overall ht. w/cord 82-1/2"; cord 10'.
One medium base lamp,
75w max.

ONE-LIGHT PENDANT

P500098-031 Matte Black
12-3/4" dia., 25" ht.
Overall ht. w/cord 91"; wire 10'.
One medium base lamp,
75w max.

BEAKER

Beaker has a heightened sense of modern industrial styling. Available in two styles, each with their own unique character. These vessels are suspended from herringbone cloth cords. Available in two finishes, half clear, half mirrored glass with Polished Chrome frame or champagne glass with Antique Bronze frame.



P5344-1530K9



P7125-2030K9



P7117-1530K9



P5344-1530K9

PENDANTS

FINISHES

- Polished Chrome - 15
- Antique Bronze - 20

ONE-LIGHT LED MINI-PENDANT

P5344-1530K9 Polished Chrome
5" dia., 11-7/8" ht.
Overall ht. w/chain 122"; cord 10'.
One 9w LED module included,
3000K, 623 source lumens, 90 CRI.

ONE-LIGHT LED WALL BRACKET

P7117-1530K9 Polished Chrome
4-3/4" W., 17" ht.
Extends 9-1/8". H/CTR 4".
One 9w LED module included,
3000K, 623 source lumens, 90 CRI.

ONE-LIGHT LED WALL BRACKET

P7125-2030K9 Antique Bronze
10-1/4" W., 16-5/8" ht.
Extends 11-7/8". H/CTR 4".
One 9w LED module included,
3000K, 623 source lumens, 90 CRI.

All fixtures:



MESH

Mesh pendants offer an interweaving open cage frame that can serve as a focal point in any lighting design.



P5337-20



P5337-20



P5338-20

PENDANTS

FINISH

- Antique Bronze - 20

MINI-PENDANT

P5337-20 Antique Bronze
8-1/2" dia., 8-3/8" ht.
Overall ht. w/stem 74-1/2", wire 10'.
One medium base lamp,
100w max.


MINI-PENDANT

P5338-20 Antique Bronze
8-1/2" dia., 8-3/8" ht.
Overall ht. w/stem 74-1/2", wire 10'.
One medium base lamp,
100w max.

*All fixtures shown with P7827-01
vintage lamp, not included.*

FINN

Finn takes a new perspective on an open cage design. The beautifully graphic frame wraps around an etched white glass shade creating a focal aperture for a single lamp. Available in Matte Black and Metallic Silver finishes.



P5324-121



P5324-31



P5324-121

PENDANTS

FINISHES

- Matte Black - 31
- Metallic Silver - 121

MINI-PENDANT

P5324-31 Matte Black
P5324-121 Metallic Silver
10" dia., 10-1/2" ht.
Overall ht. w/stem 76-1/2", wire 10'.
One medium base lamp,
100w max.

RE-BAR

Re-Bar pendants are inspired by industrial and vintage electric elements, created from a common masonry structure with a steel reinforcing bar. The coarse material is paired with bright Chrome to provide an intriguing visual contrast. In addition to Urban Industrial and Vintage Electric styles, Re-Bar is ideal for updating Modern Farmhouse interiors.



P5001120-015



P500119-015



P5001120-015

PENDANTS

FINISH

- Polished Chrome - 015

MINI-PENDANT


P500119-015 Polished Chrome
12-1/2" Sq., 12-3/8" ht.
Overall ht. w/stem 78-1/2", wire 10'.
One medium base lamp,
60w max.

FOUR-LIGHT PENDANT

P500120-015 Polished Chrome
21-7/8" Sq., 23" ht.
Overall ht. w/stem 89", wire 15'.
Four medium base lamps,
each 60w max.

FERMI

Cloth cords and sculptural details create an open framework design. Fermi features a geometric frame finished in Brushed Nickel. Red cloth adds a playful contrast to create a unique visual statement. Consider decorative bulbs to further customize Fermi fixtures.



FINISH

● Brushed Nickel - 009

FIVE-LIGHT PENDANT

P500045-009 Brushed Nickel
17-3/8" dia., 9" ht.
Overall ht. w/stem 64-1/2", wire 15'.
Five candelabra base lamps,
each 60w max.

*Fixture shown with P7827-01
vintage lamp, not included.*

MODERNA

Moderna's modern-inspired silhouette provides a signature focal point for a variety of interior spaces. Features clear outer glass with an inner etched white glass shade and a sleek linear frame.



FINISH

● Brushed Nickel - 009

ONE-LIGHT LED MINI-PENDANT

P500000-009-30 Brushed Nickel
5-3/4" dia., 9-1/2" ht.
Overall ht. w/stem 75-1/2"; wire 10'.
One 9w LED module, 3000K,
90 CRI, 623 source lumens.



CARBON

Light spills out onto a streamlined shade in the Carbon pendant and mini- pendant. Etched white glass diffuser allows the light to illuminate the Graphite or Polished Nickel shade.



P500013-143



P500013-104



P500013-143

PENDANTS

FINISHES

- Polished Nickel - 104
- Graphite - 143

MINI-PENDANT

P500013-104 Polished Nickel
P500013-143 Graphite
11" dia., 8-1/4" ht.
Overall ht. w/stem 74-1/2"; wire 10'.
One medium base lamp,
100w max.



SCONCES

DESIGN+SERIES™

METRO

Metro delivers a clean, geometric form with a pleasing balance of angular metal fittings and a crisp linen shade. The stately fixture adds a modern accent with an elegant sense of architectural distinction.



P710016-020



P710016-015



P710016-009



P710016-020

SCONCES

FINISHES

- Brushed Nickel - 009
- Polished Chrome - 015
- Antique Bronze - 020

WALL BRACKET

P710016-009 Brushed Nickel
P710016-015 Polished Chrome
P710016-020 Antique Bronze
5-1/2" W., 15-1/8" ht.
Extends 7-1/4". H/CTR 10-1/2".
One candelabra base lamp,
60w max.

AVANA

Avana features a graceful tapered candle-arm with a crisp geometric linen shade. The faceted backplate provides a rich architectural detail that complements many fashionable vanity styles.



P710025-009



P710025-009



P710025-104

SCONCES

FINISHES

- Brushed Nickel - 009
- Polished Nickel - 104

WALL BRACKET

P710025-009 Brushed Nickel
P710025-104 Polished Nickel
5-5/8" W., 16" ht.
Extends 7-1/2". H/CTR 12-1/2".
One candelabra base lamp,
60w max.

BONITA

Bonita sconces have a traditional elegance to complement luxurious living with an understated beauty. Crisp metal fittings support a graceful frame and candle topped with a linen shade. Coordinate with Marché or Glimmer collections to add a variation of textures.



ALSO AVAILABLE IN
Collections, page 216



P710019-009



P710018-009



P710019-009



P710018-012



P710019-012



P710018-015



P710019-015



P710018-020



P710019-020



P710018-031



P710019-031



SCONCES

FINISHES

- Brushed Nickel - 009
- Satin Brass - 012
- Polished Chrome - 015
- Antique Bronze - 020
- Matte Black - 031

WALL BRACKET

P710018-009 Brushed Nickel
P710018-012 Satin Brass
P710018-015 Polished Chrome
P710018-020 Antique Bronze
P710018-031 Matte Black
 9" W., 17-1/4" ht.
 Extends 6-7/8". H/CTR 13-5/8".
 One candelabra base lamp,
 40w max.

WALL BRACKET

P710019-009 Brushed Nickel
P710019-012 Satin Brass
P710019-015 Polished Chrome
P710019-020 Antique Bronze
P710019-031 Matte Black
 13-5/8" W., 17-1/4" ht.
 Extends 6-7/8". H/CTR 13-5/8".
 Two candelabra base lamps,
 each 40w max.

HOBBS

Modern traditional design is the combination of crisp geometric forms in classic shapes and materials. Hobbs delivers on this concept with an elegant beveled glass diffuser framing a vintage lamp. The rectangular and circular fittings add a sense of classic craftsmanship for a timeless design.



P710017-009



P710017-009



P710017-015



P710017-020

SCONCES

FINISHES

- Brushed Nickel - 009
- Polished Chrome - 015
- Antique Bronze - 020

WALL SCONCE

P710017-009 Brushed Nickel
P710017-015 Polished Chrome
P710017-020 Antique Bronze
6" W., 12" ht.
Extends 4-7/8" H/CTR 6".
One medium base lamp,
60w max.

*All fixtures shown with P7827-01
vintage lamps, not included.*



BATH

GLAYSE

Inspired by modern architecture, Glayse features handsome details for variety of interior design styles. The frameless unbounded beveled glass creates beautiful light and reflection. The structure of Glayse is the focal point of the design, where form follows function.

ALSO AVAILABLE IN
Collections, page 146



P300106-009



P300106-009



P300105-009



P300107-009



P300106-020



P300105-020



P300107-020

FINISHES

- Brushed Nickel - 009
- Antique Bronze - 020

ONE-LIGHT BATH

P300105-009 Brushed Nickel
P300105-020 Antique Bronze
7" W., 8-3/8" ht.
Extends 5-1/2". H/CTR 5-3/8".
One medium base lamp,
60w max.

TWO-LIGHT BATH

P300106-009 Brushed Nickel
P300106-020 Antique Bronze
14-7/8" W., 8-3/8" ht.
Extends 5-1/2". H/CTR 5-3/8".
Two medium base lamps,
each 60w max.

THREE-LIGHT BATH

P300107-009 Brushed Nickel
P300107-020 Antique Bronze
22-3/4" W., 8-3/8" ht.
Extends 5-1/2". H/CTR 5-3/8".
Three medium base lamps,
each 60w max.

All fixtures shown with P7825-01
vintage lamps, not included.

All fixtures mount up or down.

UNION SQUARE

Union Square features a reproduction gas lantern inspiration. A Stainless Steel finish complements the natural polished material and clear flat glass panels. Mechanical details – such as exaggerated knobs – provide character to the form. Open top and bottom on fixture provides easy access for cleaning and relamping.



ALSO AVAILABLE IN

Collections, page 170
Outdoor, page 356



P300135-135



P710038-135
shown with P7825-01
vintage lamp



P710038-135
shown with P7827-01
vintage lamp

FINISH

- Stainless Steel - 135

ONE-LIGHT BATH

P710038-135 Stainless Steel
5-1/4" sq., 12" ht.
Extends 5". H/CTR 6".
One medium base lamp,
60w max.

TWO-LIGHT BATH

P300135-135 Stainless Steel
16" W., 4-1/2" ht.
Extends 5". H/CTR 2-1/4".
Two medium base lamps,
each 60w max.

FOUR-LIGHT BATH

P300136-135 Stainless Steel
30" W., 4-1/2" ht.
Extends 5". H/CTR 2-1/4".
Four medium base lamps,
each 60w max.



P300135-135
shown with P7825-01
vintage lamps



P300136-135
shown with P7827-01
vintage lamps

ELEVATE

Achieve a mid-century modern look with Elevate, which boasts glass shades and a frame inspired by modern styling. Brushed Bronze and Polished Chrome finish options also available.

ALSO AVAILABLE IN
Collections, page 134



P300021-031



P300021-031



P300020-031



P300022-031



P300023-031

FINISH

- Matte Black - 031

ONE-LIGHT BATH

P300020-031 Matte Black
5" W., 8" ht.
Extends 7". H/CTR 4".
One medium base lamp,
100w max.

TWO-LIGHT BATH

P300021-031 Matte Black
15-3/8" W., 7-1/2" ht.
Extends 6-1/8". H/CTR 5".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH

P300022-031 Matte Black
24-3/4" W., 7-1/2" ht
Extends 8". H/CTR 5".
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH

P300023-031 Matte Black
34-1/2" W., 7-1/2" ht.
Extends 8". H/CTR 5".
Four medium base lamps,
each 100w max.

All fixtures mount up or down.

ELEVATE

FINISH

● Brushed Bronze - 109

ONE-LIGHT BATH

P300020-109 Brushed Bronze
5" W., 8" ht.
Extends 7". H/CTR 4".
One medium base lamp,
100w max.



P300020-109



P300021-109

TWO-LIGHT BATH

P300021-109 Brushed Bronze
15-3/8" W., 7-1/2" ht.
Extends 6-1/8". H/CTR 5".
Two medium base lamps,
each 100w max.



P300022-109

THREE-LIGHT BATH

P300022-109 Brushed Bronze
24-3/4" W., 7-1/2" ht.
Extends 8". H/CTR 5".
Three medium base lamps,
each 100w max.



P300023-109

FOUR-LIGHT BATH

P300023-109 Brushed Bronze
34-1/2" W., 7-1/2" ht.
Extends 7-3/4". H/CTR 5".
Four medium base lamps,
each 100w max.

All fixtures mount up or down.

ELEVATE

FINISH

● Polished Chrome - 015

ONE-LIGHT BATH

P300020-015 Polished Chrome
5" W., 8" ht.
Extends 7". H/CTR 4".
One medium base lamp,
100w max.



P300021-015



P300020-015

TWO-LIGHT BATH

P300021-015 Polished Chrome
15-3/8" W., 7-1/2" ht.
Extends 6-1/8". H/CTR 5".
Two medium base lamps,
each 100w max.



P300022-015

THREE-LIGHT BATH

P300022-015 Polished Chrome
24-3/4" W., 7-1/2" ht.
Extends 8". H/CTR 5".
Three medium base lamps,
each 100w max.



P300023-015

FOUR-LIGHT BATH

P300023-015 Polished Chrome
34-1/2" W., 7-1/2" ht.
Extends 7-3/4". H/CTR 5".
Four medium base lamps,
each 100w max.

All fixtures mount up or down.

MOD

Giving a nod to the space age with mid-century modern appeal. Mod features a sleek linear frame in a Polished Chrome finish. Clear, spherical glass shades offer the perfect focal point for vintage bulbs or reflector-style globes.

ALSO AVAILABLE IN
Collections, page 162



P2854-15



P2854-15



P2850-15



P2856-15



P2857-15

FINISH

- Polished Chrome - 15

ONE-LIGHT BATH

P2850-15 Polished Chrome
5-7/8" W., 7-3/4" ht.
Extends 7-3/8". H/CTR 3-7/8".
One candelabra base lamp,
60w max.

TWO-LIGHT BATH

P2854-15 Polished Chrome
15" W., 6-3/4" ht.
Extends 7-3/8". H/CTR 2-3/8".
Two candelabra base lamps,
each 60w max.

THREE-LIGHT BATH

P2856-15 Polished Chrome
24" W., 6-3/4" ht.
Extends 7-3/8". H/CTR 2-3/8".
Three candelabra base lamps,
each 60w max.

FOUR-LIGHT BATH

P2857-15 Polished Chrome
33" W., 6-3/4" ht.
Extends 7-3/8". H/CTR 2-3/8".
Four candelabra base lamps,
each 60w max.

All fixtures shown with P7826-01
vintage lamps, not included.

All fixtures mount up or down.

SPATIAL

Spatial showcases a modern form that complements Urban Industrial, Mid-Century and Bohemian styles. Overscale geometric frames feature designs inspired by metal trusses and the art of engineering. A Matte Black finish is highlighted by clear globe shades or open candles. Chandelier and pendant options are ideal for foyers and entryways, while vanity fixtures complement modern spa-like bath suites.

ALSO AVAILABLE IN
Collections, page 164



P300113-031



P300113-031



P300112-031

FINISH
● Black - 031

ONE-LIGHT BATH
P300112-031 Black
5-3/8" W., 6-1/2" ht.
Extends 8". H/CTR 3-3/8".
One candelabra base lamp,
60w max.

TWO-LIGHT BATH
P300113-031 Black
14-1/8" W., 6-1/2" ht.
Extends 8-1/2". H/CTR 2-5/8".
Two candelabra base lamps,
each 60w max.

THREE-LIGHT BATH
P300114-031 Black
22" W., 6-1/2" ht.
Extends 8-1/2". H/CTR 2-5/8".
Three candelabra base lamps,
each 60w max.

FOUR-LIGHT BATH
P300115-031 Black
31-1/8" W., 6-1/2" ht.
Extends 8-1/2". H/CTR 2-5/8".
Four candelabra base lamps,
each 60w max.



P300114-031





P300115-031

All fixtures mount up or down.

LISBON

Enjoy high status with a bath and vanity collection full of femininity, sparkle and shine. Etched opal glass shades sit atop an elegant K9 glass rod, highlighted with a Polished Nickel or Matte Black finish. The highly polished design style complements both Modern and Luxe interiors and can be mounted up or down.



P300198-104



P300198-031



P300197-031



P300199-031




P300200-031



P300198-104



P300197-104



P300199-104



P300200-104

FINISHES

- Matte Black - 031
- Polished Nickel - 104

ONE-LIGHT BATH

P300197-031 Matte Black
P300197-104 Polished Nickel
 4-3/4" W., 14" ht.
 Extends 6". H/CTR 5-5/8".
 One medium base lamp,
 100w max.

TWO-LIGHT BATH

P300198-031 Matte Black
P300198-104 Polished Nickel
 14-1/2" W., 8" ht.
 Extends 6". H/CTR 5-5/8".
 Two medium base lamps,
 each 100w max.

THREE-LIGHT BATH

P300199-031 Matte Black
P300199-104 Polished Nickel
 24" W., 8" ht.
 Extends 6". H/CTR 5-5/8".
 Three medium base lamps,
 each 100w max.

FOUR-LIGHT BATH

P300200-031 Matte Black
P300200-104 Polished Nickel
 33-1/2" W., 8" ht.
 Extends 6". H/CTR 5-5/8".
 Four medium base lamps,
 each 100w max.

All fixtures mount up or down.

CAHILL

A stylish Brushed Bronze finish frames brilliant clear beveled glass panels in the Cahill collection. Ideal for Luxe or Mid-Century Modern interiors, the visual interest provides a reinvention of the popular glass design.



ALSO AVAILABLE IN
Collections, page 138



P300109-109



P300109-109



P300108-109



P300110-109



P300111-109

FINISH

- Brushed Bronze - 109

ONE-LIGHT BATH

P300108-109 Brushed Bronze
4-1/2" W., 19-3/4" ht.
Extends 7-1/2".
One candelabra base lamp,
60w max.

TWO-LIGHT BATH

P300109-109 Brushed Bronze
16-3/4" W., 6-3/8" ht.
Extends 5-1/4". H/CTR 3-1/8".
Two candelabra base lamps,
each 60w max.

THREE-LIGHT BATH

P300110-109 Brushed Bronze
24" W., 6-3/8" ht.
Extends 5-1/4". H/CTR 3-1/8".
Three candelabra base lamps,
each 60w max.

FOUR-LIGHT BATH

P300111-109 Brushed Bronze
30" W., 6-3/8" ht.
Extends 5-1/4". H/CTR 3-1/8".
Four candelabra base lamps,
each 60w max.

*All fixtures shown with P7826-01
vintage lamps, not included.*

All fixtures mount up or down.

DEBUT

Delicate details and warm finish options, including Graphite and Brushed Nickel, create statement making focal pieces for a variety of interiors. Debut provides a fitting stage to feature nostalgic, vintage lamps. Glass accessory shades in clear or frosted seeded finishes are available to complement traditional incandescent or energy efficient lamps.

ALSO AVAILABLE IN
Collections, page 178



P300009-143
Shown with
P860003-001 shade



P300009-143
shown with
P860003-001 shade



P300008-143



P300010-143
shown with
P860003-001 shade



P300011-143
shown with
P860002-001 shade



P300009-009
shown with
P860002-001 shade



P300008-009
shown with
P860003-001 shade



P300010-009
shown with
P860003-001 shade



P300011-009

BATH COLLECTIONS

FINISHES

- Brushed Nickel - 009
- Graphite - 143

ONE-LIGHT BATH

P300008-009 Brushed Nickel
P300008-143 Graphite
4-1/2" W., 8-1/2" ht.
Extends 5-7/8". H/CTR 5".
One medium base lamp,
60w max.

TWO-LIGHT BATH

P300009-009 Brushed Nickel
P300009-143 Graphite
14-1/4" W., 7-7/8" ht.
Extends 5-3/4". H/CTR 5-5/8".
Two medium base lamps,
each 60w max.

THREE-LIGHT BATH

P300010-009 Brushed Nickel
P300010-143 Graphite
23-3/4" W., 7-7/8" ht.
Extends 8". H/CTR 5-5/8".
Three medium base lamps,
each 60w max.

FOUR-LIGHT BATH

P300011-009 Brushed Nickel
P300011-143 Graphite
30-1/4" W., 7-7/8" ht.
Extends 8". H/CTR 5-5/8".
Four medium base lamps,
each 60w max.

P860002-001
Etched glass shade.

P860003-001
Seeded glass shade.

All fixtures shown with P7825-01
vintage lamps, not included.

All fixtures mount up or down.



P860002-001



P860003-001

FLIGHT

The Flight bath and vanity collection features a variety of industrial modern elements, including a linear frame and circular wall plate. The geometric and linear design is complemented by Brushed Nickel and Polished Chrome finish options.



P300001-009



P300001-009



P300000-009



P300002-009



P300003-009



P300001-015



P300000-015



P300002-015



P300003-015

FINISHES

- Brushed Nickel - 009
- Polished Chrome - 015

ONE-LIGHT BATH

P300000-009 Brushed Nickel
P300000-015 Polished Chrome
 6-1/8" W., 8-1/4" ht.
 Extends 5-5/8". H/CTR 5-1/8".
 One medium base lamp,
 100w max.

TWO-LIGHT BATH

P300001-009 Brushed Nickel
P300001-015 Polished Chrome
 15-3/4" W., 8-1/4" ht.
 Extends 5-5/8". H/CTR 5-1/8".
 Two medium base lamps,
 each 100w max.

THREE-LIGHT BATH

P300002-009 Brushed Nickel
P300002-015 Polished Chrome
 26-1/4" W., 8-1/4" ht.
 Extends 5-5/8". H/CTR 5-1/8".
 Three medium base lamps,
 each 100w max.

FOUR-LIGHT BATH

P300003-009 Brushed Nickel
P300003-015 Polished Chrome
 36-3/4" W., 8-1/4" ht.
 Extends 5-5/8". H/CTR 5-1/8".
 Four medium base lamps,
 each 100w max.

All fixtures mount up or down.

WEST VILLAGE

Visual interest continues with a three-spoke design that holds each glass shade. Brushed Nickel with chrome accents or Antique Bronze with antique brass accents provide touches of mixed metal in all fixtures within the collection.

ALSO AVAILABLE IN
Collections, page 200



P300005-020



P300005-009

P300004-009



P300006-009



P300007-009



P300005-020

P300004-020



P300006-020



P300007-020

FINISHES

- Brushed Nickel - 009
- Antique Bronze - 020

ONE-LIGHT BATH

P300004-009 Brushed Nickel
P300004-020 Antique Bronze
5-1/8" W., 8-1/8" ht.
Extends 7". H/CTR 4-1/8".
One medium base lamp,
100w max.

TWO-LIGHT BATH

P300005-009 Brushed Nickel
P300005-020 Antique Bronze
14-1/8" W., 8-1/8" ht.
Extends 7". H/CTR 6".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH

P300006-009 Brushed Nickel
P300006-020 Antique Bronze
23-1/4" W., 8-1/8" ht.
Extends 7". H/CTR 6".
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH

P300007-009 Brushed Nickel
P300007-020 Antique Bronze
32-1/4" W., 8-1/8" ht.
Extends 7". H/CTR 6".
Four medium base lamps,
each 100w max.

All fixtures mount up or down.

CARLYN

With a glamorous, transitional appeal, Carlyn bath and vanity fixtures feature a luxurious pattern comprised of K9 glass accents. The inner lined glass shades glimmer against both finishes.



P300101-020



P300101-020

P300100-020



P300102-020



P300103-020



P300101-104

P300100-104



P300102-104



P300103-104

FINISHES

- Antique Bronze - 020
- Polished Nickel - 104

ONE-LIGHT BATH

P300100-020 Antique Bronze
P300100-104 Polished Nickel
 5-1/8" W., 11-7/8" ht.
 Extends 5-7/8". H/CTR 6-5/8".
 One medium base lamp,
 100w max.

TWO-LIGHT BATH

P300101-020 Antique Bronze
P300101-104 Polished Nickel
 13-3/8" W., 8" ht.
 Extends 6-3/8". H/CTR 5-3/4".
 Two medium base lamps,
 each 100w max.

THREE-LIGHT BATH

P300102-020 Antique Bronze
P300102-104 Polished Nickel
 22-5/8" W., 8" ht.
 Extends 6-3/8". H/CTR 5-3/4".
 Three medium base lamps,
 each 100w max.

FOUR-LIGHT BATH

P300103-020 Antique Bronze
P300103-104 Polished Nickel
 31-7/8" W., 8" ht.
 Extends 6-3/8". H/CTR 5-3/4".
 Four medium base lamps,
 each 100w max.

All fixtures mount up or down.

GLANCE

A sophisticated bath and vanity collection. Glance's stout frame and etched linen glass shades complement a variety of contemporary design schemes. Polished Chrome and Antique Bronze finishes available for the one- through four-light fixtures.



P300017-015



P300017-015

P300016-015



P300018-015



P300019-015



P300017-020

P300016-020



P300018-020



P300019-020

FINISHES

- Polished Chrome - 015
- Antique Bronze - 020

ONE-LIGHT BATH

P300016-015 Polished Chrome
P300016-020 Antique Bronze
 5-3/8" W., 7-1/4" ht.
 Extends 7-1/4". H/CTR 3-5/8".
 One medium base lamp,
 100w max.

TWO-LIGHT BATH

P300017-015 Polished Chrome
P300017-020 Antique Bronze
 14-1/2" W., 7-1/4" ht.
 Extends 7-1/4". H/CTR 3-5/8".
 Two medium base lamps,
 each 100w max.

THREE-LIGHT BATH

P300018-015 Polished Chrome
P300018-020 Antique Bronze
 24" W., 7-1/4" ht.
 Extends 7-1/4". H/CTR 3-5/8".
 Three medium base lamps,
 each 100w max.

FOUR-LIGHT BATH

P300019-015 Polished Chrome
P300019-020 Antique Bronze
 33-3/8" W., 7-1/4" ht.
 Extends 7-1/4". H/CTR 3-5/8".
 Four medium base lamps,
 each 100w max.

All fixtures mount up or down.

GLIDE

Let Glide's nautical-inspired bath and vanity collection bring elegance and a spa-like atmosphere into the home. Available in Brushed Nickel, Polished Chrome or Rubbed Bronze, the oval-shaped opal glass sits upon a pedestal while offering a traditional or formal style. One-through four-light vanity options.



P300013-009



P300013-009

P300012-009



P300014-009



P300015-009

FINISH

- Brushed Nickel - 009

ONE-LIGHT BATH
P300012-009 Brushed Nickel
 4-1/2" W., 8" ht.
 Extends 6". H/CTR 4".
 One medium base lamp,
 100w max.

TWO-LIGHT BATH
P300013-009 Brushed Nickel
 16" W., 7-3/4" ht.
 Extends 6-7/8". H/CTR 4".
 Two medium base lamps,
 each 100w max.

THREE-LIGHT BATH
P300014-009 Brushed Nickel
 24" W., 7-3/4" ht.
 Extends 6-7/8". H/CTR 4".
 Three medium base lamps,
 each 100w max.

FOUR-LIGHT BATH
P300015-009 Brushed Nickel
 34" W., 7-3/4" ht.
 Extends 6-3/4". H/CTR 4".
 Four medium base lamps,
 each 100w max.

All fixtures mount up or down.

GLIDE

FINISH

- Polished Chrome - 015

ONE-LIGHT BATH

P300012-015 Polished Chrome
4-1/2" W., 8" ht.
Extends 6". H/CTR 4".
One medium base lamp,
100w max.



P300012-015



P300013-015

TWO-LIGHT BATH

P300013-015 Polished Chrome
16" W., 7-3/4" ht.
Extends 6-7/8". H/CTR 4".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH

P300014-015 Polished Chrome
24" W., 7-3/4" ht.
Extends 6-7/8". H/CTR 4".
Three medium base lamps,
each 100w max.



P300014-015

FOUR-LIGHT BATH

P300015-015 Polished Chrome
34" W., 7-3/4" ht.
Extends 6-3/4". H/CTR 4".
Four medium base lamps,
each 100w max.



P300015-015

All fixtures mount up or down.

GLIDE

FINISH

- Rubbed Bronze - 139

ONE-LIGHT BATH

P300012-139 Rubbed Bronze
4-1/2" W., 8" ht.
Extends 6". H/CTR 4".
One medium base lamp,
100w max.



P300012-139



P300013-139

TWO-LIGHT BATH

P300013-139 Rubbed Bronze
16" W., 7-3/4" ht.
Extends 6-7/8". H/CTR 4".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH

P300014-139 Rubbed Bronze
24" W., 7-3/4" ht.
Extends 6-7/8". H/CTR 4".
Three medium base lamps,
each 100w max.



P300014-139

FOUR-LIGHT BATH

P300015-139 Rubbed Bronze
34" W., 7-3/4" ht.
Extends 6-3/4". H/CTR 4".
Four medium base lamps,
each 100w max.



P300015-139

All fixtures mount up or down.

WANDER

A Victorian-inspired bath and vanity collection, Wander wall brackets offer a clean and classic look. Etched glass shades are paired with a Polished Chrome, Brushed Nickel or Venetian Bronze finish to offer versatile styling for any home.



P300025-009



P300025-009



P300024-009



P300026-009



P300027-009

FINISH

- Brushed Nickel - 009

ONE-LIGHT BATH

P300024-009 Brushed Nickel
4-3/4" W., 8-7/8" ht.
Extends 7". H/CTR 5-3/8".
One medium base lamp,
100w max.

TWO-LIGHT BATH

P300025-009 Brushed Nickel
16" W., 8-1/4" ht.
Extends 7". H/CTR 5".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH

P300026-009 Brushed Nickel
24-1/2" W., 8-1/4" ht.
Extends 7". H/CTR 5".
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH

P300027-009 Brushed Nickel
34" W., 8-1/4" ht.
Extends 7". H/CTR 5".
Four medium base lamps,
each 100w max.

All fixtures mount up or down.

WANDER

FINISH

- Polished Chrome - 015

ONE-LIGHT BATH

P300024-015 Polished Chrome
4-3/4" W., 8-7/8" ht.
Extends 7". H/CTR 5-3/8".
One medium base lamp,
100w max.



P300024-015



P300025-015

TWO-LIGHT BATH

P300025-015 Polished Chrome
16" W., 8-1/4" ht.
Extends 7". H/CTR 5".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH

P300026-015 Polished Chrome
24-1/2" W., 8-1/4" ht.
Extends 7". H/CTR 5".
Three medium base lamps,
each 100w max.



P300026-015

FOUR-LIGHT BATH

P300027-015 Polished Chrome
34" W., 8-1/4" ht.
Extends 7". H/CTR 5".
Four medium base lamps,
each 100w max.



P300027-015

All fixtures mount up or down.

WANDER

FINISH

- Venetian Bronze - 074

ONE-LIGHT BATH

P300024-074 Venetian Bronze
4-3/4" W., 8-7/8" ht.
Extends 7". H/CTR 5-3/8".
One medium base lamp,
100w max.



P300025-074



P300024-074

TWO-LIGHT BATH

P300025-074 Venetian Bronze
16" W., 8-1/4" ht.
Extends 7". H/CTR 5".
Two medium base lamps,
each 100w max.



P300026-074

THREE-LIGHT BATH

P300026-074 Venetian Bronze
24-1/2" W., 8-1/4" ht.
Extends 7". H/CTR 5".
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH

P300027-074 Venetian Bronze
34" W., 8-1/4" ht.
Extends 7". H/CTR 5".
Four medium base lamps,
each 100w max.



P300027-074

All fixtures mount up or down.

METRIC

A simple, etched opal glass shade nestles inside a die-cast frame that is finished in either Polished Chrome or Brushed Nickel – providing light above and below the fixture.



P2194-09



P2194-09



P2193-09



P2195-09



P2196-09



P2194-15



P2193-15



P2195-15



P2196-15

FINISHES

- Brushed Nickel - 09
- Polished Chrome - 15

ONE-LIGHT BATH

P2193-09 Brushed Nickel
P2193-15 Polished Chrome
 4-5/8" W., 8" ht.
 Extends 5-1/4". H/CTR 4-1/8".
 One medium base lamp,
 100w max.

TWO-LIGHT BATH

P2194-09 Brushed Nickel
P2194-15 Polished Chrome
 13" W., 6-1/2" ht.
 Extends 5-1/4". H/CTR 4-1/8".
 Two medium base lamps
 each, 100w max.

THREE-LIGHT BATH

P2195-09 Brushed Nickel
P2195-15 Polished Chrome
 22-1/8" W., 6-1/2" ht.
 Extends 5-1/4". H/CTR 4-1/8".
 Three medium base lamps
 each, 100w max.

FOUR-LIGHT BATH

P2196-09 Brushed Nickel
P2196-15 Polished Chrome
 31-1/4" W., 6-1/2" ht.
 Extends 5-1/4". H/CTR 4-1/8".
 Four medium base lamps
 each, 100w max.

All fixtures mount up or down.

VOLO LED

Volo fixtures feature a modern repeating circular frame. Etched opal glass shades are seamlessly secured to provide a clean, contemporary look to your home. The modern LED source delivers crisp, high quality light that is the perfect choice for both general and task lighting.



P300063-009-30



P300063-009-30



P300064-009-30



P300065-009-30

FINISH

● Brushed Nickel - 009

ONE-LIGHT BATH

P300063-009-30 Brushed Nickel
10" W., 5-1/2" ht.
Extends 4-5/8". H/CTR 2-3/4".
One 9w LED module, 3000K,
90 CRI, 624 source lumens.

TWO-LIGHT BATH

P300064-009-30 Brushed Nickel
16" W., 5 1/2" ht.
Extends 4-5/8". H/CTR 2-3/4".
Two 9w LED modules, 3000K,
90 CRI, 624 source lumens per module.

THREE-LIGHT BATH

P300065-009-30 Brushed Nickel
24" W., 5-1/2" ht.
Extends 4-5/8". H/CTR 2-3/4".
Three 9w LED modules, 3000K,
90 CRI, 624 source lumens per module.

All fixtures can be installed vertically or horizontally.

All fixtures:



ZURA

Zura features triangular, etched opal glass that provides geometric elements to add modern flair. This contemporary fixture is available in a Brushed Nickel, Polished Chrome, or Matte Black finish.



P300061-009



P300061-009



P300061-015



P300061-031



P300062-009



P300062-015



P300062-031



P300062-015
shown horizontally



P300062-031
shown horizontally

FINISHES

- Brushed Nickel - 009
- Polished Chrome - 015
- Matte Black - 031

ONE-LIGHT BATH

P300061-009 Brushed Nickel
P300061-015 Polished Chrome
P300061-031 Matte Black
 4-1/2" W., 13-3/4" ht.
 Extends 7". H/CTR 9-7/8".
 One medium base lamp,
 100w max.

TWO-LIGHT BATH

P300062-009 Brushed Nickel
P300062-015 Polished Chrome
P300062-031 Matte Black
 Can be installed vertically
 or horizontally.
 4-1/2" W., 21" ht.
 Extends 7". H/CTR 10-1/2".
 Two medium base lamps,
 each 100w max.



OUTDOOR

DESIGN+SERIES™

CHATSWORTH NEW

Imagine sleepy, vintage streets and old-world architecture with the Chatsworth Collection. Elongated lantern silhouettes boast antique charm as brass tone accents highlight vintage character and inspiration.



P550067-031



P560182-031



P560183-031



P560184-031



P550067-031



P540067-031

OUTDOOR

FINISH
● Textured Black - 031

HANGING LANTERN
P550067-031 Textured Black
9" sq., 23-7/8" ht.
Overall ht. w/chain 99", wire 10".
Two candelabra base lamps,
each 60w max.

POST LANTERN
P540067-031 Textured Black
9" sq., 23-1/2" ht.
Fits 3" post (order separately).
Two candelabra base lamps,
each 60w max.

SMALL WALL LANTERN
P560182-031 Textured Black
7-1/2" W., 14-1/4" ht.
Extends 8-1/2". H/CTR 11-3/4".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN
P560183-031 Textured Black
9" W., 22" ht.
Extends 10". H/CTR 18-7/8".
Two candelabra base lamps,
each 60w max.

LARGE WALL LANTERN
P560184-031 Textured Black
11" W., 28" ht.
Extends 12". H/CTR 25-5/8".
Three candelabra base lamps,
each 60w max.

MORRISON

Morrison blends delicate geometric patterns with lasting durability in a modern form. Intricate die cast aluminum construction is paired with clear glass and an Antique Bronze or Antique Pewter finish. A tall and stately design accommodates expansive modern and traditional architecture settings that require larger scale outdoor fixtures. Available in hanging, post and wall lantern options.



P560116-020



P550041-020



P550041-103



P560116-020



P560116-103



P540016-020



P560117-020



P560117-103



P540016-103



P560118-020



P560118-103

OUTDOOR

FINISHES

- Antique Bronze - 020
- Antique Pewter- 103

POST LANTERN

P540016-020 Antique Bronze
P540016-103 Antique Pewter
 9" dia., 26-1/2" ht.
 Fits 3" post (order separately).
 One medium base lamp,
 100w max.

HANGING LANTERN

P550041-020 Antique Bronze
P550041-103 Antique Pewter
 9" dia., 22" ht.
 Overall ht. w/chain 95"; wire 10'.
 One medium base lamp,
 100w max.

SMALL WALL LANTERN

P560116-020 Antique Bronze
P560116-103 Antique Pewter
 6-1/8" W., 17-1/4" ht.
 Extends 7-5/8". H/CTR 14-1/4".
 One medium base lamp,
 100w max.

MEDIUM WALL LANTERN


P560117-020 Antique Bronze
P560117-103 Antique Pewter
 7-1/2" W., 21-3/8" ht.
 Extends 9-1/4". H/CTR 18-1/4".
 One medium base lamp,
 100w max.

LARGE WALL LANTERN

P560118-020 Antique Bronze
P560118-103 Antique Pewter
 9" W., 25-1/2" ht.
 Extends 11-1/8". H/CTR 21-5/8".
 One medium base lamp,
 100w max.

CADENCE

The Cadence collection showcases classic lantern styling. Clear water glass panels surround traditional lighting clusters. A curved, Mediterranean-influenced frame is finished in Textured Black and Oil rubbed Bronze.



P6542-108



P6080-108



P6639-108



P6640-108



P6542-108



P6638-108



P6442-108

OUTDOOR

FINISH

- Oil Rubbed Bronze - 108

SMALL WALL-LANTERN

P6080-108 Oil Rubbed Bronze
6" W., 16-1/4" ht.
Extends 7-1/4". H/CTR 7-3/4".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN

P6638-108 Oil Rubbed Bronze
8" W., 21-1/4" ht.
Extends 9-3/8". H/CTR 9-7/8".
Two candelabra base lamps,
each 60w max.

POST LANTERN

P6442-108 Oil Rubbed Bronze
10" sq., 22-5/8" ht.
Fits 3" post (order separately).
Three candelabra base lamps,
each 60w max.

HANGING LANTERN

P6542-108 Oil Rubbed Bronze
10" sq., 24" ht.
Overall ht. w/chain 99-1/2"; wire 15'.
Three candelabra base lamps,
each 60w max.

LARGE WALL LANTERN

P6639-108 Oil Rubbed Bronze
10" W., 26-5/8" ht.
Extends 11-1/2". H/CTR 9-5/8".
Three candelabra base lamps,
each 60w max.

EXTRA-LARGE WALL LANTERN

P6640-108 Oil Rubbed Bronze
12-1/4" W., 32" ht.
Extends 13-3/4". H/CTR 11-5/8".
Four candelabra base lamps,
each 60w max.

CADENCE

FINISH

- Textured Black - 31

SMALL WALL LANTERN

P6626-31CD Textured Black
6-1/8" W., 18-7/8" ht.
Extends 7-1/2". H/CTR 9-1/4".
One candelabra base lamp,
60w max.

MEDIUM WALL LANTERN

P6627-31MD Textured Black
8" W., 24-3/4" ht.
Extends 9-1/4". H/CTR 13-3/8".
One medium base lamp,
100w max.

LARGE WALL LANTERN

P6628-31MD Textured Black
10" W., 31" ht.
Extends 11-3/8". H/CTR 14-1/8".
One medium base lamp,
100w max.

*EXTRA LARGE
WALL LANTERN*

P6629-31MD Textured Black
12" W., 38" ht.
Extends 13-1/4". H/CTR 18-1/4".
One medium base lamp,
100w max.



N

P6626-31CD



N

P6627-31MD



N

P6629-31MD



N

P6628-31MD




P6627-31MD

N New Product

MAISON NEW

Maison offers French country styling for a variety of home settings. Classic and formal clear water seeded glass in a die-cast aluminum frame.



P6637-31MD



P6634-31CD



P6635-31CD



P6636-31MD



P6637-31MD

OUTDOOR

FINISH

- Textured Black - 31

SMALL WALL LANTERN

P6634-31CD Textured Black
5-3/4" W., 13-5/8" ht.
Extends 6-1/8". H/CTR 9-1/8".
One candelabra base lamp,
60w max.

MEDIUM WALL LANTERN

P6635-31CD Textured Black
7-1/4" W., 16-7/8" ht.
Extends 7-5/8". H/CTR 11-3/4".
One candelabra base lamp,
60w max.

LARGE WALL LANTERN


P6636-31MD Textured Black
8-1/2" W., 18-3/4" ht.
Extends 8-7/8". H/CTR 13-3/8".
One medium base lamp,
100w max.

EXTRA LARGE WALL LANTERN

P6637-31MD Textured Black
10-1/2" W., 23-3/4" ht.
Extends 11-1/4". H/CTR 16-3/8".
One medium base lamp,
100w max.

GIBBES STREET

Elongated frames capture the romantic charm of vintage gas lanterns. Inspired by a stroll down a Charlestonian street bearing the same name, the Gibbes Street outdoor lantern collection features clear beveled glass and a classic Black or Antique Bronze finish. Wall, post, and hanging lanterns complete the family.



P550004-020



P560021-020



P560022-020



P560023-020



P550004-020



P540004-020

OUTDOOR

FINISH

- Antique Bronze - 020

POST LANTERN

P540004-020 Antique Bronze
9-1/2" dia., 26-7/8" ht.
Fits 3" post (order separately).
Three candelabra base lamps,
each 60w max.

HANGING LANTERN

P550004-020 Antique Bronze
9-1/2" dia., 23-3/4" ht.
Overall ht. w/chain 99"; wire 10'.
Three candelabra base lamps,
each 60w max.

SMALL WALL LANTERN

P560021-020 Antique Bronze
5-1/2" W., 15-1/8" ht.
Extends 7". H/CTR 5-7/8".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN

P560022-020 Antique Bronze
7" W., 21-3/4" ht.
Extends 8-3/4". H/CTR 8-3/8".
Two candelabra base lamps,
each 60w max.

LARGE WALL LANTERN

P560023-020 Antique Bronze
9-1/2" W., 30-5/8" ht.
Extends 11-1/4". H/CTR 10-3/4".
Three candelabra base lamps,
each 60w max.

*All fixtures shown with P7826-01
vintage lamp, not included.*

GIBBES STREET



P550009-031



P560021-031 *N*



P560022-031 *N*



P560023-031 *N*



P550004-031 *N*



P540004-031 *N*

FINISH

- Textured Black - 031

POST LANTERN

P540004-031 Textured Black
9-1/2" dia., 26-7/8" ht.
Fits 3" post (order separately).
Three candelabra base lamps,
each 60w max.

HANGING LANTERN

P560021-031 Textured Black
9-1/2" dia., 23-3/4" ht.
Overall ht. w/chain 99"; wire 10'.
Three candelabra base lamps,
each 60w max.

SMALL WALL LANTERN

P560021-031 Textured Black
5-1/2" W., 15-1/8" ht.
Extends 7". H/CTR 5-7/8".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN

P560022-031 Textured Black
7" W., 21-3/4" ht.
Extends 8-3/4". H/CTR 8-3/8".
Two candelabra base lamps,
each 60w max.

LARGE WALL LANTERN

P560023-031 Textured Black
9-1/2" W., 30-5/8" ht.
Extends 11-1/4". H/CTR 10-3/4".
Three candelabra base lamps,
each 60w max.

*All fixtures shown with P7826-01
vintage lamp, not included.*

N New Product

SANTEE

A classic colonial wall lantern with contemporary touches describes Santee. Featuring a geometric frame and graphic handle, the wider beveled glass offers more refraction – and visual interest – than typical lantern designs. Choose from a Matte Black frame with stainless steel candle or an Antique Bronze frame with painted brass candle.



P560003-020



P560002-020



P560002-031



P560003-020



P560003-031

OUTDOOR

FINISHES

- Antique Bronze - 020
- Matte Black - 031

SMALL WALL LANTERN

P560002-020 Antique Bronze
P560002-031 Matte Black
 8" W., 15-1/4" ht.
 Extends 5-3/4". H/CTR 8-3/4".
 Two candelabra base lamps,
 each 60w max.

LARGE WALL LANTERN

P560003-020 Antique Bronze
P560003-031 Matte Black
 9-1/2" W., 19-5/8" ht.
 Extends 6-1/2". H/CTR 11-3/8".
 Three candelabra base lamps,
 each 60w max.

*All fixtures shown with P7826-01
 vintage lamps, not included.*

CREIGHTON

Creighton features clear water glass with Antique Bronze or Textured Black finish options. The frame's linear details are riveted to enhance mechanical detailing of the fixture. Wall, post and hanging lantern options available.



P550009-020



P560031-031



P560031-020



P560032-031



P560032-020



P560033-031



P560033-020



P540009-031



P540009-020



P550009-020



P550009-031

OUTDOOR

FINISHES

- Antique Bronze - 020
- Textured Black - 031

POST LANTERN

P540009-020 Antique Bronze
P540009-031 Textured Black
 10-1/2" dia., 21-3/4" ht.
 Fits 3" post (order separately).
 One medium base lamp,
 100w max.

HANGING LANTERN

P550009-020 Antique Bronze
P550009-031 Textured Black
 10-1/2" dia., 21-5/8" ht.
 Overall ht. w/chain 96-1/2"; wire 10'.
 One medium base lamp,
 100w max.

SMALL WALL-LANTERN

P560031-020 Antique Bronze
P560031-031 Textured Black
 6" W., 11-1/2" ht.
 Extends 7-1/4". H/CTR 2-3/8".
 One medium base lamp,
 100w max.

MEDIUM WALL-LANTERN

P560032-020 Antique Bronze
P560032-031 Textured Black
 8-3/8" W., 15-3/4" ht.
 Extends 9-3/8". H/CTR 3".
 One medium base lamp,
 100w max.

LARGE WALL-LANTERN

P560033-020 Antique Bronze
P560033-031 Textured Black
 10-1/2" W., 19-1/4" ht.
 Extends 11-1/8". H/CTR 3".
 One medium base lamp,
 100w max.

KIAWAH

Seeded glass panels and traditional detailing combine to create a soft and updated lantern design. Hinged door for easy relamping is available for post, hanging and medium, large and extra large wall lanterns.



P550001-031



P560010-031



P560011-031



P560013-031



P550001-031



P560012-031



P540001-031

OUTDOOR

FINISH

- Textured Black - 031

POST LANTERN

P540001-031 Textured Black
9-1/2" sq., 20-7/8" ht.
Fits 3" post (order separately).
Three candelabra base lamps,
each 60w max.

HANGING LANTERN

P550001-031 Textured Black
9-1/2" sq., 19-5/8" ht.
Overall ht. w/chain 94-1/2"; wire 10'.
Three candelabra base lamps,
each 60w max.

SMALL WALL LANTERN

P560010-031 Textured Black
5-5/8" W., 12-7/8" ht.
Extends 6-3/8". H/CTR 5-3/8".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN

P560011-031 Textured Black
7-1/2" W., 21-7/8" ht.
Extends 8-3/8". H/CTR 8-1/4".
Two candelabra base lamps,
each 60w max.

LARGE WALL LANTERN

P560012-031 Textured Black
9-1/2" W., 27-1/4" ht.
Extends 10-1/4". H/CTR 10".
Three candelabra base lamps,
each 60w max.

EXTRA-LARGE WALL LANTERN

P560013-031 Textured Black
12-1/2" W., 34-1/2" ht.
Extends 13-1/2". H/CTR 10-3/4".
Three candelabra base lamps,
each 60w max.

HERMOSA

Outdoor Mediterranean-style lanterns in the Hermosa family complement Transitional, Rustic Farmhouse and Modern Farmhouse exteriors. These large-scale pieces feature beautiful detail and a die cast aluminum frames. Wrought iron styling perfectly frames beautiful clear, water glass shades.



P550027-031



P560074-031



P560075-031



P560076-031



P550027-031



P540027-031

OUTDOOR

FINISH
● Textured Black - 031

POST LANTERN
P540027-031 Textured Black
12" dia., 28" ht.
Fits 3" post (order separately).
One medium base lamp,
100w max.

HANGING LANTERN
P550027-031 Textured Black
12" dia., 26-1/2" ht.
Overall ht. w/chain 101-1/2", wire 10'.
One medium base lamp,
100w max.

SMALL WALL LANTERN
P560074-031 Textured Black
8" W., 21" ht.
Extends 8-1/4". H/CTR 12-7/8".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN
P560075-031 Textured Black
10" W., 26" ht.
Extends 10-1/8". H/CTR 16-1/8".
One medium base lamp,
100w max.

LARGE WALL LANTERN
P560076-031 Textured Black
12" W., 32" ht.
Extends 12-1/4". H/CTR 20-1/8".
One medium base lamp,
100w max.

LEAWOOD LED

Leawood LED provides delicate scrollwork with dramatic shadow patterns in a modern form. Intricate die cast aluminum construction is available in classic Black or White finish options. A taller design accommodates the larger scale commonly seen in today's modern and traditional architecture. Available in hanging, post and wall lanterns.



P540037-031-30



P550037-030-30



P550037-031-30



P560104-030-30



P560104-031-30



P560105-030-30



P560105-031-30



P540037-030-30



P540037-031-30

OUTDOOR

FINISHES

- Textured White - 030
- Textured Black - 031

POST LANTERN

P540037-030-30 White
P540037-031-30 Textured Black
 10" dia., 18-7/8" ht.
 Fits 3" post (order separately).
 One 17w LED module, 3000K, 90CRI, 1276 source lumens.

HANGING LANTERN

P550037-030-30 White
P550037-031-30 Textured Black
 10" dia., 19-3/8" ht.
 Overall ht. w/chain 93-1/2", wire 10'.
 One 9w LED module, 3000K, 90CRI, 624 source lumens.

SMALL WALL LANTERN

P560104-030-30 White
P560104-031-30 Textured Black
 8" dia., 13-5/8" ht.
 Extends 9-12". H/CTR 4-5/8".
 One 9w LED module, 3000K, 90CRI, 624 source lumens.

MEDIUM WALL LANTERN

P560105-030-30 White
P560105-031-30 Textured Black
 10" dia., 17" ht.
 Extends 11-3/4". H/CTR 5-3/4".
 One 9w LED module, 3000K, 90CRI, 624 source lumens.

All fixtures:



WHITACRE LED

Inspired by traditional lantern styles, Whitacre incorporates handsome details. Clear seeded glass surrounds an etched opal glass candle diffuser. An Antique Bronze finish complements a variety of exteriors, including Transitional, Traditional and Farmhouse designs.



P550026-020-30



P560068-020-30



P560069-020-30



P560070-020-30



P550026-020-30



P540026-020-30

OUTDOOR

FINISH

- Antique Bronze - 020

POST LANTERN

P540026-020-30 Antique Bronze
12-5/16" dia., 22-7/8" ht.
Fits 3" post (order separately).
One 9w LED module, 3000K,
90 CRI, 624 source lumens.

HANGING LANTERN

P550026-020-30 Antique Bronze
12-5/16" dia., 21" ht.
Overall ht. w/chain 96", wire 10'.
One 17w LED module, 3000K,
90 CRI, 1276 source lumens.

SMALL WALL LANTERN

P560068-020-30 Antique Bronze
7-7/8" W., 14-3/8" ht.
Extends 8". H/CTR 3-5/8".
One 9w LED module, 3000K,
90 CRI, 624 source lumens.

MEDIUM WALL LANTERN

P560069-020-30 Antique Bronze
10" W., 18" ht.
Extends 10". H/CTR 4".
One 9w LED module, 3000K,
90 CRI, 624 source lumens.

LARGE WALL LANTERN


P560070-020-30 Antique Bronze
12-5/16" W., 22" ht.
Extends 12". H/CTR 4-3/4".
One 17w LED module, 3000K,
90 CRI, 1276 source lumens.

All fixtures:



DEVEREUX

Devereux features an etched white pillar shade that sits inside a clear seeded glass design. A double scrolled arm finished in Antique Bronze provides elegant scale for a variety of exterior settings. Post, hanging and wall lantern options are available.



P550003-020



P560018-020



P560019-020



P560020-020



P550003-020



P540003-020

OUTDOOR

FINISH

● Antique Bronze - 020

POST LANTERN

P540003-020 Antique Bronze
9-3/8" dia., 26-5/8" ht.
Fits 3" post (order separately).
One medium base lamp,
100w max.

HANGING LANTERN

P550003-020 Antique Bronze
9-1/2" dia., 23-5/8" ht.
Overall ht. w/chain 95-1/2"; wire 10'.
One medium base lamp,
100w max.

SMALL WALL-LANTERN

P560018-020 Antique Bronze
5-1/2" W., 20-1/4" ht.
Extends 7-7/8". H/CTR 10-1/8".
One medium base lamp,
100w max.

MEDIUM WALL-LANTERN

P560019-020 Antique Bronze
7" W., 26" ht.
Extends 9-3/4". H/CTR 13".
One medium base lamp,
100w max.

LARGE WALL-LANTERN

P560020-020 Antique Bronze
9-1/2" W., 34-1/2" ht.
Extends 12-3/4". H/CTR 17-3/8".
One medium base lamp,
100w max.

VERDAE

Classic and formal clear seeded glass complements a Textured Black or Antique Bronze finish. Open bottom or hinged door provide easy access for cleaning and relamping.



P560016-020



P560014-020



P560014-031



P560015-020



P560015-031



P560016-020



P560016-031



P560017-020



P560017-031



P550002-020



P550002-031



P540002-020



P540002-031

OUTDOOR

FINISHES

- Antique Bronze - 020
- Textured Black - 031

POST LANTERN

P540002-020 Antique Bronze
P540002-031 Textured Black
 10-3/8" dia., 22-5/8" ht.
 Fits 3" post (order separately).
 Three candelabra base lamps,
 each 60w max.

HANGING LANTERN

P550002-020 Antique Bronze
P550002-031 Textured Black
 10-3/8" dia., 18-3/8" ht.
 Overall ht. w/chain 93-1/2"; wire 10'.
 Three candelabra base lamps,
 each 60w max.

SMALL WALL-LANTERN

P560014-020 Antique Bronze
P560014-031 Textured Black
 6-1/4" W., 13-1/4" ht.
 Extends 8-5/8". H/CTR 5-3/4".
 One medium base lamp,
 100w max.

MEDIUM WALL-LANTERN

P560015-020 Antique Bronze
P560015-031 Textured Black
 8-1/4" W., 17-3/4" ht.
 Extends 11-3/8". H/CTR 10-1/8".
 One medium base lamp,
 100w max.

LARGE WALL-LANTERN

P560016-020 Antique Bronze
P560016-031 Textured Black
 10-3/8" W., 21-3/4" ht.
 Extends 13-5/8". H/CTR 10".
 Three candelabra base lamps,
 each 60w max.

EXTRA-LARGE WALL-LANTERN

P560017-020 Antique Bronze
P560017-031 Textured Black
 10-3/8" W., 30-1/2" ht.
 Extends 13-1/4". H/CTR 14-3/4".
 Three candelabra base lamps,
 each 60w max.

JANSSEN NEW

Create a home fully of modern elegance with the Janssen Collection. Sleek, elongated frames with rectangular forms hold gorgeous etched glass diffuser in an architectural design intended to add a contemporary glow while commanding visual interest.



P550044-108



P560122-108



P560123-108



P550044-108



P540017-108

OUTDOOR

FINISH

● Oil Rubbed Bronze - 108

POST LANTERN

P540017-108 Oil Rubbed Bronze
7-1/2" dia., 20-5/8" ht.
Fits 3" post (order separately).
One medium base lamp,
100w max.

HANGING LANTERN

P550044-108 Oil Rubbed Bronze
7-1/2" dia., 21" ht.
Overall ht. w/chain 96", wire 10'.
One medium base lamp,
100w max.

SMALL WALL LANTERN

P560122-108 Oil Rubbed Bronze
7-1/2" W., 12-1/2" ht.
Extends 8-1/4". H/CTR 3-1/2".
One medium base lamp,
100w max.

LARGE WALL LANTERN

P560123-108 Oil Rubbed Bronze
7-1/2" W., 19" ht.
Extends 8-1/4". H/CTR 5".
One medium base lamp,
100w max.

PATEWOOD

Patewood lanterns have a modern shadowbox housing in a sleek Black finish constructed from durable stainless steel. The pillar candle style diffusers provide crisp illumination for a pleasing complement to your home's exterior.



P550024-031



P550013-031



P550024-031



P560039-031



P560040-031



P540013-031



P560041-031

OUTDOOR

FINISH

- Black - 031

POST LANTERN

P540013-031 Black
Fits 3" post (order separately).
7" W., 19-3/8" ht.
One medium base lamp,
100w max.

HANGING LANTERN

P550013-031 Black
5-1/2" W., 15-1/8" ht.
Overall ht. w/stem 81", wire 10'.
One medium base lamp,
100w max.

HANGING LANTERN

P550024-031 Black
7 W., 18" ht.
Overall ht. w/stem 84, wire 10'.
One medium base lamp,
100w max.

SMALL WALL LANTERN

P560039-031 Black
4-1/2" W., 12" ht.
Extends 5-3/8". H/CTR 8-5/8".
One medium base lamp,
75w max.

MEDIUM WALL LANTERN

P560040-031 Black
5-11/16" W., 14-1/2" ht.
Extends 6-1/2". H/CTR 10".
One medium base lamp,
100w max.

LARGE WALL LANTERN

P560041-031 Black
7" W., 17-3/8" ht.
Extends 7-3/4". H/CTR 11-7/8".
One medium base lamp,
100w max.

UNION SQUARE

Union Square features a reproduction gas lantern inspiration. A Stainless Steel finish complements the natural polished material and clear flat glass panels. Mechanical details – such as exaggerated knobs – provide character to the form. Open bottom on wall lanterns provides easy access for cleaning and relamping.



ALSO AVAILABLE IN

Collections, page 170

Bath, page 282



P560005-135



P560004-135



P560005-135



P560006-135



P550018-135



P550007-135

OUTDOOR

FINISH

- Stainless Steel - 135

FLUSH MOUNT

P550007-135 Stainless Steel
12-3/8" sq., 5-1/2" ht.
Two medium base lamps,
each 60w max.

SMALL WALL-LANTERN

P560004-135 Stainless Steel
6-1/2" W., 15-7/8" ht.
Extends 5-1/2". H/CTR 6-1/4".
One medium base lamp,
100w max.

MEDIUM WALL-LANTERN

P560005-135 Stainless Steel
7-7/8" W., 19-3/8" ht.
Extends 6-1/2". H/CTR 7-3/4".
One medium base lamp,
100w max.

LARGE WALL-LANTERN

P560006-135 Stainless Steel
9-3/4" W., 23-5/8" ht.
Extends 8". H/CTR 9-5/8".
One medium base lamp,
100w max.

HANGING LANTERN

P550018-135 Stainless Steel
7" sq., 27-3/8" ht.
Overall ht. w/chain 102-1/2", wire 10'.
One medium base lamp,
100w max.

*All fixtures shown with P7827-01
vintage lamps, not included.*

CULLMAN

Cullman outdoor lanterns deliver dramatic scale with Craftsman appeal. Bold and linear details in an Antique Bronze finish highlight clear seeded glass. Ideal for spacious Modern architecture settings. Available in post, hanging and wall lantern options.



P560125-020



P560124-020



P560125-020



P560126-020



P550045-020



P540018-020

OUTDOOR

FINISH

- Antique Bronze - 020

POST LANTERN

P540018-020 Antique Bronze
11" sq., 22-3/4" ht.
Fits 3" post (order separately).
One medium base lamp,
100w max.

HANGING LANTERN

P550045-020 Antique Bronze
11" sq., 19-5/8" ht.
Overall ht. w/chain 94", wire 10'.
One medium base lamp,
100w max.

SMALL WALL LANTERN

P560124-020 Antique Bronze
7" W., 16-5/8" ht.
Extends 8-3/8". H/CTR 2-3/8".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN

P560125-020 Antique Bronze
9" W., 16" ht.
Extends 10-3/8". H/CTR 2-3/4".
One medium base lamp,
100w max.

LARGE WALL LANTERN

P560126-020 Antique Bronze
11" W., 19-1/4" ht.
Extends 12-1/2". H/CTR 2-3/4".
One medium base lamp,
100w max.

TWAIN

Featuring an updated prairie style, Twain's lantern collection offers visual interest for a variety of home exteriors. Solid glass with the center sand blasted, is divided by the frames vertical lines.



P550000-020



P560007-020



P560008-020



P560009-020



P550000-020



P540000-020

OUTDOOR

FINISH

- Antique Bronze - 020

POST LANTERN

P540000-020 Antique Bronze
7-3/4" sq., 16" ht.
Fits 3" post (order separately).
One medium base lamp,
100w max.

HANGING LANTERN

P550000-020 Antique Bronze
7-3/4" sq., 13-3/4" ht.
Overall ht. w/chain 88-1/2"; wire 10'.
One medium base lamp,
100w max.

SMALL WALL LANTERN

P560007-020 Antique Bronze
5-3/4" W., 10-1/4" ht.
Extends 6-3/4". H/CTR 2-3/8".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN

P560008-020 Antique Bronze
7-3/4" W., 13-1/2" ht.
Extends 8-7/8". H/CTR 2-3/4".
One medium base lamp,
100w max.

LARGE WALL LANTERN

P560009-020 Antique Bronze
9-1/2" W., 16-1/2" ht.
Extends 10-3/4". H/CTR 3-1/4".
One medium base lamp,
100w max.

NORTHAMPTON LED

Northampton LED lanterns take a designer-influenced approach for these updated outdoor wall lanterns. Two distinctive styles provide a modern or more traditional accent to your home with striking textured glass in a classic pattern. A Black frame highlights clear fluted glass panels with a metallic silver interior reflector, while the Architectural Bronze housing showcases clear seeded glass with a quatrefoil inspired metal pattern aired with a brass tone internal reflector.



P560108-031-30



P560106-129-30



P560108-031-30



P560107-129-30



P560109-031-30

OUTDOOR

FINISHES

- Architectural Bronze - 129
- Black - 031

SMALL LED WALL LANTERN

P560106-129-30 Architectural Bronze
P560108-031-30 Black
 6-3/4" W., 12-1/2" ht.
 Extends 5". H/CTR 6-1/4".
 One 9w LED module, 3000K,
 90CRI, 624 source lumens.

MEDIUM LED WALL LANTERN

P560107-129-30 Architectural Bronze
P560109-031-30 Black
 6-3/4" W., 22" ht.
 Extends 5". H/CTR 11".
 One 9w LED module, 3000K,
 90CRI, 624 source lumens.

All fixtures:



PRODUCT INDEX

P2000

P2325 207
 P2193 315
 P2194 314
 P2195 315
 P2196 315
 P2325 207
 P2326 205
 P2850 163
 P2850 289
 P2854 288
 P2856 289
 P2857 289

P3000

P300000 299
 P300001 298
 P300002 299
 P300003 299
 P300004 201, 203
 P300004 301
 P300005 300
 P300006 301
 P300007 301
 P300008 179, 181, 297
 P300009 297
 P300010 297
 P300011 297
 P300012 307, 308, 309
 P300013 306, 308, 309
 P300014 307, 308, 309
 P300015 307, 308, 309
 P300016 305
 P300017 304
 P300018 305
 P300019 305
 P300020 135, 137, 139
 P300020 285, 286, 287
 P300021 284, 286, 287
 P300022 285, 286, 287
 P300023 285, 286, 287
 P300024 311, 312, 313
 P300025 310, 312, 313
 P300026 311, 312, 313
 P300027 311, 312, 313
 P300061 318
 P300062 319
 P300063 316
 P300064 317
 P300065 317
 P300100 303
 P300101 302
 P300102 303
 P300103 303
 P300105 147, 149, 281
 P300106 280
 P300107 281
 P300108 145, 295

P300109 294
 P300110 295
 P300111 295
 P300112 291
 P300113 291
 P300114 291
 P300115 291
 P300197 293
 P300198 292
 P300199 293
 P300200 293
 P300201 155
 P300214 133
 P350029 213
 P350030 226, 227
 P350032 201, 203
 P350034 197, 199
 P350035 197, 199
 P350036 179, 181
 P350040 135, 137, 139
 P350058 206
 P350090 147, 149
 P350092 221
 P350095 143
 P350102 167, 169
 P350105 137, 139
 P350106 211
 P350118 209
 P350119 175
 P350120 131
 P350121 133
 P350128 155
 P350139 114
 P350140 105
 P350141 101
 P350142 110
 P350143 109
 P350158 123
 P350159 121
 P3598 232
 P3601 233
 P3604 127
 P3868 235

P4000

P400002 177
 P400003 177
 P400004 224
 P400005 226
 P400006 226
 P400008 201, 203
 P400009 201, 203
 P400010 201, 203
 P400011 197, 199
 P400012 197, 199
 P400013 197, 199
 P400014 197, 199
 P400015 179, 181
 P400016 179, 181
 P400017 179, 181
 P400021 135, 137, 139
 P400022 134, 137, 139
 P400023 135, 137, 139
 P400024 193, 195
 P400025 193, 195
 P400026 193, 195
 P400040 161
 P400041 161
 P400049 212
 P400051 183
 P400068 222
 P400069 223
 P400070 223
 P400071 144
 P400072 145
 P400075 220
 P400076 221
 P400077 165
 P400079 210
 P400080 185, 187
 P400081 185, 187
 P400082 185, 187
 P400083 185, 187
 P400084 165
 P400086 131
 P400089 143
 P400090 142
 P400091 143

P4000 (cont'd)

P400092 143
 P400098 150
 P400099 151
 P400100 211
 P400101 206
 P400105 167
 P400106 167
 P400108 156
 P400109 157
 P400112 170
 P400113 132
 P400114 133
 P400116 147
 P400117 192
 P400143 159
 P400144 159
 P400145 171
 P400160 208
 P400161 209
 P400164 172
 P400165 173
 P400166 173
 P400170 125
 P400172 155
 P400173 155
 P400176 140
 P400179 133
 P400180 175
 P400192 95
 P400213 128
 P400215 129
 P400216 122
 P400217 123
 P400227 216
 P4755 162
 P4756 163
 P4760 189
 P4761 188
 P4763 189
 P4766 190
 P4767 191

P5000

P500000 265
 P500006 201
 P500007 197
 P500009 185
 P500010 183
 P500011 183
 P500012 182
 P500013 266
 P500032 255
 P500033 254
 P500036 230
 P500037 231
 P500038 229
 P500039 229
 P500040 228
 P500042 177
 P500043 213
 P500045 264
 P500046 243
 P500047 242
 P500063 252
 P500064 250
 P500073 147
 P500074 147
 P500075 145
 P500076 145
 P500077 145
 P500080 221
 P500081 221
 P500082 165
 P500083 164
 P500085 211
 P500088 185
 P500089 185
 P500091 223
 P500095 146
 P500096 165
 P500098 255
 P500101 143
 P500105 151
 P500106 151
 P500107 151
 P500108 151

P500109 206
 P500115 167
 P500116 167
 P500117 166
 P500118 244
 P500119 263
 P500120 262
 P500123 215
 P500124 214
 P500151 135
 P500161 241
 P500163 240
 P500164 175
 P500165 174
 P500166 152
 P500167 153
 P500168 130
 P500173 125
 P500174 124
 P500175 154
 P500194 98
 P500195 108
 P500196 106
 P500197 104
 P500198 100
 P500199 97
 P500200 96
 P500201 105
 P500202 109
 P500203 116
 P500204 102
 P500221 238
 P500222 239
 P500232 121
 P500233 120
 P500248 129
 P500285 217
 P5015 126
 P5021 127
 P5073 233
 P5309 249
 P5311 248
 P5317 189

P5318 191
 P5319 235
 P5320 207
 P5321 204
 P5322 234
 P5324 260
 P5332 246
 P5333 247
 P5334 247
 P5337 258
 P5338 259
 P5344 256
 P5346 205
 P540000 361
 P540001 341
 P540002 351
 P540003 349
 P540004 333
 P540009 339
 P540013 355
 P540016 325
 P540017 353
 P540018 359
 P540026 347
 P540027 343
 P540037 344
 P550000 360
 P550001 340
 P550002 351
 P550003 348
 P550004 332
 P550007 357
 P550009 338
 P550013 355
 P550018 357
 P550024 354
 P550026 346
 P550027 342
 P550037 345
 P550041 325
 P550044 352
 P550045 359
 P550067 322

PRODUCT INDEX (cont'd)

P5000 (cont'd)

P560002.....	337	P560074.....	343	P6635.....	331	P710043.....	167
P560003.....	336	P560075.....	343	P6636.....	331	P710053.....	209
P560004.....	357	P560076.....	343	P6637.....	330	P710055.....	175
P560005.....	357	P560104.....	345	P6638.....	327	P710057.....	125
P560006.....	357	P560105.....	345	P6639.....	327	P710063.....	141
P560007.....	361	P560106.....	363	P6640.....	327	P710064.....	97
P560008.....	361	P560108.....	362			P710065.....	112
P560009.....	361	P560109.....	363	P7000		P710066.....	107
P560010.....	341	P560116.....	324	P710002.....	177	P710067.....	105
P560011.....	341	P560117.....	325	P710003.....	226	P710068.....	101
P560012.....	341	P560118.....	325	P710005.....	197	P710069.....	103
P560013.....	341	P560122.....	353	P710007.....	197	P710070.....	99
P560014.....	351	P560123.....	353	P710013.....	213	P710076.....	121
P560015.....	351	P560124.....	359	P710016.....	270	P710077.....	129
P560016.....	350	P560125.....	359	P710017.....	276	P710078.....	123
P560017.....	351	P560126.....	359	P710018.....	217	P7117.....	257
P560018.....	349	P560183.....	323	P710018.....	275	P7125.....	257
P560019.....	349	P560184.....	323	P710019.....	217	P7198.....	207
P560020.....	349			P710019.....	274		
P560021.....	333	P6000		P710025.....	272		
P560022.....	333	P6080.....	327	P710027.....	157		
P560023.....	333	P6442.....	327	P710029.....	221	P860000.....	225
P560031.....	339	P6626.....	329	P710030.....	211	P860001.....	225
P560032.....	339	P6627.....	328	P710032.....	223	P860002.....	179, 297
P560033.....	339	P6628.....	329	P710034.....	143	P860003.....	179, 297
P560068.....	347	P6629.....	329	P710037.....	151	P8704.....	209
P560069.....	347	P6634.....	331	P710038.....	283		
P560070.....	347			P710038.....	171		

ICON KEY



Products referencing this logo meet the energy efficiency requirements for light fixtures set forth in ENERGY STAR® product specifications. Please refer to www.energystar.gov for specific product qualifications and list of certified products.



This marking indicates fixtures that have an integrated LED or replaceable LED module that has been tested and listed in the California Appliance Database. Check for certified lamps, fixtures or LED light engines by searching the MAEDBS database. Go to cacertappliances.energyc.ca.gov



Complies with the "Americans with Disabilities Act"



Table 150.0A defines products that do not have to meet JA8 and can be used to comply with 2016 Title 24. The most common types include:

- Pin-based linear or compact fluorescent light sources using electronic ballasts
- GU-24 sockets containing light sources other than LEDs
- Inseperable SSL luminaires that are installed outdoors

EQUIP EDUCATE EXCITE

These three words define the mission of Progress Lighting. Flip through our catalog, and you'll quickly see how we equip you with the education to make all your exciting design dreams come true. Whether you're browsing our catalog or visiting our website, Progress is at your service to help you envision where and how to use our products.

To explore more of the Design Series™ visit us online:



progresslighting.com/designseries

EXPERIENCE PROGRESS

Learn how lighting can totally transform a space. Experience Progress features beautiful room images from our builder partners, design firms, social media fans and influencers bringing the Progress Lighting story to life. By working together, we're furthering a vision of providing whole home solutions to those who are seeking inspiration.

Visit progresslighting.com/experienceprogress

LET'S GET SOCIAL

Explore our blog for even more design inspiration, product integration and trend guidance to make your home into a haven of livable luxury. See progresslighting.com/blog

- @ProgressLtg
- @ProgressLtg
- @ProgressLtg
- Progress Lighting
- @ProgressLighting
- Progress-Lighting

#ProgressLighting
#DesignSeries

Every effort has been made to ensure the accuracy of information in this catalog. Progress Lighting reserves the right to make product changes from time to time, without prior notification, which may change the information provided in this catalog. Errors brought to our attention will be corrected in subsequent issues.

UL, CSA, or ETL Listed or Classified unless otherwise noted. Bulbs not included with fixtures unless specified. Specifications subject to change without notice.

Metal finishes not specified as "solid" have quality plated or painted finishes.

Finish representations are high resolution digital reproductions, and, while every effort has been made to render colors accurately, they may vary slightly from the actual product, especially hand-painted finishes, due to the nature of hand craftsmanship.

©Progress Lighting 2020
All rights reserved.
International copyright secured.



701 Millennium Blvd
Greenville, SC 29607

Featuring Desiree



COMPLETE YOUR DESIGN

with eye-catching accessories.

Enhance the style of your Design Series fixture with a selection from our lighting accessories. Add a new canopy to complement the design and personalize the fixture to fit your décor. Create your own look by mounting several pendants on a multi-pendant canopy, or swap out shades for a different style or color. Order extra stem rod or chains to extend the hanging length of the fixture. *THE CHOICE IS YOURS!*

PENDANT CANOPIES, STEM KITS, CHAINS, SHADES + MORE!



For more lighting accessory design tips: www.progresslighting.com/accessories



