



# PRODUCT LAUNCH

FALL 2021

 **PROGRESS  
LIGHTING™**

# BRIARWOOD

The Briarwood collection features a classic pattern commonly found on barn or farmhouse doors and gates. The simple geometric form features a faux-painted wood enclosure to frame vintage-style light bulbs.

[View This Collection Online](#)





P400047-031



P400047-141



P710012-031



P710012-141



## BRIARWOOD

### FOUR-LIGHT CHANDELIER

**P400047-031** Textured Black &  
20" sq., 12" ht. Cerused Black Oak  
Overall ht. w/stem 88", wire 15'.  
Four medium base lamps.  
100w max.

[Product Page](#) [Spec Sheet](#)

### FOUR-LIGHT CHANDELIER

**P400047-141** Galvanized &  
20" sq., 12" ht. Bleached Oak  
Overall ht. w/stem 88", wire 15'.  
Four medium base lamps.  
100w max.

[Product Page](#) [Spec Sheet](#)

### ONE-LIGHT WALL SCONCE

**P710012-031** Textured Black &  
6-7/8" W., 12" ht. Cerused Black Oak  
Extends 6", H/CTR 4".  
One medium base lamp.  
100w max.

[Product Page](#) [Spec Sheet](#)

### ONE-LIGHT WALL SCONCE

**P710012-141** Galvanized &  
6-7/8" W., 12" ht. Bleached Oak  
Extends 6", H/CTR 4".  
One medium base lamp.  
100w max.

[Product Page](#) [Spec Sheet](#)

**PROGRESS**  
LIGHTING™

WWW.PROGRESSLIGHTING.COM

# CANEBRAKE

Canebrake embraces traditional forms with an artisanal flair.  
The generous scale creates an elegant focal point for any room.

[View This Collection Online](#)






P400291-31M



P400292-31M



## CANEBRAKE

### *FIVE-LIGHT CHANDELIER*

P400291-31M

Matte Black

30-1/8" Dia., 18" ht.

Overall ht. w/chain 93", wire 15'.

Five candelabra base lamps.

60w max.

[Product Page](#)

[Spec Sheet](#)

### *SIX-LIGHT CHANDELIER*

P400292-31M

Matte Black

40" Dia., 24" ht.

Overall ht. w/chain 99", wire 15'.

Six candelabra base lamps.

60w max.

[Product Page](#)

[Spec Sheet](#)

**PROGRESS  
LIGHTING™**

WWW.PROGRESSLIGHTING.COM

# DRUM SHADE

A perennially popular look, the simple lines of the Drum Shade pendant are refreshed with a Brushed Bronze finish, giving an elegant update to this classic fixture.

[View This Collection Online](#)





P4217-109



## DRUM SHADE

### *FIVE-LIGHT CHANDELIER*

P4217-109

Brushed Bronze

21-5/8" Dia., 21-1/8" ht.

Overall ht. w/chain 66-1/8", wire 10'.

Five candelabra base lamps.

60w max.

[Product Page](#)

[Spec Sheet](#)

**PROGRESS**  
LIGHTING™

WWW.PROGRESSLIGHTING.COM

# CALAIS

Timeless details create an enduring silhouette for Calais. Clear glass is supported by an elegantly simple frame providing a contemporary take on a traditional style.

[View This Collection Online](#)







P300362-009



P300362-163



P300362-31M



## CALAIS

### THREE-LIGHT BATH

P300362-009

Brushed Nickel

24-1/4" W., 8-1/2" ht.

Extends 6-1/2". H/CTR 5-1/2".

Three medium base lamps.

60w max.

[Product Page](#)

[Spec Sheet](#)

### THREE-LIGHT BATH

P300362-163

Vintage Brass

24-1/4" W., 8-1/2" ht.

Extends 6-1/2". H/CTR 5-1/2".

Three medium base lamps.

60w max.

[Product Page](#)

[Spec Sheet](#)

### THREE-LIGHT BATH

P300362-31M

Matte Black

24-1/4" W., 8-1/2" ht.

Extends 6-1/2". H/CTR 5-1/2".

Three medium base lamps.

60w max.

[Product Page](#)

[Spec Sheet](#)



Fixtures mount  
up or down.

**PROGRESS**  
LIGHTING™

WWW.PROGRESSLIGHTING.COM

# ELARA

Elara features a slender, chic form with a stylized finial inspired by a chess pawn for a classically modern style.

[View This Collection Online](#)





P300358-009



P300358-163



P300358-31M



## ELARA

### *THREE-LIGHT BATH*

**P300358-009**

Brushed Nickel

22-1/8" W., 11-1/2" ht.

Extends 5-1/8". H/CTR 6-3/4".

Three candelabra base lamps.

60w max.

[Product Page](#)

[Spec Sheet](#)

### *THREE-LIGHT BATH*

**P300358-163**

Vintage Brass

22-1/8" W., 11-1/2" ht.

Extends 5-1/8". H/CTR 6-3/4".

Three candelabra base lamps.

60w max.

[Product Page](#)

[Spec Sheet](#)

### *THREE-LIGHT BATH*

**P300358-31M**

Matte Black

22-1/8" W., 11-1/2" ht.

Extends 5-1/8". H/CTR 6-3/4".

Three candelabra base lamps.

60w max.

[Product Page](#)

[Spec Sheet](#)

**PROGRESS  
LIGHTING™**

WWW.PROGRESSLIGHTING.COM

# EVA

Eva has an eye-catching, two-toned color scheme. Light reflects from the shade to offer nostalgic charm for today's home.

[View This Collection Online](#)





P350217-164

---



P350217-31M

---



Shown with G30 bulb.

## EVA

### *ONE-LIGHT FLUSH MOUNT*

**P350217-164** Coastal Blue & Brushed Nickel  
7-3/8" Dia., 4-1/2" ht.  
One medium base lamp.  
60w max.

[Product Page](#)

[Spec Sheet](#)

### *ONE-LIGHT FLUSH MOUNT*

**P350217-31M** Matte Black & Brushed Bronze  
7-3/8" Dia., 4-1/2" ht.  
One medium base lamp.  
60w max.


[Product Page](#)

[Spec Sheet](#)

**PROGRESS  
LIGHTING™**

WWW.PROGRESSLIGHTING.COM





INDOOR with DC Motor

# CARROLLWOOD

## 6 BLADE 56" CEILING FAN

P250074-009-30	Brushed Nickel
P250074-030-30	White
P250074-31M-30	Matte Black

[View This Collection Online](#)

**SIZE**  
56" Dia., 18" ht.  
80" lead wires.

**ENERGY INFORMATION AT HIGH SPEED**

<i>Airflow</i>	6857 CFM
<i>Electricity Use</i>	36 W
<i>DOE Weighted CFM/W</i>	224 CFM/WATT

[View Energy Guide](#)

**LAMP**  
18w LED Module, 3000K,  
90 CRI, 1400 lumens.



P250074-009-30  
With Chrome Accent Bands



P250074-030-30  
With Vintage Gold  
Accent Bands



P250074-31M-30  
With Vintage Gold  
Accent Bands



# KASOTA

Kasota is damp rated, making it ideal for outdoor and indoor settings. A sturdy metal housing and long lines bring contemporary style to Kasota. Three rectangular ABS fan blades with long blade arms that span the entire length are finished in a linen-like texture that softens its modern look. It has a DC motor for the highest efficacy and whisper-quiet operation. A full-function remote control with a battery and a LED light kit with a white opal glass shade is included.

[View This Collection Online](#)



INDOOR / OUTDOOR with DC Motor







INDOOR / OUTDOOR with DC Motor

P250072-108-30



P250072-143-30



P250072-152-30



## KASOTA

Indoor & Outdoor

### 3 BLADE 56" CEILING FAN

P250072-108-30	Oil Rubbed Bronze
P250072-143-30	Graphite
P250072-152-30	Painted Nickel

[View This Collection Online](#)

#### SIZE

56" Dia., 15" ht.  
80" lead wires.

#### ENERGY INFORMATION AT HIGH SPEED

<i>Airflow</i>	4844 CFM
<i>Electricity Use</i>	31 W
<i>DOE Weighted CFM/W</i>	188 CFM/WATT

[View Energy Guide](#)

#### LAMP

18w LED Module, 3000K,  
90 CRI, 1400 lumens.



**PROGRESS**  
LIGHTING™

WWW.PROGRESSLIGHTING.COM

# MESILLA

Mesilla has an organic style that delivers natural grace and beauty to indoor and outdoor rooms. Its flower-like silhouette comes from five hand-finished ABS blades that gently wrap around the housing, with a single metal band that seems to be holding the blades on, creating a beautiful focal point. Mesilla has a DC motor for the highest efficacy and whisper-quiet operation. A full-function remote control with a battery is included.

[View This Collection Online](#)



INDOOR / OUTDOOR with DC Motor





INDOOR / OUTDOOR with DC Motor

# MESILLA

Indoor & Outdoor

## 5 BLADE 60" CEILING FAN

- P250073-020                      Antique Bronze
- P250073-081                      Antique Nickel
- P250073-182                      Flat Black

[View This Collection Online](#)

**SIZE**  
60" Dia., 14-1/4" ht.  
80" lead wires.

**ENERGY INFORMATION AT HIGH SPEED**

<i>Airflow</i>	6966 CFM
<i>Electricity Use</i>	38 W
<i>DOE Weighted CFM/W</i>	217 CFM/WATT

[View Energy Guide](#)



P250073-020



P250073-081



P250073-182



# SPICER

Sleek lines and solid metal housing offer an urban industrial edge to Spicer. Three curved, hand-finished ABS blades rotate around a slim, smooth fan body, giving sophisticated style to indoor and outdoor rooms. Spicer has a DC motor for the highest efficacy and whisper-quiet operation. A full-function remote control with a battery is included.

[View This Collection Online](#)



INDOOR / OUTDOOR with DC Motor





INDOOR / OUTDOOR with DC Motor



P250071-009



P250071-020



P250071-31M

## SPICER

Indoor & Outdoor

### 3 BLADE 54" CEILING FAN

P250071-009	Brushed Nickel
P250071-020	Antique Bronze
P250071-31M	Matte Black

[View This Collection Online](#)

#### SIZE


54" Dia., 11-9/16" ht.  
80" lead wires.

#### ENERGY INFORMATION AT HIGH SPEED

<i>Airflow</i>	4521 CFM
<i>Electricity Use</i>	35 W
<i>DOE Weighted CFM/W</i>	158 CFM/WATT

[View the Energy Guide](#)





## See Yourself Here

Every home and every family has a story that's all their own. In this issue, we introduce you to the many ways Progress Lighting can bring that story to life.



PROGRESS LIGHTING

701 Millennium Boulevard  
Greenville, SC 29607

[www.progresslighting.com](http://www.progresslighting.com)



PL\_1648 08/21