



PRODUCT SUPPLEMENT WINTER 2022

 **PROGRESS**
LIGHTING™

See Yourself Here.

Lighting helps tell a story, whether it's setting the mood or enjoying a special moment. These occasions are meaningful, expressive, and shared with those we care about most. Let Progress Lighting be your guide in illuminating these spaces into special places.



Be Inspired

- [@ProgressLtg](#)
- [@ProgressLtg](#)
- [@ProgressLighting](#)
- [@ProgressLtg](#)
- [Progress Lighting](#)
- [Progress-Lighting](#)

Table of Contents

Light up your life by finding the perfect fixtures that express your personal style, inside and out.

[Pictorial Index](#) 4

[DESIGN+SERIES™ Catalog Index](#) 22




[Collections](#) 22

[Jeffrey Alan Marks](#) 24

[Collections](#) 28



[Ceiling Fan Catalog Index](#) 17



[LED Collections](#) 88



[Close-To-Ceiling](#) 112



[Pendants](#) 102



[Outdoor](#) 170



[Bath Collections](#) 126



[Recessed Downlighting](#) 200



[Surface Mount Downlighting](#) 204




[Undercabinet](#) 206



[Index](#) 207

Collections

BRIARWOOD
Galvanized p.62



BRIARWOOD
Textured Black p.65



CANEBRAKE
Matte Black p.55



CLIFTON HEIGHTS
Matte Black p.80



DRUM SHADE
Brushed Bronze p.105



LOCKHART
Matte Black p.58



MARIPOSA
Antique Gold p.28



MARIPOSA
Gilded Silver p.31



MERRY
Brushed Nickel p.82



MERRY
Matte Black p.84



ELARA
Brushed Nickel p.42



ELARA
Matte Black p.42



ELARA
Vintage Brass p.42



ELARA
Brushed Nickel p.44



ELARA
Matte Black p.44



MILL BEAM
Brushed Nickel p.46



PARKHURST
Brushed Bronze p.32



PARKHURST
Brushed Nickel p.36



PARKHURST
Matte Black p.38




PARKHURST
Brushed Bronze p.34



ELARA
Vintage Brass p.44



HEDGEROW
Brushed Nickel p.48




HEDGEROW
Distressed Brass p.50



KELLWYN
Brushed Nickel p.68



KELLWYN
Matte Black p.71




PARKHURST
Brushed Nickel p.37



PARKHURST
Matte Black p.39




PARKHURST
Brushed Bronze p.34



PARKHURST
Brushed Nickel p.37



PARKHURST
Brushed Nickel p.39



LAVELLE
Matte Black p.52



LEAGUE
Brushed Nickel p.72



LEAGUE
Matte Black p.74



LEYDEN
Brushed Nickel p.76




LEYDEN
Matte Black p.79




STOCKBRACE
Matte Black p.56



THORPE
Brushed Nickel p.40


























THORPE
Satin Brass p.40






VININGS
Brushed Nickel p.66



LED Collections

EVERLUME™ LED Brushed Nickel p.99 	EVERLUME™ LED Matte Black p.99 	GEODESIC LED Matte Black p.98 	INVERSE LED Brushed Nickel p.100 	INVERSE LED Matte Black p.100 
KYLO LED Brushed Nickel p.95 	KYLO LED Matte Black p.92 	KYLO LED Brushed Nickel p.95 	KYLO LED Matte Black p.93 	KYLO LED Brushed Nickel p.95 
KYLO LED Matte Black p.93 	PIVOT LED Burnished Nickel p.88 	PIVOT LED Matte Black p.88 	PIVOT LED Satin White p.89 	PLANCK LED Brushed Nickel p.99 
QUADRANT LED Matte Black p.96 	RADIAN LED Brushed Nickel p.101 	RADIAN LED Matte Black p.101 	RADIAN LED Satin White p.101 	SPOKE LED Brushed Nickel p.90 
SPOKE LED Matte Black p.91 	SPOKE LED Brushed Nickel p.91 	SPOKE LED Matte Black p.91 		

Pendants

ATWELL Brushed Bronze p.107 	ATWELL Brushed Nickel p.107 	ATWELL Matte Black p.107 	BRIARWOOD Galvanized p.63 	BRIARWOOD Textured Black p.65 
BRIARWOOD Galvanized p.63 	BRIARWOOD Textured Black p.65 	CHASTAIN Bleached Oak p.102 	CHASTAIN Cerused Black Oak p.103 	CLIFTON HEIGHTS Matte Black p.81 
CLIFTON HEIGHTS Matte Black p.81 	DELAYNE Brushed Bronze p.104 	DELAYNE Brushed Nickel p.104 	DELAYNE Matte Black p.104 	DRUM SHADE Brushed Bronze p.105 
HEDGEROW Brushed Nickel p.49 	HEDGEROW Distressed Brass p.51 	HINTON Brushed Nickel p.110 	HINTON Brushed Nickel p.110 	HINTON Matte Black p.110 
HINTON Matte Black p.110 	HINTON Polished Nickel p.110 	HINTON Polished Nickel p.110 	HINTON Vintage Brass p.110 	HINTON Vintage Brass p.110 

Pendants

KELLWYN Brushed Nickel p.69	KELLWYN Matte Black p.71	LAVELLE Matte Black p.53	LEAGUE Brushed Nickel p.73	LEAGUE Matte Black p.75
LEYDEN Brushed Nickel p.77	LEYDEN Matte Black p.79	LORIN Burnished Nickel p.105	LORIN Matte Black p.105	LORIN Satin White p.105
MILL BEAM Brushed Nickel p.47	PARKHURST Brushed Bronze p.33	PARKHURST Brushed Nickel p.37	PARKHURST Matte Black p.39	PARKHURST Brushed Bronze p.108
PARKHURST Brushed Nickel p.108	PARKHURST Matte Black p.108	RUSHTON Brushed Nickel p.106	RUSHTON Graphite p.106	TERRAZZO Distressed Brass p.106
TERRAZZO Graphite p.106	TREMONT Matte Black p.189	TREMONT Stainless Steel p.189		

Close-to-Ceiling

ADLEY Brushed Nickel p.121	ADLEY Satin Brass p.121	ADLEY Polished Nickel p.121	ADLEY Matte Black p.121	AIKEN Brushed Nickel p.118
AIKEN Vintage Brass p.118	ATWELL Brushed Bronze p.120	ATWELL Brushed Nickel p.120	ATWELL Matte Black p.120	BRIARWOOD Galvanized p.63
BRIARWOOD Textured Black p.65	CLIFTON HEIGHTS Matte Black p.81	DELAYNE Brushed Bronze p.114	DELAYNE Brushed Nickel p.114	DELAYNE Matte Black p.114
EVA Coastal Blue p.116	EVA Matte Black p.116	GULLIVER Galvanized Finish p.113	GULLIVER Graphite p.113	HANSFORD Vintage Brass p.117
HEDGEROW Brushed Nickel p.49	HEDGEROW Distressed Brass p.51	HINTON Brushed Nickel p.112	HINTON Matte Black p.112	HINTON Polished Nickel p.112

Close-to-Ceiling

HINTON Vintage Brass p.112 **HINTON** Brushed Nickel p.112 **HINTON** Matte Black p.112 **HINTON** Polished Nickel p.112 **HINTON** Vintage Brass p.112



INSPIRE Satin Brass p.122 **JUDSON** Antique Bronze p.116 **JUDSON** Polished Nickel p.116 **KELLWYN** Brushed Nickel p.69 **KELLWYN** Matte Black p.71



LAVELLE Matte Black p.53 **LINEN DOME** Brushed Nickel p.123 **MARIPOSA** Antique Gold p.29 **MARIPOSA** Gilded Silver p.31 **MEDAL** Graphite p.113



MEDAL Vintage Brass p.113 **PERIMETER** Brushed Nickel p.117 **PERIMETER** Matte Black p.117 **PERIMETER** Satin Brass p.117 **STOCKBRACE** Matte Black p.57



VININGS Brushed Nickel p.67



Sconces/Wall Brackets

AIKEN Brushed Nickel p.152 **AIKEN** Vintage Brass p.152 **AMBROSE** Matte Black p.144 **AMBROSE** Polished Chrome p.144 **ASHFORD** Brushed Nickel p.164



ASHFORD Polished Chrome p.164 **AXLE** Antique Bronze p.157 **AXLE** Brushed Nickel p.157 **BRIARWOOD** Galvanized p.65 **BRIARWOOD** Textured Black p.67



CALAIS Brushed Nickel p.134 **CALAIS** Matte Black p.134 **CALAIS** Vintage Brass p.134 **CALHOUN** Vintage Brass p.142 **CAISSON** Brushed Nickel p.140



CAISSON Graphite p.140 **CARRICK** Brushed Nickel p.124 **CARRICK** Vintage Brass p.124 **CARRICK** Matte Black p.124 **CLARION** Brushed Nickel p.129



CLARION Matte Black p.129 **CLARION** Polished Chrome p.129 **CLARION** Satin Brass p.129 **CLIFTON HEIGHTS** Matte Black p.166 **CONWAY** Brushed Nickel p.154



Sconces/Wall Brackets

CONWAY Matte Black p.154 **COWAN** Brushed Nickel p.130 **COWAN** Matte Black p.130 **COWAN** Satin Brass p.130 **CURVED LED** Opal White p.125



DALTON Polished Chrome p.138 **DALTON** Vintage Brass p.138 **ELARA** Brushed Nickel p.45 **ELARA** Vintage Brass p.45 **ELARA** Matte Black p.45



GILMOUR Brushed Nickel p.158 **GILMOUR** Matte Black p.158 **HANSFORD** Vintage Brass p.150 **LEAGUE** Brushed Nickel p.162 **LEAGUE** Matte Black p.162



MERRY Brushed Nickel p.167 **MERRY** Matte Black p.167 **MILL BEAM** Brushed Nickel p.156 **OPAL GLASS** Matte Black p.125 **PEARL LED** Matte Black p.126



PEARL LED Satin Brass p.126 **QUADRANT LED** Matte Black p.99 **STOCKBRACE** Matte Black p.59



Bath Collections

ADLEY Brushed Nickel p.168 **ADLEY** Matte Black p.168 **ADLEY** Satin Brass p.168 **AIKEN** Brushed Nickel p.152 **AIKEN** Vintage Brass p.152



AMBROSE Matte Black p.144 **AMBROSE** Polished Chrome p.144 **ASHFORD** Brushed Nickel p.164 **ASHFORD** Polished Chrome p.164 **AXLE** Antique Bronze p.157



AXLE Brushed Nickel p.157 **CAISSON** Brushed Nickel p.140 **CAISSON** Graphite p.140 **CALAIS** Brushed Nickel p.134 **CALAIS** Matte Black p.134




























CALAIS Vintage Brass p.134 **CALHOUN** Vintage Brass p.142 **CLARION** Brushed Nickel p.129 **CLARION** Matte Black p.129 **CLARION** Polished Chrome p.129






CLARION Satin Brass p.129 **CLIFTON HEIGHTS** Matte Black p.166 **CONWAY** Brushed Nickel p.154 **CONWAY** Matte Black p.154 **COWAN** Brushed Nickel p.130























Bath Collections

COWAN Matte Black p.130	COWAN Satin Brass p.130	DALTON Polished Chrome p.138	DALTON Vintage Brass p.138	ELARA Brushed Nickel p.132
				
ELARA Matte Black p.132	ELARA Vintage Brass p.132	EVERLUME LED Brushed Nickel p.128	EVERLUME LED Satin White p.128	GILMOUR Brushed Nickel p.158
				
GILMOUR Matte Black p.158	GRID LED Matte Black p.127	GRID LED Silver Ridge p.127	HANSFORD Vintage Brass p.150	HINTON Brushed Nickel p.146
				
HINTON Vintage Brass p.146	HINTON Matte Black p.146	LEAGUE Brushed Nickel p.162	LEAGUE Matte Black p.162	MERRY Brushed Nickel p.167
				
MERRY Matte Black p.167	MILL BEAM Brushed Nickel p.156	PEARL LED Matte Black p.126	PEARL LED Satin Brass p.126	REPLAY Antique Bronze p.169
				

Bath Collections

REPLAY Brushed Nickel p.169	REPLAY Polished Nickel p.169	REPLAY Textured Black p.169
		

Outdoor

BARLOWE Antique Bronze p.193	BARLOWE Stainless Steel p.193	BIRKDALE Antique Bronze p.175	BIRKDALE Textured Black p.175	CEDAR SPRINGS White p.174
				
CEDAR SPRINGS Black p.174	CEDAR SPRING Red p.174	CHILTON Textured Black p.176	CORD MOUNT ALUMINUM CYLINDERS Antique Bronze p.196	CORD MOUNT ALUMINUM CYLINDERS Black p.196
				
CORD MOUNT ALUMINUM CYLINDERS White p.196	CORD MOUNT ALUMINUM CYLINDERS LED Antique Bronze p.196	CORD MOUNT ALUMINUM CYLINDERS LED Black p.196	PHOTOCELL ALUMINUM CYLINDERS LED Antique Bronze p.197	PHOTOCELL ALUMINUM CYLINDERS LED Black p.197
				
ROUND WET LOCATION CYLINDERS Antique Bronze p.198	ROUND WET LOCATION CYLINDERS Black Bronze p.198	SQUARE WET LOCATION CYLINDERS Antique Bronze p.199	SQUARE WET LOCATION CYLINDERS Black p.199	CRAWFORD Antique Bronze p.191
				

Outdoor

DILLARD Antique Bronze p.180 **DILLARD** Textured Black p.180 **DISTRICT** Textured Black p.191 **EXTON** Textured Black p.188 **GABLES** Satin White p.178



GABLES Antique Bronze p.179 **GRANDBURY** Antique Bronze p.177 **HARD-NOX LED** Black p.194 **HARD-NOX LED** Satin White p.194 **HARD-NOX LED** Black p.194



HARD-NOX LED Satin White p.194 **HARD-NOX LED** Black p.194 **HARD-NOX LED** Satin White p.194 **HARD-NOX LED** Satin White p.194 **MANTEO** Cottage White p.173



MILFORD NON-METALLIC LANTERN Textured Black p.192 **NAVARRE** Matte Black p.170 **PADGETT** Antique Bronze p.190 **PADGETT** Textured Black p.190 **PAWLEY** Galvanized Finish p.172



Outdoor

PAWLEY Matte Black p.172 **STATURE** Oil Rubbed Bronze p.182 **STATURE** Textured Black p.182 **TREMONT** Matte Black p.189 **TREMONT** Stainless Steel p.189



TERRACE Matte Black p.171 **TRAFFORD NON-METALLIC LANTERN** Textured Black p.192 **WAKEFORD** Antique Copper p.183 **WALCOTT** Antique Bronze p.186 **WATCH HILL** Textured Black p.185




WHITMIRE Matte Black p.187 **WILLIAMSTON** Antique Bronze p.184 **WILLIAMSTON** Antique Pewter p.184 **Z-2020 LED** Satin White p.195 **Z-2020 LED** Textured Black p.195























Z-2025 LED Satin White p.195 **Z-2025 LED** Textured Black p.195



Indoor Ceiling Fans






See the 2022 Ceiling Fan Catalog or progresslighting.com for product details.

AIRPRO Brushed Nickel N 	AIRPRO Polished Chrome N 	AIRPRO Antique Bronze N 
AIRPRO White N 	AIRPRO Graphite N 	AIRPRO Matte Black N 
AIRPRO Brushed Nickel N 	AIRPRO White N 	AIRPRO Matte Black N 
AIRPRO Matte Black N 	AIRPRO Brushed Nickel N 	AIRPRO White N 
AIRPRO Matte Black N 	AIRPRO White N 	AIRPRO (P250066) Brushed Nickel N 
AIRPRO (P250066) White N 	AIRPRO (P250066) Matte Black N 	AIRPRO ENERGY STAR Brushed Nickel N 
AIRPRO ENERGY STAR White N 	AIRPRO ENERGY STAR Matte Black N 	

N NEW PRODUCT

WWW.PROGRESSLIGHTING.COM

Indoor Ceiling Fans


AIRPRO ENERGY STAR Brushed Nickel N 	AIRPRO ENERGY STAR White N 	AIRPRO ENERGY STAR Matte Black N 	AIRPRO ENERGY STAR Brushed Nickel N 	AIRPRO ENERGY STAR White N 
AIRPRO ENERGY STAR Matte Black N 	ALLERON Antique Nickel N 	ALLERON Flat Black N 	44" BRADEN Brushed Nickel N 	44" BRADEN Matte White N 
44" BRADEN Matte Black N 	CARROLLWOOD Brushed Nickel N 	CARROLLWOOD White N 	CARROLLWOOD Matte Black N 	CLARET Brushed Nickel N 
CLARET Matte Black N 	CLARET Oil Rubbed Bronze N 	EDWIDGE Matte White N 	EDWIDGE Matte Black N 	EDWIDGE Painted Nickel N 
GLENFALLS Brushed Nickel N 	GLENFALLS Matte White N 	GLENFALLS Matte Black N 	KAYSVILLE Antique Nickel N 	KAYSVILLE Graphite N 

N NEW PRODUCT

WWW.PROGRESSLIGHTING.COM


Indoor Ceiling Fans

See the 2022 Ceiling Fan Catalog or progresslighting.com for product details.



Outdoor Ceiling Fans

See the 2022 Ceiling Fan Catalog or progresslighting.com for product details.





See the 2022 Design Series Catalog or progresslighting.com for product details.

DESIGN SERIES CATALOG INDEX

ELEVATE
Brushed Bronze



ELEVATE
Polished Chrome



ELEVATE
Matte Black




LOWERY
Textured Black



METRO
Matte Black



METRO
Satin Brass



SAFFERT
Brushed Nickel



SAFFERT
Matte Black



SAFFERT
Vintage Brass



SAFFERT
Brushed Nickel



SAFFERT
Matte Black



SAFFERT
Vintage Brass



SAFFERT
Brushed Nickel



SAFFERT
Matte Black



SAFFERT
Vintage Brass



SAFFERT
Brushed Nickel



SAFFERT
Matte Black



SAFFERT
Vintage Brass



UNION SQUARE
Stainless Steel



N New Product

See the 2022 Design Series Catalog or progresslighting.com for product details.

JEFFREY ALAN MARKS
POINT DUME™ COLLECTION

POINT DUME™ COLLECTION

JEFFREY ALAN MARKS

DUNMERE
Galvanized



DUNMERE
Matte Black



DUNMERE
Shelter White



EDGECLIFF
Galvanized



EDGECLIFF
Oil Rubbed Bronze



EDGECLIFF
Shelter White



HOOK POND
Galvanized



HOOK POND
Shelter White



HOOK POND
Oil Rubbed Bronze



SEAMOOR
Galvanized



SEAMOOR
Oil Rubbed Bronze



SHADMORE
Galvanized



SHADMORE
Matte Black



WAKECREST LED
Galvanized



WAKECREST LED
Matte Black



WAKECREST LED
Shelter White



See the 2022 Jeffrey Alan Marks Catalog or
progresslighting.com for product details.

See the 2022 Jeffrey Alan Marks Catalog or
progresslighting.com for product details.



Neutral colors, touches of warm wood, and strong vertical lines unify an open plan space.

1

Place a pair of oversized pendants like Parkhurst to give structure and definition to the kitchen island.

2

Continue the bold lighting theme with the Saffert pendant over the dining table, whose substantial scale offers a modern urban look.

3

Stir the air in style with the sleek lines and solid metal silhouette of the Spicer ceiling fan.

Mariposa

P500416-168


FINISHES

- Antique Gold - 168
- Gilded Silver - 176

PAIR WITH

- Spicewood
- Gresham

Take a naturalistic approach to modern room design with Mariposa. Slender branches bloom outward from the central stem, bearing delicate leaves finished in bright and luxurious tones. Mariposa's organic feel is balanced by the minimalist lines of its multi-directional light arrangement, bringing a fresh touch to a range of settings seeking a global flair.



P350210-168
shown as semi-flush

Mariposa

SEMI-FLUSH CONVERTIBLE

P350210-168 Antique Gold
Hanging and ceiling mount hardware included.
20" dia., 8-3/8" ht.
Overall ht. w/stem 33-1/2", wire 36".
Five candelabra base lamps, each 60w max.

SIX-LIGHT PENDANT

P500415-168 Antique Gold
28" dia., 20" ht.
Overall ht. w/stem 75", wire 15'.
Six candelabra base lamps, each 60w max.

EIGHT-LIGHT PENDANT

P500416-168 Antique Gold
36" dia., 25" ht.
Overall ht. w/stem 77-1/2", wire 15'.
Eight candelabra base lamps, each 60w max.



Antique Gold finish detail



Featuring Mariposa and Clarion

Naturally Inspired Design

Take a naturalistic approach to modern room design with organic décor. Soothing blue-sky walls and a clean white color palette create a calming backdrop that is punctuated by the stunning Mariposa chandelier. Mariposa's organic feel is balanced by the minimalist lines of its multi-directional light arrangement, making a striking focal point. The clear glass shades of the Clarion pendants offer a simple form and functionality that complements the serene setting.

Mariposa



P500416-176

SEMI-FLUSH CONVERTIBLE
P350210-176 Gilded Silver
 Hanging and ceiling mount hardware included.
 20" dia., 8-3/8" ht.
 Overall ht. w/stem 33-1/2", wire 36".
 Five candelabra base lamps, each 60w max.

SIX-LIGHT PENDANT
P500415-176 Gilded Silver
 28" dia., 20" ht.
 Overall ht. w/stem 75", wire 15'.
 Six candelabra base lamps, each 60w max.

EIGHT-LIGHT PENDANT
P500416-176 Gilded Silver
 36" dia., 25" ht.
 Overall ht. w/stem 77-1/2", wire 15'.
 Eight candelabra base lamps, each 60w max.



Gilded Silver finish detail



P500415-176




P350210-176
 shown as semi-flush

FINISHES

- Brushed Nickel - 009
- Brushed Bronze - 109
- Matte Black - 31M

P400297-109



Graceful curves and bold angles combine to create a softly structured look in Parkhurst. An airy frame defines the form to produce unobstructed layers of light.

P400296-109



THREE-LIGHT CHANDELIER
P400295-109 Brushed Bronze
 21" dia., 12-1/4" ht.
 Overall ht. w/stem 78", wire 10'.
 Three medium base lamps,
 60w max.

FIVE-LIGHT CHANDELIER
P400296-109 Brushed Bronze
 25-1/4" dia., 12-1/2" ht.
 Overall ht. w/stem 78-1/2", wire 10'.
 Five candelabra lamps,
 each 60w max.

SIX-LIGHT CHANDELIER
P400297-109 Brushed Bronze
 30" dia., 14" ht.
 Overall ht. w/ stem 80", wire 10'.
 Six candelabra lamps,
 each 60w max.

ONE-LIGHT PENDANT
P500361-109 Brushed Bronze
 15-1/4" dia., 23-3/8" ht.
 Overall ht. w/stem 89-1/2", wire 10'.
 One medium base lamp,
 60w max.

ONE-LIGHT PENDANT
P500360-109 Brushed Bronze
 11-1/2" dia., 16-3/4" ht.
 Overall ht. w/stem 83", wire 10'.
 One medium base lamp,
 60w max.

P400295-109



P500360-109



P500361-109



SIX-LIGHT LINEAR CHANDELIER

P400300-109 Brushed Bronze
42" L., 15-1/8" ht.
Overall ht. w/stem 89-1/2", wire 10'.
Six candelabra lamps,
each 60w max.

EIGHT-LIGHT FOYER

P500371-109 Brushed Bronze
36" ht., 20" sq.
Overall ht. w/chain 108", wire 15'.
Eight candelabra lamps,
each 60w max.



See the full collection at progresslighting.com.



THREE-LIGHT CHANDELIER

P400295-009 Brushed Nickel
21" dia., 12-1/4" ht.
Overall ht. w/stem 78", wire 10'.
Three medium base lamps,
60w max.

FIVE-LIGHT CHANDELIER

P400296-009 Brushed Nickel
25-1/4" dia., 12-1/2" ht.
Overall ht. w/stem 78-1/2", wire 10'.
Five candelabra lamps,
each 60w max.

SIX-LIGHT CHANDELIER

P400297-009 Brushed Nickel
30" dia., 14" ht.
Overall ht. w/ stem 80", wire 10'.
Six candelabra lamps,
each 60w max.



SIX-LIGHT LINEAR CHANDELIER

P400300-009 Brushed Nickel
42" L., 15-1/8" ht.
Overall ht. w/stem 89-1/2", wire 10'.
Six candelabra lamps,
each 60w max.

ONE-LIGHT PENDANT

P500360-009 Brushed Nickel
11-1/2" dia., 16-3/4" ht.
Overall ht. w/stem 83", wire 10'.
One medium base lamp,
60w max.

ONE-LIGHT PENDANT

P500361-009 Brushed Nickel
15-1/4" dia., 23-3/8" ht.
Overall ht. w/stem 89-1/2", wire 10'.
One medium base lamp,
60w max.

EIGHT-LIGHT FOYER

P500371-009 Brushed Nickel
36" ht., 20" sq.
Overall ht. w/chain 108", wire 15'.
Eight candelabra lamps,
each 60w max.



See the full collection at progresslighting.com.

THREE-LIGHT CHANDELIER

P400295-31M Matte Black
21" dia., 12-1/4" ht.
Overall ht. w/stem 78", wire 10'.
Three medium base lamps,
60w max.

FIVE-LIGHT CHANDELIER

P400296-31M Matte Black
25-1/4" dia., 12-1/2" ht.
Overall ht. w/stem 78-1/2", wire 10'.
Five candelabra lamps,
each 60w max.

SIX-LIGHT CHANDELIER

P400297-31M Matte Black
30" dia., 14" ht.
Overall ht. w/ stem 80", wire 10'.
Six candelabra lamps,
each 60w max.



SIX-LIGHT LINEAR CHANDELIER

P400300-31L Matte Black
42" L., 15-1/8" ht.
Overall ht. w/stem 89-1/2", wire 10'.
Six candelabra lamps,
each 60w max.

ONE-LIGHT PENDANT

P500360-31M Matte Black
11-1/2" dia., 16-3/4" ht.
Overall ht. w/stem 83", wire 10'.
One medium base lamp,
60w max.

ONE-LIGHT PENDANT

P500361-31M Matte Black
15-1/4" dia., 23-3/8" ht.
Overall ht. w/stem 89-1/2", wire 10'.
One medium base lamp,
60w max.

EIGHT-LIGHT FOYER

P500371-31M Matte Black
36" ht., 20" sq.
Overall ht. w/chain 108", wire 15'.
Eight candelabra lamps,
each 60w max.

Thorpe

A softer, playful ambiance is brought to mid-century design with Thorpe, whose starburst form is reinvented by a rustic twist on the space-age style. Angular lines make a clean and striking silhouette. The Brushed Nickel finish features a faux Barnwood finish while the Satin Brass finish is complimented by a faux Hickory wood finish.

FINISHES

- Brushed Nickel - 009
- Satin Brass - 012

PAIR WITH

Atwell
Clarion

FIVE-LIGHT CHANDELIER

P400270-009 Brushed Nickel

P400270-012 Satin Brass

27-5/8" dia., 23-7/8" ht.

Overall ht. w/stem 80-1/2", wire 15'

Five medium base lamps,
each 60w max.



Elara features a slender, chic form with a stylized finial inspired by a chess pawn for a classically modern style.

FINISHES

- Brushed Nickel - 009
- Vintage Brass - 163
- Matte Black - 31M

FOUR-LIGHT CHANDELIER

P400293-009 Brushed Nickel

P400293-163 Vintage Brass

P400293-31M Matte Black

22-7/8" dia., 10-3/8" ht.

Overall ht. w/stem 65", wire 10'.

Four candelabra lamps, each 60w max.



SIX-LIGHT CHANDELIER

P400294-009 Brushed Nickel

P400294-163 Vintage Brass

P400294-31M Matte Black

30" dia., 10-3/8" ht.

Overall ht. w/stem 65", wire 10'.

Six candelabra lamps, each 60w max.

ACCESSORY SHADES



See page 111 for details.



FOUR-LIGHT FOYER
P500363-009 Brushed Nickel
P500363-163 Vintage Brass
P500363-31M Matte Black
 15" dia., 31-3/8" ht.
 Overall ht. w/stem 88-1/2", wire 10'.
 Four candelabra lamps,
 each 60w max.



P500363-009



P500363-163



P500363-31M



P710106-009
 shown with
 P860061-068
 shade



P710107-009



P710106-163



P710107-163
 shown with
 P860060-000
 shade



P710106-31M
 shown with
 P860059-000
 shade



P710107-31M

ONE-LIGHT WALL BRACKET
P710106-009 Brushed Nickel
P710106-163 Vintage Brass
P710106-31M Matte Black
 5-3/4" W., 16-5/8" ht.; H/CTR 5-1/2".
 Extends 4-3/8"
 One candelabra lamp,
 60w max.

TWO-LIGHT WALL BRACKET
P710107-009 Brushed Nickel
P710107-163 Vintage Brass
P710107-31M Matte Black
 5-3/4" W., 16-5/8" ht., H/CTR 5-1/2".
 Extends 4-3/8"
 Two candelabra lamps,
 each 60w max.

ACCESSORY SHADES



P860059-000
 Drum
 White Linen



P860060-000
 Tapered
 White Linen



P860061-068
 Clear Glass

See page 111 for details.

Mill Beam

FINISH


● Brushed Nickel - 009

PAIR WITH

Hemsworth
Bonn

The beautiful contrasts of gleaming and rustic finishes are epitomized in Mill Beam, a linear form in a painted Gray Concrete faux finish that gives an unexpected artisanal edginess. Its slab silhouette showcases an industrial-inspired design and creates a perfect base for recessed sockets that allow decorative bulbs to take center stage in casting an eye-catching glow.

P400269-009



P710099-009

Mill Beam

SIX-LIGHT LINEAR CHANDELIER

P400269-009 Brushed Nickel
48" L., 2-3/8" W., 2-3/4" ht.
Overall ht. w/stem 54", wire 10'.
Six medium base lamps,
each 60w max.

TWO-LIGHT CONVERTIBLE MINI-PENDANT

P500328-009 Brushed Nickel
Hanging and ceiling mount
hardware included.
2-3/8" sq., 10-1/2" ht.
Overall ht. w/stem 54", wire 10'.
Two medium base lamps,
each 60w max.

WALL BRACKET

P710099-009 Brushed Nickel
Install facing up or down.
4-3/4" W., 7-1/8" ht.
Extends 4-3/8". H/CTR 3-5/8".
One medium base lamp, 60w max.

Hedgerow

FINISHES

- Brushed Nickel - 009
- Distressed Brass - 175

PAIR WITH


- Terrazzo
- Rushton

P400253-009

Hedgerow has a softly textured, artistic faux wood finish frame that elevates the look from a typical Farmhouse fixture to one of urban sophistication. The Brushed Nickel finish features a hand-painted faux Gray Washed Oak frame while the Distressed Brass finish has a faux Aged Oak frame. Hedgerow showcases a classic windowpane design to complement the traditional form and offers an overall lighter look and feel.

*Elevated
Farmhouse Style*

*Artistic Faux
Wood*



Windowpane Design



P400254-009



P400253-009



P500317-009



P350197-009

Hedgerow

ONE-LIGHT FLUSH MOUNT

P350197-009 Brushed Nickel
10-3/8" sq., 8" ht.
One medium base lamp, 60w max.

FOUR-LIGHT CHANDELIER

P400253-009 Brushed Nickel
21-3/8" sq., 12-7/8" ht.
Overall ht. w/stem 101-1/2", wire 15'.
Four candelabra base lamps,
each 60w max.

FIVE-LIGHT LINEAR CHANDELIER

P400254-009 Brushed Nickel
40" L., 11-3/8" W., 11" ht.
Overall ht. w/stem 100-1/2", wire 15'.
Five candelabra base lamps,
each 60w max.

MINI-PENDANT

P500317-009 Brushed Nickel
10-3/8" sq., 19-3/8" ht.
Overall ht. w/stem 94-1/2", wire 10'.
One medium base lamp, 60w max.

P400253-175



Distressed Brass

Artistic Form



Softly Textured

P400254-173



Hedgerow

ONE-LIGHT FLUSH MOUNT
P350197-175 Distressed Brass
10-3/8" sq., 8" ht.
One medium base lamp, 60w max.

FOUR-LIGHT CHANDELIER
P400253-175 Distressed Brass
21-3/8" sq., 12-7/8" ht.
Overall ht. w/stem 101-1/2", wire 15'.
Four candelabra base lamps,
each 60w max.

FIVE-LIGHT LINEAR CHANDELIER
P400254-175 Distressed Brass
40" L., 11-3/8" W., 11" ht.
Overall ht. w/stem 100-1/2", wire 15'.
Five candelabra base lamps,
each 60w max.

MINI-PENDANT
P500317-175 Distressed Brass
10-3/8" sq., 19-3/8" ht.
Overall ht. w/stem 94-1/2", wire 10'.
One medium base lamp, 60w max.

P400253-173



P500317-173



P350197-173



Lavelle

P500308-031

FINISH
● Matte Black - 031

PAIR WITH
Kempsey
Caisson

Artistry and texture combine in the Lavelle pendant collection for the ultimate in global design. A softly curved, black frame complements the airy open weave of the earthy, mocha colored rattan shade. Lavelle is the perfect accent for a carefree, relaxed lifestyle that embraces the natural world.

Softly Curved Frame

Rattan Shade



Global Design



P500308-031

Lavelle

SEMI-FLUSH CONVERTIBLE

P350183-031 Matte Black
Hanging and ceiling mount hardware included.
15-5/8" dia., 14-3/8" ht.
Overall ht. w/chain 75-1/2", wire 10'.
Three medium base lamps, each 60w max.

MINI-PENDANT

P500307-031 Matte Black
8" dia., 12-5/8" ht.
Overall ht. w/chain 102", wire 10'.
One medium base lamp, 60w max.

FOUR-LIGHT PENDANT

P500308-031 Matte Black
20-1/2" dia., 13-3/8" ht.
Overall ht. w/chain 103", wire 15'.
Four medium base lamps, each 60w max.



P350183-031



P350183-031
shown as semi-flush



P500307-031



Featuring Canebrake

A Perfect Blend of New and Old

A chandelier designed on a generous scale creates an ideal focal point in a great room. The Canebrake chandelier has flowing curved arms that embrace traditional forms yet offer an updated, artisanal flair to an otherwise classic silhouette.

Canebrake NEW

Canebrake embraces traditional forms with an artisanal flair. The generous scale creates an elegant focal point for any room.

FINISH

● Matte Black - 31M

FIVE-LIGHT CHANDELIER

P400291-31M Matte Black
30-1/8" dia., 18" ht.
Overall ht. w/chain 93", wire 15'.
Five medium base lamps,
each 60w max.

SIX-LIGHT CHANDELIER

P400292-31M Matte Black
40" dia., 24" ht.
Overall ht. w/chain 99", wire 15'.
Six medium base lamps,
each 60w max.



P400291-31M



P400292-31M

Stockbrace

FINISH
● Matte Black - 031

PAIR WITH
Briarwood
Lockhart

P400243-031

Inspired by traditional post-and-beam construction, Stockbrace presents a structured sense of visual transparency with its minimalist design. A metal frame features strut-like arms descending to a loop that supports clear glass shades. Clean lines, an open design and architectural details make Stockbrace a perfect complement to casual, modern and rustic interiors.

Minimalist Design

Architectural Details

Clean Glass Shades



P400243-031

Stockbrace

THREE-LIGHT FLUSH MOUNT
P350181-031 Matte Black
12-1/2" dia., 10" ht.
Three medium base lamp,
each 60w max.

THREE-LIGHT CHANDELIER
P400235-031 Matte Black
16" dia., 18" ht.
Overall ht. w/stem 84", wire 15'.
Three medium base lamps,
each 60w max.

FIVE-LIGHT CHANDELIER
P400243-031 Matte Black
24" dia., 22-1/2" ht.
Overall ht. w/stem 88-1/2", wire 15'.
Five medium base lamps,
each 60w max.

WALL BRACKET
P710097-031 Matte Black
4-3/4" W., 13-1/2" ht.
Extends 5-1/2". H/CTR 9-1/2".
One medium base lamp, 60w max.



P400235-031



P710097-031



P350181-031

Lockhart

P500279-031

FINISH

● Matte Black - 031

PAIR WITH

Hemsworth
Rushton

Bold in scale with an industrial vibe, Lockhart mixes a central band, finished in a hand-painted Aged Oak faux wood with curved metal arms, enclosing a candle cluster that casts a soft, warm illumination. Its open form fills a room with substance without weight, a look that is ideal in homes seeking an update to popular trends.



Lockhart



FOUR-LIGHT PENDANT
P500278-031 Matte Black
19-3/4" dia., 20-5/8" ht.
Overall ht. w/chain 96", wire 15'.
Four candelabra base lamps,
each 60w max.

FIVE-LIGHT PENDANT
P500279-031 Matte Black
25-1/2" dia., 26-7/8" ht.
Overall ht. w/chain 102", wire 15'.
Five candelabra base lamps,
each 60w max.





Use subtle, soft touches of gold to bring an easy richness to an open plan space while creating a cohesive look.

1

Deliver elegance to the room's design with the Carrollwood ceiling fan whose lustrous accent bands circle the fan body and light kit.

2

Echo the circular theme over the island with two Saffert pendants featuring a textured fabric shade and a metal frame finished in glimmering gold

3

Combine graceful curves and bold angles in the dining room with the Parkhurst chandelier that casts unobstructed layers of light through its airy frame.

Briarwood

FINISHES

- Textured Black - 031
- Galvanized - 141

PAIR WITH


- Durrell
- Hemsworth

P400048-141


*Vintage Farmhouse
Detailing*

The Briarwood Collection brings vintage farmhouse detailing into the present day with a classic cross-brace pattern highlighting an airy, open-frame design. Hand-painted faux wood accentuates Briarwood's simple geometric form. The Textured Black finish is paired with a faux Cerused Black Oak while the Galvanized finish features a Bleached Oak. Briarwood adds the perfect touch of country character to Farmhouse and Rustic interiors.

Geometric Form



Cross-brace Pattern



P400048-031



P500041-141



P500178-141 N



P500047-141 N



P710012-141 N



P350022-141



P350039-141

Briarwood

ONE-LIGHT FLUSH MOUNT

P350022-141 Galvanized
9-1/2" sq., 7-5/8" ht.
One medium base lamp, 60w max.

TWO-LIGHT FLUSH MOUNT

P350039-141 Galvanized
12" sq., 6" ht.
Two medium base lamps,
each 60w max

FIVE-LIGHT LINEAR CHANDELIER

P400048-141 Galvanized
38" L., 10" W., 9" ht.
Overall ht. w/stem 75", wire 15'.
Five medium base lamps,
each 100w max.

FOUR-LIGHT CHANDELIER

P400047-141 Galvanized
20" dia., 12" ht.
Overall ht. w/stem 88", wire 15'.
Four medium base lamps,
each 100w max.

MINI-PENDANT

P500041-141 Galvanized
10" sq., 9" ht.
Overall ht. w/stem 78", wire 10'.
One medium base lamp, 100w max.

FOUR-LIGHT FOYER

P500178-141 Galvanized
15-1/2" sq., 21" ht.
Overall ht. w/stem 86-1/2", wire 15'.
Four medium base lamps,
each 60w max.

ONE-LIGHT WALL SCONCE

P710012-141 Galvanized
6-7/8" W., 12" ht.
Extends 6"
One medium base lamp, 100w max.



Featuring Briarwood

Classic, Cozy and Refined

A classic white color palette is grounded by warm touches of wood and black, bringing in a softer, earthy edge. The Briarwood linear chandelier has a classic cross-brace pattern highlighting an airy, open-frame design accentuated with faux-painted wood, adding a refined touch of country character.

Briarwood



P400048-031

ONE-LIGHT FLUSH MOUNT
P350022-031 Textured Black
 9-1/2" sq., 7-5/8" ht.
 One medium base lamp, 60w max.

TWO-LIGHT FLUSH MOUNT
P350039-031 Textured Black
 12" sq., 6" ht.
 Two medium base lamps,
 each 60w max.

FIVE-LIGHT LINEAR CHANDELIER
P400048-031 Textured Black
 38" L., 10" W., 9" ht.
 Overall ht. w/stem 75", wire 15'.
 Five medium base lamps,
 each 100w max.



P500041-031



P500178-031



FOUR-LIGHT CHANDELIER
P400047-031 Textured Black
 20" dia., 12" ht.
 Overall ht. w/stem 88", wire 15'.
 Four medium base lamps,
 each 100w max.

MINI-PENDANT
P500041-031 Textured Black
 10" sq., 9" ht.
 Overall ht. w/stem 78", wire 10'.
 One medium base lamp, 100w max.

FOUR-LIGHT FOYER
P500178-031 Textured Black
 15-1/2" sq., 21" ht.
 Overall ht. w/stem 86-1/2", wire 15'.
 Four medium base lamps,
 each 60w max.



P400047-031



P710012-031



ONE-LIGHT WALL SCONCE
P710012-031 Textured Black
 6-7/8" W., 12" ht.
 Extends 6"
 One medium base lamp, 100w max.



P350022-031



P350039-031

New Product

Vinings

FINISH
● Brushed Nickel - 009

PAIR WITH
Austelle
Winslett

P400267-009

Add a touch of casual charm with Vinings, whose graceful scrolling form creates a peaceful harmony between old and new. Vining's chic frame is ornamented with hand-painted Gray Washed Oak faux wood finish beads for a sweet play on comfortable elegance that elevates Farmhouse décor to new levels

Graceful Scrolling Form

Casual Charm

Natural Wood Finish Beads



P400267-009

Vinings

THREE-LIGHT SEMI-FLUSH
P350211-009 Brushed Nickel
14" dia., 9-3/4" ht.
Three candelabra base lamps,
each 60w max.

FIVE-LIGHT CHANDELIER
P400267-009 Brushed Nickel
22" dia., 21-1/2" ht.
Overall ht. w/chain 96-1/2", wire 15'.
Five candelabra base lamps,
each 60w max.

THREE-LIGHT FOYER
P500296-009 Brushed Nickel
15-3/4" dia., 19-1/2" ht.
Overall ht. w/chain 94-1/2", wire 15'.
Three candelabra base lamps,
each 60w max.



P500296-009



P350211-009

Kellwyn

FINISHES

- Brushed Nickel - 009
- Matte Black - 031

PAIR WITH

- Riley
- Replay

P400251-009

Balancing the best of modern and traditional, the Kellwyn Collection has a classic frame interpreted in a slender form. Kellwyn can add a clean finish to a New Traditional space or act as a relaxing counterpoint to a Modern interior. Clear glass shades complement the sleek design while adding a touch of luxury.

Slender Form

Clear Glass Shades

Classic Frame



P400252-009



P500315-009

Kellwyn

THREE-LIGHT CONVERTIBLE CHANDELIER

P400250-009 Brushed Nickel
Hanging and ceiling mount hardware included.
16" dia., 14" ht.
Overall ht. w/stem 74-1/2", wire 10'.
Three candelabra base lamps, each 60w max.

FIVE-LIGHT CHANDELIER

P400251-009 Brushed Nickel
23" dia., 24-3/8" ht.
Overall ht. w/stem 75-1/2", wire 15'.
Five candelabra base lamps, each 60w max.

NINE-LIGHT CHANDELIER

P400252-009 Brushed Nickel
28" dia., 34-1/4" ht.
Overall ht. w/stem 109-1/2", wire 15'.
Nine candelabra base lamps, each 60w max.

MINI-PENDANT

P500314-009 Brushed Nickel
5" dia., 8-7/8" ht.
Overall ht. w/stem 74-1/2", wire 10'.
One medium base lamp, 60w max.

FOUR-LIGHT FOYER

P500315-009 Brushed Nickel
18" dia., 31-3/4" ht.
Overall ht. w/stem 106-1/2", wire 15'.
Four candelabra base lamps, each 60w max.



P400251-009



P400250-009



P500314-009



P400250-009
shown as semi-flush



Featuring Kellwyn and Stature

A Perfect Blend of New and Old

Balance the best of modern and traditional with a crisp white color scheme and elegant furnishings with simple lines. Place a minimalist chandelier like Kellwyn, whose classic frame is re-interpreted in a slender form over the dining table. The Stature wall lantern adds a bold touch with clear glass doors accented by an unexpected detail of cross-hatched brass accents that provides signature style.

Kellwyn



P400252-031



P500315-031

THREE-LIGHT CONVERTIBLE CHANDELIER

P400250-031 Matte Black
Hanging and ceiling mount hardware included.
16" dia., 14" ht.
Overall ht. w/stem 74-1/2", wire 10'.
Three candelabra base lamps, each 60w max.

FIVE-LIGHT CHANDELIER

P400251-031 Matte Black
23" dia., 24-3/8" ht.
Overall ht. w/stem 75-1/2", wire 15'.
Five candelabra base lamps, each 60w max.

NINE-LIGHT CHANDELIER

P400252-031 Matte Black
28" dia., 34-1/4" ht.
Overall ht. w/stem 109-1/2", wire 15'.
Nine candelabra base lamps, each 60w max.

MINI-PENDANT

P500314-031 Matte Black
5" dia., 8-7/8" ht.
Overall ht. w/stem 74-1/2", wire 10'.
One medium base lamp, 60w max.

FOUR-LIGHT FOYER

P500315-031 Matte Black
18" dia., 31-3/4" ht.
Overall ht. w/stem 106-1/2", wire 15'.
Four candelabra base lamps, each 60w max.



P400251-031



P400250-031



P500314-031



P400250-031
shown as semi-flush

League

FINISHES

- Brushed Nickel - 009
- Matte Black - 31M

P400286-009

Clean, modern styling distinguishes the League collection. The structure is defined by sleek, steel rails that create a modern, monochromatic silhouette.

Clean Modern Style

Etched Glass Shades

Sleek Rails



P400287-009



FIVE-LIGHT CHANDELIER

P400286-009 Brushed Nickel
24" dia., 18-5/8" ht.
Overall ht. w/chain 70", wire 7.5'.
Five medium base lamps,
each 100w max.

FOUR-LIGHT LINEAR CHANDELIER

P400287-009 Brushed Nickel
39-3/4" L., 14" W., 14-1/2" ht.
Overall ht. w/stem 77-1/2", wire 7.5'.
Four medium base lamps,
each 100w max.

MINI-PENDANT

P500341-009 Brushed Nickel
5" dia., 11" ht.
Overall ht. w/stem 69", wire 7.5'.
One medium base lamp,
100w max.

THREE-LIGHT FOYER

P500342-009 Brushed Nickel
16" w., 25-5/8" ht.
Overall ht. w/chain 76-1/2", wire 10'.
Four medium base lamps,
each 100w max.

P500341-009



P500342-009



P400286-31M



Clean Modern Style

Etched Glass Shades

Sleek Rails

P400287-31M



League

FIVE-LIGHT CHANDELIER

P400286-31M Matte Black
24" dia., 18-5/8" ht.
Overall ht. w/chain 70", wire 7.5'.
Five medium base lamps,
each 100w max.

FOUR-LIGHT LINEAR CHANDELIER

P400287-31M Matte Black
39-3/4" L., 14" W., 14-1/2" ht.
Overall ht. w/stem 77-1/2", wire 7.5'.
Four medium base lamps,
each 100w max.

MINI-PENDANT

P500341-31M Matte Black
5" dia., 11" ht.
Overall ht. w/stem 69", wire 7.5'.
One medium base lamp,
100w max.

THREE-LIGHT FOYER

P500342-31M Matte Black
16" w., 25-5/8" ht.
Overall ht. w/chain 76-1/2", wire 10'.
Three medium base lamps,
each 100w max.

P500342-31M



P500341-31M



Leyden

FINISHES

- Brushed Nickel - 009
- Matte Black - 031

PAIR WITH

- Winslett
- Hemsworth

P400202-009

The Leyden Collection complements Farmhouse-inspired interiors with its casual style and subtle hints of industrial-inspired design. Gentle curves soften the classic appearance of Leyden's clean lines, providing a simple, graceful look and offering plenty of light from its open design.



P400228-009



P500303-009

Leyden

FIVE-LIGHT CHANDELIER

P400202-009 Brushed Nickel
22-3/8" dia., 20" ht.
Overall ht. w/chain 95", wire 15'.
Five candelabra base lamps,
each 60w max.

NINE-LIGHT CHANDELIER

P400228-009 Brushed Nickel
28" dia., 27" ht.
Overall ht. w/chain 102", wire 15'.
Nine candelabra base lamps,
each 60w max.

FOUR-LIGHT FOYER

P500302-009 Brushed Nickel
15" dia., 23" ht.
Overall ht. w/chain 98", wire 15'.
Four candelabra base lamps,
each 60w max.

EIGHT-LIGHT FOYER

P500303-009 Brushed Nickel
18" dia., 33" ht.
Overall ht. w/chain 108", wire 15'.
Eight candelabra base lamps,
each 60w max.

ONE-LIGHT PENDANT

P500316-009 Brushed Nickel
13" dia., 13" ht.
Overall ht. w/chain 88", wire 10'.
One medium base lamp, 60w max.



P400202-009



P500302-009



P500316-009



Featuring Leyden

An Elegant Take on Farmhouse Style

Elevate Farmhouse style with subtle hints of industrial design. A classic wooden table is surrounded by eclectic seating that has accents of metal and curving lines. The Leyden chandelier complements this look with gentle curves that soften its traditional form, providing an elegant, graceful look and offering plenty of light from its open design.

Leyden



P400228-031



P500303-031

FIVE-LIGHT CHANDELIER
P400202-031 Matte Black
 22-3/8" dia., 20" ht.
 Overall ht. w/chain 95", wire 15'.
 Five candelabra base lamps,
 each 60w max.

NINE-LIGHT CHANDELIER
P400228-031 Matte Black
 28" dia., 27" ht.
 Overall ht. w/chain 102", wire 15'.
 Nine candelabra base lamps,
 each 60w max.

FOUR-LIGHT FOYER
P500302-031 Matte Black
 15" dia., 23" ht.
 Overall ht. w/chain 98", wire 15'.
 Four candelabra base lamps,
 each 60w max.

EIGHT-LIGHT FOYER
P500303-031 Matte Black
 18" dia., 33" ht.
 Overall ht. w/chain 108", wire 15'.
 Eight candelabra base lamps,
 each 60w max.



P400202-031



P500302-031

ONE-LIGHT PENDANT
P500316-031 Matte Black
 13" dia., 13" ht.
 Overall ht. w/chain 88", wire 10'.
 One medium base lamp, 60w max.



P500316-031

Clifton Heights NEW

FINISH
● Matte Black - 31M

P400119-31M

Distinctive chiseled features and clean lines are key features within the Clifton Heights collection. Inspired by an updated interpretation of Craftsman styling, careful attention to the details delivers a dramatic accent.

Craftsman Styling

Squared-Off Shades



Distinctive Chiseled Elements



P400118-31M

Clifton Heights

FOUR-LIGHT CHANDELIER

P400118-31M Matte Black
21" dia., 23-1/2" ht.
Overall ht. w/chain 97-1/2", wire 15'.
Four medium base lamps, each 100w max.

SIX-LIGHT CHANDELIER

P400119-31M Matte Black
26" dia., 23-1/2" ht.
Overall ht. w/chain 99-1/2", wire 15'.
Six medium base lamps, each 100w max.

MINI-PENDANT

P500125-31M Matte Black
5-1/2" sq., 7-1/4" ht.
Overall ht. w/stem 73-1/2", wire 10'.
One medium base lamp, 100w max.

TWO-LIGHT INVERTED PENDANT

P500126-31M Matte Black
16" sq., 14", 24-1/2" ht.
Overall ht. w/chain 99-1/2", wire 15'.
Two medium base lamps, each 100w max.

TWO-LIGHT SEMI FLUSH

P350107-31M Matte Black
12-3/4" sq., 11" ht.
Two medium base lamps, each 60w max.



P500125-31M



P500126-31M



P350107-31M

Merry

P400276-009

FINISHES

- Brushed Nickel - 009
- Matte Black - 031

ALSO IN

Bath

PAIR WITH

Tobin

The Merry Collection brings a joyful aura to any room, with its modern vibe and clean-lined tubular frame accentuated with etched glass shades. Its generous scale and contemporary design make Merry ideal for today's open-concept Modern and Transitional spaces.

Modern Vibe

Etched Glass

Tubular Frame



P400276-009

Merry

THREE-LIGHT CHANDELIER

P400274-009 Brushed Nickel
18" dia., 16-3/8" ht.
Overall ht. w/chain 67-1/2", wire 10'.
Three medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER

P400275-009 Brushed Nickel
22-1/8" dia., 14-3/4" ht.
Overall ht. w/chain 66", wire 10'.
Five medium base lamps,
each 100w max.

NINE-LIGHT CHANDELIER

P400276-009 Brushed Nickel
28" dia., 24" ht.
Overall ht. w/chain 75", wire 10'.
Nine medium base lamps,
each 100w max.

ONE-LIGHT FOYER

P500333-009 Brushed Nickel
15" dia., 23" ht.
Overall ht. w/chain 74", wire 10'.
One medium base lamp, 100w max.



P400275-009



P500333-009



P400274-009

P400276-031



Matte Black Finish

Contemporary Design

Clean-lined Frame

P400276-031



P400275-031



P500333-031



P400274-031



Merry

THREE-LIGHT CHANDELIER

P400274-031 Matte Black
18" dia., 16-3/8" ht.
Overall ht. w/chain 67-1/2", wire 10'.
Three medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER

P400275-031 Matte Black
22-1/8" dia., 14-3/4" ht.
Overall ht. w/chain 66", wire 10'.
Five medium base lamps,
each 100w max.

NINE-LIGHT CHANDELIER

P400276-031 Matte Black
28" dia., 24" ht.
Overall ht. w/chain 75", wire 10'.
Nine medium base lamps,
each 100w max.

ONE-LIGHT FOYER

P500333-031 Matte Black
15" dia., 23" ht.
Overall ht. w/chain 74", wire 10'.
One medium base lamp, 100w max.



ILLUMINATE THE MOMENTS

Whether you're looking for the latest and greatest trends or some tried-and-true pieces, you'll find the just-right lighting choices to illuminate the special moments in your life.

Pivot LED

Capture the imagination with the Pivot LED Collection. Angled arms rotate around a central axis for a bold architectural form highlighted by lustrous LED lightbars that create a softly glowing ambient light. An integrated downlight shines from the bottom of the center column to illuminate tasks on the surface below.


FINISHES

- Burnished Nickel - 186
- Matte Black - 031

EIGHT-LIGHT LED CHANDELIER WITH DOWNLIGHT

P400261-031-30 Matte Black
P400261-186-30 Burnished Nickel
 40" dia., 10-1/16" ht.
 Overall ht. w/stem 63-7/8", wire 10'.
 29w integrated LED, 3000K,
 90CRI, 1305 delivered lumens.

JAB




Pivot LED

SIX-LIGHT LED CHANDELIER WITH DOWNLIGHT

P400260-028-30 Satin White
P400260-031-30 Matte Black
P400260-186-30 Burnished Nickel
 28-1/4" dia., 8-3/4" ht.
 Overall ht. w/stem 62-1/2", wire 10'.
 23.4w integrated LED, 3000K,
 90CRI, 1062 delivered lumens.

JAB



Spoke LED

FINISHES

- Brushed Nickel - 009
- Matte Black - 031


P400255-009-30

Modern minimalism meets the future of industrial style in the Spoke LED pendant collection. A slim disk of integrated LEDs casts an ethereal glow that creates a multi-directional wash of even light. Sleek rods anchor the luminous circles for a retro yet contemporary vibe that complements Modern spaces.

Sleek Rods

Modern Minimalist Style

Luminous Circles




FOUR-LIGHT LED CHANDELIER
P400255-009-30 Brushed Nickel
P400255-031-30 Matte Black
 25-1/2" dia., 27-1/8" ht.
 Overall ht. w/stem 57-1/2", wire 10'.
 20w integrated LED, 3000K,
 90CRI, 2096 delivered lumens.

JAB

LED PENDANT

P500318-009-30 Brushed Nickel
P500318-031-30 Matte Black
 17-3/4" dia., 6-1/2" ht.
 Overall ht. w/cord 122-3/8", wire 10'.
 20w integrated LED, 3000K,
 90CRI, 1762 delivered lumens.

JAB




Kylo LED

FINISHES

- Brushed Nickel - 009
- Matte Black - 031

P400263-031-30

Sleek metal bars capped with solid tubes of seamless light provide a futuristic effect to Kylo LED chandeliers. Stainless steel cables attach the LED light bars to a central stem, creating an asymmetrical form that adds drama to a room's design. Kylo LED pendants are available as single or multi-light option, the LED light bars are suspended on sleek stainless steel cables that can be individually adjusted for a customized appearance to suit your personal taste.



Kylo LED

FOUR-LIGHT LED CHANDELIER
P400262-031-30 Matte Black
 30" dia., 21-1/4" ht.
 Overall ht. w/stem 78-1/2", wire 10'.
 17w integrated LED, 3000K,
 90CRI, 981 delivered lumens.

JAB

SIX-LIGHT LED CHANDELIER
P400263-031-30 Matte Black
 40" dia., 22-3/4" ht.
 Overall ht. w/stem 80", wire 10'.
 23w integrated LED, 3000K,
 90CRI, 1471 delivered lumens.

JAB

LED PENDANT
P500321-031-30 Matte Black
 4-3/4" dia., 13" ht.
 Overall ht. w/cord 132-5/8", wire 10'.
 6.5w integrated LED, 3000K,
 90CRI, 420 delivered lumens.

JAB

SIX-LIGHT LED PENDANT
P500322-031-30 Matte Black
 11-3/4" dia., 13" ht.
 Overall ht. w/cord 132-5/8", wire 10'.
 23.2w integrated LED, 3000K,
 90CRI, 1790 delivered lumens.

JAB



P500322-031-30

P500321-031-30



Featuring *Kylo*, *Willacy* and *Clarion*

A Focus on Form

Lighting takes center stage against a dark neutral backdrop in this modern space. The Willacy ceiling fan swirls ribbon-like blades around a gleaming center hub, making a striking focal point. Over the sofa, the Kylo LED multi-light pendant presents a contemporary splash of minimalist style as it cascades downwards in an arrangement of seamless light. Abstract wall art lends pops of blue and is flanked by a pair of clean-lined Clarion wall sconces on the feature wall. In the dining area, the Kylo chandelier adds drama with sleek metal bars capped with solid tubes of light that hang in a stunning asymmetrical form.

Kylo LED



P400263-009-30

FOUR-LIGHT LED CHANDELIER
P400262-009-30 Brushed Nickel
 30" dia., 21-1/4" ht.
 Overall ht. w/stem 78-1/2", wire 10'.
 17w integrated LED, 3000K,
 90CRI, 981 delivered lumens.



P400262-009-30

SIX-LIGHT LED CHANDELIER
P400263-009-30 Brushed Nickel
 40" dia., 22-3/4" ht.
 Overall ht. w/stem 80", wire 10'.
 23w integrated LED, 3000K,
 90CRI, 1471 delivered lumens.



LED PENDANT
P500321-009-30 Brushed Nickel
 4-3/4" dia., 13" ht.
 Overall ht. w/cord 132-5/8", wire 10'.
 6.5w integrated LED, 3000K,
 90CRI, 420 delivered lumens.



SIX-LIGHT LED PENDANT
P500322-009-30 Brushed Nickel
 11-3/4" dia., 13" ht.
 Overall ht. w/cord 132-5/8", wire 10'.
 23.2w integrated LED, 3000K,
 90CRI, 1790 delivered lumens.



P500322-009-30

P500321-009-30

Quadrant LED

FINISH
● Matte Black - 031


P400264-031-30

With its precise arrangement of light, Quadrant LED defines space with a minimalistic approach. Metal struts tipped with integrated LED lights are arranged in a modern geometric design, giving the layered frame an impression of substance while creating airy illumination in a space.


Modern Geometric Design

Airy Illumination

Layered Frame



P400264-031-30



P710103-031-30



P350209-031-30

Quadrant LED

FOUR-LIGHT LED SEMI-FLUSHMOUNT
P350209-031-30 Matte Black
Ceiling or wall mount.
20" dia., 4" ht.
24w integrated LED, 3000K, 90CRI, 1261 delivered lumens.

JAB

SIX-LIGHT LED CHANDELIER
P400264-031-30 Matte Black
26-1/8" dia., 26-1/8" ht.
Overall ht. w/stem 71-1/16", wire 10'.
24w integrated LED, 3000K, 90CRI, 1346 delivered lumens.

JAB

TWO-LIGHT LED WALL SCONCE
P710103-031-30 Matte Black
Ceiling or wall mount. Can be installed vertically or horizontally.
8" W., 24" ht.
Extends 3-5/16". H/CTR 12".
13w integrated LED, 3000K, 90CRI, 686 delivered lumens.

JAB ADA

Geodesic LED

Geodesic radiates a magical beauty from a uniform, continuous disc of light that glows through an airy structural frame. Diffused edge-lit LED dispenses even illumination through the open diamond-patterned frame while a simple cable suspension adds to the clean style. Geodesic takes contemporary spaces to a new level.

FINISH

- Matte Black - 031

LED PENDANT

P500319-031-30 Matte Black
17-7/8" dia., 9-1/4" ht.
Overall ht. w/cord 100-3/4", wire 8'.
28w integrated LED, 3000K,
90CRI, 2067 delivered lumens.

JAB

LED PENDANT

P500320-031-30 Matte Black
27-1/8" dia., 12-5/16" ht.
Overall ht. w/cord 103-3/4", wire 8'.
38w integrated LED, 3000K,
90CRI, 3373 delivered lumens.

JAB



P500320-031-30



P500319-031-30



P500366-009-30



P500366-31M-30

Everlume™ LED Pendant NEW

Sleek and clean in style, the Everlume LED furnishes powerful, direct light through its edge-lit flat panel diffuser surrounded by a simple frame.

FINISH

- Brushed Nickel - 009
- Matte Black - 31M

P500366-009-30 Brushed Nickel
P500366-31M-30 Matte Black
11" dia., 2-1/4" ht.
Overall ht. w/cord 122"
20w integrated LED, 3000K,
90CRI, 1697 lumens.

JAB

EVERLUME™
LED LIGHTING

Planck LED

A trio of clean light bars suspended from a sleek single rod defines the Planck LED chandelier. Slices of light complement a room with modern style and provide a punch of illumination for both intimate and open spaces.

FINISH

- Brushed Nickel - 009

THREE-LIGHT LED CHANDELIER
P400257-009-30 Brushed Nickel
26-1/2" dia., 3-1/16" ht.
Overall ht. w/stem 60-3/8", wire 10'.
30w integrated LED, 3000K,
90CRI, 2245 delivered lumens.

JAB



P400257-009-30

Inverse LED NEW

A simple halo suspended by airy cables brings a minimal contemporary style to Inverse LED. Indirect illumination provided by integrated LED light source creates an inner glow that gently lights the surroundings.

FINISHES

- Brushed Nickel - 009
- Matte Black - 31M

ONE-LIGHT PENDANT

P500369-009-30 Brushed Nickel
P500369-31M-30 Matte Black
 20" dia., 2-3/8" ht.
 Overall ht. w/cord. 100".
 27w integrated LED, 3000K, 90CRI,
 1641 delivered lumens.

JAB

ONE-LIGHT PENDANT

P500370-009-30 Brushed Nickel
P500370-31M-30 Matte Black
 30" dia., 2-3/8" ht.
 Overall ht. w/cord. 100".
 38w integrated LED, 3000K, 90CRI,
 2369 delivered lumens.

JAB



Radian LED NEW

Give any room an industrial vibe with Radian LED. A domed metal shade is supported by a contrasting cap and is finished inside with a reflective coating that casts a warm glow of light.

FINISHES

- Brushed Nickel - 009
- Satin White - 028
- Matte Black - 31M

ONE-LIGHT PENDANT

P500372-009-30 Brushed Nickel
P500372-028-30 Satin White
P500372-31M-30 Matte Black
 10-1/2" dia., 10" ht.
 Overall ht. w/cord. 131", wire 120".
 20w integrated LED, 3000K, 90CRI,
 990 delivered lumens.

JAB

ONE-LIGHT PENDANT

P500373-009-30 Brushed Nickel
P500373-028-30 Satin White
P500373-31M-30 Matte Black
 16" dia., 14" ht.
 Overall ht. w/cord. 133", wire 120".
 30w integrated LED, 3000K, 90CRI,
 1546 delivered lumens.

JAB

Chastain

FINISHES

- Bleached Oak - 185
- Cerused Black Oak - 187

P500344-185

Chastain draws upon the handcrafted artistry of basket-weaving with an open, airy frame offering a graceful silhouette. The artisanal style is enhanced by a distressed faux wood finish and an impressive scale for an eye-catching element of form and function.

*Handcrafted
Artistry*



Airy Frame

Artisanal Style

Chastain

ONE-LIGHT PENDANT

P500343-185 Bleached Oak
P500343-187 Cerused Black Oak
 14" dia., 17-1/4" ht.
 Overall ht. w/stem 83", wire 10'.
 One medium base lamp,
 60W max.

THREE-LIGHT PENDANT

P500344-185 Bleached Oak
P500344-187 Cerused Black Oak
 20-7/8" dia., 25-1/4" ht.
 Overall ht. w/stem 91-1/2", wire 15'.
 Three medium base lamps, each
 60W max.

P500343-185



P500343-187



P500344-185



P500344-187



Delayne NEW

A softly curved fitted metal framework encases an opal glass globe in Delayne. The pendant offers a refined mid-century design enhanced by gently diffused light that creates an ambient glow.

FINISHES

- Brushed Nickel - 009
- Brushed Bronze - 109
- Matte Black - 31M

ONE-LIGHT PENDANT

P500358-009 Brushed Nickel

P500358-109 Brushed Bronze

P500358-31M Matte Black

9-3/8" dia., 12-3/8" ht.

Overall ht. w/stem 72-1/2", wire 10'.

One medium base lamp, 100w max

ONE-LIGHT PENDANT

P500359-009 Brushed Nickel

P500359-109 Brushed Bronze

P500359-31M Matte Black

16-1/8" dia., 21-5/8" ht.

Overall ht. w/stem 85-1/2", wire 10'.

One medium base lamp, 100w max.



P500358-009



P500359-009



P500358-109



P500359-109



P500358-31M



P500359-31M



P500365-028



P500365-186



P500365-31M



P42171-109

Lorin NEW

Elegantly designed, Lorin features sleek metal wires gathered by a smooth, wide metal collar, creating a stylized trumpet silhouette.

FINISHES

- Satin White - 028
- Burnished Nickel - 186
- Matte Black - 31M

ONE-LIGHT PENDANT

P500365-028 Satin White

P500365-186 Burnished Nickel

P500365-31M Matte Black

18" dia., 16" ht.

Overall ht. w/cord 127", wire 10'.

One medium base lamp, 60w max

Drum Shade NEW

A perennially popular look, the simple lines of the Drum Shade pendant are refreshed with a Brushed Bronze finish, giving an elegant update to this classic fixture.

FINISHES

- Brushed Bronze - 109

FIVE-LIGHT CHANDELIER

P4217-109 Brushed Bronze

21-5/8" dia., 21-1/8" ht.,

Overall ht. w/chain 66",

Five medium base lamps,

each 60w max.

Terrazzo

Terrazzo features a polished, Gray or Sandstone concrete composite shade, flecked with warm earthy hues offering a sophisticated contrast to its natural interior and clean metal stem suspension. The Terrazzo pendant expresses an artistic sensibility that is ideal for eclectic settings.

FINISHES

- Graphite - 143
- Distressed Brass - 175

PAIR WITH

Hedgerow
Bonn

ONE-LIGHT PENDANT

P500313-143 Graphite
P500313-175 Distressed Brass
10" dia., 9-3/8" ht.
Overall ht. w/stem 66-1/2", wire 10'.
One medium base lamp, 75w max.



Rushton

The Rushton collection features exposed bulbs that glow elegantly from within clear glass. Mechanical-inspired fittings complete the industrial theme to make a bold statement in your home.

FINISHES

- Brushed Nickel - 009
- Graphite - 143

PAIR WITH

Hemsworth
Lockhart

TWO-LIGHT FLUSH MOUNT

P350205-009 Brushed Nickel
P350205-143 Graphite
12" dia., 6-7/8" ht.
Two medium base lamps,
each 60w max.

ONE-LIGHT PENDANT

P500329-009 Brushed Nickel
P500329-143 Graphite
8-1/2" dia., 16-7/8" ht.
Overall ht. w/stem 82-1/2", wire 10'.
One medium base lamp, 100w max.



Atwell

Extraordinary on the first impression, but always at peace with whatever setting it calls home, Atwell blends crisp architectural detailing with circular glass for statement-making lighting design. A clear globe adds a soft contrast to the clean metal cap creating a remarkable and enduring design.

FINISHES

- Brushed Nickel - 009
- Matte Black - 031
- Brushed Bronze - 109

ALSO IN

Pendants
See www.progresslighting.com
for more details.

MINI-PENDANT

P500309-009 Brushed Nickel
P500309-031 Matte Black
P500309-109 Brushed Bronze
8" dia., 8-1/2" ht.
Overall ht. w/cord 128-1/2", wire 10'.
One medium base lamp, 60w max.

ONE-LIGHT PENDANT

P500310-009 Brushed Nickel
P500310-031 Matte Black
P500310-109 Brushed Bronze
10" dia., 10-1/2" ht.
Overall ht. w/cord 130-1/2", wire 10'.
One medium base lamp, 60w max.

ONE-LIGHT PENDANT

P500311-009 Brushed Nickel
P500311-031 Matte Black
P500311-109 Brushed Bronze
11-7/8" dia., 12-3/4" ht.
Overall ht. w/cord 132-1/2", wire 10'.
One medium base lamp, 60w max.

FINISHES

- Brushed Nickel - 009
- Brushed Bronze - 109
- Matte Black - 31M

ONE-LIGHT PENDANT

P500367-009 Brushed Nickel

P500367-109 Brushed Bronze

P500367-31M Matte Black

12-3/8" dia., 11-7/8" ht.

Overall ht. w/stem 68", wire 10'.

One medium base lamp,

60w max.

THREE-LIGHT PENDANT

P500368-009 Brushed Nickel

P500368-109 Brushed Bronze

P500368-31M Matte Black

17-7/8" dia., 15-1/4" ht.

Overall ht. w/stem 72", wire 10'.

Three medium base lamps,

60w max



Hinton

Simplicity defined is the hallmark of the Hinton Collection. Hinton's metal fittings offer an industrial demeanor, complemented by a clear seeded glass shade or opaque metal shade that provides effective task lighting wherever focused illumination is called upon.

FINISHES

- Brushed Nickel - 009
- Matte Black - 031
- Polished Nickel - 104
- Vintage Brass - 163

PAIR WITH

Winslett
Saluda

ALSO IN

Close-To-Ceiling
Sconces
See www.progresslighting.com for more details.

PENDANT WITH GLASS SHADE

P500324-009 Brushed Nickel
P500324-031 Matte Black
P500324-104 Polished Nickel
P500324-163 Vintage Brass
 12" dia., 12-1/2" ht.
 Overall ht. w/stem 78-1/2", wire 10'.
 One medium base lamp, 100w max.

PENDANT WITH METAL SHADE

P500325-009 Brushed Nickel
P500325-031 Matte Black
P500325-104 Polished Nickel
P500325-163 Vintage Brass
 12-1/4" dia., 12-1/2" ht.
 Overall ht. w/stem 78-1/2", wire 10'.
 One medium base lamp, 100w max.



P500324-009



P500325-009



P500324-031



P500325-031



P500324-104



P500325-104



P500324-163



P500325-163



P8602-31M



P8602-163



P8602-168



P8602-175



P8602-176



P8755-141



P8755-160



P8758-31M



P8758-161



P860059-000



P860060-000



P860061-068

Accessories

Stem Kits

Contains (2) 6" and (1) 12" stem.

- P8602-31M** Matte Black
- P8602-163** Vintage Brass
- P8602-168** Antique Bronze
- P8602-175** Distressed Brass
- P8602-176** Gilded Silver

9-Gauge Square Chain

- 4' feet of 9 gauge, square profile chain for Jeffrey Alan Marks Point Dume™ Collection fixtures. Permits installation of large chain-hung fixtures on high ceilings.
- Maximum fixture weight – 50 lbs.

- P8755-09** Brushed Nickel
- P8755-30** Gloss White
- P8755-81** Antique Nickel
- P8755-108** Oil Rubbed Bronze
- P8755-134** Silver Ridge
- P8755-141** Galvanized
- P8755-160** Aged Brass
- P8755-161** Distressed Brass
- P8755-192** Shelter White
- P8755-31M** Matte Black

9-Gauge Chain

- 4' feet of 9 gauge chain permits installation of large chain-hung fixtures on high ceilings.
- Maximum fixture weight – 50 lbs.

- P8758-31M** Matte Black
- P8758-175** Distressed Brass

Accessory Shade

P860059-000 White Linen Drum
1" uno-style candle fitter.
5" dia. x 5" ht.

P860060-000 White Linen Taper
1" uno-style candle fitter
5-1/2" dia. x 5-1/2" ht.

P860061-068 Clear Glass
3" dia. x 8-3/4" ht.

Hinton

SEMI-FLUSH WITH GLASS SHADE

P350198-009 Brushed Nickel
P350198-031 Matte Black
P350198-104 Polished Nickel
P350198-163 Vintage Brass
 8" dia., 10" ht.
 One medium base lamp, 60w max.

SEMI-FLUSH WITH METAL SHADE

P350199-009 Brushed Nickel
P350199-031 Matte Black
P350199-104 Polished Nickel
P350199-163 Vintage Brass
 8-1/4" dia., 10" ht.
 One medium base lamp, 60w max.



P350198-009



P350199-009



P350198-031



P350199-031



P350198-104



P350199-104



P350198-163



P350199-163
 Shown tilted

Medal

The Medal flush mount takes a cue from classic warehouse work lights with an open metal cage to create authentic industrial appeal. Knurled detailing on lamp holders adds visual interest to the automotive inspired styling.

TWO-LIGHT FLUSH MOUNT

P350195-143 Graphite
P350195-164 Coastal Blue w/ Brushed Nickel Accents
 14-1/2" dia., 7-7/8" ht.
 Two medium base lamps, each 60w max.



P350195-143




P350195-164

Gulliver

Circular bands create an open design for the Gulliver flush mount ceiling light. Gulliver features an embossed wood-grain texture with a hand-painted faux finish effect that complements Farmhouse and Coastal home decor.

TWO-LIGHT FLUSH MOUNT

P350169-141 Galvanized Finish
P350169-143 Graphite
 14-3/8" dia., 6-1/2" ht.
 Two medium base lamps, each 60w max.



P350169-141



P350169-143

Delayne NEW

Delayne has a mid-century appeal defined by arms that extend outward from a rounded, central support. Select decorative light bulbs in a clear or white finish to further enhance this dynamic style.

FIVE-LIGHT SEMI-FLUSH
P350219-009 Brushed Nickel
P350219-109 Brushed Bronze
P350219-31M Matte Black
16" dia., 5-1/2" ht.
Five candelabra lamps,
each 60w max.

*Fixture dimension does
not include lamps.*



P350219-009



P350219-109



P350219-31M



Featuring Delayne and Lorrin

Eva NEW

Eva has an eye-catching, two-toned color scheme. Light reflects from the shade to offer nostalgic charm for today's home.

ONE-LIGHT FLUSH MOUNT

P350217-164 Costal Blue

P350217-31M Matte Black

7-3/8" dia., 4-1/2" ht.

One medium base lamp,

60w max.



P350217-164



P350217-31M

Judson NEW

Vintage-look metal fittings suspend a schoolhouse-style clear glass globe.

ONE-LIGHT SEMI-FLUSH

P350220-020 Antique Bronze

P350220-104 Polished Nickel

6-1/2" L., 8" ht.

One medium base lamp,

60w max.

ALSO IN

Collections

See www.progresslighting.com

for more details



P350220-020



P350220-104



P350200-009



P350200-012



P350200-031

Hansford

The Hansford collection of fixtures feature a clear, spherical shade paired with vintage style metal fittings in a soft, Vintage Brass finish. Featuring a clean and precise design with generous scale, Hansford's classic style brings tranquility to your home.

ONE-LIGHT FLUSH MOUNT

P350046-163 Vintage Brass

10" dia., 12-3/4" ht.

One medium base lamps,
each 100w max.

See coordinating vanity fixtures
and more finish options at
progresslighting.com.



P350046-163

Perimeter

Inspired by geometric simplicity, Perimeter has a rectangular frame composed of clean, straight lines. Perimeter has a fashion-forward appeal that works across a variety of room styles.

TWO-LIGHT FLUSH MOUNT

P350200-009 Brushed Nickel

P350200-012 Satin Brass

P350200-031 Matte Black

12" sq., 4-1/2" ht.

Two medium base lamps,
each 60w max.

Aiken

Delightful details pair with clear glass to create the charm of the Aiken collection. A vintage-style cap tops a clear globe reminiscent of an apothecary bottle that has been repurposed for a new life as a light fixture.

ONE-LIGHT FLUSH MOUNT
P350214-009 Brushed Nickel
P350214-163 Vintage Brass
9" dia., 9" ht.
One medium base lamp,
60w max.

See progresslighting.com for coordinating vanity fixtures.



P350214-009



P350214-163



Extraordinary on the first impression but always at peace with whatever setting it calls home, Atwell blends crisp architectural detailing with circular glass for a statement-making lighting fixture. A clear globe adds a soft contrast to the clean metal cap creating a remarkable and enduring design.

ONE-LIGHT SEMI-FLUSH MOUNT

P350218-009 Brushed Nickel

P350218-109 Brushed Bronze

P350218-31M Matte Black

12" L., 9-3/4" ht.

One candelabra base lamp, 60w max.



P350218-009



P350218-109



P350218-31M



P350213-009



P350213-104



P350213-012



P350213-31M

Add modern sophistication with the Adley ceiling light in a hallway, over a kitchen sink or in a master bath. Clear glass is paired with a sleek frame for visually stunning illumination.

ONE-LIGHT FLUSH MOUNT

P350213-009 Brushed Nickel

P350213-012 Satin Brass

P350213-104 Polished Nickel

P350213-31M Matte Black

8-5/8" dia., 7-3/8" ht.

One medium base lamp, each 60w max.

See progresslighting.com for coordinating vanity fixtures.

Inspire

Harkening back to a simpler time, the Inspire Collection freshens a traditional form with a contemporary Satin Brass finish. Inspire features an etched glass diffuser with a Summer Linen shade.

TWO-LIGHT SEMI-FLUSH MOUNT

P350129-012 Satin Brass
13" dia., 10-1/8" ht.
Two medium base lamps,
each 75w max.



P350129-012

TWO-LIGHT FLUSH MOUNT

P350130-012 Satin Brass
13" dia., 5-1/2" ht.
Two medium base lamps,
each 60w max.



P350130-012

THREE-LIGHT SEMI-FLUSH

P350167-012 Satin Brass
18" dia., 11-1/2" ht.
Three medium base lamps,
each 60w max.



P350167-012 **N**

Also available in other sizes and finishes, see progresslighting.com

Linen Dome **NEW**

A domed, linen finish glass diffuser is discreetly supported from brushed nickel metal fittings. While outfitted with traditional sockets, these fixtures are for use only with LED lamps to maximize energy savings.

TWO-LIGHT FLUSH MOUNT

P350170-009 Brushed Nickel
12-1/4" dia., 4" ht.
Two medium base LED lamps,
each 15w max.



P350170-009

THREE-LIGHT FLUSH MOUNT

P350178-009 Brushed Nickel
16-1/4" dia., 4-1/8" ht.
Three medium base LED lamps,
each 15w max.



P350178-009

FOUR-LIGHT FLUSH MOUNT

P350179-009 Brushed Nickel
20-1/8" dia., 4-1/8" ht.
Four medium base LED lamps,
each 15w max.



P350179-009

N New Product

Carrick

The Carrick wall lamp merges function and fashion with exceptional style. A full-range swing arm supports a crisp Summer Linen shade and etched glass diffuser for glare-free task illumination. An integral rotary switch on the backplate is included for convenient control.

ONE-LIGHT WALL BRACKET

P710104-009 Brushed Nickel

P710104-163 Vintage Brass

P710104-31M Matte Black

10" dia., 11-3/4" ht.

Extends 10-7/8". H/CTR 7-7/8".

One medium base lamp, 60w max. Includes integral rotary on/off switch on backplate.



P710104-009



P710104-163



P710104-31M

Curve LED

Curve LED is simply designed with an arching acrylic shade accented by two finials that add visual interest. Curve LED brings a touch of contemporary style to interior spaces.

LED WALL SCONCE

P710102-060-30 Opal White

Includes Architectural Bronze,

Brushed Nickel and Matte

Black finials.

8" dia., 8" ht.

Extends 3-5/8", H/CTR 4".

10w Integrated LED, 3000K,

90 CRI, 744 delivered lumens.



P710102-060-30
shown with Matte Black finials

Opal Glass NEW

A flared cone-shaped half bowl in etched glass is ornamented with classic knob detailing.

FINISH

● Matte Black - 31W

ONE-LIGHT WALL SCONCE

P7153-31W Matte Black

15-3/8" L., 7" ht.

Extends 7-1/2". H/CTR 7-2-1/2".

One medium base lamp, 60w max.



P7153-31W

Pearl LED

Pearl LED combines elements of simple geometry, adding together circles and rectangles to equal an elegant streamlined design. Light is multiplied from a reflective polished chrome backplate, giving extra dimension and dazzle.

FINISHES

- Satin Brass - 012
- Matte Black - 031

ONE-LIGHT WALL BRACKET

P710105-012-30 Satin Brass
P710105-031-30 Matte Black
 5-3/4" W., 12-1/16" ht.
 6.5w integrated LED, 3000K, 90CRI, 412 delivered lumens.

TWO-LIGHT LED BATH

P300311-012-30 Satin Brass
P300311-031-30 Matte Black
 12" L., 5" ht.
 Extends 5-1/2". H/CTR 2-1/4".
 13w integrated LED, 3000K, 90CRI, 812 delivered lumens.

THREE-LIGHT LED BATH

P300312-012-30 Satin Brass
P300312-031-30 Matte Black
 18" L., 5" ht.
 Extends 5-1/2". H/CTR 2-1/2".
 19.5w integrated LED, 3000K, 90CRI, 1292 delivered lumens.

FOUR-LIGHT LED BATH

P300313-012-30 Satin Brass
P300313-031-30 Matte Black
 23-7/8" L., 5" ht.
 Extends 5-1/2". H/CTR 2-1/2".
 24w integrated LED, 3000K, 90CRI, 1692 delivered lumens.

All fixtures can be installed horizontally or vertically.

All fixtures:




N New Product



P710105-031-30 **N**



P710105-012-30 **N**




P300311-012-30




P300311-031-30



P300312-012-30



P300312-031-30



P300313-012-30



P300313-031-30

Grid LED

Grid LED pairs sleek geometric frame with a linear acrylic, etched linen shade to provide a dramatic look and soft illumination.

FINISHES

- Matte Black - 031
- Silver Ridge - 134

14" LINEAR LED BATH

P300331-031-30 Matte Black
P300331-134-30 Silver Ridge
 14" W., 4-3/4" ht.
 Extends 3-1/8". H/CTR 2-3/8".
 14w integrated LED, 3000K, 90CRI, 569 delivered lumens.

22" LINEAR LED BATH

P300332-031-30 Matte Black
P300332-134-30 Silver Ridge
 22" W., 4-3/4" ht.
 Extends 3-1/8". H/CTR 2-3/8".
 22w integrated LED, 3000K, 90CRI, 1033 delivered lumens.

30" LINEAR LED BATH

P300333-031-30 Matte Black
P300333-134-30 Silver Ridge
 30" W., 4-3/4" ht.
 Extends 3-1/8". H/CTR 2-3/8".
 32w integrated LED, 3000K, 90CRI, 1639 delivered lumens.

All fixtures can be installed horizontally or vertically.

All fixtures:



P300331-031-30



P300331-134-30



P300332-031-30



P300332-134-30



P300333-031-30



P300333-134-30

Everlume™ LED Vanity

The Everlume™ Vanity LED has a clean rectangular frame and a frosted polycarbonate diffuser lit by LEDs along the perimeter of the fixture. Light is diffused through a light guide, providing even illumination without dark spots, shadows or glare. Two color temperatures can be selected, soft white or cool white. This versatile fixture can be wall or ceiling mounted in a variety of residential and commercial settings.

FINISHES

- Brushed Nickel - 009
- Satin White - 028

16" LINEAR BATH

P300304-009-CS Brushed Nickel
P300304-028-CS Satin White
 16" W., 5" ht.
 Extends 1-3/8", H/CTR 2-1/2".
 17w Integrated LED, 3000K, 4000K,
 90 CRI, 1386 delivered lumens.

24" LINEAR BATH

P300305-009-CS Brushed Nickel
P300305-028-CS Satin White
 24" W., 5" ht.
 Extends 1-3/8", H/CTR 2-1/2".
 26w Integrated LED, 3000K, 4000K,
 90 CRI, 2182 delivered lumens.

32" LINEAR BATH

P300306-009-CS Brushed Nickel
P300306-028-CS Satin White
 32" W., 5" ht.
 Extends 1-3/8", H/CTR 2-1/2".
 32w Integrated LED, 3000K, 4000K,
 90 CRI, 2808 delivered lumens.




P300304-009-CS
Shown ceiling mounted

P300304-028-CS
Shown ceiling mounted



P300305-009-CS
Shown ceiling mounted



P300305-028-CS
Shown ceiling mounted



P300306-009-CS



P300306-028-CS



3000K
Soft White

4000K
Cool White



- ### LED FEATURES
- Damp location listed.
 - Flicker-free dimming with many Triac and ELV dimmers.
 - 120v input voltage.
 - 50,000 hour life.

All fixtures can be installed horizontally or vertically.

All fixtures:



Clarion

Clarion embraces a minimalist simplicity of style. A clear, tubular glass shade is secured by a sleek cylindrical base for a precision look that is ideal for modern settings.

FINISHES

- Brushed Nickel - 009
- Satin Brass - 012
- Polished Chrome - 015
- Matte Black - 031

ONE-LIGHT BATH

P300299-009 Brushed Nickel
P300299-012 Satin Brass
P300299-015 Polished Chrome
P300299-031 Matte Black
 5" W., 12-5/8" ht.
 Extends 4-1/4". H/CTR 2-1/2".
 One medium base T10 lamp,
 60w max.

TWO-LIGHT BATH

P300300-009 Brushed Nickel
P300300-012 Satin Brass
P300300-015 Polished Chrome
P300300-031 Matte Black
 20-3/8" W., 5" ht.
 Extends 4". H/CTR 2-1/2".
 Two medium base T10 lamps,
 each 60w max.

P300300 can be installed horizontally or vertically.



P300299-009

P300299-012

P300299-015

P300299-031



P300300-009



P300300-012



P300300-015



P300300-031

FINISHES

- Brushed Nickel - 009
- Satin Brass - 012
- Matte Black - 31M

P300369-012

Cowan boasts contemporary curved edges for a softly modern yet substantial style. A simple square etched opal glass shade with gently rounded corners complements the form.



ONE-LIGHT BATH

P300368-009 Brushed Nickel
P300368-012 Satin Brass
P300368-31M Matte Black
 4-3/4" L., 8-1/2" ht.
 Extends 5-12". H/CTR 4-9/16".
 One medium base lamp,
 100w max.



P300368-009



P300369-009

TWO-LIGHT BATH

P300369-009 Brushed Nickel
P300369-012 Satin Brass
P300369-31M Matte Black
 13-1/2" L., 8-1/2" ht.
 Extends 5-12". H/CTR 6-1/8".
 Two medium base lamps,
 each 100w max.



P300368-012



P300369-012



P300368-31M



P300369-31M

All fixtures mount up or down.

THREE-LIGHT BATH

P300370-009 Brushed Nickel
P300370-012 Satin Brass
P300370-31M Matte Black
 23-1/2" L., 8-1/2" ht.
 Extends 7-3/4". H/CTR 6-1/8".
 Three medium base lamps,
 each 100w max.



P300370-009



P300370-012



P300370-31M

FOUR-LIGHT BATH

P300371-009 Brushed Nickel
P300371-012 Satin Brass
P300371-31M Matte Black
 33-1/2" L., 8-1/2" ht.
 Extends 7-3/4". H/CTR 6-1/8".
 Four medium base lamps,
 each 100w max.



P300371-009



P300371-012



P300371-31M

All fixtures mount up or down.

FINISHES

- Brushed Nickel - 009
- Vintage Brass - 163
- Matte Black - 31M

P300357-009

Elara features a slender, chic form with a stylized finial inspired by a chess pawn for a classically modern style.



ONE-LIGHT BATH

P300356-009 Brushed Nickel
P300356-163 Vintage Brass
P300356-31M Matte Black
 4-3/4" W., 11-1/2" ht.
 Extends 5". H/CTR 6".
 One candelabra lamp,
 60w max.



TWO-LIGHT BATH

P300357-009 Brushed Nickel
P300357-163 Vintage Brass
P300357-31M Matte Black
 12-1/2" W., 11-1/2" ht.
 Extends 5-1/8". H/CTR 6-3/4"
 Two candelabra lamps,
 each 60 max.



THREE-LIGHT BATH

P300358-009 Brushed Nickel
P300358-163 Vintage Brass
P300358-31M Matte Black
 22-1/8" W., 11-1/2" ht.,
 Extends 5-1/8", H/CTR 6-3/4"
 Three candelabra base lamps,
 each 60w max.

FOUR-LIGHT BATH

P300359-009 Brushed Nickel
P300359-163 Vintage Brass
P300359-31M Matte Black
 32-5/8" W., 11-1/2" ht.
 Extends 5-1/8". H/CTR 6-3/4"
 Four candelabra lamps,
 each 60 max.



FINISHES

- Brushed Nickel - 009
- Vintage Brass - 163
- Matte Black - 31M

P300361-163

Timeless details create an enduring silhouette for Calais. Clear glass is supported by an elegantly simple frame providing a contemporary take on a traditional style.

Timeless Design

Modern Clear Glass



Simple & Elegant Frame

ONE-LIGHT BATH

P300360-009 Brushed Nickel
P300360-163 Vintage Brass
P300360-31M Matte Black
 5" L., 8-1/2" ht.
 Extends 7". H/CTR 5-1/4".
 One medium base lamp, 60w max.



P300360-009



P300361-009

TWO-LIGHT BATH

P300361-009 Brushed Nickel
P300361-163 Vintage Brass
P300361-31M Matte Black
 14-5/8" L., 8-1/2" ht.
 Extends 6-1/2". H/CTR 5-1/2".
 Two medium base lamps, each 60w max.



P300360-163



P300361-163



P300360-31M



P300361-31M



P300362-009



P300362-163



P300362-31M



P300363-009



P300363-163



P300363-31M

THREE-LIGHT BATH

P300362-009 Brushed Nickel
P300362-163 Vintage Brass
P300362-31M Matte Black
 24-1/4" L., 8-1/2" ht.
 Extends 6-1/2". H/CTR 5-1/2".
 Three medium base lamps, each 60w max.

FOUR-LIGHT BATH

P300363-009 Brushed Nickel
P300363-163 Vintage Brass
P300363-31M Matte Black
 34" L., 8-1/2" ht.
 Extends 6-1/2". H/CTR 5-1/2".
 Four medium base lamps, each 60w max.

All fixtures mount up or down.

Tie the bathroom design together with cabinet hardware, mirrors and lighting edged in a sophisticated matte black finish.

1

Use one metal finish color like matte black to pull all the bathroom details together for a cohesive design.

2

Apply pops of gray on main features to add another interesting design element against white walls.

3

Give the room a modern urban touch with the substantial scale of Saffert wall sconces and the clean lines of the Calais bath bars over the vanities.



FINISHES

- Polished Chrome - 015
- Vintage Brass - 163

P300382-015

Dalton features a metal dome shade supported by turnkey detail. The contrasting finish is an elegant way to add vintage charm and refined industrial style.



ONE-LIGHT BATH
P300381-015 Polished Chrome
P300381-163 Vintage Brass
 5-1/2" L., 9" ht.
 Extends 7-3/8". H/CTR 4-1/4".
 One medium base lamp,
 100w max.



P300381-015



P300381-163

TWO-LIGHT BATH
P300382-015 Polished Chrome
P300382-163 Vintage Brass
 15" L., 9" ht.
 Extends 7-3/8". H/CTR 4-1/4".
 Two medium base lamps,
 each 100w max.



P300382-015



P300382-163

THREE-LIGHT BATH
P300383-015 Polished Chrome
P300383-163 Vintage Brass
 24" L., 9" ht.
 Extends 7-3/8". H/CTR 4-1/4".
 Three medium base lamps,
 each 100w max.



P300383-015



P300383-163

FOUR-LIGHT BATH
P300384-015 Brushed Nickel
P300384-163 Vintage Brass
 33" L., 9" ht.
 Extends 7-3/8". H/CTR 4-1/4".
 Four medium base lamps,
 each 100w max.



P300384-015



P300384-163

All fixtures mount up or down.

Caisson

FINISHES

- Brushed Nickel - 009
- Graphite - 143

P300347-009

Infuse your home with a subtle, industrial flair with the Caisson Collection. The unique frame design takes inspiration from mechanical fittings of factory machinery, while each clear glass shade has an inwardly rolled rim for an added touch of artisanal craftsmanship.

Industrial Flair



ONE-LIGHT BATH
P300345-009 Brushed Nickel
P300345-143 Graphite
 6" W., 9-1/8" ht.
 Extends 7-1/2". H/CTR 5-5/8".
 One medium base lamp, 60w max.



P300345-009



P300346-009

TWO-LIGHT BATH
P300346-009 Brushed Nickel
P300346-143 Graphite
 14-5/8" W., 8-7/8" ht.
 Extends 7-1/2". H/CTR 6-5/8".
 Two medium base lamps, each 60w max.



P300345-143



P300346-143

Caisson

THREE-LIGHT BATH
P300347-009 Brushed Nickel
P300347-143 Graphite
 23-1/4" W., 8-7/8" ht.
 Extends 7-1/2". H/CTR 6-5/8".
 Three medium base lamps, each 60w max.



P300347-009

FOUR-LIGHT BATH
P300348-009 Brushed Nickel
P300348-143 Graphite
 31-7/8" W., 8-7/8" ht.
 Extends 7-1/2". H/CTR 6-5/8".
 Four medium base lamps, each 60w max.



P300347-143

All fixtures mount up or down.



P300348-009



P300348-143

Calhoun

FINISH

● Vintage Brass - 163

P300047-163

A delightful trend in home decor is the repurposing of antique parts into new, functional furniture and accessories. The Calhoun Collection playfully follows this lead with an apothecary style clear glass diffuser held in place with a mechanical latch. The glass shade showcases a thickened profile to create a vintage-style surface for a classic handmade appearance against a soft, Vintage Brass finish.

Vintage Brass



Clear Glass Shade

ONE-LIGHT BATH

P300045-163 Vintage Brass
5" W., 8-5/8" ht.
Extends 7-1/4". H/CTR 6-7/8".
One medium base lamp,
100w max.



P300045-163



P300046-163

TWO-LIGHT BATH

P300046-163 Vintage Brass
13-1/4" W., 8-5/8" ht.
Extends 6-7/8". H/CTR 6-3/8".
Two medium base lamp,
each 100w max.

THREE-LIGHT BATH

P300047-163 Vintage Brass
21-5/8" W., 8-5/8" ht.
Extends 6-7/8". H/CTR 6-3/8".
Three medium base lamp,
each 100w max.



P300047-163

FOUR-LIGHT BATH

P300048-163 Vintage Brass
30-1/4" W., 8-5/8" ht.
Extends 6-7/8". H/CTR 6-3/8".
Four medium base lamp,
each 100w max.



P300048-163



FINISHES

- Polished Chrome - 015
- Matte Black - 31M

P300374-015

Vintage details abound in Ambrose, creating an ageless balance of style and substance. Turned metal fittings support clear glass shades that display nostalgic charm.



ONE-LIGHT BATH
P300373-015 Polished Chrome
P300373-31M Matte Black
 5" L., 7-7/8" ht.
 Extends 6-1/2". H/CTR 5-1/2".
 One medium base lamp,
 60w max.



P300373-015



P300374-015

TWO-LIGHT BATH
P300374-015 Polished Chrome
P300374-31M Matte Black
 13" L., 7-7/8" ht.
 Extends 6-1/2". H/CTR 5-1/2".
 Two medium base lamps,
 60w max.



P300373-31M



P300374-31M

THREE-LIGHT BATH
P300375-015 Polished Chrome
P300375-31M Matte Black
 21" L., 7-7/8" ht.
 Extends 6-1/2". H/CTR 5-1/2".
 Three medium base lamps,
 60w max.



P300375-015

FOUR-LIGHT BATH
P300376-015 Polished Chrome
P300376-31M Matte Black
 29" L., 7-7/8" ht.
 Extends 6-1/2". H/CTR 5-1/2".
 Four medium base lamps,
 60w max.



P300375-31M

All fixtures mount up or down.



P300376-015



P300376-31M

Hinton

FINISHES

- Brushed Nickel - 009
- Vintage Brass - 163
- Matte Black - 31M

P300349-163

Stylish Simplicity



Industrial Demeanor

Embrace stylish simplicity with Hinton, whose industrial demeanor is softened by clear seeded glass suspended from clean metal fittings. Installed over bathroom mirrors, the fixture provides effective task lighting and focused illumination.

Clear Seeded Glass

TWO-LIGHT BATH
P300349-009 Brushed Nickel
P300349-163 Vintage Brass
P300349-31M Matte Black
 15-1/2" W., 7-3/4" ht.
 Extends 7-1/8". H/CTR 5-1/8".
 Two medium base lamps, each 60w max.



P300349-009



P300349-163



P300349-31M

Hinton



P300350-009



P300350-163



P300350-31M



P300351-009



P300351-163



P300351-31M

THREE-LIGHT BATH
P300350-009 Brushed Nickel
P300350-163 Vintage Brass
P300350-31M Matte Black
 24-1/2" W., 7-3/4" ht.
 Extends 7-1/8". H/CTR 5-1/8".
 Three medium base lamps, each 60w max.

FOUR-LIGHT BATH
P300351-009 Brushed Nickel
P300351-163 Vintage Brass
P300351-31M Matte Black
 33-1/2" W., 7-3/4" ht.
 Extends 7-1/8". H/CTR 5-1/8".
 Four medium base lamps, each 60w max.

All fixtures mount up or down.

Modern Organic Style. Wood tones, greenery, natural textures, and calming colors from nature are some of the forms and materials used to create a warm organic feel in the bath.

1

Try a rugged wooden vanity as a warming element and to balance the modern lines and shapes of the tub and sink.

2

Paint the walls in a tranquil color scheme, allowing the textures of the materials to shine.

3

Embrace stylish simplicity with the Hinton vanity light, whose industrial demeanor is softened by clear seeded glass suspended from clean metal fittings.



Hansford

FINISH

● Vintage Brass - 163

P300051-163

The Hansford collection of fixtures feature a clear, spherical shade paired with vintage style metal fittings in a soft, Vintage Brass finish. Featuring a clean and precise design with generous scale, Hansford's classic style brings tranquility to your home.

Vintage Brass

Precise Design

Classic Style



ONE-LIGHT BATH

P300049-163 Vintage Brass
6-1/2" W., 9-1/2" ht.
Extends 7-1/4". H/CTR 6-7/8".
One medium base lamp,
100w max.



P300049-163



P300050-163

TWO-LIGHT BATH

P300050-163 Vintage Brass
15-1/2" W., 10-7/8" ht.
Extends 7-1/4". H/CTR 8-1/4".
Two medium base lamp,
each 60w max.

THREE-LIGHT BATH

P300051-163 Vintage Brass
24-1/2" W., 10-7/8" ht.
Extends 7-1/4". H/CTR 8-1/4".
Three medium base lamp,
each 60w max.



P300051-163

FOUR-LIGHT BATH

P300052-163 Vintage Brass
33-1/2" W., 10-7/8" ht.
Extends 7-1/4". H/CTR 8-1/4".
Four medium base lamp,
each 60w max.



P300052-163

All fixtures mount up or down.



Aiken

FINISHES

- Brushed Nickel - 009
- Vintage Brass - 163

P300322-009

Delightful details pair with clear glass creating the charm of the Aiken Collection. Vintage-style caps top globes reminiscent of an apothecary bottle that has been repurposed for a new life as a light fixture.

*Delightful
Details*

*Vintage-Style
Caps*

Clear Glass Shades

ONE-LIGHT BATH
P300320-009 Brushed Nickel
P300320-163 Vintage Brass
 4-1/2" W., 9-7/8" ht.
 Extends 7". H/CTR 4-1/4".
 One medium base lamp, 60w max.

TWO-LIGHT BATH
P300321-009 Brushed Nickel
P300321-163 Vintage Brass
 14-5/8" W., 9" ht.
 Extends 7". H/CTR 4-1/4".
 Two medium base lamps,
 each 60w max.

All fixtures mount up or down.



P300320-009



P300320-163



P300321-009



P300321-163



P300322-009



P300322-163



P300323-009



P300323-163

Aiken

THREE-LIGHT BATH
P300322-009 Brushed Nickel
P300322-163 Vintage Brass
 23-3/8" W., 9-7/8" ht.
 Extends 7". H/CTR 4-1/4".
 Three medium base lamps,
 each 60w max.

FOUR-LIGHT BATH
P300323-009 Brushed Nickel
P300323-163 Vintage Brass
 32-1/4" W., 9-7/8" ht.
 Extends 7". H/CTR 4-1/4".
 Four medium base lamps,
 each 60w max.

All fixtures mount up or down.

ALSO IN
 Close-To-Ceiling
 See www.progresslighting.com
 for more details.

Conway

FINISHES

- Brushed Nickel - 009
- Matte Black - 031

P300296-009

Conway creates a relaxing haven with styling that gives a nod to seaside charm. A bell-shaped frame has a nautical air that pairs seeded glass with a hand painted wood-style accent.

Seaside Charm

Faux Wood Accents



Seeded Glass Shades

ONE-LIGHT BATH

P300295-009 Brushed Nickel
P300295-031 Matte Black
 6" W., 8-1/4" ht.
 Extends 7". H/CTR 3-3/4".
 One medium base lamp, 60w max.



P300295-009



P300295-031



P300296-009



P300296-031

Conway

THREE-LIGHT BATH

P300297-009 Brushed Nickel
P300297-031 Matte Black
 24" W., 8-1/4" ht.
 Extends 7". H/CTR 3-3/4".
 Three medium base lamps,
 each 60w max.



P300297-009



P300297-031

FOUR-LIGHT BATH

P300298-009 Brushed Nickel
P300298-031 Matte Black
 33" W., 8-1/4" ht.
 Extends 7". H/CTR 3-3/4".
 Four medium base lamps,
 each 60w max.



P300298-009



P300298-031


Mill Beam

FINISH

● Brushed Nickel - 009

P300319-009

The beautiful contrasts of gleaming and rustic finishes are epitomized in Mill Beam, a linear form in a painted concrete finish that gives an unexpected artisanal edginess. Its slab frame creates a perfect base for recessed sockets that allow decorative bulbs to take center stage in casting an eye-catching glow.



Faux Concrete Finish

Rustic Design

Artisanal Edginess


THREE-LIGHT BATH

P300319-009 Brushed Nickel
24" W., 4-3/4" ht.
Extends 4-1/2". H/CTR 2-3/8".
Three medium base lamps,
each 60w max.

WALL BRACKET

P710099-009 Brushed Nickel
4-3/4" W., 7-1/8" ht.
Extends 4-3/8". H/CTR 3-5/8".
One medium base lamp, 60w max.

*Fixture can be installed
horizontally or vertically.*



P300319-009



P710099-009



P710099-009
shown facing up



P300319-009
shown vertical

Axle

FINISHES

● Brushed Nickel - 009
● Antique Bronze - 020

P300190-020

Axle mixes old and new to charming effect. Industrial elements are seen in the working gooseneck arm that provides tilt adjustment for vintage style sockets. Axle provides the perfect platform to showcase bulbs that stray from the ordinary for a truly distinctive splash of style.



Vintage Style

*Gooseneck
Arm*

*Industrial
Elements*



P300189-009



P300189-020



P300191-009



P300190-009



P300191-020

ONE-LIGHT BATH

P300189-009 Brushed Nickel
P300189-020 Antique Bronze
6-1/8" W., 6-3/4" ht.
Extends 6". H/CTR 3-3/4".
One medium base lamp, 60w max.

TWO-LIGHT BATH

P300190-009 Brushed Nickel
P300190-020 Antique Bronze
16" W., 6-3/4" ht.
Extends 6". H/CTR 3-3/4".
Two medium base lamps,
each 60w max.

THREE-LIGHT BATH

P300191-009 Brushed Nickel
P300191-020 Antique Bronze
24" W., 6-3/4" ht.
Extends 6". H/CTR 3-3/4".
Three medium base lamps,
each 60w max.

All fixtures mount up or down.

FINISHES

- Brushed Nickel - 009
- Matte Black - 31M

P300378-009

Stoic squared elements are the prevailing theme of Gilmour. Clear glass shades are paired with a smooth metal arm and backplate to create a classic look with modern sensibility.

Smooth Metal Elements

Stoic Square Silhouette



Clear Squared Glass

ONE-LIGHT BATH

P300377-009 Brushed Nickel
P300377-31M Matte Black
 4-1/2" L., 7" ht.
 Extends 5-1/2". H/CTR 4-7/8".
 One medium base lamp, 60w max.



P300377-009



P300378-009

TWO-LIGHT BATH

P300378-009 Brushed Nickel
P300378-31M Matte Black
 12-1/4" L., 7" ht.
 Extends 5-1/2". H/CTR 4-7/8".
 Two medium base lamps, each 60w max.



P300377-31M



P300378-31M

All fixtures mount up or down.



P300379-009



P300379-31M

THREE-LIGHT BATH

P300379-009 Brushed Nickel
P300379-31M Matte Black
 20-1/8" L., 7" ht.
 Extends 5-1/2". H/CTR 4-7/8"
 Three medium base lamps, each 60w max.

FOUR-LIGHT BATH

P300380-009 Brushed Nickel
P300380-31M Matte Black
 27-7/8" L., 7" ht.
 Extends 5-1/2". H/CTR 4-7/8"
 Four medium base lamps, each 60w max.

All fixtures mount up or down.



P300380-009



P300380-31M



Organic and earthy details juxtaposed with modern touches create a timeless design that isn't too trendy.

1

Use a calming gray feature wall behind a contemporary wooden vanity to ground the space.

2

Create a theme of squared elements using the Gilmour vanity light offset by tall modern faucets and a wood-framed mirror and artwork.

3

Complete the peaceful aura with a deep soaking tub for the ultimate in relaxation.

League

FINISHES

- Brushed Nickel - 009
- Matte Black - 31M

Clean Modern Style



Etched Glass Shades

Sleek Rails

ONE-LIGHT BATH
P300341-009 Brushed Nickel
P300341-31M Matte Black
 4-1/2" W., 8" ht.
 Extends 5-1/2". H/CTR 4-1/2".
 One medium base lamp, 100w max.



P300341-009



P300341-31M

TWO-LIGHT BATH
P300342-009 Brushed Nickel
P300342-31M Matte Black
 13-5/8" W., 7-5/8" ht.
 Extends 5-1/2". H/CTR 5".
 Two medium base lamps, each 100w max.



P300342-009



P300342-31M

All fixtures mount up or down.

League

THREE-LIGHT BATH
P300343-009 Brushed Nickel
P300343-31M Matte Black
 23" W., 7-5/8" ht.
 Extends 5-1/2". H/CTR 5".
 Three medium base lamps, each 100w max.



P300343-009

FOUR-LIGHT BATH
P300344-009 Brushed Nickel
P300344-31M Matte Black
 32-1/2" W., 7-5/8" ht.
 Extends 5-1/2". H/CTR 5".
 Four medium base lamps, each 100w max.



P300343-31M

All fixtures mount up or down.



P300344-009



P300344-31M

Ashford

FINISHES

- Brushed Nickel - 009
- Polished Chrome - 015

Ashford provides nostalgic charm with crisp details like knurled sockets and vintage-style opal glass shades. This handsome pairing combined with a classic metallic finish is a skillful blending of old and new.

Nostalgic Charm

Metallic Finish

Opal Glass Shades



ONE-LIGHT BATH
P300314-009 Brushed Nickel
P300314-015 Polished Chrome
 5-3/8" W., 10" ht.
 Extends 8". H/CTR 5".
 One medium base lamp, 100w max.



P300314-009



P300315-009

TWO-LIGHT BATH
P300315-009 Brushed Nickel
P300315-015 Polished Chrome
 14-1/2" W., 10" ht.
 Extends 8". H/CTR 5".
 Two medium base lamps,
 each 100w max.



P300314-015



P300315-015

Ashford

THREE-LIGHT BATH
P300316-009 Brushed Nickel
P300316-015 Polished Chrome
 24" W., 10" ht.
 Extends 8". H/CTR 5".
 Three medium base lamps,
 each 100w max.

FOUR-LIGHT BATH
P300317-009 Brushed Nickel
P300317-015 Polished Chrome
 33-1/2" W., 10" ht.
 Extends 8". H/CTR 5".
 Four medium base lamps,
 each 100w max.

All fixtures mount up or down.



P300316-009



P300316-015



P300317-009



P300317-015

Clifton Heights NEW

FINISH
● Matte Black - 31M

P300160-31M

Distinctive chiseled features and clean lines are key features within the Clifton Heights collection. Inspired by an updated interpretation of Craftsman styling, careful attention to the details delivers a dramatic accent.

Craftsman Styling

Distinctive Chiseled Elements



Squared-Off Shades



P300159-31M



P300158-31M



P300160-31M



P300161-31M

ONE-LIGHT BATH
P300158-31M Matte black
5-1/2" W, 8-3/8" ht.,
Extends 7-1/8", H/CTR 4-5/8".
One medium base lamp,
100w max.

TWO-LIGHT BATH
P300159-31M Matte Black
14-1/4" W., 8-3/8" ht.,
Extends 7-1/8", H/CTR 5-5/8".
Two medium base lamp,
each 100w max.

THREE-LIGHT BATH
P300160-31M Matte Black
23" W., 8-3/8" ht.,
Extends 7-1/8", H/CTR 5-5/8".
Three medium base lamp,
each 100w max.

FOUR-LIGHT BATH
P300161-31M Matte Black
31-3/4" W., 8-3/8" ht.,
Extends 7-1/8", H/CTR 5-5/8".
Four medium base lamp,
each 100w max.

All fixtures mount up or down.

Merry

The Merry Collection brings a joyful aura to any room, with its modern vibe and clean-lined tubular frame accentuated with etched glass shades.

FINISH
● Brushed Nickel - 009
● Matte Black - 031

ONE-LIGHT BATH
P300327-009 Brushed Nickel
P300327-031 Matte Black
4-3/8" W., 8-1/4" ht.
Extends 5-3/4". H/CTR 4-7/8".
One medium base lamp, 100w max.

TWO-LIGHT BATH
P300328-009 Brushed Nickel
P300328-031 Matte Black
12" W., 8-1/4" ht.
Extends 5-3/4". H/CTR 4-7/8".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH
P300329-009 Brushed Nickel
P300329-031 Matte Black
24" W., 8-1/4" ht.
Extends 5-3/4". H/CTR 4-7/8".
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH
P300330-009 Brushed Nickel
P300330-031 Matte Black
30" W., 8-1/4" ht.
Extends 5-3/4". H/CTR 4-7/8".
Four medium base lamps,
each 100w max.

All fixtures mount up or down.



P300327-009



P300329-009



P300327-031



P300329-031



P300328-009



P300328-031



P300330-009



P300330-031

FINISHES

- Brushed Nickel - 009
- Satin Brass - 012
- Matte Black - 031

SIX-LIGHT BATH

P300372-009 Brushed Nickel
P300372-012 Satin Brass
P300372-031 Matte Black
 48-1/2" L., 7-5/8" ht.
 Extends 6". H/CTR 5-3/8".
 Six medium base lamps,
 each 60w max.

Fundamentally modern but with a traditional twist, Adley combines simple, clear glass shades with a curved edge backplate.

See the full collection at progresslighting.com.



P300372-009



P300372-012



P300372-031

All fixtures mount up or down.

FINISHES

- Brushed Nickel - 009
- Antique Bronze - 020
- Textured Black - 031
- Polished Nickel - 104

SIX-LIGHT BATH

P300385-009 Brushed Nickel
P300385-020 Antique Bronze
P300385-031 Textured Black
P300385-104 Polished Nickel
 48" L., 7-5/8" ht.
 Extends 6". H/CTR 5-3/8".
 Six medium base lamps,
 each 100w max

Smooth forms, linear details and a pleasingly elegant frame enhance a simplified modern look in the Replay Collection. This versatile fixture can be mounted up or down.

See the full collection at progresslighting.com.



P300385-009



P300385-020



P300385-104



P300385-031

All fixtures mount up or down.

Navarre

P550089-031

FINISH

● Matte Black - 031

The Navarre pendant defines indoor-outdoor gathering spaces with statement-making style. Several rectangular cubes nest within each other, forming a breezy contemporary angular silhouette. Shimmering seeded glass panels cast a pleasing glow that is punctuated by its dramatic Matte Black frame. Navarre will shine as the focal point of covered outdoor dining and entertaining areas. Listed for damp location installation.

*Dramatic
Frame*



Seeded Glass

Statement-making Style

ONE-LIGHT OUTDOOR PENDANT

P550089-031 Matte Black

10" SQ., 28-5/8" ht.

Overall ht. w/chain 102-1/2", wire 10'.

One medium base lamp, 60w max.



Terrace

P550011-31M

FINISH

● Matte Black - 31M

Terrace furnishes an elegantly rustic focal point to both outdoor and indoor entertaining spaces. A slender frame creates a captivating circular silhouette. Pleasing illumination is cast from a central seeded glass shade to highlight the coppery-bronze woven accent band.



ONE-LIGHT OUTDOOR PENDANT

P550111-31M Matte Black

17-7/8" dia., 20-1/2" ht.

Overall ht. w/chain 101", wire 10'.

One medium base lamp, 60w max.



Pawley

FINISHES

- Matte Black - 031
- Galvanized-141

Pawley has an airy basketweave design offering an organic global feel and coastal warmth. The synthetic rattan frame has a graceful, lattice-like design and a lovely, hand-applied finish that gives charm and depth. The frame's woven structure comfortably diffuses the glow from the etched glass shade at its center. Pawley's natural aesthetic is ideal for indoor-outdoor entertaining in Coastal, Rustic and Transitional settings. Listed for damp location installation.



ONE-LIGHT OUTDOOR PENDANT

P550083-031 Matte Black

P550083-141 Galvanized

12" dia., 16" ht.

Overall ht. w/stem 82", wire 10'.

One medium base lamp, 100w max.



Manteo

FINISH

- Cottage White - 151

P550084-151

Manteo features a dense woven design that infuses outdoor spaces with a rugged style. Its double-shade design filters warm, subtle light downwards to add a glowing ambiance to covered outdoor patios, porches, and dining areas. Constructed of natural-looking synthetic rattan, Manteo adds a unique, warm touch to Coastal and Transitional settings. Listed for damp location installation.



ONE-LIGHT OUTDOOR PENDANT

P550084-151 Cottage White

12" dia., 16-5/8" ht.

Overall ht. w/stem 82-1/2", wire 10'.

One medium base lamp, 100w max.



Cedar Springs

A fun take on a traditional warehouse shade, Cedar Springs can be a stylish addition to any indoor or outdoor space. This pendant brings vintage character to porches and patios or use in a kitchen to add farmhouse charm.

FINISH

- White - 030
- Black - 031
- Red - 039

ONE-LIGHT OUTDOOR PENDANT

P550116-030 White
P550116-031 Black
P550116-039 Red
 13-1/4" dia., 7-1/2" ht.
 Overall ht. w/stem 65-1/2", wire 10'.
 One medium base lamp, 100w max.



Birkdale NEW

FINISHES

- Antique Bronze - 020
- Textured Black - 031

P560317-020



Birkdale features open geometric cage paired with a stately roof to lend robust style. Using traditional or LED lamp, the design minimizes glare and reduces light trespass to protect the night sky.



P560316-020



P560316-031



P560317-020



P560317-031

MEDIUM WALL LANTERN
P560316-020 Antique Bronze
P560316-031 Textured Black
 5-3/4" W., 18-3/8" ht.
 Extends 8-1/4". H/CTR 12-1/8".
 One medium base lamp,
 100w max.

LARGE WALL LANTERN
P560317-020 Antique Bronze
P560317-031 Textured Black
 7" W., 23-1/4" ht.
 Extends 9-1/2". H/CTR 17".
 One medium base lamp,
 100w max.

All fixtures:



Chilton NEW

FINISH

● Textured Black - 031

P550120-031

Frosted Glass Diffuser

Airy Open Frame



A frosted glass cylinder is suspended inside an open frame giving Chilton an airy form. Although its lantern styling is traditional in silhouette, the frame's square, linear construction creates a modern impression.



P560315-031



P560314-031



P560313-031



P540120-31

POST LANTERN

P540120-031 Textured Black
11" sq., 21-1/8" ht.
Fits 3" post (sold separately).
One medium base lamp,
60w max.

HANGING LANTERN

P550120-031 Textured Black
11" sq., 17-1/2" ht.
Overall ht. w/chain 92-1/2".
One medium base lamp,
100w max

SMALL WALL LANTERN

P560313-031 Textured Black
7-1/2" W., 14-7/8" ht.
Extends 8-5/8", H/CTR 8".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN

P560314-031 Textured Black
8-7/8" W., 17-3/4" ht.
Extends 10-1/8". H/CTR 9-1/2".
One medium base lamp,
100w max.

LARGE WALL LANTERN

P560315-031 Textured Black
11" W., 21-5/8" ht.
Extends 12-1/4". H/CTR 11-5/8".
One medium base lamp,
100w max.

Grandbury NEW

FINISH

● Antique Bronze - 020

P550064-020

Half Loop Handle

Simple Square Frame



Partner timeless elegance with a pinch of coastal vibe with Grandbury. A beautiful square frame crafted from corrosion-proof composite polymer material features a half loop on top of the structure and is accented by clear glass panes. Made with DURASHIELD, a durable material specially designed and tested to resist harsh environmental conditions.



P560174-020



P560175-020



P560176-020



P540064-020

HANGING LANTERN

P550064-020 Antique Bronze
7" sq., 15-5/8" ht.
One medium base lamp,
75w max.

POST LANTERN

P540064-020 Antique Bronze
7" sq., 15-5/8" ht.
Fits 3" post (sold separately).
One medium base lamp,
75w max.

SMALL WALL LANTERN

P560174-020 Antique Bronze
5-1/2" W., 11-7/8" ht.
Extends 6-1/2", H/CTR 3-1/8".
One medium base lamp,
60w max.

MEDIUM WALL LANTERN

P560175-020 Antique Bronze
8" W., 13-5/8" ht.
Extends 10", H/CTR 3-1/8"
One medium base lamp,
75w max.

LARGE WALL LANTERN

P560176-020 Antique Bronze
9" W., 17-1/8" ht.
Extends 10", H/CTR 3-1/8"
Two medium base lamps,
each 60w max.

Gables

FINISH

- Satin White - 028
- Antique Bronze - 020

P560088-028 **N**



Softly Curved Design

Clear Glass Panels

Curves soften the frame of Gables, creating a distinctive silhouette. Constructed from engineered composite polymers, the corrosion-resistant housing delivers beautiful lighting and reliability. A clear glass diffuser enhances the classic design. Made with DURASHIELD, a durable material specially designed and tested to resist harsh environmental conditions.



P560087-028 **N**

P550050-028 **N**



HANGING LANTERN
P550050-028 Satin White
 7-1/2" dia., 14-1/8" ht.
 Overall ht. w/chain 89", wire 10'.
 One medium base lamp,
 75w max.

SMALL WALL LANTERN
P560087-028 Satin White
 5-7/8" W., 11-3/4" ht.
 Extends 6-7/8", H/CTR 7-5/8".
 One medium base lamp,
 60w max.

POST LANTERN
P540033-028 Satin White
 7-1/2" dia., 16-3/4" ht.
 Fits 3" post (sold separately).
 One medium base lamp,
 75w max.

LARGE WALL LANTERN
P560088-028 Satin White
 7-1/2" W., 14-1/8" ht.
 Extends 8-1/2". H/CTR 10-9/16".
 One medium base lamp,
 75w max.



P540033-028 **N**



P560088-020



P560087-020



P550050-020



P540033-020

POST LANTERN
P540033-020 Antique Bronze
 7-1/2" dia., 16-3/4" ht.
 Fits 3" post (sold separately).
 One medium base lamp,
 75w max.

HANGING LANTERN
P550050-020 Antique Bronze
 7-1/2" dia., 14-1/8" ht.
 Overall ht. w/chain 89", wire 10'.
 One medium base lamp,
 75w max.

SMALL WALL LANTERN
P560087-020 Antique Bronze
 5-7/8" W., 11-3/4" ht.
 Extends 6-7/8", H/CTR 7-5/8".
 One medium base lamp,
 60w max.

LARGE WALL LANTERN
P560088-020 Antique Bronze
 7-1/2" W., 14-1/8" ht.
 Extends 8-1/2". H/CTR 10-9/16".
 One medium base lamp,
 75w max.

N New Product

FINISHES

- Antique Bronze - 020
- Textured Black - 031

P560323-031

Traditional Form

Scrolled Arm

Clear Beveled Glass



Intricate detailing and clear beveled glass give Dillard classic appeal. A scrolled arm and traditional lantern form combine with a beveled glass panes to create a timeless, sophisticated design.



P560321-020



P560321-031



P560322-020



P560322-031



P560323-020



P560323-031

SMALL WALL LANTERN
P560321-020 Antique Bronze
P560321-031 Textured Black
 6-1/2" W., 11-3/8" ht.
 Extends 6-3/8", H/CTR 8-3/8".
 One medium base lamp,
 60w max.

LARGE WALL LANTERN
P560323-020 Antique Bronze
P560323-031 Textured Black
 9-3/4"W., 18-1/8" ht.
 Extends 9-1/2". H/CTR 10-1/2".
 One medium base lamp,
 60w max.

MEDIUM WALL LANTERN
P560322-020 Antique Bronze
P560322-031 Textured Black
 8-1/8" W., 15-1/2" ht.
 Extends 7-7/8", H/CTR 8-7/8".
 One medium base lamp,
 60w max.

P550122-020



P550122-031



POST LANTERN

P540099-020 Antique Bronze
P540099-031 Textured Black
 9-3/4" dia., 18-1/8" ht.
 Fits 3" post (sold separately).
 One medium base lamp, 60w max.

HANGING LANTERN

P550122-020 Antique Bronze
P550122-031 Textured Black
 7-1/2" dia., 13-5/8" ht.
 Overall L. w/chain 52-1/2",
 One medium base lamp, 60w max.

P540099-020



P540099-031



Stature

FINISHES

- Textured Black - 031
- Oil Rubbed Bronze - 108

P560268-108



Hinged Door

Elevate your home's curb appeal with Stature, where a traditional, gaslight look is modernized with clean lines and minimal detailing. Clear glass doors allow for bright illumination and feature a recessed hinged door that adds to the lantern's sleek style and ease of maintenance. Brass-toned accents with crosshatch pattern offer signature historical detailing.

Gaslight Look

Brass-toned Accents



P560267-031



P560267-108



P560268-031



P560268-108



P560269-031



P560269-108

SMALL WALL LANTERN

P560267-031 Textured Black
P560267-108 Oil Rubbed Bronze
 6" W., 11-1/2" ht.
 Extends 5-3/8". H/CTR 5-3/4".
 One candelabra base lamp, 60w max.

MEDIUM WALL LANTERN

P560268-031 Textured Black
P560268-108 Oil Rubbed Bronze
 8" W., 16" ht.
 Extends 5-7/8". H/CTR 8".
 Two candelabra base lamps,
 each 60w max.

LARGE WALL LANTERN

P560269-031 Textured Black
P560269-108 Oil Rubbed Bronze
 9" W., 21" ht.
 Extends 5-7/8". H/CTR 10-1/2".
 Two candelabra base lamps,
 each 60w max.

Wakeford

FINISH

- Antique Copper - 169

P560262-169

Modern Sophistication



Water Glass

Cross Brace Design

Elements of painted Antique Copper, water glass and crown molding trim give Wakeford a nostalgic look with modern sophistication. A cross brace design contrasts against the textured glass panes to offer a vintage look that fits well with both rustic and traditional exteriors.



P560261-169



P560262-169

SMALL WALL LANTERN

P560261-169 Antique Copper
 8" W., 17-7/8" ht.
 Extends 5-3/4". H/CTR 9-1/4".
 One medium base lamp, 60w max.

MEDIUM WALL LANTERN

P560262-169 Antique Copper
 10" W., 21-1/2" ht.
 Extends 6-3/4". H/CTR 11-1/4".
 One medium base lamp, 60w max.

Williamston

FINISHES

- Antique Bronze - 020
- Antique Pewter - 103

P560265-103



Curved Handle

Classic Appeal

Williamston brings the timeless details expected from an outdoor lantern into a fresh silhouette. The lantern's frame features a two-over-two grille design reminiscent of a traditional casement window frame. A curved handle accentuates the tiers of the fixture's square top for classic appeal.

Timeless Details



P560264-020



P560264-103



P560265-020



P560265-103



P560266-020



P560266-103



P540095-020



P540095-103

POST LANTERN
P540095-020 Antique Bronze
P540095-103 Antique Pewter
 7" sq., 20-1/4" ht.
 Fits 3" post (sold separately).
 One medium base lamp,
 100w max.

MEDIUM WALL LANTERN
P560265-020 Antique Bronze
P560265-103 Antique Pewter
 6" W., 14-1/4" ht.
 Extends 7". H/CTR 3-1/4".
 One medium base lamp,
 100w max.

SMALL WALL LANTERN
P560264-020 Antique Bronze
P560264-103 Antique Pewter
 5" W., 12" ht.
 Extends 6". H/CTR 2-3/4".
 One medium base lamp,
 60w max.

LARGE WALL LANTERN
P560266-020 Antique Bronze
P560266-103 Antique Pewter
 7" W., 18" ht.
 Extends 8-1/8". H/CTR 4-1/8".
 One medium base lamp,
 100w max.

Watch Hill

FINISH

- Textured Black - 031

P550292-031



Timeless Style

Elongated Design

Seeded Glass

Watch Hill features an elongated design, highlighted by slender arms curving gracefully around a seeded glass shade. With design elements inspired by Victorian-era gaslight fittings, Watch Hill has a timeless style that complements a variety of home styles.



P560255-031



P550292-031



P560256-031



P540292-031



P560257-031



P550110-031

SMALL WALL LANTERN
P560255-031 Textured Black
 6-1/8" W., 12-3/4" ht.
 Extends 7-3/8". H/CTR 4-1/2".
 One medium base lamp,
 60w max.

POST LANTERN
P540292-031 Textured Black
 8-1/8" dia., 18-1/4" ht.
 Fits 3" post (sold separately).
 One medium base lamp,
 60w max.

MEDIUM WALL LANTERN
P560256-031 Textured Black
 7-1/2" W., 17" ht.
 Extends 8-3/4". H/CTR 4-1/4".
 One medium base lamp,
 60w max.

HANGING LANTERN
P550292-031 Textured Black
 7-1/2" dia., 15-3/8" ht.
 Overall ht. w/stem 80-1/2",
 wire 10'.
 One medium base lamp,
 60w max.

LARGE WALL LANTERN
P560257-031 Textured Black
 8-1/2" W., 19-3/8" ht.
 Extends 10-1/4". H/CTR 4-1/4".
 One medium base lamp,
 60w max.

OUTDOOR FLUSH MOUNT
P550110-031 Textured Black
 8-1/2" dia., 11-5/8" ht.
 One medium base lamp,
 60w max.

Walcott

FINISH

● Antique Bronze - 020

P560287-020



Walcott lanterns combine a stately elegance with modern style. A distinctive vertical frame is glazed with clear glass panels and punctuated with brass-tone accents to add vintage charm.



P560286-020

SMALL WALL LANTERN
P560286-020 Antique Bronze
 7-1/8" W., 14" ht.
 Extends 7-3/8", H/CTR 3-1/4".
 One medium base lamp,
 60w max.

POST LANTERN
P540090-020 Antique Bronze
 8-1/4" W., 21-3/8" ht.
 Fits 3" post (sold separately).
 One medium base lamp,
 60w max.

LARGE WALL LANTERN
P560287-020 Antique Bronze
 8-1/4" W., 20" ht.
 Extends 8-1/4". H/CTR 4".
 One medium base lamp,
 60w max.



P540090-020

Whitmire

FINISH

● Matte Black - 31M

P540094-31M **N**



Whitmire blends rustic style with modern elegance, bringing a touch of cabin charm to a home's exterior. Wood-tone bands accent and frame a clear, seeded glass shade for beautiful and bright illumination.



P560282-31M



P560281-31M



P550109-31M

POST LANTERN
P540094-31M Matte Black
 7-3/8" dia., 15-3/8" ht.
 Fits 3" post (sold separately).
 One medium base lamp,
 100w max.

SMALL WALL LANTERN
P560281-31M Matte Black
 6-3/8" W., 13" ht.
 Extends 7-1/2", H/CTR 10-3/8".
 One medium base lamp,
 60w max.

OUTDOOR FLUSH MOUNT
P550109-31M Matte Black
 7-3/8" dia., 8" ht.
 One medium base lamp,
 60w max.

LARGE WALL LANTERN
P560282-31M Matte Black
 7-3/8" W., 14-1/2" ht.
 Extends 8-1/2". H/CTR 11-3/4".
 One medium base lamp,
 60w max.

N New Product

Exton

FINISH

- Textured Black - 031

P550097-031

Peaked Roof



Geometric Forms

Architectural influences blend harmoniously in Exton, resulting in a modern design that works in both urban and suburban landscapes. Clean lines and geometric forms interact in its textured black frame, culminating in an iconic peaked roof. Exton brings bold design and visual unity to contemporary elevations.



P550097-031

P560273-031

Architectural Influences

POST LANTERN

P540097-031 Textured Black
11-1/8" dia., 17-1/8" ht.
Fits 3" post (sold separately).
One medium base lamp,
100w max.

MED WALL LANTERN

P560273-031 Textured Black
9-1/8" W., 12" ht.
Extends 9-3/8". H/CTR 9".
One medium base lamp,
100w max.

HANGING LANTERN

P550097-031 Textured Black
11-1/8" dia., 16" ht.
Overall ht. w/stem 91",
wire 10'.
One medium base lamp,
100w max.

LARGE WALL LANTERN

P560274-031 Textured Black
11-1/8" W., 15-1/2" ht.
Extends 11-1/4". H/CTR 12-1/2".
One medium base lamp,
100w max.



P560274-031

P540097-031

Tremont

FINISHES

- Matte Black - 031
- Stainless Steel - 135

P550093-031

Industrial Detail



Mechanical Fittings

Seeded Glass Shade

The cool factor reigns with the Tremont collection of outdoor lighting. Mechanical stainless-steel fittings offer industrial detail to the design. A seeded glass shade gives a rustic look that's tailor-made for modern home exteriors.



P550094-031

P550094-135



P550093-031

P550093-135

OUTDOOR MINI-PENDANT

P550093-031 Matte Black
P550093-135 Stainless Steel
9" dia., 8" ht.
Overall ht. w/chain 77", wire 10'.
One medium base lamp, 60w max.

ONE-LIGHT SEMI-FLUSH

P550094-031 Matte Black
P550094-135 Stainless Steel
9" dia., 10" ht.
One medium base lamp,
60w max.

WALL LANTERN

P560263-031 Matte Black
P560263-135 Stainless Steel
9" W., 11" ht.
Extends 10". H/CTR 4-1/2".
One medium base lamp,
60w max.



P560263-031

P560263-135

Padgett NEW

Taking cues from traditional coach lanterns, Padgett features a clean, tapered form glazed with clear seeded glass. The angular finial adds a contemporary element to the classic design

FINISHES

- Antique Bronze - 020
- Textured Black - 031

POST LANTERN

P540093-020 Antique Bronze

P540093-031 Textured Black
8" sq., 18-1/2" ht.

Fits 3" post (sold separately).

One medium base lamp, 100w max.

SMALL WALL LANTERN

P560307-020 Antique Bronze

P560307-031 Textured Black
6" W., 11-1/4" ht.

Extends 7-1/4", H/CTR 8-3/4".

One medium base lamp, 100w max.

MEDIUM WALL LANTERN

P560308-020 Antique Bronze

P560308-031 Textured Black
8" W., 15" ht.

Extends 9-5/8", H/CTR 11-3/8".

One medium base lamp, 100w max.

LARGE WALL LANTERN

P560309-020 Antique Bronze

P560309-031 Textured Black
10" W., 18-7/8" ht.

Extends 11-3/4", H/CTR 14-1/2".

One medium base lamp, 100w max.



P560307-020



P560307-031



P560308-020



P560308-031



P560309-020



P560309-031



P540093-020



P540093-031



P5622-31



P5623-31



P6440-31MD

District NEW

The District Collection features a distinctive metal shade that contributes an industrial-inspired design to its versatile vintage form. Dark sky compliant.

FINISH

- Textured Black - 31

MEDIUM WALL LANTERN

P5622-31 Textured Black

8" W., 8-1/4" ht.

Extends 10-1/4", H/CTR 4-1/8".

One medium base lamp, 100w max

LARGE WALL LANTERN

P5623-31 Textured Black

12" W., 10-1/2" ht.

Extends 13-1/4", H/CTR 5".

One medium base lamp,

100w max

All fixtures:



Crawford NEW

Transform the outdoors with Crawford's timeless styling. Die-cast aluminum with etched flat glass. Hinged door for easy relamping.

FINISH

- Textured Black - 31

POST LANTERN


P6440-31MD Textured Black

9-7/8" dia., 24-5/8" ht.

Fits 3" post (sold separately).

One medium base lamp, 100w max.

Trafford Non-Metallic Lantern

Trafford modernizes the craftsman style in a crisp squared frame. Polymeric construction delivers excellent durability that resists corrosion and rust. Made in USA. 

FINISH

- Textured Black - 031

SMALL WALL LANTERN

P560288-031 Textured Black
5" W., 11-1/2" ht.
Extends 6-3/4", H/CTR 4-5/8".
One medium base lamp, 60w max.

LARGE WALL LANTERN

P560289-031 Textured Black
6" W., 14" ht.
Extends 8-1/2". H/CTR 5-5/8".
One medium base lamp, 60w max.




P560288-031



P560289-031

Milford Non-Metallic Lantern


Milford embodies classic style in a durable, corrosion-resistant polymeric housing. The ADA compliant, low-profile wall light incorporates a photocell for convenient dusk-to-dawn illumination. Made in USA. 

FINISH

- Textured Black - 031

WALL LANTERN WITH PHOTOCELL

P560283-031-PC Textured Black
7-1/2" W., 9-7/8" ht.
Extends 4", H/CTR 2".
One medium base lamp, 60w max.



INTEGRATED PHOTOCELL

Automatically turns the fixture on at dusk and off at dawn with no programming required.



Barlowe

Transform your home into a warm and cozy dream with the friendly farmhouse-style of this small wall lantern. A rustic cross brace design decorates the charming lantern silhouette. Clear seeded glass panes add an extra pop of rustic personality.

FINISHES

- Antique Bronze - 020
- Stainless Steel - 135

FLUSH MOUNT

P550069-020 Antique Bronze
P550069-135 Stainless Steel
11-1/2" sq., 5-1/2" ht.
Two medium base lamps, each 60w max.



P550069-020



P550069-135



P560158-020



P560158-135

See more from this collection at www.progresslighting.com.

Hard-Nox LED NEW

Stylish and simple, the Hard-Nox Collection features banded details that add function and durability to indoor and outdoor settings. An impact-resistant polycarbonate lens offers even illumination for residential and light commercial applications.

FINISHES

- Satin White - 028
- Black -031

ALUMINUM ROUND

P550112-028-30 Satin White
P550112-031-30 Black
 11-7/8" dia., 3" ht.
 One 25w LED module, 3000K, 90CRI, 2347 source lumens.



POLY ROUND

P550114-028-30 Satin White
P550114-031-30 Black
 9-7/8" dia., 4-3/4" ht.
 One 25w LED module, 3000K, 90CRI, 2347 source lumens.

POLY SQUARE

P550115-028-30 Satin White
P550115-031-30 Black
 10" sq., 4-1/2" ht.
 One 25w LED module, 3000K, 90CRI, 2347 source lumens.

CLEAR POLY LENS SQUARE

P550113-028-30 Satin White
 10-1/2" sq., 4" ht.
 One 25w LED module, 3000K, 90CRI, 2347 source lumens.



P550112-028-30



P550112-031-30



P550114-028-30



P550114-031-30



P550115-028-30



P550115-031-30



P550113-028-30



P560260-028-30



P560260-031-30



P560260-031-30
shown lit



P560259-028-30



P560259-031-30



P560259-031-30
shown lit

Z-2020 LED

Function follows form in Z-2020. Unlit, it functions as a sleek piece of wall art; turn it on, and its LED light presents an otherworldly glow that is strikingly reminiscent of a total eclipse. Light is cast around the edges of the form, creating a dramatic dark center.

FINISHES

- Satin White - 028
- Textured Black - 031

OUTDOOR WALL SCONCE

P560260-028-30 Satin White
P560260-031-30 Textured Black
 6-1/4" dia., 2-1/4" ht.
 One 9w LED module, 3000K, 90CRI, 623 source lumens.



Z-2025 LED

Function follows form in Z-2025. Unlit, it functions as a sleek piece of wall art; turn it on, and its LED light presents an otherworldly glow that is strikingly reminiscent of a total eclipse. Light is cast around the edges of the form, creating a dramatic dark center.

FINISHES

- Satin White - 028
- Textured Black - 031

OUTDOOR WALL SCONCE

P560259-028-30 Satin White
P560259-031-30 Textured Black
 6-1/4" sq., 2-1/4" ht.
 One 9w LED module, 3000K, 90CRI, 623 source lumens.



Cord Mount Damp Location Aluminum Cylinders

A clean and modern design allow this sleek cord hung pendant cylinder to compliment a variety of areas and settings. A field cuttable cord provides flexibility in application, making it suitable for a large range of ceiling heights.

Aluminum Cylinders

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)
P500355-020 P500355-030 P500355-031	Antique Bronze White Black	5" cord mount cylinder.	5" dia., 9-13/16" ht. Overall ht. w/ cord 130-9/16"; wire 10'	175w PAR-30 or 75w BR-30
P500356-020 P500356-030 P500356-031	Antique Bronze White Black	6" cord mount cylinder.	6" dia., 12" ht. Overall ht. w/ cord 132-13/16"; wire 10'	1250w PAR-38 or 150w BR-40

All fixtures:



P500355-020 P500355-030 P500355-031 P500356-020 P500356-030 P500356-031

Aluminum Cylinders LED

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)
P550099-020-30 P550099-031-30	Antique Bronze Black	5" LED cord mount cylinder.	5" dia., 9-13/16" ht. Overall ht. w/ cord 130-9/16"; wire 10'	118.6w integrated LED, 3000K, 90CRI, 468 delivered lumens
P550100-020-30 P550100-031-30	Antique Bronze Black	6" LED cord mount cylinder.	6" dia., 12" ht. Overall ht. w/ cord 132-13/16"; wire 10'	132.4w integrated LED, 3000K, 90CRI, 930 delivered lumens

All fixtures:



P550099-020-30 P550099-031-30 P550100-020-30 P550100-031-30

Aluminum Cylinder Accessories

PRODUCT NO.	FINISH	DESCRIPTION
P860058-030	White	150" cord replacement kit for P50355,
P860058-031	Black	P500356, P550099 and P550100.



P860058-031



P860058-030

Photocell Wet Location Aluminum Cylinders LED

Add security, energy efficiency and style to exteriors with this sleek cylinder. Its contemporary design offers a modern accent. Energy efficiency from the integrated LEDs is enhanced by the integrated photocell, which automatically turns the fixture on at dusk and off at dawn – no programming required.

5" Aluminum Cylinders LED

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)
P550101-020-30 P550101-031-30	Antique Bronze Black	Down cylinder with photocell.	5" W., 7-1/4" ht.	118.6w integrated LED, 3000K, 90CRI, 511 delivered lumens
P550102-020-30 P550102-031-30	Antique Bronze Black	Up/down cylinder with photocell. Lens cover included.	5" W., 14" ht.	136.9w integrated LED, 3000K, 90CRI, 819 delivered lumens

All fixtures:



Wet location lens included for up/down cylinders.



P550101-020-30 P550101-031-30 P550102-020-30 P550102-031-30

6" Aluminum Cylinders LED

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)
P550103-020-30 P550103-031-30	Antique Bronze Black	Down cylinder with photocell.	6" W., 12" ht.	132.5w integrated LED, 3000K, 90CRI, 953 delivered lumens
P550104-020-30 P550104-031-30	Antique Bronze Black	Up/down cylinder with photocell. Lens cover included.	6" W., 18" ht.	165.2w integrated LED, 3000K, 90CRI, 1582 delivered lumens

All fixtures:



Wet location lens included for up/down cylinders.



P550103-020-30 P550103-031-30 P550104-020-30 P550104-031-30

Round Wet Location Cylinders NEW

These stylish, sleek round cylinders provide an elegant and versatile solution for outdoor lighting needs. Offered in a choice of beautiful Antique Bronze or crisp Black finish. A wet-location rated lens is included, making the fixture ready for wet-location use right out of the box. LED or PAR light source options direct light up and down and offer beautiful, glare-free illumination.

Round Cylinders

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)
P560290-020 P560290-031	Antique Bronze Black	Up/down cylinder	5" W., 7-1/4" ht.	2 PAR30 75w
P560292-020 P560292-031	Antique Bronze Black	Up/down cylinder	6" W., 18" ht.	2 PAR38 250w

All fixtures:



Wet location lens included.



P560290-020



P560290-031



P560292-020



P560292-031

Round LED Cylinders

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)
P560291-020-30 P560291-031-30	Antique Bronze Black	Up/down cylinder	5" W., 7-1/4" ht.	37.2W integrated LED 3000K, 90CRI, 730 delivered lumens
P560293-020-30 P560293-031-30	Antique Bronze Black	Up/down cylinder	6" W., 18" ht..	64W integrated LED 3000K, 90CRI, 1833 delivered lumens

All fixtures:



Wet location lens included.



P560291-020-30



P560291-031-30



P560293-020-30



P560293-031-30

Square Wet Location Cylinders NEW

These stylish, sleek square cylinders provide an elegant and versatile solution for outdoor lighting needs. Offered in a choice of beautiful Antique Bronze or crisp Black finish. A wet-location rated lens is included, making the fixture ready for wet-location use right out of the box. LED or PAR light source options direct light up and down and offer beautiful, glare-free illumination.

Square Cylinders

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)
P560294-020 P560294-031	Antique Bronze Black	Up/down cylinder	6" W., 18" ht.	2 PAR38 250w,

All fixtures:



Wet location lens included.



P560294-020



P560294-031

Square LED Cylinders

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)
P560295-020-30 P560295-031-30	Antique Bronze Black	Up/down cylinder	6"W, 18" ht.	64W integrated LED 3000K, 90CRI, 3641 delivered lumens

All fixtures:



Wet location lens included.



P560295-020-30




P560295-031-30

6" Recessed LED

LED Shallow Housings

For complete fixture, order housing with trim.



New Construction Air-Tight IC & Non-IC with LED Quick Connect

Remodel Air-Tight IC & Non-IC with LED Quick Connect

P871-LED-001
Ceiling opening: 6-3/8" dia.
Plaster frame: 6-5/8" x 9-3/8"
Recessed depth: 5-1/2"
Pryouts: 1/2"

P1871-LED-001
Ceiling opening: 6-3/4" dia.
Recessed depth: 5-5/8"
Pryouts: 1/2"



LED Quick Connector

IC & Non-IC Trims

P800002-028-30 Satin White
7-3/8" dia., 2-3/16" ht.
8w integrated LED,
3000K, 90CRI, 759 lumens.



P800002-028-30

P800021-028-30 Satin White
7-3/8" dia., 3-3/8" ht.
13W integrated LED,
3000K,
90CRI, 1356 lumens



P800021-028-30

P800019-028-CS Satin White
7-3/8" dia., 3-7/16" ht.
8w integrated LED,
2700K, 3000K, 3500K, 4000K, 5000K,
90CRI, 771 lumens (at 3000K).



P800019-028-CS

P800018-028-CS Satin White
7-3/4" dia., 3-15/16" ht.
8w integrated LED,
2700K, 3000K, 3500K, 4000K, 5000K,
90CRI, 750 lumens (at 3000K).



P800018-028-CS




P800018-028-CS
shown adjusted

5" Recessed

Shallow New Construction Housing

For complete fixture, order housing with trim.



P841-ICAT
New Construction Air-Tight IC
Ceiling opening: 5-1/2"
Plaster frame : 10-1/4" x 7"
Recessed depth: 5-3/8"
Pryouts: 1/2"



P841-ICAT HOUSING FEATURES

- Rated for direct contact with insulated ceiling.
- Meets ASTM-E283 air flow requirements.
- Adjustable housing to accommodate ceiling thickness 1/2" to 1-1/2".
- Use with compatible items only.



IC Trims

6-1/2" outside diameter. Can also be used with P851-ICAT.



SHALLOW STEP BAFFLE
P8475-28 Satin White
Damp location listed.
Lamp: PAR30/R30, 50w max.
Compatible with **P851-ICAT** and **P1841-ICAT**.



SHOWER TRIM
P867WL-28 White
Wet location listed when used with an outdoor rated PAR30 lamp. 50w PAR30*



EYEBALL
P876-28 White
75w PAR30

*WL trims require use with outdoor rated PAR lamps

LED Trims

P800002-028-30 Satin White
7-3/8" dia., 2-3/16" ht.
8w integrated LED,
3000K, 90CRI, 759 lumens.



P800002-028-30

P800019-028-CS Satin White
7-3/8" dia., 3-7/16" ht.
8w integrated LED,
2700K, 3000K, 3500K, 4000K, 5000K,
90CRI, 771 lumens (at 3000K).



P800019-028-CS

P800018-028-CS Satin White
7-3/4" dia., 3-15/16" ht.
8w integrated LED,
2700K, 3000K, 3500K, 4000K, 5000K,
90CRI, 750 lumens (at 3000K).



P800018-028-CS



P800018-028-CS
shown adjusted

P800021-028-30 Satin White
7-3/8" dia., 3-3/8" ht.
13W integrated LED,
3000K,
90CRI, 1356 lumens



P800021-028-30

Intrinsic Recessed LED

Elevate any room's design with the Intrinsic Recessed LED collection, offered in smooth or baffle trim design options. The simple, classic design and adjustable mounting options of these light fixtures provide easy installation in a variety of 5-inch and 6-inch recessed housings. The trims are preset to work with 6-inch recessed housings out of the box and are provided with an E26 medium base socket adaptor

Smooth

A smooth polycarbonate trim ring houses an integrated LED light ready to emit general ambient lighting. The non-metallic construction is a dead front design that will not corrode. Torsion spring mounting provides easy installation into most 5-inch and 6-inch recessed housings.

P800002-028-30 Satin White
7-3/8" dia., 2-3/16" ht.
8w integrated LED,
3000K, 90CRI, 759 lumens.



P800002-028-30



COMPATIBLE RECESSED HOUSINGS

P851-ICAT P871-LED-001
P1851-ICAT P1871-LED-001
P1841-ICAT
P841-ICAT

Eyeball

The smooth metal trim provides an elevated look. The adjustable light source can be aimed allowing the trim to be used as a standard downlight, accent light, wall wash or sloped ceiling light. This unique design allows the adjustable light source to remain hidden within the trim, allowing for the cleanest appearance. An integrated ceiling pitch indicator makes adjusting the light to match the ceiling pitch easy. The 5-CCT selectable LED light engine offers flexibility in application, allowing for the choice of 5 different color temperatures: warm, soft, bright, cool or daylight.

P800018-028-CS Satin White
7-3/4" dia., 3-15/16" ht.
8w integrated LED,
2700K, 3000K, 3500K, 4000K, 5000K,
90CRI, 750 lumens (at 3000K).



P800018-028-CS



P800022-028-CS Satin White NEW
5-11/16" dia., 3-3/16 ht.
8W integrated LED,
2700K, 3000K, 3500K, 4000K, 5000K
90CRI, 801 lumens (at 3000K)



P800022-028-CS



6" EYEBALL COMPATIBLE RECESSED HOUSINGS

P851-ICAT P87-AT P86-TG P821-FBFC
P1851-ICAT P87-ATQC P186-TG P871-LED-001
P1841-ICAT P187-TG P821-FB P1871-LED-001
P841-ICAT



Scan with the camera on your smartphone to view video.

Intrinsic Recessed LED

Baffle

The baffle trim reduces glare and provides a familiar and classic look. The 5-CCT selectable LED light engine offers flexibility in application, allowing the choice of 5 different color temperatures: warm, soft, bright, cool or daylight. Select the best lighting color to highlight the décor or to match the function of the space. The friction spring mounting allows for universal installation into most 5-inch and 6-inch recessed housings.

P800019-028-CS Satin White
7-3/8" dia., 3-7/16" ht.
8w integrated LED,
2700K, 3000K, 3500K, 4000K, 5000K,
90CRI, 771 lumens (at 3000K).



P800019-028-CS



High Lumen NEW

Achieve your design vision with our Intrinsic High Lumen LED. The simple, classic design and 5 - 6 in. adjustability of this light fixture can easily be installed into a variety of style applications in both residential and light commercial settings. The baffle trim ring surrounds an integrated LED 1000 lumen light engine ready to emit bright, functional light.

P800021-028-30 Satin White
7-3/8" dia., 3-3/8" ht.
13W integrated LED,
3000K,
90CRI, 1356 lumens





P800021-028-30



COMPATIBLE RECESSED HOUSINGS

P851-ICAT P1841-ICAT P87-AT P187-TG P186-TG P1871-LED-001
P1851-ICAT P841-ICAT P87-ATQC P86-TG P871-LED-001

5 CCT SELECTABLE	2700K
	3000K
	3500K
	4000K
	5000K



6" Eyeball Trim

For insulated or non-insulated ceilings. 7-3/4" outside diameter, except where indicated.

P800020-028 Satin White
Rotates 358, tilts 30 max.
IC & Non-IC:
75w PAR30, 65w BR30



P800020-028

**COMPATIBLE
RECESSED HOUSINGS**
P87-AT
P87-ATQC
P187-TG
P821-FBFC
P821-FB

Intrinsic Surface Mount LED

Eyeball

The Intrinsic Surface Mount Eyeball LED represents the ultimate in design flexibility and ease of installation. Installation to a standard height junction box is made easy with the intuitive snap spring design. Suitable for residential and commercial needs, its clean profile elegantly accents the ceiling while the light can be adjusted to offer standard downlight, accent light, wall washer or sloped ceiling light. An integrated ceiling pitch indicator makes adjusting the light to match the ceiling pitch easy.

LED FEATURES

- Damp location listed.
- 120v input voltage.
- 60 Lumens per watt.
- Flicker-free dimming with many Triac and ELV dimmers.
- 50,000 hour life.

P810029-020-030 Antique Bronze
P810029-028-030 Satin White
7-1/4" dia., 1-1/2" ht.
15.8w integrated LED, 3000K,
90CRI, 1000 lumens.



P810029-020-30



P810029-028-30



P810029-020-30
shown adjusted



CCT Selectable

Achieve your design vision with our 5-CCT selectable 7.5" Intrinsic Surface Mount LED. The simple, classic design of this light fixture can easily be installed into a variety of style applications in both residential and light commercial settings. The smooth trim ring surrounds an integrated 5-CCT LED light fixture ready to emit ambient lighting wherever it calls home in your design plan.

P810035-028-CS Satin White
7-1/2" dia, 1-5/16" ht.
15.5w integrated LED, 2700K,
3000K, 3500K, 4000K and 5000K
90 CRI, 1110 lumens.



P810035-028-CS

5 CCT SELECTABLE	2700K
	3000K
	3500K
	4000K
	5000K

Everlume™ LED Linear Panel

The Everlume™ Linear Panel LED is a modern take on a classic rectangular wrap frame. Its clean low-profile design has a frosted polycarbonate diffuser lit by LEDs along the perimeter of the fixture. Light is diffused through a light guide, providing even illumination without dark spots, shadow or glare. Hardware and fasteners are not visible after installation, providing a clean appearance. The fixture can be mounted to off-centered junction boxes making aligning multiple fixtures on center easy. This product is a great addition to laundry rooms, kitchens, walk in closets, garages and basements.

24" LED LINEAR PANEL
P810032-028-30 Satin White
23-3/4" L., 11-15/16" W., 1-1/4" ht.
21w integrated LED, 3000K,
90CRI, 1587 lumens.

48" LED LINEAR PANEL
P810033-028-30 Satin White
47-3/4" L., 11-15/16" W., 1-1/4" ht.
43w integrated LED, 3000K,
90CRI, 3181 lumens.

LED FEATURES

- Flicker-free dimming with many Triac and ELV dimmers.
- 120v input voltage.
- 50,000 hour life.



All fixtures:



Everlume™ LED Vanity

FINISHES

- Brushed Nickel - 009
- Satin White - 028

ALSO IN
Bath
See page 130.



P810032-028-30



P810033-028-30



P300305-009-CS




P300305-028-CS



P300306-009-CS

Linear Undercabinet LED

The Hide-a-Lite Linear Undercabinet LED has an elegant design combined with energy efficient LED light, providing the ideal solution for residential and light commercial applications. The clean design of its aluminum housing features a lens that optimizes light distribution, ensuring for proper illumination of the workspace below. The 5-CCT selectable LED light engine offers flexibility in application, allowing the choice of 5 different color temperatures: Warm, Soft, Bright, Cool, Daylight, allowing for the best lighting color to fulfill the design intent of the space. An access plate and quick connect wire connectors make installation easy. Fixture is direct wired. Two armored cable fittings are also included, an on-off switch on the front allows for easy task light illumination.



P700026-028-CS





P700027-028-CS



P700028-028-CS

5 CCT SELECTABLE

- 2700K
- 3000K
- 3500K
- 4000K
- 5000K



9" LED UNDERCABINET

P700024-028-CS White
9" L., 3-1/4" W., 1-1/8" ht.
One 4w integrated LED,
2700K, 3000K, 3500K, 4000K,
5000K, 90CRI, 228 delivered
lumens (at 3000K).



CCT selector switch



Access plate



Quick connectors

12" LED UNDERCABINET

P700025-028-CS White
11-1/2" L., 3-1/4" W., 1-1/8" ht.
One 4.5w integrated LED,
2700K, 3000K, 3500K, 4000K,
5000K, 90CRI, 299 delivered
lumens (at 3000K).

18" LED UNDERCABINET

P700026-028-CS White
17-1/2" L., 3-1/4" W., 1-1/8" ht.
One 6.5w integrated LED,
2700K, 3000K, 3500K, 4000K,
5000K, 90CRI, 457 delivered
lumens (at 3000K).

24" LED UNDERCABINET

P700027-028-CS White
23-1/2" L., 3-1/4" W., 1-1/8" ht.
One 8.5w integrated LED,
2700K, 3000K, 3500K, 4000K,
5000K, 90CRI, 608 delivered
lumens (at 3000K).

36" LED UNDERCABINET

P700028-028-CS White
35-1/2" L., 3-1/4" W., 1-1/8" ht.
One 11.5w integrated LED,
2700K, 3000K, 3500K, 4000K,
5000K, 90CRI, 859 delivered
lumens (at 3000K).

All fixtures:



Product Index

P1000

P1871.....200

P3000

P300045.....142
P300046.....142
P300047.....142
P300048.....142
P300049.....150
P300050.....150
P300051.....150
P300052.....150
P300158.....166
P300159.....166
P300160.....166
P300161.....166
P300189.....157
P300190.....157
P300191.....157
P300295.....154
P300296.....154
P300297.....155
P300298.....155
P300299.....129
P300300.....129
P300304.....128
P300305.....128
P300306.....128
P300311.....126
P300312.....126
P300313.....126
P300314.....164
P300315.....164
P300316.....165
P300317.....165
P300319.....156
P300320.....152
P300321.....152
P300322.....152, 153
P300323.....153
P300327.....167
P300328.....167
P300329.....167
P300330.....167
P300331.....127
P300332.....127
P300333.....127
P300341.....162
P300342.....162
P300343.....163
P300344.....163
P300345.....140
P300346.....140
P300347.....140, 141
P300348.....141
P300349.....146
P300350.....147
P300351.....147
P300356.....132
P300357.....132
P300358.....133
P300359.....133
P300360.....134

P300361.....134
P300362.....135
P300363.....135
P300368.....130
P300369.....130
P300370.....131
P300371.....131
P300372.....168
P300373.....144
P300374.....144
P300375.....145
P300376.....145
P300377.....158
P300378.....158
P300379.....159
P300380.....159
P300381.....138
P300382.....138
P300383.....139
P300384.....139
P300385.....169
P350022.....63, 65
P350039.....63, 65
P350046.....117
P350107.....81
P350129.....122
P350130.....122
P350167.....122
P350169.....113
P350170.....123
P350178.....123
P350179.....123
P350181.....57
P350183.....53
P350195.....113
P350197.....49, 51
P350198.....112
P350199.....112
P350200.....117
P350205.....106
P350209.....97
P350210.....29, 31
P350211.....67
P350213.....121
P350214.....118
P350217.....116
P350218.....120
P350219.....114
P350220.....116

P4000

P400047.....63, 65
P400048.....63, 65
P400118.....81
P400119.....81
P400202.....77, 79
P400228.....77, 79
P400235.....57
P400243.....57
P400250.....69, 71
P400251.....69, 71
P400252.....69, 71
P400253.....49, 51
P400254.....49, 51

P400255.....91
P400257.....99
P400260.....89
P400261.....88
P400262.....93, 95
P400263.....93, 95
P400264.....97
P400267.....67
P400269.....47
P400270.....40
P400274.....83, 85
P400275.....83, 85
P400276.....83, 85
P400286.....72, 74
P400287.....73, 75
P400291.....55
P400292.....55
P400293.....42
P400294.....43
P400295.....33, 36, 38
P400296.....33, 36, 38
P400297.....33, 36, 38
P400300.....34, 37, 39
P4217.....105

P5000

P500041.....63, 65
P500125.....81
P500126.....81
P500178.....63, 65
P500278.....59
P500279.....59
P500296.....67
P500302.....77, 79
P500303.....77, 79
P500307.....53
P500308.....53
P500309.....107
P500310.....107
P500311.....107
P500313.....106
P500314.....69, 71
P500315.....69, 71
P500316.....77, 79
P500317.....49, 51
P500318.....91
P500319.....98
P500320.....98
P500321.....93, 95
P500322.....93, 95
P500324.....110
P500325.....110
P500328.....47
P500329.....106
P500333.....83, 85
P500341.....73, 75
P500342.....73, 75
P500343.....103
P500344.....103
P500355.....196
P500356.....196
P500358.....104
P500359.....104
P500360.....33, 37, 39

P500361.....33, 37, 39
P500363.....44
P500365.....105
P500366.....99
P500367.....108
P500368.....108
P500369.....100
P500370.....100
P500371.....34, 37, 39
P500372.....101
P500373.....101
P500415.....29, 31
P500416.....29, 31
P540033.....178, 179
P540064.....177
P540090.....186
P540093.....190
P540094.....187
P540095.....184
P540097.....188
P540099.....181
P540120.....176
P540292.....185
P550050.....178, 179
P550064.....117
P550069.....193
P550083.....172
P550084.....173
P550089.....170
P550093.....189
P550094.....189
P550097.....188
P550099.....196
P550100.....196
P550101.....197
P550102.....197
P550103.....197
P550104.....197
P550109.....187
P550110.....185
P550111.....171
P550112.....194
P550113.....194
P550114.....194
P550115.....194
P550116.....174
P550120.....176
P550122.....181
P550292.....185
P560087.....178, 179
P560174.....177
P560175.....177
P560176.....177
P560255.....185
P560256.....185
P560257.....185
P560259.....195
P560260.....195
P560261.....183
P560262.....183
P560263.....189
P560264.....184
P560265.....184
P560266.....184
P560267.....182

See Yourself Here

Every home and every family has a story that's all their own. In this issue, we introduce you to the many ways Progress Lighting can bring that story to life.



PROGRESS LIGHTING

701 Millennium Boulevard
Greenville, SC 29607

www.progresslighting.com