



CEILING FAN CATALOG 2021





See Yourself Here.

Lighting helps tell a story, whether it's setting the mood or enjoying a special moment. These occasions are meaningful, expressive, and shared with those we care about most. Let Progress be your guide in illuminating these spaces into special places.

Table of Contents

Fan Inspiration 10

Our ceiling fans do more than cool a room - they combine beautiful design with premium performance. Choose from fans that make a statement across a variety of design trends, from simple to spectacular.

Indoor Fans 22



Outdoor Fans 154



Accessories 186

Light Kits 190

Downrods 196

Remotes 197

Cross Reference Chart 198

Blade Finishes 202


Be Inspired

-  @ProgressLtg
-  @ProgressLtg
-  @ProgressLighting
-  @ProgressLtg
-  Progress Lighting
-  Progress-Lighting
- #ProgressLightingMoments





Indoor Ceiling Fans




Indoor Ceiling Fans




Indoor Ceiling Fans

FARRIS Oil Rubbed Bronze p.66 	FRESNO Antique Bronze p.114 	FRESNO Brushed Nickel p.115 	FRESNO White p.115 	GAZE Antique Bronze p.71 
GAZE Black p.71 	GAZE Brushed Nickel p.71 	GAZE Polished Chrome p.70 	GLANDON Antique Nickel p.84 	GLANDON Gilded Iron p.85 
GLENFALLS Brushed Nickel p.101 	GLENFALLS Matte White p.100 	GLENFALLS Matte Black p.101 	GRACEFUL Matte Black p.105 	GRACEFUL Brushed Nickel p.104 
GRACEFUL Polished Chrome p.105 	GREER Antique Nickel p.88 	GREER Gilded Iron p.89 	GULLIVER Galvanized p.34 	GULLIVER Graphite p.35 
GUST Antique Bronze p.109 	GUST Brushed Nickel p.108 	GUST Graphite p.109 	HARRANVALE Antique Bronze p.99 	HARRANVALE Graphite p.98 


Indoor Ceiling Fans

HARRANVALE White p.99 	HOLLAND Black p.77 	HOLLAND Brushed Nickel p.76 	HOLLAND Oil Rubbed Bronze p.77 	HUFF Black p.57 
HUFF Brushed Nickel p.56 	HUFF Matte White p.57 	KAYSVILLE Antique Nickel p.48 	KAYSVILLE Graphite p.49 	KUDOS Antique Bronze p.113 
KUDOS Brushed Nickel p.112 	KUDOS Polished Chrome p.113 	LINDALE Antique Nickel p.151 	LINDALE Architectural Bronze p.150 	LINDALE Matte White p.151 
LORING Galvanized p.37 	LORING Matte Black p.36 	OLSON Brushed Nickel p.107 	OLSON Graphite p.106 	ORIOLE Architectural Bronze p.78 
ORIOLE Black p.79 	ORIOLE Brushed Nickel p.79 	ROYER Antique Nickel p.83 	ROYER Forged Black p.82 	RYNE Matte White p.27 



























Indoor Ceiling Fans




























Indoor Ceiling Fans



Indoor Ceiling Fans

VERNAL Matte Black p.25	VERNAL Painted Nickel p.25	VERNAL Koa Woodgrain p.24	VOX FAN Antique Bronze p.149	VOX FAN Brushed Nickel p.148
				
VOX FAN White p.149	WILLACY Matte Black p.29	WILLACY Painted Nickel p.28	42" BUILDER FAN Antique Bronze p.139	42" BUILDER FAN Brushed Nickel p.139
				
42" BUILDER FAN White p.139	52" BUILDER FAN Brushed Nickel p.141	52" BUILDER FAN Polished Chrome p.141	52" BUILDER FAN Antique Bronze p.141	52" BUILDER FAN Graphite p.141
				
52" BUILDER FAN White p.141	52" BUILDER FAN WITH LIGHT KIT Architectural Bronze p.140	52" BUILDER FAN WITH LIGHT KIT Brushed Nickel p.140	52" BUILDER FAN WITH LIGHT KIT White p.140	42" HUGGER FAN Brushed Nickel p.153
				
42" HUGGER FAN White p.153	52" HUGGER FAN Brushed Nickel p.152	52" HUGGER FAN White p.152	52" PERFORMANCE Antique Bronze p.138	52" PERFORMANCE Brushed Nickel p.138 White p.138
				 

Outdoor Ceiling Fans

ALBIN Architectural Bronze p.178	ALBIN Matte Black p.179	ALBIN Matte White p.179	ALLERON Antique Nickel p.51	ALLERON Flat Black p.50
				
ALFRESCO Architectural Bronze p.172	ALFRESCO Blistered Iron p.173	ARLO Architectural Bronze p.63	ARLO Black p.63	ARLO Brushed Nickel p.62
				
BELVA Matte Black p.32	BELVA Cottage White p.33	BIXBY Black p.64	BIXBY White p.65	BRIARWOOD Antique Bronze p.30
				
BRIARWOOD Galvanized p.31	BRIARWOOD Graphite p.31	BRIARWOOD Matte Black p.31	DECORATIVE PATIO FAN Antique Bronze p.182	EDISTO Antique Nickel p.165
				
EDISTO Architectural Bronze p.165	EDISTO Forged Black p.164	EDWIDGE Matte White p.163	EDWIDGE Matte Black p.163	EDWIDGE Painted Nickel p.162
				

Outdoor Ceiling Fans

 Damp Location Listed

GULLIVER Galvanized p.34 **GULLIVER** Graphite p.35 **HOLLAND** Brushed Nickel p.76 **HOLLAND** Black p.77 **HOLLAND** Oil Rubbed Bronze p.77



HUFF Black p.57 **HUFF** Brushed Nickel p.56 **HUFF** Matte White p.57 **KAYSVILLE** Antique Nickel p.48 **KAYSVILLE** Graphite p.49



MIDVALE Matte White p.159 **MIDVALE** Galvanized p.158 **MIDVALE** Blistered Iron p.159 **SANFORD** Architectural Bronze p.38 **SANFORD** Brushed Nickel p.39



RUDDER Architectural Bronze p.161 **RUDDER** Matte Black p.161 **RUDDER** Matte White p.160 **RYNE** Matte White p.27 **RYNE** Matte Black p.26



RYNE Koa Woodgrain p.27 **VAST** Brushed Nickel p.59 **VAST** Antique Bronze p.59 **VAST** White p.59 **VAST** Matte Black p.58




Outdoor Ceiling Fans

 Damp Location Listed

VERNAL Matte Black p.25 **VERNAL** Painted Nickel p.25 **VERNAL** Koa Woodgrain p.24 **WHIRL** Antique Bronze p.169 **WHIRL** Antique Nickel p.168




WHIRL Forged Black p.169 **WILLACY** Matte Black p.29 **WILLACY** Painted Nickel p.28



 Wet Location Listed

LAKEHURST Antique Bronze p.180 **LAKEHURST** Forged Black p.181 **LAKEHURST** White p.181 **MONTAGUE** Antique Bronze p.177 **MONTAGUE** Forged Black p.176



MONTAGUE White p.177 **SMYRNA** Antique Bronze p.174 **SMYRNA** Forged Black p.175 **52" PATIO FAN** Antique Bronze p.184 **52" PATIO FAN** Forged Black p.184



52" PATIO FAN Galvanized p.184 **52" PATIO FAN** White p.184 **54" PATIO FAN** Antique Bronze p.184





Fan Inspiration

Ceiling Fans can serve as a statement piece or even the focal point of a room.

Today's ceiling fans incorporate beautiful features, such as hand carved blades, sleek finishes and natural elements to appeal to a variety of different design trends.

At Progress Lighting, we strive to incorporate this shift in our ceiling fan designs and are eager to present an expanded offering in this catalog.

The Perfect Fan in 5 Steps



Scan with the camera on your smartphone to take the style quiz at www.progresslighting.com/styles

Ceiling Fan Buyer's Guide

Ceiling fans are practical and efficient solutions for creating comfortable and welcoming living areas. With many styles, functions and features to choose from, narrowing down the choices can be a challenge. Here we present five tips for selecting the perfect ceiling fan for your home.

1 Settle on Style

Choose a style that complements your décor. Consider fan shape, blade features and finish to help you meet your room's design needs. Choose from Traditional, Transitional, Coastal or Farmhouse styles. The possibilities are vast!



Modernly Minimal

See full trendboard page 160



Modern + Edgy

See full trendboard page 24



Easy, Breezy, Coastal

See full trendboard page 132

Indoor



Featuring Glandon

Outdoor




Featuring Edwidge

2 Explore Indoor vs. Outdoor Uses

Fans provide a breezy setting for reading a book or catching up with friends, making them ideal for outdoor rooms. However, it's important to consider the certifications on the fan depending on the use. For high humidity areas, choose a UL-Listed fan for Damp Locations and for spaces that will be exposed to weather, choose a UL-Listed fan for Wet Locations. For interior use in dry spaces with minimal condensation, select a UL-Listed fan for Dry Locations. See testing listings defined on page 17.

The Perfect Fan in 5 Steps *continued...*



3 Get Your Height Right

You want to allow at least 7 feet (84 in.) from the floor to the bottom of the fan, with 8 or 9 feet being the ideal above-floor placement. For lower ceilings, consider a ceiling fan with a low profile to avoid disturbing inhabitants. Most ceiling fans come equipped with a down rod to help you adjust to the correct height.

4 Size It To Your Space

Size is really important when selecting your ceiling fan. If a fan is too large, it can overwhelm the space. On the flip side, if the fan is too small, the airflow may be inadequate for that area.

Room Size (in square feet)	Fan Size (in inches)
0 - 75	0 - 36
76 - 144	36 - 42
145 - 225	42 - 50
226 - 360	50 - 54
361 - 499	54 - 70
500+	70+

The Perfect Fan in 5 Steps *continued...*

5 Choose Your Features

There are many different features to choose from when browsing ceiling fans.

Blade Finish Options

Multiple blade finish options to coordinate with your home decor.

Example blade options for P2568-0930K:

- Silver
- American Walnut



Reversible Motor

Typically, ceiling fans are used to help cool you down and keep the air flowing with a counter-clockwise blade direction. However, fans can also keep you warm when the direction of the blades is reversed. Select a fan with reversible motor for the option to circulate cool or warm air. Most ceiling fans have a small switch located either on the motor housing or the switch cup.



LED

Consider an LED or Energy Star rated fixture to save energy.



P2568-1530



Light Kit

For a layered lighting effect, install a ceiling fan with a pre-installed light kit to complement your existing fixtures.



Scan for "The Perfect Fan in 5 Steps" with Steve Register or visit [youtube.com/user/ProgressLtg](https://www.youtube.com/user/ProgressLtg)

[WWW.PROGRESSLIGHTING.COM](http://www.progresslighting.com)

P2662-01

Remote Control with Full Range Dimming

Full range dimming and hand-held remote control capabilities are available to offer an added convenience in controlling a room's environment.

Control from Anywhere with Wifi



P2667-031

Wi-Fi enabled



Easily control your fan with your smartphone, tablet, voice or hand-held remote.

Compatible with Any Progress AC Motor

Breeze Mode on App

Full Range Dimming Control

On/Off Function for Fan and Light Kit

Control from your pocket




For more details, visit www.progresslighting.com/ceilingfans

Featuring Gaze

LED Light Kits

Save Money and Energy

When you select a high-quality LED fixture, you can expect a significant return on investment from an energy conservation standpoint. Here are some of the energy saving benefits of LEDs from Progress Lighting:



Whirl
P2574-8130K
shown with Driftwood blades

Features



LED sources use at least 75% less energy than incandescent lighting, allowing homeowners to save on operating expenses.



LEDs last 35 to 50 times longer than incandescent sources and approximately 2 to 5 times longer than fluorescent lighting. Meaning, less bulb maintenance!



LEDs do not use power when they are turned off. According to MSN Real Estate, LED lights can result in an annual bill as low as \$26.



LEDs do not produce heat like traditional sources, reducing cooling costs. Traditional incandescent bulbs waste 98% of the energy they consume on heat.

Find Your Rating

Indoor, Damp and Wet Location

All ceiling fans sold in the United States have been tested and rated by either Underwriters Laboratories (UL) or Intertek (ETL), each an independent product safety certification organization. It's important to pay attention to the rated listing when purchasing a ceiling fan as it will tell you what location the fan was designed for. There are three location options: dry, damp and wet.



Image: Dostie Homes



Dry Location

Please note indoor only (dry location) fans should only be used indoors. Even if an outdoor area or screened-in porch is covered, the motor and the blades can be affected when exposed to humidity. You can, however, “bring the outdoors inside” – as using outdoor ceiling fans are perfectly acceptable to use in interior spaces.

Damp Location

If you are selecting a ceiling fan for a space that is outdoors and under a roof, i.e. any covered porches; you should select either a damp rated or wet listed fan. Damp location fans may also be used indoors.





Image: Arthur Rutenberg Homes



Wet Location

If the fan comes directly into contact with water, you'll need to ensure that the ceiling fan has a “wet” listing. Ceiling fans designed for damp or wet locations feature elements, such as moisture-resistant motors and all weather blades. Wet location fans may also be used indoors.




Indoor Ceiling Fans

*Experience the versatility
ceiling fans provide*



Scan with your camera on
your smartphone or visit
www.progresslighting.com/ceilingfans

Arlo
P250026-009-30



Retro 1

2 Unique Shapes

3 Glass Accents



Steve Register
Product Manager,
Ceiling Fans

Modern + Edgy

with Steve

Quirky and functional, this style's flair comes from its modern, yet retro, juxtaposition. Mid-Century Modern style furniture adds unique shapes and pops of color to a room. Designers look for statement pieces to complete the look. This style is gravitating toward a cleaner, more minimalistic look through the incorporation of a neutral palette and softer accent colors. Mid-Century

Modern homes are largely characterized by the use of wood textures to create a sense of connection to nature and the outdoors.



Shop this style at
www.progresslighting.com/mid-century-modern



Vernal

P250059-179-30
shown with Koa Woodgrain blades

FINISHES

- Matte Black - 031
- Painted Nickel - 152
- Koa Woodgrain - 179



Wifi included

Vernal refreshes a room's decor with elegant curves and an expansive 60-inch, five-blade span for the ultimate in design-savvy comfort. Vernal includes Wi-Fi smart control: once installed, Vernal can be controlled by a voice assistant, tablet or smart phone. Finished in Koa Woodgrain, Matte Black or Painted Nickel, Vernal is designed to complement New Traditional and Transitional interiors.

Integrated Smart Control

Elegant Curves

Dimmable LED Light



P250059-031-30
shown with Matte Black blades



P250059-152-30
shown with Painted Nickel blades



P250059-179-30
shown with Koa Woodgrain blades
with Architectural Bronze accents

Vernal

P250059-031-30 Matte Black



Matte Black

P250059-152-30 Painted Nickel



Painted Nickel

P250059-179-30 Koa Woodgrain



Koa Woodgrain

ENERGY INFORMATION AT HIGH SPEED

Airflow	6,810 cubic feet per minute
Electricity Use	34 watts (excludes lights)
DOE Weighted CFM/W	242 CFM/W

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- ABS blades
- Opal shatterproof shade
- Wi-Fi enabled
- Remote control with batteries is included

SIZE

60" dia., 14-1/4" ht.
80" lead wires.

LAMP

18w LED Module, 3000K,
90 CRI, 1600 source lumens,
dimmable.



Full Function Remote Control Included
Six-speed fan operation
Full-range dimming for light
Reverse direction control



Ryne

P250060-031-30
shown with Matte Black blades

FINISHES

- Matte White- 028
- Matte Black - 031
- Koa Woodgrain - 179



Wifi compatible

The 52-inch Ryne fan is modern in appeal, with beautifully flowing blades that join in the middle to create a minimalistic housing. Ryne is smart control adaptable with the P2673 Wi-Fi Module: once installed, Ryne can be controlled by a voice assistant, tablet or smart phone. Ryne's aerodynamic design and Koa Woodgrain, Matte White or Matte Black finish perfectly suits New Traditional and Transitional interiors.

Modern Appeal

Aerodynamic Design

Dimmable LED Light



P250060-028-30
shown with Matte White blades



P250060-031-30
shown with Matte Black blades



P250060-179-30
shown with Koa Woodgrain blades
with Architectural Bronze accents

Ryne

P250060-028-30 Matte White



P250060-031-30 Matte Black



P250060-179-30 Koa Woodgrain



P2673-01

**DC FAN WI-FI MODULE
P2673-01**

Add the Wi-Fi module to your Ryne ceiling fan for control at your fingertips. You can easily control your fan with a hand-held remote; or a smart phone, tablet, voice assistant (Amazon Alexa and Google Home) via the Smart By Bond app.

ENERGY INFORMATION AT HIGH SPEED

Airflow	5,802 cubic feet per minute
Electricity Use	33 watts (excludes lights)
DOE Weighted CFM/W	204 CFM/W



Full Function Remote Control Included
Six-speed fan operation
Full-range dimming for light
Reverse direction control

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- ABS blades
- Opal shatterproof shade
- Remote control with batteries is included
- Add a P2673-01 Wi-Fi module to convert to a smart fan

SIZE

52" dia., 13-1/2" ht.
80" lead wires.

LAMP

18w LED Module, 3000K, 90 CRI,
1600 source lumens, dimmable.



Willacy

P250063-152
shown with Painted Nickel blades

FINISHES


- Matte Black - 031
- Painted Nickel - 152



Wifi included

Willacy is striking in design, inspired by flowing ribbons that swirl around a gleaming center hub to create a gentle breeze. Willacy includes Wi-Fi smart control: once installed, the fan can be controlled by a voice assistant, tablet or smart phone. Willacy features all weather hand finished ABS blades making it ideal for indoor or outdoor use.

Striking Design



Ribbon-Like Blades

For Indoor & Outdoor Use

Willacy

P250063-031 Matte Black



Matte Black

P250063-152 Painted Nickel



Painted Nickel



P250063-031
shown with Matte Black blades



P250063-152
shown with Painted Nickel blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	4,544 cubic feet per minute
Electricity Use	14 watts (excludes lights)
DOE Weighted CFM/W	318 CFM/W

FEATURES

- Limited Lifetime Warranty
- DC Motor
- ABS blades
- Wi-Fi enabled
- Remote control with batteries is included

SIZE

48" dia., 14-1/2" ht.
12" lead wires.



Full Function Remote Control Included
Six-speed fan operation
Reverse direction control

Briarwood

FINISHES

- Antique Bronze - 020
- Galvanized - 141
- Graphite - 143
- Matte Black - 31M

P250067-020-WB
with rich oak faux wood accent finish

The Briarwood ceiling fan brings vintage farmhouse detailing into the present day with a classic cross-brace pattern enclosing vintage-style bulbs and a trio of fan blades within its airy, open-frame design. Faux-painted wood accentuates Briarwood's simple geometric form, adding the perfect touch of country character to a variety of room settings.

Farmhouse Detailing

Open Frame Design

Geometric Form



Briarwood

P250067-020-WB Antique Bronze



Antique Bronze

P250067-141-WB Galvanized



Galvanized

P250067-143-WB Graphite



Graphite

P250067-31M-WB Matte Black



Matte Black



P250067-020-WB
accent color
rich oak faux wood



P250067-143-WB
accent color
white washed faux wood



P250067-141-WB
accent color
bleached oak faux wood



P250067-31M-WB
accent color
cerused black oak

ENERGY INFORMATION AT HIGH SPEED

Airflow	1,145 cubic feet per minute
Electricity Use	31 watts (excludes lights)
DOE Weighted CFM/W	37 CFM/W



Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Add a P2630-30 or P2613-30 wall control or P2662-01 hand-held remote control
- Add the P2667-031 Wi-Fi remote

SIZE

22" dia., 17" ht.
45" lead wires.

LAMP

Four medium base 2200K 5.5w vintage LED lamps included. 500 lumens/lamp, 80 CRI, dimmable. 5.5w LED max/socket.



Belva

P250068-31M-WB
with mocha colored wicker'

FINISHES

- Matte Black - 31M
- Cottage White - 151

The Belva ceiling fan offers an organic global feel and coastal charm. A lattice-like design graces the natural wicker frame, and a lovely Cottage White and Mocha finishes gives charm and depth. A trio of fan blades and vintage-style bulbs within the frame's woven structure moves air comfortably while casting a beautifully diffused glow.

Organic Feel

Natural Woven Frame

Coastal Charm



P250068-31M-WB
with mocha colored wicker'

Belva

P250068-31M-WB Matte Black



Matte Black

P250068-151-WB Cottage White



Cottage White



P250068-151-WB
with whitewashed wicker

ENERGY INFORMATION AT HIGH SPEED

Airflow	1,125 cubic feet per minute
Electricity Use	37 watts (excludes lights)
DOE Weighted CFM/W	37 CFM/W

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Add a P2630-30 or P2613-30 wall control
- Add the P2667-031 Wi-Fi remote

SIZE

25-1/4" dia., 17-7/8" ht.
45" lead wires.

LAMP

Four medium base 2200K 5.5w vintage LED lamps included. 500 lumens/lamp, 80 CRI, dimmable. 5.5w LED max/socket.



Remote Control Included
Three-speed fan operation
Full-range dimming for light



Gulliver

P250012-141-22
shown with Antique White Wood

FINISHES

- Galvanized - 141
- Graphite - 143

Three circular bands wrap together to create an open design. Non-metallic fan blades enclosed within a stylish cage design gives the rustic charm of a pendant combined with the functionality of a ceiling fan. Dual toned frame color combinations of Galvanized with antique white accents or Graphite with weathered gray accents. A hand painted wood grained texture complements rustic and modern farmhouse home decor, as well as urban industrial and coastal interior settings.

Urban Industrial Design



Rustic Charm

Hand-Painted Wood



P250012-141-22
shown with Antique White Wood



P250012-143-22
shown with Gray Wood

Gulliver

P250012-141-22 Galvanized



Antique White Wood

P250012-143-22 Graphite



Gray Wood

ENERGY INFORMATION AT HIGH SPEED

Airflow	1,297 cubic feet per minute
Electricity Use	39 watts (excludes lights)
Airflow Efficiency	33 cubic feet per minute per watt



Three-Speed Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-18.5")
- AC Motor
- Reversible Motor
- Rust-proof non-metallic blades
- Damp Location Rated
- Remote control with batteries is included
- Add the P2667-031 Wi-Fi remote

SIZE

23" dia., 18-1/8" ht.
42" lead wires.

LAMP

Three medium base 2200K 5.5w vintage LED lamps included. 500 lumens/ lamp, 80 CRI, dimmable. 5.5w LED max/socket.



Loring

FINISHES

- Black- 031
- Galvanized - 141

Outfitted with stylish mixed metal elements, the Loring collection shows off an industrial-inspired, open-cage design. Four plywood blades and a handy remote control are ready to help you and your family stay comfortable and relaxed all year round.

P250006-031
shown with Matte Black blades

Open-Cage Design



Industrial Inspired

Mixed-Metal Elements



P250006-031
shown with Gold accent
and Distressed Ebony blades



P250006-141
shown with Matte Black accent
and White Barnwood blades

Loring

P250006-031 Black

- Matte Black
- Distressed Ebony

P250006-141 Galvanized

- White Barnwood
- Driftwood

ENERGY INFORMATION AT HIGH SPEED

Airflow	1,766 cubic feet per minute
Electricity Use	43 watts (excludes lights)
DOE Weighted CFM/W	44 CFM/W



Three Speed Remote Control Included
Three-speed fan operation

FEATURES

- Limited lifetime warranty
- Close-to-ceiling installation
- AC Motor
- Reversible plywood blades
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

SIZE

33" dia., 15-1/4" ht.
12" lead wires.



Sanford

FINISHES

- Brushed Nickel - 009
- Architectural Bronze - 129

P2594-12930K

Sanford delivers ultra powerful air movement and energy efficient illumination packaged in a modern design. Ideal for both interior and outdoor settings, this "fandelier" adds a contemporary style to porches, foyers, bath and vanity areas providing a wide range of applications. Sanford includes an integrated 23W LED module, offering both form and function with energy and cost-savings benefits. A three-speed remote control is included.

Indoor or Outdoor Use

Contemporary Style



Powerful Air Movement

Sanford

P2594-0930K Brushed Nickel

P2594-12930K Architectural Bronze



P2594-0930K



P2594-12930K

ENERGY INFORMATION AT HIGH SPEED

Airflow	1,008 cubic feet per minute
Electricity Use	37 watts (excludes lights)
DOE Weighted CFM/W	27 CFM/W



Three-Speed Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-18.5")
- AC Motor
- Metal blades
- Damp Location Rated
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control
- Add the P2667-031 Wi-Fi remote

SIZE

22-7/8" dia., 17-3/4" ht.
 80" lead wires.

LAMP

26w LED module, 3000K, 90 CRI,
 2638 source lumens, dimmable.



An Industrial Edge



A simple but edgy vibe takes its cue from industrial origins.

1

Try a fandelier style ceiling fan like Sanford that delivers ultra-powerful air movement packaged in a vintage design.

2

Toss your table lamp and try two low-hanging pendants over the nightstand instead.

3

Finish the room with organic elements of wood and worn textures that celebrate the signature look of the industrial setting.

52" Springer

P250065-081


FINISHES

- Antique Nickel - 081
- Architectural Bronze - 129
- Matte Black - 31M



Wifi compatible

The sweeping style of the Springer fan is expressed in a 52" size that is ideal for boosting airflow in smaller spaces. The 12-blade ceiling fan has a rustic flair inspired by the form and function of a windmill. Springer is WiFi ready offering more versatility in control options. It is a DC motor fan and can accept the Springer light kit (sold separately). Springer offers the perfect look for Farmhouse, Industrial and Transitional settings



P250065-081



P250065-129



P250065-31M

52" Springer

P250065-081 Antique Nickel



White Barnwood

P250065-129 Architectural Bronze



Distressed Walnut

P250065-31M Matte Black



Rustic Charcoal

SPRINGER LIGHT KIT

- P260000-081-WB** Antique Nickel
- P260000-129-WB** Architectural Bronze
- P260000-31M-WB** Matte Black

Two medium base 2700K 7w vintage LED lamps included. 600 lumens/lamp, 90 CRI, dimmable. 7w LED max/socket.



**This light kit is ONLY compatible with the 52" Springer fan (P250065).*

ENERGY INFORMATION AT HIGH SPEED

Airflow	6296 cubic feet per minute
Electricity Use	30 watts (excludes lights)
DOE Weighted CFM/W	245 CFM/W

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- Add a P2673-01 module to convert your fan to Wifi smart

SIZE

52" dia., 17-3/8" ht.
80" lead wires.



Full Function Remote Control Included
Six-speed fan operation
Reverse direction control



Modern Traditional is the perfect blend of new and old.

1

Use a contemporary tonal color palette of whites and grays accented with rustic, warm wood touches to make the space feel inviting.

2

Complement the minimalist room with the rugged, statement-making style of the Springer ceiling fan.

3

Amplify modern style with the Milner wall sconce's trendy matte black finish and clear glass shades against a white-washed brick accent wall.



Springer

- FINISHES**
- Antique Nickel - 081
 - Architectural Bronze - 129
 - Matte Black - 31M

P250000-31M
shown with Rustic Charcoal blades



Dual Mount Canopy

Rustic Flair

Windmill Inspired

Springer

- P250000-081** Antique Nickel
 - White Barnwood
- P250000-129** Architectural Bronze
 - Distressed Walnut
- P250000-31M** Matte Black
 - Rustic Charcoal



P250000-081
shown with White Barnwood blades



P250000-129
shown with Distressed Walnut blades



Available in June 2021
P250000-31M
shown with Rustic Charcoal blades



Scan with the camera on your smartphone for the Springer installation video.


ENERGY INFORMATION AT HIGH SPEED

Airflow	6,377 cubic feet per minute
Electricity Use	33 watts (excludes lights)
DOE Weighted CFM/W	206 CFM/W

- FEATURES**
- Limited Lifetime Warranty
 - Dual Mount (flat or sloped ceiling-22°)
 - DC Motor
 - Plywood blades
 - Full function remote control with batteries is included

SIZE

60" dia., 17-3/8" ht.
80" lead wires.



Kaysville

P250003-081-30
shown with Chestnut blades

- FINISHES**
- Antique Nickel - 081
 - Graphite - 143

Beautiful long bent blades appear to be held only by a simple metal band in Kaysville, offering a modern industrial style. Kaysville pairs the beauty of the blades with a strong, all-weather ABS material to prevent warping.



Modern Style

Simple Metal Band

Dimmable LED Light

Kaysville

P250003-081-30 Antique Nickel



P250003-143-30 Graphite



P250003-081-30
shown with Chestnut blades



P250003-143-30
shown with Gray Weathered Wood blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	9,650 cubic feet per minute
Electricity Use	31 watts (excludes lights)
DOE Weighted CFM/W	361 CFM/W

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- ABS blades
- White Opal glass shade
- Remote control with batteries is included

SIZE

56" dia., 17-1/4" ht.
80" lead wires.

LAMP

24w LED Module, 3000K,
90 CRI, 2000 source lumens,
dimmable.



Full Function Remote Control Included
Six-speed fan operation
Full-range dimming for light
Reverse direction control



Alleron

P250009-182-30
shown with Antique Black blades

- FINISHES**
- Antique Nickel - 081
 - Flat Black - 182

Reminiscent of aviation days gone by, Alleron takes its styling cues from a set of airplane propeller blades. The hand-finished ABS blades paired with a sleek metal ceiling canopy and light kit add a modern industrial flair to indoor and covered outdoor settings.



Modern Industrial Flair

Propeller Inspired Blades

Dimmable LED Light

Alleron

P250009-081-30 Antique Nickel



P250009-182-30 Flat Black



P250009-081-30
shown with Gray Weathered Wood blades



P250009-182-30
shown with Antique Black blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	7,801 cubic feet per minute
Electricity Use	20 watts (excludes lights)
DOE Weighted CFM/W	423 CFM/W



Full Function Remote Control Included
Six-speed fan operation
Full-range dimming for light
Reverse direction control

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- ABS blades
- White opal glass shade
- Remote control with batteries is included

SIZE

56" dia., 16" ht.
80" lead wires.

LAMP

24w LED Module, 3000K,
90 CRI, 2000 source lumens,
dimmable.




Ellwood

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20

P2546-09
shown with Driftwood blades

A picture of modern design, the functional minimalism of the Ellwood 68" ceiling fan is a product of advanced design. Five long and graceful blades made of carved wood move air with remarkable efficiency. Ellwood features a dual mount system and is compatible with universal light kits. A full function remote control is included.




Modern Design

Carved Wood Blades

Dual Mount System

Ellwood

P2546-09 Brushed Nickel



P2546-20 Antique Bronze



P2546-09
shown with Driftwood blades



P2546-20
shown with Walnut blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	7,587 cubic feet per minute
Electricity Use	90 watts (excludes lights)
DOE Weighted CFM/W	92 CFM/W

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Patented carved Wood blades
- Compatible with universal light kits
- Remote control with batteries is included
- Remote control may be replaced with P2631-30 wall control

SIZE

68" dia., 16-3/4" ht.
80" lead wires.



Full Function Remote Control Included
Three-speed fan operation
Reverse direction control

Caleb

P2560-20AW
shown with Walnut blades

FINISHES

- Brushed Nickel - 09
- Brushed Nickel - 09WW
- Antique Bronze - 20
- Antique Bronze - 20AW

Beautiful and expansive in design, the 68" Caleb ceiling fan is ideal for use in large spaces. Bent carved wood blades are paired with either Brushed Nickel or Antique Bronze finishes. Caleb features a dual mount system and is compatible with universal light kits. A full function remote control is included.



P2560-09
shown with Medium Cherry blades



P2560-09WW
shown with Weathered Wood blades



P2560-20
shown with Walnut blades




P2560-20AW
shown with Walnut blades

Caleb

P2560-09 Brushed Nickel



P2560-09WW Brushed Nickel



P2560-20 Antique Bronze



P2560-20AW Antique Bronze



ENERGY INFORMATION AT HIGH SPEED

Airflow	7,045 cubic feet per minute
Electricity Use	86 watts (excludes lights)
DOE Weighted CFM/W	91 CFM/W



Full Function Remote Control Included
Three-speed fan operation
Reverse direction control

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Patented bent carved wood blades
- Compatible with universal light kits
- Remote control with batteries is included
- Remote control may be replaced with P2631-30 wall control

SIZE

68" dia., 18" ht.
80" lead wires.



Huff

P250030-009
shown with Brushed Nickel blades

FINISHES

- Brushed Nickel - 009
- Matte White- 028
- Matte Black- 031

The hassles and headaches of the day fade away under the relaxing airflow created by the Huff Collection. Six expansive aluminum blades with decorative winglets stretch out from a dual mount center. Select a Brushed Nickel, Matte White, or Matte Black finish all with their own complementary highlights to create a perfect design for your modern or transitional space.




Modern Design

Complimentary Highlights

Expansive Aluminum Blades

Huff

P250030-009 Brushed Nickel



P250030-028 Matte White



P250030-031 Matte Black



P250030-009
shown with Brushed Nickel blades
and Matte Black accents



P250030-028
shown with Matte White blades
and Brushed Nickel accents



P250030-031
shown with Black blades
and Brushed Nickel accents

ENERGY INFORMATION AT HIGH SPEED

Airflow	14,482 cubic feet per minute
Electricity Use	49 watts (excludes lights)
DOE Weighted CFM/W	344 CFM/W

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- Aluminum blades
- Damp Location Rated
- Compatible with universal light kit
- Remote control with batteries is included

SIZE

96" dia., 15-1/2" ht.
80" lead wires.



Full Function Remote Control Included
Six-speed fan operation
Reverse direction control

Vast

P2550-3130K
shown with Black blades


- FINISHES**
- Brushed Nickel - 09
 - Antique Bronze - 20
 - White - 30
 - Matte Black - 31

Beautiful and expansive in design, the 72" ceiling fan is ideal for use in large areas and outdoor covered areas for maximum cooling. A white opal shade complements a variety of finish options, including Brushed Nickel with chrome accents, Antique Bronze, White with chrome accents or Matte Black. Vast features a dual mount system and comes with a full function remote control.



Vast

P2550-0930K Brushed Nickel



P2550-2030K Antique Bronze



P2550-3030K White



P2550-3130K Matte Black



P2550-0930K
shown with Brushed Nickel blades
and Chrome accents



P2550-2030K
shown with Antique Bronze blades



P2550-3030K
shown with White blades
and Chrome accents



P2550-3130K
shown with Black blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	8,100 cubic feet per minute
Electricity Use	37 watts (excludes lights)
DOE Weighted CFN/W	247 CFM/W

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- Aluminum blades
- Damp Location Rated
- White opal glass
- Remote control with batteries is included

SIZE

72" dia., 16-3/4" ht
80" lead wires.

LAMP

18w LED Module, 3000K, 90 CRI,
1400 source lumens, dimmable.



Full Function Remote Control Included
Six-speed fan operation
Full-range dimming for light
Reverse direction control



Clean and Natural



Indoor-outdoor living begins with organic origins.

1

Select a large ceiling fan like Vast in covered outdoor areas to move air while making a design statement.

2

Bring the outdoors in with weathered wood furniture and organic decor.

3

Use a cool color palette and eye-catching architectural features like a double fireplace for a sophisticated, resort-like feel.

Arlo

P250026-009-30
shown with Brushed Nickel blades

FINISHES


- Brushed Nickel - 009
- Black - 031
- Architectural Bronze - 129

Unwind under the cooling breeze created by the clean, crisp blades of the Arlo collection's modern ceiling fan. A central LED light provides a perfect way to light a space without flooding the room with harsh light as six metal blades attach to the fan's center. Offered in three different finishes, Arlo is sure to create an intriguing, yet serene retreat in whatever space it calls home.

Modern Design

Clean Metal Blades

Dimmable LED Light



P250026-009-30
shown with Brushed Nickel blades




P250026-031-30
shown with Black blades



P250026-129-30
shown with Architectural Bronze blades

Arlo

P250026-009-30 Brushed Nickel



P250026-031-30 Black



P250026-129-30 Architectural Bronze



ENERGY INFORMATION AT HIGH SPEED

Airflow	7,558 cubic feet per minute
Electricity Use	29 watts (excludes lights)
DOE Weighted CFM/W	282 CFM/W



Full Function Remote Control Included
Six-speed fan operation
Full-range dimming for light
Reverse direction control

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- Aluminium blades
- Damp Location Rated
- White Opal glass
- Remote control with batteries is included

SIZE

60" dia., 18-1/2" ht.
80" lead wires.


LAMP

24w LED Module, 3000K, 90 CRI,
2000 source lumens, dimmable.



Bixby

P250038-231-30
shown with Black Metallic blades



Industrial Style

*Slightly Curved
Lucite Blades*

Dimmable LED Light

FINISHES

- White - 030
- Black Chrome - 231


You'll find the time to unwind under the eye-pleasing, urban industrial design of the Bixby collection's ceiling fan. Breathe easy after a warm summer day or a long day at work as Bixby fosters a refreshing current of cool air with three, slightly curved Lucite blades circling a gentle LED light as it provides soothing illumination.

Bixby

P250038-030-30 White



P250038-231-30 Black Chrome



ENERGY INFORMATION AT HIGH SPEED

Airflow	6,846 cubic feet per minute
Electricity Use	32 watts (excludes lights)
DOE Weighted CFM/W	228 CFM/W



Full Function Remote Control Included
Six-speed fan operation
Full-range dimming for light
Reverse direction control

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- Polycarbonate blades
- Damp Location Rated
- White opal glass
- Remote control with batteries is included

SIZE

60" dia., 15-1/8" ht.
80" lead wires.

LAMP

24w LED Module,
3000K, 90 CRI,
2000 source lumens, dimmable.



Farris

P250002-108-30
shown with Walnut blades

FINISHES

- Brushed Nickel - 009
- Oil Rubbed Bronze - 108
- Graphite - 143

Farris features three solid wood carved blades to form a sleek, modern design. The 60" ceiling fan includes an integrated LED light kit that is removable to provide the option in non-illuminated applications. Available in Brushed Nickel, Oil Rubbed Bronze and Graphite finishes. A full function remote control with batteries is included, and the dual mount canopy accommodates flat or sloped ceilings.



Modern Design

Wood Carved Blades

Removable, Dimmable LED Light

Farris


P250002-009-30 Brushed Nickel



P250002-108-30 Oil Rubbed Bronze



P250002-143-30 Graphite



ENERGY INFORMATION AT HIGH SPEED

Airflow	7,047 cubic feet per minute
Electricity Use	32 watts (excludes lights)
DOE Weighted CFM/W	223 CFM/W



Full Function Remote Control Included
Six-speed fan operation
Full-range dimming for light
Reverse direction control

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-13°)
- DC Motor
- Carved wood blades
- Removable light kit. Blank plate included.
- White opal shatterproof shade
- Full function remote control with batteries is included

SIZE

60" dia., 15-1/2" ht.
80" lead wires.

LAMP

18w LED Module, 3000K, 90 CRI,
1400 source lumens, dimmable.





Modern Farmhouse design embraces tradition but is firmly planted in the present.

1

Look for details like the beautifully carved, solid wood fan blades of the Farris ceiling fan that centers the room with statement-making style.

2

Modernize a traditional approach by contrasting a light and airy palette with a natural stone fireplace, weathered wood mantel and exposed beams.

3

Use organic materials for decorative accessories like greenery, wood and cozy textiles to add a welcoming touch.

Gaze

P2554-1530K
shown with White Washed blades

FINISHES

- Brushed Nickel - 09
- Polished Chrome - 15
- Antique Bronze - 20
- Black - 31

Three-blade 60" Gaze ceiling fan features an LED light source, offering both form and function with energy and cost-savings benefits. An opal white shade contains an 18W dimmable, 3000K LED module. Gaze features a dual mount system and includes a three-speed remote control with full range dimming.

Dual Mount System

Dimmable LED Light

White Opal Shade



P2554-0930K
shown with Silver blades



P2554-1530K
shown with Cherry blades




P2554-2030K
shown with Walnut blades




P2554-3130K
shown with Matte Black blades

Gaze


P2554-0930K Brushed Nickel




P2554-1530K Polished Chrome



P2554-2030K Antique Bronze



P2554-3130K Black



ENERGY INFORMATION AT HIGH SPEED

Airflow	5,902 cubic feet per minute
Electricity Use	75 watts (excludes lights)
DOE Weighted CFM/W	87 CFM/W



Three-Speed Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- Downrod installation only. Can not be flush mounted.
- AC Motor
- Manual reverse switch
- Reversible plywood blades
- White shatterproof lens
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control
- Add the P2667-031 Wi-Fi remote

SIZE

60" dia., 13-1/8" ht.
80" lead wires.

LAMP

18w LED Module, 3000K, 90 CRI,
1400 source lumens, dimmable.



Spades

FINISHES

- Brushed Nickel - 09
- Polished Chrome - 15
- Graphite - 143

P2570-15
shown with Black blades

The 56" Spades ceiling fan features a sleek contemporary two-blade design that is finished in Brushed Nickel, polished chrome or Graphite options. Spades features a dual mount system, an energy saving DC motor and ABS composite blades. A full function remote control is included.

Dual Mount System

Contemporary Design

Sleek Blades



Spades

P2570-09 Brushed Nickel



P2570-15 Polished Chrome



P2570-143 Graphite



P2570-09
shown with Silver blades



P2570-15
shown with Black blades



P2570-143
shown with Graphite blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	6,746 cubic feet per minute
Electricity Use	32 watts (excludes lights)
DOE Weighted CFM/W	215 CFM/W



Full Function Remote Control Included
Six-speed fan operation
Reverse direction control

FEATURES


- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-17°)
- Close-to-ceiling installation
- DC Motor
- Non-reversible ABS blades
- Will not accept a light kit
- Remote control with batteries is included

SIZE

56" dia., 18-1/8" ht.
(CTC 8-1/2" ht.),
80" lead wires.



CTC INSTALLATION



Inspirational Elements

1

2

3

Patterns and curves inspire the design of the room.

1

Select a sleek, contemporary fan like the two-blade Spades to harmonize with the contemporary feel of the living area.

2

Take one element, such as patterned window coverings, to inspire the rest of the room's palette.

3

Nothing jump starts design envy like architectural elements like an interesting ceiling.


Holland

P250032-009-30
shown with Silver blades

FINISHES

- Brushed Nickel - 009
- Black- 031
- Oil Rubbed Bronze - 108

Enjoy nothing but first-rate design inspiration with the gorgeous Holland collection. Four simple, yet stunning blades blend style with sustainability as they anchor to a sleek, dual mount center. An integrated LED light is ready to offer a gentle glow along with the fan's refreshing breeze. With the versatility to be installed in indoor or outdoor locations, this fan will make a design statement in any modern or transitional setting.



Dual Mount System

Dimmable LED Light

Indoor or Outdoor Use



P250032-009-30
shown with Silver blades



P250032-031-30
shown with Black blades



P250032-108-30
shown with Walnut blades

Holland

P250032-009-30 Brushed Nickel



Silver

P250032-031-30 Black



Black

P250032-108-30 Oil Rubbed Bronze



Walnut

ENERGY INFORMATION AT HIGH SPEED

Airflow	7,035 cubic feet per minute
Electricity Use	31 watts (excludes lights)
DOE Weighted CFM/W	257 CFM/W



Full Function Remote Control Included
Six-speed fan operation
Full-range dimming for light
Reverse direction control

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- ABS blades
- White opal glass
- Damp Location Rated
- Remote control with batteries is included

SIZE

60" dia., 16-5/8" ht.
80" lead wires.

LAMP

24w LED Module, 3000K, 90 CRI,
2000 source lumens, dimmable.



Oriole

FINISHES

- Brushed Nickel - 09
- Black - 31
- Architectural Bronze - 129

P2592-12930K
shown with Architectural Bronze blades



Sleek Blades

This 60" Oriole ceiling fan is the perfect addition to interior garages, industrial shops or commercial buildings to distribute the right amount of air and keep the space cool and comfortable. Oriole contains an integrated 18W LED module, with an optional finishing cap offering the user the choice to install with or without the light kit. A remote control is included to adjust speed and turn on/off the light or fan. A blank plate comes standard.

Industrial Design

Removable, Dimmable LED Light



P2592-0930K
shown with Silver blades



P2592-3130K
shown with Black blades
and light kit removed
using blank plate



P2592-12930K
shown with Architectural Bronze blades

Oriole

P2592-0930K Brushed Nickel



Silver

P2592-3130K Black



Black

P2592-12930K Architectural Bronze



Architectural Bronze

ENERGY INFORMATION AT HIGH SPEED

Airflow	6,171 cubic feet per minute
Electricity Use	51 watts (excludes lights)
DOE Weighted CFM/W	132 CFM/W



Three-Speed Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-18.5°)
- AC Motor
- ABS blades
- Removable light kit. Blank plate included.
- White opal glass shade
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control
- Add the P2667-031 Wi-Fi remote

SIZE

60" dia., 15" ht.
80" lead wires.

LAMP

18w LED Module, 3000K, 90 CRI,
1400 source lumens, dimmable.



Teasley

P250004-143
shown with Gray Weathered Wood blades

FINISHES

- Architectural Bronze - 129
- Galvanized - 141
- Graphite - 143

Featuring coastal influences and farmhouse charm, the Teasley 56" 5-blade ceiling fan is suitable for a variety of interior settings. Clear seeded bell-shaped glass shades highlight Architectural Bronze, Galvanized or Graphite finish options. Three vintage LED lamps are included, offering energy efficiency and cost savings benefits for the home, while a dual mount canopy accommodates flat or sloped ceilings.

Dual Mount System

Farmhouse Style

Vintage LED Lamps



P250004-129
shown with Brushed Bronze accents
and American Walnut blades




P250004-141
shown with Brushed Nickel accents
and Gray Weathered Wood blades



P250004-143
shown with Brushed Nickel accents
and American Walnut blades

Teasley

P250004-129 Architectural Bronze



P250004-141 Galvanized



P250004-143 Graphite



ENERGY INFORMATION AT HIGH SPEED

Airflow	5,749 cubic feet per minute
Electricity Use	76 watts (excludes lights)
DOE Weighted CFM/W	88 CFM/W

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-18.5°)
- AC Motor
- Reversible plywood blades
- Clear seeded glass shades
- Three speed pull-chain switch
- Add a P2630-30 or P2630-95 wall control or P2662-01 hand-held remote control
- Add the P2667-031 Wi-Fi remote

SIZE

56" dia., 22-1/2" ht.
80" lead wires.

LAMP

Three medium base 2700K 7w vintage LED lamps included. 600 lumens/lamp, 90 CRI, dimmable (with added remote or wall control). 10w LED or 60w incandescent max/socket.




Royer

FINISHES

- Antique Nickel - 081
- Forged Black- 080

P250010-080
shown with Distressed Ebony blades

The Royer collection's ceiling fan offers a charming, rustic look ideal for farmhouse and rustic spaces in need of a fresh breeze. Four plywood blades attach to the fixture's center by finely detailed metal arms. The crafted center is available in three finishes so you can select the perfect piece to complement your home décor.




P250010-080
shown with Matte Black blades




P250010-081
shown with Driftwood blades

Royer

P250010-080 Forged Black



P250010-081 Antique Nickel



Bottom detail of P250010-081
shown with Driftwood blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	6,255 cubic feet per minute
Electricity Use	67 watts (excludes lights)
DOE Weighted CFM/W	102 CFM/W



Three-Speed Remote Control Included
Three-speed fan operation

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Reversible plywood blades
- Not compatible with light kit
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control
- Add the P2667-031 Wi-Fi remote

SIZE

60" dia., 17-7/8" ht.
80" lead wires.




Glandon

FINISHES

- Gilded Iron - 71
- Antique Nickel - 81

P2586-8130K
shown with Driftwood blades

Glandon offers a sophisticated design that is ideal for settings requiring a touch of modern flair. Six reversible blades in a walnut/driftwood faux wood finish are strapped by a sleek Antique Nickel metal bar for an unexpected industrial detail. The 60" Glandon ceiling fan features a 17w LED module (3000K color temperature) with a shatterproof white opal shade and a dual mount system. Full range dimming and remote control is included.



Modern Style

Reversible Blades

Opal Shade




P2586-7130K
shown with Toasted Oak blades




P2586-8130K
shown with Classic Walnut blades

Glandon

P2586-7130K Gilded Iron



P2586-8130K Antique Nickel



ENERGY INFORMATION AT HIGH SPEED

Airflow	6,036 cubic feet per minute
Electricity Use	84 watts (excludes lights)
DOE Weighted CFM/W	96 CFM/W



Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Reversible plywood blades
- White opal shatterproof shade
- Remote control with batteries is included
- Add the P2667-031 Wi-Fi remote

SIZE

60" dia., 17-1/8" ht
80" lead wires.

LAMP

17w LED Module,
3000K, 90 CRI,
1400 source lumens, dimmable.





Live An Open Life

A neutral color palette adds to the airiness of an open floor plan.

1

Use a ceiling fan with a light kit to provide both light and cooling power in the living area.

2

Make an open-concept space an entertainer's paradise with a kitchen that flows into the living areas.

3

Choose lighting as a single focal point for each of the areas to create room-like settings.

Greer

FINISHES

- Gilded Iron - 71
- Antique Nickel - 81

P2584-81
shown with Classic Walnut blades

This five-blade 54" Greer ceiling fan complements either industrial or farmhouse decor. It comes with a wire meshed shade light kit that uses two vintage LED lamps (included). Remote control is also included. Greer can be hung on a flat or sloped ceiling due to its dual mount system.


Industrial Design

Dual Mount System


Wire Mesh Shade

Greer

P2584-71 Gilded Iron



P2584-81 Antique Nickel



P2584-71
shown with Toasted Oak blades



P2584-81
shown with Driftwood blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	4,794 cubic feet per minute
Electricity Use	65 watts (excludes lights)
DOE Weighted CFM/W	82 CFM/W



Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-45°)
- AC Motor
- Reversible plywood blades
- Wire basket shade light kit
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 wall control
- Add the P2667-031 Wi-Fi remote

SIZE

54" dia., 21-5/8" ht
80" lead wires.

LAMP

Two medium base 2200K 5.5w vintage LED lamps included. 500 lumens/lamp, 80 CRI, dimmable. 6.5w LED or 60W incandescent max/socket.

Fixtures shown with V6.55T19DLED922/JA8 vintage lamps.




Chapin

P250022-108
shown with Distressed Walnut blades

FINISHES

- Antique Nickel - 081
- Oil Rubbed Bronze - 108
- Graphite - 143


The Chapin Collection effortlessly unites a spacious room, creating an atmosphere that's both relaxing and reviving. Antique nickel, Graphite, or oil rubbed bronze finishes complement each other with four plywood blades and a dual mount canopy for a design destined to provide a truly relaxing experience.



P250022-081
shown with Driftwood blades



P250022-108
shown with American Walnut blades



P250022-143
shown with Grey Weathered Wood blades

Chapin

P250022-081 Antique Nickel



Driftwood
Classic Walnut

P250022-108 Oil Rubbed Bronze



Distressed Walnut
American Walnut

P250022-143 Graphite



Graphite
Gray Weathered Wood

ENERGY INFORMATION AT HIGH SPEED

Airflow	6,543 cubic feet per minute
Electricity Use	81 watts (excludes lights)
DOE Weighted CFM/W	87 CFM/W



Three-Speed Remote Control Included
Three-speed fan operation

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Reversible plywood blades
- Compatible with universal light kits
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control
- Add the P2667-031 Wi-Fi remote

SIZE

54" dia., 14-1/2" ht.
80" lead wires.





Bedwin

FINISHES


- Antique Nickel - 081
- Galvanized - 141
- Graphite - 143

P250024-081
shown with Driftwood blades

Recall charming, rustic lattice work with the Bedwin Collection's farmhouse-inspired ceiling fan. With three finishes to pick from and four rough hewn plywood blades circling a handsome dual mount canopy, this ceiling fan is sure to help transform any living space into a cool paradise of relaxation.



P250024-081
shown with Classic Walnut blades




P250024-141
shown with Gray Weathered Wood blades



P250024-143
shown with Graphite blades

Bedwin

P250024-081 Antique Nickel



P250024-141 Galvanized



P250024-143 Graphite



ENERGY INFORMATION AT HIGH SPEED

Airflow	6,044 cubic feet per minute
Electricity Use	34 watts (excludes lights)
DOE Weighted CFM/W	192 CFM/W

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- Reversible plywood blades
- Compatible with universal light kits
- Remote control with batteries is included

SIZE

56" dia., 15-1/2" ht.
80" lead wires.



Full Function Remote Control Included
Six-speed fan operation
Reverse direction control

Shaffer

FINISHES

- Matte White - 28
- Forged Black - 80
- Architectural Bronze - 129

P2590-80
shown with Silver blades

The 4-blade 56" Shaffer ceiling fan blends a streamlined design with mixed metal elements and a wire mesh housing, suitable for modern and urban industrial spaces. Available in Satin White with galvanized accents, forged black with chrome accents and Architectural Bronze with brushed bronze accents. Shaffer features a dual mount system and includes a remote control with batteries.



P2590-28
shown with Galvanized accents
and Silver blades




P2590-80
shown with Chrome accents
and Black blades




P2590-129
shown with Brushed Bronze accents
and Driftwood blades

Shaffer


P2590-28 Matte White



P2590-80 Forged Black



P2590-129 Architectural Bronze



ENERGY INFORMATION AT HIGH SPEED

Airflow	6,144 cubic feet per minute
Electricity Use	67 watts (excludes lights)
DOE Weighted CFM/W	99 CFM/W



Three-Speed Remote Control Included
Three-speed fan operation

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-18.5°)
- AC Motor
- Reversible plywood blades
- Not compatible with light kits
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

SIZE

56" dia., 16-1/4" ht.
80" lead wires.



Soar

P2542-2030K
shown with Walnut blades

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20
- White - 30

With a white opal shade and a 17W dimmable LED module, the 54" Soar ceiling fan offers energy and cost-savings benefits for a variety of living spaces. The four-blade fan comes with a remote control and is available in Brushed Nickel, Antique Bronze and white finishes. LED source features a 3000K-color temperature. Soar features a dual mount system and includes a remote control with batteries.

Dual Mount System



White Opal Shade

Dimmable LED Light



P2542-0930K
shown with Black blades



P2542-2030K
shown with Walnut blades



P2542-3030K
shown with White blades

Soar

P2542-0930K Brushed Nickel



Black

P2542-2030K Antique Bronze



Walnut

P2542-3030K White



White

ENERGY INFORMATION AT HIGH SPEED

Airflow	4,814 cubic feet per minute
Electricity Use	65 watts (excludes lights)
DOE Weighted CFM/W	83 CFM/W



Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Non-reversible plywood blades
- White opal shatterproof lens
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control
- Add the P2667-031 Wi-Fi remote

SIZE

54" dia., 15" ht.
80" lead wires.

LAMP

17w LED Module, 3000K, 90 CRI,
1400 source lumens, dimmable.



Harranvale

FINISHES

- Antique Bronze - 20
- White - 30
- Graphite - 143

P2540-14330K
shown with Graphite blades

The 54" Harranvale features a design that incorporates mixed metal design details that is very popular in today's home decor. Featuring reversible blades and opal glass shade, fans are available in three finish options: Antique Bronze with brushed bronze accent; Graphite with brushed nickel accent; and White with brushed nickel accent. Harranvale features a dual mount system and includes a remote control with batteries.


Mixed Metal Design

Opal Glass Shade


Reversible Blades

Harranvale


P2540-2030K Antique Bronze



P2540-3030K White



P2540-14330K Graphite



P2540-2030K
shown with Medium Cherry blades
and Brushed Bronze accent



P2540-3030K
shown with White blades
and Brushed Nickel accent



P2540-14330K
shown with American Walnut blades
and Brushed Nickel accent

ENERGY INFORMATION AT HIGH SPEED

Airflow	5,121 cubic feet per minute
Electricity Use	66 watts (excludes lights)
DOE Weighted CFM/W	87 CFM/W



Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20")
- AC Motor
- Reversible plywood blades
- White opal glass shade
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

SIZE

54" dia., 16-3/8" ht.
80" lead wires.

LAMP

17w LED Module, 3000K, 90 CRI,
1400 source lumens, dimmable.




Glenfalls

P250021-028-30
shown with Matte White blades and Black Chrome accents

FINISHES

- Brushed Nickel - 009
- Matte White- 028
- Matte Black - 031

Glenfalls highlights its beautiful simulated wood fan blades with bright metallic accents on the blade arms and tips to create a timeless yet modern design. Glenfalls is ideal for cooling large living areas in sophisticated style.



Timeless Design

Metallic Accents

Dimmable LED Light



P250021-009-30
shown with Chestnut blades
and Brushed Nickel accents



P250021-028-30
shown with Matte White blades
and Black Chrome accents



P250021-031-30
shown with Matte Black blades
and Brushed Nickel accents

Glenfalls

P250021-009-30 Brushed Nickel



Chestnut

P250021-028-30 Matte White



Matte White

P250021-031-30 Matte Black



Matte Black

ENERGY INFORMATION AT HIGH SPEED

Airflow	6,393 cubic feet per minute
Electricity Use	85 watts (excludes lights)
DOE Weighted CFM/W	84 CFM/W

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Plywood blades
- White opal glass shade
- Remote control with batteries is included
- Remote control may be replaced with the P2667-031 Wifi Remote

SIZE

56" dia., 14-7/8" ht.
80" lead wires.

LAMP

24w LED Module, 3000K,
90 CRI, 2000 source lumens,
dimmable.



Remote Control Included
Three-speed fan operation
Full-range dimming for light



Claret

P250007-108-30
shown with Antique Wood blades

FINISHES

- Brushed Nickel - 009
- Matte Black - 031
- Oil Rubbed Bronze - 108

Claret gracefully blends old and new with an eye-catching fluted motor housing paired with long blade arms. With its unique take on a classic design, Claret will make a statement in a variety of interiors.



Statement-Making

Fluted Motor Housing

Dimmable LED Light



P250007-009-30
shown with Matte Black blades




P250007-031-30
shown with Distressed Ebony blades



P250007-108-30
shown with Chestnut blades

Claret


P250007-009-30 Brushed Nickel



P250007-031-30 Matte Black



P250007-108-30 Oil Rubbed Bronze



ENERGY INFORMATION AT HIGH SPEED

Airflow	5,553 cubic feet per minute
Electricity Use	61 watts (excludes lights)
DOE Weighted CFM/W	106 CFM/W



Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Reversible plywood blades
- White opal glass shade
- Remote control with batteries is included
- Remote control may be replaced with the P2667-031 Wifi Remote

SIZE

54" dia., 15-1/8" ht.
80" lead wires.

LAMP

18w LED Module, 3000K,
90 CRI, 1400 source lumens,
dimmable.



Graceful

FINISHES

- Brushed Nickel - 09
- Polished Chrome - 15
- Antique Bronze - 20

P2544-0930K
shown with Medium Cherry blades

Refresh your living space with the crisp, clean style of the 54" Graceful fan. With a white opal glass shade and a 17W dimmable LED module, the five-blade fan comes with a remote control and is available in Brushed Nickel, polished chrome and Antique Bronze finishes. LED source offers a 3000K-color temperature, energy savings and maintenance benefits for the home.



P2544-0930K
shown with Silver blades



P2544-1530K
shown with Toasted Oak blades



P2544-2030K
shown with American Walnut blades

Graceful


P2544-0930K Brushed Nickel



P2544-1530K Polished Chrome



P2544-2030K Antique Bronze



ENERGY INFORMATION AT HIGH SPEED

Airflow	4,454 cubic feet per minute
Electricity Use	60 watts (excludes lights)
DOE Weighted CFM/W	83 CFM/W



Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Reversible plywood blades
- White opal glass shade
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control
- Add the P2667-031 Wi-Fi remote

SIZE

54" dia., 16-3/8" ht.
80" lead wires.

LAMP

17w LED Module, 3000K, 90 CRI,
1400 source lumens, dimmable.



Olson

P2598-143
shown with Graphite blades

FINISHES

- Brushed Nickel - 09
- Graphite - 143

The 52" Olson ceiling fan features a generously sized etched watermark glass shade and sweeping blades highlighted with metal accents in a Brushed Nickel or Graphite finish. Two LED lamps are JA8 compliant, offering both form and function with energy and cost-savings benefits. Olson features a dual mount system and a three-speed pull chain fan switch, as well as an on/off pull chain switch to operate the light.



Metal Accents

LED Light

Watermark Glass Shade




P2598-09
shown with Medium Cherry blades



P2598-143
shown with Gray Weathered Wood blades

Olson

P2598-09 Brushed Nickel



P2598-143 Graphite



ENERGY INFORMATION AT HIGH SPEED

Airflow	5,023 cubic feet per minute
Electricity Use	70 watts (excludes lights)
DOE Weighted CFM/W	83 CFM/W

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-18.5")
- AC Motor
- Reversible plywood blades
- Etched watermark glass
- Three speed pull-chain switch
- Add a P2630-30 or P2630-95 wall control, P2661-01 or P2662-01 hand-held remote control

SIZE

52" dia., 21-5/16" ht.
80" lead wires.

LAMP

Two medium base 3000K 9w LED lamps included. 800 lumens/lamp, 90 CRI, dimmable (with added remote or wall control). 10w LED max/socket



Gust

P2582-0930K
shown with Silver blades

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20
- Graphite - 143

This five-blade 54" Gust ceiling fan features a white opal glass shade that is available in a Brushed Nickel, Antique Bronze or Graphite finish. A remote control is included. Gust has a dual mount system to offer greater flexibility when installing. The 18W dimmable, 3000K LED module provides energy and cost-savings benefits to the homeowner.



Dual Mount System

Sleek Design

Dimmable LED Light



P2582-0930K
Shown with Silver blades



P2582-2030K
Shown with Walnut blades



P2582-14330K
Shown with Graphite blades

Gust

P2582-0930K Brushed Nickel



Silver

P2582-2030K Antique Bronze



Walnut

P2582-14330K Graphite



Graphite

ENERGY INFORMATION AT HIGH SPEED

Airflow	5,242 cubic feet per minute
Electricity Use	65 watts (excludes lights)
DOE Weighted CFM/W	87 CFM/W



Three-Speed Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-18.5")
- AC Motor
- Manual reverse switch
- Non-reversible plywood blades
- White opal glass shade
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control
- Add the P2667-031 Wi-Fi remote

SIZE

54" dia., 16" ht.
80" lead wires.

LAMP

18w LED Module, 3000K, 90 CRI,
1400 source lumens, dimmable.



Casual, Modern Charm



1

2

3

Craftsman style gets modern flair with clean and bright design.

1

Hang a sleek Gust fan from a paneled ceiling for Craftsman style with a modern edge.

2

Pair farmhouse-style furniture with cozy textures and neutral colors for casual comfort.

3

Break up a bright space visually with a handcrafted, dark wood door.


Kudos

FINISHES

- Brushed Nickel - 09
- Polished Chrome - 15
- Antique Bronze - 20


P2568-0930K
shown with American Walnut blades

This five-blade 52" Kudos ceiling fan features a clear Fresnel glass shade. Available in a Brushed Nickel, polished chrome or Antique Bronze finish and includes a remote control. The Kudos features a dual mount system to offer greater flexibility when installing. The 18W dimmable, 3000K LED module provides energy and cost-savings benefits to the homeowner.





Kudos

P2568-0930K Brushed Nickel

-  American Walnut
-  Silver

P2568-1530K Polished Chrome

-  Medium Cherry
-  Black

P2568-2030K Antique Bronze

-  Walnut
-  Cherry

ENERGY INFORMATION AT HIGH SPEED

Airflow	5,160 cubic feet per minute
Electricity Use	60 watts (excludes lights)
DOE Weighted CFM/W	91 CFM/W



Three-Speed Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-18.5")
- Downrod installation only. Can not be flush mounted.
- AC Motor
- Reversible plywood blades
- Clear Fresnel glass shade
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control
- Add the P2667-031 Wi-Fi remote

SIZE

52" dia., 17-5/8" ht.
80" lead wires.

LAMP

18w LED Module, 3000K, 90 CRI,
1400 source lumens, dimmable.



Fresno

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20
- White - 30

P2548-2030K
shown with Cherry blades

Five-blade 60" Fresno ceiling fan features an LED light source, offering both form and function with energy and cost-savings benefits. A white opal glass shade features an 18W dimmable, 3000K LED module. A remote control with full range dimming and remote control is included.




Clean Design

Dimmable LED Light


White Opal Glass Shade

Fresno


P2548-0930K Brushed Nickel



P2548-2030K Antique Bronze



P2548-3030K White



P2548-0930K
shown with Silver blades



P2548-2030K
shown with Dark Walnut blades



P2548-3030K
shown with White blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	5,718 cubic feet per minute
Electricity Use	79 watts (excludes lights)
DOE Weighted CFM/W	80 CFM/W



Full Function Remote Control Included
Three-speed fan operation
Full-range dimming for light
Reverse direction control

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-17.5°)
- AC Motor
- Reversible plywood blades
- White opal glass shade
- Remote control with batteries is included, receiver mounted in motor.
- Remote control may be replaced with P2631-30 wall control
- Add the P2667-031 Wi-Fi remote

SIZE

60" dia., 17-1/4" ht.
80" lead wires.

LAMP

18w LED Module, 3000K, 90 CRI,
1400 source lumens, dimmable.



Tempt

P2578-16330K
shown with Chesnut blades

FINISHES

- Polished Chrome - 15
- Antique Bronze - 20
- Vintage Brass - 163

This five-blade 52" Tempt ceiling fan features a clear, double prismatic glass shade that is available in a Polished chrome, Antique Bronze or Vintage Brass finish. A remote is included. Tempt features a dual mount system to offer greater flexibility when installing. The 17w dimmable, 3000K LED module provides energy and cost-savings benefits to the homeowner.



P2578-1530K
shown with Medium Cherry blades




P2578-2030K
shown with American Walnut blades




P2578-16330K
shown with Dark Cherry blades

Tempt


P2578-1530K Polished Chrome



P2578-2030K Antique Bronze



P2578-16330K Vintage Brass



ENERGY INFORMATION AT HIGH SPEED

Airflow	4,314 cubic feet per minute
Electricity Use	63 watts (excludes lights)
DOE Weighted CFM/W	78 CFM/W



Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Reversible plywood blades
- Clear double prismatic glass shade
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control
- Add the P2667-031 Wi-Fi remote

SIZE

52" dia., 16-1/4" ht.
80" lead wires.

LAMP

17w LED Module, 3000K, 90 CRI,
1400 source lumens, dimmable.



Verada

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20

P2558-0930K
shown with Medium Cherry blades

This five-blade 52" Verada ceiling fan combines a linen glass shade with a 17W LED source. Available in a Brushed Nickel or Antique Bronze finish. Verada features a dual mount system and a three-speed pull chain fan switch, as well as an on/off pull chain switch to operate the light. LED light kit features a 3000K color temperature.


Dual Mount System

LED Light


Linen Glass Shade

Verada

P2558-0930K Brushed Nickel



P2558-2030K Antique Bronze



P2558-0930K
shown with white linen glass
and American Walnut blades



P2558-2030K
shown with tea stained linen glass
and Medium Cherry blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	4,445 cubic feet per minute
Electricity Use	65 watts (excludes lights)
DOE Weighted CFM/W	79 CFM/W

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-30°)
- AC Motor
- Reversible plywood blades
- Linen glass shade
- 3 Speed pull chain switches
- Add a P2630-30 or P2630-95 wall control or P2662-01 hand-held remote control
- Add the P2667-031 Wi-Fi remote

SIZE

52" dia., 16" ht.
80" lead wires.

LAMP

17w LED Module, 3000K, 90 CRI,
1400 source lumens, dimmable (with
added remote or wall control).



Billows

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20
- Forged Black - 80

P2552-09
shown with White Washed blades

With a sophisticated and traditional design, the Billows offers both form and function with two energy efficient LED lamps, featuring a 3000K color temperature. The 52" Billows ceiling fan features an LED light kit with white opal glass shade and five reversible blades. The fans are available in Brushed Nickel, Antique Bronze and Forged Black finishes.

Traditional Design

Reversible Blades

White Opal Glass Shade



P2552-09
shown with Silver blades



P2552-20
shown with American Walnut blades



P2552-80
shown with Toasted Oak blades

Billows

P2552-09 Brushed Nickel

- White Washed
- Silver

P2552-20 Antique Bronze

- Cherry
- American Walnut

P2552-80 Forged Black

- Black
- Toasted Oak

ENERGY INFORMATION AT HIGH SPEED

Airflow	4,682 cubic feet per minute
Electricity Use	59 watts (excludes lights)
DOE Weighted CFM/W	92 CFM/W

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-18.5°)
- AC Motor
- Reversible plywood blades
- White opal glass shade
- Add a P2630-30 or P2630-95 wall control or P2662-01 hand-held remote control
- Add the P2667-031 Wi-Fi remote

SIZE

52" dia., 17-1/2" ht.
80" lead wires.

LAMP

Two medium base 3000K 9w LED lamps included. 800 lumens/lamp, 90 CRI, dimmable (with added remote or wall control). 10w LED max/socket.



Accessorize with Style



Pops of blue and plenty of collectibles give a room personality.

1

Select a ceiling fan like Billows, whose whitewashed-finish blades accentuate the organic textures in the room.

2

Follow your style by curating your space with treasures that you love.

3

Pick a focal point like the rough stone fireplace and use its natural color palette to inform the color choices for the rest of the space.


Signature

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20
- Forged Bronze - 77
- Forged Black - 80
- Antique Nickel - 81

P2521-09WA
Shown with Dark Walnut blades

A 52" Signature 5-blade fan features reversible blades and a 30-year limited warranty. A powerful AirPro motor features a 3-speed, triple-capacitor control that can also be reversed to provide year-round comfort. The Signature fan will also accept a universal light kit.



P2521-09
shown with White blades



P2521-09CH
Shown with Cherry blades



P2521-20
Shown with P2602-20WB light kit*
with Classic Walnut blades
* Light kit sold separately.



P2521-80
Shown with Dark Cherry blades



P2521-81
Shown with Medium Oak blades

Signature

P2521-09 Brushed Nickel

- Natural Cherry
- White

P2521-09CH Brushed Nickel

- Natural Cherry
- Cherry

P2521-09WA Brushed Nickel

- Dark Walnut
- Classic Walnut

P2521-20 Antique Bronze

- Classic Walnut
- Medium Cherry

P2521-80 Forged Black

- Dark Cherry
- Dark Walnut

P2521-81 Antique Nickel

- Cherry
- Medium Oak

ENERGY INFORMATION AT HIGH SPEED

Airflow	4,701 cubic feet per minute
Electricity Use	65 watts (excludes lights)
DOE Weighted CFM/W	84 CFM/W

FEATURES

- 30-year limited warranty
- 45° Canopy
- Close-to-ceiling installation
- SureConnect® System
- AC Motor
- Compatible with universal light kits
- Three speed pull-chain switch
- Add a P2630-30 or P2630-95 wall control or P2662-01 hand-held remote control
- Add the P2667-031 Wi-Fi remote

SIZE

52" dia., 14-5/8" ht. (CTC 11-9/16" ht.), 80" lead wires.

CTC INSTALLATION



Trevina II 44"

The Trevina collection features fans with a signature three-blade design. Perfect for modern or traditional interiors, each fan includes an LED light source to help extend your day into the evening as you and your family relax in your peaceful retreat.

FINISHES

- Brushed Nickel - 09
- Satin White - 28
- Black - 31


P2555-0930K Brushed Nickel



P2555-2830K Satin White



P2555-3130K Black



Detail of P2555-0930K shown with P2668-09 blank plate and Silver blades

BLANK PLATE

- P2668-09** Brushed Nickel
- P2668-28** Satin White
- P2668-31** Black



P2555-0930K
shown with Silver blades



P2555-2830K
shown with White blades



P2555-3130K
shown with Distressed Ebony blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	4306 cubic feet per minute
Electricity Use	42 watts (excludes lights)
DOE Weighted CFM/W	122 CFM/W

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Reversible MDF blades
- Removable light kit. Blank plate sold separately.
- White Opal glass
- Compatible with remote or hardwired wall controls (P2630, P2661-01, P2662-01, P2663-01, P2665 (sold separately))

SIZE

44" dia., 15-5/8" ht.
80" lead wires.

LAMP

18w LED Module, 3000K, 90 CRI, 1400 source lumens, dimmable.




Wall Control Included
Four-speed fan operation
Full-range dimming for light
Includes switch plate cover

Trevina II 52"

FINISHES

- Architectural Bronze - 129
- Painted Nickel - 152

P2553-129WB Architectural Bronze



P2553-152WB Painted Nickel



P2553-129WB
shown with Medium Cherry blades



P2553-152WB
shown with Black blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	5,296 cubic feet per minute
Electricity Use	56 watts (excludes lights)
DOE Weighted CFM/W	112 CFM/W

FEATURES

- Limited lifetime warranty (LED model)
- Dual Mount (flat or sloped ceiling-30°)
- AC Motor
- White opal glass
- Reversible plywood blades
- No switch included
- Compatible with remote control or hardwired wall controls (P2618-01, P2630, P2662-01 (sold separately))

SIZE

52" dia., 15-3/4" ht.
80" lead wires.

LAMP

Two medium base 3000K 9.5w LED lamps included. 800 lumens/lamp, 80 CRI, dimmable. 60w max/ socket.



P2556-3030K
shown with White blades



P2556-2030K
shown with Medium Cherry blades



P2556-0930K
shown with Silver blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	4,916 cubic feet per minute
Electricity Use	62 watts (excludes lights)
DOE Weighted CFM/W	89 CFM/W

FEATURES

- Limited lifetime warranty (LED model)
- Dual Mount (flat or sloped ceiling-30°)
- Close-to-ceiling installation
- AC Motor
- White opal glass
- Reversible plywood blades

SIZE


52" dia., 15-3/4" ht.
80" lead wires.

LAMP

17w LED Module, 3000K, 90 CRI, 1400 source lumens, dimmable.



Wall Control Included
Four-speed fan operation
Full-range dimming for light
Includes switch plate cover




CTC INSTALLATION

Trevina II 52"


FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20
- White- 30

P2556-3030K White



P2556-2030K Antique Bronze



P2556-0930K Brushed Nickel



Coolly Modern



1

2

3

Wow family and friends with a dramatic ceiling treatment.

1

Install a ceiling fan like Trevina, whose contemporary design brings both form and function.

2

Add molding or beams to the ceiling to create a spectacular "fifth wall."

3

Choose wood floors and cabinetry as a warming element to unite an open floor plan.

Signature Plus II

Five-blade 54" Signature Plus II ceiling fan features an integrated LED light source, offering both form and function with energy and cost-savings benefits. The light kit contains a white opal shatterproof shade and is comprised of a 17W dimmable 3000K LED module.

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20
- White - 30

P2539-0930K Brushed Nickel

- Driftwood
- Silver

P2539-2030K Antique Bronze

- Classic Walnut
- Medium Cherry

P2539-3030K White

- White
- White



P2539-0930K
shown with Silver blades



P2539-2030K
shown with Medium Cherry blades



P2539-3030K
shown with White blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	5,331 cubic feet per minute
Electricity Use	65 watts (excludes lights)
DOE Weighted CFM/W	92 CFM/W



Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited lifetime warranty
- 45° Canopy
- Downrod mount only
- AC Motor
- Reversible MDF blades
- White opal shatterproof shade
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

SIZE

54" dia., 15-1/2" ht.
80" lead wires.

LAMP

17w LED Module, 3000K, 90 CRI,
1400 source lumens, dimmable.



Signature Plus

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20
- White - 30

P2530-09 Brushed Nickel

- Natural Cherry
- Silver

P2530-20 Antique Bronze

- Classic Walnut
- Medium Cherry

P2530-30W White

- White
- White



P2530-20
shown with P2645-01WB
light kit* and Classic
Walnut blades

*Light kit sold separately.



P2530-09
shown with Silver blades



P2530-20
shown with Classic Walnut blades



P2530-30W
shown with White blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	4,716 cubic feet per minute
Electricity Use	65 watts (excludes lights)
DOE Weighted CFM/W	84 CFM/W

FEATURES

- 30-year limited warranty
- 45° Canopy
- Downrod mount only
- AC Motor
- Compatible with universal light kits
- Three speed pull-chain switch
- Add a P2630-30 or P2630-95 wall control or P2662-01 hand-held remote control
- Add the P2667-031 Wi-Fi remote

SIZE

54" dia., 15" ht.
80" lead wires.




Clifton Heights

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20



P2531-09
shown with Cherry blades

52" 4-blade Clifton Heights ceiling fan features distinctive, squared reversible blades. This contemporary styled fan offers great performance and value. The Clifton Heights fan features a powerful, 3-speed motor that can be reversed to provide year-round comfort. The Clifton Heights fan will also accept a universal light kit.





Clifton Heights

P2531-09 Brushed Nickel

-  Natural Cherry
-  Cherry

P2531-20 Antique Bronze

-  Classic Walnut
-  Cherry



ENERGY INFORMATION AT HIGH SPEED

Airflow	4,373 cubic feet per minute
Electricity Use	55 watts (excludes lights)
DOE Weighted CFM/W	89 CFM/W

FEATURES


- 30-year limited warranty
- 45° Canopy
- Close-to-ceiling installation
- SureConnect System
- AC Motor
- Compatible with universal light kits
- Three speed pull-chain switch
- Add a P2630-30 or P2630-95 wall control or P2662-01 hand-held remote control
- Add the P2667-031 Wi-Fi remote

SIZE

52" dia., 15-3/4" ht.
(CTC 11" ht.),
80" lead wires.



CTC INSTALLATION



Edgefield

FINISHES

- Brushed Nickel - 009
- White - 030
- Architectural Bronze - 129




P250016-129
shown with Medium Cherry blades

The 52" Edgefield fan is energy efficient and lightweight. A DC motor provides ultra quiet operation and the efficiency of the latest fan technology along with the simple convenience of a four-speed pull chain switch. Edgefield features a reversible motor for year round comfort and is available in three finish options. Pair with a universal light kit for a more customized look.

Ultra Quiet


Lightweight

Energy Efficient




Edgefield


P250016-009 Brushed Nickel



P250016-030 White



P250016-129 Antique Bronze



P250016-009
shown with American Walnut blades



P250016-030
shown with White blades



P250016-129
shown with Medium Cherry blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	5,741 cubic feet per minute
Electricity Use	34 watts (excludes lights)
DOE Weighted CFM/W	179 CFM/W

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-18.5°)
- DC motor
- Manual reverse switch
- MDF blades
- Compatible with universal light kits
- Three speed pull-chain switch
- Will not accept a wall or remote control

SIZE

52" dia., 14-9/16" ht.
80" lead wires



Air Pro

FINISHES

- Brushed Nickel - 009
- White - 030
- Matte Black - 31M




P250066-31M
shown with Distressed Ebony blades

An Energy Star rated AC motor gives this ceiling fan remarkable energy efficiency and powerful airflow while featuring classic good looks. Five fan blades circulate air comfortably. Versatile control options include remote control, WiFi and wall control choices. Its clean lines and a five-blade design complement a variety of interiors.


Clean Lines

Energy-Efficient

Classic Design



P250066-009
shown with Natural Cherry blades




P250066-030
shown with Washed Oak blades




P250066-31M
shown with Distressed Ebony blades

Air Pro

P250066-009 Brushed Nickel



P250066-030 White



P250066-31M Matte Black



ENERGY INFORMATION AT HIGH SPEED

Airflow	4986 cubic feet per minute
Electricity Use	44 watts (excludes lights)
DOE Weighted CFM/W	134 CFM/W

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-30°)
- AC Motor
- Add a P2630-30 or P2613-30 wall control or P2662-01 hand-held remote control
- Add the P2667-031 Wi-Fi remote

SIZE

52" dia., 13-1/2" ht.
80" lead wires.




52" Performance


FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20
- White - 30

P2503-09 Brushed Nickel




P2503-20 Antique Bronze



P2503-30W White




P2503-20 shown with P2650-20TWB light kit* and Medium Cherry blades
*Light kit sold separately.



P2503-09 shown with Natural Cherry blades



P2503-20 shown with Medium Cherry blades



P2503-30W shown with White blades



45° Canopy

- Standard canopy works with sloped ceilings up to 45°. (12:12 ceiling pitch)
- Outlet box mounting plate includes convenient hands-free hanger for wiring.
- Oversize, textured die-cast hanger ball reduces vibrations that can cause noise and wobble.
- Dual-mount for downrod or close-to-ceiling installation (on select fans)



SureConnect® System

- Motor screws pre-installed in blade arms to prevent them from falling out during installation.
- Special guides perfectly align blade arms to motor.
- Preinstalled rubber isolation pads prevent vibration noise.

ENERGY INFORMATION AT HIGH SPEED

Airflow	5,143 cubic feet per minute
Electricity Use	70 watts (excludes lights)
DOE Weighted CFM/W	85 CFM/W

FEATURES


- Limited lifetime warranty
- 45° Canopy
- Close-to-ceiling installation
- SureConnect® System
- AC Motor
- Compatible with universal light kits
- Three speed pull-chain switch
- Add a P2630-30 or P2630-95 wall control or P2662-01 hand-held remote control
- Add the P2667-031 Wi-Fi remote

SIZE

52" dia., 15-1/4" ht.
(CTC 10-1/2" ht.),
80" lead wires.



CTC INSTALLATION




42" Builder Fan


FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20
- White - 30


P2500-09 Brushed Nickel



P2500-20 Antique Bronze



P2500-30 White




P2500-09 shown with P2600-09WB light kit* and with Cherry blades
*Light kit sold separately.



P2500-09 shown with Cherry blades



P2500-20 shown with Classic Walnut blades



P2500-30 shown with White blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	3,053 cubic feet per minute
Electricity Use	46 watts (excludes lights)
DOE Weighted CFM/W	64 CFM/W

FEATURES


- 15-year limited warranty
- 23° Canopy
- Close-to-ceiling installation
- SureConnect® System
- AC Motor
- Compatible with universal light kits
- Three speed pull-chain switch
- Add a P2630 wall control or P2662-01 hand-held remote control

SIZE

42" dia., 12-3/8" ht.
(CTC 8-5/16" ht.),
72" lead wires.



CTC INSTALLATION





52" Builder Fan with Light Kit

FINISHES

- Brushed Nickel - 009
- White - 030
- Architectural Bronze - 129



P2599-09 Brushed Nickel

-  Natural Cherry
-  Cherry

P2599-30 White

-  White
-  White

P2599-129 Antique Bronze

-  Classic Walnut
-  Medium Cherry



P2599-09
shown with Cherry blades



P2599-30
shown with White blades



P2599-129
shown with Classic Walnut blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	4,474 cubic feet per minute
Electricity Use	65 watts (excludes lights)
DOE Weighted CFM/W	82 CFM/W

FEATURES

- 30-year limited warranty
- Dual Mount (flat or sloped ceiling-30°)
- AC Motor
- MDF/Plywood hybrid blades
- Etched white glass shade
- Three speed pull-chain switch
- Add a P2630-30 or P2630-95 wall control or P2662-01 hand-held remote control

SIZE

52" dia., 17-5/8" ht.
80" lead wires.

LAMP

Two medium base 3000K 8.5w LED lamps included. 800 lumens/lamp, 80 CRI, non-dimmable.





52" Builder Fan



FINISHES

- Brushed Nickel - 09
- Polished Chrome - 15
- Antique Bronze - 20
- White - 30
- White - 30W
- Graphite - 143



P2501-09 Brushed Nickel

-  Natural Cherry
-  Cherry



P2501-15 Polished Chrome

-  Black
-  Driftwood



P2501-20 Antique Bronze

-  Medium Cherry
-  Classic Walnut



P2501-30 White

-  White
-  Washed Oak

P2501-30W White

-  White
-  White

P2501-143 Graphite


-  Graphite
-  Black




P2501-09
shown with Cherry blades




P2501-20
shown with Medium Cherry blades



P2501-30W
shown with White blades



P2501-15
shown with Driftwood blades



P2501-30
shown with Washed Oak blades



P2501-143
shown with Black blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	4,991 cubic feet per minute
Electricity Use	63 watts (excludes lights)
DOE Weighted CFM/W	98 CFM/W

FEATURES

- 30-year limited warranty
- 45° Canopy
- Close-to-ceiling installation with accessory
- SureConnect® System
- AC Motor
- Compatible with universal light kits
- Add a P2630 wall control or P2662-01 hand-held remote control

SIZE

52" dia., 13-1/2" ht.
80" lead wires.




Drift

FINISHES

- Brushed Nickel - 009
- White - 030
- Architectural Bronze - 129


P250008-009
shown with Silver blades

Enhance your home with the perfect mix of form and function with the 32" four-blade Drift fan. Ideal for smaller spaces, such as closets, mudrooms and laundry rooms, Drift features a powerful motor and a steep pitch to circulate a lot of air within a smaller space.




Drift


P250008-009 Brushed Nickel



P250008-030 White



P250008-129 Architectural Bronze



P250008-009
shown with Driftwood blades



P250008-030
shown with Driftwood blades



P250008-129
shown with Classic Walnut blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	2,518 cubic feet per minute
Electricity Use	35 watts (excludes lights)
DOE Weighted CFM/W	88 CFM/W

FEATURES


- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-30°)
- Close-to-ceiling installation
- AC Motor
- Reversible MDF blades
- Compatible with universal light kits
- Three speed pull-chain switch
- Add a P2630-30 or P2630-95 wall control or P2662-01 hand-held remote control

SIZE

32" dia., 14-3/8" ht.
80" lead wires.



CTC INSTALLATION





44" Braden

The Braden 44 inch, three-blade, hugger-style ceiling fan features clean lines and a classic, sleek design that is ideal for Modern and Contemporary interiors. With its simple and elegant look and Brushed Nickel, Matte Black or Matte White finish, Braden complements most décor schemes.



FINISHES

- Brushed Nickel - 009
- Matte White - 028
- Matte Black - 031



P250058-009-30 Brushed Nickel

-  American Walnut
-  Silver

P250058-028-30 Matte White

-  Natural Cherry
-  White

P250058-031-30 Matte Black

-  Distressed Ebony
-  Matte Black



P250058-009-30
shown with American Walnut blades



P250058-028-30
shown with Natural Cherry blades



P250058-031-30
shown with Distressed Ebony blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	3,212 cubic feet per minute
Electricity Use	45 watts (excludes lights)
DOE Weighted CFM/W	78 CFM/W



Full Function Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited lifetime warranty
- Hugger low profile mounting
- AC Motor
- Reversible plywood blades
- Frosted shatterproof shade
- Full function remote control with batteries is included
- Remote control may be replaced with P2667-31 Wi-Fi remote control

SIZE

44" dia., 9-7/8" ht.
12" lead wires.

LAMP

18w LED Module, 3000K,
90 CRI, 1400 source lumens,
dimmable.



Featuring Braden and Clarion

Sweet Dreaming

Muted colors and a light, airy feeling offer a dreamy look to this bedroom. The Braden hugger fan lends a contemporary touch while keeping the room comfortable and welcoming. A feature wall of lightly distressed wood paneling is accented by a pair of Clarion wall sconces, whose clear glass shade and clean styling embrace minimalist modernity and functional task lighting.

Braden

P2588-1530K
shown with Black blades

FINISHES

- Brushed Nickel - 09
- Polished Chrome - 15
- Architectural Bronze - 129

This Braden 56", three-blade, hugger-style ceiling fan features clean lines and a design that complements modern interiors. A white opal glass shade contains an integrated 18W LED module, offering both form and function with energy and cost-savings benefits. Featuring a larger motor, Braden moves more air than a traditional hugger ceiling fan.



Modern Style

Dimmable LED Light

White Opal Glass Shade



P2588-0930K
shown with Silver blades




P2588-1530K
shown with American Walnut blades




P2588-12930K
shown with Medium Cherry blades

Braden


P2588-0930K Brushed Nickel



P2588-1530K Polished Chrome



P2588-12930K Architectural Bronze



ENERGY INFORMATION AT HIGH SPEED

Airflow	4,263 cubic feet per minute
Electricity Use	55 watts (excludes lights)
DOE Weighted CFM/W	85 CFM/W



Full Function Remote Control Included
Three-speed fan operation
Full-range dimming for light
Reverse direction control

FEATURES

- Limited lifetime warranty
- Hugger low profile mounting
- AC Motor
- Reversible plywood blades
- White opal glass shade
- Full function remote control with batteries is included
- Remote control may be replaced with P2631-30 wall control
- Add the P2667-031 Wi-Fi remote

SIZE

56" dia., 9-7/8" ht.
12" lead wires.

LAMP

18w LED Module, 3000K, 90 CRI, 1400 source lumens, dimmable.



Vox Fan

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20
- White - 30

P2572-0930K
shown with Medium Cherry blades

Five-blade 52" Vox hugger-style ceiling fan features an LED light source, offering both form and function with energy and cost-savings benefits. A white opal glass shade contains a 17W dimmable, 3000K LED module. A full function remote control is included. The fan mounts close to the ceiling and is available in popular Brushed Nickel, Antique Bronze and white finishes.



Dimmable LED Light

Modern Style


White Opal Glass Shade

Vox Fan

P2572-0930K Brushed Nickel

 Medium Cherry

P2572-2030K Antique Bronze

 American Walnut

P2572-3030K White

 White



P2572-0930K
shown with Medium Cherry blades



P2572-2030K
shown with American Walnut blades



P2572-3030K
shown with White blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	4,276 cubic feet per minute
Electricity Use	62 watts (excludes lights)
DOE Weighted CFM/W	76 CFM/W



Full Function Remote Control Included
Three-speed fan operation
Full-range dimming for light
Reverse direction control

FEATURES

- Limited Lifetime Warranty
- Hugger low profile mounting
- AC Motor
- Non-reversible plywood blades
- White opal glass shade
- Full function remote control with batteries is included
- Remote control may be replaced with P2631-30 wall control
- Add the P2667-031 Wi-Fi remote

SIZE

52" dia., 11-5/8" ht.
8" lead wires.

LAMP

17w LED Module, 3000K, 90 CRI, 1400 source lumens, dimmable.




Lindale

FINISHES

- Matte White- 028
- Antique Nickel - 081
- Architectural Bronze - 129

P250028-129
shown with Distressed Walnut blades

Retreat for a little rest and relaxation under the gentle airflow offered by the Lindale collection's ceiling fan. A mid-century modern style blends with a flush mount design as four rectangular plywood blades attach to the fan's vase-inspired center. Select your favorite finish from three beautiful options to customize your Lindale fan for a perfect fit in your home décor design.



Mid-Century Modern

Plywood Blades

Flush Mount Design



P250028-028
shown with Brushed Nickel accents
and Matte White blades




P250028-081
shown with White Barnwood blades




P250028-129
shown with Matte Gold accents,
Classic Walnut blades and
optional P2669-129 Light Kit

Lindale


P250028-028 Matte White



P250028-081 Antique Nickel



P250028-129 Architectural Bronze



LINDALE LIGHT KIT

P2669-028 Matte White
P2669-081 Antique Nickel
P2669-129 Architectural Bronze
24w LED Module, 3000K, 90 CRI,
2000 source lumens, dimmable.

JAB



P2669-28 P2669-81



P2669-129

ENERGY INFORMATION AT HIGH SPEED

Airflow	4,642 cubic feet per minute
Electricity Use	60 watts (excludes lights)
DOE Weighted CFM/W	87 CFM/W



Three-Speed Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited lifetime warranty
- Hugger low profile mounting
- AC Motor
- Reversible plywood blades
- Accepts P2669 light kit, sold separately.
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

SIZE


52" dia., 11-3/16" ht.
80" lead wires.




*Light kits only are JAB

52" Hugger Fan

P2525-09 Brushed Nickel




P2525-20 White



P2525-09 shown with P2610-09WB light kit* and with Cherry blades

* Light kit sold separately.



P2525-30 shown with White blades



P2525-09 shown with Cherry blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	3,229 cubic feet per minute
Electricity Use	56 watts (excludes lights)
DOE Weighted CFM/W	58 CFM/W

FEATURES

- 15-year limited warranty
- Hugger low profile mounting
- AC Motor
- Compatible with universal light kits
- Cannot be used with remote control
- Add a P2630-30 or P2630-95 wall control


SIZE

52" dia., 8-1/8" ht.




42" Hugger Fan

P2524-09 Brushed Nickel



P2524-30 White



P2524-30 shown with White blades



P2524-09 shown with P2602-09WB light kit* and with Natural Cherry blades

* Light kit sold separately.



P2524-09 shown with Natural Cherry blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	2,639 cubic feet per minute
Electricity Use	44 watts (excludes lights)
DOE Weighted CFM/W	72 CFM/W

FEATURES

- 15-year limited warranty
- Hugger low profile mounting
- AC Motor
- Compatible with universal light kits
- Cannot be used with remote control
- Add a P2630-30 or P2630-95 wall control


SIZE

42" dia., 8-5/16" ht.





Featuring 54" Patio Fan and Maison



Outdoor Ceiling Fans

Enhance outdoor living areas



Scan with your camera on your smartphone or visit www.progresslighting.com/ceilingfans



Montague
P2564-8030K

Relaxed 3

1 Organic Shapes

Beach Accents 2

Easy, Breezy, Coastal

with Dan



Dan McGinty
Product Designer

Bring your home right to the ocean side with beach-inspired accents, organic furnishings and an overall relaxed feel. Designers often create a relaxed and open environment with soft throw blankets, pillows, cozy rugs and cushioned furniture to complete the Coastal look. Focus on an all-white color palette for your coastal inspired home, while incorporating in soft beachy hues to complement the look.

When it comes to selecting materials for flooring, décor and furniture, seek out dark or weathered wood pieces to emulate a seaside environment nestled nicely by the shore.



Shop this style at
www.progresslighting.com/coastal



Midvale

FINISHES

- Matte White- 028
- Blistered Iron - 171
- Galvanized - 141

P250011-141-WB
shown with Galvanized Finish blades

Midvale offers a nostalgic appeal, with vintage-style LED bulbs inside a clear seeded glass shade, a rustic cage frame, and a banded metal ceiling canopy to complete the charming look.



Vintage Style

Nostalgic Appeal

Clear Seeded Glass



P250011-028-WB
shown with Matte White blades



P250011-141-WB
shown with Galvanized Finish blades



P250011-171-WB
shown with Blistered iron blades

Midvale


P250011-028-WB Matte White



P250011-141-WB Galvanized Finish



P250011-171-WB Blistered Iron



ENERGY INFORMATION AT HIGH SPEED

Airflow	7,627 cubic feet per minute
Electricity Use	84 watts (excludes lights)
DOE Weighted CFM/W	98 CFM/W

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- ABS blades
- Clear seeded glass shade
- Remote control with batteries is included
- Remote control may be replaced with the P2667-31 Wifi Remote

SIZE

56" dia., 20-3/8" ht.
80" lead wires.

LAMP

Two medium base 2700K 7w vintage LED lamps included. 600 lumens/lamp, 90 CRI, dimmable. 7w LED max/socket.



Remote Control Included
Three-speed fan operation
Full-range dimming for light




Rudder

FINISHES

- Matte White - 028
- Matte Black - 031
- Architectural Bronze - 129

P250040-028-30
shown with Distressed White blades

Transform any outdoor space into a cozy country abode with the charming rustic character of the Rudder collection. Four boat oar-inspired blades attach to a smooth center that features an LED light source for friendly illumination as needed. Available in a Matte White, Matte Black, or Architectural Bronze finish, Rudder is sure to fill your favorite patio or porch with a refreshing breeze wrapped in country character.



P250040-028-30
shown with Distressed White blades



P250040-031-30
shown with Distressed Ebony blades



P250040-129-30
shown with Walnut blades

Rudder

P250040-028-30 Matte White




Distressed White

P250040-031-30 Matte Black



Distressed Ebony

P250040-129-30 Architectural Bronze



Walnut

ENERGY INFORMATION AT HIGH SPEED

Airflow	6,112 cubic feet per minute
Electricity Use	35 watts (excludes lights)
DOE Weighted CFM/W	188 CFM/W



Full Function Remote Control Included
Six-speed fan operation
Full-range dimming for light
Reverse direction control

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- ABS blades
- Damp Location Rated
- White opal glass shade
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

SIZE

56" dia., 16-1/8" ht.
80" lead wires.

LAMP

24w LED Module, 3000K,
90 CRI, 2000 source lumens,
dimnable.



Edwidge

P250062-152-30
shown with Painted Nickel blades

FINISHES

- Matte White - 028
- Matte Black - 031
- Painted Nickel - 152

Edwidge cleverly houses the motor within the trio of fan blades providing a sleek, modern look. All-weather ABS fan blades and a non-metallic housing and canopy offer rust-proof, contemporary style to indoor and covered outdoor settings.

Modern Design

For Indoor & Outdoor Use

Dimmable LED Light

Edwidge

P250062-028-30 Matte White



P250062-031-30 Matte Black



P250062-152-30 Painted Nickel



P250062-028-30
shown with Matte White blades



P250062-031-30
shown with Matte Black blades



P250062-152-30
shown with Painted Nickel blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	5,874 cubic feet per minute
Electricity Use	20 watts (excludes lights)
DOE Weighted CFM/W	328 CFM/W

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- ABS blades
- Opal shatterproof shade
- Remote control with batteries is included

SIZE

52" dia., 13-9/16" ht.
80" lead wires.

LAMP

18w LED Module, 3000K, 90 CRI,
1400 source lumens, dimmable.



Full Function Remote Control Included
Six-speed fan operation
Full-range dimming for light
Reverse direction control



Edisto

FINISHES

- Forged Black - 80
- Antique Nickel - 81
- Architectural Bronze - 129

P2596-8030K
shown with Charcoal Canvas blades



Canvas Wrapped Blades

The Edisto 54" two-blade outdoor ceiling fan combines a sleek, contemporary style with high-quality performance. A wire frame supports canvas wrapped blades that feature UV inhibitors to protect the fabric from fading in the sunlight. Three fan speeds and a reversible switch keep individuals cool in the summer and warm in the winter. A white opal glass shade contains an 18W LED module light kit, offering energy efficient and cost savings benefits.

Contemporary Style

White Opal Glass Shade



P2596-8030K
shown with Charcoal Canvas blades




P2596-8130K
shown with Oatmeal Canvas blades



P2596-12930K
shown with Mushroom Canvas blades

Edisto


P2596-8030K Forged Black



P2596-8130K Antique Nickel



P2596-12930K Architectural Bronze



ENERGY INFORMATION AT HIGH SPEED

Airflow	4,371 cubic feet per minute
Electricity Use	65 watts (excludes lights)
DOE Weighted CFM/W	73 CFM/W



Three-Speed Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-18.5")
- AC Motor
- Canvas wrapped blades
- Damp Location Rated
- White opal glass shade
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

SIZE

54" dia., 14-7/8" ht.
80" lead wires.

LAMP

18w LED Module, 3000K,
90 CRI, 1400 source lumens,
dimmable.



The Living is Easy



1

2

3

Kick back and relax in a room that brings the outside in.

1

Choose a fan filled with style like Edisto, whose canvas-wrapped blades offset the sleek look of its forged black finish.

2

Use rough-hewn wooden beams to punctuate walls and ceiling with rustic style.

3

Incorporate organic touches of wood and rattan for comfortable, relaxation-ready seating.


Whirl

P2574-8130K
shown with Driftwood blades

FINISHES

- Antique Bronze - 20
- Forged Black - 80
- Antique Nickel - 81

Refresh your indoor or covered outdoor living spaces with the crisp, clean style of the 60" Whirl fan. The stylish design comes in Antique Nickel, Antique Bronze and Forged Black finish options. The five-blade fan features an all weather damp location rating to accommodate a variety of settings throughout the home.



Whirl

P2574-2030K Antique Bronze



Walnut

P2574-8030K Forged Black



Toasted Oak

P2574-8130K Antique Nickel



Driftwood

ENERGY INFORMATION AT HIGH SPEED

Airflow	6,549 cubic feet per minute
Electricity Use	70 watts (excludes lights)
DOE Weighted CFM/W	106 CFM/W

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-18.5°)
- AC Motor
- ABS all weather blades
- White Frosted Glass Shade
- Three speed pull-chain switch (fan)
- On/off pull-chain switch (light)
- Damp Location Rated
- Add a P2630-30 or P2630-95 wall control or P2662-01 hand-held remote control

SIZE

60" dia., 15-7/8" ht.
80" lead wires.

LAMP

18w LED Module, 3000K, 90 CRI, 1400 source lumens, dimmable (with added remote or wall control).



Relax All Year Long



Light-filled sunrooms offer the best of indoor-outdoor living.

1

Add a beautiful Whirl ceiling fan to move the air comfortably for ultimate relaxation.

2

Install multiple recessed fixtures to create the perfect ambiance for peaceful relaxation.

3

Accessorize with organic touches of wicker furniture topped with cozy cushions for a tranquil neutral color scheme.

Alfresco

FINISHES

- Architectural Bronze - 129
- Blistered Iron - 171

P250034-129-WB
shown with Dark Bamboo blades

Infuse a warm, nature-inspired style to your outdoor home décor with the one-of-a-kind Alfresco collection. Five blades decorated in a leaf-like design sprout from a dual mount center that artistically harbors an LED light source. Select from an Architectural Bronze and blistered iron finish to bring your bohemian dreamland to life.

Leaf-like Decorated Blades

Nature-Inspired Design

Dimmable LED Light

Alfresco

P250034-129-WB Architectural Bronze

 Dark Bamboo

P250034-171-WB Blistered Iron

 Pewter



P250034-129-WB
shown with Dark Bamboo blades



P250034-171-WB
shown with Pewter blades

ENERGY INFORMATION AT HIGH SPEED

Airflow 5,724 cubic feet per minute
Electricity Use 68 watts (excludes lights)
DOE Weighted CFM/W 90 CFM/W



Three-Speed Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- ABS blades
- Damp Location Rated
- Clear seeded glass
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

SIZE

54" dia., 19-1/4" ht.
80" lead wires.

LAMP

Two medium base 2700K 7w vintage LED lamps included. 600 lumens/lamp, 90 CRI, dimmable. 7w LED max/socket.



Smyrna

P2576-2030K
shown with Walnut blades

FINISHES

- Antique Bronze - 20
- Forged Black - 80

This 52" Smyrna ceiling fan features an LED light source, offering both form and function with energy and cost-savings benefits. The light kit contains a clear hammered glass shade and contains a 17W dimmable 3000K LED module. Includes a wall control switch for fan speed and light operation.



Traditional Style

Dimmable LED Light

Clear Hammered Glass Shade

Smyrna

P2576-2030K Antique Bronze



P2576-8030K Forged Black



P2576-2030K
shown with Walnut blades



P2576-8030K
shown with Toasted Oak blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	4,585 cubic feet per minute
Electricity Use	58 watts (excludes lights)
DOE Weighted CFM/W	91 CFM/W



Wall Control Included
Four-speed fan operation
Full-range dimming for light
Includes switch plate cover

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-30°)
- AC Motor
- ABS all weather blades
- Clear hammered glass shade
- Wet Location Rated

SIZE

52" dia., 19-1/2" ht.
80" lead wires.

LAMP

17w LED Module, 3000K,
90 CRI, 1400 source lumens,
dimmable.



Montague

FINISHES

- Antique Bronze - 20
- White - 30
- Forged Black - 80

P2564-8030K
shown with Toasted Oak blades

This five-blade 60" Montague ceiling fan features an all weather wet location rating to accommodate a variety of interior and exterior locations. The white opal glass shade contains a 18W dimmable, 3000K LED module, offering both form and function with energy and cost-savings benefits. A full function remote control is included.

Interior and Exterior Locations

Dimmable LED Light

White Opal Glass Shade

Montague

P2564-2030K Antique Bronze



P2564-3030K White



P2564-8030K Forged Black




P2564-2030K
shown with Walnut blades



P2564-3030K
shown with White blades



P2564-8030K
shown with Toasted Oak blades



Scan with the camera on your smartphone for the Montague installation video.

ENERGY INFORMATION AT HIGH SPEED

Airflow	6,693 cubic feet per minute
Electricity Use	75 watts (excludes lights)
DOE Weighted CFM/W	96 CFM/W



Full Function Remote Control Included
Three-speed fan operation
Full-range dimming for light
Reverse direction control

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-18.5")
- AC Motor
- White opal Glass Shade
- ABS all weather blades
- Wet Location Rated
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

SIZE

60" dia., 17-5/8" ht.
80" lead wires.

LAMP

18w LED Module, 3000K, 90 CRI, 1400 source lumens, dimmable.



Albin

P250036-129-30
shown with Distressed Walnut blades

FINISHES

- Matte White- 028
- Matte Black- 031
- Architectural Bronze - 129

The Albin collection offers a modern take on a traditional design that will be perfectly at home in so many outdoor spaces and lifestyles. Five blades finished with a faux wood grain texture extend from a modern-style center available in an Architectural Bronze, Satin White, or Matte Black finish. An LED light source is encased in a crisp shade to illuminate a patio or porch space that will beg to be lived in an enjoyed.

Faux Wood Grain Texture

Modern Style

Dimmable LED Light

Albin

P250036-028-30 Matte White



P250036-031-30 Matte Black



P250036-129-30 Architectural Bronze



P250036-028-30
shown with Matte White blades



P250036-031-30
shown with Toasted Oak blades



P250036-129-30
shown with Distressed Walnut blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	5,740 cubic feet per minute
Electricity Use	67 watts (excludes lights)
DOE Weighted CFM/W	95 CFM/W



Three Speed Remote Control Included
Three speed fan operation
Full range dimming with light

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Plywood blades
- Damp Location Rated
- White opal glass shade
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

SIZE

54" dia., 15-5/8" ht.
80" lead wires.

LAMP

24w LED Module, 3000K,
90 CRI, 2000 source lumens,
dimmable.



Lakehurst

FINISHES

- Antique Bronze - 20
- White - 30
- Forged Black - 80

P2562-20
shown with Walnut blades

This five-blade 60" Lakehurst ceiling fan features an all weather wet location rating (ABS) to accommodate a variety of interior and exterior locations. The Lakehurst fan will accept a universal outdoor rated light kit. Features a dual mount system and a three-speed pull chain fan switch.

Interior and Exterior Locations

Traditional Design

Dual Mount System



P2562-20
shown with Walnut blades



P2562-30
shown with White blades



P2562-80
shown with Toasted Oak blades

Lakehurst

P2562-20 Antique Bronze



Walnut

P2562-30 White



White

P2562-80 Forged Black



Toasted Oak

ENERGY INFORMATION AT HIGH SPEED

Airflow	6,440 cubic feet per minute
Electricity Use	71 watts (excludes lights)
DOE Weighted CFM/W	105 CFM/W

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-18.5")
- AC Motor
- ABS all weather blades
- Compatible with universal light kits
- 3 Speed pull chain switch
- Wet Location Rated
- Add a P2630-30 or P2630-95 wall control or P2662-01 hand-held remote control

SIZE

60" dia., 15-3/4" ht.
80" lead wires.



Decorative Patio Fan

P2526-20
shown with Washed Walnut blades


FINISH
● Antique Bronze - 20

52" Indoor/Outdoor five-blade fan with all-weather ABS blades in palm-style design and a rich Antique Bronze finish. Three-speed motor offers great performance and value that can be reversed to provide year-round comfort. Antique Brass pull chain with medium oak fob complements the Washed Walnut blades. The Patio fan will also accept a universal outdoor rated light kit.

Washed Walnut Blades

Antique Bronze Finish

Palm-Style Design



Decorative Patio Fan

P2526-20 Antique Bronze



P2526-20
shown with Washed Walnut blades



P2526-20
shown with P2636-20WB light kit*
and Washed Walnut blades
*Light kit sold separately.

ENERGY INFORMATION AT HIGH SPEED

Airflow	4,150 cubic feet per minute
Electricity Use	70 watts (excludes lights)
DOE Weighted CFM/W	77 CFM/W

FEATURES


- 15-year limited warranty
- 45° Canopy
- Close-to-ceiling installation
- SureConnect® System
- AC Motor
- ABS all-weather blades
- Compatible with universal light kits
- Damp location rated
- Add a P2630-30 or P2630-95 wall control or P2662-01 hand-held remote control

SIZE

52" dia., 17-3/8" ht.
(CTC 12-3/16 ht.),
80" lead wires.



CTC INSTALLATION



54" Patio Fan

FINISH

● Antique Bronze - 20

P2533-20 Antique Bronze

 Toasted Oak



P2533-20
shown with Toasted Oak blades
* Light kit sold separately.

ENERGY INFORMATION AT HIGH SPEED

Airflow 4,986 cubic feet per minute
Electricity Use 65 watts (excludes lights)
DOE Weighted CFM/W 74 CFM/W

FEATURES


- 30-year limited warranty
- 45° Canopy
- SureConnect® System
- AC Motor
- ABS all-weather blades
- Wet location rated
- Compatible with universal light kits
- Add a P2630-30 or P2630-95 wall control or P2662-01 hand-held remote control

SIZE

54" dia., 18-1/4" ht.
(CTC 12-3/16 ht.),
80" lead wires.



CTC INSTALLATION



52" Patio Fan


P2502-20 Antique Bronze

 Oak

P2502-80 Forged Black


 Toasted Oak

P2502-30 White

 White

P2502-141 Galvanized

 Silver



P2502-30
shown with White blades



P2502-80
shown with Toasted Oak blades



P2502-141
shown with Silver blades



P2502-20
shown with Oak blades

ENERGY INFORMATION AT HIGH SPEED

Airflow 4,991 cubic feet per minute
Electricity Use 64 watts (excludes lights)
DOE Weighted CFM/W 89 CFM/W

FEATURES



- 15-year limited warranty
- Dual Mount (flat or sloped ceiling-23°)
- Close-to-ceiling installation
- SureConnect® System
- Quick-Install canopy
- AC Motor
- ABS all-weather blades
- Compatible with universal light kits
- Three speed pull-chain switch
- Wet location rated
- Add a P2630-30 or P2630-95 wall control or P2662-01 hand-held remote control

SIZE

52" dia., 12-3/4" ht.
(CTC 9-11/16 ht.),
72" lead wires.




CTC INSTALLATION



Featuring 52" Patio Fan, Image: Arthur Rutenberg Homes



Featuring 52" Builder Fan with P2602-30WB Light Kit
Image: Kirbor Homes and Susan Wilson Interiors



Accessories

Accessorise your living area



Scan with your camera on
your smartphone or visit
www.progresslighting.com/ceilingfans



Spades
P2570-15

Minimal

1

2 *Sleek Details*

3
Glass Decor



James Thomas
Senior Product Designer


Modernly Minimalism with James

Modern interiors showcase sleek design through the use of neutrals, a minimalism approach, and the use of glass décor and technology. Take advantage of spaces with wide windows and use glass in other details such as countertops and furniture. This creates a sleek design for interior spaces. Integrate new innovations into a home's décor by adding elements, such as voice activated

devices and remote controlled light dimmers. To accentuate a Modern color palette, stick to neutral shades, as well as an overall minimalistic design to create this look.



Shop this style at
www.progresslighting.com/modern



Indoor/Outdoor

Universal-style with quick-connect wiring.

SCHOOLHOUSE

P2601-20WB Antique Bronze

P2601-30WB White

P2601-80WB Forged Black

P2601-141WB Galvanized

with opal glass.

8-1/2" dia., 7" ht.

One medium base 3000K 9w LED

lamp included. 800 lumens/lamp,

90 CRI. (dimmable) 10w LED or

60w incandescent max/socket.

Wet Location Rated.



LOW PROFILE

P2611-20WB Antique Bronze

P2611-30WB White

P2611-80WB Forged Black

with opal glass.

10-1/2" dia., 4-1/2" ht.

Two medium base 3000K 9w LED

lamps included. 800 lumens/lamp,

90 CRI. (dimmable) 10w LED or

60w incandescent max/socket.

Wet Location Rated.



ASHMORE

P2636-20WB Antique Bronze

with frosted seeded glass.

11" dia., 8-1/4" ht.

Two medium base 3000K 9w LED

lamps included. 800 lumens/lamp,

90 CRI. (dimmable) 10w LED or

60w incandescent max/socket.

Wet Location Rated.



All fixtures:



Springer

SPRINGER LIGHT KIT*

P260000-081-WB Antique Nickel

P260000-129-WB Architectural Bronze

P260000-31M-WB Matte Black

Two medium base 2700K 7w vintage

LED lamps included. 600 lumens/lamp,

90 CRI, dimmable. 7w LED max/socket.

*This light kit is ONLY compatible with the 52" Springer fan (P250065).



Torino

Universal-style light kit with quick-connect wiring.

P2645-01WB

with etched glass.

Included Finials:

-09 Brushed Nickel

-20 Antique Bronze

-80 Forged Black

12" dia., 5-3/4" ht.

Two medium base 3000K 9w LED

lamps included. 800 lumens/lamp,

90 CRI. (dimmable) 10w LED or

60w incandescent max/socket.

Indoor use only.



Gather, Bravo & Joy

Universal-style light kit with quick-connect wiring.

P2650-20TWB Antique Bronze

with tea-stained glass.

P2650-01WB

with etched glass.

Included Finials:

-09 Brushed Nickel

-20 Antique Bronze

11" dia., 5-1/2" ht.

Two medium base 3000K 9w LED

lamps included. 800 lumens/lamp,

90 CRI. (dimmable) 10w LED or

60w incandescent max/socket.

Indoor use only.



Madison

Universal-style with quick-connect wiring.

P2623-09WB Brushed Nickel

P2623-20WB Antique Bronze

with etched glass.

19" dia., 8" ht.

Three medium base 3000K 9w LED

lamps included. 800 lumens/lamp,

90 CRI. (dimmable) 10w LED or

60w incandescent max/socket.

Indoor use only.



Universal Bowl

Universal-style with quick-connect wiring.

P2612-01WB

with alabaster glass.
Included Finials:
-09 Brushed Nickel
-031 Matte Black
-20 Antique Bronze
-30 White
-15 Polished Chrome
-143 Graphite
10-3/4" dia., 5-1/2" ht.
Two medium base 3000K 9w LED lamps included. 800 lumens/lamp, 90 CRI. (dimnable) 10w LED or 60w incandescent max/socket. Indoor use only.



Wisten

Universal-style light kit with quick-connect wiring.

P2649-01WB

with etched glass.
Included Finials:
-09 Brushed Nickel
-20 Antique Bronze
11" dia., 6-1/4" ht.
Two medium base 3000K 9w LED lamps included. 800 lumens/lamp, 90 CRI. (dimnable) 10w LED or 60w incandescent max/socket. Indoor use only.




Clifton Heights

Universal-style with quick-connect wiring.

P2654-01WB

with etched glass.
Included Finials:
-09 Brushed Nickel
-20 Antique Bronze
12-1/2" sq., 6-1/4" ht.
Two medium base 3000K 9w LED lamps included. 800 lumens/lamp, 90 CRI. (dimnable) 10w LED or 60w incandescent max/socket. Indoor use only.



LED Light Kits

Universal-style with quick connect wiring.

P2659-09

Brushed Nickel
P2659-20 Antique Bronze
P2659-30 White
with etched white glass.
12-1/4" dia., 4" ht.
One 16w, 3000K LED module included.
1265 source lumens, 90 CRI. Indoor use only. (dimnable)



P2660-01

with etched alabaster glass.
Included Finials:
-09 Brushed Nickel
-20 Antique Bronze
-30 White
11-1/4" dia., 5-3/8" ht.
One 16w, 3000K LED module included.
1241 source lumens, 1150 delivered lumens, 90 CRI. Indoor use only. (dimnable)



All fixtures:



Trinity

Universal-style with quick-connect wiring.

P2628-01WB

with etched glass.
Included Finials:
-09 Brushed Nickel
-031 Matte Black
-20 Antique Bronze
-30 White
13-3/8" dia., 6-3/8" ht.
Two medium base 3000K 9w LED lamps included. 800 lumens/lamp, 90 CRI. (dimnable) 10w LED or 60w incandescent max/socket. Indoor use only.



Four Light Universal

Universal-style with quick-connect wiring.


P2643-09WB Brushed Nickel
P2643-20WB Antique Bronze
P2643-30WB White
 with alabaster glass.
 13-5/8" dia., 7-3/4" ht.
 Four medium base 3000K
 9w LED lamps included.
 800 lumens/lamp, 90 CRI.
 (dimnable) 10w LED or 60w
 incandescent max/socket.
 Indoor use only.



Three Light Universal

Universal-style with quick-connect wiring.

P2642-09WB Brushed Nickel
P2642-30WB White
 with alabaster glass.
 13-5/8" dia., 7-3/4" ht.
 Three medium base 3000K
 9w LED lamps included.
 800 lumens/lamp, 90 CRI.
 (dimnable) 10w LED or 60w
 incandescent max/socket.
 Indoor use only.



Low Profile

Universal-style with quick-connect wiring.

P2602-09WB Brushed Nickel
P2602-15WB Polished Chrome
P2602-20WB Antique Bronze
P2602-30WB White
P2602-143WB Graphite
 with white opal glass.
 10-1/2" dia., 4-1/2" ht.
 Two medium base 3000K
 9w LED lamps included.
 800 lumens/lamp, 90 CRI.
 (dimnable) 10w LED or 60w
 incandescent max/socket.
 Indoor use only.



Four Light Alabaster

Spring clip glass attachment. For use with P2500, P2501, P2502, P2524 and P2525.

P2610-09WB Brushed Nickel
P2610-15WB Polished Chrome
P2610-20WB Antique Bronze
P2610-30WB White
P2610-143WB Graphite
 with alabaster glass.
 14-1/2" dia., 6-1/4" ht.
 Four medium base 3000K
 9w LED lamps included.
 800 lumens/lamp, 90 CRI.
 (dimnable) 10w LED or 60w
 incandescent max/socket.
 Indoor use only.



Three Light Alabaster

Spring clip glass attachment. For use with P2500, P2501, P2502, P2524 and P2525.

P2600-09WB Brushed Nickel
P2600-20WB Antique Bronze
P2600-30WB White
 with alabaster glass.
 15" dia., 6-5/8" ht.
 Three medium base 3000K
 9w LED lamps included.
 800 lumens/lamp, 90 CRI.
 (dimnable) 10w LED or 60w
 incandescent max/socket.
 Indoor use only.



Schoolhouse

Universal-style with quick-connect wiring.

P2644-09WB Brushed Nickel
P2644-30WB White
 with white opal glass.
 8-1/2" dia., 6-1/2" ht.
 One medium base 3000K 9w LED
 lamp included. 800 lumens/lamp,
 90 CRI. (dimnable) 10w LED or
 60w incandescent max/socket.
 Indoor use only.



Accessory Downrods


3/4" diameter; approximately 1" outside diameter.

CEILING HT.	9'-10'	10'-11'	11'-12'	12'-14'	13'-15'	14'-16'	15'-17'
DOWNROD L.	12"	18"	24"	36"	48"	60"	72"
Brushed Nickel -9	P2603-09	P2604-09	P2605-09	P2606-09	P2607-09	P2608-09	P2609-09
Polished Chrome -15	P2603-15	P2604-15	P2605-15	P2606-15	P2607-15	P2608-15	P2609-15
Antique Bronze -20	P2603-20	P2604-20	P2605-20	P2606-20	P2607-20	P2608-20	P2609-20
Matte White -28	P2603-28	P2604-28	P2605-28	P2606-28	P2607-28	P2608-28	P2609-28
White -30	P2603-30	P2604-30	P2605-30	P2606-30	P2607-30	P2608-30	P2609-30
Matte Black -31	P2603-31	P2604-31	P2605-31	P2606-31	P2607-31	P2608-31	P2609-31
Guided Iron -71	P2603-80	P2604-80	P2605-80	P2606-80	P2607-80	P2608-80	P2609-80
Forged Bronze -77			P2605-77				P2609-77
Forged Black -80	P2603-80	P2604-80	P2605-80	P2606-80	P2607-80	P2608-80	P2609-80
Antique Nickel -81	P2603-81	P2604-81	P2605-81	P2606-81	P2607-81	P2608-81	P2609-81
Oil Rubbed Bronze -108	P2603-20	P2604-20	P2605-20	P2606-20	P2607-20	P2608-20	P2609-20
Architectural Bronze -129	P2603-20	P2604-20	P2605-20	P2606-20	P2607-20	P2608-20	P2609-20
Galvanized -141	P2603-141	P2604-141	P2605-141	P2606-141	P2607-141	P2608-141	P2609-141
Graphite -143	P2603-143	P2604-143	P2605-143	P2606-143	P2607-143	P2608-143	P2609-143
Painted Nickel -152	P2603-152	P2604-152	P2605-152	P2606-152	P2607-152		
Vintage Brass -163	P2603-163	P2604-163	P2605-163	P2606-163	P2607-163		
Blistered Iron -171	P2603-171	P2604-171	P2605-171	P2606-171	P2607-171		
Black Chrome -231	P2603-231	P2604-231	P2605-231	P2606-231	P2607-231		

Downrod Selection Guide

Allow at least 7 feet (84 in.) from the floor to the bottom of the fan, with 8 or 9 feet being the ideal above-floor placement.

*Average length downrod, included with each fan.



Remotes, Wall Controls & 45° Canopies



P2662-01
Fan/Light Remote
Universal remote operates three fan speeds and full-range dimming light control. Includes canopy receiver and wall storage bracket. Will work with LED lamps and modules. Featuring four "dip" switches and 16 code options to avoid the chance of interference from other remotes.



P2663-01
Fan/Light Remote
Universal remote with two, four or eight-hour timer option, operates three fan speeds and full-range dimming light control. Includes canopy receiver and wall storage bracket. Will work with LED lamps and modules. Featuring many code combination options to avoid the chance of interference from other remotes.



P2618-01
Fan/Light Remote
Provides fan speed and light control from convenient hand-held remote. Compatible with non-dimmable compact fluorescent lamps. For single pole applications. Receiver fits in fan canopy.



P2661-01
Universal Fan/Light Remote
Provides fan speed and full range light dimming control from a convenient hand held remote control. For single pole applications. Includes a wall plate for added storage convenience. Receiver fits in the fan canopy.



P2667-31
Wifi Fan/Light Remote
Universal Wifi remote control for AC motor fans. Control your ceiling fan or light kit via Wifi from anywhere. Pairs with Alexa, Google Home, or app on your phone or tablet. Voice control the fan with three speeds and the light with full range dimming. App control the fan with three speeds or four timer selections or full range dimming control of the light. Can be controlled with the hand held remote included with the kit.



P2665-30 White
Universal remote includes a wall mount transmitter, ideal for multi-family applications, that operates three fan speeds and full-range dimming light control. Includes canopy receiver and wall storage bracket. Will work with LED lamps and modules. Featuring four "dip" switches and 16 code options to avoid the chance of interference from other remotes.



P2631-30 White
Full-function wall control transmitter (receiver sold with ceiling fan). Use with, or in place of, hand-held remote included with fans that have a downlight. Includes switch plate cover.



P2630-95 Ivory
Four-speed fan wall control with full-range light dimmer. Fits single-gang wall box; requires two circuits. Includes switch plate cover. Not for use with multiple fans.



P2673-01
DC Fan Wi-Fi Module
Add the Wi-Fi module to your Ryne ceiling fan for control at your fingertips. You can easily control your fan with a hand-held remote; or a smart phone, tablet, voice assistant (Amazon Alexa and Google Home) via the Smart By Bond app.



P2630-30 White
Four-speed fan wall control with full-range light dimmer. Fits single-gang wall box; requires two circuits. Includes switch plate cover. Not for use with multiple fans.



P2613-95 Ivory
Four-speed fan wall control. Includes switch plate cover. Not for use with multiple fans.



P2613-30 White
Four-speed fan wall control. Includes switch plate cover. Not for use with multiple fans.



P2666-09
Brushed Nickel
45° canopy*

P2666-30 White
45° canopy*


P2666-129
Architectural Bronze
45° canopy*

*This accessory is for use with the following ceiling fan models only: P2501, P2503, P2521, P2536, P2530, P2531, P2533, and P2539. Includes ceiling bracket, canopy, hanger ball, trim ring, and CTC mounting hardware.

Cross Reference Chart

Here's where you'll find the specifications you'll need to purchase the perfect fan for your space. Search by Model Number, Name or Page Number.

Fan Diagram Reference:



Model #	Model Name	Page	Motor (MM)	Motor Type AC or DC	Fan Diameter	Blade Pitch	Dimensions				Accepts Longer Downrods	Energy Star	Remotes				P2667-31 Wifi Remote Control		P2630-30 P2630-95	P2613-01 P2613-95	Universal Light Kit	
							A	B	C	D			P2661-01	P2662-01	P2663-01	P2618-01	P2665-30	P2631-30				
P250000	Springer	46	DC-165	DC	60"	22°	17.38"	13.19"	8.38"	6.06"	Yes	No										
P250002	Farris	66	DC-125N	DC	60"	18°-13°	15.63"	12.5"	7.5"	5.13"	Yes	No										
P250003	Kaysville	48	178 X 22	DC	56"	15°	17.25"	13.25"	9.94"	6.44"	Yes	No										
P250004	Teasley	80	188 X 15	AC	56"	12.5°	22.44"	12.56"	10.88"	6.44"	Yes	No	X	X	X	X	X	X		X	X	
P250006	Loring	36	120 X 20	AC	33"	13.5°	15.19"	9.02"	6.06"	7.73"	No	No	X	X	X	X	X	X		X	X	
P250007	Claret	102	153 X 20	AC	54"	14°	15.13"	10.50"	7.88"	5.88"	Yes	No	X	X	X	X	X	X		X	X	
P250008	Drift	142	153 X 12	AC	32"	13°	14.38"	11.75"	9.25"	5.9"	Yes	No	X	X	X	X	X	X		X	X	X
P250009	Alleron	50	178 X 12	DC	56"	15°	15.94"	11.38"	9.31"	5.88"	Yes	No										
P250010	Royer	82	172 X 20	AC	56"	13°	17.82"	16.39"	10.31"	5.13"	Yes	No	X	X	X	X	X	X		X	X	
P250011	Midvale	158	188 X 25	AC	56"	13°	20.88"	12.81"	10.06"	6.44"	Yes	No	X	X	X	X	X	X		X	X	
P250012	Gulliver	34	N/A	AC	23"	N/A	18.13"	N/A	5.75"	7.31"	Yes	No	X	X	X	X	X	X		X	X	
P250016	Edgefield	134	DC-125N	DC	52"	13°	14.44"	12.5"	11.0"	5.18"	Yes	Yes										X
P250021	Glenfalls	100	188 X 22	AC	56"	13°	14.88"	12.88"	8.75"	5.18"	Yes	No	X	X	X	X	X	X		X	X	
P250022	Chapin	90	188 X 22	AC	54"	14°	15.88"	14.45"	9.75"	5.18"	Yes	No	X	X	X	X	X	X		X	X	X
P250024	Bedwin	92	DC-125N	DC	54"	14°	15.44"	12.25"	8.69"	5.18"	Yes	No										X
P250026	Arlo	62	DCI53-20NS	DC	60"	13°	18.56"	14.0"	8.25"	5.18"	Yes	No										
P250028	Lindale	150	153 X 18	AC	52"	13°	11.19"	8.0"	8.25"	5.96"	No	No	X	X	X	X	X		X	X	X	
P250030	Huff	56	DCI68-25NS	DC	96"	14°	15.44"	12.0"	11.63"	6.25"	Yes	No										X
P250032	Holland	76	DCI53-10NS	DC	60"	23°	16.63"	13.56"	8.56"	5.12"	Yes	No										
P250034	Alfresco	172	188 X 15	AC	54"	13°	19.25"	11.88"	12.0"	5.94"	Yes	No	X	X	X	X	X	X		X	X	
P250036	Albin	178	172 X 17	AC	54"	13°	15.63"	10.62"	11.01"	6.31"	Yes	No	X	X	X	X	X	X		X	X	
P250038	Bixby	64	DCI25-30NS	DC	60"	18°	17.69"	15.12"	6.93"	5.19"	Yes	No										
P250040	Rudder	160	DCI53-10NS	DC	56"	14°	16.01"	12.0"	9.13"	6.31"	Yes	No										
P250058	Braden	144	153 X 15	AC	44"	13°	9.81"	7.23"	7.70"	7.70"	No	No	X	X	X	X	X		X	X	X	
P250059	Vernal	24	156 X 12	DC	60"	12°	14.25"	9.60"	N/A	7.00"	Yes	No										
P250060	Ryne	26	156 X 8	DC	52"	12°	13.63"	9.60"	N/A	7.00"	Yes	No										
P250062	Edwidge	162	100 X 30	DC	52"	13°	13.55"	7.35"	N/A	5.75"	Yes	No										
P250063	Willacy	28	100 X 30	DC	48"	13°	14.52"	12.78"	6.14"	6.87"	No	No										
P250065	Springer 52"	42	165NL	DC	52"	22°	17.38"	13.19"	8.38"	6.06"	Yes	No										
P250066	Air Pro E Star	136	172 X 17	AC	52"	12°	13.06"	10.02"	11.0"	5.87"	Yes	Yes	X	X	X	X	X	X		X	X	X
P250067	Brairwood	30	N/A	AC	22"	N/A	15.63"	N/A	22"	7.31"	Yes	No	X	X	X	X	X	X		X	X	
P250068	Belva	32	N/A	AC	25.25"	N/A	17.75"	N/A	25.25"	7.31"	Yes	No	X	X	X	X	X	X		X	X	
P2500	Builder	139	153 X 10	AC	42"	12°	12.25"	9.65"	9.5"	5.13"	Yes	No	X	X	X	X	X	X		X	X	X

*Highlighted cells = Control does not include reverse function

Continued on following spread.

Cross Reference Chart continued

*Highlighted cells = Control does not include reverse function

Model #	Model Name	Page	Motor (MM)	Motor Type AC or DC	Fan Diameter	Blade Pitch	Dimensions				Accepts Longer Downrods	Energy Star	Remotes				P2667-31 Wifi Remote Control	P2665-30	P2631-30	P2630-30 P2630-95	P2613-01 P2613-95	Universal Light Kit
							A	B	C	D			P2661-01	P2662-01	P2663-01	P2618-01						
P2501	Builder	141	153 X 12	AC	52"	11°	12.71"	9.58"	11.0"	5.13"	Yes	No	X	X	X	X	X	X	X	X	X	
P2502	52" Patio Fan	184	153 X 17	AC	52"	11°	12.75"	10.2"	11.75"	5.13"	Yes	No	X	X	X	X	X	X	X	X	X	
P2503	Performance	138	188 X 15	AC	52"	14°	15.25"	12.56"	12.19"	6.5"	Yes	No	X	X	X	X	X	X	X	X	X	
P2521	Signature	124	153 X 18	AC	52"	12°	14.63"	11.5"	11.75"	6.5"	Yes	No	X	X	X	X	X	X	X	X	X	
P2524	Hugger	153	153 X 10	AC	42"	11°	8.31"	5.5"	10.0"	10.0"	No	No						X	X	X	X	
P2525	Hugger	152	153 X 13	AC	52"	11°	8.13"	5.93"	11.06"	11.06"	No	No						X	X	X	X	
P2526	Deco Patio Fan	182	188 X 20	AC	52"	12°	17.38"	14.25"	12.13"	6.5"	Yes	No	X	X	X	X	X	X	X	X	X	
P2530	Signature Plus	131	153 X 18	AC	54"	12°	15.13"	10.4"	11.8"	6.5"	Yes	No	X	X	X	X	X	X	X	X	X	
P2531	Clifton Heights	132	153 X 18	AC	52"	12.5°	15.75"	12.7"	7.88"	6.5"	Yes	No	X	X	X	X	X	X	X	X	X	
P2533	54" Patio Fan	184	153 X 18	AC	54"	12°	18.75"	13.34"	11.38"	6.5"	Yes	No	X	X	X	X	X	X	X	X	X	
P2539	Signature Plus II	130	153 X 18	AC	54"	12°	15.3"	11.2"	11.8"	6.5"	Yes	No	X	X	X	X	X	X	X	X	X	
P2540	Harranvale	98	153 X 20	AC	54"	12°	16.38"	12.1"	12.63"	5.88"	Yes	No	X	X	X	X	X	X	X	X	X	
P2542	Soar	96	153 X 20	AC	54"	12°	14.7"	11.05"	10.1"	5.88"	Yes	No	X	X	X	X	X	X	X	X	X	
P2544	Graceful	104	153 X 20	AC	54"	12°	16.38"	11.5"	9.75"	5.88"	Yes	No	X	X	X	X	X	X	X	X	X	
P2546	Ellwood	52	212 X 25	AC	68"	17°	16.7"	11.5"	9.63"	5.88"	Yes	No	X	X	X	X		X	X	X	X	
P2548	Fresno	114	188 X 25	AC	60"	14°	17.2"	10.8"	12.75"	5.88"	Yes	No	X	X	X	X		X	X	X		
P2550	Vast	58	DC - 165	DC	72"	14°	16.75"	13.67"	8.25"	5.13"	Yes	No										
P2552	Billows	120	153 X 15	AC	52"	12°	17.5"	11.18"	9.1"	5.88"	Yes	No	X	X	X	X	X	X	X	X	X	
P2553	Trevina II	127	153 X 15	AC	52"	12°	15.75"	10.8"	9.44"	5.88"	Yes	No	X	X	X	X	X	X	X	X	X	
P2554	Gaze	70	172 X 17	AC	60"	12°	13.13"	10.71"	6.88"	5.13"	Yes	No	X	X	X	X	X	X	X	X	X	
P2555	Trevina II	126	153 X 12	AC	44"	12°	15.68"	12.21"	8.38"	5.88"	Yes	No	X	X	X	X	X	X	X	X	X	
P2556	Trevina II	127	153 X 15	AC	52"	12°	15.75"	10.8"	9.44"	5.88"	Yes	No	X	X	X	X	X	X	X	X	X	
P2558	Verada	118	153 X 18	AC	52"	12°	16.56"	10.1"	10.19"	5.88"	Yes	No	X	X	X	X	X	X	X	X	X	
P2560	Caleb	54	212 X 25	AC	68"	17°	18.0"	11.98"	13.75"	5.88"	Yes	No	X	X	X	X		X	X	X	X	
P2562	Lakehurst	180	188 X 25	AC	60"	13.5°	15.69"	13.5"	11.25"	5.9"	Yes	No	X	X	X	X	X	X	X	X	X	
P2564	Montague	176	188 X 25	AC	60"	13°	17.63"	12.28"	9.95"	5.9"	Yes	No	X	X	X	X	X	X	X	X	X	
P2568	Kudos	112	172 X 17	AC	52"	13°	17.63"	13.11"	9.69"	5.95"	Yes	No	X	X	X	X	X	X	X	X	X	
P2570	Spades	72	DC188-10	DC	56"	22°	18.13"	16.67"	8.08"	6.42"	Yes	No										
P2572	Vox	148	153 X 18	AC	52"	12°	11.63"	7.13"	11.41"	9.91"	No	No	X	X	X	X		X	X	X		
P2574	Whirl	168	188 X 25	AC	60"	12°	15.88"	11.93"	10.01"	5.91"	Yes	No	X	X	X	X	X	X	X	X	X	
P2576	Smyrna	174	153 X 20	AC	52"	12°	19.44"	10.75"	11.94"	5.88"	Yes	No	X	X	X	X	X	X	X	X	X	
P2578	Tempt	116	153 X 18	AC	52"	12°	16.19"	9.94"	10.25"	5.88"	Yes	No	X	X	X	X	X	X	X	X	X	
P2582	Gust	108	172 X 20	AC	54"	13.5°	16.0"	13.13"	9.95"	5.91"	Yes	No	X	X	X	X	X	X	X	X	X	
P2584	Greer	88	153 X 20	AC	54"	12°	21.56"	11.61"	7.88"	5.88"	Yes	No	X	X	X	X	X	X	X	X	X	
P2586	Glandon	84	188 X 25	AC	60"	12°	17.06"	13.09"	9.06"	5.88"	Yes	No	X	X	X	X	X	X	X	X	X	
P2588	Braden	146	172 X 20	AC	56"	13°	9.81"	7.23"	7.70"	7.70"	No	No	X	X	X	X		X	X	X		
P2590	Shaffer	94	188 X 20	AC	56"	13.5°	16.31"	12.65"	10.16"	6.25"	Yes	No	X	X	X	X	X	X	X	X	X	
P2592	Oriole	78	172 X 20	AC	60"	21°	14.56"	12.5"	9.17"	6.0"	Yes	No	X	X	X	X	X	X	X	X	X	
P2594	Sanford	38	N/A	AC	23"	31.7°	17.69"	13.13"	22.81"	5.12"	Yes	No	X	X	X	X	X	X	X	X	X	
P2596	Edisto	164	172 X 17	AC	54"	20°	14.88"	9.85"	11.01"	5.91"	Yes	No	X	X	X	X	X	X	X	X	X	
P2598	Olson	106	172 X 20	AC	52"	13.5°	19.94"	8.75"	9.30"	6.0"	Yes	No	X	X	X	X	X	X	X	X	X	
P2599	Uni Pack	140	153 X 12	AC	52"	11°	17.56"	9.58"	11.0"	5.13"	Yes	No	X	X	X	X	X	X	X	X	X	

Fan Blade Finishes



American Walnut



Charcoal Fabric




Dark Walnut




Antique Bronze




Cherry



Distressed Ebony




Architectural Bronze



Chestnut




Distressed Walnut



Black




Classic Walnut



Distressed White




Black Metallic



Dark Bamboo



Driftwood




Brushed Nickel



Dark Cherry



Galvanized



Graphite



Oak



Washed Oak



Gray Weathered Wood



Oatmeal Fabric




Washed Walnut



Medium Cherry



Pewter



White




Medium Oak




Silver



White Barnwood




Mushroom Fabric



Toasted Oak



White Metallic



Natural Cherry



Walnut



White Washed



All finish representations are part of Progress Lighting's comprehensive design and specification program. Through extensive research, these finishes have been carefully chosen to complement all Progress Lighting products, including our extensive range of materials and accessory options.

These finish representations match actual finish colors as accurately as possible, and while every effort has been made to render colors accurately, they may vary slightly from the actual product, especially hand-painted finishes due to the nature of hand craftsmanship.

Symbol Legend



Products referencing this logo meet the energy efficiency requirements for light fixtures set forth in ENERGY STAR® product specifications. Please refer to www.energystar.gov for specific product qualifications and list of certified products.



Please note indoor only (dry location) fans should only be used indoors. Even if an outdoor area or screened-in porch is covered, the motor and the blades can be affected when exposed to humidity. You can, however, “bring the outdoors inside” – as using outdoor ceiling fans are perfectly acceptable to use in interior spaces.



If you are selecting a ceiling fan for a space that is outdoors and under a roof, i.e. any covered porches; you should select either a damp rated or wet listed fan. Damp location fans may also be used indoors.



If the fan comes directly into contact with water, you'll need to ensure that the ceiling fan has a “wet” listing. Ceiling fans designed for damp or wet locations feature elements, such as moisture-resistant motors and all weather blades. Wet location fans may also be used indoors.



This marking indicates fixtures that have an integrated LED or replaceable LED module that has been tested and listed in the California Appliance Database. Check for certified lamps, fixtures or LED light engines by searching the MAEDBS database. Go to cacertappliances.energ.ca.gov



Complies with “American with Disabilities Act”



Table 150.0A defines products that do not have to meet JA8 and can be used to comply with 2016 Title 24. The most common types include:

- Pin-based linear or compact fluorescent light sources using electronic ballasts
- GU-24 sockets containing light sources other than LEDs
- Inseparable SSL luminaires that are installed outdoors



Products comply with the California Appliance Efficiency Regulations. Certified products are listed on the appliance efficiency database found at www.appliances.energy.ca.gov.



Products with this icon are Dark-Sky Friendly: they are certified by the International Dark-Sky Association to minimize glare while reducing light trespass and skyglow (they don't pollute the night sky.)



The products with this logo have passed the cUL requirements and are available for sale in Canada. These products include the additional safety features needed to comply with the regulations in Canada. Items with the icon are listed with NRCAN.



Products with this icon are compatible with our P2667-31 wi-fi control. Easily control your fan with your smart phone, tablet, voice controls or a hand-held remote. Use the Smart by Bond technology to control: on/off function of the fan and light kit, full range dimming, 3 fan speeds, breeze mode and 3 timer settings.



Wifi included

Warranty

For more details regarding product warranty coverage, please consult a qualified Progress Lighting distributor or visit:

www.progresslighting.com/warranty

Where to buy

To purchase Progress Lighting products from one of our authorized dealers visit:

www.progresslighting.com/where-to-buy



Featuring Glandon,
Image: Dostie Homes and Jessie Preza Photography

Equip. Educate. Excite.

These three words define the mission of Progress Lighting. Flip through our catalog, and you'll quickly see how we equip you with the education to make all your exciting design dreams come true. Not sure where to start? Whether you're browsing our catalog or visiting our website, Progress is at your service to help you envision where and how to use our products.

Experience Progress

Learn how lighting can totally transform a space. Experience Progress features beautiful room images from our builder partners, design firms, social media fans and influencers bringing the Progress Lighting story to life. Visit www.progresslighting.com/experienceprogress

Our Blog

Explore our blog for even more design inspiration, product integration and trend guidance to make your home into a haven of livable luxury. See www.progresslighting.com/blog

Be Inspired

- @ProgressLtg
- @ProgressLtg
- @ProgressLighting
- @ProgressLtg
- Progress Lighting
- Progress-Lighting
- #ProgressLightingMoments

See Yourself Here

Every home and every family has a story that's all their own. In this issue, we introduce you to the many ways Progress Lighting can bring that story to life.



PROGRESS LIGHTING

701 Millennium Boulevard
Greenville, SC 29607

www.progresslighting.com

