



# CEILING FAN CATALOG 2022

**PROGRESS**  
LIGHTING™



See Yourself Here.

Lighting helps tell a story, whether it's setting the mood or enjoying a special moment. These occasions are meaningful, expressive, and shared with those we care about most. Let Progress be your guide in illuminating these spaces into special places.

# Table of Contents

Fan Inspiration 7

Our ceiling fans do more than cool a room - they combine beautiful design with premium performance. Choose from fans that make a statement across a variety of design trends, from simple to spectacular.

Accessories 90

Downrods 90

Remotes 91

Blade Finishes 92







Indoor Fans 14



Outdoor Fans 76




























## Be Inspired





-  @ProgressLtg
-  @ProgressLtg
-  @ProgressLighting
-  @ProgressLtg
-  Progress Lighting
-  Progress-Lighting



# Indoor Ceiling Fans

<b>ALLERON</b> Antique Nickel p.45 	<b>ALLERON</b> Flat Black p.44 	<b>ARLO</b> Architectural Bronze p.49 	<b>ARLO</b> Black p.49 	<b>ARLO</b> Brushed Nickel p.48 
<b>BEDWIN</b> Antique Nickel p.62 	<b>BEDWIN</b> Galvanized p.63 	<b>BEDWIN</b> Graphite p.63 	<b>BELVA</b> Matte Black p.26 	<b>BELVA</b> Cottage White p.27 
<b>BIXBY</b> Black Chrome p.50 	<b>BIXBY</b> White p.51 	<b>44" BRADEN</b> Brushed Nickel p.72 	<b>44" BRADEN</b> Matte Black p.72 	<b>44" BRADEN</b> Matte White p.72 
<b>BRADEN</b> Architectural Bronze p.75 	<b>BRADEN</b> Brushed Nickel p.75 	<b>BRADEN</b> Polished Chrome p.74 	<b>BRIARWOOD</b> Antique Bronze p.24 	<b>BRIARWOOD</b> Galvanized p.25 
<b>BRIARWOOD</b> Graphite p.25 	<b>BRIARWOOD</b> Matte Black p.25 	<b>CLARET</b> Brushed Nickel p.67 	<b>CLARET</b> Matte Black p.67 	<b>CLARET</b> Oil Rubbed Bronze p.66 

# Indoor Ceiling Fans

<b>FARRIS</b> Brushed Nickel p.53 	<b>FARRIS</b> Graphite p.53 	<b>FARRIS</b> Oil Rubbed Bronze p.52 	<b>GLENFALLS</b> Brushed Nickel p.65 	<b>GLENFALLS</b> Matte White p.64 
<b>GLENFALLS</b> Matte Black p.65 	<b>GULLIVER</b> Galvanized p.28 	<b>GULLIVER</b> Graphite p.29 	<b>HOLLAND</b> Black p.63 	<b>HOLLAND</b> Brushed Nickel p.56 
<b>HOLLAND</b> Oil Rubbed Bronze p.57 	<b>HUFF</b> Black p.51 	<b>HUFF</b> Brushed Nickel p.46 	<b>HUFF</b> Matte White p.47 	<b>KAYSVILLE</b> Antique Nickel p.42 
<b>KAYSVILLE</b> Graphite p.43 	<b>LORING</b> Galvanized p.31 	<b>LORING</b> Matte Black p.30 	<b>ORIOLE</b> Architectural Bronze p.58 	<b>ORIOLE</b> Black p.59 
<b>ORIOLE</b> Brushed Nickel p.59 	<b>ROYER</b> Antique Nickel p.61 	<b>ROYER</b> Forged Black p.60 	<b>RYNE</b> Matte White p.21 	<b>RYNE</b> Matte Black p.20 

# Indoor Ceiling Fans

<b>RYNE</b> Koa Woodgrain p.21 	<b>SANFORD</b> Architectural Bronze p.32 	<b>SANFORD</b> Brushed Nickel p.33 	<b>52" SPRINGER</b> Antique Nickel p.36 	<b>52" SPRINGER</b> Architectural Bronze p.37 
<b>52" SPRINGER</b> Matte Black p.37 	<b>60" SPRINGER</b> Antique Nickel p.41 	<b>60" SPRINGER</b> Architectural Bronze p.41 	<b>60" SPRINGER</b> Matte Black p.40 	<b>TREVINA II 44"</b> Black p.69 
<b>TREVINA II 44"</b> Brushed Nickel p.68 	<b>TREVINA II 44"</b> Satin White p.69 	<b>VERNAL</b> Matte Black p.19 	<b>VERNAL</b> Painted Nickel p.19 	<b>VERNAL</b> Koa Woodgrain p.18 
<b>WILLACY</b> Matte Black p.23 	<b>WILLACY</b> Painted Nickel p.22 			

# Outdoor Ceiling Fans

<b>ALBIN</b> Architectural Bronze p.88 	<b>ALBIN</b> Matte Black p.89 	<b>ALBIN</b> Matte White p.89 	<b>ALLERON</b> Antique Nickel p.45 	<b>ALLERON</b> Flat Black p.44 
<b>ALFRESCO</b> Architectural Bronze p.86 	<b>ALFRESCO</b> Blistered Iron p.87 	<b>ARLO</b> Architectural Bronze p.49 	<b>ARLO</b> Black p.49 	<b>ARLO</b> Brushed Nickel p.48 
<b>BELVA</b> Matte Black p.26 	<b>BELVA</b> Cottage White p.27 	<b>BIXBY</b> Black Chrome p.50 	<b>BIXBY</b> White p.51 	<b>BRIARWOOD</b> Antique Bronze p.24 
<b>BRIARWOOD</b> Galvanized p.25 	<b>BRIARWOOD</b> Graphite p.25 	<b>BRIARWOOD</b> Matte Black p.25 	<b>EDWIDGE</b> Matte White p.85 	<b>EDWIDGE</b> Matte Black p.85 
<b>EDWIDGE</b> Painted Nickel p.84 	<b>GULLIVER</b> Galvanized p.28 	<b>GULLIVER</b> Graphite p.29 	<b>HOLLAND</b> Brushed Nickel p.56 	<b>HOLLAND</b> Black p.57 



# Outdoor Ceiling Fans

 Damp Location Listed

**HOLLAND**  
Oil Rubbed Bronze p.57



**HUFF**  
Black p.47



**HUFF**  
Brushed Nickel p.46



**HUFF**  
Matte White p.47



**KAYSVILLE**  
Antique Nickel p.42



**KAYSVILLE**  
Graphite p.43



**MIDVALE**  
Blistered Iron p.81



**MIDVALE**  
Galvanized p.80



**MIDVALE**  
Matte White p.81



**RUDDER**  
Architectural Bronze p.83



**RUDDER**  
Matte Black p.83



**RUDDER**  
Matte White p.82



**RYNE**  
Matte White p.21



**RYNE**  
Matte Black p.20



**RYNE**  
Koa Woodgrain p.21



**SANFORD**  
Architectural Bronze p.32



**SANFORD**  
Brushed Nickel p.33



**VERNAL**  
Matte Black p.19



**VERNAL**  
Painted Nickel p.19



**VERNAL**  
Koa Woodgrain p.18



**WILLACY**  
Matte Black p.23



**WILLACY**  
Painted Nickel p.22



Featuring: Claret and Boxwood



## Fan Inspiration

Ceiling Fans can serve as a statement piece or even the focal point of a room.

Today's ceiling fans incorporate beautiful features, such as hand carved blades, sleek finishes and natural elements to appeal to a variety of different design trends.

At Progress Lighting, we strive to incorporate this shift in our ceiling fan designs and are eager to present an expanded offering in this catalog.

# The Perfect Fan in 5 Steps



Scan with the camera on your smartphone to explore more styles at [www.progresslighting.com/styles](http://www.progresslighting.com/styles)

## Ceiling Fan Buyer's Guide

Ceiling fans are practical and efficient solutions for creating comfortable and welcoming living areas. With many styles, functions and features to choose from, narrowing down the choices can be a challenge. Here we present five tips for selecting the perfect ceiling fan for your home.

### 1 Settle on Style

Choose a style that complements your décor. Consider fan shape, blade features and finish to help you meet your room's design needs. Choose from Traditional, Transitional, Coastal or Farmhouse styles. The possibilities are vast!



*Modern + Edgy*  
See full trendboard page 18



*Modernly Minimal*



*Easy, Breezy, Coastal*

See full trendboard page 84

## Indoor



Featuring Belva

## Outdoor




Featuring Rudder

### 2 Explore Indoor vs. Outdoor Uses

Fans provide a breezy setting for reading a book or catching up with friends, making them ideal for outdoor rooms. However, it's important to consider the certifications on the fan depending on the use. For high humidity areas, choose a UL-Listed fan for Damp Locations and for spaces that will be exposed to weather, choose a UL-Listed fan for Wet Locations. For interior use in dry spaces with minimal condensation, select a UL-Listed fan for Dry Locations. See testing listings defined on page 15.



## The Perfect Fan in 5 Steps *continued...*



### 3 Get Your Height Right

You want to allow at least 7 feet (84 in.) from the floor to the bottom of the fan, with 8 or 9 feet being the ideal above-floor placement. For lower ceilings, consider a ceiling fan with a low profile to avoid disturbing inhabitants. Most ceiling fans come equipped with a down rod to help you adjust to the correct height.

### 4 Size It To Your Space

Size is really important when selecting your ceiling fan. If a fan is too large, it can overwhelm the space. On the flip side, if the fan is too small, the airflow may be inadequate for that area.

Room Size (in square feet)	Fan Size (in inches)
0 - 75	0 - 36
76 - 144	36 - 42
145 - 225	42 - 50
226 - 360	50 - 54
361 - 499	54 - 70
500+	70+

## The Perfect Fan in 5 Steps *continued...*

### 5 Choose Your Features

There are many different features to choose from when browsing ceiling fans.

#### Blade Finish Options

Multiple blade finish options to coordinate with your home decor.


Example blade options for P250007-009-30

- Matte Black
- American Walnut



#### Reversible Motor

Typically, ceiling fans are used to help cool you down and keep the air flowing with a counter-clockwise blade direction. However, fans can also keep you warm when the direction of the blades is reversed. Select a fan with reversible motor for the option to circulate cool or warm air. Most ceiling fans have a small switch located either on the motor housing or the switch cup.



#### LED

Consider an LED or Energy Star rated fixture to save energy.



P2662-01

#### Remote Control with Full Range Dimming

Full range dimming and hand-held remote control capabilities are available to offer an added convenience in controlling a room's environment.



#### Light Kit

For a layered lighting effect, install a ceiling fan with a pre-installed light kit to complement your existing fixtures.



Scan for "The Perfect Fan in 5 Steps" with Steve Register or visit [youtube.com/user/ProgressLtg](https://www.youtube.com/user/ProgressLtg)

# LED Light Kits

## Save Money and Energy

When you select a high-quality LED fixture, you can expect a significant return on investment from an energy conservation standpoint. Here are some of the energy saving benefits of LEDs from Progress Lighting:



Alleron  
P250009-081-30  
shown with Gray Weathered Wood blades

## Features



LED sources use at least 75% less energy than incandescent lighting, allowing homeowners to save on operating expenses.



LEDs last 35 to 50 times longer than incandescent sources and approximately 2 to 5 times longer than fluorescent lighting. Meaning, less bulb maintenance!



LEDs do not use power when they are turned off. According to MSN Real Estate, LED lights can result in an annual bill as low as \$26.



LEDs do not produce heat like traditional sources, reducing cooling costs. Traditional incandescent bulbs waste 98% of the energy they consume on heat.

# Find Your Rating

## Indoor, Damp and Wet Location

All ceiling fans sold in the United States have been tested and rated by either Underwriters Laboratories (UL) or Intertek (ETL), each an independent product safety certification organization. It's important to pay attention to the rated listing when purchasing a ceiling fan as it will tell you what location the fan was designed for. There are three location options: dry, damp and wet.



### Dry Location

Please note indoor only (dry location) fans should only be used indoors. Even if an outdoor area or screened-in porch is covered, the motor and the blades can be affected when exposed to humidity. You can, however, “bring the outdoors inside” – as using outdoor ceiling fans are perfectly acceptable to use in interior spaces.

### Damp Location

If you are selecting a ceiling fan for a space that is outdoors and under a roof, i.e. any covered porches; you should select either a damp rated or wet listed fan. Damp location fans may also be used indoors.



Image: Arthur Rutenberg Homes  
Fan not available for purchase in Canada.


### Wet Location

If the fan comes directly into contact with water, you'll need to ensure that the ceiling fan has a “wet” listing. Ceiling fans designed for damp or wet locations feature elements, such as moisture-resistant motors and all weather blades. Wet location fans may also be used indoors.





Featuring Vernal



# Indoor Ceiling Fans


*Experience the versatility ceiling fans provide*



Scan with your camera on your smartphone or visit [www.progresslighting.com/ceilingfans](http://www.progresslighting.com/ceilingfans)



**Arlo**  
P250026-009-30



Retro 1

2 Unique Shapes

3 Glass Accents



Steve Register  
Senior Product Manager  
Ceiling Fans

## Modern + Edgy

with Steve

Quirky and functional, this style's flair comes from its modern, yet retro, juxtaposition. Mid-Century Modern style furniture adds unique shapes and pops of color to a room. Designers look for statement pieces to complete the look. This style is gravitating toward a cleaner, more minimalistic look through the incorporation of a neutral palette and softer accent colors. Mid-Century

Modern homes are largely characterized by the use of wood textures to create a sense of connection to nature and the outdoors.



Shop this style at  
[www.progresslighting.com/mid-century-modern](http://www.progresslighting.com/mid-century-modern)





# Vernal

P250059-179-30  
shown with Koa Woodgrain blades

**FINISHES**

- Matte Black - 031
- Painted Nickel - 152
- Koa Woodgrain - 179



WiFi included

Vernal refreshes a room's decor with elegant curves and an expansive 60-inch, five-blade span for the ultimate in design-savvy comfort. Vernal includes WiFi smart control: once installed, Vernal can be controlled by a voice assistant, tablet or smart phone. Finished in Koa Woodgrain, Matte Black or Painted Nickel, Vernal is designed to complement New Traditional and Transitional interiors.

*Integrated Smart Control*

*Elegant Curves*

*Dimmable LED Light*



# Vernal

**P250059-031-30** Matte Black



Matte Black

**P250059-152-30** Painted Nickel



Painted Nickel

**P250059-179-30** Koa Woodgrain



Koa Woodgrain



P250059-031-30  
shown with Matte Black blades



P250059-152-30  
shown with Painted Nickel blades



P250059-179-30  
shown with Koa Woodgrain blades  
with Architectural Bronze accents

**ENERGY INFORMATION AT HIGH SPEED**

<b>Airflow</b>	6,810 cubic feet per minute
<b>Electricity Use</b>	34 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	242 CFM/W

**FEATURES**

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- ABS blades
- Opal shatterproof shade
- WiFi enabled
- Remote control with batteries is included

**SIZE**

60" dia., 14-1/4" ht.  
80" lead wires.

**LAMP**

18w LED Module, 3000K,  
90 CRI, 1600 source lumens,  
dimmable.



Full Function Remote Control Included  
Six-speed fan operation  
Full-range dimming for light  
Reverse direction control



# Ryne

P250060-031-30  
shown with Matte Black blades

**FINISHES**

- Matte White- 028
- Matte Black - 031
- Koa Woodgrain - 179



WiFi compatible

The 52-inch Ryne fan is modern in appeal, with beautifully flowing blades that join in the middle to create a minimalistic housing. Ryne is smart control adaptable with the P2673 WiFi Module: once installed, Ryne can be controlled by a voice assistant, tablet or smart phone. Ryne's aerodynamic design and Koa Woodgrain, Matte White or Matte Black finish perfectly suits New Traditional and Transitional interiors.

*Modern Appeal*

*Aerodynamic Design*

*Dimmable LED Light*



P250060-028-30  
shown with Matte White blades



P250060-031-30  
shown with Matte Black blades




P250060-179-30  
shown with Koa Woodgrain blades  
with Architectural Bronze accents



P2673-01

# Ryne

P250060-028-30 Matte White




Matte White

P250060-031-30 Matte Black



Matte Black

P250060-179-30 Koa Woodgrain



Koa Woodgrain

**DC FAN WIFI MODULE  
P2673-01**

Add the WiFi module to your Ryne ceiling fan for control at your fingertips. You can easily control your fan with a hand-held remote; or a smart phone, tablet, voice assistant (Amazon Alexa and Google Home) via the Smart By Bond app.

**ENERGY INFORMATION AT HIGH SPEED**

<b>Airflow</b>	5,802 cubic feet per minute
<b>Electricity Use</b>	33 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	204 CFM/W



Full Function Remote Control Included  
Six-speed fan operation  
Full-range dimming for light  
Reverse direction control

**FEATURES**

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20")
- DC Motor
- ABS blades
- Opal shatterproof shade
- Remote control with batteries is included
- Add a P2673-01 WiFi module to convert to a smart fan

**SIZE**

52" dia., 13-1/2" ht.  
80" lead wires.

**LAMP**

18w LED Module, 3000K, 90 CRI,  
1600 source lumens, dimmable.





# Willacy

P250063-152  
shown with Painted Nickel blades

**FINISHES**


- Matte Black - 031
- Painted Nickel - 152



WiFi included

Willacy is striking in design, inspired by flowing ribbons that swirl around a gleaming center hub to create a gentle breeze. Willacy includes WiFi smart control: once installed, the fan can be controlled by a voice assistant, tablet or smart phone. Willacy features all weather hand finished ABS blades making it ideal for indoor or outdoor use.

*Striking Design*



*Ribbon-Like Blades*

*For Indoor & Outdoor Use*

# Willacy

**P250063-031** Matte Black



Matte Black

**P250063-152** Painted Nickel



Painted Nickel



P250063-031  
shown with Matte Black blades



P250063-152  
shown with Painted Nickel blades

**ENERGY INFORMATION AT HIGH SPEED**

<b>Airflow</b>	4,544 cubic feet per minute
<b>Electricity Use</b>	14 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	318 CFM/W

**FEATURES**

- Limited Lifetime Warranty
- DC Motor
- ABS blades
- WiFi enabled
- Remote control with batteries is included

**SIZE**

48" dia., 14-1/2" ht.  
12" lead wires.



Full Function Remote Control Included  
Six-speed fan operation  
Reverse direction control

# Briarwood

## FINISHES

- Antique Bronze - 020
- Galvanized - 141
- Graphite - 143
- Matte Black - 31M

P250067-020-WB  
with rich oak faux wood accent finish

The Briarwood ceiling fan brings vintage farmhouse detailing into the present day with a classic cross-brace pattern enclosing vintage-style bulbs and a trio of fan blades within its airy, open-frame design. Faux-painted wood accentuates Briarwood's simple geometric form, adding the perfect touch of country character to a variety of room settings.

*Farmhouse Detailing*

*Open Frame Design*

*Geometric Form*



P250067-020-WB  
accent color  
rich oak faux wood



P250067-143-WB  
accent color  
white washed faux wood



P250067-141-WB  
accent color  
bleached oak faux wood



P250067-31M-WB  
accent color  
ceruse black oak

# Briarwood

P250067-020-WB Antique Bronze



Antique Bronze

P250067-141-WB Galvanized



Galvanized

P250067-143-WB Graphite



Graphite

P250067-31M-WB Matte Black



Matte Black

## ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	1,145 cubic feet per minute
<b>Electricity Use</b>	31 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	37 CFM/W



Remote Control Included  
Three-speed fan operation  
Full-range dimming for light

## FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Add a P2630-30 or P2613-30 wall control or P2662-01 hand-held remote control
- Add the P2667-31 WiFi remote

## SIZE

22" dia., 17" ht.  
45" lead wires.

## LAMP

Four medium base 2200K 5.5w vintage LED lamps included. 500 lumens/lamp, 80 CRI, dimmable. 5.5w LED max/socket.





# Belva

P250068-31M-WB  
with mocha colored wicker'

## FINISHES


- Matte Black - 31M
- Cottage White - 151

The Belva ceiling fan offers an organic global feel and coastal charm. A lattice-like design graces the natural wicker frame, and a lovely Cottage White and Mocha finishes gives charm and depth. A trio of fan blades and vintage-style bulbs within the frame's woven structure moves air comfortably while casting a beautifully diffused glow.

*Organic Feel*

*Natural Woven Frame*

*Coastal Charm*



P250068-31M-WB  
with mocha colored wicker'

# Belva

P250068-31M-WB Matte Black



Matte Black

P250068-151-WB Cottage White



Cottage White



P250068-151-WB  
with whitewashed wicker

## ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	1,125 cubic feet per minute
<b>Electricity Use</b>	37 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	37 CFM/W

## FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Add a P2630-30 or P2613-30 wall control
- Add the P2667-31 WiFi remote

## SIZE

25-1/4" dia., 17-7/8" ht.  
45" lead wires.

## LAMP

Four medium base 2200K 5.5w vintage LED lamps included. 500 lumens/lamp, 80 CRI, dimmable. 5.5w LED max/socket.



Remote Control Included  
Three-speed fan operation  
Full-range dimming for light



# Gulliver

P250012-141-22  
shown with Antique White Wood

## FINISHES

- Galvanized - 141
- Graphite - 143

Three circular bands wrap together to create an open design. Non-metallic fan blades enclosed within a stylish cage design gives the rustic charm of a pendant combined with the functionality of a ceiling fan. Dual toned frame color combinations of Galvanized with antique white accents or Graphite with weathered gray accents. A hand painted wood grained texture complements rustic and modern farmhouse home decor, as well as urban industrial and coastal interior settings.

*Urban Industrial Design*



*Rustic Charm*

*Hand-Painted Wood*



P250012-141-22  
shown with Antique White Wood



P250012-143-22  
shown with Gray Wood

# Gulliver

P250012-141-22 Galvanized



Antique White Wood

P250012-143-22 Graphite



Gray Wood

## ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	1,297 cubic feet per minute
<b>Electricity Use</b>	39 watts (excludes lights)
<b>Airflow Efficiency</b>	33 cubic feet per minute per watt



Three-Speed Remote Control Included  
Three-speed fan operation  
Full-range dimming for light

## FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-18.5")
- AC Motor
- Reversible Motor
- Rust-proof non-metallic blades
- Damp Location Rated
- Remote control with batteries is included
- Add the P2667-31 WiFi remote

## SIZE

23" dia., 18-1/8" ht.  
42" lead wires.

## LAMP

Three medium base 2200K 5.5w vintage LED lamps included. 500 lumens/ lamp, 80 CRI, dimmable. 5.5w LED max/socket.





# Loring

## FINISHES

- Black- 031
- Galvanized - 141

P250006-031  
shown with Matte Black blades

Outfitted with stylish mixed metal elements, the Loring collection shows off an industrial-inspired, open-cage design. Four plywood blades and a handy remote control are ready to help you and your family stay comfortable and relaxed all year round.

*Open-Cage Design*



*Industrial Inspired*

*Mixed-Metal Elements*



P250006-031  
shown with Gold accent  
and Distressed Ebony blades



P250006-141  
shown with Matte Black accent  
and White Barnwood blades

# Loring

## P250006-031 Black

- Matte Black
- Distressed Ebony

## P250006-141 Galvanized

- White Barnwood
- Driftwood

## ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	1,766 cubic feet per minute
<b>Electricity Use</b>	43 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	44 CFM/W



Three Speed Remote Control Included  
Three-speed fan operation

## FEATURES

- Limited lifetime warranty
- Close-to-ceiling installation
- AC Motor
- Reversible plywood blades
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 wall control

## SIZE

33" dia., 15-1/4" ht.  
12" lead wires.



# Sanford

**FINISHES**

- Brushed Nickel - 009
- Architectural Bronze - 129

P2594-12930K

Sanford delivers ultra powerful air movement and energy efficient illumination packaged in a modern design. Ideal for both interior and outdoor settings, this "fandelier" adds a contemporary style to porches, foyers, bath and vanity areas providing a wide range of applications. Sanford includes an integrated 23W LED module, offering both form and function with energy and cost-savings benefits. A three-speed remote control is included.

*Indoor or Outdoor Use*

*Contemporary Style*



*Powerful Air Movement*

# Sanford

**P2594-0930K** Brushed Nickel

**P2594-12930K** Architectural Bronze



P2594-0930K



P2594-12930K

**ENERGY INFORMATION AT HIGH SPEED**

<b>Airflow</b>	1,008 cubic feet per minute
<b>Electricity Use</b>	37 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	27 CFM/W



Three-Speed Remote Control Included  
*Three-speed fan operation*  
*Full-range dimming for light*

**FEATURES**

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-18.5")
- AC Motor
- Metal blades
- Damp Location Rated
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 wall control
- Add the P2667-31 WiFi remote

**SIZE**

22-7/8" dia., 17-3/4" ht.  
 80" lead wires.

**LAMP**

26w LED module, 3000K, 90 CRI,  
 2638 source lumens, dimmable.





## An Industrial Edge



A simple but edgy vibe takes its cue from industrial origins.

1

Try a fandelier style ceiling fan like Sanford that delivers ultra-powerful air movement packaged in a vintage design.

2

Toss your table lamp and try two low-hanging pendants over the nightstand instead.

3

Finish the room with organic elements of wood and worn textures that celebrate the signature look of the industrial setting.



# 52" Springer

P250065-081


**FINISHES**

- Antique Nickel - 081
- Architectural Bronze - 129
- Matte Black - 31M



WiFi compatible

The sweeping style of the Springer fan is expressed in a 52" size that is ideal for boosting airflow in smaller spaces. The 12-blade ceiling fan has a rustic flair inspired by the form and function of a windmill. Springer is WiFi ready offering more versatility in control options. It is a DC motor fan and can accept the Springer light kit (sold separately). Springer offers the perfect look for Farmhouse, Industrial and Transitional settings



P250065-081



P250065-129



P250065-31M

## 52" Springer

**P250065-081** Antique Nickel



White Barnwood

**P250065-129** Architectural Bronze



Distressed Walnut

**P250065-31M** Matte Black



Rustic Charcoal

**SPRINGER LIGHT KIT**

- P260000-081-WB** Antique Nickel
- P260000-129-WB** Architectural Bronze
- P260000-31M-WB** Matte Black

Two medium base 2700K 7w vintage LED lamps included. 600 lumens/lamp, 90 CRI, dimmable. 7w LED max/socket.



*\*This light kit is only compatible with the P250065 and P250000 Springer Fans.*

**ENERGY INFORMATION AT HIGH SPEED**

<b>Airflow</b>	6296 cubic feet per minute
<b>Electricity Use</b>	30 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	245 CFM/W

**FEATURES**

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- Add a P2673-01 module to convert your fan to WiFi smart

**SIZE**

52" dia., 17-3/8" ht.  
80" lead wires.



Full Function Remote Control Included  
Six-speed fan operation  
Reverse direction control





Modern Traditional is the perfect blend of new and old.

1

Use a contemporary tonal color palette of whites and grays accented with rustic, warm wood touches to make the space feel inviting.

2

Complement the minimalist room with the rugged, statement-making style of the Springer ceiling fan.

3

Amplify modern style with the Milner wall sconce's trendy matte black finish and clear glass shades against a white-washed brick accent wall.





# Springer

**FINISHES**

- Antique Nickel - 081
- Architectural Bronze - 129
- Matte Black - 31M



Now Available  
WiFi Compatible

P250000-31M  
shown with Rustic Charcoal blades



*Dual Mount Canopy*

*Rustic Flair*

*Windmill Inspired*

## Springer


**P250000-081** Antique Nickel



**P250000-129** Architectural Bronze



**P250000-31M** Matte Black




**NOW AVAILABLE WILL ACCEPT THE P260000 LIGHT KIT**

**P260000-081-WB** Antique Nickel  
**P260000-129-WB** Architectural Bronze  
**P260000-31M-WB** Matte Black

Two medium base 2700K 7w vintage LED lamps included. 600 lumens/lamp, 90 CRI, dimmable. 7w LED max/socket.



*\*This light kit is only compatible with the P250065 and P250000 Springer Fans.*



P250000-081  
shown with White Barnwood blades



P250000-129  
shown with Distressed Walnut blades



P250000-31M  
shown with Rustic Charcoal blades



Scan with the camera on your smartphone for the Springer installation video.

**ENERGY INFORMATION AT HIGH SPEED**

**Airflow** 6,377 cubic feet per minute  
**Electricity Use** 33 watts (excludes lights)  
**DOE Weighted CFM/W** 206 CFM/W

**FEATURES**

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-22")
- DC Motor
- Plywood blades
- Full function remote control with batteries is included
- Add a P2673-01 module to convert your fan to WiFi smart

**SIZE**

60" dia., 17-3/8" ht.  
80" lead wires.



Full Function Remote Control Included  
Six-speed fan operation  
Reverse direction control



# Kaysville

P250003-081-30  
shown with Chestnut blades

**FINISHES**

- Antique Nickel - 081
- Graphite - 143

Beautiful long bent blades appear to be held only by a simple metal band in Kaysville, offering a modern industrial style. Kaysville pairs the beauty of the blades with a strong, all-weather ABS material to prevent warping.



*Modern Style*

*Simple Metal Band*

*Dimmable LED Light*

# Kaysville

**P250003-081-30** Antique Nickel



**P250003-143-30** Graphite



P250003-081-30  
shown with Chestnut blades



P250003-143-30  
shown with Gray Weathered Wood blades

**ENERGY INFORMATION AT HIGH SPEED**

<b>Airflow</b>	9,650 cubic feet per minute
<b>Electricity Use</b>	31 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	361 CFM/W

**FEATURES**

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- ABS blades
- White Opal glass shade
- Remote control with batteries is included

**SIZE**

56" dia., 17-1/4" ht.  
80" lead wires.

**LAMP**

24w LED Module, 3000K,  
90 CRI, 2000 source lumens,  
dimmable.



Full Function Remote Control Included  
Six-speed fan operation  
Full-range dimming for light  
Reverse direction control



# Alleron

P250009-182-30  
shown with Antique Black blades

**FINISHES**

- Antique Nickel - 081
- Flat Black - 182

Reminiscent of aviation days gone by, Alleron takes its styling cues from a set of airplane propeller blades. The hand-finished ABS blades paired with a sleek metal ceiling canopy and light kit add a modern industrial flair to indoor and covered outdoor settings.



*Modern Industrial Flair*

*Propeller Inspired Blades*

*Dimmable LED Light*

# Alleron

**P250009-081-30** Antique Nickel



**P250009-182-30** Flat Black



P250009-081-30  
shown with Gray Weathered Wood blades



P250009-182-30  
shown with Antique Black blades

**ENERGY INFORMATION AT HIGH SPEED**

<b>Airflow</b>	7,801 cubic feet per minute
<b>Electricity Use</b>	20 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	423 CFM/W



Full Function Remote Control Included  
Six-speed fan operation  
Full-range dimming for light  
Reverse direction control

**FEATURES**

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- ABS blades
- White opal glass shade
- Remote control with batteries is included

**SIZE**

56" dia., 16" ht.  
80" lead wires.

**LAMP**

24w LED Module, 3000K,  
90 CRI, 2000 source lumens,  
dimmable.






# Huff

P250030-009  
shown with Brushed Nickel blades

**FINISHES**

- Brushed Nickel - 009
- Matte White- 028
- Matte Black- 031

The hassles and headaches of the day fade away under the relaxing airflow created by the Huff Collection. Six expansive aluminum blades with decorative winglets stretch out from a dual mount center. Select a Brushed Nickel, Matte White, or Matte Black finish all with their own complementary highlights to create a perfect design for your modern or transitional space.




*Modern Design*

*Complimentary Highlights*

*Expansive Aluminum Blades*

# Huff

**P250030-009** Brushed Nickel



**P250030-028** Matte White



**P250030-031** Matte Black



P250030-009  
shown with Brushed Nickel blades  
and Matte Black accents



P250030-028  
shown with Matte White blades  
and Brushed Nickel accents



P250030-031  
shown with Black blades  
and Brushed Nickel accents

**ENERGY INFORMATION AT HIGH SPEED**

<b>Airflow</b>	14,482 cubic feet per minute
<b>Electricity Use</b>	49 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	344 CFM/W

**FEATURES**

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- Aluminum blades
- Damp Location Rated
- Compatible with universal light kit
- Remote control with batteries is included

**SIZE**

96" dia., 15-1/2" ht.  
80" lead wires.



Full Function Remote Control Included  
Six-speed fan operation  
Reverse direction control

# Arlo

P250026-009-30  
shown with Brushed Nickel blades

**FINISHES**


- Brushed Nickel - 009
- Black - 031
- Architectural Bronze - 129

Unwind under the cooling breeze created by the clean, crisp blades of the Arlo collection's modern ceiling fan. A central LED light provides a perfect way to light a space without flooding the room with harsh light as six metal blades attach to the fan's center. Offered in three different finishes, Arlo is sure to create an intriguing, yet serene retreat in whatever space it calls home.

*Modern Design*

*Clean Metal Blades*

*Dimmable LED Light*



P250026-009-30  
shown with Brushed Nickel blades




P250026-031-30  
shown with Black blades



P250026-129-30  
shown with Architectural Bronze blades

# Arlo

**P250026-009-30** Brushed Nickel



**P250026-031-30** Black



**P250026-129-30** Architectural Bronze



**ENERGY INFORMATION AT HIGH SPEED**

<b>Airflow</b>	7,558 cubic feet per minute
<b>Electricity Use</b>	29 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	282 CFM/W



Full Function Remote Control Included  
Six-speed fan operation  
Full-range dimming for light  
Reverse direction control

**FEATURES**

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- Aluminium blades
- Damp Location Rated
- White Opal glass
- Remote control with batteries is included

**SIZE**

60" dia., 18-1/2" ht.  
80" lead wires.

**LAMP**


24w LED Module, 3000K, 90 CRI,  
2000 source lumens, dimmable.





# Bixby

P250038-231-30  
shown with Black Metallic blades



*Industrial Style*

*Slightly Curved  
Lucite Blades*

*Dimmable LED Light*

**FINISHES**

- White - 030
- Black Chrome - 231

You'll find the time to unwind under the eye-pleasing, urban industrial design of the Bixby collection's ceiling fan. Breathe easy after a warm summer day or a long day at work as Bixby fosters a refreshing current of cool air with three, slightly curved Lucite blades circling a gentle LED light as it provides soothing illumination.

# Bixby

**P250038-030-30** White



White Metallic

**P250038-231-30** Black Chrome



Black Metallic



P250038-030-30  
shown with White Metallic blades



P250038-231-30  
shown with Black Metallic blades

**ENERGY INFORMATION AT HIGH SPEED**

<b>Airflow</b>	6,846 cubic feet per minute
<b>Electricity Use</b>	32 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	228 CFM/W



Full Function Remote Control Included  
Six-speed fan operation  
Full-range dimming for light  
Reverse direction control

**FEATURES**

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- Polycarbonate blades
- Damp Location Rated
- White opal glass
- Remote control with batteries is included

**SIZE**

60" dia., 15-1/8" ht.  
80" lead wires.

**LAMP**

24w LED Module,  
3000K, 90 CRI,  
2000 source lumens, dimmable.



# Farris

P250002-108-30  
shown with Walnut blades

**FINISHES**

- Brushed Nickel - 009
- Oil Rubbed Bronze - 108
- Graphite - 143

Farris features three solid wood carved blades to form a sleek, modern design. The 60" ceiling fan includes an integrated LED light kit that is removable to provide the option in non-illuminated applications. Available in Brushed Nickel, Oil Rubbed Bronze and Graphite finishes. A full function remote control with batteries is included, and the dual mount canopy accommodates flat or sloped ceilings.



*Modern Design*

*Wood Carved Blades*

*Removable, Dimmable LED Light*

# Farris


**P250002-009-30** Brushed Nickel



**P250002-108-30** Oil Rubbed Bronze



**P250002-143-30** Graphite



**ENERGY INFORMATION AT HIGH SPEED**

<b>Airflow</b>	7,047 cubic feet per minute
<b>Electricity Use</b>	32 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	223 CFM/W



Full Function Remote Control Included  
Six-speed fan operation  
Full-range dimming for light  
Reverse direction control

**FEATURES**

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-13°)
- DC Motor
- Carved wood blades
- Removable light kit. Blank plate included.
- White opal shatterproof shade
- Full function remote control with batteries is included

**SIZE**

60" dia., 15-1/2" ht.  
80" lead wires.

**LAMP**

18w LED Module, 3000K, 90 CRI,  
1400 source lumens, dimmable.







Modern Farmhouse design embraces tradition but is firmly planted in the present.

1

Look for details like the beautifully carved, solid wood fan blades of the Farris ceiling fan that centers the room with statement-making style.

2

Modernize a traditional approach by contrasting a light and airy palette with a natural stone fireplace, weathered wood mantel and exposed beams.

3

Use organic materials for decorative accessories like greenery, wood and cozy textiles to add a welcoming touch.




# Holland

P250032-009-30  
shown with Silver blades

**FINISHES**

- Brushed Nickel - 009
- Black- 031
- Oil Rubbed Bronze - 108

Enjoy nothing but first-rate design inspiration with the gorgeous Holland collection. Four simple, yet stunning blades blend style with sustainability as they anchor to a sleek, dual mount center. An integrated LED light is ready to offer a gentle glow along with the fan's refreshing breeze. With the versatility to be installed in indoor or outdoor locations, this fan will make a design statement in any modern or transitional setting.



Dual Mount System

Dimmable LED Light

Indoor or Outdoor Use

# Holland

**P250032-009-30** Brushed Nickel



Silver

**P250032-031-30** Black



Black

**P250032-108-30** Oil Rubbed Bronze



Walnut



P250032-009-30  
shown with Silver blades



P250032-031-30  
shown with Black blades



P250032-108-30  
shown with Walnut blades

**ENERGY INFORMATION AT HIGH SPEED**

<b>Airflow</b>	7,035 cubic feet per minute
<b>Electricity Use</b>	31 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	257 CFM/W



Full Function Remote Control Included  
Six-speed fan operation  
Full-range dimming for light  
Reverse direction control

**FEATURES**

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- ABS blades
- White opal glass
- Damp Location Rated
- Remote control with batteries is included

**SIZE**

60" dia., 16-5/8" ht.  
80" lead wires.

**LAMP**

24w LED Module, 3000K, 90 CRI,  
2000 source lumens, dimmable.





# Oriole

## FINISHES

- Brushed Nickel - 09
- Black - 31
- Architectural Bronze - 129

P2592-12930K  
shown with Architectural Bronze blades



*Sleek Blades*

This 60" Oriole ceiling fan is the perfect addition to interior garages, industrial shops or commercial buildings to distribute the right amount of air and keep the space cool and comfortable. Oriole contains an integrated 18W LED module, with an optional finishing cap offering the user the choice to install with or without the light kit. A remote control is included to adjust speed and turn on/off the light or fan. A blank plate comes standard.

*Industrial Design*

*Removable, Dimmable LED Light*



P2592-0930K  
shown with Silver blades



P2592-3130K  
shown with Black blades  
and light kit removed  
using blank plate



P2592-12930K  
shown with Architectural Bronze blades

# Oriole

P2592-0930K Brushed Nickel



P2592-3130K Black



P2592-12930K Architectural Bronze



## ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	6,171 cubic feet per minute
<b>Electricity Use</b>	51 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	132 CFM/W



Three-Speed Remote Control Included  
Three-speed fan operation  
Full-range dimming for light

## FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-18.5°)
- AC Motor
- ABS blades
- Removable light kit. Blank plate included.
- White opal glass shade
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 wall control
- Add the P2667-31 WiFi remote

## SIZE

60" dia., 15" ht.  
80" lead wires.

## LAMP

18w LED Module, 3000K, 90 CRI,  
1400 source lumens, dimmable.




# Royer

## FINISHES

- Antique Nickel - 081
- Forged Black- 080

P250010-080  
shown with Distressed Ebony blades

The Royer collection's ceiling fan offers a charming, rustic look ideal for farmhouse and rustic spaces in need of a fresh breeze. Four plywood blades attach to the fixture's center by finely detailed metal arms. The crafted center is available in three finishes so you can select the perfect piece to complement your home décor.



P250010-080  
shown with Matte Black blades




P250010-081  
shown with Driftwood blades

# Royer

P250010-080 Forged Black



P250010-081 Antique Nickel



Bottom detail of P250010-081  
shown with Driftwood blades

## ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	6,255 cubic feet per minute
<b>Electricity Use</b>	67 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	102 CFM/W



Three-Speed Remote Control Included  
Three-speed fan operation

## FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Reversible plywood blades
- Not compatible with light kit
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 wall control
- Add the P2667-31 WiFi remote

## SIZE

60" dia., 17-7/8" ht.  
80" lead wires.







# Bedwin

**FINISHES**


- Antique Nickel - 081
- Galvanized - 141
- Graphite - 143

P250024-081  
shown with Driftwood blades

Recall charming, rustic lattice work with the Bedwin Collection's farmhouse-inspired ceiling fan. With three finishes to pick from and four rough hewn plywood blades circling a handsome dual mount canopy, this ceiling fan is sure to help transform any living space into a cool paradise of relaxation.



P250024-081  
shown with Classic Walnut blades




P250024-141  
shown with Gray Weathered Wood blades



P250024-143  
shown with Graphite blades

## Bedwin

**P250024-081** Antique Nickel



**P250024-141** Galvanized



**P250024-143** Graphite



ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	6,044 cubic feet per minute
<b>Electricity Use</b>	34 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	192 CFM/W

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- Reversible plywood blades
- Compatible with universal light kits
- Remote control with batteries is included

SIZE

56" dia., 15-1/2" ht.  
80" lead wires.



Full Function Remote Control Included  
Six-speed fan operation  
Reverse direction control


# Glenfalls

P250021-028-30  
shown with Matte White blades and Black Chrome accents

## FINISHES

- Brushed Nickel - 009
- Matte White- 028
- Matte Black - 031

Glenfalls highlights its beautiful simulated wood fan blades with bright metallic accents on the blade arms and tips to create a timeless yet modern design. Glenfalls is ideal for cooling large living areas in sophisticated style.



*Timeless Design*

*Metallic Accents*

*Dimmable LED Light*



P250021-009-30  
shown with Chestnut blades  
and Brushed Nickel accents



P250021-028-30  
shown with Matte White blades  
and Black Chrome accents



P250021-031-30  
shown with Matte Black blades  
and Brushed Nickel accents

# Glenfalls

P250021-009-30 Brushed Nickel



Chestnut

P250021-028-30 Matte White



Matte White

P250021-031-30 Matte Black



Matte Black

## ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	6,393 cubic feet per minute
<b>Electricity Use</b>	85 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	84 CFM/W

## FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Plywood blades
- White opal glass shade
- Remote control with batteries is included
- Remote control may be replaced with the P2667-31 WiFi Remote

## SIZE

56" dia., 14-7/8" ht.  
80" lead wires.

## LAMP

24w LED Module, 3000K,  
90 CRI, 2000 source lumens,  
dimmiabie.



Remote Control Included  
Three-speed fan operation  
Full-range dimming for light





# Claret

P250007-108-30  
shown with Antique Wood blades

## FINISHES

- Brushed Nickel - 009
- Matte Black - 031
- Oil Rubbed Bronze - 108

Claret gracefully blends old and new with an eye-catching fluted motor housing paired with long blade arms. With its unique take on a classic design, Claret will make a statement in a variety of interiors.



*Statement-Making*

*Fluted Motor Housing*

*Dimmable LED Light*



P250007-009-30  
shown with Matte Black blades



P250007-031-30  
shown with Distressed Ebony blades



P250007-108-30  
shown with Chestnut blades

# Claret

**P250007-009-30** Brushed Nickel

- Matte Black
- American Walnut

**P250007-031-30** Matte Black

- Distressed Ebony
- Gray Weathered Wood

**P250007-108-30** Oil Rubbed Bronze

- Antique Wood
- Chestnut

## ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	5,553 cubic feet per minute
<b>Electricity Use</b>	61 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	106 CFM/W



Remote Control Included  
Three-speed fan operation  
Full-range dimming for light

## FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Reversible plywood blades
- White opal glass shade
- Remote control with batteries is included
- Remote control may be replaced with the P2667-31 WiFi Remote

## SIZE

54" dia., 15-1/8" ht.  
80" lead wires.

## LAMP

18w LED Module, 3000K,  
90 CRI, 1400 source lumens,  
dimmable.



# Trevina II 44"

## FINISHES

- Brushed Nickel - 09
- Satin White - 28
- Black - 31

P2555-0930K  
shown with Silver blades



The Trevina collection features fans with a signature three-blade design. Perfect for modern or traditional interiors, each fan includes an LED light source to help extend your day into the evening as you and your family relax in your peaceful retreat.

*Modern and Traditional*

*Three Blade Design*

*LED Light Source*



P2555-0930K  
shown with Silver blades



P2555-2830K  
shown with White blades



P2555-3130K  
shown with Distressed Ebony blades

# Trevina II 44"

**P2555-0930K** Brushed Nickel



Silver

**P2555-2830K** Satin White



White

**P2555-3130K** Black



Black

**P2555-3130K** Distressed Ebony



Distressed Ebony



Detail of P2555-0930K shown with P2668-09 blank plate and Silver blades



P2668-09



P2668-28



P2668-31

## BLANK PLATE

**P2668-09** Brushed Nickel

**P2668-28** Satin White

**P2668-31** Black

## ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	4306 cubic feet per minute
<b>Electricity Use</b>	42 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	122 CFM/W



Wall Control Included  
Four-speed fan operation  
Full-range dimming for light  
Includes switch plate cover

## FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Reversible MDF blades
- Removable light kit. Blank plate sold separately.
- White Opal glass
- Compatible with remote or hardwired wall controls (P2630, P2661-01, P2662-01, P2663-01, P2665 (sold separately))

## SIZE

44" dia., 15-5/8" ht.  
80" lead wires.

## LAMP

18w LED Module,  
3000K, 90 CRI,  
1400 source lumens, dimmable.





# Coolly Modern



Wow family and friends with a dramatic ceiling treatment.

1 Install a ceiling fan like Trevina, whose contemporary design brings both form and function.

2 Add molding or beams to the ceiling to create a spectacular "fifth wall."

3 Choose wood floors and cabinetry as a warming element to unite an open floor plan.





# 44" Braden

The Braden 44 inch, three-blade, hugger-style ceiling fan features clean lines and a classic, sleek design that is ideal for Modern and Contemporary interiors. With its simple and elegant look and Brushed Nickel, Matte Black or Matte White finish, Braden complements most décor schemes.



## FINISHES

- Brushed Nickel - 009
- Matte White - 028
- Matte Black - 031



### P250058-009-30 Brushed Nickel

-  American Walnut
-  Silver

### P250058-028-30 Matte White

-  Natural Cherry
-  White

### P250058-031-30 Matte Black

-  Distressed Ebony
-  Matte Black



P250058-009-30  
shown with American Walnut blades



P250058-028-30  
shown with Natural Cherry blades



P250058-031-30  
shown with Distressed Ebony blades

## ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	3,212 cubic feet per minute
<b>Electricity Use</b>	45 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	78 CFM/W



Full Function Remote Control Included  
Three-speed fan operation  
Full-range dimming for light

## FEATURES

- Limited lifetime warranty
- Hugger low profile mounting
- AC Motor
- Reversible plywood blades
- Frosted shatterproof shade
- Full function remote control with batteries is included
- Remote control may be replaced with P2667-31 WiFi remote control

## SIZE

44" dia., 9-7/8" ht.  
12" lead wires.

## LAMP

18w LED Module, 3000K,  
90 CRI, 1400 source lumens,  
dimmable.



Featuring Braden and Clarion

## Sweet Dreaming

Muted colors and a light, airy feeling offer a dreamy look to this bedroom. The Braden hugger fan lends a contemporary touch while keeping the room comfortable and welcoming. A feature wall of lightly distressed wood paneling is accented by a pair of Clarion wall sconces, whose clear glass shade and clean styling embrace minimalist modernity and functional task lighting.



# Braden

## FINISHES

- Brushed Nickel - 09
- Polished Chrome - 15
- Architectural Bronze - 129

P2588-1530K  
shown with Black blades

This Braden 56", three-blade, hugger-style ceiling fan features clean lines and a design that complements modern interiors. A white opal glass shade contains an integrated 18W LED module, offering both form and function with energy and cost-savings benefits. Featuring a larger motor, Braden moves more air than a traditional hugger ceiling fan.



*Modern Style*

*Dimmable LED Light*

*White Opal Glass Shade*



P2588-0930K  
shown with Silver blades




P2588-1530K  
shown with American Walnut blades




P2588-12930K  
shown with Medium Cherry blades

# Braden


**P2588-0930K** Brushed Nickel



**P2588-1530K** Polished Chrome



**P2588-12930K** Architectural Bronze



## ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	4,263 cubic feet per minute
<b>Electricity Use</b>	55 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	85 CFM/W



Full Function Remote Control Included  
Three-speed fan operation  
Full-range dimming for light  
Reverse direction control

## FEATURES

- Limited lifetime warranty
- Hugger low profile mounting
- AC Motor
- Reversible plywood blades
- White opal glass shade
- Full function remote control with batteries is included
- Remote control may be replaced with P2631-30 wall control
- Add the P2667-31 WiFi remote

## SIZE

56" dia., 9-7/8" ht.  
12" lead wires.


## LAMP

18w LED Module, 3000K, 90 CRI, 1400 source lumens, dimmable.





Featuring Midvale




# Outdoor Ceiling Fans

*Enhance outdoor living areas*



Scan with your camera on your smartphone or visit [www.progresslighting.com/ceilingfans](http://www.progresslighting.com/ceilingfans)





**Midvale**  
P250011-171-WB

Relaxed 3

1 Organic Shapes

Beach Accents 2

## Easy, Breezy, Coastal

with Dan



Dan McGinty  
Product Designer

Bring your home right to the ocean side with beach-inspired accents, organic furnishings and an overall relaxed feel. Designers often create a relaxed and open environment with soft throw blankets, pillows, cozy rugs and cushioned furniture to complete the Coastal look. Focus on an all-white color palette for your coastal inspired home, while incorporating in soft beachy hues to complement the look.

When it comes to selecting materials for flooring, décor and furniture, seek out dark or weathered wood pieces to emulate a seaside environment nestled nicely by the shore.



Shop this style at  
[www.progresslighting.com/coastal](http://www.progresslighting.com/coastal)





# Midvale

## FINISHES

- Matte White- 028
- Blistered Iron - 171
- Galvanized - 141

P250011-141-WB  
shown with Galvanized Finish blades

Midvale offers a nostalgic appeal, with vintage-style LED bulbs inside a clear seeded glass shade, a rustic cage frame, and a banded metal ceiling canopy to complete the charming look.



*Vintage Style*

*Nostalgic Appeal*

*Clear Seeded Glass*



P250011-028-WB  
shown with Matte White blades



P250011-141-WB  
shown with Galvanized blades



P250011-171-WB  
shown with Blistered iron blades

# Midvale

**P250011-028-WB** Matte White



**P250011-141-WB** Galvanized Finish



**P250011-171-WB** Blistered Iron



## ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	7,627 cubic feet per minute
<b>Electricity Use</b>	84 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	98 CFM/W



Remote Control Included  
Three-speed fan operation  
Full-range dimming for light

## FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- ABS blades
- Clear seeded glass shade
- Remote control with batteries is included
- Remote control may be replaced with the P2667-31 WiFi Remote

## SIZE

56" dia., 20-3/8" ht.  
80" lead wires.

## LAMP

Two medium base 2700K 7w vintage LED lamps included. 600 lumens/lamp, 90 CRI, dimmable. 7w LED max/socket.






# Rudder

**FINISHES**

- Matte White - 028
- Matte Black - 031
- Architectural Bronze - 129

P250040-028-30  
shown with Distressed White blades

Transform any outdoor space into a cozy country abode with the charming rustic character of the Rudder collection. Four boat oar-inspired blades attach to a smooth center that features an LED light source for friendly illumination as needed. Available in a Matte White, Matte Black, or Architectural Bronze finish, Rudder is sure to fill your favorite patio or porch with a refreshing breeze wrapped in country character.



P250040-028-30  
shown with Distressed White blades



P250040-031-30  
shown with Distressed Ebony blades



P250040-129-30  
shown with Walnut blades


## Rudder

**P250040-028-30** Matte White



Distressed White

**P250040-031-30** Matte Black



Distressed Ebony

**P250040-129-30** Architectural Bronze



Walnut

**ENERGY INFORMATION AT HIGH SPEED**

<b>Airflow</b>	6,112 cubic feet per minute
<b>Electricity Use</b>	35 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	188 CFM/W



Full Function Remote Control Included  
Six-speed fan operation  
Full-range dimming for light  
Reverse direction control

**FEATURES**

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- ABS blades
- Damp Location Rated
- White opal glass shade
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 wall control

**SIZE**

56" dia., 16-1/8" ht.  
80" lead wires.

**LAMP**

24w LED Module, 3000K,  
90 CRI, 2000 source lumens,  
dimnable.



# Edwidge

P250062-152-30  
shown with Painted Nickel blades

**FINISHES**

- Matte White - 028
- Matte Black - 031
- Painted Nickel - 152

Edwidge cleverly houses the motor within the trio of fan blades providing a sleek, modern look. All-weather ABS fan blades and a non-metallic housing and canopy offer rust-proof, contemporary style to indoor and covered outdoor settings.

*Modern Design*

*For Indoor & Outdoor Use*

*Dimmable LED Light*

# Edwidge

**P250062-028-30** Matte White



**P250062-031-30** Matte Black



**P250062-152-30** Painted Nickel



P250062-028-30  
shown with Matte White blades



P250062-031-30  
shown with Matte Black blades



P250062-152-30  
shown with Painted Nickel blades

**ENERGY INFORMATION AT HIGH SPEED**

<b>Airflow</b>	5,874 cubic feet per minute
<b>Electricity Use</b>	20 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	328 CFM/W

**FEATURES**

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- ABS blades
- Opal shatterproof shade
- Remote control with batteries is included

**SIZE**

52" dia., 13-9/16" ht.  
80" lead wires.

**LAMP**

18w LED Module, 3000K, 90 CRI,  
1400 source lumens, dimmable.



Full Function Remote Control Included  
Six-speed fan operation  
Full-range dimming for light  
Reverse direction control





# Alfresco

## FINISHES

- Architectural Bronze - 129
- Blistered Iron - 171

P250034-129-WB  
shown with Dark Bamboo blades

Infuse a warm, nature-inspired style to your outdoor home décor with the one-of-a-kind Alfresco collection. Five blades decorated in a leaf-like design sprout from a dual mount center that artistically harbors an LED light source. Select from an Architectural Bronze and blistered iron finish to bring your bohemian dreamland to life.

*Leaf-like Decorated Blades*

*Nature-Inspired Design*

*Dimmable LED Light*

# Alfresco

**P250034-129-WB** Architectural Bronze

 Dark Bamboo

**P250034-171-WB** Blistered Iron

 Pewter



P250034-129-WB  
shown with Dark Bamboo blades



P250034-171-WB  
shown with Pewter blades

## ENERGY INFORMATION AT HIGH SPEED

**Airflow** 5,724 cubic feet per minute  
**Electricity Use** 68 watts (excludes lights)  
**DOE Weighted CFM/W** 90 CFM/W



Three-Speed Remote Control Included  
Three-speed fan operation  
Full-range dimming for light

## FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- ABS blades
- Damp Location Rated
- Clear seeded glass
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 wall control

## SIZE

54" dia., 19-1/4" ht.  
80" lead wires.

## LAMP

Two medium base 2700K 7w vintage LED lamps included. 600 lumens/lamp, 90 CRI, dimmable. 7w LED max/socket.



# Albin

P250036-129-30  
shown with Distressed Walnut blades

## FINISHES

- Matte White- 028
- Matte Black- 031
- Architectural Bronze - 129

The Albin collection offers a modern take on a traditional design that will be perfectly at home in so many outdoor spaces and lifestyles. Five blades finished with a faux wood grain texture extend from a modern-style center available in an Architectural Bronze, Matte White, or Matte Black finish. An LED light source is encased in a crisp shade to illuminate a patio or porch space that will beg to be lived in an enjoyed.

*Faux Wood Grain Texture*

*Modern Style*

*Dimmable LED Light*

# Albin

P250036-028-30 Matte White

Matte White

P250036-031-30 Matte Black

Toasted Oak

P250036-129-30 Architectural Bronze

Distressed Walnut



P250036-028-30  
shown with Matte White blades



P250036-031-30  
shown with Toasted Oak blades



P250036-129-30  
shown with Distressed Walnut blades

## ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	5,740 cubic feet per minute
<b>Electricity Use</b>	67 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	95 CFM/W



Three Speed Remote Control Included  
Three speed fan operation  
Full range dimming with light

## FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Plywood blades
- Damp Location Rated
- White opal glass shade
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 wall control

## SIZE

54" dia., 15-5/8" ht.  
80" lead wires.

## LAMP

24w LED Module, 3000K,  
90 CRI, 2000 source lumens,  
dimmable.





# Accessory Downrods


3/4" diameter; approximately 1" outside diameter.

CEILING HT.	9'-10'	10'-11'	11'-12'	12'-14'	13'-15'	14'-16'	15'-17'
DOWNROD L.	12"	18"	24"	36"	48"	60"	72"
Brushed Nickel -09	P2603-09	P2604-09	P2605-09	P2606-09	P2607-09	P2608-09	P2609-09
Polished Chrome -15	P2603-15	P2604-15	P2605-15	P2606-15	P2607-15	P2608-15	P2609-15
Antique Bronze -20	P2603-20	P2604-20	P2605-20	P2606-20	P2607-20	P2608-20	P2609-20
Matte White -28	P2603-28	P2604-28	P2605-28	P2606-28	P2607-28	P2608-28	P2609-28
White -30	P2603-30	P2604-30	P2605-30	P2606-30	P2607-30	P2608-30	P2609-30
Matte Black -31	P2603-31	P2604-31	P2605-31	P2606-31	P2607-31	P2608-31	P2609-31
Guided Iron -71	P2603-80	P2604-80	P2605-80	P2606-80	P2607-80	P2608-80	P2609-80
Forged Black -80	P2603-80	P2604-80	P2605-80	P2606-80	P2607-80	P2608-80	P2609-80
Antique Nickel -81	P2603-81	P2604-81	P2605-81	P2606-81	P2607-81	P2608-81	P2609-81
Oil Rubbed Bronze -108	P2603-20	P2604-20	P2605-20	P2606-20	P2607-20	P2608-20	P2609-20
Architectural Bronze -129	P2603-20	P2604-20	P2605-20	P2606-20	P2607-20	P2608-20	P2609-20
Galvanized -141	P2603-141	P2604-141	P2605-141	P2606-141	P2607-141	P2608-141	P2609-141
Graphite -143	P2603-143	P2604-143	P2605-143	P2606-143	P2607-143	P2608-143	P2609-143
Painted Nickel -152	P2603-152	P2604-152	P2605-152	P2606-152	P2607-152		
Vintage Brass -163	P2603-163	P2604-163	P2605-163	P2606-163	P2607-163		
Blistered Iron -171	P2603-171	P2604-171	P2605-171	P2606-171	P2607-171		
Black Chrome -231	P2603-231	P2604-231	P2605-231	P2606-231	P2607-231		

# Downrod Selection Guide

Allow at least 7 feet (84 in.) from the floor to the bottom of the fan, with 8 or 9 feet being the ideal above-floor placement.

\*Average length downrod, included with each fan.



# Remotes, Wall Controls & 45° Canopies



**P2663-01**  
Fan/Light Remote  
Universal remote with two, four or eight-hour timer option, operates three fan speeds and full-range dimming light control. Includes canopy receiver and wall storage bracket. Will work with LED lamps and modules. Featuring many code combination options to avoid the chance of interference from other remotes.



**P2661-01**  
Universal Fan/Light Remote  
Provides fan speed and full range light dimming control from a convenient hand held remote control. For single pole applications. Includes a wall plate for added storage convenience. Receiver fits in the fan canopy.



**P2665-30 White**  
Universal remote includes a wall mount transmitter, that operates three fan speeds and full-range dimming light control. Includes canopy receiver and wall storage bracket. Will work with LED lamps and modules. Featuring four "dip" switches and 16 code options to avoid the chance of interference from other remotes.



**P2630-30 White**  
Four-speed fan wall control with full-range light dimmer. Fits single-gang wall box; requires two circuits. Includes switch plate cover. Not for use with multiple fans.



**P2613-30 White**  
Four-speed fan wall control. Includes switch plate cover. Not for use with multiple fans.

# Fan Blade Finishes



American Walnut




Black Chrome



Cottage White



Driftwood




Natural Cherry




Walnut



Antique Black



Blistered Iron



Dark Bamboo



Galvanized



Oak



Washed Oak




Antique Bronze



Brushed Nickel



Dark Cherry



Graphite



Rustic Charcoal



White Barnwood




Antique Wood



Cherry



Dark Walnut



Gray Weathered Wood



Pewter



White Metallic




Architectural Bronze



Chestnut



Distressed Ebony




Koa Woodgrain



Silver



White Washed




Black



Classic Walnut



Distressed Walnut



Distressed White



Medium Cherry



Toasted Oak



All finish representations are part of Progress Lighting's comprehensive design and specification program. Through extensive research, these finishes have been carefully chosen to complement all Progress Lighting products, including our extensive range of materials and accessory options.

These finish representations match actual finish colors as accurately as possible, and while every effort has been made to render colors accurately, they may vary slightly from the actual product, especially hand-painted finishes due to the nature of hand craftsmanship.



# Symbol Legend



Products referencing this logo meet the energy efficiency requirements for ceiling fans and or ceiling fan light kits set forth in ENERGY STAR® product specifications. Please refer to [www.energystar.gov](http://www.energystar.gov) for specific product qualifications and list of certified products.



Please note indoor only (dry location) fans should only be used indoors. Even if an outdoor area or screened-in porch is covered, the motor and the blades can be affected when exposed to humidity. You can, however, “bring the outdoors inside” – as using outdoor ceiling fans are perfectly acceptable to use in interior spaces.



If you are selecting a ceiling fan for a space that is outdoors and under a roof, i.e. any covered porches; you should select either a damp rated or wet listed fan. Damp location fans may also be used indoors.



If the fan comes directly into contact with water, you’ll need to ensure that the ceiling fan has a “wet” listing. Ceiling fans designed for damp or wet locations feature elements, such as moisture-resistant motors and all weather blades. Wet location fans may also be used indoors.



This marking indicates fixtures that have an integrated LED or replaceable LED module or LED lamps that has been tested and listed in the California Appliance Database. Check for certified lamps, fixtures or LED light engines by searching the MAEDBS database. Go to [cacertappliances.energystar.gov](http://cacertappliances.energystar.gov)



Complies with “American with Disabilities Act”



Products comply with the California Appliance Efficiency Regulations. Certified products are listed on the appliance efficiency database found at [www.appliances.energy.ca.gov](http://www.appliances.energy.ca.gov).



Products with this icon are Dark-Sky Friendly: they are certified by the International Dark-Sky Association to minimize glare while reducing light trespass and skyglow (they don’t pollute the night sky.)



The products with this logo have passed the cUL requirements and are available for sale in Canada. These products include the additional safety features needed to comply with the regulations in Canada. Items with the icon are listed with NRCan.



Products with this icon are WiFi compatible and may be controlled with WiFi when one of the following controls is added;

- AC Motor fans can add the P2667-31 WiFi remote control
- DC Motor fans that are WiFi compatible can add the P2673-01 WiFi module.

With the addition of one of the above controls, you may easily control your fan or light with your smart phone, tablet, voice controls, or hand held remote. Use the Smart by Bond technology to control on/off function of the fan and the light kit along with full range dimming and fan speed control..



Products with this icon have WiFi Control Included. Easily control your fan with your smart phone, tablet, voice controls, or a hand held remote. Use the Smart by Bond technology to control on/off function of the fan and the light kit along with full range dimming and fan speed control.

## Warranty

For more details regarding product warranty coverage, please consult a qualified Progress Lighting distributor or visit:

[www.progresslighting.com/warranty](http://www.progresslighting.com/warranty)

## Where to buy

To purchase Progress Lighting products from one of our authorized dealers visit:

[www.progresslighting.com/where-to-buy](http://www.progresslighting.com/where-to-buy)

## See Yourself Here

---

Every home and every family has a story that's all their own. In this issue, we introduce you to the many ways Progress Lighting can bring that story to life.



PROGRESS LIGHTING

701 Millennium Boulevard  
Greenville, SC 29607

[www.progresslighting.com](http://www.progresslighting.com)

