



# CEILING FAN CATALOG 2022





See Yourself Here.

Lighting helps tell a story, whether it's setting the mood or enjoying a special moment. These occasions are meaningful, expressive, and shared with those we care about most. Let Progress be your guide in illuminating these spaces into special places.

# Table of Contents

Fan Inspiration 16

Our ceiling fans do more than cool a room - they combine beautiful design with premium performance. Choose from fans that make a statement across a variety of design trends, from simple to spectacular.

Indoor Fans 24



Outdoor Fans 170



Accessories 202

Light Kits 206






Downrods 212

Remotes 213


Cross Reference Chart 214

Blade Finishes 218

## Be Inspired

-  @ProgressLtg
-  @ProgressLtg
-  @ProgressLighting
-  @ProgressLtg
-  Progress Lighting
-  Progress-Lighting

# Indoor Ceiling Fans



# Indoor Ceiling Fans




























# Indoor Ceiling Fans

<b>BRIARWOOD</b> Graphite p.35	<b>BRIARWOOD</b> Matte Black p.35	<b>42" BUILDER FAN</b> Antique Bronze p.153	<b>42" BUILDER FAN</b> Brushed Nickel p.153	<b>42" BUILDER FAN</b> White p.153
<b>52" BUILDER FAN</b> Antique Bronze p.155	<b>52" BUILDER FAN</b> Brushed Nickel p.155	<b>52" BUILDER FAN</b> Graphite p.155	<b>52" BUILDER FAN</b> Polished Chrome p.155	<b>52" BUILDER FAN</b> White p.155
<b>52" BUILDER FAN WITH LIGHT KIT</b> Architectural Bronze p.154	<b>52" BUILDER FAN WITH LIGHT KIT</b> Brushed Nickel p.154	<b>52" BUILDER FAN WITH LIGHT KIT</b> White p.154	<b>CALEB</b> Antique Bronze p.64	<b>CALEB</b> Antique Bronze p.65
<b>CALEB</b> Brushed Nickel p.65	<b>CALEB</b> Brushed Nickel p.65	<b>CARROLLWOOD</b> Brushed Nickel p.95	<b>CARROLLWOOD</b> Matte Black p.94	<b>CARROLLWOOD</b> White p.95
<b>CHAPIN</b> Antique Nickel p.103	<b>CHAPIN</b> Graphite p.103	<b>CHAPIN</b> Oil Rubbed Bronze p.102	<b>CLARET</b> Brushed Nickel p.113	<b>CLARET</b> Matte Black p.113

# Indoor Ceiling Fans

<b>CLARET</b> Oil Rubbed Bronze p.112	<b>CLIFTON HEIGHTS</b> Antique Bronze p.141	<b>CLIFTON HEIGHTS</b> Brushed Nickel p.140	<b>DRIFT</b> Architectural Bronze p.159	<b>DRIFT</b> Brushed Nickel p.158
<b>DRIFT</b> White p.159	<b>EDGEFIELD</b> Antique Bronze p.156	<b>EDGEFIELD</b> Brushed Nickel p.157	<b>EDGEFIELD</b> White p.157	<b>ELLWOOD</b> Antique Bronze p.63
<b>ELLWOOD</b> Brushed Nickel p.62	<b>FARRIS</b> Brushed Nickel p.79	<b>FARRIS</b> Graphite p.79	<b>FARRIS</b> Oil Rubbed Bronze p.78	<b>FRESNO</b> Antique Bronze p.122
<b>FRESNO</b> Brushed Nickel p.123	<b>FRESNO</b> White p.123	<b>GAZE</b> Antique Bronze p.83	<b>GAZE</b> Black p.83	<b>GAZE</b> Brushed Nickel p.83
<b>GAZE</b> Polished Chrome p.82	<b>GLANDON</b> Antique Nickel p.96	<b>GLANDON</b> Gilded Iron p.97	<b>GLENFALLS</b> Brushed Nickel p.111	<b>GLENFALLS</b> Matte White p.110

# Indoor Ceiling Fans

<b>GLENFALLS</b> Matte Black p.111 	<b>GRACEFUL</b> Antique Bronze p.115 	<b>GRACEFUL</b> Brushed Nickel p.114 	<b>GRACEFUL</b> Polished Chrome p.115 	<b>GREER</b> Antique Nickel p.100 
<b>GREER</b> Gilded Iron p.101 	<b>GULLIVER</b> Galvanized p.38 	<b>GULLIVER</b> Graphite p.39 	<b>GUST</b> Antique Bronze p.117 	<b>GUST</b> Brushed Nickel p.116 
<b>GUST</b> Graphite p.117 	<b>HARRANVALE</b> Antique Bronze p.109 	<b>HARRANVALE</b> Graphite p.108 	<b>HARRANVALE</b> White p.109 	<b>HOLLAND</b> Black p.89 
<b>HOLLAND</b> Brushed Nickel p.88 	<b>HOLLAND</b> Oil Rubbed Bronze p.89 	<b>42" HUGGER FAN</b> Brushed Nickel p.169 	<b>42" HUGGER FAN</b> White p.169 	<b>52" HUGGER FAN</b> Brushed Nickel p.168 
<b>52" HUGGER FAN</b> White p.168 	<b>HUFF</b> Black p.67 	<b>HUFF</b> Brushed Nickel p.66 	<b>HUFF</b> Matte White p.67 	<b>KAYVILLE</b> Antique Nickel p.52 

# Indoor Ceiling Fans

<b>KAYVILLE</b> Graphite p.53 	<b>KASOTA</b> Graphite p.175 	<b>KASOTA</b> Oil Rubbed Bronze p.174 	<b>KASOTA</b> Painted Nickel p.175 	<b>KENNEDEALE</b> Matte White p.193 
<b>KENNEDEALE</b> Painted Nickel p.193 	<b>KENNEDEALE</b> Matte Black p.192 	<b>KUDOS</b> Brushed Nickel p.120 	<b>LINDALE</b> Antique Nickel p.167 	<b>LINDALE</b> Architectural Bronze p.166 
<b>LINDALE</b> Matte White p.167 	<b>LORING</b> Galvanized p.41 	<b>LORING</b> Matte Black p.40 	<b>MANVEL</b> Antique Bronze p.77 	<b>MANVEL</b> Antique Nickel p.76 
<b>MANVEL</b> Matte Black p.77 	<b>MESILLA</b> Antique Bronze p.55 	<b>MESILLA</b> Antique Nickel p.54 	<b>MESILLA</b> Flat Black p.55 	<b>ORIOLE</b> Architectural Bronze p.90 
<b>ORIOLE</b> Black p.91 	<b>ORIOLE</b> Brushed Nickel p.91 	<b>52" PERFORMANCE</b> Antique Bronze p.152 	<b>52" PERFORMANCE</b> Brushed Nickel p.152 	<b>52" PERFORMANCE</b> White p.152 

# Indoor Ceiling Fans

<b>ROYER</b> Antique Nickel p.93	<b>ROYER</b> Forged Black p.92	<b>RYNE</b> Matte White p.31	<b>RYNE</b> Matte Black p.30	<b>RYNE</b> Koa Woodgrain p.31
<b>SANFORD</b> Architectural Bronze p.42	<b>SANFORD</b> Brushed Nickel p.43	<b>SIGNATURE</b> Antique Bronze p.133	<b>SIGNATURE</b> Brushed Nickel p.132	<b>SIGNATURE</b> Brushed Nickel p.133
<b>SIGNATURE</b> Forged Black p.133	<b>SIGNATURE PLUS</b> Antique Bronze p.139	<b>SIGNATURE PLUS</b> Brushed Nickel p.139	<b>SIGNATURE PLUS</b> White p.139	<b>SIGNATURE PLUS II</b> Antique Bronze p.138
<b>SIGNATURE PLUS II</b> Brushed Nickel p.138	<b>SIGNATURE PLUS II</b> White p.138	<b>SOAR</b> Antique Bronze p.106	<b>SOAR</b> Brushed Nickel p.107	<b>SOAR</b> White p.107
<b>SPADES</b> Brushed Nickel p.85	<b>SPADES</b> Graphite p.85	<b>SPADES</b> Polished Chrome p.84	<b>SPICER</b> Brushed Nickel p.61	<b>SPICER</b> Antique Bronze p.60

# Indoor Ceiling Fans


<b>SPICER</b> Matte Black p.61	<b>52" SPRINGER</b> Antique Nickel p.46	<b>52" SPRINGER</b> Architectural Bronze p.47	<b>52" SPRINGER</b> Matte Black p.47	<b>60" SPRINGER</b> Antique Nickel p.51
<b>60" SPRINGER</b> Architectural Bronze p.51	<b>60" SPRINGER</b> Matte Black p.50	<b>TEMPT</b> Antique Bronze p.125	<b>TEMPT</b> Polished Chrome p.125	<b>TEMPT</b> Vintage Brass p.124
<b>TREVINA II 44"</b> Black p.134	<b>TREVINA II 44"</b> Brushed Nickel p.134	<b>TREVINA II 44"</b> Satin White p.134	<b>TREVINA II 52"</b> Antique Bronze p.135	<b>TREVINA II 52"</b> Architectural Bronze p.135
<b>TREVINA II 52"</b> Brushed Nickel p.135	<b>TREVINA II 52"</b> Painted Nickel p.135	<b>TREVINA II 52"</b> White p.135	<b>VAST</b> Antique Bronze p.69	<b>VAST</b> Brushed Nickel p.69
<b>VAST</b> Matte Black p.68	<b>VAST</b> White p.69	<b>VERADA</b> Antique Bronze p.127	<b>VERADA</b> Brushed Nickel p.126	<b>VERNAL</b> Matte Black p.29

# Indoor Ceiling Fans

**VERNAL** Painted Nickel p.29    **VERNAL** Koa Woodgrain p.28    **VOX FAN** Antique Bronze p.165    **VOX FAN** Brushed Nickel p.164    **VOX FAN** White p.165



**WILLACY** Matte Black p.33    **WILLACY** Painted Nickel p.32



# Outdoor Ceiling Fans

 Damp Location Listed

**ALBIN** Architectural Bronze p.194    **ALBIN** Matte Black p.195    **ALBIN** Matte White p.195    **ALLERON** Antique Nickel p.57    **ALLERON** Flat Black p.56



**ALFRESCO** Architectural Bronze p.186    **ALFRESCO** Blistered Iron p.187    **ARLO** Architectural Bronze p.73    **ARLO** Black p.73    **ARLO** Brushed Nickel p.72



# Outdoor Ceiling Fans

 Damp Location Listed

**BELVA** Matte Black p.36    **BELVA** Cottage White p.37    **BIXBY** Black Chrome p.74    **BIXBY** White p.75    **BRIARWOOD** Antique Bronze p.34



**BRIARWOOD** Galvanized p.35    **BRIARWOOD** Graphite p.35    **BRIARWOOD** Matte Black p.35    **DECORATIVE PATIO FAN** Antique Bronze p.198    **EDWIDGE** Matte White p.181



**EDWIDGE** Matte Black p.181    **EDWIDGE** Painted Nickel p.180    **GULLIVER** Galvanized p.38    **GULLIVER** Graphite p.39    **HOLLAND** Brushed Nickel p.88



**HOLLAND** Black p.89    **HOLLAND** Oil Rubbed Bronze p.89    **HUFF** Black p.67    **HUFF** Brushed Nickel p.66    **HUFF** Matte White p.67



**KASOTA** Graphite p.175    **KASOTA** Oil Rubbed Bronze p.174    **KASOTA** Painted Nickel p.175    **KAYSVILLE** Antique Nickel p.52    **KAYSVILLE** Graphite p.53













# Outdoor Ceiling Fans

 Damp Location Listed

<p><b>KENNEDEALE</b> Matte White p.193</p> 	<p><b>KENNEDEALE</b> Painted Nickel p.193</p> 	<p><b>KENNEDEALE</b> Matte Black p.192</p> 	<p><b>MANVEL</b> Antique Bronze p.77</p> 	<p><b>MANVEL</b> Antique Nickel p.76</p> 
<p><b>MANVEL</b> Matte Black p.77</p> 	<p><b>MESILLA</b> Antique Bronze p.55 </p> 	<p><b>MESILLA</b> Antique Nickel p.54 </p> 	<p><b>MESILLA</b> Flat Black p.55 </p> 	<p><b>MIDVALE</b> Blistered Iron p.177</p> 
<p><b>MIDVALE</b> Galvanized p.176</p> 	<p><b>MIDVALE</b> Matte White p.177</p> 	<p><b>RUDDER</b> Architectural Bronze p.179</p> 	<p><b>RUDDER</b> Matte Black p.179</p> 	<p><b>RUDDER</b> Matte White p.178</p> 
<p><b>RYNE</b> Matte White p.31</p> 	<p><b>RYNE</b> Matte Black p.30</p> 	<p><b>RYNE</b> Koa Woodgrain p.31</p> 	<p><b>SANFORD</b> Architectural Bronze p.42</p> 	<p><b>SANFORD</b> Brushed Nickel p.43</p> 
<p><b>SPICER</b> Brushed Nickel p.61 </p> 	<p><b>SPICER</b> Antique Bronze p.60 </p> 	<p><b>SPICER</b> Matte Black p.61 </p> 	<p><b>VAST</b> Antique Bronze p.69</p> 	<p><b>VAST</b> Brushed Nickel p.69</p> 














# Outdoor Ceiling Fans

 Damp Location Listed

<p><b>VAST</b> Matte Black p.68</p> 	<p><b>VAST</b> White p.69</p> 	<p><b>VERNAL</b> Matte Black p.29</p> 	<p><b>VERNAL</b> Painted Nickel p.29</p> 	<p><b>VERNAL</b> Koa Woodgrain p.28</p> 
<p><b>WHIRL</b> Antique Bronze p.183</p> 	<p><b>WHIRL</b> Antique Nickel p.182</p> 	<p><b>WHIRL</b> Forged Black p.183</p> 	<p><b>WILLACY</b> Matte Black p.33</p> 	<p><b>WILLACY</b> Painted Nickel p.32</p> 

# Outdoor Ceiling Fans

 Wet Location Listed

<p><b>LAKEHURST</b> Antique Bronze p.196</p> 	<p><b>LAKEHURST</b> Forged Black p.197</p> 	<p><b>LAKEHURST</b> White p.197</p> 	<p><b>MONTAGUE</b> Antique Bronze p.191</p> 	<p><b>MONTAGUE</b> Forged Black p.190</p> 
<p><b>MONTAGUE</b> White p.191</p> 	<p><b>52" PATIO FAN</b> Antique Bronze p.200</p> 	<p><b>52" PATIO FAN</b> Forged Black p.200</p> 	<p><b>52" PATIO FAN</b> Galvanized p.200</p> 	<p><b>52" PATIO FAN</b> White p.200</p> 
<p><b>54" PATIO FAN</b> Antique Bronze p.200</p> 	<p><b>SMYRNA</b> Antique Bronze p.188</p> 	<p><b>SMYRNA</b> Forged Black p.189</p> 		





# Introducing the New AirPro 52" 5-Blade Ceiling Fan



**NEW**  
CONTEMPORARY DESIGN  
(from P2501)

STYLISH  
MOTOR  
HOUSING

MODERN  
FAN BLADE  
BRACKET

SLEEK BLADES

SHATTERPROOF  
LIGHT SHADE  
*(except P250085)*

The AirPro 52" 5-blade ceiling fan refreshes interiors with a sleek, modern form. Five clean-lined fan blades extend outward from a streamlined motor housing that contains a powerful AC motor. Its versatile yet timeless design makes it ideal for a wide range of interior décor styles. The fan can be installed on a flat or sloped ceiling.

### Multiple options

- Three AC motor Energy Star rated models
- Light kits (single poly dome shades, 4-light seeded glass or poly shades)
- On-trend finishes

**SEE PAGE 142 - 149 FOR PRODUCT DETAILS.**

**Captive Screws**  
allow for quick and easy fan blade arm installation.

**Unipack Options**  
package the light kit with the fan, eliminating need to order the light kit separately.

**Accessories**  
All fans can accept an accessory wall and remote control (sold separately).

**Light Kits**  
All light kits include medium based, 3000K LED lamps.



# Fan Inspiration

Ceiling Fans can serve as a statement piece or even the focal point of a room.

Today's ceiling fans incorporate beautiful features, such as hand carved blades, sleek finishes and natural elements to appeal to a variety of different design trends.

At Progress Lighting, we strive to incorporate this shift in our ceiling fan designs and are eager to present an expanded offering in this catalog.

# The Perfect Fan in 5 Steps



Scan with the camera on your smartphone to explore more styles at [www.progresslighting.com/styles](http://www.progresslighting.com/styles)

## Ceiling Fan Buyer's Guide

Ceiling fans are practical and efficient solutions for creating comfortable and welcoming living areas. With many styles, functions and features to choose from, narrowing down the choices can be a challenge. Here we present five tips for selecting the perfect ceiling fan for your home.

1

### Settle on Style

Choose a style that complements your décor. Consider fan shape, blade features and finish to help you meet your room's design needs. Choose from Traditional, Transitional, Coastal or Farmhouse styles. The possibilities are vast!



*Modernly Minimal*

See full trendboard page 204



*Modern + Edgy*

See full trendboard page 26



*Easy, Breezy, Coastal*

See full trendboard page 172

# Indoor



Featuring Glandon

# Outdoor




Featuring Spicer

## 2 Explore Indoor vs. Outdoor Uses

Fans provide a breezy setting for reading a book or catching up with friends, making them ideal for outdoor rooms. However, it's important to consider the certifications on the fan depending on the use. For high humidity areas, choose a UL-Listed fan for Damp Locations and for spaces that will be exposed to weather, choose a UL-Listed fan for Wet Locations. For interior use in dry spaces with minimal condensation, select a UL-Listed fan for Dry Locations. See testing listings defined on page 23.

## The Perfect Fan in 5 Steps *continued...*



### 3 Get Your Height Right

You want to allow at least 7 feet (84 in.) from the floor to the bottom of the fan, with 8 or 9 feet being the ideal above-floor placement. For lower ceilings, consider a ceiling fan with a low profile to avoid disturbing inhabitants. Most ceiling fans come equipped with a down rod to help you adjust to the correct height.

### 4 Size It To Your Space

Size is really important when selecting your ceiling fan. If a fan is too large, it can overwhelm the space. On the flip side, if the fan is too small, the airflow may be inadequate for that area.

Room Size (in square feet)	Fan Size (in inches)
0 - 75	0 - 36
76 - 144	36 - 42
145 - 225	42 - 50
226 - 360	50 - 54
361 - 499	54 - 70
500+	70+

# The Perfect Fan in 5 Steps *continued...*

## 5 Choose Your Features

There are many different features to choose from when browsing ceiling fans.

### Blade Finish Options

Multiple blade finish options to coordinate with your home decor.

Example blade options for P2568-0930K:

- Silver
- American Walnut



### Reversible Motor

Typically, ceiling fans are used to help cool you down and keep the air flowing with a counter-clockwise blade direction. However, fans can also keep you warm when the direction of the blades is reversed. Select a fan with reversible motor for the option to circulate cool or warm air. Most ceiling fans have a small switch located either on the motor housing or the switch cup.



### LED

Consider an LED or Energy Star rated fixture to save energy.



P2568-0930K



### Light Kit

For a layered lighting effect, install a ceiling fan with a pre-installed light kit to complement your existing fixtures.



Scan for "The Perfect Fan in 5 Steps" with Steve Register or visit [youtube.com/user/ProgressLtg](https://www.youtube.com/user/ProgressLtg)

[WWW.PROGRESSLIGHTING.COM](http://www.progresslighting.com)

P2662-01

### Remote Control with Full Range Dimming

Full range dimming and hand-held remote control capabilities are available to offer an added convenience in controlling a room's environment.

# Control from Anywhere with WiFi



P2667-31

WiFi enabled



Easily control your fan with your smartphone, tablet, voice or hand-held remote.

*Compatible with Any Progress AC Motor*

*Full Range Dimming Control*

*Breeze Mode on App*

*On/Off Function for Fan and Light Kit*

*Control from your pocket*




For more details, visit [www.progresslighting.com/ceilingfans](http://www.progresslighting.com/ceilingfans)

Featuring Gaze

# LED Light Kits

## Save Money and Energy

When you select a high-quality LED fixture, you can expect a significant return on investment from an energy conservation standpoint. Here are some of the energy saving benefits of LEDs from Progress Lighting:



Whirl  
P2574-8130K  
shown with Driftwood blades

## Features



LED sources use at least 75% less energy than incandescent lighting, allowing homeowners to save on operating expenses.



LEDs last 35 to 50 times longer than incandescent sources and approximately 2 to 5 times longer than fluorescent lighting. Meaning, less bulb maintenance!



LEDs do not use power when they are turned off. According to MSN Real Estate, LED lights can result in an annual bill as low as \$26.



LEDs do not produce heat like traditional sources, reducing cooling costs. Traditional incandescent bulbs waste 98% of the energy they consume on heat.

# Find Your Rating

## Indoor, Damp and Wet Location

All ceiling fans sold in the United States have been tested and rated by either Underwriters Laboratories (UL) or Intertek (ETL), each an independent product safety certification organization. It's important to pay attention to the rated listing when purchasing a ceiling fan as it will tell you what location the fan was designed for. There are three location options: dry, damp and wet.



Image: Dostie Homes



### Dry Location

Please note indoor only (dry location) fans should only be used indoors. Even if an outdoor area or screened-in porch is covered, the motor and the blades can be affected when exposed to humidity. You can, however, “bring the outdoors inside” – as using outdoor ceiling fans are perfectly acceptable to use in interior spaces.

### Damp Location

If you are selecting a ceiling fan for a space that is outdoors and under a roof, i.e. any covered porches; you should select either a damp rated or wet listed fan. Damp location fans may also be used indoors.





Image: Arthur Rutenberg Homes



### Wet Location

If the fan comes directly into contact with water, you'll need to ensure that the ceiling fan has a “wet” listing. Ceiling fans designed for damp or wet locations feature elements, such as moisture-resistant motors and all weather blades. Wet location fans may also be used indoors.



# Indoor Ceiling Fans

*Experience the versatility  
ceiling fans provide*



Scan with your camera on  
your smartphone or visit  
[www.progresslighting.com/ceilingfans](http://www.progresslighting.com/ceilingfans)

**Arlo**  
P250026-009-30



Steve Register  
Senior Product Manager  
Ceiling Fans

## Modern + Edgy

with Steve

Quirky and functional, this style's flair comes from its modern, yet retro, juxtaposition. Mid-Century Modern style furniture adds unique shapes and pops of color to a room. Designers look for statement pieces to complete the look. This style is gravitating toward a cleaner, more minimalistic look through the incorporation of a neutral palette and softer accent colors. Mid-Century

Modern homes are largely characterized by the use of wood textures to create a sense of connection to nature and the outdoors.



Shop this style at  
[www.progresslighting.com/mid-century-modern](http://www.progresslighting.com/mid-century-modern)



# Vernal

P250059-179-30  
shown with Koa Woodgrain blades

**FINISHES**

- Matte Black - 031
- Painted Nickel - 152
- Koa Woodgrain - 179



WiFi included

Vernal refreshes a room's decor with elegant curves and an expansive 60-inch, five-blade span for the ultimate in design-savvy comfort. Vernal includes WiFi smart control: once installed, Vernal can be controlled by a voice assistant, tablet or smart phone. Finished in Koa Woodgrain, Matte Black or Painted Nickel, Vernal is designed to complement New Traditional and Transitional interiors.

*Integrated Smart Control*

*Elegant Curves*

*Dimmable LED Light*



P250059-031-30  
shown with Matte Black blades



P250059-152-30  
shown with Painted Nickel blades



P250059-179-30  
shown with Koa Woodgrain blades  
with Architectural Bronze accents

# Vernal

P250059-031-30 Matte Black



Matte Black

P250059-152-30 Painted Nickel



Painted Nickel

P250059-179-30 Koa Woodgrain



Koa Woodgrain

**ENERGY INFORMATION AT HIGH SPEED**

<b>Airflow</b>	6,810 cubic feet per minute
<b>Electricity Use</b>	34 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	242 CFM/W

**FEATURES**

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- ABS blades
- Opal shatterproof shade
- WiFi enabled
- Remote control with batteries is included

**SIZE**

60" dia., 14-1/4" ht.  
80" lead wires.

**LAMP**

18w LED Module, 3000K,  
90 CRI, 1600 source lumens,  
dimmable.



Full Function Remote Control Included  
Six-speed fan operation  
Full-range dimming for light  
Reverse direction control





# Ryne

P250060-031-30  
shown with Matte Black blades

**FINISHES**

- Matte White- 028
- Matte Black - 031
- Koa Woodgrain - 179



WiFi compatible

The 52-inch Ryne fan is modern in appeal, with beautifully flowing blades that join in the middle to create a minimalistic housing. Ryne is smart control adaptable with the P2673 WiFi Module: once installed, Ryne can be controlled by a voice assistant, tablet or smart phone. Ryne's aerodynamic design and Koa Woodgrain, Matte White or Matte Black finish perfectly suits New Traditional and Transitional interiors.

*Modern Appeal*

*Aerodynamic Design*

*Dimmable LED Light*



P250060-028-30  
shown with Matte White blades



P250060-031-30  
shown with Matte Black blades



P250060-179-30  
shown with Koa Woodgrain blades  
with Architectural Bronze accents



P2673-01

# Ryne

**P250060-028-30** Matte White




Matte White

**P250060-031-30** Matte Black



Matte Black

**P250060-179-30** Koa Woodgrain



Koa Woodgrain

**DC FAN WIFI MODULE  
P2673-01**

Add the WiFi module to your Ryne ceiling fan for control at your fingertips. You can easily control your fan with a hand-held remote; or a smart phone, tablet, voice assistant (Amazon Alexa and Google Home) via the Smart By Bond app.

**ENERGY INFORMATION AT HIGH SPEED**

<b>Airflow</b>	5,802 cubic feet per minute
<b>Electricity Use</b>	33 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	204 CFM/W



Full Function Remote Control Included  
Six-speed fan operation  
Full-range dimming for light  
Reverse direction control

**FEATURES**

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- ABS blades
- Opal shatterproof shade
- Remote control with batteries is included
- Add a P2673-01 WiFi module to convert to a smart fan

**SIZE**

52" dia., 13-1/2" ht.  
80" lead wires.

**LAMP**

18w LED Module, 3000K, 90 CRI,  
1600 source lumens, dimmable.



# Willacy

P250063-152  
shown with Painted Nickel blades

**FINISHES**


- Matte Black - 031
- Painted Nickel - 152



WiFi included

Willacy is striking in design, inspired by flowing ribbons that swirl around a gleaming center hub to create a gentle breeze. Willacy includes WiFi smart control: once installed, the fan can be controlled by a voice assistant, tablet or smart phone. Willacy features all weather hand finished ABS blades making it ideal for indoor or outdoor use.

*Striking Design*



*Ribbon-Like Blades*

*For Indoor & Outdoor Use*

# Willacy

**P250063-031** Matte Black



Matte Black

**P250063-152** Painted Nickel



Painted Nickel



P250063-031  
shown with Matte Black blades



P250063-152  
shown with Painted Nickel blades

**ENERGY INFORMATION AT HIGH SPEED**

<b>Airflow</b>	4,544 cubic feet per minute
<b>Electricity Use</b>	14 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	318 CFM/W

**FEATURES**

- Limited Lifetime Warranty
- DC Motor
- ABS blades
- WiFi enabled
- Remote control with batteries is included

**SIZE**

48" dia., 14-1/2" ht.  
12" lead wires.



Full Function Remote Control Included  
Six-speed fan operation  
Reverse direction control

# Briarwood

## FINISHES

- Antique Bronze - 020
- Galvanized - 141
- Graphite - 143
- Matte Black - 31M

P250067-020-WB  
with rich oak faux wood accent finish

The Briarwood ceiling fan brings vintage farmhouse detailing into the present day with a classic cross-brace pattern enclosing vintage-style bulbs and a trio of fan blades within its airy, open-frame design. Faux-painted wood accentuates Briarwood's simple geometric form, adding the perfect touch of country character to a variety of room settings.

*Farmhouse Detailing*

*Open Frame Design*

*Geometric Form*



# Briarwood

P250067-020-WB Antique Bronze



Antique Bronze

P250067-141-WB Galvanized



Galvanized

P250067-143-WB Graphite



Graphite

P250067-31M-WB Matte Black



Matte Black



P250067-020-WB  
accent color  
rich oak faux wood



P250067-143-WB  
accent color  
white washed faux wood



P250067-141-WB  
accent color  
bleached oak faux wood



P250067-31M-WB  
accent color  
ceruse black oak

## ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	1,145 cubic feet per minute
<b>Electricity Use</b>	31 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	37 CFM/W



Remote Control Included  
Three-speed fan operation  
Full-range dimming for light

## FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Add a P2630-30 or P2613-30 wall control or P2662-01 hand-held remote control
- Add the P2667-31 WiFi remote

## SIZE

22" dia., 17" ht.  
45" lead wires.

## LAMP

Four medium base 2200K 5.5w vintage LED lamps included. 500 lumens/lamp, 80 CRI, dimmable. 5.5w LED max/socket.



# Belva

P250068-31M-WB  
with mocha colored wicker'

## FINISHES


- Matte Black - 31M
- Cottage White - 151

The Belva ceiling fan offers an organic global feel and coastal charm. A lattice-like design graces the natural wicker frame, and a lovely Cottage White and Mocha finishes gives charm and depth. A trio of fan blades and vintage-style bulbs within the frame's woven structure moves air comfortably while casting a beautifully diffused glow.

*Organic Feel*

*Natural Woven Frame*

*Coastal Charm*



P250068-31M-WB  
with mocha colored wicker'

# Belva

P250068-31M-WB Matte Black



P250068-151-WB Cottage White



P250068-151-WB  
with whitewashed wicker

## ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	1,125 cubic feet per minute
<b>Electricity Use</b>	37 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	37 CFM/W

## FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Add a P2630-30 or P2613-30 wall control
- Add the P2667-31 WiFi remote

## SIZE

25-1/4" dia., 17-7/8" ht.  
45" lead wires.

## LAMP

Four medium base 2200K 5.5w vintage LED lamps included. 500 lumens/lamp, 80 CRI, dimmable. 5.5w LED max/socket.



Remote Control Included  
Three-speed fan operation  
Full-range dimming for light



# Gulliver

P250012-141-22  
shown with Antique White Wood

## FINISHES

- Galvanized - 141
- Graphite - 143

Three circular bands wrap together to create an open design. Non-metallic fan blades enclosed within a stylish cage design gives the rustic charm of a pendant combined with the functionality of a ceiling fan. Dual toned frame color combinations of Galvanized with antique white accents or Graphite with weathered gray accents. A hand painted wood grained texture complements rustic and modern farmhouse home decor, as well as urban industrial and coastal interior settings.

*Urban Industrial Design*



*Rustic Charm*

*Hand-Painted Wood*



P250012-141-22  
shown with Antique White Wood



P250012-143-22  
shown with Gray Wood

# Gulliver

P250012-141-22 Galvanized



Antique White Wood

P250012-143-22 Graphite



Gray Wood

## ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	1,297 cubic feet per minute
<b>Electricity Use</b>	39 watts (excludes lights)
<b>Airflow Efficiency</b>	33 cubic feet per minute per watt



Three-Speed Remote Control Included  
Three-speed fan operation  
Full-range dimming for light

## FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-18.5")
- AC Motor
- Reversible Motor
- Rust-proof non-metallic blades
- Damp Location Rated
- Remote control with batteries is included
- Add the P2667-31 WiFi remote

## SIZE

23" dia., 18-1/8" ht.  
42" lead wires.

## LAMP

Three medium base 2200K 5.5w vintage LED lamps included. 500 lumens/ lamp, 80 CRI, dimmable. 5.5w LED max/socket.



# Loring

## FINISHES

- Black- 031
- Galvanized - 141

Outfitted with stylish mixed metal elements, the Loring collection shows off an industrial-inspired, open-cage design. Four plywood blades and a handy remote control are ready to help you and your family stay comfortable and relaxed all year round.

P250006-031  
shown with Matte Black blades

*Open-Cage Design*



*Industrial Inspired*

*Mixed-Metal Elements*



P250006-031  
shown with Gold accent  
and Distressed Ebony blades



P250006-141  
shown with Matte Black accent  
and White Barnwood blades

# Loring

## P250006-031 Black

- Matte Black
- Distressed Ebony

## P250006-141 Galvanized

- White Barnwood
- Driftwood

## ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	1,766 cubic feet per minute
<b>Electricity Use</b>	43 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	44 CFM/W



Three Speed Remote Control Included  
Three-speed fan operation

## FEATURES

- Limited lifetime warranty
- Close-to-ceiling installation
- AC Motor
- Reversible plywood blades
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 wall control

## SIZE

33" dia., 15-1/4" ht.  
12" lead wires.



# Sanford

## FINISHES

- Brushed Nickel - 009
- Architectural Bronze - 129

P2594-12930K

Sanford delivers ultra powerful air movement and energy efficient illumination packaged in a modern design. Ideal for both interior and outdoor settings, this "fandelier" adds a contemporary style to porches, foyers, bath and vanity areas providing a wide range of applications. Sanford includes an integrated 23W LED module, offering both form and function with energy and cost-savings benefits. A three-speed remote control is included.

*Indoor or Outdoor Use*

*Contemporary Style*



*Powerful Air Movement*



P2594-0930K



P2594-12930K

# Sanford

**P2594-0930K** Brushed Nickel

**P2594-12930K** Architectural Bronze

## ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	1,008 cubic feet per minute
<b>Electricity Use</b>	37 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	27 CFM/W



Three-Speed Remote Control Included  
*Three-speed fan operation*  
*Full-range dimming for light*

## FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-18.5")
- AC Motor
- Metal blades
- Damp Location Rated
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 wall control
- Add the P2667-31 WiFi remote

## SIZE

22-7/8" dia., 17-3/4" ht.  
 80" lead wires.

## LAMP

26w LED module, 3000K, 90 CRI,  
 2638 source lumens, dimmable.



## An Industrial Edge



A simple but edgy vibe takes its cue from industrial origins.

1

Try a fandelier style ceiling fan like Sanford that delivers ultra-powerful air movement packaged in a vintage design.

2

Toss your table lamp and try two low-hanging pendants over the nightstand instead.

3

Finish the room with organic elements of wood and worn textures that celebrate the signature look of the industrial setting.



# 52" Springer

P250065-081


**FINISHES**

- Antique Nickel - 081
- Architectural Bronze - 129
- Matte Black - 31M



WiFi compatible

The sweeping style of the Springer fan is expressed in a 52" size that is ideal for boosting airflow in smaller spaces. The 12-blade ceiling fan has a rustic flair inspired by the form and function of a windmill. Springer is WiFi ready offering more versatility in control options. It is a DC motor fan and can accept the Springer light kit (sold separately). Springer offers the perfect look for Farmhouse, Industrial and Transitional settings



P250065-081




P250065-129



P250065-31M


## 52" Springer

**P250065-081** Antique Nickel




White Barnwood

**P250065-129** Architectural Bronze



Distressed Walnut

**P250065-31M** Matte Black



Rustic Charcoal

**SPRINGER LIGHT KIT**

**P260000-081-WB** Antique Nickel

**P260000-129-WB** Architectural Bronze

**P260000-31M-WB** Matte Black

Two medium base 2700K 7w vintage LED lamps included. 600 lumens/lamp, 90 CRI, dimmable. 7w LED max/socket.



*\*This light kit is only compatible with the P250065 and P250000 Springer Fans.*

**ENERGY INFORMATION AT HIGH SPEED**

<b>Airflow</b>	6296 cubic feet per minute
<b>Electricity Use</b>	30 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	245 CFM/W

**FEATURES**

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- Add a P2673-01 module to convert your fan to WiFi smart

**SIZE**

52" dia., 17-3/8" ht.  
80" lead wires.



Full Function Remote Control Included  
Six-speed fan operation  
Reverse direction control



Modern Traditional is the perfect blend of new and old.

1

Use a contemporary tonal color palette of whites and grays accented with rustic, warm wood touches to make the space feel inviting.

2

Complement the minimalist room with the rugged, statement-making style of the Springer ceiling fan.

3

Amplify modern style with the Milner wall sconce's trendy matte black finish and clear glass shades against a white-washed brick accent wall.



# Springer

- FINISHES**
- Antique Nickel - 081
  - Architectural Bronze - 129
  - Matte Black - 31M




Now Available WiFi Compatible

P250000-31M  
shown with Rustic Charcoal blades



*Windmill Inspired*



P250000-081  
shown with White Barnwood blades



P250000-129  
shown with Distressed Walnut blades




P250000-31M  
shown with Rustic Charcoal blades

## Springer


**P250000-081** Antique Nickel



**P250000-129** Architectural Bronze



**P250000-31M** Matte Black




**NOW AVAILABLE WILL ACCEPT THE P260000 LIGHT KIT**

**P260000-081-WB** Antique Nickel  
**P260000-129-WB** Architectural Bronze  
**P260000-31M-WB** Matte Black

Two medium base 2700K 7w vintage LED lamps included. 600 lumens/lamp, 90 CRI, dimmable. 7w LED max/socket.



*\*This light kit is only compatible with the P250065 and P250000 Springer Fans.*



Scan with the camera on your smartphone for the Springer installation video.

**ENERGY INFORMATION AT HIGH SPEED**

<b>Airflow</b>	6,377 cubic feet per minute
<b>Electricity Use</b>	33 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	206 CFM/W



Full Function Remote Control Included  
Six-speed fan operation  
Reverse direction control

**FEATURES**

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-22")
- DC Motor
- Plywood blades
- Full function remote control with batteries is included
- Add a P2673-01 module to convert your fan to WiFi smart

**SIZE**

60" dia., 17-3/8" ht.  
80" lead wires.



# Kaysville

P250003-081-30  
shown with Chestnut blades

- FINISHES**
- Antique Nickel - 081
  - Graphite - 143

Beautiful long bent blades appear to be held only by a simple metal band in Kaysville, offering a modern industrial style. Kaysville pairs the beauty of the blades with a strong, all-weather ABS material to prevent warping.

*Modern Style*

*Simple Metal Band*

*Dimmable LED Light*



# Kaysville

**P250003-081-30** Antique Nickel



**P250003-143-30** Graphite



P250003-081-30  
shown with Chestnut blades



P250003-143-30  
shown with Gray Weathered Wood blades

**ENERGY INFORMATION AT HIGH SPEED**

<b>Airflow</b>	9,650 cubic feet per minute
<b>Electricity Use</b>	31 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	361 CFM/W

**FEATURES**

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- ABS blades
- White Opal glass shade
- Remote control with batteries is included

**SIZE**

56" dia., 17-1/4" ht.  
80" lead wires.

**LAMP**

24w LED Module, 3000K,  
90 CRI, 2000 source lumens,  
dimmable.



Full Function Remote Control Included  
Six-speed fan operation  
Full-range dimming for light  
Reverse direction control

# Mesilla NEW

P250073-081  
shown with White Barnwood blades

**FINISHES**


- Antique Bronze - 020
- Antique Nickel - 081
- Flat Black - 182

Mesilla has an organic style that delivers natural grace and beauty to indoor and outdoor rooms. Its flower-like silhouette comes from five hand-finished ABS blades that gently wrap around the housing, with a single metal band that seems to be holding the blades on, creating a beautiful focal point. Mesilla has a DC motor for the highest efficacy and whisper-quiet operation. A full-function remote control with a battery is included.

*Organic Style*

*Natural Grace*

*Focal Point*



P250073-020  
shown with Antique Wood blades



P250073-081  
shown with White Barnwood blades



P250073-182  
shown with Gray Weathered Wood blades

## Mesilla

**P250073-020** Antique Bronze



**P250073-081** Antique Nickel



**P250073-182** Flat Black



**ENERGY INFORMATION AT HIGH SPEED**

<b>Airflow</b>	6,966 cubic feet per minute
<b>Electricity Use</b>	38 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	217 CFM/W

**FEATURES**

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- ABS blades
- Remote control with batteries is included

**SIZE**

60" dia., 14-1/4" ht.  
80" lead wires.



Full Function Remote Control Included  
Six-speed fan operation  
Full-range dimming for light  
Reverse direction control

# Alleron

P250009-182-30  
shown with Antique Black blades

- FINISHES**
- Antique Nickel - 081
  - Flat Black - 182

Reminiscent of aviation days gone by, Alleron takes its styling cues from a set of airplane propeller blades. The hand-finished ABS blades paired with a sleek metal ceiling canopy and light kit add a modern industrial flair to indoor and covered outdoor settings.



*Modern Industrial Flair*

*Propeller Inspired Blades*

*Dimmable LED Light*

# Alleron

**P250009-081-30** Antique Nickel



**P250009-182-30** Flat Black



P250009-081-30  
shown with Gray Weathered Wood blades



P250009-182-30  
shown with Antique Black blades

**ENERGY INFORMATION AT HIGH SPEED**

<b>Airflow</b>	7,801 cubic feet per minute
<b>Electricity Use</b>	20 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	423 CFM/W



Full Function Remote Control Included  
Six-speed fan operation  
Full-range dimming for light  
Reverse direction control

**FEATURES**

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- ABS blades
- White opal glass shade
- Remote control with batteries is included

**SIZE**

56" dia., 16" ht.  
80" lead wires.

**LAMP**

24w LED Module, 3000K,  
90 CRI, 2000 source lumens,  
dimmable.



# Modern Romance



Use subtle notes of soft gold and rich blue to create a romantic backdrop for dramatic black finishes and clean white walls.

1

Choose black finishes for lighting, décor and trims to add an industrial vibe to the room.

2

Create a cohesive look by selecting lighting fixtures from the same collection, like the Elara wall sconces and foyer light that showcase the collection's signature slender, chic form.

3

Punctuate the ceiling with an impressive ceiling fan like Spicer, whose clean style delivers a contemporary element.

# Spicer NEW

P250071-020  
shown with Antique Wood blades

**FINISHES**

- Brushed Nickel - 009
- Antique Bronze - 020
- Matte Black- 31M

Sleek lines and solid metal housing offer an urban industrial edge to Spicer. Three curved, hand-finished ABS blades rotate around a slim, smooth fan body, giving sophisticated style to indoor and outdoor rooms. Spicer has a DC motor for the highest efficacy and whisper-quiet operation. A full-function remote control with a battery is included.



P250071-009  
shown with Grey Weathered Wood blades



P250071-020  
shown with Antique Wood blades



P250071-31M  
shown with Antique Black blades

## Spicer

**P250071-009** Brushed Nickel



Grey Weathered Wood

**P250071-020** Antique Bronze



Antique Wood

**P250071-31M** Matte Black



Antique Black

**ENERGY INFORMATION AT HIGH SPEED**

<b>Airflow</b>	4,521 cubic feet per minute
<b>Electricity Use</b>	35 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	158 CFM/W

**FEATURES**

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- ABS blades
- Remote control with batteries is included

**SIZE**

54" dia., 11-9/16" ht.  
80" lead wires.



Full Function Remote Control Included  
Six-speed fan operation  
Reverse direction control




# Ellwood

## FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20

P2546-09  
shown with Driftwood blades

A picture of modern design, the functional minimalism of the Ellwood 68" ceiling fan is a product of advanced design. Five long and graceful blades made of carved wood move air with remarkable efficiency. Ellwood features a dual mount system and is compatible with universal light kits. A full function remote control is included.




*Modern Design*

*Carved Wood Blades*

*Dual Mount System*

# Ellwood

P2546-09 Brushed Nickel



P2546-20 Antique Bronze



P2546-09  
shown with Driftwood blades



P2546-20  
shown with Walnut blades

## ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	7,587 cubic feet per minute
<b>Electricity Use</b>	90 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	92 CFM/W

## FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Patented carved Wood blades
- Compatible with universal light kits
- Remote control with batteries is included
- Remote control may be replaced with P2631-30 wall control

## SIZE

68" dia., 16-3/4" ht.  
80" lead wires.



Full Function Remote Control Included  
Three-speed fan operation  
Reverse direction control

# Caleb

P2560-20AW  
shown with Walnut blades

## FINISHES

- Brushed Nickel - 09
- Brushed Nickel - 09WW
- Antique Bronze - 20
- Antique Bronze - 20AW

Beautiful and expansive in design, the 68" Caleb ceiling fan is ideal for use in large spaces. Bent carved wood blades are paired with either Brushed Nickel or Antique Bronze finishes. Caleb features a dual mount system and is compatible with universal light kits. A full function remote control is included.



P2560-09  
shown with Medium Cherry blades



P2560-09WW  
shown with Weathered Wood blades



P2560-20  
shown with Walnut blades



P2560-20AW  
shown with Walnut blades

# Caleb

**P2560-09** Brushed Nickel



Medium Cherry

**P2560-09WW** Brushed Nickel



Weathered Wood

**P2560-20** Antique Bronze



Walnut

**P2560-20AW** Antique Bronze



Antique Wood

## ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	7,045 cubic feet per minute
<b>Electricity Use</b>	86 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	91 CFM/W



Full Function Remote Control Included  
Three-speed fan operation  
Reverse direction control

## FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Patented bent carved wood blades
- Compatible with universal light kits
- Remote control with batteries is included
- Remote control may be replaced with P2631-30 wall control

## SIZE

68" dia., 18" ht.  
80" lead wires.




# Huff

P250030-009  
shown with Brushed Nickel blades

**FINISHES**

- Brushed Nickel - 009
- Matte White- 028
- Matte Black- 031

The hassles and headaches of the day fade away under the relaxing airflow created by the Huff Collection. Six expansive aluminum blades with decorative winglets stretch out from a dual mount center. Select a Brushed Nickel, Matte White, or Matte Black finish all with their own complementary highlights to create a perfect design for your modern or transitional space.




*Modern Design*

*Complimentary Highlights*

*Expansive Aluminum Blades*

# Huff

P250030-009 Brushed Nickel



P250030-028 Matte White



P250030-031 Matte Black



P250030-009  
shown with Brushed Nickel blades  
and Matte Black accents



P250030-028  
shown with Matte White blades  
and Brushed Nickel accents



P250030-031  
shown with Black blades  
and Brushed Nickel accents

**ENERGY INFORMATION AT HIGH SPEED**

<b>Airflow</b>	14,482 cubic feet per minute
<b>Electricity Use</b>	49 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	344 CFM/W

**FEATURES**

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- Aluminum blades
- Damp Location Rated
- Compatible with universal light kit
- Remote control with batteries is included

**SIZE**

96" dia., 15-1/2" ht.  
80" lead wires.



Full Function Remote Control Included  
Six-speed fan operation  
Reverse direction control

# Vast

P2550-3130K  
shown with Black blades


- FINISHES**
- Brushed Nickel - 09
  - Antique Bronze - 20
  - White - 30
  - Matte Black - 31

Beautiful and expansive in design, the 72" ceiling fan is ideal for use in large areas and outdoor covered areas for maximum cooling. A white opal shade complements a variety of finish options, including Brushed Nickel with chrome accents, Antique Bronze, White with chrome accents or Matte Black. Vast features a dual mount system and comes with a full function remote control.



# Vast


P2550-0930K Brushed Nickel



P2550-2030K Antique Bronze



P2550-3030K White



P2550-3130K Matte Black



P2550-0930K  
shown with Brushed Nickel blades  
and Chrome accents



P2550-2030K  
shown with Antique Bronze blades



P2550-3030K  
shown with White blades  
and Chrome accents



P2550-3130K  
shown with Black blades

**ENERGY INFORMATION AT HIGH SPEED**

<b>Airflow</b>	8,100 cubic feet per minute
<b>Electricity Use</b>	37 watts (excludes lights)
<b>DOE Weighted CFN/W</b>	247 CFM/W

**FEATURES**

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- Aluminum blades
- Damp Location Rated
- White opal glass
- Remote control with batteries is included

**SIZE**

72" dia., 16-3/4" ht  
80" lead wires.

**LAMP**

18w LED Module, 3000K, 90 CRI,  
1400 source lumens, dimmable.



Full Function Remote Control Included  
Six-speed fan operation  
Full-range dimming for light  
Reverse direction control



## Clean and Natural



Indoor-outdoor living begins with organic origins.

1

Select a large ceiling fan like Vast in covered outdoor areas to move air while making a design statement.

2

Bring the outdoors in with weathered wood furniture and organic decor.

3

Use a cool color palette and eye-catching architectural features like a double fireplace for a sophisticated, resort-like feel.

# Arlo

P250026-009-30  
shown with Brushed Nickel blades

**FINISHES**


- Brushed Nickel - 009
- Black - 031
- Architectural Bronze - 129

Unwind under the cooling breeze created by the clean, crisp blades of the Arlo collection's modern ceiling fan. A central LED light provides a perfect way to light a space without flooding the room with harsh light as six metal blades attach to the fan's center. Offered in three different finishes, Arlo is sure to create an intriguing, yet serene retreat in whatever space it calls home.

*Modern Design*

*Clean Metal Blades*

*Dimmable LED Light*



P250026-009-30  
shown with Brushed Nickel blades




P250026-031-30  
shown with Black blades



P250026-129-30  
shown with Architectural Bronze blades

## Arlo

**P250026-009-30** Brushed Nickel



**P250026-031-30** Black



**P250026-129-30** Architectural Bronze



**ENERGY INFORMATION AT HIGH SPEED**

<b>Airflow</b>	7,558 cubic feet per minute
<b>Electricity Use</b>	29 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	282 CFM/W



Full Function Remote Control Included  
Six-speed fan operation  
Full-range dimming for light  
Reverse direction control

**FEATURES**

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- Aluminium blades
- Damp Location Rated
- White Opal glass
- Remote control with batteries is included

**SIZE**

60" dia., 18-1/2" ht.  
80" lead wires.

**LAMP**

24w LED Module, 3000K, 90 CRI,  
2000 source lumens, dimmable.




# Bixby

**FINISHES**

- White - 030
- Black Chrome - 231

P250038-231-30  
shown with Black Metallic blades



*Industrial Style*

You'll find the time to unwind under the eye-pleasing, urban industrial design of the Bixby collection's ceiling fan. Breathe easy after a warm summer day or a long day at work as Bixby fosters a refreshing current of cool air with three, slightly curved Lucite blades circling a gentle LED light as it provides soothing illumination.

*Slightly Curved  
Lucite Blades*

*Dimmable LED Light*

# Bixby

**P250038-030-30** White



White Metallic

**P250038-231-30** Black Chrome



Black Metallic



P250038-030-30  
shown with White Metallic blades



P250038-231-30  
shown with Black Metallic blades

**ENERGY INFORMATION AT HIGH SPEED**

<b>Airflow</b>	6,846 cubic feet per minute
<b>Electricity Use</b>	32 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	228 CFM/W



Full Function Remote Control Included  
Six-speed fan operation  
Full-range dimming for light  
Reverse direction control

**FEATURES**

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- Polycarbonate blades
- Damp Location Rated
- White opal glass
- Remote control with batteries is included

**SIZE**

60" dia., 15-1/8" ht.  
80" lead wires.

**LAMP**

24w LED Module,  
3000K, 90 CRI,  
2000 source lumens, dimmable.



# Manvel

P250069-081  
Shown with Antique Wood Blades

**FINISHES**

- Antique Bronze - 020
- Antique Nickel - 081
- Matte Black - 31M

Offering modern elegance in a sleek form, Manvel is a 60" fan rated for indoor/outdoor with a DC motor. Three hand-finished, premium construction ABS blades give Manvel a stylish look, making it an ideal centerpiece for living rooms, great rooms or an outdoor covered porch. Manvel includes a six-speed full function remote control.



*Sleek Form*

*Premium Construction*

*Ideal Centerpiece*

# Manvel

**P250069-020** Antique Bronze



**P250069-081** Antique Nickel



**P250069-31M** Matte Black



**ENERGY INFORMATION AT HIGH SPEED**

<b>Airflow</b>	6127 cubic feet per minute
<b>Electricity Use</b>	19 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	310 CFM/W

**FEATURES**

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-25°)
- DC Motor
- ABS Blades
- Remote control with batteries is included

**SIZE**

60" dia., 11-1/4" ht.  
80" lead wires.



Full Function Remote Control Included  
Six-speed fan operation  
Reverse direction control



# Farris

P250002-108-30  
shown with Walnut blades

**FINISHES**

- Brushed Nickel - 009
- Oil Rubbed Bronze - 108
- Graphite - 143

Farris features three solid wood carved blades to form a sleek, modern design. The 60" ceiling fan includes an integrated LED light kit that is removable to provide the option in non-illuminated applications. Available in Brushed Nickel, Oil Rubbed Bronze and Graphite finishes. A full function remote control with batteries is included, and the dual mount canopy accommodates flat or sloped ceilings.



*Modern Design*

*Wood Carved Blades*

*Removable, Dimmable LED Light*

# Farris


**P250002-009-30** Brushed Nickel



**P250002-108-30** Oil Rubbed Bronze



**P250002-143-30** Graphite



**ENERGY INFORMATION AT HIGH SPEED**

<b>Airflow</b>	7,047 cubic feet per minute
<b>Electricity Use</b>	32 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	223 CFM/W



Full Function Remote Control Included  
Six-speed fan operation  
Full-range dimming for light  
Reverse direction control

**FEATURES**

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-13°)
- DC Motor
- Carved wood blades
- Removable light kit. Blank plate included.
- White opal shatterproof shade
- Full function remote control with batteries is included

**SIZE**

60" dia., 15-1/2" ht.  
80" lead wires.

**LAMP**

18w LED Module, 3000K, 90 CRI,  
1400 source lumens, dimmable.





Modern Farmhouse design embraces tradition but is firmly planted in the present.

1

Look for details like the beautifully carved, solid wood fan blades of the Farris ceiling fan that centers the room with statement-making style.

2

Modernize a traditional approach by contrasting a light and airy palette with a natural stone fireplace, weathered wood mantel and exposed beams.

3

Use organic materials for decorative accessories like greenery, wood and cozy textiles to add a welcoming touch.


# Gaze

P2554-1530K  
shown with White Washed blades

## FINISHES

- Brushed Nickel - 09
- Polished Chrome - 15
- Antique Bronze - 20
- Black - 31

Three-blade 60" Gaze ceiling fan features an LED light source, offering both form and function with energy and cost-savings benefits. An opal white shade contains an 18W dimmable, 3000K LED module. Gaze features a dual mount system and includes a three-speed remote control with full range dimming.



Dual Mount System

Dimmable LED Light

White Opal Shade



P2554-0930K  
shown with Silver blades



P2554-1530K  
shown with Cherry blades




P2554-2030K  
shown with Walnut blades




P2554-3130K  
shown with Matte Black blades

# Gaze


P2554-0930K Brushed Nickel




P2554-1530K Polished Chrome



P2554-2030K Antique Bronze



P2554-3130K Black



## ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	5,902 cubic feet per minute
<b>Electricity Use</b>	75 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	87 CFM/W



Three-Speed Remote Control Included  
Three-speed fan operation  
Full-range dimming for light

## FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- Downrod installation only. Can not be flush mounted.
- AC Motor
- Manual reverse switch
- Reversible plywood blades
- White shatterproof lens
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 wall control
- Add the P2667-31 WiFi remote

## SIZE

60" dia., 13-1/8" ht.  
80" lead wires.

## LAMP

18w LED Module, 3000K, 90 CRI,  
1400 source lumens, dimmable.



# Spades

**FINISHES**

- Brushed Nickel - 09
- Polished Chrome - 15
- Graphite - 143

P2570-15  
shown with Black blades

The 56" Spades ceiling fan features a sleek contemporary two-blade design that is finished in Brushed Nickel, polished chrome or Graphite options. Spades features a dual mount system, an energy saving DC motor and ABS composite blades. A full function remote control is included.

*Dual Mount System*

*Contemporary Design*

*Sleek Blades*



# Spades

**P2570-09** Brushed Nickel



**P2570-15** Polished Chrome



**P2570-143** Graphite



P2570-09  
shown with Silver blades



P2570-15  
shown with Black blades



P2570-143  
shown with Graphite blades

**ENERGY INFORMATION AT HIGH SPEED**

<b>Airflow</b>	6,746 cubic feet per minute
<b>Electricity Use</b>	32 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	215 CFM/W



Full Function Remote Control Included  
Six-speed fan operation  
Reverse direction control

**FEATURES**


- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-17°)
- Close-to-ceiling installation
- DC Motor
- Non-reversible ABS blades
- Will not accept a light kit
- Remote control with batteries is included

**SIZE**

56" dia., 18-1/8" ht.  
(CTC 8-1/2" ht.),  
80" lead wires.



**CTC INSTALLATION**



## Inspirational Elements

---

1

2

3

Patterns and curves inspire the design of the room.

1

Select a sleek, contemporary fan like the two-blade Spades to harmonize with the contemporary feel of the living area.

2

Take one element, such as patterned window coverings, to inspire the rest of the room's palette.

3

Nothing jump starts design envy like architectural elements like an interesting ceiling.


# Holland

P250032-009-30  
shown with Silver blades

**FINISHES**

- Brushed Nickel - 009
- Black- 031
- Oil Rubbed Bronze - 108

Enjoy nothing but first-rate design inspiration with the gorgeous Holland collection. Four simple, yet stunning blades blend style with sustainability as they anchor to a sleek, dual mount center. An integrated LED light is ready to offer a gentle glow along with the fan's refreshing breeze. With the versatility to be installed in indoor or outdoor locations, this fan will make a design statement in any modern or transitional setting.



*Dual Mount System*

*Dimmable LED Light*

*Indoor or Outdoor Use*



P250032-009-30  
shown with Silver blades



P250032-031-30  
shown with Black blades



P250032-108-30  
shown with Walnut blades

## Holland

**P250032-009-30** Brushed Nickel



Silver

**P250032-031-30** Black



Black

**P250032-108-30** Oil Rubbed Bronze



Walnut

**ENERGY INFORMATION AT HIGH SPEED**

<b>Airflow</b>	7,035 cubic feet per minute
<b>Electricity Use</b>	31 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	257 CFM/W



Full Function Remote Control Included  
Six-speed fan operation  
Full-range dimming for light  
Reverse direction control

**FEATURES**

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- ABS blades
- White opal glass
- Damp Location Rated
- Remote control with batteries is included

**SIZE**

60" dia., 16-5/8" ht.  
80" lead wires.

**LAMP**

24w LED Module, 3000K, 90 CRI,  
2000 source lumens, dimmable.



# Oriole

## FINISHES

- Brushed Nickel - 09
- Black - 31
- Architectural Bronze - 129

P2592-12930K  
shown with Architectural Bronze blades



*Sleek Blades*

This 60" Oriole ceiling fan is the perfect addition to interior garages, industrial shops or commercial buildings to distribute the right amount of air and keep the space cool and comfortable. Oriole contains an integrated 18W LED module, with an optional finishing cap offering the user the choice to install with or without the light kit. A remote control is included to adjust speed and turn on/off the light or fan. A blank plate comes standard.

*Industrial Design*

*Removable, Dimmable LED Light*



P2592-0930K  
shown with Silver blades



P2592-3130K  
shown with Black blades  
and light kit removed  
using blank plate



P2592-12930K  
shown with Architectural Bronze blades

# Oriole

**P2592-0930K** Brushed Nickel



Silver

**P2592-3130K** Black



Black

**P2592-12930K** Architectural Bronze



Architectural Bronze

## ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	6,171 cubic feet per minute
<b>Electricity Use</b>	51 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	132 CFM/W



Three-Speed Remote Control Included  
Three-speed fan operation  
Full-range dimming for light

## FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-18.5°)
- AC Motor
- ABS blades
- Removable light kit. Blank plate included.
- White opal glass shade
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 wall control
- Add the P2667-31 WiFi remote

## SIZE

60" dia., 15" ht.  
80" lead wires.

## LAMP

18w LED Module, 3000K, 90 CRI,  
1400 source lumens, dimmable.




# Royer

## FINISHES

- Antique Nickel - 081
- Forged Black- 080

P250010-080  
shown with Distressed Ebony blades

The Royer collection's ceiling fan offers a charming, rustic look ideal for farmhouse and rustic spaces in need of a fresh breeze. Four plywood blades attach to the fixture's center by finely detailed metal arms. The crafted center is available in three finishes so you can select the perfect piece to complement your home décor.




# Royer

P250010-080 Forged Black



P250010-081 Antique Nickel



P250010-080  
shown with Matte Black blades



P250010-081  
shown with Driftwood blades



Bottom detail of P250010-081  
shown with Driftwood blades

## ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	6,255 cubic feet per minute
<b>Electricity Use</b>	67 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	102 CFM/W



Three-Speed Remote Control Included  
Three-speed fan operation

## FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Reversible plywood blades
- Not compatible with light kit
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 wall control
- Add the P2667-31 WiFi remote

## SIZE

60" dia., 17-7/8" ht.  
80" lead wires.





# Carrollwood NEW

**FINISHES**

- Brushed Nickel - 009
- White - 030
- Matte Black- 31M

P250074-31M-30  
shown with Chestnut blades  
and Vintage Gold accent bands

With an emphasis on elegance, Carrollwood makes a statement in any room. Lustrous accent bands circle the fan body and light kit, delivering a luxurious element to the fan's striking design. Carrollwood is offered in three tasteful finishes with complementing plywood blades. The light is an LED module covered by a shatterproof shade and is dimmable. A remote control is included for added convenience.



P250074-009-30  
shown with American Walnut  
blades and Chrome accent bands



P250074-030-30  
shown with Natural Cherry blades  
and Vintage Gold accent bands



P250074-31M-30  
shown with Matte Black blades  
and Vintage Gold accent bands

## Carrollwood

**P250074-009-30** Brushed Nickel

- American Walnut
- Silver

**P250074-030-30** White

- Natural Cherry
- White

**P250074-31M-30** Matte Black

- Chestnut
- Black

**ENERGY INFORMATION AT HIGH SPEED**

<b>Airflow</b>	6,857 cubic feet per minute
<b>Electricity Use</b>	42 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	224 CFM/W

**FEATURES**

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- Reversible plywood blades
- Remote control with batteries is included

**SIZE**

56" dia., 18" ht.  
80" lead wires.

**LAMP**

18w LED Module,  
3000K, 90 CRI,  
1400 source lumens, dimmable.



Full Function Remote Control Included  
Six-speed fan operation  
Reverse direction control  
Full-range dimming for light


# Glandon

## FINISHES

- Gilded Iron - 71
- Antique Nickel - 81

P2586-8130K  
shown with Driftwood blades

Glandon offers a sophisticated design that is ideal for settings requiring a touch of modern flair. Six reversible blades in a walnut/driftwood faux wood finish are strapped by a sleek Antique Nickel metal bar for an unexpected industrial detail. The 60" Glandon ceiling fan features a 17w LED module (3000K color temperature) with a shatterproof white opal shade and a dual mount system. Full range dimming and remote control is included.




*Modern Style*

*Reversible Blades*


*Opal Shade*

# Glandon

**P2586-7130K** Gilded Iron



**P2586-8130K** Antique Nickel



P2586-7130K  
shown with Toasted Oak blades



P2586-8130K  
shown with Classic Walnut blades

## ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	6,036 cubic feet per minute
<b>Electricity Use</b>	84 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	96 CFM/W



Remote Control Included  
Three-speed fan operation  
Full-range dimming for light

## FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Reversible plywood blades
- White opal shatterproof shade
- Remote control with batteries is included
- Add the P2667-31 WiFi remote

## SIZE

60" dia., 17-1/8" ht  
80" lead wires.

## LAMP

17w LED Module,  
3000K, 90 CRI,  
1400 source lumens, dimmable.





## Live An Open Life

A neutral color palette adds to the airiness of an open floor plan.

1

Use a ceiling fan with a light kit to provide both light and cooling power in the living area.

2

Make an open-concept space an entertainer's paradise with a kitchen that flows into the living areas.

3

Choose lighting as a single focal point for each of the areas to create room-like settings.

# Greer

## FINISHES

- Gilded Iron - 71
- Antique Nickel - 81

P2584-81  
shown with Classic Walnut blades

This five-blade 54" Greer ceiling fan complements either industrial or farmhouse decor. It comes with a wire meshed shade light kit that uses two vintage LED lamps (included). Remote control is also included. Greer can be hung on a flat or sloped ceiling due to its dual mount system.


*Industrial Design*

*Dual Mount System*


*Wire Mesh Shade*

# Greer

## P2584-71 Gilded Iron



## P2584-81 Antique Nickel



P2584-71  
shown with Toasted Oak blades



P2584-81  
shown with Driftwood blades

## ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	4,794 cubic feet per minute
<b>Electricity Use</b>	65 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	82 CFM/W



Remote Control Included  
Three-speed fan operation  
Full-range dimming for light

## FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-45°)
- AC Motor
- Reversible plywood blades
- Wire basket shade light kit
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 wall control
- Add the P2667-31 WiFi remote

## SIZE

54" dia., 21-5/8" ht  
80" lead wires.

## LAMP

Two medium base 2200K 5.5w vintage LED lamps included. 500 lumens/lamp, 80 CRI, dimmable. 6.5w LED or 60W incandescent max/ socket.

Fixtures shown with V6.55T19DLED922/JA8 vintage lamps.




# Chapin

P250022-108  
shown with Distressed Walnut blades

## FINISHES

- Antique Nickel - 081
- Oil Rubbed Bronze - 108
- Graphite - 143

The Chapin Collection effortlessly unites a spacious room, creating an atmosphere that's both relaxing and reviving. Antique nickel, Graphite, or oil rubbed bronze finishes complement each other with four plywood blades and a dual mount canopy for a design destined to provide a truly relaxing experience.



Dual Mount System

Plywood Blades


Relaxed Style



P250022-081  
shown with Driftwood blades




P250022-108  
shown with American Walnut blades




P250022-143  
shown with Grey Weathered Wood blades

# Chapin

## P250022-081 Antique Nickel



## P250022-108 Oil Rubbed Bronze



## P250022-143 Graphite



### ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	6,543 cubic feet per minute
<b>Electricity Use</b>	81 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	87 CFM/W



Three-Speed Remote Control Included  
Three-speed fan operation

### FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Reversible plywood blades
- Compatible with universal light kits
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 wall control
- Add the P2667-31 WiFi remote

### SIZE

54" dia., 14-1/2" ht.  
80" lead wires.





# Bedwin

**FINISHES**


- Antique Nickel - 081
- Galvanized - 141
- Graphite - 143

P250024-081  
shown with Driftwood blades

Recall charming, rustic lattice work with the Bedwin Collection's farmhouse-inspired ceiling fan. With three finishes to pick from and four rough hewn plywood blades circling a handsome dual mount canopy, this ceiling fan is sure to help transform any living space into a cool paradise of relaxation.



P250024-081  
shown with Classic Walnut blades




P250024-141  
shown with Gray Weathered Wood blades



P250024-143  
shown with Graphite blades

## Bedwin

**P250024-081** Antique Nickel



**P250024-141** Galvanized



**P250024-143** Graphite



ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	6,044 cubic feet per minute
<b>Electricity Use</b>	34 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	192 CFM/W

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- Reversible plywood blades
- Compatible with universal light kits
- Remote control with batteries is included

SIZE

56" dia., 15-1/2" ht.  
80" lead wires.



Full Function Remote Control Included  
Six-speed fan operation  
Reverse direction control

# Soar

P2542-2030K  
shown with Walnut blades

## FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20
- White - 30

With a white opal shade and a 17W dimmable LED module, the 54" Soar ceiling fan offers energy and cost-savings benefits for a variety of living spaces. The four-blade fan comes with a remote control and is available in Brushed Nickel, Antique Bronze and white finishes. LED source features a 3000K-color temperature. Soar features a dual mount system and includes a remote control with batteries.

*Dual Mount System*



*White Opal Shade*

*Dimmable LED Light*



P2542-0930K  
shown with Black blades



P2542-2030K  
shown with Walnut blades



P2542-3030K  
shown with White blades

# Soar

**P2542-0930K** Brushed Nickel



Black

**P2542-2030K** Antique Bronze



Walnut

**P2542-3030K** White



White

## ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	4,814 cubic feet per minute
<b>Electricity Use</b>	65 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	83 CFM/W



Remote Control Included  
Three-speed fan operation  
Full-range dimming for light

## FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Non-reversible plywood blades
- White opal shatterproof lens
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 wall control
- Add the P2667-31 WiFi remote

## SIZE

54" dia., 15" ht.  
80" lead wires.

## LAMP

17w LED Module, 3000K, 90 CRI,  
1400 source lumens, dimmable.



# Harranvale

## FINISHES

- Antique Bronze - 20
- White - 30
- Graphite - 143

P2540-14330K  
shown with Graphite blades

The 54" Harranvale features a design that incorporates mixed metal design details that is very popular in today's home decor. Featuring reversible blades and opal glass shade, fans are available in three finish options: Antique Bronze with brushed bronze accent; Graphite with brushed nickel accent; and White with brushed nickel accent. Harranvale features a dual mount system and includes a remote control with batteries.


*Mixed Metal Design*

*Opal Glass Shade*


*Reversible Blades*

# Harranvale


## P2540-2030K Antique Bronze



## P2540-3030K White



## P2540-14330K Graphite



P2540-2030K  
shown with Medium Cherry blades  
and Brushed Bronze accent



P2540-3030K  
shown with White blades  
and Brushed Nickel accent



P2540-14330K  
shown with American Walnut blades  
and Brushed Nickel accent

### ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	5,121 cubic feet per minute
<b>Electricity Use</b>	66 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	87 CFM/W



Remote Control Included  
Three-speed fan operation  
Full-range dimming for light

### FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20")
- AC Motor
- Reversible plywood blades
- White opal glass shade
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 wall control

### SIZE

54" dia., 16-3/8" ht.  
80" lead wires.

### LAMP

17w LED Module, 3000K, 90 CRI,  
1400 source lumens, dimmable.





# Glenfalls

P250021-028-30  
shown with Matte White blades and Black Chrome accents

## FINISHES

- Brushed Nickel - 009
- Matte White- 028
- Matte Black - 031

Glenfalls highlights its beautiful simulated wood fan blades with bright metallic accents on the blade arms and tips to create a timeless yet modern design. Glenfalls is ideal for cooling large living areas in sophisticated style.

*Timeless Design*

*Metallic Accents*

*Dimmable LED Light*

# Glenfalls

**P250021-009-30** Brushed Nickel

 Chestnut

**P250021-028-30** Matte White

 Matte White

**P250021-031-30** Matte Black

 Matte Black



P250021-009-30  
shown with Chestnut blades  
and Brushed Nickel accents



P250021-028-30  
shown with Matte White blades  
and Black Chrome accents



P250021-031-30  
shown with Matte Black blades  
and Brushed Nickel accents

## ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	6,393 cubic feet per minute
<b>Electricity Use</b>	85 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	84 CFM/W

## FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Plywood blades
- White opal glass shade
- Remote control with batteries is included
- Remote control may be replaced with the P2667-31 WiFi Remote

## SIZE

56" dia., 14-7/8" ht.  
80" lead wires.

## LAMP

24w LED Module, 3000K,  
90 CRI, 2000 source lumens,  
dimmiabie.



Remote Control Included  
Three-speed fan operation  
Full-range dimming for light



# Claret

P250007-108-30  
shown with Antique Wood blades

## FINISHES

- Brushed Nickel - 009
- Matte Black - 031
- Oil Rubbed Bronze - 108

Claret gracefully blends old and new with an eye-catching fluted motor housing paired with long blade arms. With its unique take on a classic design, Claret will make a statement in a variety of interiors.



*Statement-Making*

*Fluted Motor Housing*

*Dimmable LED Light*



P250007-009-30  
shown with Matte Black blades




P250007-031-30  
shown with Distressed Ebony blades



P250007-108-30  
shown with Chestnut blades

# Claret


**P250007-009-30** Brushed Nickel



**P250007-031-30** Matte Black



**P250007-108-30** Oil Rubbed Bronze



## ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	5,553 cubic feet per minute
<b>Electricity Use</b>	61 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	106 CFM/W



Remote Control Included  
Three-speed fan operation  
Full-range dimming for light

## FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Reversible plywood blades
- White opal glass shade
- Remote control with batteries is included
- Remote control may be replaced with the P2667-31 WiFi Remote

## SIZE

54" dia., 15-1/8" ht.  
80" lead wires.

## LAMP

18w LED Module, 3000K,  
90 CRI, 1400 source lumens,  
dimmable.



# Graceful

## FINISHES

- Brushed Nickel - 09
- Polished Chrome - 15
- Antique Bronze - 20

P2544-0930K  
shown with Medium Cherry blades

Refresh your living space with the crisp, clean style of the 54" Graceful fan. With a white opal glass shade and a 17W dimmable LED module, the five-blade fan comes with a remote control and is available in Brushed Nickel, polished chrome and Antique Bronze finishes. LED source offers a 3000K-color temperature, energy savings and maintenance benefits for the home.



P2544-0930K  
shown with Silver blades



P2544-1530K  
shown with Toasted Oak blades



P2544-2030K  
shown with American Walnut blades

# Graceful


**P2544-0930K** Brushed Nickel



**P2544-1530K** Polished Chrome



**P2544-2030K** Antique Bronze



## ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	4,454 cubic feet per minute
<b>Electricity Use</b>	60 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	83 CFM/W



Remote Control Included  
Three-speed fan operation  
Full-range dimming for light

## FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Reversible plywood blades
- White opal glass shade
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 wall control
- Add the P2667-31 WiFi remote

## SIZE

54" dia., 16-3/8" ht.  
80" lead wires.

## LAMP

17w LED Module, 3000K, 90 CRI,  
1400 source lumens, dimmable.



# Gust

P2582-0930K  
shown with Silver blades

## FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20
- Graphite - 143

This five-blade 54" Gust ceiling fan features a white opal glass shade that is available in a Brushed Nickel, Antique Bronze or Graphite finish. A remote control is included. Gust has a dual mount system to offer greater flexibility when installing. The 18W dimmable, 3000K LED module provides energy and cost-savings benefits to the homeowner.



*Dual Mount System*

*Sleek Design*

*Dimmable LED Light*



P2582-0930K  
Shown with Silver blades



P2582-2030K  
Shown with Walnut blades



P2582-14330K  
Shown with Graphite blades

# Gust

**P2582-0930K** Brushed Nickel



Silver

**P2582-2030K** Antique Bronze



Walnut

**P2582-14330K** Graphite



Graphite

## ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	5,242 cubic feet per minute
<b>Electricity Use</b>	65 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	87 CFM/W



Three-Speed Remote Control Included  
Three-speed fan operation  
Full-range dimming for light

## FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-18.5")
- AC Motor
- Manual reverse switch
- Non-reversible plywood blades
- White opal glass shade
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 wall control
- Add the P2667-31 WiFi remote

## SIZE

54" dia., 16" ht.  
80" lead wires.

## LAMP

18w LED Module, 3000K, 90 CRI,  
1400 source lumens, dimmable.



## Casual, Modern Charm



1

Craftsman style gets modern flair with clean and bright design.

1

Hang a sleek Gust fan from a paneled ceiling for Craftsman style with a modern edge.

2

Pair farmhouse-style furniture with cozy textures and neutral colors for casual comfort.

3

Break up a bright space visually with a handcrafted, dark wood door.

2

3

# Kudos

P2568-0930K  
shown with American Walnut blades

**FINISH**  
● Brushed Nickel - 09

This five-blade 52" Kudos ceiling fan features a clear Fresnel glass shade. Available in a Brushed Nickel finish and includes a remote control. The Kudos features a dual mount system to offer greater flexibility when installing. The 18W dimmable, 3000K LED module provides energy and cost-savings benefits to the homeowner.



P2568-0930K  
shown with Silver blades



P2568-0930K  
shown with American Walnut blades

## Kudos

**P2568-0930K** Brushed Nickel



### ENERGY INFORMATION AT HIGH SPEED

**Airflow** 5,160 cubic feet per minute  
**Electricity Use** 60 watts (excludes lights)  
**DOE Weighted CFM/W** 91 CFM/W



Three-Speed Remote Control Included  
Three-speed fan operation  
Full-range dimming for light

### FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-18.5")
- Downrod installation only. Can not be flush mounted.
- AC Motor
- Reversible plywood blades
- Clear Fresnel glass shade
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 wall control
- Add the P2667-31 WiFi remote

### SIZE

52" dia., 17-5/8" ht.  
80" lead wires.

### LAMP

18w LED Module, 3000K, 90 CRI, 1400 source lumens, dimmable.



# Fresno

## FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20
- White - 30

P2548-2030K  
shown with Cherry blades

Five-blade 60" Fresno ceiling fan features an LED light source, offering both form and function with energy and cost-savings benefits. A white opal glass shade features an 18W dimmable, 3000K LED module. A remote control with full range dimming and remote control is included.




*Clean Design*

*Dimmable LED Light*


*White Opal Glass Shade*

# Fresno


**P2548-0930K** Brushed Nickel



**P2548-2030K** Antique Bronze



**P2548-3030K** White



P2548-0930K  
shown with Silver blades



P2548-2030K  
shown with Dark Walnut blades



P2548-3030K  
shown with White blades

## ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	5,718 cubic feet per minute
<b>Electricity Use</b>	79 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	80 CFM/W



Full Function Remote Control Included  
Three-speed fan operation  
Full-range dimming for light  
Reverse direction control

## FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-17.5°)
- AC Motor
- Reversible plywood blades
- White opal glass shade
- Remote control with batteries is included, receiver mounted in motor.
- Remote control may be replaced with P2631-30 wall control
- Add the P2667-31 WiFi remote

## SIZE

60" dia., 17-1/4" ht.  
80" lead wires.

## LAMP

18w LED Module, 3000K, 90 CRI,  
1400 source lumens, dimmable.



# Tempt

P2578-16330K  
shown with Chesnut blades

## FINISHES

- Polished Chrome - 15
- Antique Bronze - 20
- Vintage Brass - 163

This five-blade 52" Tempt ceiling fan features a clear, double prismatic glass shade that is available in a Polished chrome, Antique Bronze or Vintage Brass finish. A remote is included. Tempt features a dual mount system to offer greater flexibility when installing. The 17w dimmable, 3000K LED module provides energy and cost-savings benefits to the homeowner.



P2578-1530K  
shown with Medium Cherry blades




P2578-2030K  
shown with American Walnut blades




P2578-16330K  
shown with Dark Cherry blades

# Tempt


**P2578-1530K** Polished Chrome



**P2578-2030K** Antique Bronze



**P2578-16330K** Vintage Brass



## ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	4,314 cubic feet per minute
<b>Electricity Use</b>	63 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	78 CFM/W



Remote Control Included  
Three-speed fan operation  
Full-range dimming for light

## FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Reversible plywood blades
- Clear double prismatic glass shade
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 wall control
- Add the P2667-31 WiFi remote

## SIZE

52" dia., 16-1/4" ht.  
80" lead wires.

## LAMP

17w LED Module, 3000K, 90 CRI,  
1400 source lumens, dimmable.





# Verada

## FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20

P2558-0930K  
shown with Medium Cherry blades

This five-blade 52" Verada ceiling fan combines a linen glass shade with a 17W LED source. Available in a Brushed Nickel or Antique Bronze finish. Verada features a dual mount system and a three-speed pull chain fan switch, as well as an on/off pull chain switch to operate the light. LED light kit features a 3000K color temperature.

*Dual Mount System*

*LED Light*

*Linen Glass Shade*

# Verada

**P2558-0930K** Brushed Nickel



Medium Cherry  
American Walnut

**P2558-2030K** Antique Bronze



Medium Cherry  
American Walnut



P2558-0930K  
shown with white linen glass  
and American Walnut blades



P2558-2030K  
shown with tea stained linen glass  
and Medium Cherry blades

## ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	4,445 cubic feet per minute
<b>Electricity Use</b>	65 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	79 CFM/W

## FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-30°)
- AC Motor
- Reversible plywood blades
- Linen glass shade
- 3 Speed pull chain switches
- Add a P2630-30 wall control or P2662-01 hand-held remote control
- Add the P2667-31 WiFi remote

## SIZE

52" dia., 16" ht.  
80" lead wires.

## LAMP

17w LED Module, 3000K, 90 CRI,  
1400 source lumens, dimmable (with  
added remote wall control).



# Billows

## FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20
- Forged Black - 80

P2552-09  
shown with White Washed blades

With a sophisticated and traditional design, the Billows offers both form and function with two energy efficient LED lamps, featuring a 3000K color temperature. The 52" Billows ceiling fan features an LED light kit with white opal glass shade and five reversible blades. The fans are available in Brushed Nickel, Antique Bronze and Forged Black finishes.

*Traditional Design*

*Reversible Blades*

*White Opal Glass Shade*



P2552-09  
shown with Silver blades




P2552-20  
shown with American Walnut blades




P2552-80  
shown with Toasted Oak blades

## Billows


### P2552-09 Brushed Nickel



### P2552-20 Antique Bronze



### P2552-80 Forged Black



#### ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	4,682 cubic feet per minute
<b>Electricity Use</b>	59 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	92 CFM/W

#### FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-18.5°)
- AC Motor
- Reversible plywood blades
- White opal glass shade
- Add a P2630-30 wall control or P2662-01 hand-held remote control
- Add the P2667-31 WiFi remote

#### SIZE

52" dia., 17-1/2" ht.  
80" lead wires.

#### LAMP

Two medium base 3000K 9w LED lamps included. 800 lumens/lamp, 90 CRI, dimmable (with added remote wall control). 10w LED max/ socket.



## Accessorize with Style



Pops of blue and plenty of collectibles give a room personality.

1

Select a ceiling fan like Billows, whose whitewashed-finish blades accentuate the organic textures in the room.

2

Follow your style by curating your space with treasures that you love.

3

Pick a focal point like the rough stone fireplace and use its natural color palette to inform the color choices for the rest of the space.


# Signature

## FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20
- Forged Bronze - 77
- Forged Black - 80
- Antique Nickel - 81

P2521-09WA  
Shown with Dark Walnut blades

A 52" Signature 5-blade fan features reversible blades and a 30-year limited warranty. A powerful AirPro motor features a 3-speed, triple-capacitor control that can also be reversed to provide year-round comfort. The Signature fan will also accept a universal light kit.



P2521-09  
shown with White blades



P2521-09CH  
Shown with Cherry blades




P2521-80  
Shown with Dark Cherry blades



P2521-20  
Shown with P2602-20WB light kit\*  
with Classic Walnut blades  
\* Light kit sold separately.

# Signature


## P2521-09 Brushed Nickel




## P2521-09CH Brushed Nickel




## P2521-09WA Brushed Nickel



## P2521-20 Antique Bronze



## P2521-80 Forged Black



## ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	4,701 cubic feet per minute
<b>Electricity Use</b>	65 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	84 CFM/W


## FEATURES

- 30-year limited warranty
- 45° Canopy
- Close-to-ceiling installation
- SureConnect® System
- AC Motor
- Compatible with universal light kits
- Three speed pull-chain switch
- Add a P2630-30 wall control or P2662-01 hand-held remote control
- Add the P2667-31 WiFi remote

## SIZE

52" dia., 14-5/8" ht. (CTC 11-9/16" ht.), 80" lead wires.

## CTC INSTALLATION



# Trevina II 44"

The Trevina collection features fans with a signature three-blade design. Perfect for modern or traditional interiors, each fan includes an LED light source to help extend your day into the evening as you and your family relax in your peaceful retreat.

## FINISHES


- Brushed Nickel - 09
- Satin White - 28
- Black - 31

**P2555-0930K** Brushed Nickel



Silver

**P2555-2830K** Satin White



White

**P2555-3130K** Black



Black

Distressed Ebony



Detail of P2555-0930K shown with P2668-09 blank plate and Silver blades

## BLANK PLATE

- P2668-09** Brushed Nickel
- P2668-28** Satin White
- P2668-31** Black



P2668-09



P2668-28



P2668-31



P2555-0930K  
shown with Silver blades



P2555-2830K  
shown with White blades



P2555-3130K  
shown with Distressed Ebony blades

## ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	4306 cubic feet per minute
<b>Electricity Use</b>	42 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	122 CFM/W

## FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Reversible MDF blades
- Removable light kit. Blank plate sold separately.
- White Opal glass
- Compatible with remote or hardwired wall controls (P2630, P2661-01, P2662-01, P2663-01, P2665 (sold separately))

## SIZE

44" dia., 15-5/8" ht.  
80" lead wires.

## LAMP

18w LED Module,  
3000K, 90 CRI,  
1400 source lumens, dimmable.



Wall Control Included  
Four-speed fan operation  
Full-range dimming for light  
Includes switch plate cover

# Trevina II 52"

## FINISHES

- Architectural Bronze - 129
- Painted Nickel - 152

**P2553-129WB** Architectural Bronze



Medium Cherry  
Classic Walnut

**P2553-152WB** Painted Nickel



Black  
Silver



P2553-129WB  
shown with Medium Cherry blades



P2553-152WB  
shown with Black blades

## ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	5,296 cubic feet per minute
<b>Electricity Use</b>	56 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	112 CFM/W

## FEATURES

- Limited lifetime warranty (LED model)
- Dual Mount (flat or sloped ceiling-30°)
- AC Motor
- White opal glass
- Reversible plywood blades
- No switch included
- Compatible with remote control or hardwired wall controls (P2618-01, P2630, P2662-01 (sold separately))

## SIZE

52" dia., 15-3/4" ht.  
80" lead wires.

## LAMP

Two medium base 3000K  
9.5w LED lamps included.  
800 lumens/lamp, 80 CRI,  
dimmable. 60w max/  
socket.



P2556-3030K  
shown with White blades



P2556-2030K  
shown with Medium Cherry blades



P2556-0930K  
shown with Silver blades

## ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	4,916 cubic feet per minute
<b>Electricity Use</b>	62 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	89 CFM/W

## FEATURES

- Limited lifetime warranty (LED model)
- Dual Mount (flat or sloped ceiling-30°)
- Close-to-ceiling installation
- AC Motor
- White opal glass
- Reversible plywood blades

## SIZE


52" dia., 15-3/4" ht.  
80" lead wires.

## LAMP

17w LED Module, 3000K,  
90 CRI, 1400 source lumens,  
dimmable.



Wall Control Included  
Four-speed fan operation  
Full-range dimming for light  
Includes switch plate cover




## CTC INSTALLATION

# Trevina II 52"

## FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20
- White- 30

**P2556-3030K** White



White

Natural Cherry

**P2556-2030K** Antique Bronze



Medium Cherry

Classic Walnut

**P2556-0930K** Brushed Nickel



Silver

# Coolly Modern



1

2

3

Wow family and friends with a dramatic ceiling treatment.

1

Install a ceiling fan like Trevina, whose contemporary design brings both form and function.

2

Add molding or beams to the ceiling to create a spectacular "fifth wall."

3

Choose wood floors and cabinetry as a warming element to unite an open floor plan.

# Signature Plus II

Five-blade 54" Signature Plus II ceiling fan features an integrated LED light source, offering both form and function with energy and cost-savings benefits. The light kit contains a white opal shatterproof shade and is comprised of a 17W dimmable 3000K LED module.

## FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20
- White - 30

### P2539-0930K Brushed Nickel

- Driftwood
- Silver

### P2539-2030K Antique Bronze

- Classic Walnut
- Medium Cherry

### P2539-3030K White

- White
- White



P2539-0930K  
shown with Silver blades



P2539-2030K  
shown with Medium Cherry blades



P2539-3030K  
shown with White blades

## ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	5,331 cubic feet per minute
<b>Electricity Use</b>	65 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	92 CFM/W



Remote Control Included  
Three-speed fan operation  
Full-range dimming for light

## FEATURES

- Limited lifetime warranty
- 45° Canopy
- Downrod mount only
- AC Motor
- Reversible MDF blades
- White opal shatterproof shade
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 wall control

## SIZE

54" dia., 15-1/2" ht.  
80" lead wires.

## LAMP

17w LED Module, 3000K, 90 CRI,  
1400 source lumens, dimmable.



# Signature Plus

## FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20
- White - 30

### P2530-09 Brushed Nickel

- Natural Cherry
- Silver

### P2530-20 Antique Bronze

- Classic Walnut
- Medium Cherry

### P2530-30W White

- White
- White



P2530-20  
shown with P2645-01WB  
light kit\* and Classic  
Walnut blades

\*Light kit sold separately.

## ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	4,716 cubic feet per minute
<b>Electricity Use</b>	65 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	84 CFM/W

## FEATURES

- 30-year limited warranty
- 45° Canopy
- Downrod mount only
- AC Motor
- Compatible with universal light kits
- Three speed pull-chain switch
- Add a P2630-30 wall control or P2662-01 hand-held remote control
- Add the P2667-31 WiFi remote

## SIZE

54" dia., 15" ht.  
80" lead wires.




# Clifton Heights

## FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20



P2531-09  
shown with Cherry blades

52" 4-blade Clifton Heights ceiling fan features distinctive, squared reversible blades. This contemporary styled fan offers great performance and value. The Clifton Heights fan features a powerful, 3-speed motor that can be reversed to provide year-round comfort. The Clifton Heights fan will also accept a universal light kit.





# Clifton Heights

## P2531-09 Brushed Nickel

-  Natural Cherry
-  Cherry

## P2531-20 Antique Bronze

-  Classic Walnut
-  Cherry

### ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	4,373 cubic feet per minute
<b>Electricity Use</b>	55 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	89 CFM/W

### FEATURES


- 30-year limited warranty
- 45° Canopy
- Close-to-ceiling installation
- SureConnect System
- AC Motor
- Compatible with universal light kits
- Three speed pull-chain switch
- Add a P2630-30 wall control or P2662-01 hand-held remote control
- Add the P2667-31 WiFi remote

### SIZE

52" dia., 15-3/4" ht.  
(CTC 11" ht.),  
80" lead wires.



### CTC INSTALLATION





# AirPro NEW

## FINISHES

- Brushed Nickel - 009
- Polished Chrome - 015
- Antique Bronze - 020
- White - 030
- Graphite - 143
- Matte Black - 31M

P250080-015  
shown with Black blades

The AirPro 52" 5-blade ceiling fan refreshes interiors with a sleek, modern form. Five clean-lined fan blades extend outward from a streamlined motor housing that contains a powerful AC motor. Its versatile yet timeless design makes it ideal for a wide range of interior décor styles.

*Powerful AC Motor*

*Versatile*

*Timeless Design*

# AirPro


## FINISHES

- Brushed Nickel - 009
- Polished Chrome - 015
- Antique Bronze - 020
- White - 030
- Graphite - 143
- Matte Black - 31M


### P250080-009 Brushed Nickel



### P250080-015 Polished Chrome




### P250080-020 Antique Bronze




### P250080-030 White



### P250080-143 Graphite



### P250080-31M Matte Black



P250080-009  
shown with  
Grey Weathered Wood blades



P250080-015  
shown with  
Rustic Charcoal blades



P250080-020  
shown with  
Distressed Walnut blades



P250080-030  
shown with  
Antique Wood blades



P250080-143  
shown with  
Graphite blades



P250080-31M  
shown with  
Rustic Charcoal blades

## ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	4,591 cubic feet per minute
<b>Electricity Use</b>	58 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	93 CFM/W

## FEATURES

- 30-year limited warranty
- AC Motor
- Compatible with universal light kits
- Add a P2630 wall control or P2663-01 hand-held remote control

## SIZE

52" dia., 12-5/8" ht.  
80" lead wires.



**FINISHES**

- Brushed Nickel - 009
- White - 030
- Matte Black - 31M

**P250081-009-WB** Brushed Nickel

- Grey Weathered Wood
- Silver



P250081-009-WB  
shown with  
Grey Weathered Wood blades

**P250081-030-WB** White

- White
- Antique Wood



P250081-030-WB  
shown with  
Antique Wood blades

**P250081-31M-WB** Matte Black

- Rustic Charcoal
- Black



P250081-31M-WB  
shown with  
Black blades

**P250085-009-WB** Brushed Nickel

- Grey Weathered Wood
- Silver



P250085-009-WB  
shown with  
Silver blades

**P250085-030-WB** White

- White
- Antique Wood



P250085-030-WB  
shown with  
White blades

**P250085-31M-WB** Matte Black

- Rustic Charcoal
- Black



P250085-31M-WB  
shown with  
Rustic Charcoal blades

**FINISHES**

- Brushed Nickel - 009
- White - 030
- Matte Black - 31M

**P250082-009-WB** Brushed Nickel

- Grey Weathered Wood
- Silver



P250082-009-WB  
shown with  
Grey Weathered Wood blades

**P250082-030-WB** White

- White
- Antique Wood



P250082-030-WB  
shown with  
White blades

**P250082-31M-WB** Matte Black

- Rustic Charcoal
- Black



P250082-31M-WB  
shown with  
Rustic Charcoal blades

ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	4,857 cubic feet per minute
<b>Electricity Use</b>	58 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	93 CFM/W

FEATURES

- 30-year limited warranty
- AC Motor
- P250081 series has white opal shatterproof shades.
- P250085 series has clear seeded glass shades.
- Add a P2630 wall control or P2663-01 hand-held remote control

SIZE

52" dia., 18-3/4" ht.  
80" lead wires.

LAMP

Four medium base 3000K 8.5w LED lamps included. 800 lumens/lamp, 80 CRI, non-dimmable.



ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	4,494 cubic feet per minute
<b>Electricity Use</b>	58 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	92 CFM/W

FEATURES

- 30-year limited warranty
- AC Motor
- Includes shatterproof shade
- Add a P2630 wall control or P2663-01 hand-held remote control

SIZE

52" dia., 16-11/16" ht.  
80" lead wires.

LAMP

Two medium base 3000K 8.5w LED lamps included. 800 lumens/lamp, 80 CRI, non-dimmable.



# AirPro NEW Energy Star

## FINISHES

- Brushed Nickel - 009
- White - 030
- Matte Black - 31M



P250084-009  
shown with Silver blades

The AirPro 52" 5-blade ceiling fan refreshes interiors with a sleek, modern form. Five clean-lined fan blades extend outward from a streamlined motor housing that contains a powerful AC motor. Its versatile yet timeless design makes it ideal for a wide range of interior décor styles.

*Powerful AC Motor*

*Versatile*

*Timeless Design*

# AirPro Energy Star


## FINISHES

- Brushed Nickel - 009
- White - 030
- Matte Black - 31M


### P250084-009 Brushed Nickel



### P250084-030 White



### P250084-31M Matte Black



P250084-009  
shown with  
Grey Weathered Wood blades



P250084-030  
shown with  
Antique Wood blades



P250084-31M  
shown with  
Rustic Charcoal blades

## ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	4,337 cubic feet per minute
<b>Electricity Use</b>	45 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	112 CFM/W

## FEATURES

- 30-year limited warranty
- AC Motor
- Add a P2630 wall control or P2663-01 hand-held remote control
- Will accept a universal Energy Star rated light kit

## SIZE

52" dia., 16-11/16" ht.  
80" lead wires.



**FINISHES**

- Brushed Nickel - 009
- White - 030
- Matte Black - 31M



**P250077-009-WB** Brushed Nickel

-  Grey Weathered Wood
-  Silver



P250077-009-WB  
*shown with  
 Grey Weathered Wood blades*



**P250077-030-WB** White

-  White
-  Antique Wood



P250077-030-WB  
*shown with  
 Antique Wood blades*

**P250077-31M-WB** Matte Black

-  Rustic Charcoal
-  Black



P250077-31M-WB  
*shown with  
 Black blades*

ENERGY INFORMATION AT HIGH SPEED

**Airflow** 4,311 cubic feet per minute  
**Electricity Use** 45 watts (excludes lights)  
**DOE Weighted CFM/W** 111 CFM/W

FEATURES

- 30-year limited warranty
- AC Motor
- Includes shatterproof shades
- Add a P2630 wall control or P2663-01 hand-held remote control

SIZE

52" dia., 13-1/2" ht.  
 80" lead wires.

LAMP

Four medium base  
 3000K 9w LED lamps included.  
 800 lumens/lamp, 90 CRI,  
 dimmable.



**FINISHES**

- Brushed Nickel - 009
- White - 030
- Matte Black - 31M

**P250078-009-WB** Brushed Nickel


-  Grey Weathered Wood
-  Silver



P250078-009-WB  
*shown with  
 Silver blades*



**P250078-030-WB** White

-  White
-  Antique Wood



P250078-030-WB  
*shown with  
 White blades*

**P250078-31M-WB** Matte Black

-  Rustic Charcoal
-  Black



P250078-31M-WB  
*shown with  
 Rustic Charcoal blades*

ENERGY INFORMATION AT HIGH SPEED

**Airflow** 4,311 cubic feet per minute  
**Electricity Use** 45 watts (excludes lights)  
**DOE Weighted CFM/W** 111 CFM/W

FEATURES

- 30-year limited warranty
- AC Motor
- Includes shatterproof shade
- Add a P2630 wall control or P2663-01 hand-held remote control

SIZE

52" dia., 13-1/2" ht.  
 80" lead wires.

LAMP

Two medium base  
 3000K 9w LED lamps included.  
 800 lumens/lamp, 90 CRI,  
 dimmable.



# AirPro

## FINISHES

- Brushed Nickel - 009
- White - 030
- Matte Black - 31M




P250066-31M  
shown with Distressed Ebony blades

An Energy Star rated AC motor gives this ceiling fan remarkable energy efficiency and powerful airflow while featuring classic good looks. Five fan blades circulate air comfortably. Versatile control options include remote control, WiFi and wall control choices. Its clean lines and a five-blade design complement a variety of interiors.

*Clean Lines*

*Energy-Efficient*

*Classic Design*



P250066-009  
shown with Natural Cherry blades




P250066-030  
shown with Washed Oak blades




P250066-31M  
shown with Distressed Ebony blades

# AirPro

## P250066-009 Brushed Nickel



## P250066-030 White



## P250066-31M Matte Black



### ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	4986 cubic feet per minute
<b>Electricity Use</b>	44 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	134 CFM/W

### FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-30°)
- AC Motor
- Add a P2630-30 or P2613-30 wall control or P2663-01 hand-held remote control
- Add the P2667-31 WiFi remote

### SIZE

52" dia., 13-1/2" ht.  
80" lead wires.




# 52" Performance


## FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20
- White - 30


### P2503-09 Brushed Nickel




### P2503-20 Antique Bronze



### P2503-30W White




P2503-20 shown with P2645-20 light kit\* and Medium Cherry blades  
\*Light kit sold separately.



P2503-09 shown with Natural Cherry blades



P2503-20 shown with Medium Cherry blades



P2503-30W shown with White blades



## 45° Canopy

- Standard canopy works with sloped ceilings up to 45°. (12:12 ceiling pitch)
- Outlet box mounting plate includes convenient hands-free hanger for wiring.
- Oversize, textured die-cast hanger ball reduces vibrations that can cause noise and wobble.
- Dual-mount for downrod or close-to-ceiling installation (on select fans)



## SureConnect® System

- Motor screws pre-installed in blade arms to prevent them from falling out during installation.
- Special guides perfectly align blade arms to motor.
- Preinstalled rubber isolation pads prevent vibration noise.

### ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	5,143 cubic feet per minute
<b>Electricity Use</b>	70 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	85 CFM/W

### FEATURES


- Limited lifetime warranty
- 45° Canopy
- Close-to-ceiling installation
- SureConnect® System
- AC Motor
- Compatible with universal light kits
- Three speed pull-chain switch
- Add a P2630-30 wall control or P2662-01 hand-held remote control
- Add the P2667-31 WiFi remote

### SIZE

52" dia., 15-1/4" ht.  
(CTC 10-1/2" ht.),  
80" lead wires.



### CTC INSTALLATION




# 42" Builder Fan


## FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20
- White - 30


### P2500-09 Brushed Nickel



### P2500-20 Antique Bronze



### P2500-30 White




P2500-09 shown with P2600-09WB light kit\* and with Cherry blades  
\*Light kit sold separately.



P2500-09 shown with Cherry blades



P2500-20 shown with Classic Walnut blades



P2500-30 shown with White blades

### ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	3,053 cubic feet per minute
<b>Electricity Use</b>	46 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	64 CFM/W

### FEATURES


- 15-year limited warranty
- 23° Canopy
- Close-to-ceiling installation
- SureConnect® System
- AC Motor
- Compatible with universal light kits
- Three speed pull-chain switch
- Add a P2630 wall control or P2662-01 hand-held remote control

### SIZE

42" dia., 12-3/8" ht.  
(CTC 8-5/16" ht.),  
72" lead wires.



### CTC INSTALLATION





# 52" Builder Fan with Light Kit


## FINISHES

- Brushed Nickel - 009
- White - 030
- Architectural Bronze - 129



### P2599-09 Brushed Nickel

-  Natural Cherry
-  Cherry

### P2599-30 White

-  White
-  White

### P2599-129 Antique Bronze

-  Classic Walnut
-  Medium Cherry



P2599-09  
shown with Cherry blades



P2599-30  
shown with White blades



P2599-129  
shown with Classic Walnut blades

## ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	4,474 cubic feet per minute
<b>Electricity Use</b>	65 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	82 CFM/W

## FEATURES

- 30-year limited warranty
- Dual Mount (flat or sloped ceiling-30°)
- AC Motor
- MDF/Plywood hybrid blades
- Etched white glass shade
- Three speed pull-chain switch
- Add a P2630-30 wall control or P2663-01 hand-held remote control

## SIZE

52" dia., 17-5/8" ht.  
80" lead wires.

## LAMP

Two medium base 3000K 8.5w LED lamps included. 800 lumens/lamp, 80 CRI, non-dimmable.





# 52" Builder Fan



## FINISHES

- Brushed Nickel - 09
- Polished Chrome - 15
- Antique Bronze - 20
- White - 30
- White - 30W
- Graphite - 143



### P2501-09 Brushed Nickel

-  Natural Cherry
-  Cherry



### P2501-15 Polished Chrome

-  Black
-  Driftwood



### P2501-20 Antique Bronze

-  Medium Cherry
-  Classic Walnut


### P2501-30 White

-  White
-  Washed Oak

### P2501-30W White

-  White
-  White

### P2501-143 Graphite

-  Graphite
-  Black



P2501-09  
shown with Cherry blades




P2501-15  
shown with Driftwood blades



P2501-20  
shown with Medium Cherry blades



P2501-30  
shown with Washed Oak blades



P2501-30W  
shown with White blades



P2501-143  
shown with Black blades

## ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	4,991 cubic feet per minute
<b>Electricity Use</b>	63 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	98 CFM/W

## FEATURES

- 30-year limited warranty
- 45° Canopy
- Close-to-ceiling installation with accessory
- SureConnect® System
- AC Motor
- Compatible with universal light kits
- Add a P2630 wall control or P2663-01 hand-held remote control

## SIZE

52" dia., 13-1/2" ht.  
80" lead wires.



# Edgefield

**FINISHES**

- Brushed Nickel - 009
- White - 030
- Architectural Bronze - 129




P250016-129  
shown with Medium Cherry blades

The 52" Edgefield fan is energy efficient and lightweight. A DC motor provides ultra quiet operation and the efficiency of the latest fan technology along with the simple convenience of a four-speed pull chain switch. Edgefield features a reversible motor for year round comfort and is available in three finish options. Pair with a universal light kit for a more customized look.

*Ultra Quiet*


*Lightweight*

*Energy Efficient*




# Edgefield


**P250016-009** Brushed Nickel




**P250016-030** White



**P250016-129** Antique Bronze



P250016-009  
shown with American Walnut blades



P250016-030  
shown with White blades



P250016-129  
shown with Medium Cherry blades

**ENERGY INFORMATION AT HIGH SPEED**

<b>Airflow</b>	5,741 cubic feet per minute
<b>Electricity Use</b>	34 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	179 CFM/W

**FEATURES**

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-18.5")
- DC motor
- Manual reverse switch
- MDF blades
- Compatible with universal light kits
- Three speed pull-chain switch
- Will not accept a wall or remote control

**SIZE**

52" dia., 14-9/16" ht.  
80" lead wires






# Drift

## FINISHES

- Brushed Nickel - 009
- White - 030
- Architectural Bronze - 129


P250008-009  
shown with Silver blades

Enhance your home with the perfect mix of form and function with the 32" four-blade Drift fan. Ideal for smaller spaces, such as closets, mudrooms and laundry rooms, Drift features a powerful motor and a steep pitch to circulate a lot of air within a smaller space.




# Drift


**P250008-009** Brushed Nickel



**P250008-030** White



**P250008-129** Architectural Bronze



## ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	2,518 cubic feet per minute
<b>Electricity Use</b>	35 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	88 CFM/W

## FEATURES


- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-30°)
- Close-to-ceiling installation
- AC Motor
- Reversible MDF blades
- Compatible with universal light kits
- Three speed pull-chain switch
- Add a P2630-30 wall control or P2663-01 hand-held remote control

## SIZE

32" dia., 14-3/8" ht.  
80" lead wires.



## CTC INSTALLATION





# 44" Braden

The Braden 44 inch, three-blade, hugger-style ceiling fan features clean lines and a classic, sleek design that is ideal for Modern and Contemporary interiors. With its simple and elegant look and Brushed Nickel, Matte Black or Matte White finish, Braden complements most décor schemes.



## FINISHES

- Brushed Nickel - 009
- Matte White - 028
- Matte Black - 031



### P250058-009-30 Brushed Nickel

-  American Walnut
-  Silver

### P250058-028-30 Matte White

-  Natural Cherry
-  White

### P250058-031-30 Matte Black

-  Distressed Ebony
-  Matte Black



P250058-009-30  
shown with American Walnut blades



P250058-028-30  
shown with Natural Cherry blades



P250058-031-30  
shown with Distressed Ebony blades

## ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	3,212 cubic feet per minute
<b>Electricity Use</b>	45 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	78 CFM/W



Full Function Remote Control Included  
Three-speed fan operation  
Full-range dimming for light

## FEATURES

- Limited lifetime warranty
- Hugger low profile mounting
- AC Motor
- Reversible plywood blades
- Frosted shatterproof shade
- Full function remote control with batteries is included
- Remote control may be replaced with P2667-31 WiFi remote control

## SIZE

44" dia., 9-7/8" ht.  
12" lead wires.

## LAMP

18w LED Module, 3000K,  
90 CRI, 1400 source lumens,  
dimmable.



Featuring Braden and Clarion

## Sweet Dreaming

Muted colors and a light, airy feeling offer a dreamy look to this bedroom. The Braden hugger fan lends a contemporary touch while keeping the room comfortable and welcoming. A feature wall of lightly distressed wood paneling is accented by a pair of Clarion wall sconces, whose clear glass shade and clean styling embrace minimalist modernity and functional task lighting.

# Braden

P2588-1530K  
shown with Black blades

## FINISHES

- Brushed Nickel - 09
- Polished Chrome - 15
- Architectural Bronze - 129

This Braden 56", three-blade, hugger-style ceiling fan features clean lines and a design that complements modern interiors. A white opal glass shade contains an integrated 18W LED module, offering both form and function with energy and cost-savings benefits. Featuring a larger motor, Braden moves more air than a traditional hugger ceiling fan.



P2588-0930K  
shown with Silver blades




P2588-1530K  
shown with American Walnut blades




P2588-12930K  
shown with Medium Cherry blades

# Braden


**P2588-0930K** Brushed Nickel



**P2588-1530K** Polished Chrome



**P2588-12930K** Architectural Bronze



## ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	4,263 cubic feet per minute
<b>Electricity Use</b>	55 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	85 CFM/W



Full Function Remote Control Included  
Three-speed fan operation  
Full-range dimming for light  
Reverse direction control

## FEATURES

- Limited lifetime warranty
- Hugger low profile mounting
- AC Motor
- Reversible plywood blades
- White opal glass shade
- Full function remote control with batteries is included
- Remote control may be replaced with P2631-30 wall control
- Add the P2667-31 WiFi remote

## SIZE

56" dia., 9-7/8" ht.  
12" lead wires.

## LAMP

18w LED Module, 3000K, 90 CRI, 1400 source lumens, dimmable.



# Vox Fan

## FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20
- White - 30

P2572-0930K  
shown with Medium Cherry blades

Five-blade 52" Vox hugger-style ceiling fan features an LED light source, offering both form and function with energy and cost-savings benefits. A white opal glass shade contains a 17W dimmable, 3000K LED module. A full function remote control is included. The fan mounts close to the ceiling and is available in popular Brushed Nickel, Antique Bronze and white finishes.



*Dimmable LED Light*

*Modern Style*


*White Opal Glass Shade*

# Vox Fan

**P2572-0930K** Brushed Nickel

 Medium Cherry

**P2572-2030K** Antique Bronze

 American Walnut

**P2572-3030K** White

 White



P2572-0930K  
shown with Medium Cherry blades



P2572-2030K  
shown with American Walnut blades



P2572-3030K  
shown with White blades

## ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	4,276 cubic feet per minute
<b>Electricity Use</b>	62 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	76 CFM/W



Full Function Remote Control Included  
Three-speed fan operation  
Full-range dimming for light  
Reverse direction control

## FEATURES

- Limited Lifetime Warranty
- Hugger low profile mounting
- AC Motor
- Non-reversible plywood blades
- White opal glass shade
- Full function remote control with batteries is included
- Remote control may be replaced with P2631-30 wall control
- Add the P2667-31 WiFi remote

## SIZE

52" dia., 11-5/8" ht.  
8" lead wires.

## LAMP

17w LED Module, 3000K, 90 CRI, 1400 source lumens, dimmable.



# Lindale

P250028-129  
shown with Distressed Walnut blades

## FINISHES

- Matte White- 028
- Antique Nickel - 081
- Architectural Bronze - 129

Retreat for a little rest and relaxation under the gentle airflow offered by the Lindale collection's ceiling fan. A mid-century modern style blends with a flush mount design as four rectangular plywood blades attach to the fan's vase-inspired center. Select your favorite finish from three beautiful options to customize your Lindale fan for a perfect fit in your home décor design.



*Flush Mount Design*

*Mid-Century Modern*

*Plywood Blades*



P250028-028  
shown with Brushed Nickel accents  
and Matte White blades




P250028-081  
shown with White Barnwood blades




P250028-129  
shown with Matte Gold accents,  
Classic Walnut blades and  
optional P2669-129 Light Kit

# Lindale


**P250028-028** Matte White



**P250028-081** Antique Nickel




**P250028-129** Architectural Bronze



## LINDALE LIGHT KIT

**P2669-028** Matte White  
**P2669-081** Antique Nickel  
**P2669-129** Architectural Bronze  
24w LED Module, 3000K, 90 CRI,  
2000 source lumens, dimmable.

JAB



P2669-28 P2669-81



P2669-129

## ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	4,642 cubic feet per minute
<b>Electricity Use</b>	60 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	87 CFM/W



Three-Speed Remote Control Included  
Three-speed fan operation  
Full-range dimming for light

## FEATURES

- Limited lifetime warranty
- Hugger low profile mounting
- AC Motor
- Reversible plywood blades
- Accepts P2669 light kit, sold separately.
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 wall control

## SIZE


52" dia., 11-3/16" ht.  
80" lead wires.




\*Light kits only are JAB

# 52" Hugger Fan

**P2525-09** Brushed Nickel



**P2525-20** White



P2525-09 shown with P2610-09WB light kit\* and with Cherry blades

\* Light kit sold separately.



P2525-30 shown with White blades



P2525-09 shown with Cherry blades

## ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	3,229 cubic feet per minute
<b>Electricity Use</b>	56 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	58 CFM/W

## FEATURES

- 15-year limited warranty
- Hugger low profile mounting
- AC Motor
- Compatible with universal light kits
- Cannot be used with remote control
- Add a P2630-30 wall control


## SIZE

52" dia., 8-1/8" ht.




# 42" Hugger Fan

**P2524-09** Brushed Nickel



**P2524-30** White



P2524-09 shown with P2602-09WB light kit\* and with Natural Cherry blades

\* Light kit sold separately.



P2524-30 shown with White blades



P2524-09 shown with Natural Cherry blades

## ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	2,639 cubic feet per minute
<b>Electricity Use</b>	44 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	72 CFM/W

## FEATURES

- 15-year limited warranty
- Hugger low profile mounting
- AC Motor
- Compatible with universal light kits
- Cannot be used with remote control
- Add a P2630-30 wall control


## SIZE

42" dia., 8-5/16" ht.





Featuring 54" Patio Fan and Maison



# Outdoor Ceiling Fans

*Enhance outdoor living areas*



Scan with your camera on  
your smartphone or visit  
[www.progresslighting.com/ceilingfans](http://www.progresslighting.com/ceilingfans)



**Montague**  
P2564-8030K

Relaxed 3

Organic Shapes 1

Beach Accents 2



Dan McGinty  
Product Designer

## Easy, Breezy, Coastal

with Dan

Bring your home right to the ocean side with beach-inspired accents, organic furnishings and an overall relaxed feel. Designers often create a relaxed and open environment with soft throw blankets, pillows, cozy rugs and cushioned furniture to complete the Coastal look. Focus on an all-white color palette for your coastal inspired home, while incorporating in soft beachy hues to complement the look.

When it comes to selecting materials for flooring, décor and furniture, seek out dark or weathered wood pieces to emulate a seaside environment nestled nicely by the shore.



Shop this style at  
[www.progresslighting.com/coastal](http://www.progresslighting.com/coastal)





# Kasota NEW

P250072-108-30  
shown with Tan Linen blades

**FINISHES**

- Oil Rubbed Bronze - 108
- Graphite - 143
- Painted Nickel - 152

A sturdy metal housing and long lines bring contemporary style to Kasota. Three rectangular fan blades with long blade arms that span the entire length are finished in a linen-like texture that softens its modern look. Kasota is damp rated, making it ideal for outdoor and indoor settings. Inside. It has a DC motor for the highest efficacy and whisper-quiet operation. A full-function remote control with a battery and a LED light kit with a white opal glass shade is included.

*Contemporary Style*

*Modern Look*

*White Opal Glass*



P250072-108-30  
shown with Tan Linen blades




P250072-143-30  
shown with Charcoal Linen blades




P250072-152-30  
shown with Charcoal Linen blades

## Kasota

**P250072-108-30** Oil Rubbed Bronze



**P250072-143-30** Graphite



**P250072-152-30** Painted Nickel



**ENERGY INFORMATION AT HIGH SPEED**

<b>Airflow</b>	4,844 cubic feet per minute
<b>Electricity Use</b>	31 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	188 CFM/W

**FEATURES**

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- ABS blades
- Remote control with batteries is included

**SIZE**

56" dia., 15" ht.  
80" lead wires.

**LAMP**

18w LED Module, 3000K, 90 CRI, 1400 source lumens, dimmable.



Full Function Remote Control Included  
Six-speed fan operation  
Full-range dimming for light  
Reverse direction control

# Midvale

P250011-141-WB  
shown with Galvanized Finish blades

## FINISHES

- Matte White- 028
- Blistered Iron - 171
- Galvanized - 141

Midvale offers a nostalgic appeal, with vintage-style LED bulbs inside a clear seeded glass shade, a rustic cage frame, and a banded metal ceiling canopy to complete the charming look.



*Vintage Style*

*Nostalgic Appeal*

*Clear Seeded Glass*



P250011-028-WB  
shown with Matte White blades



P250011-141-WB  
shown with Galvanized blades



P250011-171-WB  
shown with Blistered iron blades

# Midvale

P250011-028-WB Matte White



P250011-141-WB Galvanized Finish



P250011-171-WB Blistered Iron



## ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	7,627 cubic feet per minute
<b>Electricity Use</b>	84 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	98 CFM/W



Remote Control Included  
Three-speed fan operation  
Full-range dimming for light

## FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- ABS blades
- Clear seeded glass shade
- Remote control with batteries is included
- Remote control may be replaced with the P2667-31 WiFi Remote

## SIZE

56" dia., 20-3/8" ht.  
80" lead wires.

## LAMP

Two medium base 2700K 7w vintage LED lamps included. 600 lumens/lamp, 90 CRI, dimmable. 7w LED max/socket.




# Rudder

**FINISHES**

- Matte White - 028
- Matte Black - 031
- Architectural Bronze - 129

P250040-028-30  
shown with Distressed White blades

Transform any outdoor space into a cozy country abode with the charming rustic character of the Rudder collection. Four boat oar-inspired blades attach to a smooth center that features an LED light source for friendly illumination as needed. Available in a Matte White, Matte Black, or Architectural Bronze finish, Rudder is sure to fill your favorite patio or porch with a refreshing breeze wrapped in country character.



P250040-028-30  
shown with Distressed White blades



P250040-031-30  
shown with Distressed Ebony blades



P250040-129-30  
shown with Walnut blades


## Rudder

**P250040-028-30** Matte White



Distressed White

**P250040-031-30** Matte Black



Distressed Ebony

**P250040-129-30** Architectural Bronze



Walnut

**ENERGY INFORMATION AT HIGH SPEED**

<b>Airflow</b>	6,112 cubic feet per minute
<b>Electricity Use</b>	35 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	188 CFM/W



Full Function Remote Control Included  
Six-speed fan operation  
Full-range dimming for light  
Reverse direction control

**FEATURES**

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- ABS blades
- Damp Location Rated
- White opal glass shade
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 wall control

**SIZE**

56" dia., 16-1/8" ht.  
80" lead wires.

**LAMP**

24w LED Module, 3000K,  
90 CRI, 2000 source lumens,  
dimnable.



# Edwidge

P250062-152-30  
shown with Painted Nickel blades

**FINISHES**

- Matte White - 028
- Matte Black - 031
- Painted Nickel - 152

Edwidge cleverly houses the motor within the trio of fan blades providing a sleek, modern look. All-weather ABS fan blades and a non-metallic housing and canopy offer rust-proof, contemporary style to indoor and covered outdoor settings.

*Modern Design*

*For Indoor & Outdoor Use*

*Dimmable LED Light*

# Edwidge

**P250062-028-30** Matte White



**P250062-031-30** Matte Black



**P250062-152-30** Painted Nickel



P250062-028-30  
shown with Matte White blades



P250062-031-30  
shown with Matte Black blades



P250062-152-30  
shown with Painted Nickel blades

**ENERGY INFORMATION AT HIGH SPEED**

<b>Airflow</b>	5,874 cubic feet per minute
<b>Electricity Use</b>	20 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	328 CFM/W

**FEATURES**

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- ABS blades
- Opal shatterproof shade
- Remote control with batteries is included

**SIZE**

52" dia., 13-9/16" ht.  
80" lead wires.

**LAMP**

18w LED Module, 3000K, 90 CRI,  
1400 source lumens, dimmable.



Full Function Remote Control Included  
Six-speed fan operation  
Full-range dimming for light  
Reverse direction control




# Whirl

P2574-8130K  
shown with Driftwood blades

## FINISHES

- Antique Bronze - 20
- Forged Black - 80
- Antique Nickel - 81

Refresh your indoor or covered outdoor living spaces with the crisp, clean style of the 60" Whirl fan. The stylish design comes in Antique Nickel, Antique Bronze and Forged Black finish options. The five-blade fan features an all weather damp location rating to accommodate a variety of settings throughout the home.



# Whirl

**P2574-2030K** Antique Bronze



**P2574-8030K** Forged Black



**P2574-8130K** Antique Nickel



## ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	6,549 cubic feet per minute
<b>Electricity Use</b>	70 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	106 CFM/W

## FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-18.5°)
- AC Motor
- ABS all weather blades
- White Frosted Glass Shade
- Three speed pull-chain switch (fan)
- On/off pull-chain switch (light)
- Damp Location Rated
- Add a P2630-30 wall control or P2662-01 hand-held remote control

## SIZE

60" dia., 15-7/8" ht.  
80" lead wires.

## LAMP

18w LED Module, 3000K, 90 CRI, 1400 source lumens, dimmable (with added remote wall control).



## Relax All Year Long



1

2

3

Light-filled sunrooms offer the best of indoor-outdoor living.

1

Add a beautiful Whirl ceiling fan to move the air comfortably for ultimate relaxation.

2

Install multiple recessed fixtures to create the perfect ambiance for peaceful relaxation.

3

Accessorize with organic touches of wicker furniture topped with cozy cushions for a tranquil neutral color scheme.

# Alfresco

## FINISHES

- Architectural Bronze - 129
- Blistered Iron - 171

P250034-129-WB  
shown with Dark Bamboo blades

Infuse a warm, nature-inspired style to your outdoor home décor with the one-of-a-kind Alfresco collection. Five blades decorated in a leaf-like design sprout from a dual mount center that artistically harbors an LED light source. Select from an Architectural Bronze and blistered iron finish to bring your bohemian dreamland to life.

*Leaf-like Decorated Blades*

*Nature-Inspired Design*

*Dimmable LED Light*

# Alfresco

**P250034-129-WB** Architectural Bronze

 Dark Bamboo

**P250034-171-WB** Blistered Iron

 Pewter



P250034-129-WB  
shown with Dark Bamboo blades



P250034-171-WB  
shown with Pewter blades

## ENERGY INFORMATION AT HIGH SPEED

**Airflow** 5,724 cubic feet per minute  
**Electricity Use** 68 watts (excludes lights)  
**DOE Weighted CFM/W** 90 CFM/W



Three-Speed Remote Control Included  
Three-speed fan operation  
Full-range dimming for light

## FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- ABS blades
- Damp Location Rated
- Clear seeded glass
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 wall control

## SIZE

54" dia., 19-1/4" ht.  
80" lead wires.

## LAMP

Two medium base 2700K 7w vintage LED lamps included. 600 lumens/lamp, 90 CRI, dimmable. 7w LED max/socket.



# Smyrna

P2576-2030K  
shown with Walnut blades

## FINISHES

- Antique Bronze - 20
- Forged Black - 80

This 52" Smyrna ceiling fan features an LED light source, offering both form and function with energy and cost-savings benefits. The light kit contains a clear hammered glass shade and contains a 17W dimmable 3000K LED module. Includes a wall control switch for fan speed and light operation.



*Traditional Style*

*Dimmable LED Light*

*Clear Hammered Glass Shade*

# Smyrna

**P2576-2030K** Antique Bronze



**P2576-8030K** Forged Black



P2576-2030K  
shown with Walnut blades



P2576-8030K  
shown with Toasted Oak blades

## ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	4,585 cubic feet per minute
<b>Electricity Use</b>	58 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	91 CFM/W



Wall Control Included  
Four-speed fan operation  
Full-range dimming for light  
Includes switch plate cover

## FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-30°)
- AC Motor
- ABS all weather blades
- Clear hammered glass shade
- Wet Location Rated

## SIZE

52" dia., 19-1/2" ht.  
80" lead wires.

## LAMP

17w LED Module, 3000K,  
90 CRI, 1400 source lumens,  
dimmable.





# Montague

## FINISHES

- Antique Bronze - 20
- White - 30
- Forged Black - 80

P2564-8030K  
shown with Toasted Oak blades

This five-blade 60" Montague ceiling fan features an all weather wet location rating to accommodate a variety of interior and exterior locations. The white opal glass shade contains a 18W dimmable, 3000K LED module, offering both form and function with energy and cost-savings benefits. A full function remote control is included.

*Interior and Exterior Locations*

*Dimmable LED Light*

*White Opal Glass Shade*

# Montague

P2564-2030K Antique Bronze



P2564-3030K White



P2564-8030K Forged Black




P2564-2030K  
shown with Walnut blades



P2564-3030K  
shown with White blades



P2564-8030K  
shown with Toasted Oak blades



Scan with the camera on your smartphone for the Montague installation video.

## ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	6,693 cubic feet per minute
<b>Electricity Use</b>	75 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	96 CFM/W



Full Function Remote Control Included  
Three-speed fan operation  
Full-range dimming for light  
Reverse direction control

## FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-18.5")
- AC Motor
- White opal Glass Shade
- ABS all weather blades
- Wet Location Rated
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 wall control

## SIZE

60" dia., 17-5/8" ht.  
80" lead wires.

## LAMP

18w LED Module, 3000K, 90 CRI, 1400 source lumens, dimmable.



# Kennedale

P250070-31M  
shown with Rustic Charcoal blades

**FINISHES**

- Matte White - 028
- Painted Nickel - 152
- Matte Black - 31M

Perfect for cooling large spaces inside or out, Kennedale is a 72" damp-rated DC motor fan. Classically styled with UV protected, faux wood finished reversible blades, Kennedale offers a substantial look for traditional and transitional décor and is ideal for an open floor plan or a large porch. A six-speed full function handheld remote is included. Kennedale will accept a Universal Light Kit.


*Indoor and Outdoor*

*Classically Styled*


*Substantial Look*

# Kennedale


**P250070-028** Matte White



**P250070-152** Painted Nickel



**P250070-31M** Matte Black



P250070-028  
shown with Driftwood blades



P250070-152  
shown with Grey Weathered Wood blades



P250070-31M  
shown with Rustic Charcoal blades

**ENERGY INFORMATION AT HIGH SPEED**

<b>Airflow</b>	8760 cubic feet per minute
<b>Electricity Use</b>	33 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	293 CFM/W

**FEATURES**

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-25°)
- DC Motor
- Reversible Plywood Blades
- Will accept a light kit
- Remote control with batteries is included

**SIZE**

72" dia., 18" ht.  
80" lead wires.



Full Function Remote Control Included  
Six-speed fan operation  
Reverse direction control

# Albin

P250036-129-30  
shown with Distressed Walnut blades

## FINISHES

- Matte White- 028
- Matte Black- 031
- Architectural Bronze - 129

The Albin collection offers a modern take on a traditional design that will be perfectly at home in so many outdoor spaces and lifestyles. Five blades finished with a faux wood grain texture extend from a modern-style center available in an Architectural Bronze, Matte White, or Matte Black finish. An LED light source is encased in a crisp shade to illuminate a patio or porch space that will beg to be lived in an enjoyed.

*Faux Wood Grain Texture*

*Modern Style*

*Dimmable LED Light*

# Albin

P250036-028-30 Matte White

 Matte White

P250036-031-30 Matte Black

 Toasted Oak

P250036-129-30 Architectural Bronze

 Distressed Walnut



P250036-028-30  
shown with Matte White blades



P250036-031-30  
shown with Toasted Oak blades



P250036-129-30  
shown with Distressed Walnut blades

## ENERGY INFORMATION AT HIGH SPEED

**Airflow** 5,740 cubic feet per minute  
**Electricity Use** 67 watts (excludes lights)  
**DOE Weighted CFM/W** 95 CFM/W



Three Speed Remote Control Included  
*Three speed fan operation*  
*Full range dimming with light*

## FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Plywood blades
- Damp Location Rated
- White opal glass shade
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 wall control

## SIZE

54" dia., 15-5/8" ht.  
 80" lead wires.

## LAMP

24w LED Module, 3000K,  
 90 CRI, 2000 source lumens,  
 dimmable.



# Lakehurst

## FINISHES

- Antique Bronze - 20
- White - 30
- Forged Black - 80

P2562-20  
shown with Walnut blades

This five-blade 60" Lakehurst ceiling fan features an all weather wet location rating (ABS) to accommodate a variety of interior and exterior locations. The Lakehurst fan will accept a universal outdoor rated light kit. Features a dual mount system and a three-speed pull chain fan switch.

*Interior and Exterior Locations*

*Traditional Design*

*Dual Mount System*



P2562-20  
shown with Walnut blades



P2562-30  
shown with White blades



P2562-80  
shown with Toasted Oak blades

# Lakehurst

**P2562-20** Antique Bronze



Walnut

**P2562-30** White



White

**P2562-80** Forged Black



Toasted Oak

## ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	6,440 cubic feet per minute
<b>Electricity Use</b>	71 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	105 CFM/W

## FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-18.5")
- AC Motor
- ABS all weather blades
- Compatible with universal light kits
- 3 Speed pull chain switch
- Wet Location Rated
- Add a P2630-30 wall control or P2662-01 hand-held remote control

## SIZE

60" dia., 15-3/4" ht.  
80" lead wires.



# Decorative Patio Fan

P2526-20  
shown with Washed Walnut blades

## FINISH


● Antique Bronze - 20

52" Indoor/Outdoor five-blade fan with all-weather ABS blades in palm-style design and a rich Antique Bronze finish. Three-speed motor offers great performance and value that can be reversed to provide year-round comfort. Antique Brass pull chain with medium oak fob complements the Washed Walnut blades. The Patio fan will also accept a universal outdoor rated light kit.

Washed Walnut Blades

Antique Bronze Finish

Palm-Style Design



# Decorative Patio Fan

P2526-20 Antique Bronze



P2526-20  
shown with Washed Walnut blades



P2526-20  
shown with P2636-20WB light kit\*  
and Washed Walnut blades  
\*Light kit sold separately.

## ENERGY INFORMATION AT HIGH SPEED

**Airflow** 4,150 cubic feet per minute  
**Electricity Use** 70 watts (excludes lights)  
**DOE Weighted CFM/W** 77 CFM/W

## FEATURES


- 15-year limited warranty
- 45° Canopy
- Close-to-ceiling installation
- SureConnect® System
- AC Motor
- ABS all-weather blades
- Compatible with universal light kits
- Damp location rated
- Add a P2630-30 wall control or P2662-01 hand-held remote control

## SIZE

52" dia., 17-3/8" ht.  
(CTC 12-3/16 ht.),  
80" lead wires.



## CTC INSTALLATION



# 54" Patio Fan

## FINISH

● Antique Bronze - 20

**P2533-20** Antique Bronze

 Toasted Oak



P2533-20  
shown with Toasted Oak blades  
\* Light kit sold separately.

## ENERGY INFORMATION AT HIGH SPEED

**Airflow** 4,986 cubic feet per minute  
**Electricity Use** 65 watts (excludes lights)  
**DOE Weighted CFM/W** 74 CFM/W

## FEATURES


- 30-year limited warranty
- 45° Canopy
- SureConnect® System
- AC Motor
- ABS all-weather blades
- Wet location rated
- Compatible with universal light kits
- Add a P2630-30 wall control or P2662-01 hand-held remote control

## SIZE

54" dia., 18-1/4" ht.  
 (CTC 12-3/16 ht.),  
 80" lead wires.



## CTC INSTALLATION



# 52" Patio Fan

**P2502-20** Antique Bronze

 Oak

**P2502-80** Forged Black


 Toasted Oak

**P2502-30** White

 White

**P2502-141** Galvanized

 Silver



P2502-30  
shown with White blades



P2502-80  
shown with Toasted Oak blades



P2502-141  
shown with Silver blades



P2502-20  
shown with Oak blades

## ENERGY INFORMATION AT HIGH SPEED

**Airflow** 4,991 cubic feet per minute  
**Electricity Use** 64 watts (excludes lights)  
**DOE Weighted CFM/W** 89 CFM/W

## FEATURES


- 15-year limited warranty
- Dual Mount (flat or sloped ceiling-23°)
- Close-to-ceiling installation
- SureConnect® System
- Quick-Install canopy
- AC Motor
- ABS all-weather blades
- Compatible with universal light kits
- Three speed pull-chain switch
- Wet location rated
- Add a P2630-30 wall control or P2662-01 hand-held remote control

## SIZE

52" dia., 12-3/4" ht.  
 (CTC 9-11/16 ht.),  
 72" lead wires.




## CTC INSTALLATION





Featuring 52" Builder Fan with P2602-30WB Light Kit  
Image: Kirbor Homes and Susan Wilson Interiors



# Accessories

*Accessorise your living area*



Scan with your camera on  
your smartphone or visit  
[www.progresslighting.com/ceilingfans](http://www.progresslighting.com/ceilingfans)

Spades  
P2570-15

Minimal

1

2 Sleek Details

3

Glass Decor



James Thomas  
Senior Product Designer

## Modernly Minimalism


with James

Modern interiors showcase sleek design through the use of neutrals, a minimalism approach, and the use of glass décor and technology. Take advantage of spaces with wide windows and use glass in other details such as countertops and furniture. This creates a sleek design for interior spaces. Integrate new innovations into a home's décor by adding elements, such as voice activated

devices and remote controlled light dimmers. To accentuate a Modern color palette, stick to neutral shades, as well as an overall minimalistic design to create this look.



Shop this style at  
[www.progresslighting.com/modern](http://www.progresslighting.com/modern)





# Indoor/Outdoor

Universal-style with quick-connect wiring.

## SCHOOLHOUSE

**P2601-20WB** Antique Bronze

**P2601-30WB** White

**P2601-80WB** Forged Black

**P2601-141WB** Galvanized

with opal glass.

8-1/2" dia., 7" ht.

One medium base 3000K 9w LED

lamp included. 800 lumens/lamp,

90 CRI. (dimmable) 10w LED or

60w incandescent max/socket.

Wet Location Rated.



## LOW PROFILE

**P2611-20WB** Antique Bronze

**P2611-30WB** White

**P2611-80WB** Forged Black

with opal glass.

10-1/2" dia., 4-1/2" ht.

Two medium base 3000K 9w LED

lamps included. 800 lumens/lamp,

90 CRI. (dimmable) 10w LED or

60w incandescent max/socket.

Wet Location Rated.



## ASHMORE

**P2636-20WB** Antique Bronze

with frosted seeded glass.

11" dia., 8-1/4" ht.

Two medium base 3000K 9w LED

lamps included. 800 lumens/lamp,

90 CRI. (dimmable) 10w LED or

60w incandescent max/socket.

Wet Location Rated.



All fixtures:



# Springer NEW

## SPRINGER LIGHT KIT\*

**P260000-081-WB** Antique Nickel

**P260000-129-WB** Architectural Bronze

**P260000-31M-WB** Matte Black

Two medium base 2700K 7w vintage

LED lamps included. 600 lumens/lamp,

90 CRI, dimmable. 7w LED max/socket.

\*This light kit is only compatible with the P250065 and P250000 Springer Fans.



# Torino

Universal-style light kit with quick-connect wiring.

## P2645-01WB

with etched glass.

Included Finials:

-09 Brushed Nickel

-20 Antique Bronze

-80 Forged Black

12" dia., 5-3/4" ht.

Two medium base 3000K 9w LED

lamps included. 800 lumens/lamp,

90 CRI. (dimmable) 10w LED or

60w incandescent max/socket.

Indoor use only.



# Gather, Bravo & Joy

Universal-style light kit with quick-connect wiring.

## P2650-01WB

with etched glass.

Included Finials:

-09 Brushed Nickel

-20 Antique Bronze

11" dia., 5-1/2" ht.

Two medium base 3000K 9w LED

lamps included. 800 lumens/lamp,

90 CRI. (dimmable) 10w LED or

60w incandescent max/socket.

Indoor use only.



# Madison

Universal-style with quick-connect wiring.

**P2623-09WB** Brushed Nickel

**P2623-20WB** Antique Bronze

with etched glass.

19" dia., 8" ht.

Three medium base 3000K 9w LED

lamps included. 800 lumens/lamp,

90 CRI. (dimmable) 10w LED or

60w incandescent max/socket.

Indoor use only.



# Universal Bowl

Universal-style with quick-connect wiring.

## P2612-01WB

with alabaster glass.  
Included Finials:  
-09 Brushed Nickel  
-031 Matte Black  
-20 Antique Bronze  
-30 White  
-15 Polished Chrome  
-143 Graphite  
10-3/4" dia., 5-1/2" ht.  
Two medium base 3000K 9w LED lamps included. 800 lumens/lamp, 90 CRI. (dimnable) 10w LED or 60w incandescent max/socket. Indoor use only.



# Wisten

Universal-style light kit with quick-connect wiring.

## P2649-01WB

with etched glass.  
Included Finials:  
-09 Brushed Nickel  
-20 Antique Bronze  
11" dia., 6-1/4" ht.  
Two medium base 3000K 9w LED lamps included. 800 lumens/lamp, 90 CRI. (dimnable) 10w LED or 60w incandescent max/socket. Indoor use only.




# Clifton Heights

Universal-style with quick-connect wiring.

## P2654-01WB

with etched glass.  
Included Finials:  
-09 Brushed Nickel  
-20 Antique Bronze  
12-1/2" sq., 6-1/4" ht.  
Two medium base 3000K 9w LED lamps included. 800 lumens/lamp, 90 CRI. (dimnable) 10w LED or 60w incandescent max/socket. Indoor use only.



# LED Light Kits

Universal-style with quick connect wiring.

## P2659-09

Brushed Nickel  
P2659-20 Antique Bronze  
P2659-30 White  
with etched white glass.  
12-1/4" dia., 4" ht.  
One 16w, 3000K LED module included. 1265 source lumens, 960 delivered lumens, 90 CRI. Indoor use only. (dimnable)



## P2660-01

with etched alabaster glass.  
Included Finials:  
-09 Brushed Nickel  
-20 Antique Bronze  
-30 White  
11-1/4" dia., 5-3/8" ht.  
One 16w, 3000K LED module included. 1241 source lumens, 1150 delivered lumens, 90 CRI. Indoor use only. (dimnable)



All fixtures:



# Trinity

Universal-style with quick-connect wiring.

## P2628-01WB

with etched glass.  
Included Finials:  
-09 Brushed Nickel  
-031 Matte Black  
-20 Antique Bronze  
-30 White  
13-3/8" dia., 6-3/8" ht.  
Two medium base 3000K 9w LED lamps included. 800 lumens/lamp, 90 CRI. (dimnable) 10w LED or 60w incandescent max/socket. Indoor use only.



## Four Light Universal

Universal-style with quick-connect wiring.


**P2643-09WB** Brushed Nickel  
**P2643-20WB** Antique Bronze  
**P2643-30WB** White  
 with alabaster glass.  
 13-5/8" dia., 7-3/4" ht.  
 Four medium base 3000K  
 9w LED lamps included.  
 800 lumens/lamp, 90 CRI.  
 (dimnable) 10w LED or 60w  
 incandescent max/socket.  
 Indoor use only.



## Three Light Universal

Universal-style with quick-connect wiring.

**P2642-09WB** Brushed Nickel  
**P2642-30WB** White  
 with alabaster glass.  
 13-5/8" dia., 7-3/4" ht.  
 Three medium base 3000K  
 9w LED lamps included.  
 800 lumens/lamp, 90 CRI.  
 (dimnable) 10w LED or 60w  
 incandescent max/socket.  
 Indoor use only.



## Low Profile

Universal-style with quick-connect wiring.

**P2602-09WB** Brushed Nickel  
**P2602-15WB** Polished Chrome  
**P2602-20WB** Antique Bronze  
**P2602-30WB** White  
**P2602-143WB** Graphite  
 with white opal glass.  
 10-1/2" dia., 4-1/2" ht.  
 Two medium base 3000K  
 9w LED lamps included.  
 800 lumens/lamp, 90 CRI.  
 (dimnable) 10w LED or 60w  
 incandescent max/socket.  
 Indoor use only.



## Four Light Alabaster

Spring clip glass attachment. For use with P2500, P2501, P2502, P2524 and P2525.

**P2610-09WB** Brushed Nickel  
**P2610-15WB** Polished Chrome  
**P2610-20WB** Antique Bronze  
**P2610-30WB** White  
**P2610-143WB** Graphite  
 with alabaster glass.  
 14-1/2" dia., 6-1/4" ht.  
 Four medium base 3000K  
 9w LED lamps included.  
 800 lumens/lamp, 90 CRI.  
 (dimnable) 10w LED or 60w  
 incandescent max/socket.  
 Indoor use only.



## Three Light Alabaster

Spring clip glass attachment. For use with P2500, P2501, P2502, P2524 and P2525.


**P2600-09WB** Brushed Nickel  
**P2600-20WB** Antique Bronze  
**P2600-30WB** White  
 with alabaster glass.  
 15" dia., 6-5/8" ht.  
 Three medium base 3000K  
 9w LED lamps included.  
 800 lumens/lamp, 90 CRI.  
 (dimnable) 10w LED or 60w  
 incandescent max/socket.  
 Indoor use only.



## Schoolhouse

Universal-style with quick-connect wiring.

**P2644-09WB** Brushed Nickel  
**P2644-30WB** White  
 with white opal glass.  
 8-1/2" dia., 6-1/2" ht.  
 One medium base 3000K 9w LED  
 lamp included. 800 lumens/lamp,  
 90 CRI. (dimnable) 10w LED or  
 60w incandescent max/socket.  
 Indoor use only.



# Accessory Downrods


3/4" diameter; approximately 1" outside diameter.

CEILING HT. DOWNROD L.	9'-10'	10'-11'	11'-12'	12'-14'	13'-15'	14'-16'	15'-17'
Brushed Nickel -09	P2603-09	P2604-09	P2605-09	P2606-09	P2607-09	P2608-09	P2609-09
Polished Chrome -15	P2603-15	P2604-15	P2605-15	P2606-15	P2607-15	P2608-15	P2609-15
Antique Bronze -20	P2603-20	P2604-20	P2605-20	P2606-20	P2607-20	P2608-20	P2609-20
Matte White -28	P2603-28	P2604-28	P2605-28	P2606-28	P2607-28	P2608-28	P2609-28
White -30	P2603-30	P2604-30	P2605-30	P2606-30	P2607-30	P2608-30	P2609-30
Matte Black -31	P2603-31	P2604-31	P2605-31	P2606-31	P2607-31	P2608-31	P2609-31
Guided Iron -71	P2603-80	P2604-80	P2605-80	P2606-80	P2607-80	P2608-80	P2609-80
Forged Black -80	P2603-80	P2604-80	P2605-80	P2606-80	P2607-80	P2608-80	P2609-80
Antique Nickel -81	P2603-81	P2604-81	P2605-81	P2606-81	P2607-81	P2608-81	P2609-81
Oil Rubbed Bronze -108	P2603-20	P2604-20	P2605-20	P2606-20	P2607-20	P2608-20	P2609-20
Architectural Bronze -129	P2603-20	P2604-20	P2605-20	P2606-20	P2607-20	P2608-20	P2609-20
Galvanized -141	P2603-141	P2604-141	P2605-141	P2606-141	P2607-141	P2608-141	P2609-141
Graphite -143	P2603-143	P2604-143	P2605-143	P2606-143	P2607-143	P2608-143	P2609-143
Painted Nickel -152	P2603-152	P2604-152	P2605-152	P2606-152	P2607-152		
Vintage Brass -163	P2603-163	P2604-163	P2605-163	P2606-163	P2607-163		
Blistered Iron -171	P2603-171	P2604-171	P2605-171	P2606-171	P2607-171		
Black Chrome -231	P2603-231	P2604-231	P2605-231	P2606-231	P2607-231		

# Downrod Selection Guide

Allow at least 7 feet (84 in.) from the floor to the bottom of the fan, with 8 or 9 feet being the ideal above-floor placement.

\*Average length downrod, included with each fan.



# Remotes, Wall Controls & 45° Canopies



**P2662-01**  
Fan/Light Remote  
Universal remote operates three fan speeds and full-range dimming light control. Includes canopy receiver and wall storage bracket. Will work with LED lamps and modules. Featuring four "dip" switches and 16 code options to avoid the chance of interference from other remotes.



**P2663-01**  
Fan/Light Remote  
Universal remote with two, four or eight-hour timer option, operates three fan speeds and full-range dimming light control. Includes canopy receiver and wall storage bracket. Will work with LED lamps and modules. Featuring many code combination options to avoid the chance of interference from other remotes.



**P2618-01**  
Fan/Light Remote  
Provides fan speed and light control from convenient hand-held remote. Compatible with non-dimmable compact fluorescent lamps. For single pole applications. Receiver fits in fan canopy.



**P2661-01**  
Universal Fan/Light Remote  
Provides fan speed and full range light dimming control from a convenient hand held remote control. For single pole applications. Includes a wall plate for added storage convenience. Receiver fits in the fan canopy.



**P2667-31**  
WiFi Fan/Light Remote  
Universal WiFi remote control for AC motor fans. Control your ceiling fan or light kit via WiFi from anywhere. Pairs with Alexa, Google Home, or app on your phone or tablet. Voice control the fan with three speeds and the light with full range dimming. App control the fan with three speeds or four timer selections or full range dimming control of the light. Can be controlled with the hand held remote included with the kit.



**P2665-30** White  
Universal remote includes a wall mount transmitter, that operates three fan speeds and full-range dimming light control. Includes canopy receiver and wall storage bracket. Will work with LED lamps and modules. Featuring four "dip" switches and 16 code options to avoid the chance of interference from other remotes.



**P2631-30** White  
Full-function wall control transmitter (receiver sold with ceiling fan). Use with, or in place of, hand-held remote included with fans that have a downlight and a reverse module. Includes switch plate cover.



**P2630-30** White  
Four-speed fan wall control with full-range light dimmer. Fits single-gang wall box; requires two circuits. Includes switch plate cover. Not for use with multiple fans.



**P2613-30** White  
Four-speed fan wall control. Includes switch plate cover. Not for use with multiple fans.



**P2673-01**  
DC Fan WiFi Module  
Add the WiFi module to your Ryne or 52" Springer ceiling fan for control at your fingertips. You can easily control your fan with a hand-held remote; or a smart phone, tablet, voice assistant (Amazon Alexa and Google Home) via the Smart By Bond app.



**P2666-09**  
Brushed Nickel  
45° canopy\*



**P2666-31M**  
Matte Black  
45° canopy\*



**P2666-30**  
White  
45° canopy\*



**P2666-143**  
Graphite  
45° canopy\*



**P2666-15**  
Polished Chrome  
45° canopy\*




**P2666-129**  
Architectural Bronze  
45° canopy\*

*This accessory is for use with any Progress Lighting ceiling fans with a hanging weight of 25 lbs or less. Includes ceiling bracket, canopy, hanger ball, trim ring, and CTC mounting hardware. The only fans that can be CTC mounted are P2501, P2503, P2521, P2536, and P2531.*

# Cross Reference Chart

Here's where you'll find the specifications you'll need to purchase the perfect fan for your space. Search by Model Number, Name or Page Number.



Model #	Model Name	Page	Motor (MM)	Motor Type AC or DC	Fan Diameter	Blade Pitch	Dimensions				Accepts Longer Downrods	Energy Star	Remotes				P2667-31 WiFi Remote Control	P2665-30	P2631-30	P2630-30	P2613-01	Universal Light Kit
							A	B	C	D			P2661-01	P2662-01	P2663-01	P2618-01						
P250000	Springer	50	DC-165	DC	60"	22°	17.38"	13.19"	8.38"	6.06"	Yes	No										
P250002	Farris	78	DC-125N	DC	60"	18°-13°	15.63"	12.5"	7.5"	5.13"	Yes	No										
P250003	Kaysville	52	178 X 22	DC	56"	15°	17.25"	13.25"	9.94"	6.44"	Yes	No										
P250006	Loring	40	120 X 20	AC	33"	13.5°	15.19"	9.02"	6.06"	7.73"	No	No	X	X	X	X	X	X		X	X	
P250007	Claret	112	153 X 20	AC	54"	14°	15.13"	10.50"	7.88"	5.88"	Yes	No	X	X	X	X	X	X		X	X	
P250008	Drift	158	153 X 12	AC	32"	13°	14.38"	11.75"	9.25"	5.9"	Yes	No	X	X	X	X	X	X		X	X	X
P250009	Alleron	56	178 X 12	DC	56"	15°	15.94"	11.38"	9.31"	5.88"	Yes	No										
P250010	Royer	92	172 X 20	AC	56"	13°	17.82"	16.39"	10.31"	5.13"	Yes	No	X	X	X	X	X	X		X	X	
P250011	Midvale	176	188 X 25	AC	56"	13°	20.88"	12.81"	10.06"	6.44"	Yes	No	X	X	X	X	X	X		X	X	
P250012	Gulliver	38	N/A	AC	23"	N/A	18.13"	N/A	5.75"	7.31"	Yes	No	X	X	X	X	X	X		X	X	
P250016	Edgefield	156	DC-125N	DC	52"	13°	14.44"	12.5"	11.0"	5.18"	Yes	Yes										X
P250021	Glenfalls	110	188 X 22	AC	56"	13°	14.88"	12.88"	8.75"	5.18"	Yes	No	X	X	X	X	X	X		X	X	
P250022	Chapin	102	188 X 22	AC	54"	14°	15.88"	14.45"	9.75"	5.18"	Yes	No	X	X	X	X	X	X		X	X	X
P250024	Bedwin	104	DC-125N	DC	54"	14°	15.44"	12.25"	8.69"	5.18"	Yes	No										X
P250026	Arlo	72	DC153-20NS	DC	60"	13°	18.56"	14.0"	8.25"	5.18"	Yes	No										
P250028	Lindale	166	153 X 18	AC	52"	13°	11.19"	8.0"	8.25"	5.96"	No	No	X	X	X	X	X		X	X	X	
P250030	Huff	66	DC168-25NS	DC	96"	14°	15.44"	12.0"	11.63"	6.25"	Yes	No										X
P250032	Holland	88	DC153-10NS	DC	60"	23°	16.63"	13.56"	8.56"	5.12"	Yes	No										
P250034	Alfresco	186	188 X 15	AC	54"	13°	19.25"	11.88"	12.0"	5.94"	Yes	No	X	X	X	X	X	X		X	X	
P250036	Albin	194	172 X 17	AC	54"	13°	15.63"	10.62"	11.01"	6.31"	Yes	No	X	X	X	X	X	X		X	X	
P250038	Bixby	74	DC125-30NS	DC	60"	18°	17.69"	15.12"	6.93"	5.19"	Yes	No										
P250040	Rudder	178	DC153-10NS	DC	56"	14°	16.01"	12.0"	9.13"	6.31"	Yes	No										
P250058	Braden	160	153 X 15	AC	44"	13°	9.81"	7.23"	7.70"	7.70"	No	No	X	X	X	X	X		X	X	X	
P250059	Vernal	28	156 X 12	DC	60"	12°	14.25"	9.60"	N/A	7.00"	Yes	No										
P250060	Ryne	30	156 X 8	DC	52"	12°	13.63"	9.60"	N/A	7.00"	Yes	No										
P250062	Edwidge	180	100 X 30	DC	52"	13°	13.55"	7.35"	N/A	5.75"	Yes	No										
P250063	Willacy	32	100 X 30	DC	48"	13°	14.52"	12.78"	6.14"	6.87"	No	No										
P250065	Springer 52"	46	165NL	DC	52"	22°	17.38"	13.19"	8.38"	6.06"	Yes	No										
P250066	AirPro E Star	150	172 X 17	AC	52"	12°	13.06"	10.02"	11.0"	5.87"	Yes	Yes	X	X	X	X	X	X		X	X	X
P250067	Briarwood	34	N/A	AC	22"	N/A	15.63"	N/A	22"	7.31"	Yes	No	X	X	X	X	X	X		X	X	
P250068	Belva	36	N/A	AC	25.25"	N/A	17.75"	N/A	25.25"	7.31"	Yes	No	X	X	X	X	X	X		X	X	
P250069	Manvel	76	100 X 30	DC	60"	13°	11.13"	10.87"	7.36"	6.31"	Yes	No										
P250070	Kennedale	192	153 X 25	DC	72"	12°	18.05"	16.50"	13.0"	6.31"	Yes	No										X
P250071	Spicer	60	178 X 12	DC	54"	28°	11.56"	8.00"	11.00"	6.44"	Yes	No										
P250072	Kasota	174	178 X 12	DC	56"	12°	15.00"	12.25"	9.75"	6.44"	Yes	No										
P250073	Mesilla	54	178 X 22	DC	60"	18°	14.25"	8.19"	11.81"	6.44"	Yes	No										
P250074	Carrollwood	94	178 X 12	DC	56"	13°	18.00"	13.09"	8.06"	6.44"	Yes	No										
P250077	AirPro E Star	148	172X17	AC	52"	11.5°	18.69"	10.01"	11.00"	5.125"	Yes	Yes	X	X	X	X	X	X		X		
P250078	AirPro E Star	149	172X17	AC	52"	11.5°	16.69"	10.01"	11.00"	5.125"	Yes	Yes	X	X	X	X	X	X		X	X	
P250080	AirPro Builder	142	153X12	AC	52"	11.5°	12.57"	10.01"	11.00"	5.125"	Yes	No	X	X	X	X	X	X		X	X	X

Continued on following spread.

\*Highlighted cells = Control does not include reverse function

Cross Reference Chart *continued*

\*Highlighted cells = Control does not include reverse function

Model #	Model Name	Page	Motor (MM)	Motor Type AC or DC	Fan Diameter	Blade Pitch	Dimensions				Accepts Longer Downrods	Energy Star	Remotes				P2667-31 WiFi Remote Control	P2665-30	P2631-30	P2630-30	P2613-01	Universal Light Kit
							A	B	C	D			P2661-01	P2662-01	P2663-01	P2618-01						
P250081	AirPro Builder	144	153X12	AC	52"	11.5°	18.69"	10.01"	11.00"	5.125"	Yes	No	X	X	X	X	X	X		X	X	
P250082	AirPro Builder	145	153X12	AC	52"	11.5°	16.69"	10.01"	11.00"	5.125"	Yes	No	X	X	X	X	X	X		X	X	
P250084	AirPro E Star	146	172X17	AC	52"	11.5°	12.57"	10.01"	11.00"	5.125"	Yes	Yes	X	X	X	X	X	X		X	X	X
P250085	AirPro Builder	144	153X12	AC	52"	11.5°	18.69"	10.01"	11.00"	5.125"	Yes	No	X	X	X	X	X	X		X	X	
P2500	42" Builder	153	153 X 10	AC	42"	12°	12.25"	9.65"	9.5"	5.13"	Yes	No	X	X	X	X	X	X		X	X	X
P2501	Builder	155	153 X 12	AC	52"	11°	12.71"	9.58"	11.0"	5.13"	Yes	No	X	X	X	X	X	X		X	X	X
P2502	52" Patio Fan	200	153 X 17	AC	52"	11°	12.75"	10.2"	11.75"	5.13"	Yes	No	X	X	X	X	X	X		X	X	X
P2503	Performance	152	188 X 15	AC	52"	14°	15.25"	12.56"	12.19"	6.5"	Yes	No	X	X	X	X	X	X		X	X	X
P2521	Signature	132	153 X 18	AC	52"	12°	14.63"	11.5"	11.75"	6.5"	Yes	No	X	X	X	X	X	X		X	X	X
P2524	42" Hugger	169	153 X 10	AC	42"	11°	8.31"	5.5"	10.0"	10.0"	No	No								X	X	X
P2525	52" Hugger	168	153 X 13	AC	52"	11°	8.13"	5.93"	11.06"	11.06"	No	No								X	X	X
P2526	Deco Patio Fan	198	188 X 20	AC	52"	12°	17.38"	14.25"	12.13"	6.5"	Yes	No	X	X	X	X	X	X		X	X	X
P2530	Signature Plus	139	153 X 18	AC	54"	12°	15.13"	10.4"	11.8"	6.5"	Yes	No	X	X	X	X	X	X		X	X	X
P2531	Clifton Heights	140	153 X 18	AC	52"	12.5°	15.75"	12.7"	7.88"	6.5"	Yes	No	X	X	X	X	X	X		X	X	X
P2533	54" Patio Fan	200	153 X 18	AC	54"	12°	18.75"	13.34"	11.38"	6.5"	Yes	No	X	X	X	X	X	X		X	X	X
P2539	Signature Plus II	138	153 X 18	AC	54"	12°	15.3"	11.2"	11.8"	6.5"	Yes	No	X	X	X	X	X	X		X	X	
P2540	Harranvale	108	153 X 20	AC	54"	12°	16.38"	12.1"	12.63"	5.88"	Yes	No	X	X	X	X	X	X		X	X	
P2542	Soar	106	153 X 20	AC	54"	12°	14.7"	11.05"	10.1"	5.88"	Yes	No	X	X	X	X	X	X		X	X	
P2544	Graceful	114	153 X 20	AC	54"	12°	16.38"	11.5"	9.75"	5.88"	Yes	No	X	X	X	X	X	X		X	X	
P2546	Ellwood	62	212 X 25	AC	68"	17°	16.7"	11.5"	9.63"	5.88"	Yes	No	X	X	X	X	X	X	X	X	X	X
P2548	Fresno	122	188 X 25	AC	60"	14°	17.2"	10.8"	12.75"	5.88"	Yes	No						X				
P2550	Vast	68	DC - 165	DC	72"	14°	16.75"	13.67"	8.25"	5.13"	Yes	No										
P2552	Billows	128	153 X 15	AC	52"	12°	17.5"	11.18"	9.1"	5.88"	Yes	No	X	X	X	X	X	X		X	X	
P2553	Trevina II	135	153 X 15	AC	52"	12°	15.75"	10.8"	9.44"	5.88"	Yes	No	X	X	X	X	X	X		X	X	
P2554	Gaze	82	172 X 17	AC	60"	12°	13.13"	10.71"	6.88"	5.13"	Yes	No	X	X	X	X	X	X		X	X	
P2555	Trevina II 44"	134	153 X 12	AC	44"	12°	15.68"	12.21"	8.38"	5.88"	Yes	No	X	X	X	X	X	X		X	X	
P2556	Trevina II 52"	135	153 X 15	AC	52"	12°	15.75"	10.8"	9.44"	5.88"	Yes	No	X	X	X	X	X	X		X	X	
P2558	Verada	126	153 X 18	AC	52"	12°	16.56"	10.1"	10.19"	5.88"	Yes	No	X	X	X	X	X	X		X	X	
P2560	Caleb	64	212 X 25	AC	68"	17°	18.0"	11.98"	13.75"	5.88"	Yes	No	X	X	X	X	X	X	X	X	X	X
P2562	Lakehurst	196	188 X 25	AC	60"	13.5°	15.69"	13.5"	11.25"	5.9"	Yes	No	X	X	X	X	X	X		X	X	X
P2564	Montague	190	188 X 25	AC	60"	13°	17.63"	12.28"	9.95"	5.9"	Yes	No	X	X	X	X	X	X		X	X	
P2568	Kudos	120	172 X 17	AC	52"	13°	17.63"	13.11"	9.69"	5.95"	Yes	No	X	X	X	X	X	X		X	X	
P2570	Spades	84	DC188-10	DC	56"	22°	18.13"	16.67"	8.08"	6.42"	Yes	No										
P2572	Vox	164	153 X 18	AC	52"	12°	11.63"	7.13"	11.41"	9.91"	No	No	X	X	X	X	X	X	X	X	X	
P2574	Whirl	182	188 X 25	AC	60"	12°	15.88"	11.93"	10.01"	5.91"	Yes	No	X	X	X	X	X	X		X	X	
P2576	Smyrna	188	153 X 20	AC	52"	12°	19.44"	10.75"	11.94"	5.88"	Yes	No	X	X	X	X	X	X		X	X	
P2578	Tempt	124	153 X 18	AC	52"	12°	16.19"	9.94"	10.25"	5.88"	Yes	No	X	X	X	X	X	X		X	X	
P2582	Gust	116	172 X 20	AC	54"	13.5°	16.0"	13.13"	9.95"	5.91"	Yes	No	X	X	X	X	X	X		X	X	
P2584	Greer	100	153 X 20	AC	54"	12°	21.56"	11.61"	7.88"	5.88"	Yes	No	X	X	X	X	X	X		X	X	
P2586	Glandon	96	188 X 25	AC	60"	12°	17.06"	13.09"	9.06"	5.88"	Yes	No	X	X	X	X	X	X		X	X	
P2588	Braden	162	172 X 20	AC	56"	13°	9.81"	7.23"	7.70"	7.70"	No	No	X	X	X	X	X	X	X	X	X	
P2592	Oriole	90	172 X 20	AC	60"	21°	14.56"	12.5"	9.17"	6.0"	Yes	No	X	X	X	X	X	X		X	X	
P2594	Sanford	42	N/A	AC	23"	31.7°	17.69"	13.13"	22.81"	5.12"	Yes	No	X	X	X	X	X	X		X	X	
P2599	Uni Pack	154	153 X 12	AC	52"	11°	17.56"	9.58"	11.0"	5.13"	Yes	No	X	X	X	X	X	X		X	X	X

# Fan Blade Finishes



American Walnut



Black Chrome



Cottage White



Driftwood




Natural Cherry




Walnut



Antique Black



Blistered Iron



Dark Bamboo



Galvanized



Oak



Washed Oak




Antique Bronze



Brushed Nickel



Dark Cherry



Graphite



Rustic Charcoal



White Barnwood




Antique Wood




Cherry




Dark Walnut



Gray Weathered Wood



Pewter



White Metallic




Architectural Bronze



Chestnut



Distressed Ebony




Koa Woodgrain



Silver



White Washed




Black



Classic Walnut



Distressed Walnut



Distressed White



Medium Cherry



Toasted Oak



All finish representations are part of Progress Lighting's comprehensive design and specification program. Through extensive research, these finishes have been carefully chosen to complement all Progress Lighting products, including our extensive range of materials and accessory options.

These finish representations match actual finish colors as accurately as possible, and while every effort has been made to render colors accurately, they may vary slightly from the actual product, especially hand-painted finishes due to the nature of hand craftsmanship.







# Symbol Legend



Products referencing this logo meet the energy efficiency requirements for ceiling fans and or ceiling fan light kits set forth in ENERGY STAR® product specifications. Please refer to [www.energystar.gov](http://www.energystar.gov) for specific product qualifications and list of certified products.



Please note indoor only (dry location) fans should only be used indoors. Even if an outdoor area or screened-in porch is covered, the motor and the blades can be affected when exposed to humidity. You can, however, “bring the outdoors inside” – as using outdoor ceiling fans are perfectly acceptable to use in interior spaces.



If you are selecting a ceiling fan for a space that is outdoors and under a roof, i.e. any covered porches; you should select either a damp rated or wet listed fan. Damp location fans may also be used indoors.



If the fan comes directly into contact with water, you'll need to ensure that the ceiling fan has a “wet” listing. Ceiling fans designed for damp or wet locations feature elements, such as moisture-resistant motors and all weather blades. Wet location fans may also be used indoors.



This marking indicates fixtures that have an integrated LED or replaceable LED module or LED lamps that has been tested and listed in the California Appliance Database. Check for certified lamps, fixtures or LED light engines by searching the MAEDBS database. Go to [cacertappliances.energystar.gov](http://cacertappliances.energystar.gov)



Complies with “American with Disabilities Act”



Products comply with the California Appliance Efficiency Regulations. Certified products are listed on the appliance efficiency database found at [www.appliances.energy.ca.gov](http://www.appliances.energy.ca.gov).



Products with this icon are Dark-Sky Friendly: they are certified by the International Dark-Sky Association to minimize glare while reducing light trespass and skyglow (they don't pollute the night sky.)



The products with this logo have passed the cUL requirements and are available for sale in Canada. These products include the additional safety features needed to comply with the regulations in Canada. Items with the icon are listed with NRCAN.



Products with this icon are WiFi compatible and may be controlled with WiFi when one of the following controls is added;

- AC Motor fans can add the P2667-31 WiFi remote control
- DC Motor fans that are WiFi compatible can add the P2673-01 WiFi module.

With the addition of one of the above controls, you may easily control your fan or light with your smart phone, tablet, voice controls, or hand held remote. Use the Smart by Bond technology to control on/off function of the fan and the light kit along with full range dimming and fan speed control..



Products with this icon have WiFi Control Included. Easily control your fan with your smart phone, tablet, voice controls, or a hand held remote. Use the Smart by Bond technology to control on/off function of the fan and the light kit along with full range dimming and fan speed control.

## Warranty

For more details regarding product warranty coverage, please consult a qualified Progress Lighting distributor or visit:

[www.progresslighting.com/warranty](http://www.progresslighting.com/warranty)

## Where to buy

To purchase Progress Lighting products from one of our authorized dealers visit:

[www.progresslighting.com/where-to-buy](http://www.progresslighting.com/where-to-buy)



Featuring Glandon,  
Image: Dostie Homes and Jessie Preza Photography

# Equip. Educate. Excite.

These three words define the mission of Progress Lighting. Flip through our catalog, and you'll quickly see how we equip you with the education to make all your exciting design dreams come true. Not sure where to start? Whether you're browsing our catalog or visiting our website, Progress is at your service to help you envision where and how to use our products.

## Experience Progress

Learn how lighting can totally transform a space. Experience Progress features beautiful room images from our builder partners, design firms, social media fans and influencers bringing the Progress Lighting story to life. Visit [www.progresslighting.com/experienceprogress](http://www.progresslighting.com/experienceprogress)

## Our Blog

Explore our blog for even more design inspiration, product integration and trend guidance to make your home into a haven of livable luxury. See [www.progresslighting.com/blog](http://www.progresslighting.com/blog)

## Be Inspired

- @ProgressLtg
- @ProgressLtg
- @ProgressLighting
- @ProgressLtg
- Progress Lighting
- Progress-Lighting

## See Yourself Here

---

Every home and every family has a story that's all their own. In this issue, we introduce you to the many ways Progress Lighting can bring that story to life.



PROGRESS LIGHTING

701 Millennium Boulevard  
Greenville, SC 29607

[www.progresslighting.com](http://www.progresslighting.com)

