

Ceiling Fan Catalog

SUMMER 2023



Your guide to selecting the perfect ceiling fan.

The ceiling fans you select for your home should not only be functional, but also show an expression of your personality and elevate each room’s design aesthetic. While there are many choices to make during the selection process, it doesn’t have to be overwhelming. This catalog is intentionally designed to easily select the perfect ceiling fan for your space.

BE INSPIRED

- @ProgressLtg
- @ProgressLtg
- @ProgressLighting
- @ProgressLtg
- Progress Lighting
- Progress-Lighting

2
PRODUCT FINDER

Use the Product Finder to find the perfect ceiling fan.

18
FAN INSPIRATION

Our ceiling fans do more than cool a room – they combine beautiful design with premium performance. Choose from fans that make a statement across a variety of design trends, from simple to spectacular.

26
INDOOR FANS



154
OUTDOOR FANS











































186
ACCESSORIES

Light Kits	188
Downrods	194
Remotes	195
Cross Reference Chart	198
Blade Finishes	204





















207
PRODUCT INDEX

Ceiling Fans Indoor

AIRPRO® Brushed Nickel	AIRPRO® Matte Black	AIRPRO® White	AIRPRO® Brushed Nickel
137 	137 	137 	136 
AIRPRO® Matte Black	AIRPRO® White	AIRPRO® Brushed Nickel	AIRPRO® Matte Black
136 	136 	135 	135 
AIRPRO® White	AIRPRO® Antique Bronze	AIRPRO® Brushed Nickel	AIRPRO® Graphite
135 	128 	128 	129 
AIRPRO® Matte Black	AIRPRO® Polished Chrome	AIRPRO® White	AIRPRO® ENERGY STAR Brushed Nickel
129 	128 	129 	139 
AIRPRO® ENERGY STAR Matte Black	AIRPRO® ENERGY STAR White	AIRPRO® ENERGY STAR Brushed Nickel	AIRPRO® ENERGY STAR Matte Black
139 	139 	141 	141 

AIRPRO® ENERGY STAR White	AIRPRO® ENERGY STAR Brushed Nickel	AIRPRO® ENERGY STAR Matte Black	AIRPRO® ENERGY STAR White
141 	142 	142 	142 
AIRPRO® ENERGY STAR Brushed Nickel	AIRPRO® ENERGY STAR Matte Black	AIRPRO® ENERGY STAR White	ALLERON Antique Nickel
138 	138 	138 	55 
ALLERON Flat Black	ARLO Black	ARLO Brushed Nickel	BASTROP Brushed Nickel
55 	71 	71 	35 
BASTROP Graphite	BASTROP Matte Black	BEDWIN Antique Nickel	BEDWIN Graphite
35 	35 	89 	89 
BELVA Cottage White	BELVA Matte Black	BEXAR Brushed Nickel	BEXAR Matte Black
37 	37 	145 	145 

Ceiling Fans Indoor

BILLOWS Antique Bronze	BILLOWS Brushed Nickel	BILLOWS Forged Black	BRADEN 44" Brushed Nickel
105 	105 	105 	146 
BRADEN 44" Satin White	BRADEN 44" Black	BRADEN 56" Brushed Nickel	BRADEN 56" Polished Chrome
148 	148 	146 	146 
BRADEN 56" Architectural Bronze	BRADEN 56" Satin White	BRADEN 56" Matte Black	BRAZAS Brushed Nickel
146 	147 	147 	115 
BRAZAS Matte Black	BRIARWOOD Antique Bronze	BRIARWOOD Galvanized Finish	BRIARWOOD Graphite
115 	41 	41 	41 
BRIARWOOD Matte Black	BUILDER FAN 42" Antique Bronze	BUILDER FAN 42" Brushed Nickel	BUILDER FAN 42" White
41 	143 	143 	143 











BUILDER FAN 52" Antique Bronze	BUILDER FAN 52" Brushed Nickel	BUILDER FAN 52" Graphite	BUILDER FAN 52" Polished Chrome
130 	131 	130 	130 
BUILDER FAN 52" White	BUILDER FAN 52" White	BUILDER FAN 52" W/LIGHT KIT Architectural Bronze	BUILDER FAN 52" W/LIGHT KIT Brushed Nickel
131 	131 	134 	134 
BUILDER FAN 52" W/LIGHT KIT White	BYARS Brushed Nickel	BYARS Matte Black	CALEB Antique Bronze
134 	57 	57 	65 
CALEB Black	CALEB Brushed Nickel	CARROLLWOOD Matte Black	CARROLLWOOD Brushed Nickel
65 	65 	77 	77 
CARROLLWOOD White	CLARET Black	CLARET Brushed Nickel	CLARET Oil Rubbed Bronze
77 	95 	95 	95 





















Ceiling Fans Indoor

CLIFTON HEIGHTS Antique Bronze 133 	CLIFTON HEIGHTS Brushed Nickel 133 	DALLAM Brushed Nickel 79 	DALLAM Matte Black 79 
DRIFT Architectural Bronze 144 	DRIFT Brushed Nickel 144 	DRIFT White 144 	EDGEFIELD Architectural Bronze 140 
EDGEFIELD Brushed Nickel 140 	EDGEFIELD White 140 	ELLWOOD Antique Bronze 63 	ELLWOOD Brushed Nickel 63 
FARRIS Brushed Nickel 75 	FARRIS Graphite 75 	FARRIS Oil Rubbed Bronze 75 	FREESTONE Antique Bronze 51 
FREESTONE Brushed Nickel 51 	FREESTONE Matte Black 51 	FRESNO Antique Bronze 107 	FRESNO Brushed Nickel 107 





















FRESNO White 107 	GAZE Antique Bronze 83 	GAZE Black 83 	GAZE Brushed Nickel 83 
GAZE Polished Chrome 83 	GILLEN Blistered Iron 59 	GILLEN Matte Black 59 	GILLEN Vintage Brass 59 
GLANDON Antique Nickel 91 	GLANDON Gilded Iron 91 	GLENFALLS Black 97 	GLENFALLS Brushed Nickel 97 
GLENFALLS Satin White 97 	GRACEFUL Polished Chrome 111 	GREER Gilded Iron 93 	GULLIVER Galvanized Finish 39 
GULLIVER Graphite 39 	GUST Antique Bronze 103 	GUST Brushed Nickel 103 	GUST Graphite 103 





















Ceiling Fans Indoor

HARRANVALE Antique Bronze	HARRANVALE Graphite	HARRANVALE White	HUFF Black
113 	113 	113 	67 
HUFF Brushed Nickel	HUFF Satin White	HUGGER 42" Brushed Nickel	HUGGER 42" White
67 	67 	152 	152 
HUGGER 52" Brushed Nickel	HUGGER 52" White	KAYSVILLE Antique Nickel	KAYSVILLE Graphite
151 	151 	49 	49 
LINDALE Antique Nickel	LINDALE Architectural Bronze	MANVEL Antique Bronze	MANVEL Antique Nickel
150 	150 	73 	73 
MANVEL Cottage White	MANVEL Matte Black	MCLENNAN II Brushed Nickel	MESILLA Antique Bronze
73 	73 	117 	53 


MESILLA Antique Nickel	MESILLA Flat Black	ORIOLE Architectural Bronze	ORIOLE Brushed Nickel
53 	53 	87 	87 
ORIOLE Black	PERFORMANCE 52" Antique Bronze	PERFORMANCE 52" Brushed Nickel	PERFORMANCE 52" White
87 	132 	132 	132 
RYNE Architectural Bronze	RYNE Black	RYNE Satin White	SANFORD Architectural Bronze
31 	31 	31 	43 
SANFORD Brushed Nickel	SIGNATURE Antique Bronze	SIGNATURE Brushed Nickel	SIGNATURE Forged Black
43 	127 	127 	127 
SIGNATURE PLUS Antique Bronze	SIGNATURE PLUS Brushed Nickel	SIGNATURE PLUS White	SIGNATURE PLUS II Antique Bronze
126 	126 	126 	125 

Ceiling Fans Indoor









SIGNATURE PLUS II Brushed Nickel 125 	SIGNATURE PLUS II White 125 	SOAR Brushed Nickel 99 	SOAR White 99 
SPADES Brushed Nickel 85 	SPADES Graphite 85 	SPADES Polished Chrome 85 	SPICER Antique Bronze 61 
SPICER Brushed Nickel 61 	SPICER Matte Black 61 	SPRINGER 52" Antique Nickel 45 	SPRINGER 52" Architectural Bronze 45 
SPRINGER 52" Matte Black 45 	SPRINGER 60" Antique Nickel 47 	SPRINGER 60" Architectural Bronze 47 	SPRINGER 60" Matte Black 47 
TARSUS Brushed Nickel 81 	TARSUS Matte Black 81 	TEMPT Vintage Brass 109 	TOMPKINS Brushed Nickel 101 

TOMPKINS Matte Black 101 	TREVINA II 44" Black 122 	TREVINA II 44" Brushed Nickel 122 	TREVINA II 44" Satin White 122 
TREVINA II 52" Architectural Bronze 123 	TREVINA II 52" Painted Nickel 123 	TREVINA II 52" LED Antique Bronze 124 	TREVINA II 52" LED Brushed Nickel 124 
TREVINA II 52" LED White 124 	TREVINA IV Painted Nickel 119 	TREVINA V ENERGY STAR Matte Black 121 	TREVINA V ENERGY STAR Painted Nickel 121 
TREVINA V ENERGY STAR Satin White 121 	VAST Antique Bronze 69 	VAST Black 69 	VAST Brushed Nickel 69 
VAST White 69 	VERNAL Architectural Bronze 29 	VERNAL Black 29 	VERNAL Painted Nickel 29 




















Ceiling Fans Indoor



VOX Antique Bronze	VOX Brushed Nickel	VOX White	WILLACY Black
149	149	149	33
			
WILLACY Painted Nickel			
33			
			

Ceiling Fans Outdoor




















ALBIN Architectural Bronze	ALBIN Black	ALFRESCO Architectural Bronze	ALFRESCO Blistered Iron
55	55	173	173
			
ALLERON Antique Nickel	ALLERON Flat Black	ARLO Black	ARLO Brushed Nickel
71	71	71	71
			
BASTROP Brushed Nickel	BASTROP Graphite	BASTROP Matte Black	BELVA Cottage White
35	35	35	37
			
BELVA Matte Black	BRAZAS Brushed Nickel	BRAZAS Matte Black	BRIARWOOD Antique Bronze
37	115	115	41
			
BRIARWOOD Galvanized Finish	BRIARWOOD Graphite	BRIARWOOD Matte Black	CALEB Antique Bronze
41	41	41	65
			

Ceiling Fans Outdoor

CALEB Black 65 	CALEB Brushed Nickel 65 	DALLAM Brushed Nickel 79 	DALLAM Matte Black 79 
DECORATIVE PATIO FAN Antique Bronze 183 	EDWIDGE Black 169 	EDWIDGE Painted Nickel 169 	EDWIDGE Satin White 169 
GILLEN Blistered Iron 59 	GILLEN Matte Black 59 	GILLEN Vintage Brass 59 	GULLIVER Galvanized Finish 39 
GULLIVER Graphite 39 	HUFF Black 67 	HUFF Brushed Nickel 67 	HUFF Satin White 67 
KASOTA Graphite 161 	KASOTA Oil Rubbed Bronze 161 	KASOTA Painted Nickel 161 	KAYSVILLE Antique Nickel 49 

KAYSVILLE Graphite 49 	KENNEDALE Matte Black 181 	KENNEDALE Painted Nickel 181 	KENNEDALE Satin White 181 
LAKEHURST Antique Bronze 182 	LAKEHURST Forged Black 182 	LAKEHURST White 182 	MANVEL Antique Bronze 73 
MANVEL Antique Nickel 73 	MANVEL Cottage White 73 	MANVEL Matte Black 73 	MESILLA Antique Bronze 53 
MESILLA Antique Nickel 53 	MESILLA Flat Black 53 	MIDVALE Blistered Iron 167 	MIDVALE Galvanized Finish 167 
MIDVALE Matte White 167 	MONTAGUE Antique Bronze 177 	MONTAGUE Forged Black 177 	MONTAGUE White 177 

Ceiling Fans Outdoor

PATIO FAN 52" Antique Bronze	PATIO FAN 52" Forged Black	PATIO FAN 52" White	PATIO FAN 54" Antique Bronze
185 	185 	185 	184 
RYNE Architectural Bronze	RYNE Black	RYNE Satin White	SANFORD Architectural Bronze
31 	31 	31 	43 
SANFORD Brushed Nickel	SCHAAL Matte Black	SCHAAL Satin White	SCHAFFER II Antique Nickel
43 	159 	159 	165 
SCHAFFER II Matte Black	SCHAFFER II Satin White	SMYRNA Antique Bronze	SMYRNA Forged Black
165 	165 	175 	175 
SPICER Antique Bronze	SPICER Brushed Nickel	SPICER Matte Black	SPRINGER II Antique Nickel
61 	61 	61 	157 

SPRINGER II Architectural Bronze	SPRINGER II Matte Black	TOMPKINS Brushed Nickel	TOMPKINS Matte Black
157 	157 	101 	101 
UPSHUR Antique Bronze	UPSHUR Brushed Nickel	UPSHUR Matte Black	VAST Antique Bronze
163 	163 	163 	69 
VAST Black	VAST Brushed Nickel	VAST White	VERNAL Architectural Bronze
69 	69 	69 	29 
VERNAL Black	VERNAL Painted Nickel	WHIRL Antique Bronze	WHIRL Antique Nickel
29 	29 	171 	171 
WHIRL Forged Black	WILLACY Black	WILLACY Painted Nickel	
171 	33 	33 	



Fan Inspiration

Today's ceiling fans incorporate beautiful features, such as hand carved blades, sleek finishes and natural elements to appeal to a variety of different design trends. At Progress Lighting, we strive to incorporate this shift in our ceiling fan designs and are eager to present an expanded offering in this catalog.

The Perfect Fan in 5 Steps

Ceiling Fan *Buyer's Guide*

Ceiling fans are practical and efficient solutions for creating comfortable and welcoming living areas. With many styles, functions and features to choose from, narrowing down the choices can be a challenge. Here we present five tips for selecting the perfect ceiling fan for your home.

1 Settle on Style

Choose a style that complements your décor. Consider fan shape, blade features and finish to help you meet your room's design needs. Choose from Traditional, Transitional, Coastal or Farmhouse styles. The possibilities are vast!



Transitional



Organic Modern



Industrial



Indoor

Featuring Vernal




Outdoor

Featuring Mesilla

2 Explore Indoor vs. Outdoor Uses

Fans provide a breezy setting for reading a book or catching up with friends, making them ideal for outdoor rooms. However, it's important to consider the certifications on the fan depending on the use. For high humidity areas, choose a UL-Listed fan for Damp Locations and for spaces that will be exposed to weather, choose a UL-Listed fan for Wet Locations. For interior use in dry spaces with minimal condensation, select a UL-Listed fan for Dry Locations. See testing listings defined on page 25.

The Perfect Fan in 5 Steps *continued...*



3 Get Your Height Right

You want to allow at least 7 feet (84 in.) from the floor to the bottom of the fan, with 8 or 9 feet being the ideal above-floor placement. For lower ceilings, consider a ceiling fan with a low profile to avoid disturbing inhabitants. Most ceiling fans come equipped with a down rod to help you adjust to the correct height.

4 Size It To Your Space

Size is really important when selecting your ceiling fan. If a fan is too large, it can overwhelm the space. On the flip side, if the fan is too small, the airflow may be inadequate for that area.

Room Size	Fan Size
(in square feet)	(in inches)
0 - 75	0 - 36
76 - 144	36 - 42
145 - 225	42 - 50
226 - 360	50 - 54
361 - 499	54 - 70
500+	70+

The Perfect Fan in 5 Steps continued...



P250102-31M-CS

5 Choose Your Features

There are many different features to choose from when browsing ceiling fans.

Scan for "The Perfect Fan in 5 Steps" with Steve Register



BLADE FINISH OPTIONS

Multiple blade finish options to coordinate with your home decor.

Example blade options for P250102-31M-CS:

- Rustic Charcoal
- Matte Black



LED

Consider an LED or Energy Star rated fixture to save energy.



LIGHT KIT

For a layered lighting effect, install a ceiling fan with a pre-installed light kit to complement your existing fixtures.

CCT TECHNOLOGY



Some fan models offer Correlated Color Temperature selection. Warmer color temperatures will lend a glow that is cozy and inviting. Cooler color temperatures can make the room look and feel fresh and bright. Choose the color temperature that best suits your space.



REVERSIBLE MOTOR

Typically, ceiling fans are used to help cool you down and keep the air flowing with a counter-clockwise blade direction. However, fans can also keep you warm when the direction of the blades is reversed. Select a fan with reversible motor for the option to circulate cool or warm air. Most ceiling fans have a small switch located either on the motor housing or the switch cup.



REMOTE CONTROL WITH FULL RANGE DIMMING

Full range dimming and hand-held remote control capabilities are available to offer an added convenience in controlling a room's environment.



BREEZE MODE ON APP

COMPATIBLE WITH ANY PROGRESS AC MOTOR

FULL RANGE DIMMING CONTROL

ON/OFF FUNCTION FOR FAN AND LIGHT KIT

CONTROL FROM YOUR POCKET

Control from Anywhere with WiFi

Easily control your fan with your smartphone, tablet, voice or hand-held remote.

Visit progresslighting.com for more details.

WiFi COMPATIBLE



P2667-31

Look for these icons:



WiFi compatible



WiFi control included

LED Light Kits

Save Money and Energy

When you select a high-quality LED fixture, you can expect a significant return on investment from an energy conservation standpoint. Here are some of the energy saving benefits of LEDs from Progress Lighting:

Vernal
P250059-129-30

Features



LED sources use at least 75% less energy than incandescent lighting, allowing homeowners to save on operating expenses.



LEDs last 35 to 50 times longer than incandescent sources and approximately 2 to 5 times longer than fluorescent lighting. Meaning, less bulb maintenance!



LEDs do not use power when they are turned off. According to MSN Real Estate, LED lights can result in an annual bill as low as \$26.



LEDs do not produce heat like traditional sources, reducing cooling costs. Traditional incandescent bulbs waste 98% of the energy they consume on heat.



Find Your Rating

Indoor, Damp and Wet Location

All ceiling fans sold in the United States have been tested and rated by either Underwriters Laboratories (UL) or Intertek (ETL), each an independent product safety certification organization. It's important to pay attention to the rated listing when purchasing a ceiling fan as it will tell you what location the fan was designed for. There are three location options: dry, damp and wet.



Dry Location

Please note indoor only (dry location) fans should only be used indoors. Even if an outdoor area or screened-in porch is covered, the motor and the blades can be affected when exposed to humidity. You can, however, “bring the outdoors inside” – as using outdoor ceiling fans are perfectly acceptable to use in interior spaces.

Damp Location

If you are selecting a ceiling fan for a space that is outdoors and under a roof, i.e. any covered porches; you should select either a damp rated or wet listed fan. Damp location fans may also be used indoors.



Wet Location

If the fan comes directly into contact with water, you'll need to ensure that the ceiling fan has a “wet” listing. Ceiling fans designed for damp or wet locations feature elements, such as moisture-resistant motors and all weather blades. Wet location fans may also be used indoors.



Featuring Bexar and Design Series™ Cordova

Indoor Ceiling Fans

Vernal

031 Black 129 Architectural Bronze 152 Painted Nickel

Vernal refreshes a room’s decor with elegant curves and an expansive 60-inch, five- blade span for the ultimate in design-savvy comfort. Vernal includes WiFi smart control: once installed, Vernal can be controlled by a voice assistant, tablet or smart phone. Finished in Koa Woodgrain, Matte Black or Painted Nickel, Vernal is designed to complement New Traditional and Transitional interiors.



P250059-129-30

Vernal

P250059-031-30 Black
60" dia., 13.63" ht.
Shown with Matte Black blades

Matte Black



P250059-129-30 Architectural Bronze
60" dia., 13.63" ht.
Shown with Koa Woodgrain blades

Koa Woodgrain



P250059-152-30 Painted Nickel
60" dia., 13.63" ht.
Shown with Painted Nickel blades

Painted Nickel



ENERGY INFORMATION

Airflow 6,810 cubic feet per minute
Electricity Use 34 watts (excludes lights)
DOE Weighted CFM/W 242 CFM/W



Full Function Remote Control Included
Six-speed fan operation
Full-range dimming for light
Reverse direction control

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- ABS blades
- Opal shatterproof shade
- Damp Rated
- WiFi enabled
- Remote control with batteries included

LAMPING

18w LED Module, 3000K, 90 CRI,
1600 source lumens, dimmable.

All fixtures:



Ryne

028 Satin White 031 Black 129 Architectural Bronze

The 52-inch Ryne fan is modern in appeal, with beautifully flowing blades that join in the middle to create a minimalistic housing. Ryne is smart control adaptable with the P2673 WiFi Module: once installed, Ryne can be controlled by a voice assistant, tablet or smart phone. Ryne's aerodynamic design and Koa Woodgrain, Matte White or Matte Black finish perfectly suits New Traditional and Transitional interiors.



P250060-031-30

Ryne

P250060-028-30 Satin White
52" dia., 13.5" ht.
Shown with Satin White blades

 Satin White




P250060-031-30 Black
52" dia., 13.5" ht.
Shown with Matte Black blades

 Matte Black



P250060-129-30 Architectural Bronze
52" dia., 13.5" ht.
Shown with Koa Woodgrain blades

 Koa Woodgrain



ENERGY INFORMATION

Airflow 5,802 cubic feet per minute
Electricity Use 33 watts (excludes lights)
DOE Weighted CFM/W 204 CFM/W



Full Function Remote Control Included
Six-speed fan operation
Full-range dimming for light
Reverse direction control

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- ABS blades
- Opal shatterproof shade
- Damp Rated
- Remote control with batteries included
- Add a P2673-01 WiFi module to convert to a smart fan

LAMPING

18w LED Module, 3000K, 90 CRI, 1600 source lumens, dimmable.

All fixtures:



Willacy

031 Black 152 Painted Nickel

Willacy is striking in design, inspired by flowing ribbons that swirl around a gleaming center hub to create a gentral breeze. Willacy includes WiFi smart control: once installed, the fan can be controlled by a voice assistant, tablet or smart phone. Willacy features all weather hand finished ABS blades making it ideal for indoor or outdoor use.



P250063-152

Willacy

P250063-031 Black
48" dia., 14.5" ht.
Shown with Matte Black blades

Matte Black



P250063-152 Painted Nickel
48" dia., 14.5" ht.
Shown with Painted Nickel blades

Painted Nickel



ENERGY INFORMATION

Airflow 4,544 cubic feet per minute
Electricity Use 14 watts (excludes lights)
DOE Weighted CFM/W 318 CFM/W

Full Function Remote Control Included
Six-speed fan operation
Reverse direction control



FEATURES

- Limited Lifetime Warranty
- DC Motor
- ABS blades
- Damp Rated
- WiFi enabled
- Remote control with batteries included

All fixtures:



Search the product number on [progresslighting.com](https://www.progresslighting.com) for full product details

Bastrop

009 Brushed Nickel 31M Matte Black 143 Graphite

Introduce a rustic industrial style to your home with Bastrop, whose updated vintage design comes from its wood tone and metal cage frame construction. Curved fan blades feature an interesting bend that heightens the fan’s industrial aesthetic. A damp location rating makes Bastrop ideal for both indoor and covered outdoor use. An included remote control operates the fan.



P250096-009

Bastrop

P250096-009 Brushed Nickel
26" dia., 13.6" ht.
Shown with Grey Weathered Wood blades

 Grey Weathered Wood



P250096-31M Matte Black
26" dia., 13.6" ht.
Shown with Rustic Charcoal blades

 Rustic Charcoal




P250096-143 Graphite
26" dia., 13.6" ht.
Shown with Aged Oak blades

 Aged Oak



ENERGY INFORMATION	
Airflow	1474 cubic feet per minute
Electricity Use	11 watts
DOE Weighted CFM/W	100 CFM/W



Three-speed Remote Control Included
Three-speed fan operation

- FEATURES**
- Limited Lifetime warranty
 - AC Motor
 - ABS blades
 - Damp Rated
 - Remote control with batteries included
 - Remote control may be replaced with P2630-30 wall control
 - Add the P2667-31 WiFi remote control

All fixtures:

Search the product number on [progresslighting.com](https://www.progresslighting.com) for full product details

Belva



P250068-31M-WB

The Belva ceiling fan offers an organic global feel and coastal charm. A lattice-like design graces the natural wicker frame, and a lovely Cottage White and Mocha finishes gives charm and depth. A trio of fan blades and vintage-style bulbs within the frame’s woven structure moves air comfortably while casting a beautifully diffused glow.

Belva

P250068-31M-WB Matte Black
25.25" dia., 17.87" ht.
Shown with Mocha colored wicker



P250068-151-WB CottageWhite
25.25" dia., 17.87" ht.
Shown with Whitewashed wicker



ENERGY INFORMATION

Airflow	1,125 cubic feet per minute
Electricity Use	37 watts (excludes lights)
DOE Weighted CFM/W	37 CFM/W



Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Damp Rated
- Remote control with batteries included
- Add a P2630-30 or P2613-30 wall control
- Add the P2667-31 WiFi remote control

LAMPING

Four medium base 2200K
5.5w vintage LED lamps included.
500 lumens/lamp, 80 CRI, dimmable.
5.5w LED max/socket.


All fixtures:



Gulliver

Three circular bands wrap together to create an open design. Non-metallic fan blades enclosed within a stylish cage design gives the rustic charm of a pendant combined with the functionality of a ceiling fan. Dual toned frame color combinations of Galvanized with antique white accents or Graphite with weathered gray accents. A hand painted wood grained texture complements rustic and modern farmhouse home decor, as well as urban industrial and coastal interior settings.

141 Galvanized Finish 143 Graphite



Gulliver

P250012-141-22 Galvanized Finish
23.5" dia., 18.12" ht.
Shown with Antique White Wood

 Antique White Wood



P250012-143-22 Graphite
23.5" dia., 18.12" ht.
Shown with Gray Wood

 Gray Wood



ENERGY INFORMATION

Airflow	1,297 cubic feet per minute
Electricity Use	39 watts (excludes lights)
Airflow Efficiency	33 cubic feet per minute per watt



Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-18.5°)
- AC Motor
- Reversible Motor
- Rust-proof non-metallic blades
- Damp Rated
- Remote control with batteries included
- Add the P2667-31 WiFi remote control

LAMPING

Three medium base 2200K
5.5w vintage LED lamps included.
500 lumens/ lamp, 80 CRI, dimmable.
5.5w LED max/socket.

All fixtures:



Briarwood

- 020 Antique Bronze
- 31M Matte Black
- 141 Galvanized Finish
- 143 Graphite

The Briarwood ceiling fan brings vintage farmhouse detailing into the present day with a classic cross-brace pattern enclosing vintage-style bulbs and a trio of fan blades within its airy, open-frame design. Faux-painted wood accentuates Briarwood's simple geometric form, adding the perfect touch of country character to a variety of room settings.



P250067-020-WB

Briarwood

P250067-020-WB Antique Bronze
22" sq., 22" sq., 17" ht.
Shown with Rich Oak faux wood

Antique Bronze




P250067-31M-WB Matte Black
22" sq., 22" sq., 17" ht.
Shown with Ceruse Black Oak faux wood

Matte Black



P250067-141-WB Galvanized Finish
22" sq., 22" sq., 17" ht.
Shown with Bleached Oak faux wood

Galvanized Finish



P250067-143-WB Graphite
22" sq., 22" sq., 17" ht.
Shown with White Washed faux wood

Graphite



ENERGY INFORMATION

Airflow 1,145 cubic feet per minute
Electricity Use 31 watts (excludes lights)
DOE Weighted CFM/W 37 CFM/W



Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Damp Rated
- Remote control with batteries included
- Add a P2630-30 or P2613-30 wall control or P2662-01 hand-held remote control
- Add the P2667-31 WiFi remote control

LAMPING

Four medium base 2200K
5.5w vintage LED lamps included.
500 lumens/lamp, 80 CRI, dimmable.
5.5w LED max/socket.

All fixtures:



Sanford

09 Brushed Nickel 129 Architectural Bronze



P2594-12930K

Sanford delivers ultra powerful air movement and energy efficient illumination packaged in a modern design. Ideal for both interior and outdoor settings, this "fandelier" adds a contemporary style to porches, foyers, bath and vanity areas providing a wide range of applications. Sanford includes an integrated 23W LED module, offering both form and function with energy and cost-savings benefits. A three-speed remote control is included.

Sanford

P2594-0930K Brushed Nickel
22.87" dia., 17.75" ht.



P2594-12930K Architectural Bronze
22.87" dia., 17.75" ht.



ENERGY INFORMATION

Airflow	1,008 cubic feet per minute
Electricity Use	37 watts (excludes lights)
DOE Weighted CFM/W	27 CFM/W



Three-speed Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-18.5°)
- AC Motor
- Metal blades
- Damp Rated
- Remote control with batteries included
- Remote control may be replaced with P2630-30 wall control
- Add the P2667-31 WiFi remote control

LAMPING

26w LED module, 3000K, 90 CRI,
2638 source lumens, dimmable.


All fixtures:



52" Springer

- 31M Matte Black
- 081 Antique Nickel
- 129 Architectural Bronze


The sweeping style of the Springer fan is expressed in a 52" size that is ideal for boosting airflow in smaller spaces. The 12-blade ceiling fan has a rustic flair inspired by the form and function of a windmill. Springer is WiFi ready offering more versatility in control options. It is a DC motor fan and can accept the Springer light kit (sold separately). Springer offers the perfect look for Farmhouse, Industrial and Transitional settings.



P250065-081

52" Springer

P250065-31M Matte Black
52" dia., 17.37" ht.
Shown with Rustic Charcoal blades

 Rustic Charcoal




P250065-081 Antique Nickel
52" dia., 17.37" ht.
Shown with White Barnwood blades

 White Barnwood



P250065-129 Architectural Bronze
52" dia., 17.37" ht.
Shown with Distressed Walnut blades

 Distressed Walnut



ENERGY INFORMATION

Airflow	6,296 cubic feet per minute
Electricity Use	30 watts (excludes lights)
DOE Weighted CFM/W	245 CFM/W



Full Function Remote Control Included
Six-speed fan operation
Reverse direction control

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-22°)
- DC Motor
- Plywood blades
- Remote control with batteries included
- Add a P2673-01 WiFi module to convert to a smart fan

All fixtures:    

LAMPING

P260000-31M-WB Matte Black
P260000-081-WB Antique Nickel
P260000-129-WB Architectural Bronze
11.87" dia., 7.5" ht.
2 medium base, 7w max.



Search the product number on progresslighting.com for full product details

60" Springer

- 31M Matte Black
- 081 Antique Nickel
- 129 Architectural Bronze

The sweeping style of the Springer fan is expressed in a 60" size that is ideal for boosting airflow in smaller spaces. The 12-blade ceiling fan has a rustic flair inspired by the form and function of a windmill. Springer is WiFi ready offering more versatility in control options. It is a DC motor fan and can accept the Springer light kit (sold separately). Springer offers the perfect look for Farmhouse, Industrial and Transitional settings.



P250000-31M


60" Springer

P250000-31M Matte Black
60" dia., 17.37" ht.
Shown with Rustic Charcoal blades

 Rustic Charcoal




P250000-081 Antique Nickel
60" dia., 17.37" ht.
Shown with White Barnwood blades

 White Barnwood



P250000-129 Architectural Bronze
60" dia., 17.37" ht.
Shown with Distressed Walnut blades

 Distressed Walnut



ENERGY INFORMATION

Airflow 6,377 cubic feet per minute
Electricity Use 33 watts (excludes lights)
DOE Weighted CFM/W 206 CFM/W



Full Function Remote Control Included
Six-speed fan operation
Reverse direction control

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-22°)
- DC Motor
- Plywood blades
- Remote control with batteries included
- Add a P2673-01 WiFi module to convert to a smart fan

All fixtures:     

ALSO IN: LIGHT KITS

P260000-31M-WB Matte Black
P260000-081-WB Antique Nickel
P260000-129-WB Architectural Bronze
11.87" dia., 7.5" ht.
2 medium base, 7w max.



Kaysville

Beautiful long bent blades appear to be held only by a simple metal band in Kaysville, offering a modern industrial style. Kaysville pairs the beauty of the blades with a strong, all-weather ABS material to prevent warping.

081 Antique Nickel 143 Graphite



P250003-081-30

Kaysville

P250003-081-30 Antique Nickel
56" dia., 17.25" ht.
Shown with Chestnut blades



Chestnut



P250003-143-30 Graphite
56" dia., 17.25" ht.
Shown with Gray Weathered Wood blades



Gray Weathered Wood



ENERGY INFORMATION

Airflow 9,650 cubic feet per minute
Electricity Use 31 watts (excludes lights)
DOE Weighted CFM/W 361 CFM/W



Full Function Remote Control Included
Six-speed fan operation
Full-range dimming for light
Reverse direction control

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- ABS blades
- White opal glass shade
- Damp Rated
- Remote control with batteries included

LAMPING

24w LED Module, 3000K, 90 CRI,
2000 source lumens, dimmable.

All fixtures:



Freestone

009 Brushed Nickel 020 Antique Bronze 31M Matte Black

A wire-formed cage adds a touch of casual style to Freestone. Five reversible plywood fans offer a customizable option to complement the room's decor style. The light kit features a white opal shatterproof shade for a soft glow and includes medium-based LED lamps for energy efficiency. Individual pull chains operate both the fan and the light.



P250095-009-WB

Freestone

P250095-009-WB Brushed Nickel
52" dia., 15" ht.
Shown with Silver blades

- Silver
- Gray Weathered Wood



P250095-020-WB Antique Bronze
52" dia., 15" ht.
Shown with Walnut blades

- Walnut
- Distressed Walnut



P250095-31M-WB Matte Black
52" dia., 15" ht.
Shown with Matte Black blades

- Matte Black
- Gray Weathered Wood



ENERGY INFORMATION

Airflow	3236 cubic feet per minute
Electricity Use	36 watts (excludes lights)
DOE Weighted CFM/W	90 CFM/W

FEATURES

- Limited Lifetime Warranty
- AC Motor
- Reversible plywood blades
- White opal shatterproof shade
- 3 Speed pull chain switches
- Add the P2667-31 WiFi remote control

LAMPING

2 medium base, 3000K, 6w LED lamps included, 500 lumens/lamp, dimmable.

All fixtures:



Mesilla

020 Antique Bronze 081 Antique Nickel 182 Flat Black

Mesilla has an organic style that delivers natural grace and beauty to indoor and outdoor rooms. Its flower-like silhouette comes from five hand-finished ABS blades that gently wrap around the housing, with a single metal band that seems to be holding the blades on, creating a beautiful focal point. Mesilla has a DC motor for the highest efficacy and whisper-quiet operation. A full-function remote control with a battery is included.



P250073-081

Mesilla

P250073-020 Antique Bronze
60" dia., 14.25" ht.
Shown with Antique Wood blades

Antique Wood



P250073-081 Antique Nickel
60" dia., 14.25" ht.
Shown with White Barnwood blades

White Barnwood



P250073-182 Flat Black
60" dia., 14.25" ht.
Shown with Gray Weathered Wood blades

Gray Weathered Wood



ENERGY INFORMATION

Airflow 6,966 cubic feet per minute
Electricity Use 38 watts (excludes lights)
DOE Weighted CFM/W 217 CFM/W



Full Function Remote Control Included
Six-speed fan operation
Full-range dimming for light
Reverse direction control

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- ABS blades
- Damp Rated
- Remote control with batteries included

All fixtures:



Alleron

081 Antique Nickel 182 Flat Black


Reminiscent of aviation days gone by, Alleron takes its styling cues from a set of airplane propeller blades. The hand-finished ABS blades paired with a sleek metal ceiling canopy and light kit add a modern industrial flair to indoor and covered outdoor settings.



P250009-182-30


Alleron

P250009-081-30 Antique Nickel
56" dia., 16" ht.
Shown with Gray Weathered Wood blades

 Gray Weathered Wood



P250009-182-30 Flat Black
56" dia., 16" ht.
Shown with Antique Black blades

 Antique Black



ENERGY INFORMATION

Airflow	7,801 cubic feet per minute
Electricity Use	20 watts (excludes lights)
DOE Weighted CFM/W	423 CFM/W



Full Function Remote Control Included
Six-speed fan operation
Full-range dimming for light
Reverse direction control

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- ABS blades
- White opal glass shade
- Damp Rated
- Remote control with batteries included

LAMPING

24w LED Module, 3000K, 90 CRI,
2000 source lumens, dimmable.

All fixtures:



Byars

Deep functionality meets modern transitional styling in the Byars 54-in. Ceiling Fan. A clean-lined motor housing featuring a DC motor descends from the down rod, holding five reversible plywood blades with softly squared edges for optimal airflow. Byars offers both soft uplight and even downlight illumination with Dual-Lens combination integrated LED light sources that can be controlled individually with the 6 speed, full-function remote control with full range dimming.

009 Brushed Nickel 31M Matte Black



P250061-31M-30

Byars

P250061-009-30 Brushed Nickel
54" dia., 16" ht.
Shown with American Walnut blades

- American Walnut
- Chesnut



P250061-31M-30 Matte Black
54" dia., 16" ht.
Shown with Black blades

- Black
- Antique Black



ENERGY INFORMATION

Airflow	6,477 cubic feet per minute
Electricity Use	30 watts (excludes lights)
DOE Weighted CFM/W	250 CFM/W



Full Function Remote Control Included
Six-speed fan operation
Full-range dimming for light
Reverse direction control

FEATURES

- Limited Lifetime Warranty
- DC Motor
- Reversible plywood blades
- Up and down light
- Double lens shades
- Remote control with batteries included

LAMPING

Downlight - 18w LED Module, 3000K, 90 CRI, 1400 source lumens, dimmable.
Uplight - 12w LED Module, 3000K, 90 CRI, 1100 source lumens, dimmable.

All fixtures:



Gillen

31M Matte Black 163 Vintage Brass 171 Blistered Iron

Retro styling brings a nostalgic look to the Gillen 56-in Ceiling Fan. A small motor housing allows its vintage design to take center stage, showcasing an aged metal patina finish and clear glass globe shade. A DC motor controlled by a 6-speed full-function remote with full range dimming compatibility circulates the air as desired. Add charm and warmth with 1 – 7 watt, vintage-style LED Bulb (included).



P250075-171-WB

Gillen

P250075-31M-WB Matte Black
56" dia., 21.65" ht.
Shown with Rustic Charcoal blades

Rustic Charcoal



P250075-163-WB Vintage Brass
56" dia., 21.65" ht.
Shown with Chesnut blades

Chesnut



P250075-171-WB Blistered Iron
56" dia., 21.65" ht.
Shown with Grey Weathered Wood blades

Grey Weathered Wood



ENERGY INFORMATION

Airflow 6,500 cubic feet per minute
Electricity Use 35 watts (excludes lights)
DOE Weighted CFM/W 198 CFM/W



Full Function Remote Control Included
Six-speed fan operation
Reverse direction control

FEATURES

- Limited Lifetime Warranty
- DC Motor
- Plywood blades
- Clear glass lens shade
- Damp Rated
- Remote control with batteries included

LAMPING

7w LED lamp included, 2700K, 90 CRI, 600 source lumens, dimmable.

All fixtures:



Spicer

- 009 Brushed Nickel
- 020 Antique Bronze
- 31M Matte Black


Sleek lines and solid metal housing offer an urban industrial edge to Spicer. Three curved, hand-finished ABS blades rotate around a slim, smooth fan body, giving sophisticated style to indoor and outdoor rooms. Spicer has a DC motor for the highest efficacy and whisper-quiet operation. A full-function remote control with a battery is included.



P250071-020


Spicer

P250071-009 Brushed Nickel
54" dia., 11.5" ht.
Shown with Gray Weathered Wood blades

 Gray Weathered Wood



P250071-020 Antique Bronze
54" dia., 11.5" ht.
Shown with Antique Wood blades

 Antique Wood



P250071-31M Matte Black
54" dia., 11.5" ht.
Shown with Antique Black blades

 Antique Black



ENERGY INFORMATION

Airflow	4,521 cubic feet per minute
Electricity Use	35 watts (excludes lights)
DOE Weighted CFM/W	158 CFM/W



Full Function Remote Control Included
Six-speed fan operation
Reverse direction control

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- ABS blades
- Damp Rated
- Remote control with batteries included

All fixtures:



Search the product number on progresslighting.com for full product details

Ellwood

09 Brushed Nickel 20 Antique Bronze

A picture of modern design, the functional minimalism of the Ellwood 68" ceiling fan is a product of advanced design. Five long and graceful blades made of carved wood move air with remarkable efficiency. Ellwood features a dual mount system and is compatible with universal light kits. A full function remote control is included.



P2546-09

Ellwood

P2546-09 Brushed Nickel
68" dia., 15.7" ht.
Shown with Driftwood blades

Driftwood



P2546-20 Antique Bronze
68" dia., 15.7" ht.
Shown with Walnut blades

Walnut



ENERGY INFORMATION

Airflow	7,587 cubic feet per minute
Electricity Use	90 watts (excludes lights)
DOE Weighted CFM/W	92 CFM/W



Full Function Remote Control Included
Three-speed fan operation
Reverse direction control

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Patented carved wood blades
- Compatible with universal light kits
- Remote control with batteries included
- Remote control may be replaced with P2631-30 wall control
- Add the P2667-31 WiFi remote control

All fixtures:



Caleb

- 09 Brushed Nickel
- 20 Antique Bronze
- 31 Black


Beautiful and expansive in design, the 68" Caleb ceiling fan is ideal for use in large spaces. Bent carved wood blades are paired with either Brushed Nickel or Antique Bronze finishes. Caleb features a dual mount system and is compatible with universal light kits. A full function remote control is included.



P2560-20AW

Caleb

P2560-09WW Brushed Nickel
68" dia., 18" ht.
Shown with Gray Weathered Wood blades

 Gray Weathered Wood



P2560-20 Antique Bronze
68" dia., 18" ht.
Shown with Walnut blades

 Walnut



P2560-20AW Antique Bronze
68" dia., 18" ht.
Shown with Antique Wood blades

 Antique Wood



ENERGY INFORMATION

Airflow	7,045 cubic feet per minute
Electricity Use	86 watts (excludes lights)
DOE Weighted CFM/W	91 CFM/W



Full Function Remote Control Included
Three-speed fan operation
Reverse direction control

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Patented bent carved wood blades
- Compatible with universal light kits
- Remote control with batteries included
- Remote control may be replaced with P2631-30 wall control
- Add the P2667-31 WiFi remote control

All fixtures:



Huff

The hassles and headaches of the day fade away under the relaxing airflow created by the Huff Collection. Six expansive aluminum blades with decorative winglets stretch out from a dual mount center. Select a Brushed Nickel, Matte White, or Matte Black finish all with their own complementary highlights to create a perfect design for your modern or transitional space.

- 009 Brushed Nickel
- 028 Satin White
- 031 Black



P250030-009

Huff

P250030-009 Brushed Nickel
96" dia., 15.44" ht.
Shown with Brushed Nickel blades

Brushed Nickel



P250030-028 Satin White
96" dia., 15.44" ht.
Shown with Satin White blades

Satin White



P250030-031 Black
96" dia., 15.44" ht.
Shown with Black blades

Black



ENERGY INFORMATION

Airflow 14,482 cubic feet per minute
Electricity Use 49 watts (excludes lights)
DOE Weighted CFM/W 344 CFM/W



Full Function Remote Control Included
Six-speed fan operation
Reverse direction control

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- Aluminum blades
- Damp Rated
- Compatible with universal light kit
- Remote control with batteries included

All fixtures:



Search the product number on [progresslighting.com](https://www.progresslighting.com) for full product details

Vast

- 09 Brushed Nickel
- 20 Antique Bronze
- 30 White
- 31 Black

Beautiful and expansive in design, the 72" ceiling fan is ideal for use in large areas and outdoor covered areas for maximum cooling. A white opal shade complements a variety of finish options, including Brushed Nickel with chrome accents, Antique Bronze, White with chrome accents or Matte Black. Vast features a dual mount system and comes with a full function remote control.



P2550-3130K

Vast

P2550-0930K Brushed Nickel
72" dia., 16.75" ht.
Shown with Brushed Nickel blades

Brushed Nickel



P2550-2030K Antique Bronze
72" dia., 16.75" ht.
Shown with Antique Bronze blades

Antique Bronze



P2550-3030K White
72" dia., 16.75" ht.
Shown with White blades

White



P2550-3130K Black
72" dia., 16.75" ht.
Shown with Black blades

Black



ENERGY INFORMATION

Airflow	8,163 cubic feet per minute
Electricity Use	35 watts (excludes lights)
DOE Weighted CFM/W	262 CFM/W



Full Function Remote Control Included
Six-speed fan operation
Full-range dimming for light
Reverse direction control

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- Aluminum blades
- White opal glass shade
- Damp Rated
- Remote control with batteries included

LAMPING

18w LED Module, 3000K, 90 CRI,
1400 source lumens, dimmable.

All fixtures:



Arlo

Unwind under the cooling breeze created by the clean, crisp blades of the Arlo collection's modern ceiling fan. A central LED light provides a perfect way to light a space without flooding the room with harsh light as six metal blades attach to the fan's center. Offered in three different finishes, Arlo is sure to create an intriguing, yet serene retreat in whatever space it calls home.

009 Brushed Nickel 031 Black



P250026-009-30

Arlo

P250026-009-30 Brushed Nickel
60" dia., 18.57" ht.
Shown with Brushed Nickel blades

Brushed Nickel



P250026-031-30 Black
60" dia., 18.57" ht.
Shown with Black blades

Black



ENERGY INFORMATION

Airflow 7,558 cubic feet per minute
Electricity Use 29 watts (excludes lights)
DOE Weighted CFM/W 282 CFM/W



Full Function Remote Control Included
Six-speed fan operation
Full-range dimming for light
Reverse direction control

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- Aluminium blades
- White opal glass shade
- Damp Rated
- Remote control with batteries included

LAMPING

24w LED Module, 3000K, 90 CRI,
2000 source lumens, dimmable.

All fixtures:



Manvel

- 020 Antique Bronze
- 31M Matte Black
- 081 Antique Nickel
- 151 Cottage White


Offering modern elegance in a sleek form, Manvel is a 60” fan rated for indoor/outdoor with a DC motor. Three hand-finished, premium construction ABS blades give Manvel a stylish look, making it an ideal centerpiece for living rooms, great rooms or an outdoor covered porch. Manvel includes a six-speed full function remote control.



P250069-081

Manvel

P250069-020 Antique Bronze
60” dia., 11.25” ht.
Shown with Dark Walnut blades



P250069-31M Matte Black
60” dia., 11.25” ht.
Shown with Rustic Charcoal blades



P250069-081 Antique Nickel
60” dia., 11.25” ht.
Shown with Antique Nickel Wood blades



P250069-151 Cottage White
60” dia., 11.25” ht.
Shown with Salt Aged Cypress blades



ENERGY INFORMATION

Airflow	6,127 cubic feet per minute
Electricity Use	20 watts
DOE Weighted CFN/W	310 CFM/W



Full Function Remote Control Included
Six-speed fan operation
Full-range dimming for light
Reverse direction control

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- Aluminum blades
- Damp Rated
- Remote control with batteries included

All fixtures:



Farris

009 Brushed Nickel 108 Oil Rubbed Bronze 143 Graphite


Farris features three solid wood carved blades to form a sleek, modern design. The 60" ceiling fan includes an integrated LED light kit that is removable to provide the option in non-illuminated applications. Available in Brushed Nickel, Oil Rubbed Bronze and Graphite finishes. A full function remote control with batteries is included, and the dual mount canopy accommodates flat or sloped ceilings.



P250002-108-30

Farris

P250002-009-30 Brushed Nickel
60" dia., 15.5" ht.
Shown with Gray Weathered Wood blades

 Gray Weathered Wood



P250002-108-30 Oil Rubbed Bronze
60" dia., 15.5" ht.
Shown with Walnut blades and light kit removed using blank plate

 Walnut



P250002-143-30 Graphite
60" dia., 15.5" ht.
Shown with Driftwood blades

 Driftwood



ENERGY INFORMATION

Airflow	7,047 cubic feet per minute
Electricity Use	32 watts (excludes lights)
DOE Weighted CFM/W	223 CFM/W



Full Function Remote Control Included
Six-speed fan operation
Full-range dimming for light
Reverse direction control

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-13°)
- DC Motor
- Carved wood blades
- Removable light kit
- White opal shatterproof shade
- Remote control with batteries included

LAMPING

18w LED Module, 3000K, 90 CRI, 1400 source lumens, dimmable.

All fixtures:



Carrollwood

With an emphasis on elegance, Carrollwood makes a statement in any room. Lustrous accent bands circle the fan body and light kit, delivering a luxurious element to the fan’s striking design. Carrollwood is offered in three tasteful finishes with complementing plywood blades. The light is an LED module covered by a shatterproof shade and is dimmable. A remote control is included for added convenience.

009 Brushed Nickel 030 White 31M Matte Black



P250074-31M-30

Carrollwood

P250074-009-30 Brushed Nickel
56" dia., 18" ht.
*Shown with American Walnut blades
and Chrome accent bands*

American Walnut
Silver



P250074-030-30 White
56" dia., 18" ht.
*Shown with Natural Cherry blades
and Vintage Gold accent bands*

Natural Cherry
Matte White



P250074-31M-30 Matte Black
56" dia., 18" ht.
*Shown with Chestnut blades
and Vintage Gold accent bands*

Chestnut
Matte Black



ENERGY INFORMATION

Airflow 6,857 cubic feet per minute
Electricity Use 42 watts (excludes lights)
DOE Weighted CFM/W 224 CFM/W



Full Function Remote Control Included
*Six-speed fan operation
Reverse direction control
Full-range dimming for light*

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- Reversible plywood blades
- White opal shatterproof shade
- Remote control with batteries included

LAMPING

18w LED Module, 3000K, 90 CRI,
1400 source lumens, dimmable.

All fixtures:



Dallam

The Dallam ceiling fan gracefully creates the impression of a flower in bloom as its six blades wrap around gently around its opal white shade. This 60-inch design is available in Silver and Chestnut with a Brushed Nickel housing or Matte Black and Rustic Charcoal with a Matte Black housing, offering a rustic presence to any space it occupies. The white opal shaded light kit is an integrated 20W LED module offering color-selectable 90 CRI illumination in a gentle 2700K, 3000K soft light or a bright 5000K light that you select from the included full-function remote control. Its DC motor is whisper-quiet, and UL damp location listed for indoor and outdoor covered areas.

009 Brushed Nickel 31M Matte Black



P250103-31M-CS

Dallam

P250103-009-CS Brushed Nickel
60" dia., 14" ht.
Shown with Silver blades

- Silver
- Dark Cherry



P250103-31M-CS Matte Black
60" dia., 14" ht.
Shown with Matte Black blades

- Walnut
- Matte Black



3-CCT
SELECTABLE

2700K

3000K

5000K

ENERGY INFORMATION

Airflow	5787 cubic feet per minute
Electricity Use	33 watts (excludes lights)
DOE Weighted CFM/W	201 CFM/W



Full Function Remote Control Included
Six-speed fan operation
Full-range dimming for light
Reverse direction control

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- Reversible plywood blades
- White opal glass shade
- Damp Rated
- Remote control with batteries included

LAMPING

20w LED Module, 2700K, 3000K, 5000K, 90 CRI, 1700 source lumens, dimmable.

All fixtures:



Tarsus

A clean, modern design and color-selectable LED technology give the Tarsus 52-inch ceiling fan high function and a distinctive style. This fan illuminates indoor contemporary spaces with 25W integrated LED light source. Choose from a gentle 2700K, 3000K soft light or a bright 5000K light on the included full-function remote control. Five reversible plywood blades are finished in a choice of Silver and Chestnut with a Brushed Nickel housing or Matte Black and Rustic Charcoal with a Matte Black housing. Its DC motor is UL rated for indoor use and operates with whisper-quiet efficiency.

009 Brushed Nickel 31M Matte Black



P250102-31M-CS

Tarsus

P250102-009-CS Brushed Nickel
52" dia., 14.75" ht.
Shown with Chestnut blades

Silver
Chestnut



P250102-31M-CS Matte Black
52" dia., 14.75" ht.
Shown with Rustic Charcoal blades

Rustic Charcoal
Matte Black



3-CCT
SELECTABLE

2700K

3000K

5000K

ENERGY INFORMATION

Airflow 4,950 cubic feet per minute
Electricity Use 60 watts (excludes lights)
DOE Weighted CFM/W 94 CFM/W



Full Function Remote Control Included
Six-speed fan operation
Full-range dimming for light
Reverse direction control

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- Reversible plywood blades
- White opal glass shade
- Remote control with batteries included

LAMPING

25w LED Module, 90 CRI + 10w Linear LED Module, 80 CRI, 2700K, 3000K, 5000K, 2000 source lumens, dimmable.

All fixtures:



Gaze

- 09 Brushed Nickel
- 15 Polished Chrome
- 20 Antique Bronze
- 31 Black



P2554-1530K

Three-blade 60" Gaze ceiling fan features an LED light source, offering both form and function with energy and cost-savings benefits. An opal white shade contains an 18W dimmable, 3000K LED module. Gaze features a dual mount system and includes a three-speed remote control with full range dimming.

Gaze

P2554-0930K Brushed Nickel
60" dia., 13.12" ht.
Shown with Silver blades

- Silver
- Cherry



P2554-1530K Polished Chrome
60" dia., 13.12" ht.
Shown with White Washed blades

- White Washed
- Cherry



P2554-2030K Antique Bronze
60" dia., 13.12" ht.
Shown with Cherry blades

- Walnut
- Cherry



P2554-3130K Black
60" dia., 13.12" ht.
Shown with Matte Black blades

- Matte Black
- Distressed Ebony



ENERGY INFORMATION

Airflow	5,902 cubic feet per minute
Electricity Use	75 watts (excludes lights)
DOE Weighted CFM/W	87 CFM/W



Three-speed Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Reversible plywood blades
- White shatterproof lens
- Remote control with batteries included
- Remote control may be replaced with P2630-30 wall control
- Add the P2667-31 WiFi remote control

LAMPING

18w LED Module, 3000K, 90 CRI, 1400 source lumens, dimmable.


All fixtures:



Spades

- 09 Brushed Nickel
- 15 Polished Chrome
- 143 Graphite

The 56" Spades ceiling fan features a sleek contemporary two-blade design that is finished in Brushed Nickel, polished chrome or Graphite options. Spades features a dual mount system, an energy saving DC motor and ABS composite blades. A full function remote control is included.



Spades


P2570-09 Brushed Nickel
56" dia., 18.12" ht.
Shown with Silver blades



P2570-15 Polished Chrome
56" dia., 18.12" ht.
Shown with Black blades



P2570-143 Graphite
56" dia., 18.12" ht.
Shown with Graphite blades



ENERGY INFORMATION

Airflow	6,746 cubic feet per minute
Electricity Use	32 watts (excludes lights)
DOE Weighted CFM/W	215 CFM/W



Full Function Remote Control Included
Six-speed fan operation
Reverse direction control


FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-17°)
- Close-to-ceiling installation
- DC Motor
- Non-reversible ABS blades
- Remote control with batteries included

All fixtures:



INSTALLATION



Oriole

- 09 Brushed Nickel
- 31 Black
- 129 Architectural Bronze

This 60" Oriole ceiling fan is the perfect addition to interior garages, industrial shops or commercial buildings to distribute the right amount of air and keep the space cool and comfortable. Oriole contains an integrated 18W LED module, with an optional finishing cap offering the user the choice to install with or without the light kit. A remote control is included to adjust speed and turn on/off the light or fan. A blank plate comes standard.



P2592-12930K

Oriole

P2592-0930K Brushed Nickel
60" dia., 14.5" ht.
Shown with Silver blades



Silver



P2592-3130K Black
60" dia., 14.5" ht.
Shown with Black blades and light kit removed using blank plate



Black



P2592-12930K Architectural Bronze
60" dia., 14.5" ht.
Shown with Architectural Bronze blades



Architectural Bronze



ENERGY INFORMATION

Airflow	6,171 cubic feet per minute
Electricity Use	51 watts (excludes lights)
DOE Weighted CFM/W	132 CFM/W



Three-speed Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-18.5°)
- AC Motor
- ABS blades
- White opal glass shade
- Remote control with batteries included
- Remote control may be replaced with P2630-30 wall control
- Add the P2667-31 WiFi remote control

LAMPING

18w LED Module, 3000K, 90 CRI, 1400 source lumens, dimmable.

All fixtures:



Bedwin

Recall charming, rustic lattice work with the Bedwin Collection's farmhouse-inspired ceiling fan. With three finishes to pick from and four rough hewn plywood blades circling a handsome dual mount canopy, this ceiling fan is sure to help transform any living space into a cool paradise of relaxation.

081 Antique Nickel 143 Graphite




P250024-081

Bedwin

P250024-081 Antique Nickel
56" dia., 15.4055" ht.
Shown with Driftwood blades

- Driftwood
- Classic Walnut



P250024-143 Graphite
56" dia., 15.4055" ht.
Shown with Graphite blades

- Graphite
- Gray Weathered Wood



ENERGY INFORMATION

Airflow 6,044 cubic feet per minute
Electricity Use 34 watts (excludes lights)
DOE Weighted CFM/W 192 CFM/W



Full Function Remote Control Included
Six-speed fan operation
Reverse direction control

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- Reversible plywood blades
- Compatible with universal light kits
- Remote control with batteries included

All fixtures:



Search the product number on progresslighting.com for full product details

Glandon

71 Gilded Iron 81 Antique Nickel



Glandon offers a sophisticated design that is ideal for settings requiring a touch of modern flair. Six reversible blades in a walnut/driftwood faux wood finish are strapped by a sleek Antique Nickel metal bar for an unexpected industrial detail. The 60" Glandon ceiling fan features a 17w LED module (3000K color temperature) with a shatterproof white opal shade and a dual mount system. Full range dimming and remote control is included.



P2586-8130K



Glandon

P2586-7130K Gilded Iron
60" dia., 17.12" ht.
Shown with Toasted Oak blades

-  Toasted Oak
-  Driftwood




P2586-8130K Antique Nickel
60" dia., 17.12" ht.
Shown with Classic Walnut blades

-  Classic Walnut
-  Driftwood



ENERGY INFORMATION

Airflow	6,036 cubic feet per minute
Electricity Use	84 watts (excludes lights)
DOE Weighted CFM/W	96 CFM/W



FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Reversible plywood blades
- White opal glass shade
- Remote control with batteries included
- Add the P2667-31 WIFI remote control

LAMPING

17w LED Module, 3000K, 90 CRI, 1400 source lumens, dimmable.



Greer

This five-blade 54" Greer ceiling fan complements either industrial or farmhouse decor. It comes with a wire meshed shade light kit that uses two vintage LED lamps (included). Remote control is also included. Greer can be hung on a flat or sloped ceiling due to its dual mount system.




P2584-81

71 Gilded Iron

Greer

P2584-71 Gilded Iron
54" dia., 20" ht.
Shown with Toasted Oak blades and Driftwood blades

 Toasted Oak



 Driftwood



ENERGY INFORMATION

Airflow	4,794 cubic feet per minute
Electricity Use	65 watts (excludes lights)
DOE Weighted CFM/W	82 CFM/W



Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-45°)
- AC Motor
- Reversible plywood blades
- Wire basket shade light kit
- Remote control with batteries included
- Remote control may be replaced with P2630-30 wall control

LAMPING

Two medium base 2200K
5.5w vintage LED lamps included.
500 lumens/lamp, 80 CRI, dimmable.
6.5w LED or 60W incandescent max/socket.

All fixtures:



Claret

Claret gracefully blends old and new with an eye-catching fluted motor housing paired with long blade arms. With its unique take on a classic design, Claret will make a statement in a variety of interiors.

- 009 Brushed Nickel
- 031 Black
- 108 Oil Rubbed Bronze



P250007-108-30

Claret

P250007-009-30 Brushed Nickel
54" dia., 15.15" ht.
Shown with American Walnut blades

- American Walnut
- Matte Black



P250007-031-30 Black
54" dia., 15.15" ht.
Shown with Distressed Ebony blades

- Gray Weathered Wood
- Distressed Ebony



P250007-108-30 Oil Rubbed Bronze
54" dia., 15.15" ht.
Shown with Antique Wood blades

- Antique Wood
- Chestnut



ENERGY INFORMATION

Airflow 5,553 cubic feet per minute
Electricity Use 61 watts (excludes lights)
DOE Weighted CFM/W 106 CFM/W



Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Reversible plywood blades
- White opal glass shade
- Remote control with batteries included
- Add the P2667-31 WiFi remote control

LAMPING

18w LED Module, 3000K, 90 CRI,
1400 source lumens, dimmable.

All fixtures:



Glenfalls

Glenfalls highlights its beautiful simulated wood fan blades with bright metallic accents on the blade arms and tips to create a timeless yet modern design. Glenfalls is ideal for cooling large living areas in sophisticated style.

- 009 Brushed Nickel
- 028 Satin White
- 031 Black



P250021-028-30

Glenfalls

P250021-009-30 Brushed Nickel
56" dia., 14.87" ht.
Shown with Brushed Nickel accents



Chestnut



P250021-028-30 Satin White
56" dia., 14.87" ht.
Shown with Brushed Nickel accents



Satin White



P250021-031-30 Black
56" dia., 14.87" ht.
Shown with Brushed Nickel accents



Matte Black



ENERGY INFORMATION

Airflow	6,393 cubic feet per minute
Electricity Use	85 watts (excludes lights)
DOE Weighted CFM/W	84 CFM/W



Remote Control Included
*Three-speed fan operation
Full-range dimming for light*

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Plywood blades
- White opal glass shade
- Remote control with batteries included
- Add the P2667-31 WiFi remote control

LAMPING

24w LED Module, 3000K, 90 CRI,
2000 source lumens, dimmable.

All fixtures:



Soar

09 Brushed Nickel 30 White

With a white opal shade and a 17W dimmable LED module, the 54" Soar ceiling fan offers energy and cost-savings benefits for a variety of living spaces. The four-blade fan comes with a remote control and is available in Brushed Nickel, Antique Bronze and white finishes. LED source features a 3000K-color temperature. Soar features a dual mount system and includes a remote control with batteries.



P2542-3030K

Soar

P2542-0930K Brushed Nickel
54" dia., 14.5" ht.
Shown with Black blades

Black



P2542-3030K White
54" dia., 14.5" ht.
Shown with White blades

White



ENERGY INFORMATION

Airflow	4,814 cubic feet per minute
Electricity Use	65 watts (excludes lights)
DOE Weighted CFM/W	83 CFM/W



Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- White opal shatterproof lens
- Remote control with batteries included
- Remote control may be replaced with P2630-30 wall control
- Add the P2667-31 WiFi remote control

LAMPING

17w LED Module, 3000K, 90 CRI, 1400 source lumens, dimmable.

All fixtures:



Tompkins

Clear hammered glass shade delivers lovely textured illumination, creating a striking focal point for the Tompkins 52-inch ceiling fan. Its five reversible square plywood fan blades are held in place by a contrasting metal detail and are available in a choice of Silver and Walnut with a Brushed Nickel housing or Matte Black and Toasted Oak and a Matte Black housing. An integrated 24W LED module offers color-selectable 90 CRI illumination in a gentle 2700K, 3000K soft light or a bright 5000K light that you select from the included full-function remote control. Tompkins is UL damp location listed, making it ideal for sending cooling breezes in indoor or outdoor covered areas in coastal and modern farmhouse settings.

009 Brushed Nickel 31M Matte Black



Tompkins

P250104-009-CS Brushed Nickel
52" dia., 17" ht.
Shown with American Walnut blades

- Silver
- American Walnut



P250104-31M-CS Matte Black
52" dia., 17" ht.
Shown with Toasted Oak blades

- Toasted Oak
- Matte Black



3-CCT
SELECTABLE

2700K

3000K

5000K

ENERGY INFORMATION

Airflow	4,660 cubic feet per minute
Electricity Use	61 watts (excludes lights)
DOE Weighted CFM/W	86 CFM/W

Three-speed Remote Control Included
Three-speed fan operation
Full-range dimming for light
Three-CCT selectable

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Reversible plywood blades
- Hammered clear glass shade
- Damp Rated
- Remote control with batteries included

LAMPING

24w LED Module, 2700K, 3000K, 5000K, 90 CRI, 1900 source lumens, dimmable.

All fixtures:

JAB

Gust

- 09 Brushed Nickel
- 20 Antique Bronze
- 143 Graphite



P2582-0930K

This five-blade 54" Gust ceiling fan features a white opal glass shade that is available in a Brushed Nickel, Antique Bronze or Graphite finish. A remote control is included. Gust has a dual mount system to offer greater flexibility when installing. The 18W dimmable, 3000K LED module provides energy and cost-savings benefits to the homeowner.

Gust

P2582-0930K Brushed Nickel
54" dia., 16" ht.
Shown with Silver blades



Silver



P2582-2030K Antique Bronze
54" dia., 16" ht.
Shown with Walnut blades



Walnut



P2582-14330K Graphite
54" dia., 16" ht.
Shown with Graphite blades



Graphite



ENERGY INFORMATION

Airflow	5,242 cubic feet per minute
Electricity Use	65 watts (excludes lights)
DOE Weighted CFM/W	87 CFM/W



Three-speed Remote Control Included
*Three-speed fan operation
Full-range dimming for light*

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-18.5°)
- AC Motor
- White opal glass shade
- Remote control with batteries included
- Remote control may be replaced with P2630-30 wall control
- Add the P2667-31 WiFi remote control

LAMPING

18w LED Module, 3000K, 90 CRI, 1400 source lumens, dimmable.

All fixtures:



Billows

09 Brushed Nickel 20 Antique Bronze 80 Forged Black

With a sophisticated and traditional design, the Billows offers both form and function with two energy efficient LED lamps, featuring a 3000K color temperature. The 52" Billows ceiling fan features an LED light kit with white opal glass shade and five reversible blades. The fans are available in Brushed Nickel, Antique Bronze and Forged Black finishes. With a sophisticated and traditional design, the Billows offers both form and function with two energy efficient LED lamps, featuring a 3000K color temperature. The 52" Billows ceiling fan features an LED light kit with white opal glass shade and five reversible blades. The fans are available in Brushed Nickel, Antique Bronze and Forged Black finishes.



P2552-09

Billows

P2552-09 Brushed Nickel
52" dia., 17.5" ht.
shown with Silver blades

- White Washed
- Silver



P2552-20 Antique Bronze
52" dia., 17.5" ht.
shown with American Walnut blades

- Cherry
- American Walnut



P2552-80 Forged Black
52" dia., 17.5" ht.
shown with Toasted Oak blades

- Black
- Toasted Oak



ENERGY INFORMATION

Airflow	4,682 cubic feet per minute
Electricity Use	59 watts (excludes lights)
DOE Weighted CFM/W	92 CFM/W

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-18.5°)
- AC Motor
- Reversible plywood blades
- White opal glass shade
- Add a P2630-30 wall control or P2662-01 hand-held remote control
- Add the P2667-31 WiFi remote control

LAMPING

Two medium base 3000K 9w LED lamps included. 800 lumens/lamp, 90 CRI, dimmable (with added remote wall control). 10w LED max/socket.

All fixtures:



Fresno

09 Brushed Nickel 20 Antique Bronze 30 White

Five-blade 60" Fresno ceiling fan features an LED light source, offering both form and function with energy and cost-savings benefits. A white opal glass shade features an 18W dimmable, 3000K LED module. A remote control with full range dimming and remote control is included.



P2548-2030K

Fresno

P2548-0930K Brushed Nickel
60" dia., 17.25" ht.
shown with Silver blades

- Black
- Silver



P2548-2030K Antique Bronze
60" dia., 17.25" ht.
shown with Dark Walnut blades

- Dark Walnut
- Cherry



P2548-3030K White
60" dia., 17.25" ht.
shown with White blades

- White



ENERGY INFORMATION

Airflow	5,718 cubic feet per minute
Electricity Use	79 watts (excludes lights)
DOE Weighted CFM/W	80 CFM/W



Full Function Remote Control Included
Three-speed fan operation
Full-range dimming for light
Reverse direction control

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-17.5°)
- AC Motor
- Reversible plywood blades
- White opal glass shade
- Remote control with batteries included, receiver mounted in motor
- Remote control may be replaced with P2631-30 wall control

LAMPING

18w LED Module, 3000K, 90 CRI, 1400 source lumens, dimmable.

All fixtures:

- T20
- JAB
- Watermark icon

Tempt

163 Vintage Brass

This five-blade 52" Tempt ceiling fan features a clear, double prismatic glass shade that is available in a Polished chrome, Antique Bronze or Vintage Brass finish. A remote is included. Tempt features a dual mount system to offer greater flexibility when installing. The 17w dimmable, 3000K LED module provides energy and cost-savings benefits to the homeowner.




Shown with Chestnut blades

P2578-16330K

Tempt

P2578-16330K Vintage Brass
52" dia., 16.25" ht.
Shown with Dark Cherry blades and Chestnut blades

 Dark Cherry




 Chestnut



ENERGY INFORMATION

Airflow	4,314 cubic feet per minute
Electricity Use	63 watts (excludes lights)
DOE Weighted CFM/W	78 CFM/W



Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Reversible plywood blades
- Clear double prismatic glass shade
- Remote control with batteries included
- Remote control may be replaced with P2630-30 wall control
- Add the P2667-31 WiFi remote control

LAMPING

17w LED Module, 3000K, 90 CRI, 1400 source lumens, dimmable.

All fixtures:



Graceful

15 Polished Chrome

Refresh your living space with the crisp, clean style of the 54" Graceful fan. With a white opal glass shade and a 17W dimmable LED module, the five-blade fan comes with a remote control and is available in Brushed Nickel, polished chrome and Antique Bronze finishes. LED source offers a 3000K-color temperature, energy savings and maintenance benefits for the home.




Shown with Toasted Oak blades

P2544-0930K

Graceful

P2544-1530K Polished Chrome
54" dia., 16.9" ht.
Shown with Toasted Oak blades and Silver blades

 Toasted Oak



 Silver



ENERGY INFORMATION

Airflow	4,454 cubic feet per minute
Electricity Use	60 watts (excludes lights)
DOE Weighted CFM/W	83 CFM/W



Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Reversible plywood blades
- White opal glass shade
- Remote control with batteries included
- Remote control may be replaced with P2630-30 wall control
- Add the P2667-31 WiFi remote control

LAMPING

17w LED Module, 3000K, 90 CRI,
1400 source lumens, dimmable.

All fixtures:



Harranvale

20 Antique Bronze 30 White 143 Graphite



P2540-14330K

The 54" Harranvale features a design that incorporates mixed metal design details that is very popular in today's home decor. Featuring reversible blades and opal glass shade, fans are available in three finish options: Antique Bronze with brushed bronze accent; Graphite with brushed nickel accent; and White with brushed nickel accent. Harranvale features a dual mount system and includes a remote control with batteries.

Harranvale

P2540-2030K Antique Bronze
54" dia., 15.5" ht.
*Shown with Medium Cherry blades
and Brushed Bronze accent*

Classic Walnut
Medium Cherry



P2540-3030K White
54" dia., 15.5" ht.
*Shown with White blades
and Brushed Nickel accent*

White




P2540-14330K Graphite
54" dia., 15.5" ht.
*Shown with Graphite blades
and Brushed Nickel accent*

Graphite
American Walnut



ENERGY INFORMATION

Airflow 5,121 cubic feet per minute
Electricity Use 66 watts (excludes lights)
DOE Weighted CFM/W 87 CFM/W



Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Reversible plywood blades
- White opal glass shade
- Remote control with batteries included
- Remote control may be replaced with P2630-30 wall control
- Add the P2667-31 WiFi remote control

LAMPING

17w LED Module, 3000K, 90 CRI,
1400 source lumens, dimmable.

All fixtures:



Brazas

Fashionably detailed with bracketed trim, the Brazas 56-inch ceiling fan features six ABS fan blades and a quiet and energy-efficient DC motor to keep spaces cool in style. This fan is light kit adaptable and includes a full-function remote control with a wall bracket. Available in matte black with distressed ebony blades and brushed nickel with grey weathered wood blades and a UL damp rating, Brazas fits beautifully into transitional indoor or outdoor settings.

009 Brushed Nickel 31M Matte Black



P250100-31M

Brazas

P250100-009 Brushed Nickel
56" dia., 13" ht.
Shown with Gray Weathered Wood blades

Grey Weathered Wood



P250100-31M Matte Black
56" dia., 13" ht.
Shown with Distressed Ebony blades

Distressed Ebony



ENERGY INFORMATION

Airflow 6,621 cubic feet per minute
Electricity Use 31 watts (excludes lights)
DOE Weighted CFM/W 245 CFM/W



Full Function Remote Control Included
Six-speed fan operation
Full-range dimming for light
Reverse direction control

FEATURES

- Limited Lifetime Warranty
- DC Motor
- ABS blades
- Damp Rated
- Remote control with batteries included

All fixtures:



McLennan II

009 Brushed Nickel

This five-blade 52" Tempt ceiling fan features a clear, double prismatic glass shade that is available in a Polished chrome, Antique Bronze or Vintage Brass finish. A remote is included. Tempt features a dual mount system to offer greater flexibility when installing. The 17w dimmable, 3000K LED module provides energy and cost-savings benefits to the homeowner.



Shown with Walnut blades

P250089-020-WB

McLennan II

P250089-009-WB Brushed Nickel
52" dia., 14.31" ht.
Shown with Walnut blades and Silver blades

Walnut



Silver



ENERGY INFORMATION

Airflow 4,040 cubic feet per minute
Electricity Use 34 Watts (excludes lights)
DOE Weighted CFM/W 85 CFM/W

FEATURES

- Limited Lifetime Warranty
- AC Motor
- Reversible plywood blades
- White opal shatterproof shade
- 3 Speed pull chain switches
- Add a P2630-30 or P2613-30 wall control
- Add the P2667-31 WiFi remote control

LAMPING

2 medium base base, 3000K,
6w LED lamps included, 90 CRI,
500 lumens/lamp, dimmable.

All fixtures:



Trevina IV

152 Painted Nickel

The Trevina collection features fans with a signature three-blade design. Perfect for modern or traditional interiors, each fan includes an LED light source to help extend your day into the evening as you and your family relax in your peaceful retreat.



P250093-152-WB

Trevina IV

P250093-152-WB Painted Nickel
52" dia., 13.8125" ht.
Shown with Walnut blades and Silver blades

 Walnut



 Silver



ENERGY INFORMATION

Airflow 4085 cubic feet per minute
Electricity Use 31 watts (excludes lights)
DOE Weighted CFM/W 88 CFM/W



Wall Control Included
*Three-speed selection
and a light switch.*

FEATURES

- Limited Lifetime Warranty
- AC Motor
- Reversible plywood blades
- White opal shatterproof shade
- Wall control is included
- Add the P2667-31 WiFi remote control

LAMPING

2 medium base base, 3000K,
6w LED lamps included, 90 CRI,
500 lumens/lamp.

All fixtures:



Trevina Energy Star

The Trevina collection features fans with a signature three-blade design. Perfect for modern or traditional interiors, each fan includes an LED light source to help extend your day into the evening as you and your family relax in your peaceful retreat.

- 028 Satin White
- 31M Matte Black
- 152 Painted Nickel



P250076-028-WB

Trevina V Energy Star

P250076-028-WB Satin White
52" dia., 16.5" ht.
Shown with Natural Cherry blades

- Natural Cherry
- Matte White



P250076-31M-WB Matte Black
52" dia., 16.5" ht.
Shown with Distressed Ebony blades

- Distressed Ebony
- Matte Black



P250076-152-WB Painted Nickel
52" dia., 16.5" ht.
Shown with Black blades

- Black
- Silver



ENERGY INFORMATION

Airflow	4,364 cubic feet per minute
Electricity Use	14 watts (excludes lights)
DOE Weighted CFM/W	116 CFM/W

FEATURES

- Limited Lifetime Warranty
- AC Motor
- Reversible plywood blades
- White opal glass shade
- Add a P2663-01 remote or P2630-30 wall control
- Add the P2667-31 WiFi remote control

LAMPING

Two 9w LED Lamps, 3000K, 90 CRI, 800 source lumens, dimmable.

All fixtures:



Trevina II 44"

- 09 Brushed Nickel
- 28 Satin White
- 31 Black


P2555-0930K Brushed Nickel
44" dia., 15.62" ht.
Shown with Silver blades



P2555-2830K Satin White
44" dia., 15.62" ht.
Shown with White blades



P2555-3130K Black
44" dia., 15.62" ht.
Shown with Distressed Ebony blades



BLANK PLATE
P2668-09 Brushed Nickel
P2668-28 Satin White
P2668-31 Black
8" dia., 1.6" ht.



ENERGY INFORMATION

Airflow 4306 cubic feet per minute
Electricity Use 42 watts (excludes lights)
DOE Weighted CFM/W 122 CFM/W



Wall Control Included
Four-speed fan operation
Full-range dimming for light
Includes switch plate cover

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Reversible MDF blades
- White opal glass shade
- Compatible with remote or hardwired wall controls (P2630, P2661-01, P2662-01, P2663-01, P2665 (sold separately)

LAMPING

18w LED Module, 3000K, 90 CRI,
1400 source lumens, dimmable.

All fixtures:




Trevina II 52"

- 129 Architectural Bronze
- 152 Painted Nickel

P2553-129WB Architectural Bronze
52" dia., 15.75" ht.
Shown with Medium Cherry blades



P2553-152WB Painted Nickel
52" dia., 15.75" ht.
Shown with Black blades



ENERGY INFORMATION

Airflow 5,296 cubic feet per minute
Electricity Use 56 watts (excludes lights)
DOE Weighted CFM/W 112 CFM/W

FEATURES

- Limited Lifetime Warranty (LED model)
- Dual Mount (flat or sloped ceiling)
- AC Motor
- Close-to-ceiling installation
- Reversible plywood blades
- White opal glass shade
- No wall control included. Add a wall or remote control to adjust fan speed and light kit function
- Compatible with remote control or hardwired wall controls (P2618-01, P2630, P2662-01, sold separately)
- Add the P2667-31 WiFi remote control


LAMPING

Two medium base 3000K
9.5w LED lamps included.
800 lumens/lamp, 80 CRI,
dimmable. 60w max/socket.

All fixtures:



INSTALLATION



Trevina II 52" LED

- 09 Brushed Nickel
- 20 Antique Bronze
- 30 White

P2556-0930K Brushed Nickel
52" dia., 15.75" ht.
Shown with Silver blades



Silver



P2556-2030K Antique Bronze
52" dia., 15.75" ht.
Shown with Medium Cherry blades



Medium Cherry



Classic Walnut



P2556-3030K White
52" dia., 15.75" ht.
Shown with White blades



White



Natural Cherry



ENERGY INFORMATION

Airflow 4,916 cubic feet per minute
Electricity Use 62 watts (excludes lights)
DOE Weighted CFM/W 89 CFM/W



Wall Control Included
Four-speed fan operation
Full-range dimming for light
Includes switch plate cover

FEATURES

- Limited Lifetime Warranty (LED model)
- Dual Mount (flat or sloped ceiling-30°)
- Close-to-ceiling installation
- AC Motor
- Reversible plywood blades
- White opal glass shade


LAMPING

17w LED Module, 3000K, 90 CRI, 1400 source lumens, dimmable.

All fixtures:



INSTALLATION



Signature Plus II

- 09 Brushed Nickel
- 20 Antique Bronze
- 30 White

P2539-0930K Brushed Nickel
54" dia., 15.25" ht.
Shown with Silver blades



Silver



Driftwood



P2539-2030K Antique Bronze
54" dia., 15.25" ht.
Shown with Medium Cherry blades



Medium Cherry



Classic Walnut



P2539-3030K White
54" dia., 15.25" ht.
Shown with White blades



White



ENERGY INFORMATION

Airflow 5,331 cubic feet per minute
Electricity Use 65 watts (excludes lights)
DOE Weighted CFM/W 92 CFM/W



Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited Lifetime Warranty
- 45° Canopy
- Downrod mount only
- AC Motor
- Reversible MDF blades
- Opal shatterproof shade
- Remote control with batteries included
- Remote control may be replaced with P2630-30 wall control control

LAMPING

17w LED Module, 3000K, 90 CRI, 1400 source lumens, dimmable.

All fixtures:



Signature Plus

- 09 Brushed Nickel
- 20 Antique Bronze
- 30 White

P2530-09 Brushed Nickel
54" dia., 15" ht.
Shown with Silver blades

- Silver
- Natural Cherry



P2530-20 Antique Bronze
54" dia., 15" ht.
Shown with Classic Walnut blades

- Classic Walnut
- Medium Cherry



P2530-30W White
54" dia., 15" ht.
Shown with White blades

- White



ENERGY INFORMATION

Airflow 4,716 cubic feet per minute
Electricity Use 65 watts (excludes lights)
DOE Weighted CFM/W 84 CFM/W

FEATURES

- 30-year limited warranty
- 45° Canopy
- Downrod mount only
- AC Motor
- Reversible MDF blades
- Compatible with universal light kits
- Three speed pull-chain switch
- Add a P2630-30 wall control or P2662-01 hand-held remote control
- Add the P2667-31 WiFi remote control

All fixtures:



Signature

- 09 Brushed Nickel
- 20 Antique Bronze
- 80 Forged Black

P2521-09 Brushed Nickel
52" dia., 14.62" ht.
Shown with White blades

- White
- Natural Cherry



P2521-20 Antique Bronze
52" dia., 14.62" ht.
Shown with Classic Walnut blades

- Classic Walnut
- Medium Cherry



P2521-80 Forged Black
52" dia., 14.62" ht.
Shown with Dark Cherry blades

- Dark Cherry
- Dark Walnut



ENERGY INFORMATION

Airflow 4,701 cubic feet per minute
Electricity Use 65 watts (excludes lights)
DOE Weighted CFM/W 84 CFM/W


FEATURES

- 30-year limited warranty
- 45° Canopy
- Close-to-ceiling installation with the addition of the P2666 Canopy
- SureConnect® System
- AC Motor
- Reversible plywood blades
- Compatible with universal light kits
- Three speed pull-chain switch
- Add a P2630-30 wall control or P2614-01 hand-held remote control
- Add the P2667-31 WiFi remote control

All fixtures:



INSTALLATION



AIRPRO®

- 009 Brushed Nickel
- 015 Polished Chrome
- 020 Antique Bronze

P250080-009 Brushed Nickel
52" dia., 12.6" ht.
Shown with Gray Weathered Wood blades

- Gray Weathered Wood
- Silver



P250080-015 Polished Chrome
52" dia., 12.6" ht.
Shown with Black blades

- Black
- Rustic Charcoal



P250080-020 Antique Bronze
52" dia., 12.6" ht.
Shown with Classic Walnut blades

- Classic Walnut
- Distressed Walnut



ENERGY INFORMATION

Airflow 4,591 cubic feet per minute
Electricity Use 58 watts (excludes lights)
DOE Weighted CFM/W 93 CFM/W

FEATURES

- 30-year limited warranty
- AC Motor
- Reversible plywood blades
- Compatible with universal light kits
- Add a P2630 wall control or P2663-01 hand-held remote control
- Add the P2667-31 WiFi remote control

All fixtures:



AIRPRO®

- 030 White
- 31M Matte Black
- 143 Graphite

P250080-030 White
52" dia., 12.6" ht.
Shown with White blades

- White
- Antique Wood



P250080-31M Matte Black
52" dia., 12.6" ht.
Shown with Matte Black blades

- Matte Black
- Rustic Charcoal



P250080-143 Graphite
52" dia., 12.6" ht.
Shown with Graphite blades

- Graphite
- Matte Black



ENERGY INFORMATION

Airflow 4,591 cubic feet per minute
Electricity Use 58 watts (excludes lights)
DOE Weighted CFM/W 93 CFM/W

FEATURES

- 30-year limited warranty
- AC Motor
- Reversible plywood blades
- Compatible with universal light kits
- Add a P2630 wall control or P2663-01 hand-held remote control
- Add the P2667-31 WiFi remote control

All fixtures:



52" Builder Fan

- 15 Polished Chrome
- 20 Antique Bronze
- 143 Graphite

P2501-15 Polished Chrome
52" dia., 13.5" ht.
Shown with Driftwood blades

- Driftwood
- Black



P2501-20 Antique Bronze
52" dia., 13.5" ht.
Shown with Medium Cherry blades

- Medium Cherry
- Classic Walnut



P2501-143 Graphite
52" dia., 13.5" ht.
Shown with Black blades

- Black
- Graphite



ENERGY INFORMATION

Airflow	4,991 cubic feet per minute
Electricity Use	63 watts (excludes lights)
DOE Weighted CFM/W	98 CFM/W

FEATURES

- 30-year limited warranty
- 45° Canopy
- Close-to-ceiling installation with the addition of the P2666 Canopy
- SureConnect® System
- AC Motor
- Reversible plywood blades
- Compatible with universal light kits
- Add a P2630 wall control or P2662-01 hand-held remote control
- Add the P2667-31 WiFi remote control

All fixtures:



52" Builder Fan

- 09 Brushed Nickel
- 30 White

P2501-09 Brushed Nickel
52" dia., 13.5" ht.
Shown with Cherry blades

- Cherry
- Natural Cherry



P2501-30W White
52" dia., 13.5" ht.
Shown with White blades

- White



P2501-30 White
52" dia., 13.5" ht.
Shown with Washed Oak blades

- White
- Washed Oak



ENERGY INFORMATION

Airflow	4,991 cubic feet per minute
Electricity Use	63 watts (excludes lights)
DOE Weighted CFM/W	98 CFM/W

FEATURES

- 30-year limited warranty
- 45° Canopy
- Close-to-ceiling installation with the addition of the P2666 Canopy
- SureConnect® System
- AC Motor
- Reversible plywood blades
- Compatible with universal light kits
- Add a P2630 wall control or P2662-01 hand-held remote control
- Add the P2667-31 WiFi remote control

All fixtures:



52" Performance

- 09 Brushed Nickel
- 20 Antique Bronze
- 30 White

P2503-09 Brushed Nickel
52" dia., 15.25" ht.
shown with Natural Cherry blades

- Natural Cherry
- Medium Cherry



P2503-20 Antique Bronze
52" dia., 15.25" ht.
shown with Medium Cherry blades

- Medium Cherry
- Classic Walnut



P2503-30W White
52" dia., 15.25" ht.
shown with White blades

- White



ENERGY INFORMATION

Airflow	5,143 cubic feet per minute
Electricity Use	70 watts (excludes lights)
DOE Weighted CFM/W	85 CFM/W


FEATURES

- Limited Lifetime Warranty
- 45° Canopy
- Close-to-ceiling installation
- SureConnect® System
- AC Motor
- Reversible plywood blades
- Compatible with universal light kits
- Three speed pull-chain switch
- Add a P2630-30 wall control or P2663-01 hand-held remote control
- Add the P2667-31 WiFi remote control

All fixtures:



INSTALLATION



Clifton Heights

- 09 Brushed Nickel
- 20 Antique Bronze

P2531-09 Brushed Nickel
52" dia., 15.75" ht.
Shown with Natural Cherry blades

- Natural Cherry
- Cherry



P2531-20 Antique Bronze
52" dia., 15.75" ht.
Shown with Cherry blades

- Cherry
- Classic Walnut



ENERGY INFORMATION

Airflow	4,373 cubic feet per minute
Electricity Use	55 watts (excludes lights)
DOE Weighted CFM/W	89 CFM/W


FEATURES

- 30-year limited warranty
- 45° Canopy
- Close-to-ceiling installation with the addition of the P2666 Canopy
- SureConnect System
- AC Motor
- Reversible plywood blades
- Compatible with universal light kits
- Three speed pull-chain switch
- Add a P2630-30 wall control or P2662-01 hand-held remote control
- Add the P2667-31 WiFi remote control

All fixtures:



INSTALLATION



52" Builder Fan with Light kit

- 09 Brushed Nickel
- 30 White
- 129 Architectural Bronze

P2599-09 Brushed Nickel
52" dia., 19.12" ht. x
Shown with Cherry blades

- Cherry
- Medium Cherry



P2599-30 White
52" dia., 19.12" ht.
Shown with White blades

- White



P2599-129 Architectural Bronze
52" dia., 19.12" ht.
Shown with Classic Walnut blades

- Classic Walnut
- Medium Cherry



ENERGY INFORMATION

Airflow 4,474 cubic feet per minute
Electricity Use 65 watts (excludes lights)
DOE Weighted CFM/W 82 CFM/W

FEATURES

- 30-year limited warranty
- Dual Mount (flat or sloped ceiling-30")
- AC Motor
- MDF/Plywood hybrid blades
- Frosted white glass shade
- Three speed pull-chain switch
- Add a P2630-30 wall control or P2663-01 hand-held remote control

LAMPING

Two medium base, 3000K, 8.5w LED lamps included. 800 lumens/lamp, 80 CRI, non-dimmable.

All fixtures:



AIRPRO®

- 009 Brushed Nickel
- 030 White
- 31M Matte Black

P250082-009-WB Brushed Nickel
52" dia., 16.7" ht.
Shown with Gray Weathered Wood blades

- Gray Weathered Wood
- Silver



P250082-030-WB White
52" dia., 16.7" ht.
Shown with White blades

- White
- Antique Wood



P250082-31M-WB Matte Black
52" dia., 16.7" ht.
Shown with Black blades

- Black
- Rustic Charcoal



ENERGY INFORMATION

Airflow 4,494 cubic feet per minute
Electricity Use 58 watts (excludes lights)
DOE Weighted CFM/W 92 CFM/W

FEATURES

- 30-year limited warranty
- AC Motor
- Reversible plywood blades
- Includes shatterproof shade
- Add a P2630 wall control or P2663-01 hand-held remote control

LAMPING

Two medium base, 3000K, 8.5w LED lamps included. 800 lumens/lamp, 80 CRI, non-dimmable.

All fixtures:



AIRPRO®

009 Brushed Nickel 030 White 31M Matte Black

P250081-009-WB Brushed Nickel
52" dia., 18.7" ht.
Shown with Gray Weathered Wood blades

- Gray Weathered Wood
- Silver



P250081-030-WB White
52" dia., 18.7" ht.
Shown with White blades

- White
- Antique Wood



P250081-31M-WB Matte Black
52" dia., 18.7" ht.
Shown with Black blades

- Black
- Rustic Charcoal



ENERGY INFORMATION

Airflow 4,857 cubic feet per minute
Electricity Use 58 watts (excludes lights)
DOE Weighted CFM/W 93 CFM/W

FEATURES

- 30-year limited warranty
- AC Motor
- Reversible plywood blades
- P250081 series has white opal shatterproof shades
- P250085 series has clear seeded glass shades
- Add a P2630 wall control or P2663-01 hand-held remote control

LAMPING

Four medium base, 3000K, 8.5w LED lamps included. 800 lumens/lamp, 80 CRI, non-dimmable.

All fixtures:



AIRPRO®

009 Brushed Nickel 030 White 31M Matte Black

P250085-009-WB Brushed Nickel
52" dia., 18.7" ht.
Shown with Gray Weathered Wood blades

- Gray Weathered Wood
- Silver



P250085-030-WB White
52" dia., 18.7" ht.
Shown with White blades

- White
- Antique Wood



P250085-31M-WB Matte Black
52" dia., 18.7" ht.
Shown with Black blades

- Black
- Rustic Charcoal



ENERGY INFORMATION

Airflow 4,857 cubic feet per minute
Electricity Use 58 watts (excludes lights)
DOE Weighted CFM/W 93 CFM/W

FEATURES

- 30-year limited warranty
- AC Motor
- Reversible plywood blades
- P250081 series has white opal shatterproof shades
- P250085 series has clear seeded glass shades
- Add a P2630 wall control or P2663-01 hand-held remote control

LAMPING

Four medium base, 3000K, 8.5w LED lamps included. 800 lumens/lamp, 80 CRI, non-dimmable.

All fixtures:



AIRPRO® Energy Star

009

Brushed Nickel

030

White

31M

Matte Black

P250084-009 Brushed Nickel
52" dia., 12.5" ht.
Shown with Gray Weathered Wood blades

- Gray Weathered Wood
- Silver



P250084-030 White
52" dia., 12.5" ht.
Shown with White blades

- White
- Antique Wood



P250084-31M Matte Black
52" dia., 12.5" ht.
Shown with Black blades

- Black
- Rustic Charcoal



ENERGY INFORMATION

Airflow 4,337 cubic feet per minute
Electricity Use 45 watts (excludes lights)
DOE Weighted CFM/W 112 CFM/W

FEATURES

- 30-year limited warranty
- AC Motor
- Reversible plywood blades
- Add a P2630 wall control or P2663-01 hand-held remote control
- Will accept a universal Energy Star rated light kit

All fixtures:



AIRPRO® Energy Star

009

Brushed Nickel

030

White

31M

Matte Black

P250066-009 Brushed Nickel
52" dia., 13.5" ht.
Shown with Natural Cherry blades

- Natural Cherry
- Cherry



P250066-030 White
52" dia., 13.5" ht.
Shown with White blades

- White
- Washed Oak



P250066-31M Matte Black
52" dia., 13.5" ht.
Shown with Matte Black blades

- Matte Black
- Rustic Charcoal



ENERGY INFORMATION

Airflow 4986 cubic feet per minute
Electricity Use 44 watts (excludes lights)
DOE Weighted CFM/W 134 CFM/W

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-30°)
- AC Motor
- Reversible plywood blades
- Add a P2630-30 or P2613-30 wall control or P2663-01 hand-held remote control
- Add the P2667-31 WiFi remote control

All fixtures:



Edgefield

- 009 Brushed Nickel
- 030 White
- 129 Architectural Bronze

P250016-009 Brushed Nickel
52" dia., 14.62" ht.
Shown with American Walnut blades

- American Walnut
- Cherry



P250016-030 White
52" dia., 14.62" ht.
Shown with White blades

- White



P250016-129 Architectural Bronze
52" dia., 14.62" ht.
Shown with Medium Cherry blades

- Medium Cherry
- Classic Walnut



ENERGY INFORMATION

Airflow 5,741 cubic feet per minute
Electricity Use 34 watts (excludes lights)
DOE Weighted CFM/W 179 CFM/W

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-18.5°)
- DC motor
- MDF blades
- Compatible with universal light kits
- Three speed pull-chain switch
- Will not accept a wall or remote control

All fixtures:



AIRPRO® Energy Star

- 009 Brushed Nickel
- 030 White
- 31M Matte Black

P250077-009-WB Brushed Nickel
52" dia., 18.7" ht.
Shown with Gray Weathered Wood blades

- Gray Weathered Wood
- Silver



P250077-030-WB White
52" dia., 18.7" ht.
Shown with White blades

- White
- Antique Wood



P250077-31M-WB Matte Black
52" dia., 18.7" ht.
Shown with Matte Black blades

- Matte Black
- Rustic Charcoal



ENERGY INFORMATION

Airflow 4,311 cubic feet per minute
Electricity Use 45 watts (excludes lights)
DOE Weighted CFM/W 111 CFM/W

FEATURES

- 30-year limited warranty
- AC Motor
- Reversible plywood blades
- Includes shatterproof shades
- Add a P2630 wall control or P2663-01 hand-held remote control

LAMPING

Four medium base, 3000K, 9w LED lamps included. 800 lumens/lamp, 90 CRI, dimmable.

All fixtures:



AIRPRO® Energy Star

009

Brushed Nickel

030

White

31M

Matte Black

P250078-009-WB Brushed Nickel
52" dia., 16.7" ht.
Shown with Gray Weathered Wood blades

- Gray Weathered Wood
- Silver



P250078-030-WB White
52" dia., 16.7" ht.
Shown with White blades

- White
- Antique Wood



P250078-31M-WB Matte Black
52" dia., 16.7" ht.
Shown with Black blades

- Black
- Rustic Charcoal



ENERGY INFORMATION

Airflow 4,311 cubic feet per minute
Electricity Use 45 watts (excludes lights)
DOE Weighted CFM/W 111 CFM/W

FEATURES

- 30-year limited warranty
- AC Motor
- Reversible plywood blades
- Includes shatterproof shade
- Add a P2630 wall control or P2663-01 hand-held remote control
- Add the P2667-31 WiFi remote control

LAMPING

Two medium base, 3000K, 9w LED lamps included. 800 lumens/lamp, 90 CRI, dimmable.

All fixtures:



42" Builder Fan

09

Brushed Nickel

20

Antique Bronze

30

White

P2500-09 Brushed Nickel
42" dia., 12.37" ht.
Shown with Cherry blades

- Cherry
- Natural Cherry



P2500-20 Antique Bronze
42" dia., 12.37" ht.
Shown with Classic Walnut blades

- Classic Walnut
- Medium Cherry



P2500-30 White
42" dia., 12.37" ht.
Shown with White blades

- White
- Washed Oak



ENERGY INFORMATION

Airflow 3,053 cubic feet per minute
Electricity Use 46 watts (excludes lights)
DOE Weighted CFM/W 64 CFM/W


FEATURES

- 15-year limited warranty
- 23° Canopy
- Close-to-ceiling installation
- SureConnect® System
- AC Motor
- Reversible plywood blades
- Compatible with universal light kits
- Three speed pull-chain switch
- Add a P2630 wall control or P2662-01 hand-held remote control
- Add the P2667-31 WiFi remote control

All fixtures:



INSTALLATION



Drift

- 009 Brushed Nickel
- 030 White
- 129 Architectural Bronze

P250008-009 Brushed Nickel
32" dia., 14.37" ht.
Shown with Driftwood blades

- Driftwood
- Silver



P250008-030 White
32" dia., 14.37" ht.
Shown with Driftwood blades

- Driftwood
- White



P250008-129 Architectural Bronze
32" dia., 14.37" ht.
Shown with Classic Walnut blades

- Classic Walnut
- Medium Cherry



ENERGY INFORMATION

Airflow	2,518 cubic feet per minute
Electricity Use	35 watts (excludes lights)
DOE Weighted CFM/W	88 CFM/W


FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-30°)
- Close-to-ceiling installation
- AC Motor
- Reversible MDF blades
- Compatible with universal light kits
- Three speed pull-chain switch
- Add a P2630-30 or wall control or P2662-01 hand-held remote control
- Add the P2667-31 WiFi remote control

All fixtures:



INSTALLATION



Bexar

- 009 Brushed Nickel
- 31M Matte Black

P250099-009-30 Brushed Nickel
54" dia., 11.5" ht.
Shown with Dark Cherry blades

- Silver
- Dark Cherry



P250099-31M-30 Matte Black
54" dia., 11.5" ht.
Shown with Distressed Ebony blades

- Distressed Ebony
- Matte Black



ENERGY INFORMATION

Airflow	3,576 cubic feet per minute
Electricity Use	64 Watts (excludes lights)
DOE Weighted CFM/W	64 CFM/W

FEATURES

- Limited Lifetime Warranty
- AC Motor
- Reversible plywood blades
- White opal glass shade
- Remote control with batteries included
- Add the P2667-31 WiFi remote control

LAMPING

18w LED Module, 3000K, 90 CRI,
1600 source lumens, dimmable.

All fixtures:



Three-speed Remote Control Included
Three-speed fan operation

56" Braden

- 09 Brushed Nickel
- 15 Polished Chrome
- 129 Architectural Bronze

P2588-0930K Brushed Nickel
56" dia., 9.87" ht.
Shown with American Walnut blades

- American Walnut
- Silver



P2588-1530K Polished Chrome
56" dia., 9.87" ht.
Shown with Black blades

- Black
- American Walnut




P2588-12930K Architectural Bronze
56" dia., 9.87" ht.
Shown with Medium Cherry blades

- Medium Cherry
- Classic Walnut



ENERGY INFORMATION

Airflow 4,263 cubic feet per minute
Electricity Use 55 watts (excludes lights)
DOE Weighted CFM/W 85 CFM/W

 Full Function Remote Control Included
Three-speed fan operation
Full-range dimming for light
Reverse direction control

FEATURES

- Limited Lifetime Warranty
- Hugger low profile mounting
- AC Motor
- Reversible plywood blades
- White opal glass shade
- Full function remote control with batteries included
- Remote control may be replaced with P2631-30 wall control
- Add the P2667-31 WiFi remote control

LAMPING

18w LED Module, 3000K, 90 CRI, 1400 source lumens, dimmable.

All fixtures:
    

56" Braden

- 28 Satin White
- 31M Matte Black

P2588-2830K Satin White
56" dia., 9.75" ht.
Shown with Natural Cherry blades

- Natural Cherry
- Matte White




P2588-31M30K Matte Black
56" dia., 9.75" ht.
Shown with Matte Black blades

- Matte Black
- Distressed Ebony



ENERGY INFORMATION

Airflow 4,263 cubic feet per minute
Electricity Use 55 watts (excludes lights)
DOE Weighted CFM/W 85 CFM/W

 Full Function Remote Control Included
Three-speed fan operation
Full-range dimming for light
Reverse direction control

FEATURES

- Limited Lifetime Warranty
- Hugger low profile mounting
- AC Motor
- Reversible plywood blades
- White opal glass shade
- Full function remote control with batteries included
- Remote control may be replaced with P2631-30 wall control
- Add the P2667-31 WiFi remote control

LAMPING

18w LED Module, 3000K, 90 CRI, 1400 source lumens, dimmable.

All fixtures:
   

44" Braden

- 009 Brushed Nickel
- 028 Satin White
- 031 Black

P250058-009-30 Brushed Nickel
44" dia., 9.81" ht.
Shown with Brushed Nickel blades

- Brushed Nickel
- American Walnut



P250058-028-30 Satin White
44" dia., 9.81" ht.
Shown with Natural Cherry blades

- Natural Cherry
- Matte White



P250058-031-30 Black
44" dia., 9.81" ht.
Shown with Black blades

- Black
- Distressed Ebony



ENERGY INFORMATION

Airflow 3,212 cubic feet per minute
Electricity Use 45 watts (excludes lights)
DOE Weighted CFM/W 78 CFM/W

Full Function Remote Control Included
Three-speed fan operation
Full-range dimming for light
Reverse direction control

FEATURES

- Limited Lifetime Warranty
- Hugger low profile mounting
- AC Motor
- Reversible plywood blades
- Frosted shatterproof shade
- Remote control with batteries included
- Add the P2667-31 WiFi remote control

LAMPING

18w LED Module, 3000K, 90 CRI,
1400 source lumens, dimmable.

All fixtures:

Vox

- 09 Brushed Nickel
- 20 Antique Bronze
- 30 White

P2572-0930K Brushed Nickel
52" dia., 11.62" ht.
Shown with Medium Cherry blades

- Medium Cherry



P2572-2030K Antique Bronze
52" dia., 11.62" ht.
Shown with American Walnut blades

- American Walnut



P2572-3030K White
52" dia., 11.62" ht.
Shown with White blades

- White



ENERGY INFORMATION

Airflow 4,276 cubic feet per minute
Electricity Use 62 watts (excludes lights)
DOE Weighted CFM/W 76 CFM/W

Full Function Remote Control Included
Three-speed fan operation
Full-range dimming for light
Reverse direction control

FEATURES

- Limited Lifetime Warranty
- Hugger low profile mounting
- AC Motor
- White opal glass shade
- Full function remote control with batteries included
- Remote control may be replaced with P2631-30 wall control
- Add the P2667-31 WiFi remote control

LAMPING

17w LED Module, 3000K, 90 CRI,
1400 source lumens, dimmable.

All fixtures:

Lindale

081 Antique Nickel 129 Architectural Bronze

P250028-081 Antique Nickel
52" dia., 11.18" ht.
Shown with White Barnwood blades

- White Barnwood
- Driftwood



P250028-129 Architectural Bronze
52" dia., 11.18" ht.
Shown with Distressed Walnut blades and optional P2669-129 Light Kit

- Distressed Walnut
- Classic Walnut



LINDALE LIGHT KIT
P2669-028 Satin White
P2669-081 Antique Nickel
P2669-129 Architectural Bronze



P2669-028



P2669-081



P2669-129

ENERGY INFORMATION

Airflow 4,642 cubic feet per minute
Electricity Use 60 watts (excludes lights)
DOE Weighted CFM/W 87 CFM/W



Three-speed Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited Lifetime Warranty
- Hugger low profile mounting
- AC Motor
- Reversible plywood blades
- Accepts P2669 light kit, sold separately
- Remote control with batteries included
- Remote control may be replaced with P2630-30 wall control
- Add the P2667-31 WiFi remote control

LAMPING

24w LED Module, 3000K, 90 CRI, 2000 source lumens, dimmable.

All fixtures:



52" Hugger Fan

09 Brushed Nickel 30 White

P2525-09 Brushed Nickel
52" dia., 8.12" ht.
Shown with Cherry blades

- Cherry
- Natural Cherry



P2525-30 White
52" dia., 8.12" ht.
Shown with white blades

- White



ENERGY INFORMATION

Airflow 3,229 cubic feet per minute
Electricity Use 56 watts (excludes lights)
DOE Weighted CFM/W 58 CFM/W

FEATURES

- 15-year limited warranty
- Hugger low profile mounting
- AC Motor
- Reversible plywood blades
- Compatible with universal light kits
- Cannot be used with remote control
- Add a P2630-30 wall control
- Add the P2667-31 WiFi remote control

All fixtures:



42" Hugger Fan

09 Brushed Nickel 30 White

P2524-09 Brushed Nickel
42" dia., 8.31" ht.
Shown with Natural Cherry blades

- Natural Cherry
- Cherry



P2524-30 White
42" dia., 8.31" ht.
Shown with White blades

- White



ENERGY INFORMATION

Airflow	2,639 cubic feet per minute
Electricity Use	44 watts (excludes lights)
DOE Weighted CFM/W	72 CFM/W

FEATURES

- 15-year limited warranty
- Hugger low profile mounting
- AC Motor
- Reversible plywood blades
- Compatible with universal light kits
- Cannot be used with remote control
- Add the P2630-30 wall control
- Add the P2667-31 WiFi remote control

All fixtures:



Featuring Willacy

Outdoor Ceiling Fans

Featuring Albin and Whitmire

Springer II

31M Matte Black 081 Antique Nickel 129 Architectural Bronze

Relax under the refreshing breeze of the Springer Collection 60-Inch Windmill Ceiling Fan. Its large scale and windmill-style blades make it ideal for any great room, bedroom, living room, or bonus room in modern farmhouse, rustic, and coastal-style settings. Its twelve sweeping blades are coated in a choice of Distressed Charcoal with a Matte Black housing, Antique Nickel with Galvanized blades, and Distressed Walnut finished blades with an Architectural Bronze body for a rustic flair. Its cULus damp rating makes this lovely fan ideal for use inside or in outdoor covered areas. A full-function remote control and wall bracket are included.



P250098-31M

Springer II


P250098-31M Matte Black
60" dia., 16.26" ht.
Shown with Distressed Charcoal blades

Distressed Charcoal



P250098-081 Antique Nickel
60" dia., 16.26" ht.
Shown with Galvanized blades

Galvanized



P250098-129 Architectural Bronze
60" dia., 16.26" ht.
Shown with Distressed blades

Distressed Walnut



ENERGY INFORMATION

Airflow 6,158 cubic feet per minute
Electricity Use 35 Watts (excludes lights)
DOE Weighted CFM/W 205 CFM/W



Full Function Remote Control Included
Six-speed fan operation
Reverse direction control

FEATURES

- Limited Lifetime Warranty
- DC Motor
- Hand painted aluminum blades
- Damp Rated
- Remote control with batteries included
- Add the P2673 WiFi remote

ALSO IN: LIGHT KITS



All fixtures:



Schaal

028 Satin White 31M Matte Black

With a unique, wicker-wrapped shade and five reversible fan blades, the 52-inch Schaal ceiling fan brings a global presence to rooms in coastal settings. An 18W integrated LED module delivers soft, 3000K 90 CRI illumination through white opal glass. Schaal is offered in Matte White and Chestnut reversible blades with a Satin White housing or a Matte Black housing with Rustic Charcoal and Matte Black reversible blades. Its UL damp rating makes this lovely fan ideal for use inside or in outdoor covered areas. A full-function remote control and wall bracket are included.



P250101-31M-30

Schaal

P250101-028-30 Satin White
52" dia., 16" ht.
*Shown with Chestnut blades
and Synthetic rope accent*

Matte White
Chestnut



P250101-31M-30 Matte Black
52" dia., 16" ht.
*Shown with Rustic Charcoal blades
and Synthetic rope accent*

Rustic Charcoal
Matte Black



ENERGY INFORMATION

Airflow 4,687 cubic feet per minute
Electricity Use 59 watts (excludes lights)
DOE Weighted CFM/W 89 CFM/W



Full Function Remote Control Included
Three-speed fan operation
Full-range dimming for light
Reverse direction control

FEATURES

- Limited Lifetime Warranty
- DC Motor
- Reversible plywood blades
- White opal shade
- Damp Rated
- Remote control with batteries included

LAMPING

18w LED Module, 3000K, 90 CRI,
1600 source lumens, dimmable.

All fixtures:



Kasota

108 Oil Rubbed Bronze 143 Graphite 152 Painted Nickel

A sturdy metal housing and long lines bring contemporary style to Kasota. Three rectangular fan blades with long blade arms that span the entire length are finished in a linen-like texture that softens its modern look. Kasota is damp rated, making it ideal for outdoor and indoor settings. Inside, it has a DC motor for the highest efficacy and whisper-quiet operation. A full-function remote control with a battery and a LED light kit with a white opal glass shade is included.



P250072-108-30

Kasota

P250072-108-30 Oil Rubbed Bronze
56" dia., 15" ht.
Shown with Tan Linen blades



P250072-143-30 Graphite
56" dia., 15" ht.
Shown with Charcoal Linen blades



P250072-152-30 Painted Nickel
56" dia., 15" ht.
Shown with Charcoal Linen blades



ENERGY INFORMATION

Airflow	4,844 cubic feet per minute
Electricity Use	31 watts (excludes lights)
DOE Weighted CFM/W	188 CFM/W



Full Function Remote Control Included
Six-speed fan operation
Full-range dimming for light
Reverse direction control

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- ABS blades
- White opal shatterproof shade
- Damp Rated
- Remote control with batteries included

LAMPING

18w LED Module, 3000K, 90 CRI, 1400 source lumens, dimmable.

All fixtures:



Upshur

009 Brushed Nickel 020 Antique Bronze 31M Matte Black


Angles and curves bring contemporary style to Upshur. Three hand-finished ABS blades have a distinctive, angled design and are mounted directly to the flywheel to complete the fan's sleek, modern look. An AC Motor offers quiet operation and creates powerful cool breezes, while a dimmable LED light kit is energy efficient and casts the perfect glow. The included remote control operates the fan, including reverse and full light dimming functions.



P250094-009-30

Upshur

P250094-009-30 Brushed Nickel
52" dia., 13.7" ht.
Shown with Gray Weathered Wood blades

 Gray Weathered Wood




P250094-020-30 Antique Bronze
52" dia., 13.7" ht.
Shown with Walnut blades

 Walnut




P250094-31M-30 Matte Black
52" dia., 13.7" ht.
Shown with Rustic Charcoal blades

 Rustic Charcoal



ENERGY INFORMATION
Airflow 4,631 cubic feet per minute
Electricity Use 34 watts (excludes lights)
DOE Weighted CFM/W 102 CFM/W

 Full Function Remote Control Included
*Three-speed fan operation
Full-range dimming for light
Reverse direction control*

FEATURES

- Limited Lifetime Warranty
- AC Motor
- ABS blades
- White opal shatterproof shade
- Damp Rated
- Remote control with batteries included
- Add the P2667-31 WiFi remote control

LAMPING
18w LED Module, 3000K, 90 CRI,
1500 source lumens, dimmable.

All fixtures:
    

Schaffer II

028 Satin White 31M Matte Black 081 Antique Nickel

Natural jute rope offers modern organic styling to the housing of the Schaffer four-blade ceiling fan, softening the housing's look and making it perfect for coastal and global spaces. This 52-inch ceiling fan has four reversible plywood blades offered in a choice of Classic Walnut and Grey Weathered Wood and an Antique Nickel housing, Matte Black and Rustic Charcoal with a Matte Black body, or Matte White and Natural Cherry and a Satin White housing. An 18W integrated LED module delivers soft, 3000K 90 CRI illumination through white opal glass. Its UL damp rating makes this lovely fan ideal for use inside or in outdoor covered areas. A 3-speed remote control and wall bracket are included.



P250097-028-30

Schaffer II

P250097-028-30 Satin White
56" dia., 15.5" ht.
*Shown with Natural Cherry blades
and Natural Jute rope accent*

Matte White
Natural Cherry



P250097-31M-30 Matte Black
56" dia., 15.5" ht.
*Shown with Rustic Charcoal blades,
Natural Jute rope accent and light kit
removed using blank plate*

Rustic Charcoal
Matte Black



P250097-081-30 Antique Nickel
56" dia., 15.5" ht.
*Shown with Classic Walnut blades
and Natural Jute rope accent*

Classic Walnut
Grey Weathered Wood



ENERGY INFORMATION

Airflow 6,177 cubic feet per minute
Electricity Use 67 watts (excludes lights)
DOE Weighted CFM/W 98 CFM/W



Three-speed Remote Control Included
*Three-speed fan operation
Full-range dimming for light*

FEATURES

- Limited Lifetime Warranty
- AC Motor
- Reversible plywood blades
- White opal glass shade
- Damp Rated
- Remote control with batteries included
- Remote control may be replaced with P2630-30 wall control
- Add the P2667-31 WiFi remote control

LAMPING

18w LED Module, 3000K, 90 CRI,
1600 source lumens, dimmable.


All fixtures:



Midvale

- 028 Matte White
- 141 Galvanized Finish
- 171 Blistered Iron

Midvale offers a nostalgic appeal, with vintage-style LED bulbs inside a clear seeded glass shade, a rustic cage frame, and a banded metal ceiling canopy to complete the charming look.



P250011-141-WB

Midvale

P250011-028-WB Matte White
56" dia., 20.37" ht.
Shown with Matte White blades

Matte White

P250011-141-WB Galvanized Finish
56" dia., 20.37" ht.
Shown with Galvanized Finish blades

Galvanized Finish

P250011-171-WB Blistered Iron
56" dia., 20.37" ht.
Shown with Blistered Iron blades

Blistered Iron

ENERGY INFORMATION

Airflow	7,627 cubic feet per minute
Electricity Use	84 watts (excludes lights)
DOE Weighted CFM/W	98 CFM/W



Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- ABS blades
- Clear seeded glass shade
- Damp Rated
- Remote control with batteries included
- Remote control may be replaced with P2667-31 WiFi remote control

LAMPING

Two medium base 2700K
7w vintage LED lamps included.
600 lumens/lamp, 90 CRI, dimmable.
7w LED max/socket.

All fixtures:



Edwidge

Edwidge cleverly houses the motor within the trio of fan blades providing a sleek, modern look. All-weather ABS fan blades and a non-metallic housing and canopy offer rust-proof, contemporary style to indoor and covered outdoor settings.

- 028 Satin White
- 031 Black
- 152 Painted Nickel



P250062-152-30

Edwidge

P250062-028-30 Satin White
52" dia., 13.55" ht.
Shown with Satin White blades

 Satin White



P250062-031-30 Black
52" dia., 13.55" ht.
Shown with Black blades

 Black



P250062-152-30 Painted Nickel
52" dia., 13.55" ht.
Shown with Painted Nickel blades

 Painted Nickel



ENERGY INFORMATION

Airflow 5,873 cubic feet per minute
Electricity Use 20 watts (excludes lights)
DOE Weighted CFM/W 328 CFM/W



Full Function Remote Control Included
Six-speed fan operation
Full-range dimming for light
Reverse direction control

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- ABS blades
- White opal glass shade
- Damp Rated
- Remote control with batteries included

LAMPING

18w LED Module, 3000K, 90 CRI,
1400 source lumens, dimmable.

All fixtures:



Whirl

- 20Antique Bronze
- 80Forged Black
- 81Antique Nickel



P2574-8130K

Whirl

P2574-2030K Antique Bronze
60" dia., 15.87" ht.
Shown with Walnut blades



Walnut



P2574-8030K Forged Black
60" dia., 15.87" ht.
Shown with Toasted Oak blades



Toasted Oak



P2574-8130K Antique Nickel
60" dia., 15.87" ht.
Shown with Driftwood blades



Driftwood



ENERGY INFORMATION

Airflow	6,549 cubic feet per minute
Electricity Use	70 watts (excludes lights)
DOE Weighted CFM/W	106 CFM/W

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-18.5°)
- AC Motor
- ABS all weather blades
- White frosted glass shade
- Three speed pull-chain switch (fan)
- On/off pull-chain switch (light)
- Damp Rated
- Add a P2630-30 wall control or P2662-01 hand-held remote control
- Add the P2667-31 WiFi remote control

LAMPING

18w LED Module, 3000K, 90 CRI, 1400 source lumens, dimmable (with added remote wall control).

All fixtures:




Search the product number on progresslighting.com for full product details

Alfresco

Infuse a warm, nature-inspired style to your outdoor home décor with the one-of-a-kind Alfresco collection. Five blades decorated in a leaf-like design sprout from a dual mount center that artistically harbors an LED light source. Select from an Architectural Bronze and blistered iron finish to bring your bohemian dreamland to life.

129 Architectural Bronze 171 Blistered Iron



P250034-129-WB

Alfresco

P250034-129-WB Architectural Bronze
54" dia., 19.25" ht.
Shown with Dark Bamboo blades

Dark Bamboo



P250034-171-WB Blistered Iron
54" dia., 19.25" ht.
Shown with Pewter blades

Pewter



ENERGY INFORMATION

Airflow 5,724 cubic feet per minute
Electricity Use 68 watts (excludes lights)
DOE Weighted CFM/W 90 CFM/W



Three-speed Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- ABS blades
- Clear seeded glass shade
- Damp Rated
- Remote control with batteries included
- Remote control may be replaced with P2630-30 wall control
- Add the P2667-31 WiFi remote control

LAMPING

Two medium base 2700K
7w vintage LED lamps included.
600 lumens/lamp, 90 CRI,
dimmable. 7w LED max/socket.

All fixtures:



Smyrna

20 Antique Bronze 80 Forged Black

This 52" Smyrna ceiling fan features an LED light source, offering both form and function with energy and cost-savings benefits. The light kit contains a clear hammered glass shade and contains a 17W dimmable 3000K LED module. Includes a wall control switch for fan speed and light operation.



P2576-2030K

Smyrna

P2576-2030K Antique Bronze
52" dia., 19.5" ht.
Shown with Walnut blades

Walnut



P2576-8030K Forged Black
52" dia., 19.5" ht.
Shown with Toasted Oak blades

Toasted Oak



ENERGY INFORMATION

Airflow	4,585 cubic feet per minute
Electricity Use	58 watts (excludes lights)
DOE Weighted CFM/W	91 CFM/W



Wall Control Included
Four-speed fan operation
Full-range dimming for light
Includes switch plate cover

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-30°)
- AC Motor
- ABS all weather blades
- Clear hammered glass shade
- Wet Rated

LAMPING

17w LED Module, 3000K, 90 CRI,
1400 source lumens, dimmable.

All fixtures:



Montague

20 Antique Bronze 30 White 80 Forged Black

This five-blade 60" Montague ceiling fan features an all weather wet location rating to accommodate a variety of interior and exterior locations. The white opal glass shade contains a 18W dimmable, 3000K LED module, offering both form and function with energy and cost-savings benefits. A full function remote control is included.



P2564-8030K

Montague

P2564-2030K Antique Bronze
60" dia., 17.62" ht.
Shown with Walnut blades

Walnut



P2564-3030K White
60" dia., 17.62" ht.
Shown with White blades

White



P2564-8030K Forged Black
60" dia., 17.62" ht.
Shown with Toasted Oak blades

Toasted Oak



ENERGY INFORMATION

Airflow 6,693 cubic feet per minute
Electricity Use 75 watts (excludes lights)
DOE Weighted CFM/W 96 CFM/W



Full Function Remote Control Included
Three-speed fan operation
Full-range dimming for light
Reverse direction control

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-18.5°)
- AC Motor
- ABS all weather blades
- White opal glass shade
- Wet Rated
- Remote control with batteries included
- Remote control may be replaced with P2630-30 wall control

LAMPING

18w LED Module, 3000K, 90 CRI,
1400 source lumens, dimmable.

All fixtures:



Albin

The Albin collection offers a modern take on a traditional design that will be perfectly at home in so many outdoor spaces and lifestyles. Five blades finished with a faux wood grain texture extend from a modern-style center available in an Architectural Bronze, Matte White, or Matte Black finish. An LED light source is encased in a crisp shade to illuminate a patio or porch space that will beg to be lived in an enjoyed.


031 Black 129 Architectural Bronze



P250036-129-30


Albin

P250036-031-30 Black
54" dia., 15.61" ht.
Shown with Toasted Oak blades

 Toasted Oak



P250036-129-30 Architectural Bronze
54" dia., 15.61" ht.
Shown with Distressed Walnut blades

 Distressed Walnut



ENERGY INFORMATION

Airflow	5,740 cubic feet per minute
Electricity Use	67 watts (excludes lights)
DOE Weighted CFM/W	95 CFM/W



Three-speed Remote Control Included
Three-speed fan operation
Full range dimming with light

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- White opal glass shade
- Damp Rated
- Remote control with batteries included
- Remote control may be replaced with P2630-30 wall control
- Add the P2667-31 WiFi remote control

LAMPING

24w LED Module, 3000K, 90 CRI, 2000 source lumens, dimmable.

All fixtures:



Kennedale

028 Satin White 31M Matte Black 152 Painted Nickel

Perfect for cooling large spaces inside or out, Kennedale is a 72" damp-rated DC motor fan. Classically styled with UV protected, faux wood finished reversible blades, Kennedale offers a substantial look for traditional and transitional décor and is ideal for an open floor plan or a large porch. A six-speed full function handheld remote is included. Kennedale will accept a Universal Light Kit.



P250070-31M

Kennedale

P250070-028 Satin White
72" dia., 18" ht.
Shown with Driftwood blades

Driftwood
Matte White



P250070-31M Matte Black
72" dia., 18" ht.
Shown with Black blades

Black
Rustic Charcoal



P250070-152 Painted Nickel
72" dia., 18" ht.
Shown with Gray Weathered Wood blades

Gray Weathered Wood
Painted Nickel



ENERGY INFORMATION

Airflow 8760 cubic feet per minute
Electricity Use 33 watts (excludes lights)
DOE Weighted CFM/W 293 CFM/W



Full Function Remote Control Included
Six-speed fan operation
Reverse direction control

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-25°)
- DC Motor
- Reversible plywood blades
- Will accept a light kit
- Damp Rated
- Remote control with batteries included

All fixtures:



Lakehurst

- 20Antique Bronze
- 30White
- 80Forged Black

P2562-20 Antique Bronze
60" dia., 15.75" ht.
Shown with Walnut blades



Walnut



P2562-30 White
60" dia., 15.75" ht.
Shown with White blades



White



P2562-80 Forged Black
60" dia., 15.75" ht.
Shown with Toasted Oak blades



Toasted Oak



ENERGY INFORMATION

Airflow 6,440 cubic feet per minute
Electricity Use 71 watts (excludes lights)
DOE Weighted CFM/W 105 CFM/W

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-18.5°)
- AC Motor
- ABS all weather blades
- Compatible with universal light kits
- 3 Speed pull chain switch
- Wet Rated
- Add a P2630-30 wall control or P2662-01 hand-held remote control
- Add the P2667-31 WiFi remote control

All fixtures:



Decorative Patio Fan

- 20Antique Bronze

P2526-20 Antique Bronze
52" dia., 17.37" ht.
Shown with Washed Walnut blades



Washed Walnut



P2526-20 Antique Bronze
52" dia., 17.37" ht.
Shown with Washed Walnut blades and with P2636-20WB accessory light kit



Washed Walnut



ENERGY INFORMATION

Airflow 4,150 cubic feet per minute
Electricity Use 70 watts (excludes lights)
DOE Weighted CFM/W 77 CFM/W


FEATURES

- 15-year limited warranty
- 45° Canopy
- Close-to-ceiling installation
- SureConnect® System
- AC Motor
- ABS all weather blades
- Compatible with universal light kits
- Damp Rated
- Add a P2630-30 wall control or P2662-01 hand-held remote control

All fixtures:



INSTALLATION




54" Patio Fan

20 Antique Bronze



P2533-20 Antique Bronze
54" dia., 18.25" ht.
*Shown with Toasted Oak blades
and with P2636-20WB accessory light kit*



Toasted Oak




ENERGY INFORMATION

Airflow	4,986 cubic feet per minute
Electricity Use	65 watts (excludes lights)
DOE Weighted CFM/W	74 CFM/W

FEATURES

- 30-year limited warranty
- 45° Canopy
- SureConnect® System
- AC Motor
- ABS all weather blades
- Compatible with universal light kits
- Wet Rated
- Add a P2630-30 wall control or P2662-01 hand-held remote control

INSTALLATION



ALSO IN: LIGHT KITS



All fixtures:



52" Patio Fan

20 Antique Bronze 30 White 80 Forged Black

P2502-20 Antique Bronze
52" dia., 11" ht.
Shown with Oak blades



Oak



P2502-30 White
52" dia., 11" ht.
Shown with White blades



White



P2502-80 Forged Black
52" dia., 11" ht.
Shown with Toasted Oak blades



Toasted Oak



ENERGY INFORMATION

Airflow	4,991 cubic feet per minute
Electricity Use	64 watts (excludes lights)
DOE Weighted CFM/W	89 CFM/W


FEATURES

- 15-year limited warranty
- Dual Mount (flat or sloped ceiling-23°)
- Close-to-ceiling installation
- SureConnect® System
- Quick-Install canopy
- AC Motor
- ABS all weather blades
- Compatible with universal light kits
- Three speed pull-chain switch
- Wet Rated
- Add a P2630-30 wall control or P2662-01 hand-held remote control

All fixtures:



INSTALLATION



Accessories- Ceiling Fans



Indoor/Outdoor

SCHOOLHOUSE
P2601-20WB Antique Bronze
P2601-30WB White
P2601-80WB Forged Black
with opal glass.
8.5" dia., 7" ht.
One medium base, 3000K,
LED lamp included.
800 lumens/lamp,
90 CRI, dimmable.
*Universal-style with
quick-connect wiring.*



LOW PROFILE
P2611-20WB Antique Bronze
P2611-30WB White
P2611-80WB Forged Black
with opal glass.
10.5" dia., 4.5" ht.
Two medium base, 3000K,
LED lamp included.
800 lumens/lamp,
90 CRI, dimmable.



ASHMORE
P2636-20WB Antique Bronze
11" dia., 8.25" ht.
2 medium base, 9w max.



All fixtures:
JAB

AIRPRO® Edgelit LED
Light Kit

P260002-028-30 Satin White
P260002-31M-30 Matte Black
P260002-152-30 Painted Nickel
7.45" dia., 1" ht.
14w LED Module, 3000K, 90 CRI,
1000 source lumens, dimmable.

All fixtures:
T20 JAB



Springer II

P260004-31M-WB Matte Black
P260004-081-WB Antique Nickel
P260004-129-WB Architectural Bronze
12" dia., 11" ht.
2 medium base, 7w LED.
Only for use with P250000,
P250065 and P250098.

All fixtures:
JAB



Springer

P260000-31M-WB Matte Black
P260000-081-WB Antique Nickel
P260000-129-WB Architectural Bronze
11.87" dia., 7.5" ht.
2 medium base, 7w max.

All fixtures:
JAB



Clifton Heights

009 Brushed Nickel 020 Antique Bronze

P2654-01WB
with etched glass.
Included Finials:
009 Brushed Nickel
020 Antique Bronze
12.25" dia., 6.25" ht.
2 medium base, 9w max
800 lumens/lamp, 90 CRI.
Indoor use only. dimmable
*Universal-style with
quick-connect wiring.*



Torino

009 Brushed Nickel 020 Antique Bronze 080 Forged Black

P2645-01WB
with etched glass.
Included Finials:
009 Brushed Nickel
020 Antique Bronze
080 Forged Black
12" dia., 5.75" ht.
2 medium base, 9w max
800 lumens/lamp, 90 CRI.
Indoor use only. dimmable
*Universal-style with
quick-connect wiring.*



Gather, Bravo & Joy

009 Brushed Nickel 020 Antique Bronze

P2650-01WB
with etched glass.
Included Finials:
009 Brushed Nickel
020 Antique Bronze
11" dia., 5.5" ht.
2 medium base, 9w max
800 lumens/lamp, 90 CRI.
Indoor use only. dimmable
*Universal-style with
quick-connect wiring.*



All fixtures:



Search the product number on progresslighting.com for full product details

Four Light Universal

09 Brushed Nickel 20 Antique Bronze 30 White

P2643-09WB Brushed Nickel
P2643-20WB Antique Bronze
P2643-30WB White
13.75" dia., 8" ht.
4 medium base, 9w max
800 lumens/lamp, 90 CRI.
Indoor use only. dimmable
*Universal-style with
quick-connect wiring.*



Three Light Universal

09 Brushed Nickel 30 White

P2642-09WB Brushed Nickel
P2642-30WB White
13.62" dia., 7" ht.
3 medium base, 9w max
800 lumens/lamp, 90 CRI.
Indoor use only. dimmable
*Universal-style with
quick-connect wiring.*



Low Profile

09 Brushed Nickel 15 Polished Chrome
20 Antique Bronze 30 White 143 Graphite

P2602-09WB Brushed Nickel
P2602-15WB Polished Chrome
P2602-20WB Antique Bronze
P2602-30WB White
P2602-143WB Graphite
With White Opal glass
10.5" dia., 3.81" ht.
2 medium base, 9w max
800 lumens/lamp, 90 CRI.
Indoor use only. dimmable
*Universal-style with
quick-connect wiring.*



All fixtures:



Search the product number on progresslighting.com for full product details

Universal Bowl

P2612-01WB
with alabaster glass.
Included Finials:
009 Brushed Nickel
020 Antique Bronze
030 White
015 Polished Chrome
143 Graphite
10.75" dia., 5.5" ht.
Two medium base, 7w max.
*Universal-style with
quick-connect wiring.*



- 009 Brushed Nickel
- 015 Polished Chrome
- 020 Antique Bronze
- 030 White
- 143 Graphite

LED Light Kits

P2659-09 Brushed Nickel
P2659-20 Antique Bronze
with etched white glass.
12.25" dia., 4" ht.
One 16w 3000K
LED module included.
1265 source lumens,
960 delivered lumens,
90 CRI, dimmable.
Indoor use only.



- 09 Brushed Nickel
- 20 Antique Bronze

Trinity

P2628-01WB Unfinished
with etched glass.
Included Finials:
09 Brushed Nickel
031 Matte Black
20 Antique Bronze
30 White
13.37" dia., 6.37" ht.
2 medium base, 9w max
Indoor use only.



*shown with
Brushed Nickel finial*

*shown with
Antique Bronze finial*

*shown with
Matte Black finial*

*shown with
White finial*

- 09 Brushed Nickel
- 031 Matte Black
- 20 Antique Bronze
- 30 White

All fixtures:



Search the product number on progresslighting.com for full product details

Four Light Alabaster

P2610-09WB Brushed Nickel
P2610-15WB Polished Chrome
P2610-20WB Antique Bronze
P2610-30WB White
P2610-143WB Graphite
with alabaster glass.
15" dia., 6.25" ht.
Four medium base, 3000K,
LED lamps included.
800 lumens/lamp,
90 CRI, dimmable.
Indoor use only.



- 09 Brushed Nickel
- 15 Polished Chrome
- 20 Antique Bronze
- 30 White
- 143 Graphite

Three Light Alabaster

P2600-09WB Brushed Nickel
P2600-20WB Antique Bronze
P2600-30WB White
with alabaster glass.
15" dia., 6.62" ht.
3 medium base, 9w max
Indoor use only.



- 09 Brushed Nickel
- 20 Antique Bronze
- 30 White

Schoolhouse

P2644-09WB Brushed Nickel
With White Opal glass
8.5" dia., 6.5" ht.
One medium base, 3000K,
LED lamp included.
800 lumens/lamp,
90 CRI, dimmable.
Indoor use only.



- 09 Brushed Nickel

All fixtures:



Search the product number on progresslighting.com for full product details

Accessory Downrods


3/4" diameter; approximately 1" outside diameter.

Ceiling HT. Downrod L.	9'-10' 12"	10'-11' 18"	11'-12' 24"	12'-14' 36"	13'-15' 48"	14'-16' 60"	15'-17' 72"
Brushed Nickel	P2603-09	P2604-09	P2605-09	P2606-09	P2607-09	P2608-09	P2609-09
Polished Chrome	P2603-15	P2604-15	P2605-15	P2606-15	P2607-15	P2608-15	P2609-15
Antique Bronze	P2603-20	P2604-20	P2605-20	P2606-20	P2607-20	P2608-20	P2609-20
Matte White	P2603-28	P2604-28	P2605-28	P2606-28	P2607-28	-	-
White	P2603-30	P2604-30	P2605-30	P2606-30	P2607-30	P2608-30	P2609-30
Matte Black	P2603-31	P2604-31	P2605-31	P2606-31	P2607-31	-	-
Gilded Iron	P2603-80	P2604-80	P2605-80	P2606-80	P2607-80	P2608-80	P2609-80
Forged Black	P2603-80	P2604-80	P2605-80	P2606-80	P2607-80	P2608-80	P2609-80
Antique Nickel	P2603-81	P2604-81	P2605-81	P2606-81	P2607-81	P2608-81	P2609-81
Architectural Bronze	P2603-20	P2604-20	P2605-20	P2606-20	P2607-20	P2608-20	P2609-20
Galvanized	P2603-141	P2604-141	P2605-141	P2606-141	P2607-141	-	-
Graphite	P2603-143	P2604-143	P2605-143	P2606-143	P2607-143	P2608-143	P2609-143
Painted Nickel	P2603-152	P2604-152	P2605-152	P2606-152	P2607-152	-	-
Vintage Brass	P2603-163	P2604-163	P2605-163	P2606-163	P2607-163	-	-
Blistered Iron	P2603-171	P2604-171	P2605-171	P2606-171	P2607-171	-	-

Downrod Selection Guide

Allow at least 7 feet (84 in.) from the floor to the bottom of the fan, with 8 or 9 feet being the ideal above-floor placement.

**Average length downrod, included with each fan.*



Remotes and Wall Controls



P2662-01 Fan/Light Remote
2.37" L, 0.87" D, 4.5" ht.
Universal remote operates three fan speeds and full-range dimming light control. Includes canopy receiver and wall storage bracket. Will work with LED lamps and modules. Featuring four “dip” switches and 16 code options to avoid the chance of interference from other remotes.



P2667-031 WiFi Fan/Light Remote
1.75" L, 0.5" D, 4.37" ht.
Universal WiFi remote control for AC motor fans. Control your ceiling fan or light kit via WiFi from anywhere. Pairs with Alexa, Google Home, or app on your phone or tablet. Voice control the fan with three speeds and the light with full range dimming. App control the fan with three speeds or four timer selections or full range dimming control of the light. Can be controlled with the hand held remote included with the kit.



P2663-01 Fan/Light Remote
1.75" L, 0.5" D, 4.37" ht.
Universal remote with two, four or eight-hour timer option, operates three fan speeds and full-range dimming light control. Includes canopy receiver and wall storage bracket. Will work with LED lamps and modules. Featuring many code combination options to avoid the chance of interference from other remotes.



P2618-01 Fan/Light Remote
2.12" L, 1.12" D, 4.75" ht.
Provides fan speed and light control from convenient hand-held remote. Compatible with non-dimmable compact fluorescent lamps. For single pole applications. Receiver fits in fan canopy.



P2661-01 Universal Fan/Light Remote
2.75" L, 0.87" D, 4.56" ht.
Provides fan speed and full range light dimming control from a convenient hand held remote control. For single pole applications. Includes a wall plate for added storage convenience. Receiver fits in the fan canopy.



P2665-30 White
Universal remote includes a wall mount transmitter, ideal for multi-family applications, that operates three fan speeds and full-range dimming light control. Includes canopy receiver and wall storage bracket. Will work with LED lamps and modules. Featuring four “dip” switches and 16 code options to avoid the chance of interference from other remotes.



P2631-30 White
Full-function wall control transmitter (receiver sold with ceiling fan). Use with, or in place of, hand-held remote included with fans that have a downlight. Includes switch plate cover.



P2630-30 White
Four-speed fan wall control with full-range light dimmer. Fits single-gang wall box; requires two circuits. Includes switch plate cover. Not for use with multiple fans.



ENERGY INFORMATION



P2613-30 White
Four-speed fan wall control. Includes switch plate cover. Not for use with multiple fans.



FEATURES



P2673-01 Unfinished LAMPING
DC Fan WiFi Module
Add the WiFi module to your Ryne or 52" Springer ceiling fan for control at your fingertips. You can easily control your fan with a hand-held remote; or a smart phone, tablet, voice assistant (Amazon Alexa and Google Home) via the Smart By Bond app. 2" L, 2" D, 0.9" ht.

45° Canopies

P2666-09 Brushed Nickel
6.62" dia., 4" ht.



P2666-15 Polished Chrome
6.62" dia., 4" ht.



P2666-30 White
6.62" dia., 4" ht.



P2666-31M Matte Black
6.62" dia., 4" ht.



P2666-129 Architectural Bronze
6.62" dia., 4" ht.



P2666-143 Graphite
6.62" dia., 4" ht.




This accessory is for use with any Progress Lighting ceiling fans with a hanging weight of 25 lbs or less. Includes ceiling bracket, canopy, hanger ball, trim ring, and CTC mounting hardware. The only fans that can be CTC mounted are P2501, P2503, P2521, P2536, and P2531.



Featuring Freestone

Cross Reference Chart

Here's where you'll find the specifications you'll need to purchase the perfect fan for your space. Search by Model Number or Collection Name.



Model #	Collection Name	Motor	Motor Type: AC or DC	Fan Diameter	Blade Pitch	Dimensions				Includes downrod	Accepts Longer Downrods	Energy Star	Remotes		P2663-01	P2618-01	P2667-31 WiFi Remote Control	P2665-30	P2631-30	P2630-30	P2613-01	Universal Light Kit
						A	B	C	D				P2661-01	P2662-01								
P2500	Builder	153 X 10	AC	42"	12°	12.25"	9.65"	9.5"	5.13"	Yes	Yes	No	X	X	X	X	X	X		X	X	X
P250000	Springer	DC-165	DC	60"	22°	17.38"	13.19"	8.38"	6.06"	Yes	Yes	No										
P250002	Farris	DC-125N	DC	60"	18°-13°	15.63"	12.5"	7.5"	5.13"	Yes	Yes	No										
P250003	Kaysville	178 X 22	DC	56"	15°	17.25"	13.25"	9.94"	6.44"	Yes	No	No										
P250007	Claret	153 X 20	AC	54"	14°	15.13"	10.50"	7.88"	5.88"	Yes	Yes	No	X	X	X	X	X		X	X		
P250008	Drift	153 X 12	AC	32"	13°	14.38"	11.75"	9.25"	5.9"	Yes	Yes	No	X	X	X	X	X		X	X		X
P250009	Alleron	178 X 12	DC	56"	15°	15.94"	11.38"	9.31"	5.88"	Yes	Yes	No										
P250011	Midvale	188 X 25	AC	56"	13°	20.88"	12.81"	10.06"	6.44"	Yes	Yes	No	X	X	X	X	X		X	X		
P250012	Gulliver	N/A	AC	23"	N/A	18.13"	12.81"	5.75"	7.31"	Yes	Yes	No	X	X	X	X	X		X	X		
P250016	Edgefield	DC-125N	DC	52"	13°	14.44"	12.5"	11.0"	5.18"	Yes	Yes	Yes										X
P250021	Glenfalls	188 X 22	AC	56"	13°	14.88"	12.88"	8.75"	5.18"	Yes	Yes	No	X	X	X	X	X		X	X		
P250022	Chapin	188 X 22	AC	54"	14°	15.88"	14.45"	9.75"	5.18"	Yes	Yes	No	X	X	X	X	X		X	X		X
P250024	Bedwin	DC-125N	DC	54"	14°	15.44"	12.25"	8.69"	5.18"	Yes	Yes	No										X
P250026	Arlo	DC153-20NS	DC	60"	13°	18.56"	14.0"	8.25"	5.18"	Yes	Yes	No										
P250028	Lindale	153 X 18	AC	52"	13°	11.19"	8.0"	8.25"	5.96"	No	Yes	No	X	X	X	X	X		X	X		
P250030	Huff	DC168-25NS	DC	96"	14°	15.44"	12.0"	11.63"	6.25"	Yes	No	No										X
P250034	Alfresco	188 X 15	AC	54"	13°	19.25"	11.88"	12.0"	5.94"	Yes	Yes	No	X	X	X	X	X		X	X		
P250036	Albin	172 X 17	AC	54"	13°	15.63"	10.62"	11.01"	6.31"	Yes	Yes	No	X	X	X	X	X		X	X		
P250058	Braden	153 X 15	AC	44"	13°	9.81"	7.23"	7.70"	7.70"	No	Yes	No	X	X	X	X	X		X	X		
P250059	Vernal	156 X 12	DC	60"	12°	14.25"	9.60"	N/A	7.00"	Yes	Yes	No										
P250060	Ryne	156 X 8	DC	52"	12°	13.63"	9.60"	N/A	7.00"	Yes	Yes	No										
P250062	Edwidge	100 X 30	DC	52"	13°	13.55"	7.35"	N/A	5.75"	Yes	Yes	No										
P250063	Willacy	100 X 30	DC	48"	13°	14.52	12.78"	6.14"	6.87"	No	No	No										
P250065	Springer 52"	165NL	DC	52"	22°	17.38"	13.19"	8.38"	6.06"	Yes	Yes	No										
P250066	Air Pro E Star	172 X 17	AC	52"	12°	13.06"	10.02"	11.0"	5.87"	Yes	Yes	Yes	X	X	X	X	X		X	X		X
P250067	Brairwood	N/A	AC	22"	N/A	15.63"	N/A	22"	7.31"	Yes	Yes	No	X	X	X	X	X		X	X		
P250068	Belva	N/A	AC	25.25"	N/A	17.75"	N/A	25.25"	7.31"	Yes	No	No	X	X	X	X	X		X	X		
P250069	Manvel	100 X 30	DC	60"	13°	11.13"	10.87"	7.36"	6.31"	Yes	Yes	No										
P250070	Kennedale	153 X 25	DC	72"	12°	18.05"	16.50"	13.0"	6.31"	Yes	Yes	No										X
P250071	Spicer	178 X 12	DC	54"	28°	11.56"	8.00"	11.00"	6.44"	Yes	Yes	No										
P250072	Kasota	178 X 12	DC	56"	12°	15.00"	12.25"	9.75"	6.44"	Yes	Yes	No										
P250073	Mesilla	178 X 22	DC	60"	18°	14.25"	8.19"	11.81"	6.44"	Yes	Yes	No										
P250074	Carrollwood	178 X 12	DC	56"	13°	18.00"	13.09"	8.06"	6.44"	Yes	Yes	No										
P250076	Trevina V	172 X 17	AC	52"	12°	16.56"	11.93"	9.19"	5.88"	Yes	Yes	Yes	X	X	X	X	X		X	X		
P250077	Air Pro E Star	178 X 12	AC	52"	11.5°	18.69"	10.25"	11.0"	5.125"	Yes	Yes	Yes	X	X	X		X	X		X	X	X
P250078	Air Pro E Star	178 X 12	AC	52"	11.5°	16.69"	10.25"	11.0"	5.125"	Yes	Yes	Yes	X	X	X		X	X		X	X	X
P250080	Air Pro Builder	153 X 12	AC	52"	11.5°	12.56"	10.25"	11.0"	5.125"	Yes	Yes	No	X	X	X		X	X		X	X	X
P250077	AirPro E Star	172X17	AC	52"	11.5°	18.69"	10.01"	11.00"	5.125"	Yes	Yes	Yes	X	X	X	X	X		X			
P250078	AirPro E Star	172X17	AC	52"	11.5°	16.69"	10.01"	11.00"	5.125"	Yes	Yes	Yes	X	X	X	X	X		X	X		
P250080	AirPro Builder	153X12	AC	52"	11.5°	12.57"	10.01"	11.00"	5.125"	Yes	Yes	No	X	X	X	X	X		X	X		X

*Highlighted cells = Control does not include reverse function

Cross Reference Chart

Here's where you'll find the specifications you'll need to purchase the perfect fan for your space. Search by Model Number or Collection Name.

*Highlighted cells = Control does not include reverse function

Model #	Collection Name	Motor	Motor Type: AC or DC	Fan Diameter	Blade Pitch	Dimensions				Includes downrod	Accepts Longer Downrods	Energy Star	Remotes				P2667-31 WiFi Remote Control	P2665-30	P2631-30	P2630-30	P2613-01	Universal Light Kit
						A	B	C	D				P2661-01	P2662-01	P2663-01	P2618-01						
P250081	Air Pro Builder	153 X 12	AC	52"	11.5°	18.69"	10.25"	11.0"	5.125"	Yes	Yes	No	X	X	X		X	X		X	X	X
P250082	Air Pro Builder	153 X 12	AC	52"	11.5°	16.69"	10.25"	11.0"	5.125"	Yes	Yes	No	X	X	X		X	X		X	X	X
P250084	Air Pro E Star	178 X 12	AC	52"	11.5°	12.56"	10.25"	11.0"	5.125"	Yes	Yes	Yes	X	X	X		X	X		X	X	X
P250085	Air Pro Builder	153 X 12	AC	52"	11.5°	18.69"	10.25"	11.0"	5.125"	Yes	Yes	No	X	X	X		X	X		X	X	X
P250089	McLennan II	153 X 12	AC	52"	12°	14.31"	9.47"	9.21"	5.86"	Yes	Yes	No	X	X	X	X	X	X		X	X	
P250093	Trevina IV	153 X 12	AC	52"	11°	16.56"	11.85	8.03"	5.5"	Yes	Yes	No	X	X	X	X	X	X		X	X	
P250094	Upshur	153 X 17	AC	52"	14°	13.9"	11.56"	7.32"	6.31"	Yes	Yes	No	X	X	X	X	X	X		X	X	
P250095	Freestone	153 X 20	AC	52"	12°	15.0"	11.09"	12.2"	6.31"	Yes	Yes	No	X	X	X	X	X	X		X	X	
P250096	Bastrop	153 X 12	AC	26.24"	22°	12.11"	9.07"	6.87"	6.3"	Yes	Yes	No	X	X	X	X	X	X		X	X	
P250097	Schaffer II	188 X 20	AC	52"	13.5°	15.25"	12.6"	8.64"	6.3"	Yes	No	No	X	X	X	X	X	X		X	X	
P250098	Springer II	DC-165	DC	60"	22°	17.38"	13.19"	8.38"	6.06"	Yes	No	No										
P250099	Bexar	153 X 20	AC	52"	12°	10.4"	8.4"	9.3"	N/A	Yes	Yes	No	X	X	X	X	X	X		X	X	
P2501	Builder	153 X 12	AC	52"	11°	12.71"	9.58"	11.0"	5.13"	Yes	Yes	No	X	X	X	X	X	X		X	X	X
P250100	Brazas	155 X 12	DC	56"	13°	14.25"	11.56"	8.125"	5.86"	Yes	Yes	No										X
P250101	Schaal	153 X 18	AC	52"	12°	17.0"	10.6"	7.9"	6.5"	Yes	Yes	No	X	X	X	X	X	X		X	X	
P250102	Tarsus	153 X 18	DC	52"	12°	16.31"	11.125"	11.0"	5.86"	Yes	Yes	No										
P250103	Dallam	155 X 12	DC	60"	12°	14.6"	11.9"	6.7"	6.5"	Yes	Yes	No										
P250104	Tompkins	153 X 18	AC	52"	12°					Yes	Yes	No	X	X	X	X	X	X		X	X	
P2502	52" Patio Fan	153 X 17	AC	52"	11°	12.75"	10.2"	11.75"	5.13"	Yes	Yes	No	X	X	X	X	X	X		X	X	X
P2503	Performance	188 X 15	AC	52"	14°	15.25"	12.56"	12.19"	6.5"	Yes	Yes	No	X	X	X	X	X	X		X	X	X
P2521	Signature	153 X 18	AC	52"	12°	14.63"	11.5"	11.75"	6.5"	Yes	Yes	No	X	X	X	X	X	X		X	X	X
P2524	Hugger	153 X 10	AC	42"	11°	8.31"	5.5"	10.0"	10.0"	No	Yes	No								X	X	X
P2525	Hugger	153 X 13	AC	52"	11°	8.13"	5.93"	11.06"	11.06"	No	Yes	No								X	X	X
P2526	Deco Patio Fan	188 X 20	AC	52"	12°	17.38"	14.25"	12.13"	6.5"	Yes	Yes	No	X	X	X	X	X	X		X	X	X
P2530	Signature Plus	153 X 18	AC	54"	12°	15.13"	10.4"	11.8"	6.5"	Yes	Yes	No	X	X	X	X	X	X		X	X	X
P2531	North Park	153 X 18	AC	52"	12.5°	15.75"	12.7"	7.88"	6.5"	Yes	Yes	No	X	X	X	X	X	X		X	X	X
P2533	Patio Fan	153 X 18	AC	54"	12°	18.75"	13.34"	11.38"	6.5"	Yes	Yes	No	X	X	X	X	X	X		X	X	X
P2539	Signature Plus II	153 X 18	AC	54"	12°	15.3"	11.2"	11.8"	6.5"	Yes	Yes	No	X	X	X	X	X	X		X	X	
P2540	Harranvale	153 X 20	AC	54"	12°	16.38"	12.1"	12.63"	5.88"	Yes	Yes	No	X	X	X	X	X	X		X	X	
P2542	Soar	153 X 20	AC	54"	12°	14.7"	11.05"	10.1"	5.88"	Yes	Yes	No	X	X	X	X	X	X		X	X	
P2544	Graceful	153 X 20	AC	54"	12°	16.38"	11.5"	9.75"	5.88"	Yes	Yes	No	X	X	X	X	X	X		X	X	
P2546	Ellwood	212 X 25	AC	68"	17°	16.7"	11.5"	9.63"	5.88"	Yes	Yes	No	X	X	X	X	X		X	X	X	
P2548	Fresno	188 X 25	AC	60"	14°	17.2"	10.8"	12.75"	5.88"	Yes	Yes	No	X	X	X	X	X		X	X		
P2550	Vast	DC - 165	DC	72"	14°	16.75"	13.67"	8.25"	5.13"	Yes	No	No										
P2552	Billows	153 X 15	AC	52"	12°	17.5"	11.18"	9.1"	5.88"	Yes	Yes	No	X	X	X	X	X	X		X	X	
P2553	Trevina II	153 X 15	AC	52"	12°	15.75"	10.8"	9.44"	5.88"	Yes	Yes	No	X	X	X	X	X	X		X	X	
P2554	Gaze	172 X 17	AC	60"	12°	13.13"	10.71"	6.88"	5.13"	Yes	Yes	No	X	X	X	X	X	X		X	X	
P2555	Trevina II	153 X 12	AC	44"	12°	15.68"	12.21"	8.38"	5.88"	Yes	Yes	No	X	X	X	X	X	X		X	X	
P2556	Trevina II	153 X 15	AC	52"	12°	15.75"	10.8"	9.44"	5.88"	Yes	Yes	No	X	X	X	X	X	X		X	X	
P2560	Caleb	212 X 25	AC	68"	17°	18.0"	11.98"	13.75"	5.88"	Yes	Yes	No	X	X	X	X	X		X	X	X	
P2562	Lakehurst	188 X 25	AC	60"	13.5°	15.69"	13.5"	11.25"	5.9"	Yes	No	No	X	X	X	X	X	X		X	X	X
P2564	Montague	188 X 25	AC	60"	13°	17.63"	12.28"	9.95"	5.9"	Yes	Yes	No	X	X	X	X	X	X		X	X	

Continued on following spread.


Cross Reference Chart

Here's where you'll find the specifications you'll need to purchase the perfect fan for your space. Search by Model Number or Collection Name.

*Highlighted cells = Control does not include reverse function

Model #	Collection Name	Motor	Motor Type: AC or DC	Fan Diameter	Blade Pitch	Dimensions				Includes downrod	Accepts Longer Downrods	Energy Star	Remotes				P2667-31 WiFi Remote Control	P2665-30	P2631-30	P2630-30	P2613-01	Universal Light Kit
						A	B	C	D				P2661-01	P2662-01	P2663-01	P2618-01						
P2568	Kudos	172 X 17	AC	52"	13°	17.63"	13.11"	9.69"	5.95"	Yes		No	X	X	X	X	X	X		X	X	
P2570	Spades	DC188-10	DC	56"	22°	18.13"	16.67"	8.08"	6.42"	Yes		No										
P2572	Vox	153 X 18	AC	52"	12°	11.63"	7.13"	11.41"	9.91"	No		No	X	X	X	X	X		X	X	X	
P2574	Whirl	188 X 25	AC	60"	12°	15.88"	11.93"	10.01"	5.91"	Yes		No	X	X	X	X	X	X		X	X	
P2576	Smyrna	153 X 20	AC	52"	12°	19.44"	10.75"	11.94"	5.88"	Yes		No	X	X	X	X	X	X		X	X	
P2578	Tempt	153 X 18	AC	52"	12°	16.19"	9.94"	10.25"	5.88"	Yes		No	X	X	X	X	X	X		X	X	
P2582	Gust	172 X 20	AC	54"	13.5°	16.0"	13.13"	9.95"	5.91"	Yes		No	X	X	X	X	X	X		X	X	
P2584	Greer	153 X 20	AC	54"	12°	21.56"	11.61"	7.88"	5.88"	Yes		No	X	X	X	X	X	X		X	X	
P2586	Glandon	188 X 25	AC	60"	12°	17.06"	13.09"	9.06"	5.88"	Yes		No	X	X	X	X	X	X		X	X	
P2588	Braden	172 X 20	AC	56"	13°	9.81"	7.23"	7.70"	7.70"	No		No	X	X	X	X	X		X	X	X	
P2592	Oriole	172 X 20	AC	60"	21°	14.56"	12.5"	9.17"	6.0"	Yes		No	X	X	X	X	X	X		X	X	
P2594	Sanford	N/A	AC	23"	31.7°	17.69"	13.13"	22.81"	5.12"	Yes		No	X	X	X	X	X	X		X	X	
P2599	Uni Pack	153 X 12	AC	52"	11°	17.56"	9.58"	11.0"	5.13"	Yes		No	X	X	X	X	X	X		X	X	X


Fan Blade Finishes



American Walnut




Brushed Nickel



Dark Walnut



Antique Black



Cherry



Distressed Ebony



Antique Bronze



Chestnut




Distressed Walnut




Antique Wood




Classic Walnut



Distressed White




Architectural Bronze




Cottage White



Driftwood




Black




Dark Bamboo




Galvanized



Blistered Iron



Dark Cherry



Graphite

Fan Blade Finishes




Gray Weathered Wood



Pewter



Walnut



Koa Woodgrain




Rustic Charcoal



Washed Oak



Medium Cherry



Salt Aged Cypress



White Barnwood



Natural Cherry



Silver



White Washed



Oak



Toasted Oak



All finish representations are part of Progress Lighting's comprehensive design and specification program. Through extensive research, these finishes have been carefully chosen to complement all Progress Lighting products, including our extensive range of materials and accessory options.

These finish representations match actual finish colors as accurately as possible, and while every effort has been made to render colors accurately, they may vary slightly from the actual product, especially hand-painted finishes due to the nature of hand craftsmanship.

Icon Guide



Products referencing this logo meet the energy efficiency requirements for ceiling fans and or ceiling fan light kits set forth in ENERGY STAR® product specifications. Please refer to www.energystar.gov for specific product qualifications and list of certified products.



Please note indoor only (dry location) fans should only be used indoors. Even if an outdoor area or screened-in porch is covered, the motor and the blades can be affected when exposed to humidity. You can, however, “bring the outdoors inside” – as using outdoor ceiling fans are perfectly acceptable to use in interior spaces.



If you are selecting a ceiling fan for a space that is outdoors and under a roof, i.e. any covered porches; you should select either a damp rated or wet listed fan. Damp location fans may also be used indoors.



If the fan comes directly into contact with water, you'll need to ensure that the ceiling fan has a “wet” listing. Ceiling fans designed for damp or wet locations feature elements, such as moisture-resistant motors and all weather blades. Wet location fans may also be used indoors.



This marking indicates fixtures that have an integrated LED or replaceable LED module or LED lamps that has been tested and listed in the California Appliance Database. Check for certified lamps, fixtures or LED light engines by searching the MAEDBS database. Go to cacertappliances.enegy.ca.gov



DC motor ceiling fan feature high torque for increased air movement, whisper quiet operation, and greater energy efficiency than AC motors



Products comply with the California Appliance Efficiency Regulations. Certified products are listed on the appliance efficiency database found at www.appliances.energy.ca.gov.



Products with this icon are Dark-Sky Friendly: they are certified by the International Dark-Sky Association to minimize glare while reducing light trespass and skyglow (they don't pollute the night sky.)



The products with this logo have passed the cUL requirements and are available for sale in Canada. These products include the additional safety features needed to comply with the regulations in Canada. Items with the icon are listed with NRCan.



Products with this icon are WiFi compatible and may be controlled with WiFi when one of the following controls is added;

- AC Motor fans can add the P2667-31 WiFi remote control
- DC Motor fans that are WiFi compatible can add the P2673-01 WiFi module.

With the addition of one of the above controls, you may easily control your fan or light with your smart phone, tablet, voice controls, or hand held remote. Use the Smart by Bond technology to control on/off function of the fan and the light kit along with full range dimming and fan speed control.



Products with this icon have WiFi Control Included. Easily control your fan with your smart phone, tablet, voice controls, or a hand held remote. Use the Smart by Bond technology to control on/off function of the fan and the light kit along with full range dimming and fan speed control.



Products with this icon have a feature that allows for selectable CCT (correlated color temperature)

Warranty

For more details regarding product warranty coverage, please consult a qualified Progress Lighting distributor or visit:

www.progresslighting.com/warranty

Where to Buy

To purchase Progress Lighting products from one of our authorized dealers visit:

www.progresslighting.com/where-to-buy

Product Index

P2500	143	P250085	137
P250000	47	P250089	117
P250002	75	P250093	119
P250003	49	P250094	163
P250007	95	P250095	51
P250008	144	P250096	35
P250009	55	P250097	165
P250011	167	P250098	157
P250012	39	P250099	145
P250016	140	P2501	130, 131
P250021	97	P250100	115
P250024	89	P250101	159
P250026	71	P250102	81
P250028	150	P250103	79
P250030	67	P250104	101
P250034	173	P2502	185
P250036	179	P2503	132
P250058	148	P2521	127
P250059	29	P2524	152
P250060	31	P2525	151
P250061	57	P2526	183
P250062	169	P2530	126
P250063	33	P2531	133
P250065	45	P2533	184
P250066	139	P2539	125
P250067	41	P2540	113
P250068	37	P2542	99
P250069	73	P2544	111
P250070	181	P2546	63
P250071	61	P2548	107
P250072	161	P2550	69
P250073	53	P2552	105
P250074	77	P2553	123
P250075	59	P2554	83
P250076	121	P2555	122
P250077	141	P2556	124
P250078	142	P2560	65
P250080	128, 129	P2562	182
P250081	136	P2564	177
P250082	135	P2570	85
P250084	138	P2572	149

Product Index

P2574	171	P2663	195
P2576	175	P2665	195
P2578	109	P2666	196
P2582	103	P2667	195
P2584	93	P2668	122
P2586	91	P2669	150
P2588	146, 147	P2673	195
P2592	87		
P2594	43		
P2599	134		
P2600	193		
P260000	189		
P260002	189		
P260004	189		
P2601	188		
P2602	191		
P2603	194		
P2604	194		
P2605	194		
P2606	194		
P2607	194		
P2608	194		
P2609	194		
P2610	193		
P2611	188		
P2612	192		
P2613	195		
P2618	195		
P2628	192		
P2630	195		
P2631	195		
P2636	188		
P2642	191		
P2643	191		
P2644	193		
P2645	190		
P2650	190		
P2654	190		
P2659	192		
P2661	195		
P2662	195		

Equip. Educate. Excite.

These three words define the mission of Progress Lighting. Flip through our catalog, and you'll quickly see how we equip you with the education to make all your exciting design dreams come true. Not sure where to start? Whether you're browsing our catalog or visiting our website, Progress is at your service to help you envision where and how to use our products.







Experience Progress

Learn how lighting can totally transform a space. Experience Progress features beautiful room images from our builder partners, design firms, social media fans and influencers bringing the Progress Lighting story to life. Visit www.progresslighting.com/experienceprogress

Our Blog

Explore our blog for even more design inspiration, product integration and trend guidance to make your home into a haven of livable luxury. See www.progresslighting.com/blog

Be Inspired

-  @ProgressLtg
-  @ProgressLtg
-  @ProgressLighting
-  @ProgressLtg
-  Progress Lighting
-  Progress-Lighting



A proud member of the Hubbell family.

PROGRESS LIGHTING
701 Millennium Boulevard
Greenville, South Carolina
29607

progresslighting.com

