


SELECTABLE CCT LED LUMINAIRES

Progress Lighting has expanded its popular Intrinsic, Hide-a-lite & Everlume portfolio of LED luminaires to include new products with an integrated Correlated Color Temperature adjustment feature that enables for selection of CCT.



5 CCT SELECTABLE	2700K
	3000K
	3500K
	4000K
	5000K



Intrinsic Recessed LED

EYEBALL



P800018-028-CS

Satin White
7-3/4" dia., 3-15/16" ht.
8w integrated LED,
2700K, 3000K, 3500K, 4000K, 5000K,
90CRI, 750 lumens (at 3000K).



COMPATIBLE RECESSED HOUSINGS

P851-ICAT
P1851-ICAT
P1841-ICAT
P821-FBFC
P871-LED-001
P1871-LED-001
P87-AT
P87-ATQC
P187-TG
P86-TG
P186-TG
P821-FB

BAFFLE



P800019-028-CS

Satin White
7-3/8" dia., 3-7/16" ht.
8w integrated LED,
2700K, 3000K, 3500K, 4000K, 5000K,
90CRI, 771 lumens (at 3000K).



COMPATIBLE RECESSED HOUSINGS

P851-ICAT
P1851-ICAT
P1841-ICAT
P871-LED-001
P1871-LED-001
P86-TG
P186-TG
P87-AT
P87-ATQC
P187-TG

Everlume™ Vanity LED



P300306-009-CS

16" LINEAR BATH

P300304-009-CS Brushed Nickel

P300304-028-CS Satin White

16" W., 5" ht.

Extends 1-3/8", H/CTR 2-1/2".

17w Integrated LED, 3000K, 4000K, 90 CRI, 1386 delivered lumens.

24" LINEAR BATH

P300305-009-CS Brushed Nickel

P300305-028-CS Satin White

24" W., 5" ht.

Extends 1-3/8", H/CTR 2-1/2".

26w Integrated LED, 3000K, 4000K, 90 CRI, 2182 delivered lumens.

32" LINEAR BATH

P300306-009-CS Brushed Nickel

P300306-028-CS Satin White

32" W., 5" ht.

Extends 1-3/8", H/CTR 2-1/2".

32w Integrated LED, 3000K, 4000K, 90 CRI, 2808 delivered lumens.

FINISHES

- Brushed Nickel - 009
- Satin White - 028

LED FEATURES

- Damp location listed.
- Flicker-free dimming with many Triac and ELV dimmers.
- 120v input voltage.
- 50,000 hour life.

All fixtures:



2 CCT SELECTABLE	3000K
	4000K

Hide-a-lite™ Undercabinet LED

HIDE-a-LITE™



P700028-028-CS

9" LED UNDERCABINET

P700024-028-CS White

9" L., 3-1/4" W., 1-1/8" ht.

One 4w integrated LED, 2700K, 3000K, 3500K, 4000K, 5000K, 90CRI, 228 delivered lumens (at 3000K).

12" LED UNDERCABINET

P700025-028-CS White

11-1/2" L., 3-1/4" W., 1-1/8" ht.

One 4.5w integrated LED, 2700K, 3000K, 3500K, 4000K, 5000K, 90CRI, 299 delivered lumens (at 3000K).

18" LED UNDERCABINET

P700026-028-CS White

17-1/2" L., 3-1/4" W., 1-1/8" ht.

One 6.5w integrated LED, 2700K, 3000K, 3500K, 4000K, 5000K, 90CRI, 457 delivered lumens (at 3000K).

24" LED UNDERCABINET

P700027-028-CS White

23-1/2" L., 3-1/4" W., 1-1/8" ht.

One 8.5w integrated LED, 2700K, 3000K, 3500K, 4000K, 5000K, 90CRI, 608 delivered lumens (at 3000K).

36" LED UNDERCABINET

P700028-028-CS White

35-1/2" L., 3-1/4" W., 1-1/8" ht.

One 11.5w integrated LED, 2700K, 3000K, 3500K, 4000K, 5000K, 90CRI, 859 delivered lumens (at 3000K).

All fixtures:



5 CCT SELECTABLE	2700K
	3000K
	3500K
	4000K
	5000K



CCT selector switch



Access plate



Quick connectors