



2019 CALIFORNIA TITLE 24, PART 6 RESIDENTIAL LIGHTING PRODUCT GUIDE

JUNE 2019



CALIFORNIA TITLE 24, PART 6 RESIDENTIAL LIGHTING

Title 24 is California's building energy efficiency standard. It is required to be met for any building that requires a permit.

Lighting installations in all newly constructed buildings and additions and alterations of existing buildings must meet applicable Title 24 requirements in order to receive an occupancy permit. Compliance is verified by building inspectors.

Title 24 is updated every 3 years by the California Energy Commission (CEC).

- T24 2016 is the current version
- T24 2019 takes effect beginning January 2020

WHAT HAS CHANGED SINCE TITLE 24 2016?

CALIFORNIA TITLE 24, PART 6 NON-RESIDENTIAL LIGHTING

Includes certain mandatory measures such as:

- Area controls to operate lighting
- Multi-level lighting requirements for dimming based on square footage and qty of luminaires/lamps
- Daylighting controls capable of shedding load to eliminate energy waste

Includes energy budget with two options:

- Prescriptive approach: based on LPD (lighting power density)
- Performance approach: combined measures based on TDV (time dependent valuation)

CALIFORNIA TITLE 24, PART 6 RESIDENTIAL LIGHTING

Includes certain mandatory measures such as:

- All lighting installed in residential construction must be "High Efficacy"
- All luminaires must include a compliant light source at the time of inspection
- LED light sources do not necessarily need to be included in the packaging with the fixture
- LED light sources or luminaires must be registered with the state and appropriately marked "JA8-YYYY" or "JA8-YYYY-E" (elevated temp/enclosed rated)
- YYYY = 2016 or 2019

RESIDENTIAL REQUIREMENTS ARE PRODUCT/APPLICATION SPECIFIC, NON-RESIDENTIAL REQUIREMENTS CONSIDER THE ENTIRE BUILDING AS THE APPLICATION

RESIDENTIAL SCOPE

All indoor and outdoor lighting attached to single family buildings, within dwellings in multi-family buildings. Residential spaces in non-residential buildings include:

- Single Family Buildings, indoor and outdoor lighting
- High Rise multifamily residential units
- Hotel and motel guest rooms
- Fire station dwellings
- Dormitory and senior housing dwellings
- Sheds and garages on residential sites



TERMS / SYMBOLS

T24

Any fixture with a socket (other than recessed housings) may be used to support compliance when a JA8 listed light bulb is installed. The light bulb must be marked either as: JA8-YYYY or JA8-YYYY-E (YYYY = 2016 or 2019). The E indicates that the bulb has been tested and meets requirements established for use in enclosed fixtures (ex: flush mounts)

JA8

Any fixture that has an integrated LED or replaceable LED light engine that has been tested and listed in the California Appliance Database. Check for certified bulbs or fixtures by searching the MAEDBS database.




Fixtures that support compliance when used in outdoor lighting applications

2019 CALIFORNIA TITLE 24, PART 6 - RESIDENTIAL LIGHTING TERMS & REQUIREMENTS



RECESSED LIGHTING

Recessed Downlight housings must be rated for direct contact with insulation (Type IC), as well as be labeled and certified airtight with air leakage less than 2.0 CFM at 75 Pascals when tested with accordance with ASTM E283. The opening must be sealed with a gasket or caulk between the housing and ceiling. **The recessed housing shall not contain a screw based socket.** In addition, the light source must be high efficacy and comply with Reference Joint Appendix JA8. It must also be marked "JA8-2016" or "JA8-2019".



CONTROL REQUIREMENTS BY SPACE

At least one luminaire in the bathroom, garage, laundry room and utility room must be controlled by a vacancy sensor. Preset scene controllers and EMCS can take the place of dimmers as long as the functionality meets code requirements.



SCREW-BASE LUMINAIRES

All luminaires that utilize a screw-based socket must contain lamps that comply with JA8 high efficacy requirements. All enclosed, screw-base luminaires, must utilize a compliant lamp rated for elevated temperatures.



OUTDOOR LIGHTING

Per Table 150.0-A, light sources, including LED, installed in outdoor luminaires do not have to meet JA8.



OUTDOOR LIGHTING: CONTROL SWITCH

Luminaires providing outdoor lighting shall meet the following requirements: Controlled by a manual ON and OFF switch* that permits the automatic actions of the following:

- Photocell and either a motion sensor, or automatic time switch control
- Controlled by an astronomical time clock control.

** Refer to standard for additional requirements*



CONSTRUCTION & INSPECTION

The builder must now provide new homeowners with a schedule that includes a list of installed lamps and luminaires.





Table of Contents

8	RECESSED & SURFACE MOUNTS	11	UNDERCABINET	14	CLOSE-TO-CEILING
---	---------------------------	----	--------------	----	------------------



25	CEILING FANS & LIGHT KITS	34	BATH COLLECTIONS
----	---------------------------	----	------------------



51	OUTDOOR	77	INTERIOR DECORATIVE	89	UTILITY
----	---------	----	---------------------	----	---------



95	INDEX
----	-------



Featuring Recessed Lighting (image: Carrington Homes)


RECESSED & SURFACE MOUNTS

EDGE LIT RECESSED Brushed Nickel p.17	EDGE LIT RECESSED Antique Bronze p.17	EDGE LIT RECESSED White p.17	EDGE LIT RECESSED Black p.17	SLIM-LINE SURFACE MT Satin White p.18
				
EDGE LIT FLUSHMOUNT White p.18	SURFACE MOUNT Brushed Nickel p.19	SLIM-LINE SURFACE MT Antique Bronze p.19	SLIM-LINE SURFACE MT Antique Bronze p.19	
				






UNDERCABINET

LED UNDERCABINET White p.21	LED UNDERCABINET Antique Bronze p.21	LED PUCK White p.22	LED PUCK Antique Bronze p.22	LED TAPE White p.24
				

CLOSE-TO-CEILING

BEZEL LED Brushed Nickel p.27	BEZEL LED Antique Bronze p.27	INSPIRE LED Brushed Nickel p.28	INSPIRE LED Antique Bronze p.28	INSPIRE LED Brushed Nickel p.28
				
INSPIRE LED Graphite p.28	ELEVATE LED Brushed Bronze p.29	ELEVATE LED Polished Chrome p.29	LED ALABASTER Brushed Nickel p.29	LED ALABASTER Antique Bronze p.29
				
LED FLUSH MOUNT Brushed Nickel p.30	LED FLUSH MOUNT Antique Bronze p.30	LED FLUSH MOUNT Polished Chrome p.31	FINESSE LED Vintage Gold p.32	FINESSE LED Metallic Silver p.32
				
FINESSE LED Graphite p.32	FRESNEL LED Brushed Bronze p.32	FRESNEL LED Polished Chrome p.32	FRESNEL LED Oil Rubbed Bronze p.32	LED LINEN Brushed Nickel p.33
				
LED SQUARE FLUSH MT Brushed Nickel p.34	LED SQUARE FLUSH MT Antique Bronze p.34	LED SQUARE GLASS Brushed Nickel p.34	LED SQUARE GLASS Antique Bronze p.34	OPAL-LINEN LED Brushed Nickel p.35
				
OPAL-LINEN LED Antique Bronze p.35	MAIER LED Brushed Nickel p.36	MAIER LED Antique Bronze p.36	MAIER LED White p.36	
				

INDOOR FANS - INTEGRATED LIGHT

BRADEN p.38	FARRIS p.38	FRESNO p.38	GAZE p.38	GLANDON p.38
				
GRACEFUL p.38	GUST p.38	HARRANVALE p.38	KUDOS p.38	ORIOLE p.38
				
SIGNATURE PLUS II p.38	SOAR p.38	TEMPT p.38	TREVINA II p.38	VAST p.38
				
VERADA p.38	VOX FAN p.38			
				

INDOOR FANS - LIGHT KIT ADAPTABLE

NORTH PARK p.39	PERFORMANCE p.39	SIGNATURE p.39	SIGNATURE PLUS p.39
			

OUTDOOR FANS - INTEGRATED LIGHT

EDISTO p.39	MONTAGUE p.39	SMYRNA p.39	WHIRL p.39
			

OUTDOOR FANS - LIGHT KIT ADAPTABLE

52" PATIO p.39	54" PATIO p.39	DECORATIVE PATIO p.39
		




LIGHT KITS

SCHOOLHOUSE Antique Bronze p.40	SCHOOLHOUSE White p.40	SCHOOLHOUSE Forged Black p.40	SCHOOLHOUSE Galvanized p.40	SCHOOLHOUSE Brushed Nickel p.40
				
ASHMORE Antique Bronze p.40	TORINO Brushed Nickel p.41	TORINO Antique Bronze p.41	TORINO Forged Black p.41	TORINO Forged Bronze p.41
				
NORTH PARK Brushed Nickel p.41	NORTH PARK Antique Bronze p.41	UNIVERSAL BOWL Polished Chrome p.42	UNIVERSAL BOWL Brushed Nickel p.42	UNIVERSAL BOWL White p.42
				

LIGHT KITS

UNIVERSAL BOWL Graphite p.42	UNIVERSAL BOWL Antique Bronze p.42	AIRPRO Antique Bronze p.42	AIRPRO White p.42	AIRPRO Brushed Nickel p.42
				
LED LIGHT KITS Antique Bronze p.43	LED LIGHT KITS White p.43	LED LIGHT KITS Brushed Nickel p.43	TRINITY Antique Bronze p.43	TRINITY Forged Bronze p.43
				
TRINITY White p.43	TRINITY Brushed Nickel p.43	LOW PROFILE Antique Bronze p.44	LOW PROFILE White p.44	LOW PROFILE Polished Chrome p.44
				
LOW PROFILE Graphite p.44	LOW PROFILE Brushed Nickel p.44	LOW PROFILE Forged Black p.44	WISTEN Brushed Nickel p.44	WISTEN Antique Bronze p.44
				
ALABASTER Polished Chrome p.45	ALABASTER White p.45	ALABASTER Graphite p.45	ALABASTER Brushed Nickel p.45	ALABASTER Antique Bronze p.45
				
GATHER, BRAVO, JOY Brushed Nickel p.45	GATHER, BRAVO, JOY Antique Bronze p.45			
				


BATH COLLECTIONS

BLANCO LED Faux White Marble p.47	BEAM LED Brushed Nickel p.48	BEAM LED Polished Chrome p.48	BEAM LED Architectural Bronze p.48	VOLO LED Brushed Nickel p.50
				
CAPELLI LED Polished Chrome p.50	COLONNADE LED Brushed Nickel p.52	COLONNADE LED Polished Chrome p.52	CONCOURSE LED Brushed Nickel p.54	MITER LED Brushed Nickel p.55
				
PARALLEL LED Brushed Nickel p.56	PARALLEL LED Polished Chrome p.56	PARALLEL LED Architectural Bronze p.56	PHASE 1.1 LED Brushed Nickel p.58	PHASE 1.2 LED Brushed Nickel p.59
				
PHASE 2.1 LED Brushed Nickel p.60	PHASE 2.2 LED Brushed Nickel p.61	PONDER LED Antique Bronze p.62	PONDER LED Graphite p.62	
				

OUTDOOR

WHITACRE LED Antique Bronze p.64	LEAWOOD LED White p.65	LEAWOOD LED Black p.65	NORTHAMPTON LED Architectural Bronze p.66	NORTHAMPTON LED Black p.66
				

OUTDOOR

ARRIVE LED Black p.67	ENDORSE LED Black p.68	DERBY LED Antique Bronze p.69	WISH LED Antique Bronze p.70	WISH LED Black p.70
				
CALLAHAN LED Antique Bronze p.71	CALLAHAN LED Antique Pewter p.71	BROOKSIDE LED Brushed Nickel p.72	BROOKSIDE LED Copper p.72	BROOKSIDE LED Gilded Iron p.72
				
BROOKSIDE LED Antique Nickel p.72	DISTRICT LED Antique Bronze p.73	DISTRICT LED Metallic Gray p.73	EAST HAVEN LED Antique Bronze p.74	EAST HAVEN LED Black p.74
				
WESTPORT LED Antique Bronze p.75	WESTPORT LED Black p.75	BELL LED Antique Bronze p.76	BELL LED Textured Graphite p.76	PIER 33 LED Black p.76
				
LED BULKHEADS White p.77	LED BULKHEADS Black p.77	MILFORD LED Black p.78	DIE-CAST LED Black p.78	ANSON LED Architllectual Bronze p.79
				
VALERA LED Architectural Bronze p.79	STRATA White p.80	STRATA Black p.80	STRATA Antique Bronze p.80	STRATA Metallic Gray p.80
				


OUTDOOR

CORNICE LED Black p.80	CORNICE LED Antique Bronze p.80	CORNICE LED Metallic Gray p.80	Z-1010 LED Black p.81	Z-1010 LED Architectural Bronze p.81
				
Z-1020 LED Black p.81	Z-1020 LED Architectural Bronze p.81	Z-1030 LED White p.82	Z-1030 LED Black p.82	Z-1030 LED Antique Bronze p.82
				
Z-1030 LED Metallic Gray p.82	Z-1050 LED Black p.83	Z-1060 LED Black p.83	3" CYLINDER LED White p.84	3" CYLINDER LED Graphite p.84
				
3" CYLINDER LED Antique Bronze p.84	3" CYLINDER LED Satin Nickel p.84	5" CYLINDER LED White p.85	5" CYLINDER LED Black p.85	5" CYLINDER LED Antique Bronze p.85
				
5" CYLINDER LED Metallic Gray p.85	6" CYLINDER LED White p.86	6" CYLINDER LED Black p.86	6" CYLINDER LED Antique Bronze p.86	6" CYLINDER LED Metallic Gray p.86
				
ALUMINUM LED SQUARES White p.88	ALUMINUM LED SQUARES Black p.88	ALUMINUM LED SQUARES Antique Bronze p.88	ALUMINUM LED SQUARES Metallic Gray p.88	
				

INTERIOR DECORATIVE


APOGEE LED Brushed Nickel p.90	APOGEE LED Antique Bronze p.92	GLOBE LED Brushed Bronze p.94	GLOBE LED Brushed Nickel p.95	GLOBE LED Polished Chrome p.95
				
CONCOURSE LED Brushed Nickel p.96	NEAT LED Brushed Nickel p.97	NEAT LED Antique Bronze p.97	MODERNA LED Brushed Nickel p.97	GATHER LED Brushed Nickel p.98
				
GATHER LED Polished Chrome p.98	GATHER LED Antique Bronze p.98	LED SCONCE Brushed Nickel p.98	LED SCONCE Architectural Bronze p.98	INSPIRE LED Summer Linen p.99
				
INSPIRE LED Off Linen White p.99				
				

UTILITY

LED STRIP White p.101	LINEAR CLOUD LED Brushed Nickel p.101	LINEAR CLOUD LED Urban Bronze p.101	LINEAR CLOUD LED White p.101	LED TRACK Satin White p.102
				
LED TRACK Black p.102	SURFACE MOUNT LED Brushed Nickel p.103	SURFACE MOUNT LED Purban Bronze p.103	WRAP-AROUNDS White p.104	LED DRUM White p.104
				
LED DRUM Black p.104	LED CLOUD White p.104	LED LAMPS p.105	PHOTO CONTROL p.105	
				



Featuring Concourse LED



Featuring Recessed Lighting (Image: Arthur Rutenberg Homes)


Recessed & Surface Mount

LED EDGELIT RECESSED


The LED edgelit recessed downlight combines a slim, low profile design with innovative technology, aesthetics, functionality and affordability. A separate recessed housing or junction box is not required for installation. The wet location listing allows for the product to be used in many applications, including showers. The low profile downlight is ideal for many residential, multi-family, commercial and hospitality applications. The detachable driver box can be removed from the fixture and mounted remotely when installing into shallow ceiling applications. The energy efficient design provides up to a 75% energy savings and up to 50,000 hours of LED life. The edgelit recessed luminaire can dimmed down to 10%, flicker free, and is compatible with many forward phase (TRIAC) and electronic low voltage (ELV) dimmers.

FINISHES

- Brushed Nickel - 009
- Antique Bronze - 020
- White - 28
- Black - 031



DETACHED JUNCTION BOX



ATTACHED JUNCTION BOX

5" LED EDGELIT
P800004-009-30 Brushed Nickel
P800004-020-30 Antique Bronze
P800004-028-30 White
P800004-031-30 Black
5" W., 3" ht.
9.5w LED, 3000K,
90CRI, 550 delivered lumens.



P800004-009-30



P800004-028-30



P800004-020-30



P800004-031-30

7" LED EDGELIT
P800005-009-30 Brushed Nickel
P800005-020-30 Antique Bronze
P800005-028-30 White
P800005-031-30 Black
7" W., 3" ht.
13w LED, 3000K,
90CRI, 800 delivered lumens.



P800005-009-30



P800005-028-30



P800005-020-30



P800005-031-30

LED SLIM-LINE SURFACE MOUNT


The LED slim line surface mount delivers a solution for both residential and commercial markets. An integrated AC LED light engine allows for installation to 4” octagonal junction boxes and 4x1/2” ceiling pan junction boxes. The construction features a die cast aluminum heatsink for thermal management, ensuring a 50,000 hour LED lifetime. Integrated gasketing and a powder coat paint finish make the product suitable for use in wet locations. The diffused polycarbonate lens controls glare and hides LED pixilation. Spring steel mounting clips offer an easy and intuitive snap in installation. The lumen output is comparable to a 60W incandescent lamp.

FINISH
○ Satin White - 028

LED SLIM-LINE SURFACE MOUNT
P810027-028-30 Satin White
5-1/2” dia., 1-13/64” ht.
12.5w integrated LED, 3000K,
90CRI, 750 delivered lumens.



P810027-028-30



Shown installed into
1/2” ceiling pan J-box

- LED FEATURES**
- Wet location listed
 - Flicker-free dimming with many Triac and ELV dimmers
 - 120v input voltage
 - 50,000 hour life



LED EDGELIT FLUSH MOUNT

Edgelit technology creates a large glare free and evenly illuminated surface for a variety of applications for both residential and commercial applications. Offering a low profile design, LED Edgelit Flush Mount is available in four sizes: 7”, 11”, 14”, and 18” in a White finish. The integrated driver does not recess into junction box, allowing for easy installation into 4” octagonal, 4” round PVC and 4” x 1/2” ceiling pan junction boxes. LED Edgelit Flush Mount is wet location listed and offers a 50,000-hour LED life.

FINISHES
○ White - 030

7” LED EDGELIT FLUSH MOUNT
P810015-030-30 White
7” dia., 1-1/8” ht.
15w integrated LED, 3000K,
90CRI, 1000 delivered lumens.



11” LED EDGELIT FLUSH MOUNT
P810016-030-30 White
11” dia., 1-1/8” ht.
17w integrated LED, 3000K,
90CRI, 1325 delivered lumens.



14” LED EDGELIT FLUSH MOUNT
P810017-030-30 White
14” dia., 1-1/8” ht.
20w integrated LED, 3000K,
90CRI, 1550 delivered lumens.



18” LED EDGELIT FLUSH MOUNT
P810018-030-30 White
18” dia., 1-1/8” ht.
23w integrated LED, 3000K,
90CRI, 1875 delivered lumens.



- LED FEATURES**
- Wet location listed
 - Flicker-free dimming with many Triac and ELV dimmers
 - 120v input voltage
 - 50,000 hour life



P810015-030-30



P810016-030-30



P810017-030-30



P810018-030-30



LED SURFACE MOUNT ROUND

The LED surface mounts deliver a solution for both residential and commercial markets. An integrated AC LED light engine allows for installation to standard 4” octagonal junction boxes. The construction features a die cast aluminum heatsink for thermal management, ensuring a 50,000 hour LED lifetime. Integrated gasketing and a powder coat paint finish make the product suitable for use in wet locations. The diffused polycarbonate lens controls glare and hides LED pixilation. Spring steel mounting clips offer an easy and intuitive snap in installation. The lumen output is comparable to a 60W incandescent lamp.

FINISH
○ White - 28
● Antique Bronze - 020

5-1/2” ROUND
P8108-20-30K Antique Bronze
5-1/2” dia., 2-3/4” ht.
11.75w integrated LED, 3000K
90CRI, 685 delivered lumens.
Triac/forward phase dimming.



P8108-20-30K

7-1/4” ROUND
P8222-28-30K White
7-1/4” round flush mount
7-1/4” dia., 1-1/4” ht.
17w integrated LED, 3000K
90CRI, 1170 delivered lumens.



P8222-28-30K

LED DECORATIVE SURFACE MOUNT ROUND

The LED decorative surface mounts combine function and aesthetics. The Brushed Nickel finish and decorative glass ring complement the look of the room. These luminaires are a good solution for both residential and commercial markets. An integrated AC LED light engine allows for installation to standard 4” octagonal junction boxes. The construction features a die cast aluminum heatsink for thermal management, ensuring a 50,000 hour LED lifetime. Integrated gasketing and a powder coat paint finish make the product suitable for use in wet locations. The diffused polycarbonate lens controls glare and hides LED pixilation. Spring steel mounting clips offer an easy and intuitive snap in installation. The lumen output is comparable to a 60W incandescent lamp.

5-1/2” DECORATIVE ROUND
P8247-09-30K Brushed Nickel
Round with etched glass
5-1/2” round, 1-1/2” ht.
10.5w integrated LED, 3000K
90CRI, 690 delivered lumens
Triac/forward phase dimming.



P8247-09-30K

7-1/4” DECORATIVE ROUND
P8147-09-30K Brushed Nickel
Round trim with etched glass
7-1/4” dia., 1-5/8” ht.
17w LED module, 3000K
90CRI, 1035 delivered lumens.
Triac/forward phase dimming.



P8147-09-30K

FINISH
● Brushed Nickel - 09



Undercabinet

LED UNDERCABINET

The HIDE-a-LITE™ Linear undercabinet series provides the ideal solution for residential and light commercial applications. The luminaire is constructed from an aluminum housing and features a lens designed to optimize light distribution, ensuring for proper illumination of the work space below. The HIDE-A-LITE linear undercabinet utilizes a through hole mounting method to allow for an easy installation. The luminaire can be direct wired, removing the need for separate cords. Two armored cable fittings are included with the product for applications requiring the use of armored cable. An on/off switch is located on the front of the luminaire, allowing for easy access when used as a task light. The energy efficient LEDs can be dimmed down to 10% with many forward phase (TRIAC) and electronic low voltage (ELV) dimmers.

HIDE a LITE™

FINISHES

- Antique Bronze - 020
- White - 028

9" LED UNDERCABINET

P700000-020-30 Antique Bronze
P700000-028-30 White
9" L., 3-1/4" W., 1-1/8" ht.
One 4.5w integrated LED, 3000K, 90CRI, 300 delivered lumens.



P700000-028-30



P700000-020-30

12" LED UNDERCABINET

P700001-020-30 Antique Bronze
P700001-028-30 White
11-1/2" L., 3-1/4" W., 1-1/8" ht.
One 7.5w integrated LED, 3000K, 90CRI, 500 delivered lumens.



P700001-028-30



P700001-020-30

18" LED UNDERCABINET

P700002-020-30 Antique Bronze
P700002-028-30 White
17-1/2" L., 3-1/4" W., 1-1/8" ht.
One 12.5w integrated LED, 3000K, 90CRI, 815 delivered lumens.



P700002-028-30



P700002-020-30

24" LED UNDERCABINET

P700003-020-30 Antique Bronze
P700003-028-30 White
23-1/2" L., 3-1/4" W., 1-1/8" ht.
One 15.5w integrated LED, 3000K, 90CRI, 980 delivered lumens.




P700003-028-30



P700003-020-30

36" LED UNDERCABINET

P700004-020-30 Antique Bronze
P700004-028-30 White
35-1/2" L., 3-1/4" W., 1-1/8" ht.
One 20w integrated LED, 3000K, 90CRI, 1500 delivered lumens.



P700004-028-30



P700004-020-30

LED PUCK

The HIDE-a-LITE™ LED Puck provides an ideal solution for many applications. The low profile design provides versatility to allow installations inside a cabinet or under a cabinet. It can also be used above cabinets to provide up light. The HIDE-a-LITE LED Puck utilizes a simple through hole mounting. It is direct wired using SPT-2 wire, removing the need for seperate cords. The LED Puck is Energy Star listed and meets CA T24 JA8-2016 requirements. The LED Puck is compatible with many forward phase (Triac) and electronic low voltage (ELV) dimmers and can be dimmed down to 10%

HIDE a LITE™



Featuring Puck Undercabinet
(image: Beazer Homes)

LED PUCK
P700005-020-30 Antique Bronze
P700005-028-30 Satin White
3" dia., 1" ht.
3w integrated LED 3000K, 90CRI
120V LED, 140 delivered lumens
Damp location listed.



ACCESSORIES
HAL3 JUNCTION BOX.
P8740-20 Antique Bronze
P8740-30 White
3-1/2" L., 3-1/4" W., 1" ht.

3FT DIRECT WIRE CABLE
P860031-020 Antique Bronze
P860031-028 Satin White
36" Direct Wire Cable
(when used with P8740)

50FT CABLE
P860029-020 Antique Bronze
P860029-028 Satin White
50' 18 AWG SPT-2 Cable


100FT CABLE
P860030-020 Antique Bronze
P860030-028 Satin White
100' 18 AWG SPT-2 Cable



P700005-020-30



P700005-028-30



P8740-20



P8740-30



P860031-020



P860031-028



P860029-020
P860030-020



P860029-028
P860030-028

FINISHES
● Antique Bronze - 020
○ Satin White - 028



Featuring Undercabinet & Puck Lighting
(image: Stephen Alexander Homes)

LED TAPE UNDERCABINET SYSTEM

LED Tape provides lighting to enhance aesthetics, while also aiding in tasks around the home. Common applications for LED Tape include; undercabinet lighting in kitchens to add illumination to work surfaces, highlighting back splashes in kitchens or bathroom areas and adding toe kick lighting at the bases of cabinets for dramatic and functional lighting.



FOLLOW FOUR SIMPLE STEPS:

1. CHOOSE A TAPE LENGTH



12", 60" and 240" lengths to meet different sized projects and features an adhesive backing for easy application to desired surfaces.



Flexible tape can be cut every 4 inches (cut ends can be reconnected, allowing for full use of LED tape).



Tape is fully enclosed in silicone to allow for use in damp location. 24 VDC tape pairs with 24 VDC power supplies.

PRODUCT NO.	COLOR TEMP.	SIZE	
P700008-000-27 P700008-000-30	2700K 3000K	12" L., 3/8" W., 1/8" ht.	
P700009-000-27 P700009-000-30	2700K 3000K	60" L., 3/8" W., 1/8" ht.	
P700010-000-27 P700010-000-30	2700K 3000K	240" L., 3/8" W., 1/8" ht.	

- LED FEATURES**
- 90CRI, 50,000 hr. life
 - 300 lumens per foot and consumes 4.2 watts per foot (71 lumens/w)
 - Field cuttable at every 4" to end of run.
 - cETLus listed damp location
 - 5 year warranty



2. SELECT TRANSFORMER

Progress Lighting offers multiple power supplies to meet various project sizes. Power supplies can be dimmed, flicker-free, on Forward Phase (TRIAC) and Reverse Phase (ELV) dimmers down to 10% output.

PRODUCT NO.	FINISH	SIZE	WATT	MAX LENGTH OF TAPE
P700020-031	Black	8-3/16" L., . 2" W., 1-3/4" HT	25w	60" Tape
P700021-031	Black	8-3/16" L., 2" W., 1-3/4" HT.	40w	120" Tape
P700023-031	Black	9-3/16" L., 3-3/8" W., 1-15/16" HT.	80w	240" Tape

- PRODUCT FEATURES**
- Maximum operating temperature -20° C to +40° C
 - Enclosure provided
 - Wire nuts and additional hardware included



P700020-000
P700021-000
P700023-000

3. ADDITIONAL SYSTEM CONNECTORS

Various connectors allow for customized layouts. Use linking connectors to join runs of tape. Use the L Connector for 90° bends and use the Y Connector to split one run of tape into two.



Connectors feature piercing conductors for secure connection.



Y, L and multi-linking connectors allow for flexibility in design.



2" CONNECTOR CORD
P700011-000 Black
Connect tape sections (P700008, P700009, P700010)
2" L., 5/8" W., 1/4" ht.



72" CONNECTOR CORD
P700015-000 Black
Connect tape sections (P700008, P700009, P700010)
72" L., 5/8" W., 1/4" ht.



12" CONNECTOR CORD
P700012-000 Black
Connect tape sections (P700008, P700009, P700010)
12" L., 5/8" W., 1/4" ht.



L CONNECTOR
P700016-000 Black
90° connector for connecting sections of tape (P700008, P700009, P700010) on corners.
2-1/16" L., 2-1/16" W., 1/6" ht.



18" CONNECTOR CORD
P700013-000 Black
Connect tape sections (P700008, P700009, P700010)
18" L., 5/8" W., 1/4" ht.



Y CONNECTOR
P700017-000 Black
Three-way Y connector for connecting sections of tape (P700008, P700009, P700010)
3-3/16" L., 3-3/16" W., 1/4" ht.



36" CONNECTOR CORD
P700014-000 Black
Connect tape sections (P700008, P700009, P700010)
36" L., 5/8" W., 1/4" ht.



OUTPUT POWER CONNECTOR
P700022-000 Black
60" L., 5/8" W., 1/4" ht.



4. MOUNTING CLIPS/END CLIPS

Select end caps or add mounting clips to finish the installation.

P700018-000
Pack of 10 clips/screws for straight runs for added support (2 clips per foot recommended)
1-1/8" L., 1/4" W., 1/8" ht.



P700019-000
End caps to terminate run of LED tape. For use when tape has been cut at end of run. Sold in sets of 10.
1/2" L., 1/2" W., 1/4" ht.





Close-to-Ceiling

BEZEL LED



Featuring a sleek and slim appearance, Bezel LED is an architectural series of flush mount options. Etched white glass is accented by a metal trim in a metallic finish. The glass shade is illuminated on both the bottom and sides to provide a pleasing lighted effect.

FINISHES

- Brushed Nickel - 009
- Polished Chrome - 015
- Antique Bronze - 020

LED FLUSH MOUNT

P350085-009-30 Brushed Nickel
P350085-015-30 Polished Chrome
P350085-020-30 Antique Bronze
10-1/2" dia., 3-1/2" ht.
One 17w LED module, 3000K, 90CRI, 1276 source lumens.



LED FLUSH MOUNT

P350086-009-30 Brushed Nickel
P350086-015-30 Polished Chrome
P350086-020-30 Antique Bronze
13" dia., 3-7/8" ht.
One 25w LED module, 3000K, 90CRI, 1770 source lumens.



LED FLUSH MOUNT

P350087-009-30 Brushed Nickel
P350087-015-30 Polished Chrome
P350087-020-30 Antique Bronze
16" dia., 4-3/4" ht.
One 26w LED module, 3000K, 90CRI, 1770 source lumens.



P350085-009-30

P350086-009-30



P350087-009-30



P350085-015-30

P350086-015-30



P350087-015-30



P350085-020-30

P350086-020-30



P350087-020-30

INSPIRE LED

With Off-White Linen shade

- FINISHES**
- Brushed Nickel - 09
 - Antique Bronze - 20

LED SEMI-FLUSH MOUNT
P3683-0930K9 Brushed Nickel
P3683-2030K9 Antique Bronze
13" dia., 10-5/8" ht.
One 17w LED module, 3000K,
90CRI, 1452 source lumens..



P3683-2030K9



P3683-0930K9

LED FLUSH MOUNT
P3696-0930K9 Brushed Nickel
P3696-2030K9 Antique Bronze
13" dia., 6" ht.
One 17w LED module, 3000K,
90CRI, 1452 source lumens.



P3696-2030K9



P3696-0930K9

INSPIRE LED

With Summer Linen shade

- FINISHES**
- Brushed Nickel - 009
 - Graphite - 143

LED SEMI-FLUSH
P350134-009-30 Brushed Nickel
P350134-143-30 Graphite
13" dia., 10-5/8" ht.
One 17w LED module, 3000K,
90CRI, 1452 source lumens.



P350134-143-30



P350134-009-30

LED FLUSH MOUNT
P350135-009-30 Brushed Nickel
P350135-143-30 Graphite
13" dia., 6" ht.
One 17w LED module, 3000K,
90CRI, 1452 source lumens.



P350135-143-30



P350135-009-30

DESIGN+SERIES™

ELEVATE LED

Etched white glass

- FINISHES**
- Brushed Bronze - 109
 - Polished Chrome - 015

LED FLUSH MOUNT
P350105-109-30 Brushed Bronze
P350105-015-30 Polished Chrome
13" dia., 5-1/4" ht.
One 17W LED module, 3000K,
90 CRI, 1452 source lumens.



P350105-109-30



P350105-015-30

LED ALABASTER

Alabaster finish glass

- FINISHES**
- Brushed Nickel - 009
 - Antique Bronze - 020

LED FLUSH MOUNT
P350002-009-30 Brushed Nickel
P350002-020-30 Antique Bronze
13" dia., 6-1/2" ht.
21w integrated LED, 3000K,
90CRI, 1231 delivered lumens.



P350002-009-30



P350003-009-30

LED FLUSH MOUNT
P350003-009-30 Brushed Nickel
P350003-020-30 Antique Bronze
15" dia., 6-3/4" ht.
28w integrated LED, 3000K,
90CRI, 1416 delivered lumens.



P350002-020-30



P350003-020-30

LED FLUSH MOUNT

Etched glass

- FINISHES**
- Brushed Nickel - 009
 - Antique Bronze - 020

LED FLUSH MOUNT
P350051-009-30 Brushed Nickel
P350051-020-30 Antique Bronze
11" dia., 4-3/16" ht.
One 17w LED module
90CRI, 1452 source lumens.



LED FLUSH MOUNT
P350052-009-30 Brushed Nickel
P350052-020-30 Antique Bronze
12-9/16" dia., 4-1/2": ht.
One 25w LED module,
90CRI, 2015 source lumens.



LED FLUSH MOUNT
P350053-009-30 Brushed Nickel
P350053-020-30 Antique Bronze
11" dia., 4" ht.
One 17w LED module
90CRI, 1452 source lumens.



LED FLUSH MOUNT
P350054-009-30 Brushed Nickel
P350054-020-30 Antique Bronze
13-1/4" dia., 4-3/4" ht.
One 25w LED module
90CRI, 2015 source lumens.



P350051-009-30



P350051-020-30



P350052-009-30



P350052-020-30



P350053-009-30



P350053-020-30



P350054-009-30



P350054-020-30

LED FLUSH MOUNT

Etched glass

- FINISHES**
- Brushed Nickel - 009
 - Polished Chrome - 015
 - Antique Bronze - 020

LED FLUSH MOUNT
P350100-009-30 Brushed Nickel
P350100-015-30 Polished Chrome
P350100-020-30 Antique Bronze
11" dia., 4-1/4" ht.
One 17w LED module, 3000K,
90CRI, 1276 source lumens.



LED FLUSH MOUNT
P350101-009-30 Brushed Nickel
P350101-015-30 Polished Chrome
P350101-020-30 Antique Bronze
13-1/2" dia., 4-1/2": ht.
One 25w LED module, 3000K,
90CRI, 1770 source lumens.



LED FLUSH MOUNT
P350131-009-30 Brushed Nickel
P350131-015-30 Polished Chrome
P350131-020-30 Antique Bronze
15-1/2" dia., 5-1/4" ht.
One 25w LED module, 3000K,
90CRI, 1770 source lumens.



P350100-009-30



P350101-009-30



P350131-009-30



P350100-015-30



P350101-015-30



P350131-015-30



P350100-020-30



P350101-020-30




P350131-020-30

FINESSE LED

Finesse LED flush mount fixtures take on a new perspective with an open cage design. The beautifully graphic frame, available in Vintage Gold, Metallic Silver or Graphite, closes to create a circular pattern. The form casts a pleasing illumination and complements popular wire designs found in other home accents and furniture. Ideal for 8 to 9 foot ceilings in spaces that showcase Mid-Century or Modern styling.

- FINISHES**
- Vintage Gold - 078
 - Metallic Silver - 121
 - Graphite - 143

LED FLUSH MOUNT
P350089-078-30 Vintage Gold
P350089-121-30 Metallic Silver
P350089-143-30 Graphite
15" dia., 4-1/2" ht.
One 17w LED module, 3000K, 90CRI, 1452 source lumens.



FRESNEL LED

The Fresnel LED flush mount features a nautical-inspired fresnel glass lens, with industrial roots in form and function. Ideal for Farmhouse, Coastal and Industrial interiors.

- FINISHES**
- Brushed Nickel - 009
 - Polished Chrome - 015
 - Oil Rubbed Bronze - 108

LED FLUSH MOUNT
P350113-009-30 Brushed Nickel
P350113-015-30 Polished Chrome
P350113-108-30 Oil Rubbed Bronze
12-3/4" dia., 4-1/2" ht.
One 17w LED module, 3000K, 90CRI, 1276 source lumens.



LED LINEN

Linen finish glass

- FINISH**
- Brushed Nickel - 09

LED FLUSH MOUNT
P350005-009-30 Brushed Nickel
11" dia., 4-5/8" ht.
21w integrated LED, 3000K, 90CRI, 921 delivered lumens



LED FLUSH MOUNT
P350006-009-30 Brushed Nickel
13" dia., 5-3/8" ht.
21w integrated LED, 3000K, 90CRI, 1152 delivered lumens



LED FLUSH MOUNT
P350007-009-30 Brushed Nickel
15" dia., 5-7/8" ht.
28w integrated LED, 3000K, 90CRI, 1389 delivered lumens



LED FLUSH MOUNT
P350008-009-30 Brushed Nickel
19" dia., 7-1/8" ht.
30w integrated LED, 3000K, 90CRI, 1984 delivered lumens



P350005-009-30



P350006-009-30



P350007-009-30



P350008-009-30

LED SQUARE FLUSH MOUNT

Linen finish glass

- FINISHES**
- Brushed Nickel - 009
 - Antique Bronze - 020

LED FLUSH MOUNT
P350023-009-30 Brushed Nickel
P350023-020-30 Antique Bronze
9-1/2" sq., 4-3/8" ht.
One 17w LED module, 3000K,
90CRI, 1452 source lumens



LED FLUSH MOUNT
P350024-009-30 Brushed Nickel
P350024-020-30 Antique Bronze
11-1/2" sq., 4-7/8" ht.
One 25w LED module, 3000K,
90CRI, 2015 source lumens



P350023-009-30



P350024-009-30



P350023-020-30



P350024-020-30

LED SQUARE GLASS

Alabaster finish glass

- FINISHES**
- Brushed Nickel - 009
 - Antique Bronze - 020

LED FLUSH MOUNT
P350019-009-30 Brushed Nickel
P350019-020-30 Antique Bronze
9-1/2" sq., 4-3/8" ht.
One 17w LED module, 3000K,
90CRI, 1452 source lumens



LED FLUSH MOUNT
P350020-009-30 Brushed Nickel
P350020-020-30 Antique Bronze
11-3/8" sq., 5" ht.
One 25w LED module, 3000K,
90CRI, 2015 source lumens



P350019-009-30



P350019-020-30



P350020-009-30



P350020-020-30

OPAL-LINEN LED



Opal-Linen LED features architectural details for a variety of home styles. A combination of glass textures work together to create an interesting effect for today's interiors. Metallic finishes complement the opal/linen double glass.

- FINISHES**
- Brushed Nickel - 009
 - Antique Bronze - 020

LED FLUSH MOUNT
P350081-009-30 Brushed Nickel
P350081-020-30 Antique Bronze
12" dia., 4-3/4" ht.
One 17w LED module, 3000K,
90CRI, 1452 source lumens.



LED FLUSH MOUNT
P350082-009-30 Brushed Nickel
P350082-020-30 Antique Bronze
15" dia., 5" ht.
One 25w LED module, 3000K,
90CRI, 2015 source lumens.



P350081-020-30



P350082-020-30



P350081-009-30



P350082-009-30

MAIER LED

The Maier LED flush mounts feature an acrylic diffuser which twists into the frame so there are no exposed fasteners for a clean modern look.

FINISHES

- Brushed Nickel - 009
- Antique Bronze - 020
- White - 030

LED SEMI-FLUSH
P350076-009-30 Brushed Nickel
P350076-020-30 Antique Bronze
P350076-030-30 White
9-1/16" dia., 4-5/16" ht.
20.5w integrated LED, 3000K,
90CRI, 1354 delivered lumens.



LED SEMI-FLUSH
P350077-009-30 Brushed Nickel
P350077-020-30 Antique Bronze
P350077-030-30 White
14" dia., 4-3/4" ht.
26w integrated LED, 3000K,
90CRI, 2016 delivered lumens.



LED SEMI-FLUSH
P350078-009-30 Brushed Nickel
P350078-020-30 Antique Bronze
P350078-030-30 White
18" dia., 5-1/4" ht.
28.5w integrated LED, 3000K,
90CRI, 2064 delivered lumens.



P350078-030-30



P350076-030-30



P350077-030-30



P350078-009-30



P350076-009-30



P350077-009-30



P350078-020-30



P350076-020-30



P350077-020-30



Featuring Montague Ceiling Fan

Ceiling Fans & Light Kits

INDOOR FANS - INTEGRATED LIGHT

BRADEN P2588-1530K  OTHER FINISHES P2588-0930K P2588-12930K	FARRIS P250002-143-30  OTHER FINISHES P250002-009-30 P250002-108-30	FRESNO P2548-3030K  OTHER FINISHES P2548-0930K P2548-2030K	GAZE P2554-2030K  OTHER FINISHES P2554-1530K P2554-0930K P2554-3130K
GLANDON P2586-7130K  OTHER FINISHES P2586-8130K	GRACEFUL P2544-0930K  OTHER FINISHES P2544-1530K P2544-2030K	GUST P2582-0930K  OTHER FINISHES P2582-14330K P2582-2030K	HARRANVALE P2540-14330K  OTHER FINISHES P2540-2030K P2540-3030K
KUDOS P2568-2030K  OTHER FINISHES P2568-0930K P2568-1530K	ORIOLE P2592-0930K  OTHER FINISHES P2592-3130K P2592-12930K	SIGNATURE PLUS II P2539-2030K  OTHER FINISHES P2539-0930K P2539-3030K	SOAR P2542-3030K  OTHER FINISHES P2542-0930K P2542-2030K
TEMPT P2578-1530K  OTHER FINISHES P2578-2030K	TREVINA II P2556-2030K  OTHER FINISHES P2556-0930K P2556-3030K	VAST P2550-0930K  OTHER FINISHES P2550-2030K P2550-3030K P2550-3130K	VERADA P2558-2030K  OTHER FINISHES P2558-0930K
VOX FAN P2572-0930K  OTHER FINISHES P2572-2030K P2572-3030K	For more information on ceiling fans, please see the 2019 Progress Lighting ceiling fan catalog or progresslighting.com		

INDOOR FANS - LIGHT KIT ADAPTABLE

NORTH PARK P2531-20  OTHER FINISHES P2531-09	PERFORMANCE P2503-30W  OTHER FINISHES P2503-09 P2503-20	SIGNATURE P2521-09  OTHER FINISHES P2521-09CH P2521-09WA P2521-20 P2521-77 P2521-80 P2521-81	SIGNATURE PLUS P2530-09  OTHER FINISHES P2530-20 P2530-30W
---	---	--	--

OUTDOOR FANS - INTEGRATED LIGHT

EDISTO P2596-8130K  OTHER FINISHES P2596-8030K P2596-12930K	MONTAGUE P2564-3030K  OTHER FINISHES P2564-2030K P2564-8030K	SMYRNA P2576-8030K  OTHER FINISHES P2576-2030K	WHIRL P2574-8030K  OTHER FINISHES P2574-2030K P2574-8130K
--	---	--	--

OUTDOOR FANS - LIGHT KIT ADAPTABLE

52" PATIO P2502-20  OTHER FINISHES P2502-30 P2502-80 P2502-141	54" PATIO P2533-20 	DECORATIVE PATIO P2526-20 
---	---	--

SCHOOLHOUSE

Universal-style with quick-connect wiring.

- FINISHES
- Antique Bronze - 20
 - White - 30
 - Forged Black - 80
 - Galvanized - 141
 - Brushed Nickel - 09

P2601-20WB Antique Bronze
P2601-30WB White
P2601-80WB Forged Black
P2601-141WB Galvanized
with opal glass.
8-1/2" dia., 7" ht.
One medium base, 3000K,
LED lamp included.
800 lumens/lamp, 90 CRI.
(dimnable)



P2644-09WB Brushed Nickel
P2644-30WB White
with white opal glass.
8-1/2" dia., 6-1/2" ht.
One medium base, 3000K,
LED lamp included.
800 lumens/lamp, 90 CRI.
Indoor use only. (dimnable)



P2601-20WB



P2601-30WB



P2601-80WB



P2601-141WB



P2644-09WB



P2644-30WB

ASHMORE

- FINISH
- Antique Bronze - 20

ASHMORE
P2636-20WB Antique Bronze
with frosted seeded glass.
11" dia., 8-1/4" ht.
Two medium base, 3000K,
LED lamp included.
800 lumens/lamp, 90 CRI.
(dimnable)



P2636-20WB

TORINO

Universal-style light kit with quick-connect wiring.

- FINISHES
- Brushed Nickel - 09
 - Antique Bronze - 20
 - Forged Black - 80
 - Forged Bronze - 77

P2645-77WB Forged Bronze
with tea-stained glass.
P2645-01WB
with etched glass.
Included Finials:
-09 Brushed Nickel
-20 Antique Bronze
-80 Forged Black
12" dia., 5-3/4" ht.
Two medium base, 3000K,
LED lamps included.
800 lumens/lamp, 90 CRI.
Indoor use only. (dimnable)



P2645-77WB



P2645-01WB
Shown with
-09 finial



P2645-01WB
Shown with
-20 finial



P2645-01WB
Shown with
-80 finial

NORTH PARK

Universal-style with quick-connect wiring.

- FINISHES
- Brushed Nickel - 09
 - Antique Bronze - 20

P2654-01WB
with etched glass.
Included Finials:
-09 Brushed Nickel
-20 Antique Bronze
12-1/2" sq., 6-1/4" ht.
Two medium base, 3000K,
LED lamps included.
800 lumens/lamp, 90 CRI.
Indoor use only. (dimnable)



P2654-01WB
Shown with
-09 finial



P2654-01WB
Shown with
-20 finial

UNIVERSAL BOWL

Universal-style with quick-connect wiring.

FINISHES

- Brushed Nickel - 09
- Polished Chrome - 15
- Antique Bronze - 20
- White - 30
- Graphite - 143

P2612-20TWB Antique Bronze with tea-stained glass.
P2612-01WB with alabaster glass.
Included Finials:
-09 Brushed Nickel
-20 Antique Bronze
-30 White
-15 Polished Chrome
-143 Graphite
10-3/4" dia., 5-1/2" ht.
Two medium base, 3000K, LED lamps included.
800 lumens/lamp, 90 CRI. Indoor use only. (dimnable)



P2612-20TWB



P2612-01WB
Shown with
-20 finial



P2612-01WB
Shown with
-09 finial



P2612-01WB
Shown with
-30 finial



P2612-01WB
Shown with
-15 finial



P2612-01WB
Shown with
-143 finial

AIRPRO

Universal-style with quick-connect wiring.

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20
- White - 30

P2643-09WB Brushed Nickel
P2643-20WB Antique Bronze
P2643-30WB White with alabaster glass.
P2643-20TWB Antique Bronze with tea stained alabaster glass.
13-5/8" dia., 7-3/4" ht.
Four medium base, 3000K, LED lamps included.
800 lumens/lamp, 90 CRI. Indoor use only. (dimnable)



P2643-09WB



P2643-30WB




P2642-09WB



P2643-20WB



P2643-20TWB



P2642-30WB

P2642-09WB Brushed Nickel
P2642-30WB White with alabaster glass.
13-5/8" dia., 7-3/4" ht.
Three medium base, 3000K, LED lamps included.
800 lumens/lamp, 90 CRI. Indoor use only. (dimnable)



LED LIGHT KITS

Universal-style light kits with quick connect wiring.

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20
- White - 30

P2659-09 Brushed Nickel
P2659-20 Antique Bronze
P2659-30 White with etched white glass.
12-1/4" dia., 4" ht.
One 16w, 3000K LED module included.
1265 source lumens, 960 delivered lumens, 90 CRI. Indoor use only. (dimnable)



P2659-09



P2659-20



P2659-30

P2660-01 with etched alabaster glass.
Included Finials:
-09 Brushed Nickel
-20 Antique Bronze
-30 White
11-1/4" dia., 5-3/8" ht.
One 16w, 3000K LED module included.
1241 source lumens, 1150 delivered lumens, 90 CRI. Indoor use only. (dimnable)



P2660-01
Shown with
-09 finial



P2660-01
Shown with
-20 finial



P2660-01
Shown with
-30 finial

TRINITY

Universal-style with quick-connect wiring.

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20
- White - 30
- Forged Bronze - 77

P2628-01WB with etched glass.
Included Finials:
-09 Brushed Nickel
-20 Antique Bronze
-30 White
-77 Forged Bronze
13-3/8" dia., 6-3/8" ht.
Two medium base, 3000K, LED lamps included.
800 lumens/lamp, 90 CRI. Indoor use only. (dimnable)



P2628-01WB
Shown with
-09 finial



P2628-01WB
Shown with
-20 finial



P2628-01WB
Shown with
-30 finial



P2628-01WB
Shown with
-77 finial

LOW PROFILE

Universal-style with quick-connect wiring.

- FINISHES**
- Brushed Nickel - 09
 - Polished Chrome - 15
 - Antique Bronze - 20
 - White - 30
 - Graphite - 143
 - Forged Black - 80

P2602-09WB Brushed Nickel
P2602-15WB Polished Chrome
P2602-20WB Antique Bronze
P2602-30WB White
P2602-143WB Graphite with white opal glass.
10-1/2" dia., 4-1/2" ht.
Two medium base, 3000K, LED lamps included.
800 lumens/lamp, 90 CRI.
Indoor use only. (dimnable)



P2611-20WB Antique Bronze
P2611-30WB White
P2611-80WB Forged Black with opal glass.
10-1/2" dia., 4-1/2" ht.
Two medium base, 3000K, LED lamp included.
800 lumens/lamp, 90 CRI.
(dimnable)



P2602-09WB



P2602-15WB



P2602-20WB



P2602-30WB



P2602-143WB



P2611-20WB



P2611-30WB



P2611-80WB

WISTEN

Universal-style light kit with quick-connect wiring.

- FINISHES**
- Brushed Nickel - 09
 - Antique Bronze - 20

P2649-01WB with etched glass.
Included Finials:
-09 Brushed Nickel
-20 Antique Bronze
11" dia., 6-1/4" ht.
Two medium base, 3000K, LED lamps included.
800 lumens/lamp, 90 CRI.
Indoor use only. (dimnable)



P2649-01WB
Shown with
-09 finial



P2649-01WB
Shown with
-20 finial

ALABASTER

Spring clip glass attachment. For use with P2500, P2501, P2502, P2524 and P2525.

- FINISHES**
- Brushed Nickel - 09
 - Polished Chrome - 15
 - Antique Bronze - 20
 - White - 30
 - Graphite - 143

P2610-09WB Brushed Nickel
P2610-15WB Polished Chrome
P2610-20WB Antique Bronze
P2610-30WB White
P2610-143WB Graphite with alabaster glass.
14-1/2" dia., 6-1/4" ht.
Four medium base, 3000K, LED lamps included.
800 lumens/lamp, 90 CRI.
Indoor use only. (dimnable)



P2600-09WB Brushed Nickel
P2600-20WB Antique Bronze
P2600-30WB White with alabaster glass.
15" dia., 6-5/8" ht.
Three medium base, 3000K, LED lamps included.
800 lumens/lamp, 90 CRI.
Indoor use only. (dimnable)




P2610-09WB



P2610-15WB



P2610-20WB



P2610-30WB



P2610-143WB



P2600-09WB



P2600-20WB



P2600-30WB

GATHER, BRAVO & JOY

Universal-style light kit with quick-connect wiring.

- FINISHES**
- Brushed Nickel - 09
 - Antique Bronze - 20

P2650-20TWB Antique Bronze with tea-stained glass.
P2650-01WB with etched glass.
Included Finials:
-09 Brushed Nickel
-20 Antique Bronze
11" dia., 5-1/2" ht.
Two medium base, 3000K, LED lamps included.
800 lumens/lamp, 90 CRI.
Indoor use only. (dimnable)



P2650-20TWB



P2650-01WB
Shown with
-09 finial




P2650-01WB
Shown with
-80 finial



Featuring Blanco

Bath Collections

PROGRESSLIGHTING.COM



P300150-150-30

LED vanity and sconce in the Blanco collection highlight a classic form with contemporary updates. Brushed Nickel accents complement a Faux White Marble frame and canopy with a design that minimizes all visible hardware for an elegantly modern effect. Suitable for residential and commercial applications, the 22" and 32" sizes can be installed vertically or horizontally to complement Modern, Luxe or Mid-Century interiors.

FINISH

● Faux White Marble - 150

LED WALL BRACKET


P710047-150-30 Faux White Marble
4-3/4" W., 11-3/4" ht.
Extends 3-5/8". H/CTR 8-3/8".
16w integrated LED, 3000K,
90CRI, 820 delivered lumens.

ADA **JA8****22" LINEAR LED BATH**

P300150-150-30 Faux White Marble
22-1/4" W., 4-3/4" ht.
Extends 3-5/8". H/CTR 2-3/8".
36w integrated LED, 3000K,
90CRI, 1940 delivered lumens.

ADA **JA8****32" LINEAR LED BATH**

P300151-150-30 Faux White Marble
32-3/8" W., 4-3/4" ht.
Extends 3-3/4". H/CTR 2-3/8".
53w integrated LED, 3000K,
90CRI, 2750 delivered lumens.

ADA **JA8**

P710047-150-30

P300150-150-30

P300151-150-30

P300150-150-30
mounted vertical

PROGRESSLIGHTING.COM



P300182-129-30

Beam LED vanity and sconces feature a squared, tubular opal glass diffuser paired with a simple, modern metal canopy. An integrated LED source provides a variety of energy and cost savings benefits. Suitable for residential and commercial applications, the 22" fixture can be installed vertically or horizontally. Available in three finish options, including Brushed Nickel, Polished Chrome and Architectural Bronze.

LED WALL BRACKET

P710049-009-30 Brushed Nickel
P710049-015-30 Polished Chrome
P710049-129-30 Architectural Bronze
4-3/4" W., 10-1/2" ht.
Extends 3-1/4". H/CTR 8-3/8".
16w integrated LED, 3000K,
90CRI, 1000 delivered lumens.

ADA 



P710049-009-30



P710049-015-30



P710049-129-30

FINISHES

- Brushed Nickel - 009
- Polished Chrome - 015
- Architectural Bronze - 129



P300182-009-30



P300182-015-30



P300182-129-30

22" LINEAR LED BATH
P300182-009-30 Brushed Nickel
P300182-015-30 Polished Chrome
P300182-129-30 Architectural Bronze
22-1/4" W., 4-3/4" ht.
Extends 3". H/CTR 2-3/8".
36w integrated LED, 3000K,
90CRI, 2200 delivered lumens.

ADA 



P300182-009-30
mounted vertical



P300182-015-30
mounted vertical



P300182-129-30
mounted vertical

VOLO LED



P300065-009-30

Volo fixtures feature a modern repeating circular frame. Etched opal glass shades are seamlessly secured to provide a clean, contemporary look to your home. The modern LED source delivers crisp, high quality light that is the perfect choice for both general and task lighting.

ONE-LIGHT BATH
P300063-009-30 Brushed Nickel
10" W., 5-1/2" ht.
Extends 4-5/8". H/CTR 2-3/4".
One 9w LED module, 3000K,
90CRI, 624 source lumens per module



P300063-009-30

TWO-LIGHT BATH
P300064-009-30 Brushed Nickel
16" W., 5 1/2" ht.
Extends 4-5/8". H/CTR 2-3/4".
Two 9w LED modules, 3000K,
90CRI, 624 source lumens per module



P300064-009-30

THREE-LIGHT BATH
P300065-009-30 Brushed Nickel
24" W., 5-1/2" ht.
Extends 4-5/8". H/CTR 2-3/4".
Three 9w LED modules, 3000K,
90CRI, 624 source lumens per module



P300065-009-30

FINISH

● Brushed Nickel - 009

*Can be installed vertically
or horizontally.*

CAPELLI LED



P350054-015-30

Inspired by the beauty of frozen ice forms, Capelli LED sconces feature intriguing layers resulting in a sophisticated form. The integrated LED technology runs across the length of the fixture, allowing the illumination to showcase the unique effects of the handmade work of art. The back plate and knob details are finished in Chrome. Can be installed vertically or horizontally.

FINISH

● Polished Chrome - 015

12" LED WALL SCONCE
P710062-015-30 Polished Chrome
4-3/4" W., 12" ht.
Extends 3-3/4". H/CTR 2-3/8".
16w integrated LED, 3000K,
90CRI, 1125 delivered lumens.



P710062-015-30



P300054-015-30



*P300054-015-30
mounted vertical*

24" LINEAR LED BATH
P300054-015-30 Polished Chrome
24" W., 4-3/4" ht.
Extends 3-3/4". H/CTR 2-3/8".
36w integrated LED, 3000K,
90CRI, 2600 delivered lumens.




33" LINEAR LED BATH
P300055-015-30 Polished Chrome
33" W., 4-3/4" ht.
Extends 3-3/4". H/CTR 2-3/8".
53w integrated LED, 3000K,
90CRI, 3850 delivered lumens.



P300055-015-30

COLONNADE LED



P300187-009-30

Tubular etched glass shades pop against geometric back plate to create Colonnade, an LED bath and vanity collection. Available in one, two, three and four-light options in Brushed Nickel or Polished Chrome finishes. Modern style and continuous illumination are ideal for a variety of bath and vanity settings – including Mid-Century and Luxe. LED source features 3000K and 90 CRI benefits, as well as a lifespan of more than 50,000 hours.

ONE-LIGHT LED BATH

P300185-009-30 Brushed Nickel
P300185-015-30 Polished Chrome
4-3/4" W., 7-12" ht.
Extends 3-7/8". H/CTR 3-7/8".
9.5w integrated LED, 3000K,
90CRI, 500 delivered lumens.

ADA 



P300185-009-30



P300186-009-30

TWO-LIGHT LED BATH

P300186-009-30 Brushed Nickel
P300186-015-30 Polished Chrome
13-1/4" W., 7-1/2" ht.
Extends 3-7/8". H/CTR 3-7/8".
19w integrated LED, 3000K,
90CRI, 1000 delivered lumens.

ADA 



P300185-015-30




P300186-015-30

FINISHES

-  Brushed Nickel - 009
-  Polished Chrome - 015



P300187-009-30



P300187-015-30

THREE-LIGHT LED BATH

P300187-009-30 Brushed Nickel
P300187-015-30 Polished Chrome
22" W., 7-1/2" ht.
Extends 3-7/8". H/CTR 3-7/8".
28.5w integrated LED, 3000K,
90CRI, 1500 delivered lumens.

ADA 

FOUR-LIGHT LED BATH

P300188-009-30 Brushed Nickel
P300188-015-30 Polished Chrome
31-3/8" W., 7-1/2" ht.
Extends 3-7/8". H/CTR 3-7/8".
38w integrated LED, 3000K,
90CRI, 2000 delivered lumens.

ADA 



P300188-009-30



P300188-015-30

CONCOURSE LED



P300094-009-30

Architectural details and a full size canopy are key elements in Concourse LED vanity fixtures. A dual tone reflector frames the canopy to provide a mirror like effect. Etched opal glass is paired with Brushed Nickel and polished stainless accents in this versatile cylindrical fixture. Mounts horizontal and vertical.

ONE-LIGHT BATH
P300093-009-30 Brushed Nickel
24" W., 4-3/4" ht.
Extends 3-1/2". H/CTR 2-3/8".
37w integrated LED, 3000K,
90CRI, 2191 delivered lumens.
ADA 

ONE-LIGHT BATH
P300094-009-30 Brushed Nickel
36" W., 4-3/4" ht.
Extends 3-1/2". H/CTR 2-3/8".
53w integrated LED, 3000K,
90CRI, 2969 delivered lumens.
ADA 



P300093-009-30
mounted vertical



P300093-009-30



P300094-009-30

FINISH

● Brushed Nickel - 009

MITER LED



P300152-009-30

The Miter LED wall sconce highlights a beautiful layered effect to enhance a variety of interior areas. Each clear beveled glass panel is hand cut and positioned together, creating visual interest that extend to the corners. To complete the form, a back plate and linear accents frame the glass in a Brushed Nickel finish. Can be installed horizontally or vertically. An integrated LED source provides a variety of energy and cost savings benefits.



P710061-009-30



P300152-009-30



P300152-009-30
mounted vertical



P300153-009-30

FINISH

● Brushed Nickel - 009

12" LED WALL BRACKET
P710061-009-30 Brushed Nickel
5" W., 12-1/4" ht.
Extends 3-7/8". H/CTR 6-1/8".
16w integrated LED, 3000K,
90CRI, 825 delivered lumens.
ADA 

24" LINEAR LED BATH
P300152-009-30 Brushed Nickel
24" W., 5" ht.
Extends 3-7/8". H/CTR 2-1/2".
36w integrated LED, 3000K,
90CRI, 1975 delivered lumens.
ADA 

34" LINEAR LED BATH
P300153-009-30 Brushed Nickel
34-1/8" W., 5" ht.
Extends 3-7/8". H/CTR 2-1/2".
53w integrated LED, 3000K,
90CRI, 2825 delivered lumens.
ADA 

PARALLEL LED



Parallel LED vanity and sconces feature a tubular opal glass diffuser paired with a simple, modern metal canopy. An integrated LED source provides a variety of energy and cost savings benefits. Suitable for residential and commercial applications, the 22" and 32" sizes can be installed vertically or horizontally. Available in three finish options, including Brushed Nickel, Polished Chrome and Architectural Bronze.

LED WALL BRACKET

P710050-009-30 Brushed Nickel
P710050-015-30 Polished Chrome
P710050-129-30 Architectural Bronze
4-3/4" W., 11" ht.
Extends 2-3/4". H/CTR 7-1/2".
16w integrated LED, 3000K, 90CRI,
930 delivered lumens.

ADA 



P710050-009-30



P710050-015-30



P710050-129-30

FINISHES

- Brushed Nickel - 009
- Polished Chrome - 015
- Architectural Bronze - 129

22" LINEAR LED BATH

P300183-009-30 Brushed Nickel
P300183-015-30 Polished Chrome
P300183-129-30 Architectural Bronze
22-3/8" W., 4-3/4"ht.
Extends 2-3/4". H/CTR 2-3/8".
36w integrated LED, 3000K, 90CRI,
2400 delivered lumens.
ADA 

32" LINEAR LED BATH

P300184-009-30 Brushed Nickel
P300184-015-30 Polished Chrome
P300184-129-30 Architectural Bronze
32" W., 4-3/4" ht.
Extends 2-3/4". H/CTR 2-3/8".
53w integrated LED, 3000K, 90CRI,
3200 delivered lumens.
ADA 



P300183-009-30



P300184-009-30



P300183-015-30



P300184-015-30



P300183-129-30



P300184-129-30



P300183-129-30
mounted vertical

P300184-129-30
mounted vertical

PHASE 1.1 LED



Featuring a cylindrical acrylic diffuser and a simple rectangular back plate, Phase 1.1 offers a variety of lengths to accommodate residential, light commercial and multi-family applications. An integrated LED source provides uniform illumination, as well as energy and cost savings benefits. Can be installed vertically or horizontally.

24" LINEAR LED BATH
P300223-009-30 Brushed Nickel
24" W., 4-3/4" ht.
Extends 4". H/CTR 2-3/8".
22w integrated LED, 3000K, 90CRI,
1675 delivered lumens.



P300223-009-30

36" LINEAR LED BATH
P300224-009-30 Brushed Nickel
36" W., 4-3/4" ht.
Extends 4". H/CTR 2-3/8".
33w integrated LED, 3000K, 90CRI,
2600 delivered lumens.



P300224-009-30

48" LINEAR LED BATH
P300225-009-30 Brushed Nickel
48" W., 4-3/4" ht.
Extends 4". H/CTR 2-3/8".
42w integrated LED, 3000K, 90CRI,
3500 delivered lumens.



P300225-009-30

P300223-009-30



P300223-009-30
mounted vertical

FINISH
● Brushed Nickel - 009

PHASE 1.2 LED



A classic form with contemporary updates, this elongated acrylic shade comes with decorative accents. Both a faux stone option and white geometric decorative diffuser are included to further customize the fixture. An integrated LED source provides uniform illumination, as well as energy and cost savings benefits. Can be installed vertically or horizontally and is suitable for Modern interiors.



P300205-009-30
shown with faux stone diffuser



P300206-009-30
shown with decorative geometric diffuser



P300207-009-30
shown with faux stone diffuser

FINISH
● Brushed Nickel - 009

24" LINEAR LED BATH
P300205-009-30 Brushed Nickel
24" W., 4-3/4" ht.
Extends 4-1/2". H/CTR 2-3/8".
22w integrated LED, 3000K, 90CRI,
1575 delivered lumens.



36" LINEAR LED BATH
P300206-009-30 Brushed Nickel
36" W., 4-3/4" ht.
Extends 4-1/2". H/CTR 2-3/8".
33w integrated LED, 3000K, 90CRI,
2475 delivered lumens.



48" LINEAR LED BATH
P300207-009-30 Brushed Nickel
48" W., 4-3/4" ht.
Extends 4-1/2". H/CTR 2-3/8".
42w integrated LED, 3000K, 90CRI,
3400 delivered lumens.



Detail of faux
stone accent




Detail of
geometric accent

PHASE 2.1 LED




Phase 2.1 features an acrylic lens that provides even illumination. This specially designed linear fixture delivers ambient light to surfaces free of shadows. Phase 2.1 is a perfect addition to modern applications. An integrated LED source provides energy and cost savings benefits. Can be installed vertically or horizontally.

24" LINEAR LED BATH
P300208-009-30 Brushed Nickel
24" W., 4-3/4" ht.
Extends 3-1/2". H/CTR 2-3/8".
23w integrated LED, 3000K, 90CRI,
1600 delivered lumens.
ADA



36" LINEAR LED BATH
P300209-009-30 Brushed Nickel
36" W., 4-3/4" ht.
Extends 3-1/2". H/CTR 2-3/8".
34w integrated LED, 3000K, 90CRI,
2450 delivered lumens.
ADA




48" LINEAR LED BATH
P300210-009-30 Brushed Nickel
48" W., 4-3/4" ht.
Extends 3-1/2". H/CTR 2-3/8".
44w integrated LED, 3000K, 90CRI,
3300 delivered lumens.
ADA




FINISH
● Brushed Nickel - 009

PHASE 2.2 LED



Phase 2.2 features an acrylic shade framed by architectural accents in Brushed Nickel complete the design to deliver ambient light to surfaces free of shadows. Ideal for residential, commercial and multi-family applications. An integrated LED source provides energy and cost savings benefits. Can be installed vertically or horizontally.



FINISH
● Brushed Nickel - 009

24" LINEAR LED BATH
P300211-009-30 Brushed Nickel
24" W., 4-3/4" ht.
Extends 4". H/CTR 2-3/8".
23w integrated LED, 3000K, 90CRI,
1550 delivered lumens.
ADA

36" LINEAR LED BATH
P300212-009-30 Brushed Nickel
36" W., 4-3/4" ht.
Extends 4". H/CTR 2-3/8".
34w integrated LED, 3000K, 90CRI,
2400 delivered lumens.
ADA

48" LINEAR LED BATH
P300213-009-30 Brushed Nickel
48" W., 4-3/4" ht.
Extends 4". H/CTR 2-3/8".
44w integrated LED, 3000K, 90CRI,
3250 delivered lumens.
ADA

PONDER LED



P300092-020-30

Ponder vanity fixtures with prismatic glass shades offer a sleek, industrial-inspired appearance. Etched prismatic glass is framed within a die cast bezel to enhance visual interest in Urban Industrial or Farmhouse-style interiors.

FINISH

- Antique Bronze - 020
- Graphite - 143

TWO-LIGHT BATH

P300091-020-30 Antique Bronze
P300091-143-30 Graphite
 16-1/8" W., 4-5/8" ht.
 Extends 3-5/8". H/CTR 2-3/8".
 Two 9w LED modules, 3000K, 90CRI,
 670 source lumens per module.



P300091-020-30



P300091-143-30

THREE-LIGHT BATH

P300092-020-30 Antique Bronze
P300092-143-30 Graphite
 25-3/8" W., 4-5/8" ht.
 Extends 3-5/8". H/CTR 2-3/8".
 Three 9w LED modules, 3000K, 90CRI,
 670 source lumens per module.




P300092-020-30



P300092-143-30

PROGRESSLIGHTING.COM



Featuring Square Cylinder

Outdoor

PROGRESSLIGHTING.COM

DESIGN+SERIES™
WHITACRE LED



Inspired by traditional lantern styles, Whitacre incorporates handsome details. Clear seeded glass surrounds an etched opal glass candle diffuser. An Antique Bronze finish complements a variety of exteriors, including Transitional and Traditional and Farmhouse designs.

FINISH
● Antique Bronze - 20

POST LANTERN
P540026-020-30 Antique Bronze
12-5/16" dia., 22-7/8" ht.
Fits 3" post (order separately).
One 9w LED module, 3000K,
90 CRI, 624 source lumens.



HANGING LANTERN
P550026-020-30 Antique Bronze
12-5/16" dia., 21" ht.
Overall ht. w/chain 96", wire 10'.
One 17w LED module, 3000K,
90 CRI, 1276 source lumens.



SMALL WALL LANTERN
P560068-020-30 Antique Bronze
7-7/8" W., 14-3/8" ht.
Extends 8". H/CTR 3-5/8".
One 9w LED module, 3000K,
90 CRI, 624 source lumens.



MEDIUM WALL LANTERN
P560069-020-30 Antique Bronze
10" W., 18" ht.
Extends 10". H/CTR 4".
One 9w LED module, 3000K,
90 CRI, 624 source lumens.



LARGE WALL LANTERN
P560070-020-30 Antique Bronze
12-5/16" W., 22" ht.
Extends 12". H/CTR 4-3/4".
One 17w LED module, 3000K,
90 CRI, 1276 source lumens.



P560070-020-30

DESIGN+SERIES™
LEAWOOD LED



Leawood LED provides delicate scrollwork with dramatic shadow patterns in a modern form. Intricate die cast aluminum construction is available in classic Black or White finish options. A taller design accommodates the larger scale commonly seen in today's modern and traditional architecture. Available in hanging, post and wall lanterns.

FINISHES
○ White - 30
● Black - 31

LED POST LANTERN
P540037-030-30 White
P540037-031-30 Black
10" dia., 18-7/8" ht.
Fits 3" post (order separately).
One 17w LED module, 3000K,
90CRI, 1276 source lumens.



LED HANGING LANTERN
P550037-030-30 White
P550037-031-30 Black
10" dia., 19-3/8" ht.
Overall ht. w/chain 93-1/2", wire 10'.
One 9w LED module, 3000K,
90CRI, 624 source lumens.



LED SMALL WALL LANTERN
P560104-030-30 White
P560104-031-30 Black
8" dia., 13-5/8" ht.
Extends 9-12". H/CTR 4-5/8".
One 9w LED module, 3000K,
90CRI, 624 source lumens.



LED MEDIUM WALL LANTERN
P560105-030-30 White
P560105-031-30 Black
10" dia., 17" ht.
Extends 11-3/4". H/CTR 5-3/4".
One 9w LED module, 3000K,
90CRI, 624 source lumens.



P550037-030-30



P550037-031-30



P560104-030-30



P560104-031-30



P560105-030-30



P560105-031-30



P540037-030-30



P540037-031-30

DESIGN+SERIES™
NORTHAMPTON LED



Northampton LED lanterns take a designer-influenced approach for these updated outdoor wall lanterns. Two distinctive styles provide a modern or more traditional accent to your home with striking textured glass in a classic pattern. A Black frame highlights clear fluted glass panels with a metallic silver interior reflector, while the Architectural Bronze housing showcases clear seeded glass with a quatrefoil inspired metal pattern paired with a brass tone internal reflector.

- FINISH**
- Architectural Bronze - 129
 - Black - 031

SMALL LED WALL LANTERN
P560106-129-30 Architectural Bronze
P560108-031-30 Black
6-3/4" W., 12-1/2" ht.
Extends 5". H/CTR 6-1/4".
One 9w LED module, 3000K, 90CRI, 624 source lumens.



MEDIUM LED WALL LANTERN
P560107-129-30 Architectural Bronze
P560109-031-30 Black
6-3/4" W., 22" ht.
Extends 5". H/CTR 11".
One 9w LED module, 3000K, 90CRI, 624 source lumens.



P560106-129-30



P560108-031-30



P560107-129-30



P560109-031-30

ARRIVE LED



Arrive LED lanterns feature a die-cast aluminum powder coated frame and heavily textured glass to create a unique visual effect.



P6067-3130K9



P6069-3130K9



P6068-3130K9



P6076-3130K9



P6427-3130K9



P6527-3130K9

- FINISH**
- Black - 31

SMALL WALL LANTERN
P6067-3130K9 Black
6" W., 8-3/4" ht.
Extends 7-3/8". H/CTR 4".
One 9w LED module, 3000K, 90CRI, 623 source lumens.



MEDIUM WALL LANTERN
P6068-3130K9 Black
7-1/2" W., 11-1/8" ht.
Extends 8-3/4". H/CTR 5-1/4".
One 9w LED module, 3000K, 90CRI, 623 source lumens.



LARGE WALL LANTERN
P6069-3130K9 Black
9" W., 13" ht.
Extends 10-1/4". H/CTR 5-3/4".
One 17w LED module, 3000K, 90CRI, 1211 source lumens



EXTRA LARGE WALL LANTERN
P6076-3130K9 Black
11" W., 16" ht.
Extends 12-1/4". H/CTR 8-5/8".
One 17w LED module, 3000K, 90CRI, 1211 source lumens



POST LANTERN
P6427-3130K9 Black
9" sq., 15-7/8" ht.
Fits 3" post (order separately).
One 17w LED module, 3000K, 90CRI, 1211 source lumens



HANGING LANTERN
P6527-3130K9 Black
9" sq., 15-1/8" ht. Overall ht. w/chain 88-1/4"; wire 15'.
One 17w LED module, 3000K, 90CRI, 1211 source lumens



ENDORSE LED



Endorse celebrates the traditional form of a gas-powered coach light with illumination from a modern LED source. A die-cast aluminum, powder coated frame creates an intriguing visual effect with clear beveled glass. To add a decorative element in the lantern, a fluted frosted glass column is offered as an accessory.

FINISH
● Black - 31

SMALL WALL LANTERN
P6056-3130K9 Black
6-3/4" W., 12" ht.
Extends 7-5/8". H/CTR 3-1/4".
One 9w LED module, 3000K, 90CRI, 623 source lumens.



MEDIUM WALL LANTERN
P6057-3130K9 Black
8-3/4" W., 14-3/4" ht.
Extends 9-3/4". H/CTR 4".
One 9w LED module, 3000K, 90CRI, 623 source lumens.



LARGE WALL LANTERN
P6058-3130K9 Black
10-3/4" W., 17-3/4" ht.
Extends 11-3/4". H/CTR 4".
One 9w LED module, 3000K, 90CRI, 623 source lumens.



POST LANTERN
P6426-3130K9 Black
10-3/4" W., 21" ht.
One 9w LED module, 3000K, 90CRI, 623 source lumens.



P6056-3130K9



P6056-3130K9
*Shown with P8774-31
accessory column*



P6057-3130K9



P6057-3130K9
*Shown with P8775-31
accessory column*



P6058-3130K9



P6426-3130K9

DERBY LED



Craftsman styling marries traditional and rustic details. Derby boasts an artistic glass diffuser with a die-cast aluminum, powder coated Antique Bronze frame.

FINISH
● Antique Bronze - 20

SMALL WALL LANTERN
P5749-2030K9 Antique Bronze
6-1/2" W., 8-3/8" ht.
Extends 7-3/8". H/CTR 3".
One 9w LED module, 3000K, 90CRI, 623 source lumens.



MEDIUM WALL LANTERN
P5750-2030K9 Antique Bronze
8-1/2" W., 11-1/4" ht.
Extends 9-3/8". H/CTR 4-1/4".
One 9w LED module, 3000K, 90CRI, 623 source lumens.



LARGE WALL LANTERN
P5751-2030K9 Antique Bronze
10-5/8" W., 15-1/2" ht.
Extends 11-5/8". H/CTR 3-3/8".
One 9w LED module, 3000K, 90CRI, 623 source lumens.



P5749-2030K9



P5750-2030K9



P5751-2030K9

WISH LED

The Wish Collection recognizes the growing trend seeking to protect views of the night sky. This innovative style conceals a full cutoff shield to combine a traditional lantern aesthetic with dark sky performance. To further extend the versatility of this classic style, the shield can be removed for those that like the style, but don't require dark sky compliance. Available in wall, hanging or post applications. Post light does not include full cutoff shield.

FINISHES
● Antique Bronze - 20
● Black - 31

SMALL WALL LANTERN
P6084-2030K9 Antique Bronze
P6084-3130K9 Black
7" W., 10-3/8" ht.
Extends 8-5/8". H/CTR 3-1/8".
One 9w LED module, 3000K, 90CRI, 623 source lumens.

MEDIUM WALL LANTERN
P6085-2030K9 Antique Bronze
P6085-3130K9 Black
9" W., 12-1/2" ht.
Extends 10-1/2". H/CTR 3-1/8".
One 17w LED module, 3000K, 90CRI, 623 source lumens.

POST LANTERN
P6424-2030K9 Antique Bronze
P6424-3130K9 Black
Dark Sky shield not included.
9" dia., 15-1/4" ht.
Fits 3" post (order separately).
One 9w LED module, 3000K, 90CRI, 623 source lumens.



Dark sky cylinder included, except the post lantern.



P6084-2030K9



P6084-3130K9



P6085-2030K9



P6085-3130K9



P6424-2030K9



P6424-3130K9

CALLAHAN LED



Callahan draws inspiration from farmhouse decor. Hidden within this vintage frame is a modern LED light source that delivers energy-efficient performance. The inner surface of the shade is accented with a contrasting finish to complete the nostalgic look. Additionally, the full reflector provides illumination that is compliant with Dark Sky requirements for full cutoff lighting.

FINISHES
● Antique Bronze - 020
● Antique Pewter - 103

SMALL WALL LANTERN
P560052-020-30 Antique Bronze
P560052-103-30 Antique Pewter
8-1/2" W., 10" ht.
Extends 8-7/8". H/CTR 3-3/4".
One 9w LED module , 3000K, 90CRI, 624 source lumens.

MEDIUM WALL LANTERN
P560053-020-30 Antique Bronze
P560053-103-30 Antique Pewter
11" W., 11-1/2" ht.
Extends 11-1/2". H/CTR 4-1/4".
One 17w LED module, 3000K, 90CRI, 1273 source lumens.



P560052-020-30



P560053-020-30



P560052-103-30



P560053-103-30

BROOKSIDE LED

Get inspired by vintage undertones and train station styling with this outdoor lantern collection Available in Brushed Nickel, Antique Bronze, aluminium with Gilded Iron finish or solid brass Antique Nickel or solid Copper that ages to a patina finish. Dark Sky compliant.

- FINISHES**
- Brushed Nickel- 09
 - Copper - 14
 - Gilded Iron - 71
 - Antique Nickel - 81

LED PENDANT
P5024-0930K9 Brushed Nickel
12" dia., 9-1/8" ht.
Overall ht. w/stem 65"; wire 15'.
One 9w LED module, 3000K, 90CRI, 623 source lumens.



LARGE WALL LANTERN
P5723-1430K9 Copper
P5723-7130K9 Gilded Iron
P5723-8130K9 Antique Nickel
12" W., 12-1/4" ht.
Extends 13-1/4". H/CTR 6-7/8".
One 17w LED module, 3000K, 90CRI, 1211 source lumens.



P5024-0930K9



P5723-1430K9



P5723-7130K9



P5723-8130K9

DISTRICT LED

The outdoor lanterns from the District Collection features a metal shade that offers an industrial-inspired design. The versatile vintage form can be used in outdoor applications. Dark sky compliant.

- FINISHES**
- Antique Bronze - 20
 - Metallic Gray -82

MEDIUM WALL LANTERN
P5622-2030K9 Antique Bronze
P5622-8230K9 Metallic Gray
8" W., 8-1/4" ht.
Extends 10-1/4". H/CTR 4-1/8".
One 9w LED module, 3000K, 90CRI, 623 source lumens.



LARGE WALL LANTERN
P5623-2030K9 Antique Bronze
P5623-8230K9 Metallic Gray
12" W., 10-1/2" ht.
Extends 13-1/4". H/CTR 5".
One 9w LED module, 3000K, 90CRI, 623 source lumens.



P5622-2030K9



P5622-8230K9



P5623-2030K9



P5623-8230K9



Featuring District LED, Chronicle pendants (image: Landmark Homes)

EAST HAVEN LED

East Haven offers contemporary styling to complement today's home styles. A Black or Antique Bronze frame cradles a seeded glass shade.

- FINISHES**
- Antique Bronze - 20
 - Black - 31

SMALL WALL LANTERN
P6077-2030K9 Antique Bronze
P6077-3130K9 Black
5-3/4" W., 7-7/8" ht.
Extends 7-1/2". H/CTR 4-3/4".
One 9w LED module, 3000K, 90CRI, 623 source lumens.



P6077-2030K9



P6077-3130K9

MEDIUM WALL LANTERN
P6078-2030K9 Antique Bronze
P6078-3130K9 Black
7-1/2" W., 9-3/4" ht.
Extends 9-1/8". H/CTR 4-3/4".
One 9w LED module, 3000K, 90CRI, 623 source lumens.



P6078-2030K9



P6078-3130K9

LARGE WALL LANTERN
P6079-2030K9 Antique Bronze
P6079-3130K9 Black
9-1/2" W., 12" ht.
Extends 11-1/8". H/CTR 4-3/4".
One 17w LED module, 3000K, 90CRI, 1211 source lumens.



P6079-2030K9



P6079-3130K9

POST LANTERN
P6430-2030K9 Antique Bronze
P6430-3130K9 Black
7-1/2" dia., 15" ht.
Fits 3" post (order separately).
One 9w LED module, 3000K, 90CRI, 623 source lumens.



P6430-2030K9



P6430-3130K9

WESTPORT LED

Westport LED offers traditional styling to complement a variety of home décor options. A durable, die-cast aluminum frame cradles a softly diffused, seeded glass shade.

- FINISHES**
- Antique Bronze - 20
 - Black - 31

POST LANTERN
P5445-2030K9 Antique Bronze
P5445-3130K9 Black
9" dia., 16-3/8" ht.
Fits 3" post (order separately).
One 9w LED module, 3000K, 90CRI, 623 source lumens.



P5862-2030K9



P5862-3130K9

SMALL WALL LANTERN
P5862-2030K9 Antique Bronze
P5862-3130K9 Black
6-7/8" W., 10-1/4" ht.
Extends 8-3/8". H/CTR 3-1/8".
One 9w LED module, 3000K, 90CRI, 623 source lumens.



P5863-2030K9



P5863-3130K9

MEDIUM WALL LANTERN
P5863-2030K9 Antique Bronze
P5863-3130K9 Black
9" W., 12-7/8" ht.
Extends 10-3/8". H/CTR 3-3/4".
One 9w LED module, 3000K, 90CRI, 623 source lumens.



P5864-2030K9



P5864-3130K9

LARGE WALL LANTERN
P5864-2030K9 Antique Bronze
P5864-3130K9 Black
11" W., 15-3/8" ht.
Extends 12-7/8". H/CTR 4".
One 17w LED module, 3000K, 90CRI, 1211 source lumens.



P5445-2030K9



P5445-3130K9

BELL LED

Featuring nautical undertones, the Bell LED outdoor collection offers cage lights reminiscent of industrial architecture.

- FINISHES**
- Antique Bronze - 20
 - Textured Graphite -136

WALL LANTERN
P5676-2030K9 Antique Bronze
P5676-13630K9 Textured Graphite
5-1/2" W., 10-5/8" ht.
Extends 7-3/8". H/CTR 3".
One 9w LED module, 3000K,
90CRI, 623 source lumens.



P5676-2030K9



P5676-13630K9

PIER 33 LED

Outdoor wall lanterns from the Pier 33 LED collection feature coastal undertones and a design reminiscent of industrial spaces. Comprised of a die-cast frame. Clear seeded glass complements a Black finish.

- FINISH**
- Black - 031

LED WALL LANTERN
P560071-031-30 Black
8-1/8" W., 8" ht.
Extends 9". H/CTR 3-1/8".
One 9w LED module, 3000K,
90CRI, 624 source lumens.



P560071-031-30

LED WALL LANTERN
P560034-031-30 Black
8-1/8" dia., 13" ht.
Extends 9". H/CTR 3-1/4".
One 9w LED module, 3000K,
90CRI, 624 source lumens.



P560034-031-30

LED BULKHEADS

Robust and energy efficient, LED bulkheads are a general-purpose luminaire. Comprised of a die-cast aluminum frame and polycarbonate diffuser. Fixtures are impact resistant and offer various mounting options and can be widely adopted for outdoor applications.

- FINISHES**
- White - 30
 - Black - 31

LED BULKHEAD
P3647-3030K9 White
P3647-3130K9 Black
6-1/2" W., 10-1/2" ht.
Extends 4-3/8". H/CTR 5-1/4".
One 9w LED module, 3000K,
90CRI, 623 source lumens.



P3647-3030K9
shown wall-mounted



P3647-3130K9
shown ceiling-mounted

LED BULKHEAD
P3648-3030K9 White
P3648-3130K9 Black
9-1/2" W., 4-3/8" ht.
H/CTR 4-3/4".
One 17w LED module, 3000K,
90CRI, 623 source lumens.



P3648-3030K9
shown ceiling-mounted



P3648-3130K9
shown wall-mounted

LED BULKHEAD
P3649-3030K9 White
P3649-3130K9 Black
6-1/2" W., 10-1/2" ht.
Extends 4-1/2". H/CTR 5-1/4".
One 9w LED module, 3000K,
90CRI, 623 source lumens.



P3649-3030K9
shown ceiling-mounted



P3649-3130K9
shown wall-mounted

LED BULKHEAD
P3650-3030K9 White
P3650-3130K9 Black
9-1/2" W., 4-1/2" ht.
H/CTR 4-3/4".
One 17w LED module, 3000K,
90CRI, 623 source lumens.



P3650-3030K9
shown ceiling-mounted



P3650-3130K9
shown wall-mounted

MILFORD LED

Etched glass surrounded by a die-cast aluminum frame, ideal for outdoor applications.

FINISHES

- Black - 31

ONE-LIGHT FLUSH MOUNT
P3665-3130K9 Black
8-5/8" dia., 4-1/8" ht.
One 17w LED module, 3000K,
90CRI, 1211 source lumens.



P3665-3130K9

ONE-LIGHT FLUSH MOUNT
P3673-3130K9 Black
10-5/8" dia., 4-7/8" ht.
One 17w LED module, 3000K,
90CRI, 1211 source lumens.



P3673-3130K9

DIE-CAST LED

This energy efficient LED wall lantern features a Black finish on a die-cast aluminum frame. This fixture includes integrated LED technology with no bulbs to replace. The frosted glass panels have a warm quality that adds to the lantern's traditional design.

- FINISH
- Black - 031

LED WALL LANTERN
P560136-031-30 Black
5-5/8" dia., 8-7/8" ht.
Extends 6-5/8". H/CTR 6-5/8".
One 11w integrated LED, 3000K,
80CRI, 560 delivered lumens.



P560136-031-30

ANSON LED

Stainless steel frame with polycarbonate diffuser

FINISH

- Architectural Bronze - 129

WALL LANTERN
P560001-129-30 Architectural Bronze
10" W., 3" ht.
One 17w LED module, 3000K,
90CRI, 1452 source lumens.



P560001-129-30

VALERA LED

White acrylic diffuser

FINISH

- Architectural Bronze - 129

LED WALL LANTERN
P5800-12930K9 Architectural Bronze
5-5/8" W., 8" ht.
Extends 4". H/CTR 4".
One 9w LED module, 3000K,
90 CRI, 623 lumens per module.



P5806-12930K9

LED WALL LANTERN
P5801-12930K9 Architectural Bronze
8-5/8" W., 11" ht.
Extends 4". H/CTR 5-1/2".
One 17w LED module, 3000K,
90 CRI, 1211 lumens per module.



LED WALL LANTERN
P5806-12930K9 Architectural Bronze
5-5/8" W., 16" ht.
Extends 4". H/CTR 8".
Two 9w LED modules, 3000K,
90 CRI, 623 lumens per module.



P5800-12930K9




P5801-12930K9

STRATA

The Strata features a modern, low profile design ideal for residential and multifamily applications. Energy efficient and functional, wall mounted, can be installed indoor and outdoor.

- FINISHES**
- White - 030
 - Metallic Gray - 82
 - Antique Bronze - 020
 - Black - 031
- WALL LANTERN**
P560090-020-30K Antique Bronze
P560090-030-30K White
P560090-031-30K Black
P560090-082-30K Metallic Gray
6-5/8" W., 5-1/2" ht.
12w integrated LED, 3000K, 90CRI,
825 delivered lumens.



P560090-030-30K



P560090-082-30K



P560090-020-30K



P560090-031-30K

CORNICE LED

Modern geometric outdoor LED sconces are designed to complement a range of residential and commercial architectural styles.

- FINISHES**
- Antique Bronze - 20
 - Black - 31
 - Metallic Gray - 82
- LED OUTDOOR WALL SCONCE**
P5634-2030K9 Antique Bronze
P5634-3130K9 Black
P5634-8230K9 Metallic Gray
5-1/4" W., 4-3/4" ht.
Extends 4". H/CTR 2-3/8".
One 9w LED module, 3000K,
623 source lumens.



- LED OUTDOOR WALL SCONCE**
P5635-2030K9 Antique Bronze
P5635-3130K9 Black
P5635-8230K9 Metallic Gray
6-1/8" W., 5" ht.
Extends 4". H/CTR 2-3/8".
One 9w LED module, 3000K,
623 source lumens.



P5634-2030K9



P5635-2030K9



P5634-3130K9



P5635-3130K9



P5634-8230K9



P5635-8230K9

Z-1010 LED

A modern outdoor sconce with an open linear frame and seeded glass diffuser. Finished in Black or Architectural Bronze.

- FINISHES**
- Black - 031
 - Architectural Bronze - 129

- LED WALL LANTERN**
P560029-031-30 Black
P560029-129-30 Architectural Bronze
7-1/2" W., 16" ht.
Extends 4". H/CTR 4-1/4".
One 9w LED module. 3000K
90CRI, 624 source lumens.



P560029-031-30



P560029-129-30

Z-1020 LED

A modern outdoor sconce with white glass shade is suspended in a curved frame that serves as a reflector when illuminated. Finished in Black or Architectural Bronze.

- FINISHES**
- Black - 031
 - Architectural Bronze - 129

- LED WALL LANTERN**
P560030-031-30 Black
P560030-129-30 Architectural Bronze
7-1/2" W., 13-1/2" ht.
Extends 4-3/4". H/CTR 11-1/8".
One 9w LED module. 3000K
90CRI, 670 source lumens.



P560030-031-30



P560030-129-30

Z-1030 LED

A modern outdoor LED sconce with an architectural-inspired open linear frame and clear glass diffuser. Finished in Black, White, Metallic Gray or Antique Bronze. Meets California Title 24 high efficacy requirements for outdoor use only.

- FINISHES**
- Antique Bronze - 020
 - White - 030
 - Black - 031
 - Metallic Gray -082

SMALL WALL LANTERN
P560051-020-30 Antique Bronze
P560051-030-30 White
P560051-031-30 Black
P560051-082-30 Metallic Gray
5-1/8" W., 12" ht.
Extends 5-3/4". H/CTR 2-1/4".
One 9w LED module, 3000K, 90CRI, 624 source lumens



P560051-020-30



P560051-030-30



P560051-031-30



P560051-082-30


MEDIUM WALL LANTERN
P560056-020-30 Antique Bronze
P560056-030-30 White
P560056-031-30 Black
P560056-082-30 Metallic Gray
5-1/8" W., 20" ht.
Extends 5-3/4". H/CTR 2-1/4".
One 9w LED module, 3000K, 90CRI, 624 source lumens



P560056-020-30



P560056-030-30



P560056-031-30



P560056-082-30

Z-1050 LED

Featuring a modern design, the Z-1050 LED sconce is suitable for a variety of exterior or interior architecture settings. Wall sconce is wet location listed with a replaceable LED module protected within a glass enclosure.

- FINISH**
- Black - 031

MEDIUM WALL LANTERN
P560093-031-30 Black
12" dia., 12" ht.
Extends 3". H/CTR 6".
One 9w LED module, 3000K, 90CRI, 670 source lumens.



P560093-031-30

Z-1060 LED

Z-1060 presents a functional design with a modern sensibility. Architectural style housing is die-cast for added durability. The glass diffuser is secured without visible fasteners for an overall clean appearance. LED source delivers both energy efficiency and maintenance-free operation.

- FINISH**
- Black - 031

SMALL WALL LANTERN
P560072-031-30 Black
4-1/2" W., 4-1/2" ht.
Extends 4-3/4". H/CTR 2-1/4".
One 9w LED module, 3000K, 90CRI, 624 source lumens.



P560072-031-30

SMALL WALL LANTERN
P560073-031-30 Black
Shown with glass
4-1/2" W., 4-1/2" ht.
Extends 4-3/4". H/CTR 2-1/4".
One 9w LED module, 3000K, 90CRI, 624 source lumens.



P560073-031-30

3" LED CYLINDERS



LED Cylinders are sleek and modern in design and are available in a variety of finish options and sizes. Suitable for interior and exterior applications, LED Cylinders feature a die-cast aluminum framing that is fade and chip-resistant. LED Cylinders are UL listed for wet locations.

- FINISHES**
 - Antique Bronze - 020
 - White - 030
 - Graphite - 143
 - Satin Nickel - 147
- 3" DOWNLIGHT CYLINDER**

P563000-020-30K Antique Bronze
P563000-030-30K White
P563000-143-30K Graphite
P563000-147-30K Satin Nickel
5-1/2" W., 5-5/8" ht.
12w integrated LED, 3000K, 90CRI, 900 delivered lumens.



- 3" UP/DOWNLIGHT CYLINDER**

P563001-020-30K Antique Bronze
P563001-030-30K White
P563001-143-30K Graphite
P563001-147-30K Satin Nickel
5-1/2" W., 8-1/4" ht.
24w integrated LED, 3000K, 90CRI, 1800 delivered lumens.



P563000-020-30K



P563001-020-30K



P563000-030-30K



P563001-030-30K



P563000-143-30K



P563001-143-30K



P563000-147-30K



P563001-147-30K

5" LED CYLINDERS

LED Cylinders are sleek and modern in design and are available in a variety of finish options and sizes. Suitable for interior and exterior applications, LED Cylinders feature a die-cast aluminum framing that is fade and chip-resistant. LED Cylinders are UL listed for wet locations when used with a lens cover accessory.

- FINISHES**
 - Antique Bronze - 20
 - White - 30
 - Black - 31
 - Metallic Gray - 82
- 5" FLUSH MOUNT CYLINDER**

P5774-20/30K Bronze
P5774-30/30K White
P5774-31/30K Black
P5774-82/30K Metallic Gray
5" W., 6-1/2" ht.
17w integrated LED, 3000K, 90CRI, 764 delivered lumens.



- 5" DOWNLIGHT CYLINDER**

P5674-20/30K Bronze
P5674-30/30K White
P5674-31/30K Black
P5674-82/30K Metallic Gray
5" W., 7-1/4" ht.
Extends 8". H/CTR 2-1/2".
17w integrated LED, 3000K, 90CRI, 531 delivered lumens.



- 5" UP/DOWNLIGHT CYLINDER**

P5675-20/30K Bronze
P5675-30/30K White
P5675-31/30K Black
P5675-82/30K Metallic Gray
5" W., 14" ht.
Extends 8". H/CTR 7".
34w integrated LED, 3000K, 90CRI, 1025 delivered lumens.
**Requires Top cover lens, P860038-031*



P5774-20/30K



P5774-30/30K



P5774-31/30K



P5774-82/30K



P5674-20/30K



P5674-30/30K



P5674-31/30K



P5674-82/30K



P5675-20/30K



P5675-30/30K



P5675-31/30K



P5675-82/30K

6" LED CYLINDERS

LED Cylinders are sleek and modern in design and are available in a variety of finish options and sizes. Suitable for interior and exterior applications, LED Cylinders feature a die-cast aluminum framing that is fade and chip-resistant. LED Cylinders are UL listed for wet locations when used with a lens cover accessory.

FINISHES

- Antique Bronze - 20
- White - 30
- Black - 31
- Metallic Gray - 82

6" FLUSH MOUNT CYLINDER

P5741-20/30K Bronze
P5741-30/30K White
P5741-31/30K Black
P5741-82/30K Metallic Gray
6" W., 12" ht.
29w integrated LED, 3000K, 90CRI, 1800 delivered lumens



P5741-20/30K



P5741-30/30K



P5741-31/30K



P5741-82/30K

6" DOWNLIGHT CYLINDER

P5641-20/30K Bronze
P5641-30/30K White
P5641-31/30K Black
P5641-82/30K Metallic Gray
6" W., 12" ht.
Extends 8-7/8". H/CTR 4-1/2".
29w integrated LED, 3000K, 90CRI, 1800 delivered lumens



P5641-20/30K



P5641-30/30K



P5641-31/30K



P5641-82/30K

6" UP/DOWNLIGHT CYLINDER

P5642-20/30K Bronze
P5642-30/30K White
P5642-31/30K Black
P5642-82/30K Metallic Gray
6" W., 18" ht.
Extends 8-7/8".. H/CTR 9".
29w integrated LED, 3000K, 90CRI, 2566 delivered lumens
**Requires Top cover lens, P860039-031*



P5642-20/30K



P5642-30/30K



P5642-31/30K



P5642-82/30K



Featuring Square Cylinders

ALUMINUM LED SQUARES

Aluminum LED Squares are heavy-duty in design and are available in a variety of finish options. Suitable for interior and exterior applications, LED Squares feature a powder coat that is fade and chip-resistant. LED Cylinders are UL listed for wet locations when used with a lens cover accessory.

FINISHES

- Antique Bronze - 20
- White - 30
- Black - 31
- Metallic Gray - 82

6" DOWNLIGHT SQUARE

P5643-20/30K Bronze
P5643-30/30K White
P5643-31/30K Black
P5643-82/30K Metallic Gray
6" W., 12" ht.
Extends 8-7/8". H/CTR 4-1/2".
29w integrated LED, 3000K, 90CRI, 1800 delivered lumens



P5643-20-30K



P5643-30-30K



P5643-31-30K



P5643-82-30K

6" UP/DOWNLIGHT SQUARE

P5644-20/30K Bronze
P5644-30/30K White
P5644-31/30K Black
P5644-82/30K Metallic Gray
6" W., 18" ht.
Extends 8-7/8". H/CTR 8".
29w integrated LED, 3000K, 90CRI, 1800 delivered lumens



*Requires Top cover lens, P8797-31



P5644-20-30K



P5644-30-30K



P5644-31-30K



P5644-82-30K



Featuring Globe LED

Interior Decorative

APOGEE LED



P350066-009-30

Designed for both commercial and residential interiors, Apogee fixtures deliver both style and bright illumination. The collection includes flush mount and pendant options that can also be installed as a semi-flush mount fixture. All fixtures feature 120-277V input with standard 0-10V dimming. Etched glass shade provides an even and pleasing light effect.

FINISHES

- Brushed Nickel - 009
- Architectural Bronze - 129



P350065-009-30



P350066-009-30



P350071-009-30



P710036-009-30



P350064-009-30
shown as semi-flush



P350064-009-30
shown as pendant



P350070-009-30



P350072-009-30

SEMI-FLUSH CONVERTIBLE
P350064-009-30 Brushed Nickel
Hanging and ceiling mount hardware included.
15" dia., 10-3/4" ht.
Overall ht. w/chain 85-1/4, wire 15'.
30w integrated LED, 3000K, 90CRI, 1855 delivered lumens, 120-277V, 0-10V dimming.



SEMI-FLUSH CONVERTIBLE
P350065-009-30 Brushed Nickel
Hanging and ceiling mount hardware included.
21" dia., 14-1/2" ht.
Overall ht. w/chain 92", wire 15'.
45w integrated LED, 3000K, 90CRI, 2765 delivered lumens, 120-277V, 0-10V dimming.



SEMI-FLUSH CONVERTIBLE
P350066-009-30 Brushed Nickel
Hanging and ceiling mount hardware included.
27" dia., 20-5/8" ht.
Overall ht. w/chain 98, wire 15'.
71w integrated LED, 3000K, 90CRI, 4215 delivered lumens, 120-277V, 0-10V dimming.



FLUSH MOUNT
P350070-009-30 Brushed Nickel
15" dia., 3-11/16" ht.
30w integrated LED, 3000K, 90CRI, 1660 delivered lumens, 120-277V, 0-10V dimming.



FLUSH MOUNT
P350071-009-30 Brushed Nickel
21" dia., 4-1/2" ht.
45w integrated LED, 3000K, 90CRI, 2550 delivered lumens, 120-277V, 0-10V dimming.



FLUSH MOUNT
P350072-009-30 Brushed Nickel
27" dia., 5-3/8" ht.
71w integrated LED, 3000K, 90CRI, 3850 delivered lumens, 120-277V, 0-10V dimming.



WALL SCONCE
P710036-009-30 Brushed Nickel
15" W., 7-1/2" ht., Extends 3-11/16"
20w integrated LED, 3000K, 90CRI, 940 delivered lumens, 120-277V, 0-10V dimming.





P350066-129-30

APOGEE LED

SEMI-FLUSH CONVERTIBLE
P350064-129-30 Architectural Bronze
Hanging and ceiling mount hardware included.
15" dia., 10-3/4" ht.
Overall ht. w/chain 85-1/4", wire 15'.
30w integrated LED, 3000K, 90CRI, 1855 delivered lumens, 120-277V, 0-10V dimming.



SEMI-FLUSH CONVERTIBLE
P350065-129-30 Architectural Bronze
Hanging and ceiling mount hardware included.
21" dia., 14-1/2" ht.
Overall ht. w/chain 92", wire 15'.
45w integrated LED, 3000K, 90CRI, 2765 delivered lumens, 120-277V, 0-10V dimming.



SEMI-FLUSH CONVERTIBLE
P350066-129-30 Architectural Bronze
Hanging and ceiling mount hardware included.
27" dia., 20-5/8" ht.
Overall ht. w/chain 98", wire 15'.
71w integrated LED, 3000K, 90CRI, 4215 delivered lumens, 120-277V, 0-10V dimming.



FLUSH MOUNT
P350070-129-30 Architectural Bronze
15" dia., 3-11/16" ht.
30w integrated LED, 3000K, 90CRI, 1660 delivered lumens, 120-277V, 0-10V dimming.



FLUSH MOUNT
P350071-129-30 Architectural Bronze
21" dia., 4-1/2" ht.
45w integrated LED, 3000K, 90CRI, 2550 delivered lumens, 120-277V, 0-10V dimming.



FLUSH MOUNT
P350072-129-30 Architectural Bronze
27" dia., 5-3/8" ht.
71w integrated LED, 3000K, 90CRI, 3850 delivered lumens, 120-277V, 0-10V dimming.



WALL SCONCE
P710036-129-30
Architectural Bronze
15" W., 7-1/2" ht., Extends 3-11/16".
20w integrated LED, 3000K, 90CRI, 940 delivered lumens, 120-277V, 0-10V dimming.



P350065-129-30

P710036-129-30

P350066-129-30

P350064-129-30
shown as semi-flush

P350064-129-30
shown as pendant

P350071-129-30

P350070-129-30

P350072-129-30

GLOBE LED



P500147-109-30



Distinctive Classic globe pendants are accented by striking metal caps in three finish options: Brushed Nickel, Polished Chrome and Brushed Bronze. Ideal for Modern, Mid-Century or Farmhouse interior design styles. These versatile pendants can be displayed singularly or in groupings of two or more by mixing and matching finish options and lengths to create custom lighting designs for the home.

FINISHES

- Brushed Nickel - 009
- Polished Chrome - 015
- Brushed Bronze - 109

LED PENDANT

P500147-009-30 Brushed Nickel

P500147-015-30 Polished Chrome

P500147-109-30 Brushed Bronze
8" dia., 9-3/4" ht.


Overall ht. w/cord 122", wire 120".

One 9w LED module, 3000K,
90CRI, 624 source lumens.



See canopy accessory options at
progresslighting.com






The Concourse LED linear pendant features minimalist design styling and a slim profile that appears to float along the ceiling. Offering energy efficiency and low maintenance benefits, Concourse LED is suitable for both home and commercial applications providing direct, ambient, beautifully diffused light. A Brushed Nickel frame completes the clean seamless look.



FINISH
● Brushed Nickel - 009

LED LINEAR PENDANT
P500002-009-30 Brushed Nickel
40" W., 113" ht. Extends 5-1/4".
39w integrated LED, 3000K, 90CRI,
2400 delivered lumens.

JAB



P500002-009-30
Alternate view

NEAT LED

These timeless and classic LED pendants feature designer oriented details and polished opal glass. Can be displayed singularly or in groupings of two or more in a variety of spaces, such as Modern Farmhouse, Coastal and Mid-Century Modern environments.

FINISHES
● Brushed Nickel - 009
● Antique Bronze - 020

ONE-LIGHT PENDANT
P500065-009-30 Brushed Nickel
P500065-020-30 Antique Bronze
4-3/8" dia., 13-1/2" ht.
Overall ht. W/Cord 124-1/2", wire 10'.
One 9w LED module, 3000K,
90CRI, 624 source lumens.



ONE-LIGHT PENDANT
P500066-009-30 Brushed Nickel
P500066-020-30 Antique Bronze
6-5/8" dia., 13-1/2" ht.
Overall ht. W/Cord 124-1/2", wire 10'.
One 9w LED module, 3000K,
90CRI, 624 source lumens.



P500065-009-30



P500065-020-30



P500066-009-30



P500066-020-30

MODERNA LED

Moderna's modern-inspired silhouette provides a signature focal point for a variety of interior spaces. Features clear outer glass with an inner etched white glass shade and a sleek linear frame.

FINISH
● Brushed Nickel - 009

ONE-LIGHT LED
MINI-PENDANT
P500000-009-30 Brushed Nickel
5-3/4" dia., 9-1/2" ht.
Overall ht. w/stem 75-1/2"; wire 10'.
One 9w LED module, 3000K,
90 CRI, 670 source lumens.



P500000-009-30

GATHER LED

Simplified frame with updated styling and elegant etched glass shades. Energy efficient version is available with select fixtures in the Brushed Nickel finish.

FINISHES

- Brushed Nickel - 009
- Polished Chrome - 015
- Antique Bronze - 020

LED SEMI-FLUSH CONVERTIBLE

P350088-009-30 Brushed Nickel
P350088-015-30 Polished Chrome
P350088-020-30 Antique Bronze
Hanging and ceiling mount hardware included.
12-7/8" dia., 10-3/8" ht.
Overall ht. w/chain 50", wire 10'.
One 17w LED module, 3000K, 90CRI, 1276 source lumens.



P350088-015-30
Shown as pendant



P350088-020-30
Shown as pendant



P350088-009-30
Shown as pendant

LED SCONCE

An elegant white linen shade that is open on the top and bottom diffuses light efficiently. Ideal for vanity and hospitality applications.

FINISHES

- Brushed Nickel - 009
- Architectural Bronze - 129

LED WALL SCONCE

P710010-009-30 Brushed Nickel
P710010-129-30 Architectural Bronze
6-3/4" W., 12" ht. Extends 4". H/CTR 6".
One 9w LED module, 3000K 90CRI, 624 source lumens.



P710010-009-30



P710010-129-30

INSPIRE LED

Harkening back to a simpler time, the Inspire Collection freshens traditional forms with its clean lines. Now debuting with an integrated LED light source, the wall scone softly shines through a textured Summer Linen Shade or a creamy Off-White Linen Shade.

FINISHES

- Summer Linen - 030
- Off White Linen - 159

LED WALL SCONCE

P710071-030-30 Summer Linen
P710071-159-30 Off White Linen
6-1/4" W., 9" ht., Extends 3-1/8".
One 9w LED module, 3000K, 90CRI, 624 source lumens.



P710071-030-30



P710071-159-30

UTILITY

PROGRESSLIGHTING.COM

LED STRIP

FINISH

○ White - 030

LED STRIP

P7265-3030K9 White
1-3/4" W., 1-7/8 ht.
19w integrated LED, 3000K,
90CRI, 1500 delivered lumens.



P7265-3030K9

LED STRIP

P7267-3030K9 White
1-3/4" W., 1-7/8 ht.
37w integrated LED, 3000K,
90CRI, 2900 delivered lumens.



P7267-3030K9

LINEAR CLOUD

*Dimmable to 10% with Triac
and ELV dimmers*

FINISHES


● Brushed Nickel - 09
● Urban Bronze - 174
○ White - 030

FLUSH MOUNT LINEAR LED

P7258-0930K9 Brushed Nickel
P7258-17430K9 Urban Bronze
48-1/2" L., 11-13/16" W., 4-1/2" ht.
53w integrated LED, 3000K,
90CRI, 3559 delivered lumens.



P7258-0930K9



P7258-17430K9

LED LINEAR CLOUD

P7278-3030K9 White
26" L., 10-1/4" W., 3-1/4" ht.
27w integrated LED, 3000K,
90CRI, 1974 delivered lumens.



P7278-3030K9

LED LINEAR CLOUD

P7279-3030K9 White
51" L., 11-3/4" W., 4-3/4" ht.
40w integrated LED, 3000K,
90CRI, 2908 delivered lumens.



P7279-3030K9

PROGRESSLIGHTING.COM

Shown: Track Lighting

LED TRACK

Ideal for residential and light commercial applications, this LED Track Kit is provided with all components required for installation. Track Kits include 42" of linear track, a floating power feed, three AC LED Track Heads and installation hardware. Track Heads feature a frosted glass lens to reduce glare and are compatible with P9054 and P9058 track and accessories.

TRACK KITS




FINISHES
○ Satin White - 028
● Black - 031

P900002-028-27 Satin White
P900002-031-27 Black
42" L., 2-7/8" W., 6-1/2" ht.,
Extends 2-3/4".
Three 9.5W LED,
2700K, 1575 delivered lumens.

P900003-028-27 Satin White
P900003-031-27 Black
42" L., 3-1/4" W., 7-1/2" ht.,
Extends 3-1/4".
Three 14.5W LED,
2700K, 2350 delivered lumens.

AC LED TRACK HEADS

P900000 and P900001 Track Heads are compatible with P900002 and P900003 Track Kits. These AC LED Track Heads can be added to a track kit to provide more light when needed.



P900000-028-27 Satin White
P900000-031-27 Black
2-7/8" W., 6-1/2" ht.,
Extends 2-3/4".
One 9.5W LED,
2700K, 533 delivered lumens.

P900001-028-27 Satin White
P900001-031-27 Black
3-1/4" W., 7-1/2" ht.,
Extends 3-1/4".
One 14.5W LED,
2700K, 797 delivered lumens.

SURFACE MOUNT LED

White acrylic diffuser for kitchen, bath, laundry, workshop or family area. 90 CRI, 3000K.

FINISHES
● Brushed Nickel - 09
● Urban Bronze - 174

LED SURFACE MOUNT
P7249-0930K9 Brushed Nickel
P7249-17430K9 Urban Bronze
10-3/8" W., 3-1/2 ht.
21.7w integrated LED, 3000K,
90CRI, 1027 delivered lumens.

LED SURFACE MOUNT
P7250-0930K9 Brushed Nickel
P7250-17430K9 Urban Bronze
17-3/4" W., 4-3/4" ht.
30w integrated LED, 3000K,
90CRI, 1765 delivered lumens.

LED SURFACE MOUNT
P7251-0930K9 Brushed Nickel
P7251-17430K9 Urban Bronze
32-1/2" L., 18"W., 4-3/4" ht.
39w integrated LED, 3000K,
90CRI, 2649 delivered lumens,
120-277V.

LED SURFACE MOUNT
P7252-0930K9 Brushed Nickel
P7252-17430K9 Urban Bronze
31-3/4 dia., 5" ht.
52w integrated LED, 3000K,
90CRI, 3200 delivered lumens,
120-277V.

LED SURFACE MOUNT
P7253-0930K9 Brushed Nickel
P7253-17430K9 Urban Bronze
14 dia., 3-3/4" ht.
22w integrated LED, 3000K,
90CRI, 1184 delivered lumens.




WRAP-AROUNDS

Clear extruded prismatic acrylic diffuser, squared white end caps and white chassis. General utility fluorescents for individual or continuous run ceiling mounting.

FINISH
○ White - 30

WRAP-AROUNDS
P7186-30EB White
49" L., 7-3/4" W., 3" ht.
120v HPF, 2-F32FT8 lamps

WRAP-AROUNDS
P7196-30EB White
48" L., 14-5/8" W., 3" ht.
120v HPF, 4-F32FT8 lamp



P7186-30EB



P7196-30EB

CLOUD LED + DRUM

FINISHES
○ White - 030
● Black - 031

LED DRUM
P730005-030-30 White
P730005-031-30 Black
11" W., 4" ht.
21w integrated LED, 3000K, 90CRI, 1680 lumens.

LED DRUM
P730002-030-30 White
13-5/8" W., 4" ht.
22.5w integrated LED, 3000K, 90CRI, 2025 lumens.

LED DRUM
P730003-030-30 White
17" W., 4" ht.
28w integrated LED, 3000K, 90CRI, 2520 lumens.

*Dimmable to 10% with
Triac and ELV dimmers*

LED CLOUD
P730008-030-30 White
11" W., 4" ht.
21w integrated LED, 3000K, 90CRI, 1575 lumens.

LED CLOUD
P730006-030-30 White
13-5/8" W., 4" ht.
22.5w integrated LED, 3000K, 90CRI, 1845 lumens.

LED CLOUD
P730007-030-30 White
17" W., 4" ht.
28w integrated LED, 3000K, 90CRI, 2548 lumens.



P730005-031-30



P730005-030-30



P730002-030-30



P730003-030-30



P730008-030-30



P730006-030-30



P730007-030-30

LED LAMPS



LED LAMP
F4T10DLED927/JA8
5-5/16" ht.
4w T10 LED medium base
filament lamp
2700K, 300 lumens,
15,000 hours, dimmable.



LED LAMP
F8.5A19D927/JA8
8.5W A19 LED medium base
filament lamp. 2700K, 800 lumens,
15,000 hours

PHOTO CONTROL

Remote mount photo control installs into standard, rain-tight junction box and includes faceplate and gasket. Max load 2000 watts. Operating range -40 + 140F. Consumes less than 1 watt.

PTORK3010
3" W., 5" ht.



PTORK3010

PRODUCT INDEX

P200000

P250002-009-30	38
P250002-108-30	38
P250002-143-30	38
P2502-20	39
P2502-30	39
P2502-80	39
P2502-141	39
P2503-09	39
P2503-20	39
P2503-30W	39
P2521-09	39
P2521-09CH	39
P2521-09WA	39
P2521-20	39
P2521-77	39
P2521-80	39
P2521-81	39
P2526-20	39
P2530-09	39
P2530-20	39
P2530-30W	39
P2531-09	39
P2531-20	39
P2533-20	39
P2539-0930K	38
P2539-2030K	38
P2539-3030K	38
P2540-2030K	38
P2540-3030K	38
P2540-14330K	38
P2542-0930K	38
P2542-2030K	38
P2542-3030K	38
P2544-1530K	38
P2544-0930K	38
P2544-2030K	38
P2548-0930K	38
P2548-2030K	38
P2548-3030K	38
P2550-0930K	38
P2550-2030K	38
P2550-3030K	38
P2550-3130K	38
P2554-2030K	38
P2554-1530K	38
P2554-0930K	38
P2554-3130K	38
P2556-0930K	38
P2556-3030K	38
P2556-2030K	38
P2558-0930K	38
P2558-2030K	38
P2564-2030K	39
P2564-3030K	39

P2564-8030K	39
P2568-0930K	38
P2568-1530K	38
P2568-2030K	38
P2572-2030K	38
P2572-3030K	38
P2572-0930K	38
P2574-2030K	39
P2574-8030K	39
P2574-8130K	39
P2576-2030K	39
P2576-8030K	39
P2578-1530K	38
P2578-2030K	38
P2582-14330K	38
P2582-2030K	38
P2582-0930K	38
P2586-7130K	38
P2586-8030K	38
P2588-0930K	38
P2588-12930K	38
P2588-1530K	38
P2592-0930K	38
P2592-12930K	38
P2592-3130K	38
P2596-8030K	39
P2596-8130K	39
P2596-12930K	39
P2600-09WB	45
P2600-30WB	45
P2601-20WB	40
P2601-30WB	40
P2601-80WB	40
P2601-141WB	40
P2602-09WB	44
P2602-15WB	44
P2602-20WB	44
P2602-30WB	44
P2602-143VB	44
P2610-09WB	45
P2610-15WB	45
P2610-20WB	45
P2610-30WB	45
P2610-143WB	45
P2611-20WB	44
P2611-30WB	44
P2611-80WB	44
P2612-20TWB	42
P2612-01WB	42
P2628-01WB	43
P2636-20WB	40
P2642-09WB	42
P2642-30WB	42
P2643-09WB	42

P2643-20WB	42
P2643-30WB	42
P2643-20TWB	42
P2644-09WB	40
P2644-30WB	40
P2645-01WB	41
P2645-77WB	41
P2649-01WB	44
P2650-01WB	45
P2650-20TWB	45
P2654-01WB	41
P2659-09	43
P2659-20	43
P2659-30	43
P2660-01	43

P300000

P300054-015-30	51
P300055-015-30	51
P300063-009-30	50
P300064-009-30	50
P300065-009-30	50
P300091-020-30	62
P300091-143-30	62
P300092-020-30	62
P300092-143-30	62
P300093-009-30	54
P300094-009-30	54
P300150-150-30	47
P300151-150-30	47
P300152-009-30	55
P300153-009-30	55
P300182-009-30	49
P300182-015-30	49
P300182-129-30	49
P300183-009-30	57
P300183-015-30	57
P300183-129-30	57
P300184-009-30	57
P300184-015-30	57
P300184-129-30	57
P300185-009-30	52
P300185-015-30	52
P300186-009-30	52
P300186-015-30	52
P300187-009-30	53
P300187-015-30	53
P300188-009-30	53
P300188-015-30	53
P300205-009-30	59
P300206-009-30	59
P300207-009-30	59
P300208-009-30	60
P300209-009-30	60
P300210-009-30	60

P300211-009-30	61
P300212-009-30	61
P300213-009-30	61
P300223-009-30	58
P300224-009-30	58
P300225-009-30	58
P350002-009-30	29
P350002-020-30	29
P350003-009-30	29
P350003-020-30	29
P350005-009-30	33
P350006-009-30	33
P350007-009-30	33
P350008-009-30	33
P350019-009-30	34
P350019-020-30	34
P350020-009-30	34
P350020-020-30	34
P350023-009-30	34
P350023-020-30	34
P350024-009-30	34
P350024-020-30	34
P350051-009-30	30
P350051-020-30	30
P350052-009-30	30
P350052-020-30	30
P350053-009-30	30
P350053-020-300	30
P350054-009-30	30
P350054-020-30	30
P350064-009-30	91
P350064-129-30	93
P350065-009-30	91
P350065-129-30	93
P350066-009-30	91
P350066-129-30	93
P350070-009-30	91
P350070-129-30	93
P350071-009-30	91
P350071-129-30	93
P350072-009-30	91
P350072-129-30	93
P350076-009-30	36
P350076-020-30	36
P350076-030-30	36
P350077-009-30	36
P350077-020-30	36
P350077-030-30	36
P350078-009-30	36
P350078-020-30	36
P350078-030-30	36
P350081-009-30	35
P350081-020-30	35
P350082-009-30	35
P350082-020-30	35
P350085-009-30	27

P350085-015-30	27
P350085-020-30	27
P350086-009-30	27
P350086-015-30	27
P350086-020-30	27
P350087-009-30	27
P350087-015-30	27
P350087-020-30	27
P350088-009-30	98
P350088-015-30	98
P350088-020-30	98
P350089-078-30	32
P350089-121-30	32
P350089-143-30	32
P350100-009-30	31
P350100-015-30	31
P350100-020-30	31
P350101-009-30	31
P350101-015-30	31
P350101-020-30	31
P350105-109-30	29
P350105-015-30	29
P350113-009-30	32
P350113-015-30	32
P350113-108-30	32
P350131-009-30	31
P350131-015-30	31
P350131-020-30	31
P350134-009-30	28
P350134-143-30	28
P350135-009-30	28
P350135-143-30	28
P3647-3030K9	77
P3647-3130K9	77
P3648-3030K9	77
P3648-3130K9	77
P3649-3030K9	77
P3649-3130K9	77
P3650-3030K9	77
P3650-3130K9	77
P3665-3130K9	78
P3673-3130K9	78
P3683-0930K9	28
P3683-2030K9	28
P3696-0930K9	28
P3696-2030K9	28

P500000

P500000-009-30	97
P500002-009-30	96
P500065-009-30	97
P500065-020-30	97
P500066-009-30	97
P500066-020-30	97
P500147-009-30	95

PRODUCT INDEX

P500147-015-30	95
P500147-109-30	95
P5024-0930K9	72
P540026-020-30	64
P540037-030-30	65
P540037-031-30	65
P5445-2030K9	75
P5445-3130K9	75
P550026-020-30	64
P550037-030-30	65
P550037-031-30	65
P560001-129-30	79
P560029-031-30	81
P560029-129-30	81
P560030-031-30	81
P560030-129-30	81
P560034-031-30	76
P560051-020-30	82
P560051-030-30	82
P560051-031-30	82
P560051-082-30	82
P560052-020-30	71
P560052-103-30	71
P560053-020-30	71
P560053-103-30	71
P560056-020-30	82
P560056-030-30	82
P560056-031-30	82
P560056-082-30	82
P560068-020-30	64
P560069-020-30	64
P560070-020-30	64
P560071-031-30	76
P560072-031-30	83
P560073-031-30	83
P560090-020-30K	80
P560090-030-30K	80
P560090-031-30K	80
P560090-082-30K	80
P560093-031-30	83
P560104-030-30	65
P560104-031-30	65
P560105-030-30	65
P560105-031-30	65
P560106-129-30	66
P560107-129-30	66
P560108-031-30	66
P560109-031-30	66
P560136-031-30	78
P563000-020-30K	84
P563000-030-30K	84
P563000-143-30K	84
P563000-147-30K	84
P563001-020-30K	84
P563001-030-30K	84
P563001-143-30K	84

P563001-147-30K	84
P5622-2030K9	73
P5622-8230K9	73
P5623-2030K9	73
P5623-8230K9	73
P5634-2030K9	80
P5634-3130K9	80
P5634-8230K9	80
P5635-2030K9	80
P5635-3130K9	80
P5635-8230K9	80
P5641-20/30K9	86
P5641-30/30K9	86
P5641-31/30K9	86
P5641-82/30K9	86
P5642-20/30K9	86
P5642-30/30K9	86
P5642-82/30K9	86
P5643-20/30K9	88
P5643-30/30K9	88
P5643-31/30K9	88
P5643-82/30K9	88
P5644-20/30K9	88
P5644-30/30K9	88
P5644-31/30K9	88
P5644-82/30K9	88
P5644-82/30K9	85
P5674-20/30K9	85
P5674-30/30K9	85
P5674-31/30K9	85
P5674-82/30K9	85
P5675-20/30K9	85
P5675-30/30K9	85
P5675-31/30K9	85
P5675-82/30K9	85
P5676-2030K9	76
P5676-13630K9	76
P5723-1430K9	72
P5723-7130K9	72
P5723-8130K9	72
P5741-20/30K9	86
P5741-30/30K9	86
P5741-31/30K9	86
P5741-82/30K9	86
P5749-2030K9	69
P5750-2030K9	69
P5751-2030K9	69
P5774-20/30K9	85
P5774-30/30K9	85
P5774-31/30K9	85
P5774-82/30K9	85
P5800-12930K9	79
P5801-12930K9	79
P5806-12930K9	79
P5862-2030K9	75
P5862-3130K9	75

P5863-2030K9	75
P5863-3130K9	75
P5864-2030K9	75
P5864-3130K9	75

P600000

P6056-3130K9	68
P6057-3130K9	68
P6058-3130K9	68
P6067-3130K9	67
P6068-3130K9	67
P6069-3130K9	67
P6076-3130K9	67
P6077-2030K9	74
P6077-3130K9	74
P6078-2030K9	74
P6078-3130K9	74
P6079-2030K9	74
P6079-3130K9	74
P6084-2030K9	70
P6084-3130K9	70
P6085-2030K9	70
P6085-3130K9	70
P6424-2030K9	70
P6424-3130K9	70
P6426-3130K9	68
P6427-3130K9	67
P6430-2030K9	74
P6430-3130K9	74
P6527-3130K9	67

P700000

P700000-020-30	21
P700000-028-30	21
P700001-020-30	21
P700001-028-30	21
P700002-020-30	21
P700002-028-30	21
P700003-020-30	21
P700003-028-30	21
P700004-020-30	21
P700004-028-30	21
P700005-020-30	21
P700005-028-30	21
P700008-000-27	24
P700008-000-30	24
P700009-000-27	24
P700009-000-30	24
P700010-000-27	24
P700010-000-30	24
P700011-000	24
P700012-000	24
P700013-000	24
P700014-000	24



Featuring Vast Ceiling Fan

 **PROGRESS**
LIGHTING™

701 Millennium Boulevard
Greenville, SC 29607
progresslighting.com

