



CEILING FAN CATALOG 2020





See Yourself Here.

Lighting helps tell a story, whether it's setting the mood or enjoying a special moment. These occasions are meaningful, expressive, and shared with those we care about most. Let Progress be your guide in illuminating these spaces into special places.

Table of Contents

Fan Inspiration	10
-----------------	----

Our ceiling fans do more than cool a room - they combine beautiful design with premium performance. Choose from fans that make a statement across a variety of design trends, from simple to spectacular.

Indoor Fans	18
-------------	----



Outdoor Fans	130
--------------	-----



Accessories	158
-------------	-----

Light Kits	162
------------	-----

Downrods	168
----------	-----

Remotes	169
---------	-----

Cross Reference Chart	170
-----------------------	-----

Blade Finishes	174
----------------	-----

Index	176
-------	-----

Be Inspired

 @ProgressLtg

 @ProgressLtg

 @ProgressLighting

 @ProgressLtg

 Progress Lighting

 Progress-Lighting

#ProgressLightingMoments

Indoor Ceiling Fans

ARLO
Architectural Bronze p.51



ARLO
Black p.51



ARLO
Brushed Nickel p.50



BEDWIN
Antique Nickel p.76



BEDWIN
Galvanized p.77



BEDWIN
Graphite p.77



BILLOWS
Antique Bronze p.101



BILLOWS
Brushed Nickel p.100



BILLOWS
Forged Black p.101



BIXBY
Black p.52



BIXBY
White p.53



BRADEN
Architectural Bronze p.125



BRADEN
Brushed Nickel p.125



BRADEN
Polished Chrome p.124



CALEB
Antique Bronze p.42



CALEB
Brushed Nickel p.43



CHAPIN
Antique Nickel p.75



CHAPIN
Graphite p.75



CHAPIN
Oil Rubbed Bronze p.74



CLIFTON HEIGHTS
Antique Bronze p.115



CLIFTON HEIGHTS
Brushed Nickel p.114



DRIFT
Architectural Bronze p.121



DRIFT
Brushed Nickel p.120



DRIFT
White p.121



EDGEFIELD
Antique Bronze p.112



Indoor Ceiling Fans

EDGEFIELD
Brushed Nickel p.112



EDGEFIELD
White p.113



ELLWOOD
Antique Bronze p.41



ELLWOOD
Brushed Nickel p.40



FARRIS
Brushed Nickel p.29



FARRIS
Graphite p.29



FARRIS
Oil Rubbed Bronze p.28



FRESNO
Antique Bronze p.94



FRESNO
Brushed Nickel p.95



FRESNO
White p.95



GAZE
Antique Bronze p.55



GAZE
Black p.55



GAZE
Brushed Nickel p.55



GAZE
Polished Chrome p.54



GLANDON
Antique Nickel p.68



GLANDON
Gilded Iron p.69



GRACEFUL
Antique Bronze p.85



GRACEFUL
Brushed Nickel p.84



GRACEFUL
Polished Chrome p.85



GREER
Antique Nickel p.72



GREER
Gilded Iron p.73



GULLIVER
Galvanized p.32



GULLIVER
Graphite p.33



GUST
Antique Bronze p.89



GUST
Brushed Nickel p.88



Indoor Ceiling Fans

GUST
Graphite p.89



HARRANVALE
Antique Bronze p.83



HARRANVALE
Graphite p.82



HARRANVALE
White p.83



HOLLAND
Black p.61



HOLLAND
Brushed Nickel p.60



HOLLAND
Oil Rubbed Bronze p.61



HUFF
Black p.45



HUFF
Brushed Nickel p.44



HUFF
Satin White p.45



KUDOS
Antique Bronze p.93



KUDOS
Brushed Nickel p.92



KUDOS
Polished Chrome p.93



LINDALE
Antique Nickel p.123



LINDALE
Architectural Bronze p.122



LINDALE
Satin White p.123



LORING
Galvanized p.35



LORING
Matte Black p.34



OLSON
Brushed Nickel p.87



OLSON
Graphite p.86



ORIOLE
Architectural Bronze p.62



ORIOLE
Black p.63



ORIOLE
Brushed Nickel p.63



ROYER
Antique Nickel p.67



ROYER
Forged Black p.66



Indoor Ceiling Fans

SANFORD
Architectural Bronze p.36



SANFORD
Brushed Nickel p.37



SHAFFER
Architectural Bronze p.79



SHAFFER
Forged Black p.78



SHAFFER
Satin White p.79



SIGNATURE
Antique Bronze p.105



SIGNATURE
Antique Nickel p.105



SIGNATURE
Brushed Nickel p.104



SIGNATURE
Forged Black p.105



SIGNATURE
Forged Bronze p.105



SIGNATURE PLUS
Antique Bronze p.111



SIGNATURE PLUS
Brushed Nickel p.111



SIGNATURE PLUS
White p.111



SIGNATURE PLUS II
Antique Bronze p.110



SIGNATURE PLUS II
Brushed Nickel p.110



SIGNATURE PLUS II
White p.110



SOAR
Antique Bronze p.80



SOAR
Brushed Nickel p.81



SOAR
White p.81



SPRINGER
Antique Nickel p.26



SPRINGER
Architectural Bronze p.27



SPADES
Brushed Nickel p.57



SPADES
Graphite p.57



SPADES
Polished Chrome p.56



TEASLEY
Architectural Bronze p.65



Indoor Ceiling Fans

TEASLEY
Galvanized p.65



TEASLEY
Graphite p.64



TEMPT
Antique Bronze p.97



TEMPT
Polished Chrome p.97



TEMPT
Vintage Brass p.96



TREVINA II 44"
Black p.106



TREVINA II 44"
Brushed Nickel p.106



TREVINA II 44"
Satin White p.106



TREVINA II 52"
Antique Bronze p.107



TREVINA II 52"
Architectural Bronze p.107



TREVINA II 52"
Brushed Nickel p.107



TREVINA II 52"
Painted Nickel p.107



TREVINA II 52"
White p.107



VAST
Antique Bronze p.47



VAST
Brushed Nickel p.47



VAST
Matte Black p.46



VAST
White p.47



VERADA
Antique Bronze p.99



VERADA
Brushed Nickel p.98



VOX FAN
Antique Bronze p.127



VOX FAN
Brushed Nickel p.126



VOX FAN
White p.127



42" BUILDER FAN
Antique Bronze p.117



42" BUILDER FAN
Brushed Nickel p.117



42" BUILDER FAN
White p.117



Indoor Ceiling Fans

52" BUILDER FAN
Brushed Nickel p.119



52" BUILDER FAN
Polished Chrome p.119



52" BUILDER FAN
Antique Bronze p.119



52" BUILDER FAN
Graphite p.119



52" BUILDER FAN
White p.119



52" BUILDER FAN WITH LIGHT KIT
Architectural Bronze p.118



52" BUILDER FAN WITH LIGHT KIT
Brushed Nickel p.118



52" BUILDER FAN WITH LIGHT KIT
White p.118



42" HUGGER FAN
Brushed Nickel p.129



42" HUGGER FAN
White p.129



52" HUGGER FAN
Brushed Nickel p.128



52" HUGGER FAN
White p.128



52" PERFORMANCE
Antique Bronze p.116



52" PERFORMANCE
Brushed Nickel p.116



52" PERFORMANCE
White p.116



Outdoor Ceiling Fans

 Damp Location Listed

ALBIN
Architectural Bronze p.150



ALBIN
Black p.151



ALBIN
Satin White p.151



ALFRESCO
Architectural Bronze p.134



ALFRESCO
Blistered Iron p.135



ARLO
Architectural Bronze p.51



ARLO
Black p.51



ARLO
Brushed Nickel p.50



BIXBY
Black p.52



BIXBY
White p.53



DECORATIVE PATIO FAN
Antique Bronze p.154



EDISTO
Antique Nickel p.139



EDISTO
Architectural Bronze p.139



EDISTO
Forged Black p.138



GULLIVER
Galvanized p.32



GULLIVER
Graphite p.33



HOLLAND
Brushed Nickel p.60



HOLLAND
Oil Rubbed Bronze p.61



HUFF
Black p.45



HUFF
Brushed Nickel p.44



HUFF
Satin White p.45



SANFORD
Architectural Bronze p.36



SANFORD
Brushed Nickel p.37



RUDDER
Architectural Bronze p.137



RUDDER
Matte Black p.137



Outdoor Ceiling Fans

 Damp Location Listed

RUDDER
Matte White p.136



VAST
Matte Black p.46



VAST
White p.47



WHIRL
Antique Bronze p.143



WHIRL
Antique Nickel p.142



WHIRL
Forged Black p.143



 Wet Location Listed

LAKEHURST
Antique Bronze p.152



LAKEHURST
Forged Black p.153



LAKEHURST
White p.153



MONTAGUE
Antique Bronze p.149



MONTAGUE
Forged Black p.148



MONTAGUE
White p.149



SMYRNA
Antique Bronze p.146



SMYRNA
Forged Black p.147



52" PATIO FAN
Antique Bronze p.156



52" PATIO FAN
Forged Black p.156



52" PATIO FAN
Galvanized p.156



52" PATIO FAN
White p.156



54" PATIO FAN
Antique Bronze p.156





Fan Inspiration

Ceiling Fans can serve as a statement piece or even the focal point of a room.

Today's ceiling fans incorporate beautiful features, such as hand carved blades, sleek finishes and natural elements to appeal to a variety of different design trends.

At Progress Lighting, we strive to incorporate this shift in our ceiling fan designs and are eager to present an expanded offering in this catalog.

The Perfect Fan in 5 Steps



Scan with the camera on your smartphone to take the style quiz at www.progresslighting.com/styles

Ceiling Fan Buyer's Guide

Ceiling fans are practical and efficient solutions for creating comfortable and welcoming living areas. With many styles, functions and features to choose from, narrowing down the choices can be a challenge. Here we present five tips for selecting the perfect ceiling fan for your home.

1 Settle on Style

Choose a style that complements your décor. Consider fan shape, blade features and finish to help you meet your room's design needs. Choose from Traditional, Transitional, Coastal or Farmhouse styles. The possibilities are vast!



Modern + Edgy
See full trendboard page 24



Modernly Minimal
See full trendboard page 160



Easy, Breezy, Coastal
See full trendboard page 132

Indoor



Featuring Glandon

Outdoor




Featuring Edisto

2 Explore Indoor vs. Outdoor Uses

Fans provide a breezy setting for reading a book or catching up with friends, making them ideal for outdoor rooms. However, it's important to consider the certifications on the fan depending on the use. For high humidity areas, choose a UL-Listed fan for Damp Locations and for spaces that will be exposed to weather, choose a UL-Listed fan for Wet Locations. For interior use in dry spaces with minimal condensation, select a UL-Listed fan for Dry Locations. See testing listings defined on page 17.

The Perfect Fan in 5 Steps *continued...*



3 Get Your Height Right

You want to allow at least 7 feet (84 in.) from the floor to the bottom of the fan, with 8 or 9 feet being the ideal above-floor placement. For lower ceilings, consider a ceiling fan with a low profile to avoid disturbing inhabitants. Most ceiling fans come equipped with a down rod to help you adjust to the correct height.

4 Size It To Your Space

Size is really important when selecting your ceiling fan. If a fan is too large, it can overwhelm the space. On the flip side, if the fan is too small, the airflow may be inadequate for that area.

Room Size

Fan Size

(in square feet)

(in inches)

0 - 75

0 - 36

76 - 144

36 - 42

145 - 225

42 - 50

226 - 360

50 - 54

361 - 499

54 - 70

500+

70+

The Perfect Fan in 5 Steps *continued...*

5 Choose Your Features

There are many different features to choose from when browsing ceiling fans.

Blade Finish Options

Multiple blade finish options to coordinate with your home decor.

Example blade options for P2568-1530:

- Medium Cherry
- Black

Reversible Motor

Typically, ceiling fans are used to help cool you down and keep the air flowing with a counter-clockwise blade direction. However, fans can also keep you warm when the direction of the blades is reversed. Select a fan with reversible motor for the option to circulate cool or warm air. Most ceiling fans have a small switch located either on the motor housing or the switch cup.

LED

Consider an LED or Energy Star rated fixture to save energy.

Remote Control with Full Range Dimming

Full range dimming and hand-held remote control capabilities are available to offer an added convenience in controlling a room's environment.

Light Kit

For a layered lighting effect, install a ceiling fan with a pre-installed light kit to complement your existing fixtures.

P2568-1530



Scan for "The Perfect Fan in 5 Steps" with Steve Register or visit [youtube.com/user/ProgressLtg](https://www.youtube.com/user/ProgressLtg)

Control from Anywhere

Easily control your fan with your smartphone, tablet, voice or hand-held remote.



Wi-Fi enabled



P2667-031

Compatible with Any Progress AC Motor

Full Range Dimming Control

Breeze Mode on App

On/Off Function for Fan and Light Kit

Control from your pocket




Featuring Gaze

For more details, visit www.progresslighting.com/ceilingfans

LED Light Kits

Save Money and Energy

When you select a high-quality LED fixture, you can expect a significant return on investment from an energy conservation standpoint. Here are some of the energy saving benefits of LEDs from Progress Lighting:



Whirl
P2574-8130K
shown with Driftwood blades

Features



LED sources use at least 75% less energy than incandescent lighting, allowing homeowners to save on operating expenses.



LEDs last 35 to 50 times longer than incandescent sources and approximately 2 to 5 times longer than fluorescent lighting. Meaning, less bulb maintenance!



LEDs do not use power when they are turned off. According to MSN Real Estate, LED lights can result in an annual bill as low as \$26.



LEDs do not produce heat like traditional sources, reducing cooling costs. Traditional incandescent bulbs waste 98% of the energy they consume on heat.

Find Your Rating

Indoor, Damp and Wet Location

All ceiling fans sold in the United States have been tested and rated by either Underwriters Laboratories (UL) or Intertek (ETL), each an independent product safety certification organization. It's important to pay attention to the rated listing when purchasing a ceiling fan as it will tell you what location the fan was designed for. There are three location options: dry, damp and wet.



Dry Location

Please note indoor only (dry location) fans should only be used indoors. Even if an outdoor area or screened-in porch is covered, the motor and the blades can be affected when exposed to humidity. You can, however, “bring the outdoors inside” – as using outdoor ceiling fans are perfectly acceptable to use in interior spaces.

Damp Location

If you are selecting a ceiling fan for a space that is outdoors and under a roof, i.e. any covered porches; you should select either a damp rated or wet listed fan. Damp location fans may also be used indoors.



Wet Location

If the fan comes directly into contact with water, you'll need to ensure that the ceiling fan has a “wet” listing. Ceiling fans designed for damp or wet locations feature elements, such as moisture-resistant motors and all weather blades. Wet location fans may also be used indoors.





Indoor Ceiling Fans

Experience the versatility
ceiling fans provide



Scan with your camera on
your smartphone or visit
www.progresslighting.com/ceilingfans

Vast
P2550-0930K

Retro 1

2 Unique Shapes

3 Glass Accents



Steve Register
Product Manager,
Ceiling Fans

Modern + Edgy

with Steve

Quirky and functional, this style's flair comes from its modern, yet retro, juxtaposition. Mid-Century Modern style furniture adds unique shapes and pops of color to a room. Designers look for statement pieces to complete the look. This style is gravitating toward a cleaner, more minimalistic look through the incorporation of a neutral palette and softer accent colors. Mid-Century

Modern homes are largely characterized by the use of wood textures to create a sense of connection to nature and the outdoors.



Shop this style at
www.progresslighting.com/mid-century-modern




Springer

FINISHES

- Antique Nickel - 081
- Architectural Bronze - 129

P250000-081
shown with White Barnwood blades

Springer is a statement-making ceiling fan with a rustic flair. The 12-blade, 60" ceiling fan was inspired by the form and function of a windmill and is ideal for Farmhouse, Industrial and Transitional interior settings. A full function remote control with batteries is included along with a dual mount canopy that accommodates flat or sloped ceilings.



Springer

P250000-081 Antique Nickel



White Barnwood

P250000-129 Architectural Bronze



Distressed Walnut



P250000-081
shown with White Barnwood blades



P250000-129
shown with Distressed Walnut blades



Scan with the camera on your smartphone for the Springer installation video.

ENERGY INFORMATION AT HIGH SPEED

Airflow	6,377 cubic feet per minute
Electricity Use	33 watts (excludes lights)
DOE Weighted CFM/W	206 CFM/W

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-22°)
- DC Motor
- Plywood blades
- Will not accept light kit
- Full function remote control with batteries is included

SIZE

60" dia., 17-3/8" ht.
80" lead wires.



Full Function Remote Control Included
Six-speed fan operation
Reverse direction control

Farris

FINISHES

- Brushed Nickel - 009
- Oil Rubbed Bronze - 108
- Graphite - 143

P250002-108-30
shown with Walnut blades

Farris features three solid wood carved blades to form a sleek, modern design. The 60" ceiling fan includes an integrated LED light kit that is removable to provide the option in non-illuminated applications. Available in Brushed Nickel, Oil Rubbed Bronze and Graphite finishes. A full function remote control with batteries is included, and the dual mount canopy accommodates flat or sloped ceilings.



Wood Carved Blades

Modern Design

Removable, Dimmable LED Light

Farris



P250002-009-30
shown with Gray Weathered Wood blades

P250002-009-30 Brushed Nickel



Gray Weathered Wood

P250002-108-30 Oil Rubbed Bronze



Walnut

P250002-143-30 Graphite



Driftwood



P250002-108-30
shown with Walnut blades
and light kit removed



P250002-143-30
shown with Driftwood blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	7,047 cubic feet per minute
Electricity Use	32 watts (excludes lights)
DOE Weighted CFM/W	223 CFM/W

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-13°)
- DC Motor
- Carved wood blades
- Removable light kit. Blank plate included.
- White opal shatterproof shade
- Full function remote control with batteries is included

SIZE

60" dia., 15-1/2" ht.
80" lead wires.

LAMP

18w LED Module, 3000K, 90 CRI,
1400 lumens, dimmable.



Full Function Remote Control Included
Six-speed fan operation
Full-range dimming for light
Reverse direction control





1

2



Modern Farmhouse design embraces tradition but is firmly planted in the present.

1

Look for details like the beautifully carved, solid wood fan blades of the Farris ceiling fan that centers the room with statement-making style.

2

Modernize a traditional approach by contrasting a light and airy palette with a natural stone fireplace, weathered wood mantel and exposed beams.

3

Use organic materials for decorative accessories like greenery, wood and cozy textiles to add a welcoming touch.

Gulliver

FINISHES

- Galvanized - 141
- Graphite - 143

P250012-141-22
shown with Antique White Wood

Three circular bands wrap together to create an open design. Non-metallic fan blades enclosed within a stylish cage design gives the rustic charm of a pendant combined with the functionality of a ceiling fan. Dual toned frame color combinations of Galvanized with antique white accents or Graphite with weathered gray accents. A hand painted wood grained texture complements rustic and modern farmhouse home decor, as well as urban industrial and coastal interior settings.

Urban Industrial Design



Rustic Charm

Hand-Painted Wood

Gulliver

P250012-141-22 Galvanized



Antique White Wood

P250012-143-22 Graphite



Gray Wood



P250012-141-22
shown with Antique White Wood



P250012-143-22
shown with Gray Wood

ENERGY INFORMATION AT HIGH SPEED

Airflow	1,297 cubic feet per minute
Electricity Use	39 watts (excludes lights)
Airflow Efficiency	33 cubic feet per minute per watt



Three-Speed Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-18.5")
- AC Motor
- Reversible Motor
- Rust-proof non-metallic blades
- Damp Location Rated
- Remote control with batteries is included

SIZE

23" dia., 18-1/8" ht.
42" lead wires.

LAMP

Three LED medium base vintage lamps, 2200K, 80 CRI, 5.5w max each, included, dimmable.



Loring

FINISHES

- Black- 031
- Galvanized - 141

P250006-031
shown with Matte Black blades

Outfitted with stylish mixed metal elements, the Loring collection shows off an industrial-inspired, open-cage design. Four plywood blades and a handy remote control are ready to help you and your family stay comfortable and relaxed all year round.

Open-Cage Design



Industrial Inspired

Mixed-Metal Elements

Loring

P250006-031 Black



Matte Black
Distressed Ebony

P250006-141 Galvanized



White Barnwood
Driftwood



P250006-031
shown with Gold accent
and Distressed Ebony blades



P250006-141
shown with Matte Black accent
and White Barnwood blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	1,766 cubic feet per minute
Electricity Use	43 watts (excludes lights)
DOE Weighted CFM/W	44 CFM/W



Three Speed Remote Control Included
Three-speed fan operation

FEATURES

- Limited lifetime warranty
- Close-to-ceiling installation
- AC Motor
- Reversible plywood blades
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

SIZE

33" dia., 15-1/4" ht.
12" lead wires.



Sanford

FINISHES

- Brushed Nickel - 009
- Architectural Bronze - 129

P2594-12930K

Sanford delivers ultra powerful air movement and energy efficient illumination packaged in a modern design. Ideal for both interior and outdoor settings, this "fandelier" adds a contemporary style to porches, foyers, bath and vanity areas providing a wide range of applications. Sanford includes an integrated 23W LED module, offering both form and function with energy and cost-savings benefits. A three-speed remote control is included.

Indoor or Outdoor Use

Contemporary Style



Powerful Air Movement

Sanford

P2594-0930K Brushed Nickel

P2594-12930K Architectural Bronze



P2594-0930K



P2594-12930K

ENERGY INFORMATION AT HIGH SPEED

Airflow	1,008 cubic feet per minute
Electricity Use	37 watts (excludes lights)
DOE Weighted CFM/W	27 CFM/W



Three-Speed Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-18.5°)
- AC Motor
- Metal blades
- Damp Location Rated
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

SIZE

22-7/8" dia., 17-3/4" ht.
80" lead wires.

LAMP

23w LED Module, 3000K,
90 CRI, dimmable.



An Industrial Edge

2



3





1

A simple but edgy
vibe takes its cue from
industrial origins.

1

Try a fandelier style ceiling fan like Sanford that delivers ultra-powerful air movement packaged in a vintage design.

2

Toss your table lamp and try two low-hanging pendants over the nightstand instead.

3

Finish the room with organic elements of wood and worn textures that celebrate the signature look of the industrial setting.

Ellwood

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20

P2546-09
shown with Driftwood blades

A picture of modern design, the functional minimalism of the Ellwood 68" ceiling fan is a product of advanced design. Five long and graceful blades made of carved wood move air with remarkable efficiency. Ellwood features a dual mount system and is compatible with universal light kits. A full function remote control is included.

Modern Design

Carved Wood Blades

Dual Mount System

Ellwood

P2546-09 Brushed Nickel



Driftwood

P2546-20 Antique Bronze



Walnut



P2546-09
shown with Driftwood blades



P2546-20
shown with Walnut blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	7,587 cubic feet per minute
Electricity Use	90 watts (excludes lights)
DOE Weighted CFM/W	92 CFM/W



Full Function Remote Control Included
Three-speed fan operation
Reverse direction control

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Patented carved Wood blades
- Compatible with universal light kits
- Remote control with batteries is included
- Remote control may be replaced with P2631-30 wall control

SIZE

68" dia., 16-3/4" ht.
80" lead wires.



Caleb

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20

P2560-20
shown with Walnut Blades

Beautiful and expansive in design, the 68" Caleb ceiling fan is ideal for use in large spaces. Bent carved wood blades are paired with either Brushed Nickel or Antique Bronze finishes. Caleb features a dual mount system and is compatible with universal light kits. A full function remote control is included.



Beautiful Design

Expansive Wood Blades

Dual Mount System

Caleb

P2560-09 Brushed Nickel



Medium Cherry

P2560-20 Antique Bronze



Walnut



P2560-09
shown with Medium Cherry blades



P2560-20
shown with Walnut blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	7,045 cubic feet per minute
Electricity Use	86 watts (excludes lights)
DOE Weighted CFM/W	91 CFM/W



Full Function Remote Control Included
Three-speed fan operation
Reverse direction control

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Patented bent carved wood blades
- Compatible with universal light kits
- Remote control with batteries is included
- Remote control may be replaced with P2631-30 wall control

SIZE

68" dia., 18" ht.
80" lead wires.




Huff

FINISHES

- Brushed Nickel - 009
- Satin White- 028
- Matte Black- 031

P250030-009
shown with Brushed Nickel blades

The hassles and headaches of the day fade away under the relaxing airflow created by the Huff Collection. Six expansive aluminum blades with decorative winglets stretch out from a dual mount center. Select a Brushed Nickel, Satin White, or Matte Black finish all with their own complementary highlights to create a perfect design for your modern or transitional space.



Complimentary Highlights

Modern Design

Expansive Aluminum Blades

Huff



P250030-009
shown with Brushed Nickel blades
and Matte Black accents

P250030-009 Brushed Nickel



P250030-028 Satin White



P250030-031 Matte Black



P250030-028
shown with Satin White blades
and Brushed Nickel accents



P250030-031
shown with Black blades
and Brushed Nickel accents

ENERGY INFORMATION AT HIGH SPEED

Airflow	14,482 cubic feet per minute
Electricity Use	49 watts (excludes lights)
DOE Weighted CFM/W	344 CFM/W



Full Function Remote Control Included
Six-speed fan operation
Reverse direction control

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- Aluminum blades
- Damp Location Rated
- Compatible with universal light kit
- Remote control with batteries is included

SIZE

96" dia., 15-1/2" ht.
80" lead wires.



Vast

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20
- White - 30
- Matte Black - 31

P2550-3130K
shown with Black blades

Beautiful and expansive in design, the 72" ceiling fan is ideal for use in large areas and outdoor covered areas for maximum cooling. A white opal shade complements a variety of finish options, including Brushed Nickel with chrome accents, Antique Bronze, White with chrome accents or Matte Black. Vast features a dual mount system and comes with a full function remote control.



Expansive Blades

Minimal Design

White Opal Shade

Vast



P2550-0930K
shown with Brushed Nickel blades
and Chrome accents

P2550-0930K Brushed Nickel



Brushed Nickel

P2550-2030K Antique Bronze



Antique Bronze

P2550-3030K White



White

P2550-3130K Matte Black



Black



P2550-2030K
shown with Antique Bronze blades



P2550-3030K
shown with White blades
and Chrome accents



P2550-3130K
shown with Black blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	8,100 cubic feet per minute
Electricity Use	37 watts (excludes lights)
DOE Weighted CFN/W	247 CFM/W



Full Function Remote Control Included
Six-speed fan operation
Full-range dimming for light
Reverse direction control

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- Aluminum blades
- Damp Location Rated
- White opal glass
- Remote control with batteries is included

SIZE

72" dia., 16-3/4" ht
80" lead wires.

LAMP

18w LED Module, 3000K, 90 CRI,
1400 lumens, dimmable.



1

Clean and Natural

2

3



Indoor-outdoor living begins with organic origins.

1

Select a large ceiling fan like Vast in covered outdoor areas to move air while making a design statement.

2

Bring the outdoors in with weathered wood furniture and organic decor.

3

Use a cool color palette and eye-catching architectural features like a double fireplace for a sophisticated, resort-like feel.

Arlo

FINISHES

- Brushed Nickel - 009
- Black - 031
- Architectural Bronze - 129

P250026-009-30
shown with Brushed Nickel blades

Unwind under the cooling breeze created by the clean, crisp blades of the Arlo collection's modern ceiling fan. A central LED light provides a perfect way to light a space without flooding the room with harsh light as six metal blades attach to the fan's center. Offered in three different finishes, Arlo is sure to create an intriguing, yet serene retreat in whatever space it calls home.

Modern Design

Clean Metal Blades

Dimmable LED Light

Arlo



P250026-009-30
shown with Brushed Nickel blades

P250026-009-30 Brushed Nickel



P250026-031-30 Black



P250026-129-30 Architectural Bronze



P250026-031-30
shown with Black blades



P250026-129-30
shown with Architectural Bronze blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	7,558 cubic feet per minute
Electricity Use	29 watts (excludes lights)
DOE Weighted CFM/W	282 CFM/W

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- Aluminium blades
- Damp Location Rated
- White Opal glass
- Remote control with batteries is included

SIZE

60" dia., 18-1/2" ht.
80" lead wires.

LAMP

24w LED Module, 3000K, 90 CRI,
2000 lumens, dimmable.



Full Function Remote Control Included
Six-speed fan operation
Full-range dimming for light
Reverse direction control



Bixby

FINISHES

- White - 030
- Black Chrome - 231

P250038-231-30
shown with Black Metallic blades

You'll find the time to unwind under the eye-pleasing, urban industrial design of the Bixby collection's ceiling fan. Breathe easy after a warm summer day or a long day at work as Bixby fosters a refreshing current of cool air with three, slightly curved Lucite blades circling a gentle LED light as it provides soothing illumination.

Industrial Style

*Slightly Curved
Lucite Blades*

Dimmable LED Light

Bixby

P250038-030-30 White



White Metallic

P250038-231-30 Black Chrome



Black Metallic



P250038-030-30
shown with White Metallic blades



P250038-231-30
shown with Black Metallic blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	6,846 cubic feet per minute
Electricity Use	32 watts (excludes lights)
DOE Weighted CFM/W	228 CFM/W



Full Function Remote Control Included
Six-speed fan operation
Full-range dimming for light
Reverse direction control

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- Polycarbonate blades
- Damp Location Rated
- White opal glass
- Remote control with batteries is included

SIZE

60" dia., 15-1/8" ht.
80" lead wires.

LAMP

24w LED Module,
3000K, 90 CRI,
2000 lumens, dimmable.



Gaze

FINISHES

- Brushed Nickel - 09
- Polished Chrome - 15
- Antique Bronze - 20
- Black - 31

P2554-1530K

shown with White Washed blades

Three-blade 60" Gaze ceiling fan features an LED light source, offering both form and function with energy and cost-savings benefits. An opal white shade contains an 18W dimmable, 3000K LED module. Gaze features a dual mount system and includes a three-speed remote control with full range dimming.

Dual Mount System

Dimmable LED Light


White Opal Shade

Gaze




P2554-0930K
shown with Silver blades

P2554-0930K Brushed Nickel




P2554-1530K
shown with Cherry blades

P2554-1530K Polished Chrome



P2554-2030K
shown with Walnut blades

P2554-2030K Antique Bronze



P2554-3130K
shown with Matte Black blades

P2554-3130K Black



ENERGY INFORMATION AT HIGH SPEED

Airflow	5,902 cubic feet per minute
Electricity Use	75 watts (excludes lights)
DOE Weighted CFM/W	87 CFM/W

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- Downrod installation only. Can not be flush mounted.
- AC Motor
- Manual reverse switch
- Reversible plywood blades
- White shatterproof lens
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

SIZE

60" dia., 13-1/8" ht.
80" lead wires.

LAMP

18w LED Module, 3000K, 90 CRI,
1400 lumens, dimmable.



Three-Speed Remote Control Included
Three-speed fan operation
Full-range dimming for light

Spades

FINISHES

- Brushed Nickel - 09
- Polished Chrome - 15
- Graphite - 143

P2570-15
shown with Black blades

The 56" Spades ceiling fan features a sleek contemporary two-blade design that is finished in Brushed Nickel, polished chrome or Graphite options. Spades features a dual mount system, an energy saving DC motor and ABS composite blades. A full function remote control is included.

Dual Mount System

Contemporary Design

Sleek Blades

Spades



P2570-09
shown with Silver blades

P2570-09 Brushed Nickel



Silver

P2570-15 Polished Chrome



Black

P2570-143 Graphite



Graphite



P2570-15
shown with Black blades



P2570-143
shown with Graphite blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	6,746 cubic feet per minute
Electricity Use	32 watts (excludes lights)
DOE Weighted CFM/W	215 CFM/W

FEATURES


- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-17°)
- Close-to-ceiling installation
- DC Motor
- Non-reversible ABS blades
- Will not accept a light kit
- Remote control with batteries is included

SIZE

56" dia., 18-1/8" ht.
(CTC 8-1/2" ht.),
80" lead wires.



CTC INSTALLATION



Full Function Remote Control Included
Six-speed fan operation
Reverse direction control

1

Inspirational Elements

2





Patterns and curves inspire the design of the room.

1

Select a sleek, contemporary fan like the two-blade Spades to harmonize with the contemporary feel of the living area.

2

Take one element, such as patterned window coverings, to inspire the rest of the room's palette.

3

Nothing jump starts design envy like architectural elements like an interesting ceiling.


Holland

FINISHES

- Brushed Nickel - 009
- Black- 031
- Oil Rubbed Bronze - 108

P250032-009-30
shown with Silver blades

Enjoy nothing but first-rate design inspiration with the gorgeous Holland collection. Four simple, yet stunning blades blend style with sustainability as they anchor to a sleek, dual mount center. An integrated LED light is ready to offer a gentle glow along with the fan's refreshing breeze. With the versatility to be installed in indoor or outdoor locations, this fan will make a design statement in any modern or transitional setting.



Dual Mount System

Indoor or Outdoor Use

Dimmable LED Light

Holland



P250032-009-30
shown with Silver blades

P250032-009-30 Brushed Nickel



Silver

P250032-031-30 Black



Black

P250032-108-30 Oil Rubbed Bronze



Walnut



P250032-031-30
shown with Black blades



P250032-108-30
shown with Walnut blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	7,035 cubic feet per minute
Electricity Use	31 watts (excludes lights)
DOE Weighted CFM/W	257 CFM/W

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- ABS blades
- White opal glass
- Damp Location Rated
- Remote control with batteries is included

SIZE

60" dia., 16-5/8" ht.
80" lead wires.

LAMP

24w LED Module, 3000K, 90 CRI,
2000 lumens, dimmable.



Full Function Remote Control Included
Six-speed fan operation
Full-range dimming for light
Reverse direction control



Oriole

FINISHES

- Brushed Nickel - 09
- Black - 31
- Architectural Bronze - 129

P2592-12930K
shown with Architectural Bronze blades

This 60" Oriole ceiling fan is the perfect addition to interior garages, industrial shops or commercial buildings to distribute the right amount of air and keep the space cool and comfortable. Oriole contains an integrated 18W LED module, with an optional finishing cap offering the user the choice to install with or without the light kit. A remote control is included to adjust speed and turn on/off the light or fan. A blank plate comes standard.

Sleek Blades

Industrial Design

Removable, Dimmable LED Light

Oriole



P2592-0930K
shown with Silver blades

P2592-0930K Brushed Nickel



Silver

P2592-3130K Black



Black

P2592-12930K Architectural Bronze



Architectural Bronze



P2592-3130K
shown with Black blades
and light kit removed
using blank plate



P2592-12930K
shown with Architectural Bronze blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	6,171 cubic feet per minute
Electricity Use	51 watts (excludes lights)
DOE Weighted CFM/W	132 CFM/W



Three-Speed Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-18.5°)
- AC Motor
- ABS blades
- Removable light kit. Blank plate included.
- White opal glass shade
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

SIZE

60" dia., 15" ht.
80" lead wires.

LAMP

18w LED Module, 3000K, 90 CRI,
1400 lumens, dimmable.



Teasley

FINISHES

- Architectural Bronze - 129
- Galvanized - 141
- Graphite - 143

P250004-143

shown with Gray Weathered Wood blades

Featuring coastal influences and farmhouse charm, the Teasley 56" 5-blade ceiling fan is suitable for a variety of interior settings. Clear seeded bell-shaped glass shades highlight Architectural Bronze, Galvanized or Graphite finish options. Three vintage LED lamps are included, offering energy efficiency and cost savings benefits for the home, while a dual mount canopy accommodates flat or sloped ceilings.

Dual Mount System

Farmhouse Style

Vintage LED Lamps

Teasley



P250004-129
shown with *Brushed Bronze* accents
and *American Walnut* blades

P250004-129 Architectural Bronze



Distressed Walnut

American Walnut


P250004-141 Galvanized



Driftwood

Gray Weathered Wood

P250004-143 Graphite



American Walnut

Gray Weathered Wood



P250004-141
shown with *Brushed Nickel* accents
and *Gray Weathered Wood* blades



P250004-143
shown with *Brushed Nickel* accents
and *American Walnut* blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	5,749 cubic feet per minute
Electricity Use	76 watts (excludes lights)
DOE Weighted CFM/W	88 CFM/W

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-18.5°)
- AC Motor
- Reversible plywood blades
- Clear seeded glass shades
- Three speed pull-chain switch
- Add a P2630-30 or P2630-95 wall control or P2662-01 hand-held remote control

SIZE

56" dia., 22-1/2" ht.
80" lead wires.

LAMP

Three medium base vintage lamps, each 7w max included, dimmable (with added remote or wall control).




Royer

FINISHES

- Antique Nickel - 081
- Forged Black- 080

P250010-080
shown with Distressed Ebony blades

The Royer collection's ceiling fan offers a charming, rustic look ideal for farmhouse and rustic spaces in need of a fresh breeze. Four plywood blades attach to the fixture's center by finely detailed metal arms. The crafted center is available in three finishes so you can select the perfect piece to complement your home décor.



Plywood Blades

Rustic Style

Detailed Metal Design

Royer

P250010-080 Forged Black



Matte Black
Distressed Ebony

P250010-081 Antique Nickel



Driftwood
Chesnut



P250010-080
shown with Matte Black blades



P250010-081
shown with Driftwood blades



Bottom detail of P250010-081
shown with Driftwood blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	6,255 cubic feet per minute
Electricity Use	67 watts (excludes lights)
DOE Weighted CFM/W	102 CFM/W



Three-Speed Remote Control Included
Three-speed fan operation

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Reversible plywood blades
- Not compatible with light kit
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

SIZE

60" dia., 17-7/8" ht.
80" lead wires.




Glandon

FINISHES

- Gilded Iron - 71
- Antique Nickel - 81

P2586-8130K
shown with Drifwood blades

Glandon offers a sophisticated design that is ideal for settings requiring a touch of modern flair. Six reversible blades in a walnut/driftwood faux wood finish are strapped by a sleek Antique Nickel metal bar for an unexpected industrial detail. The 60" Glandon ceiling fan features a 17w LED module (3000K color temperature) with a shatterproof white opal shade and a dual mount system. Full range dimming and remote control is included.




Modern Style

Reversible Blades

Opal Shade

Glandon

P2586-7130K Gilded Iron



Driftwood

Toasted Oak

P2586-8130K Antique Nickel



Driftwood

Classic Walnut



P2586-7130K
shown with Toasted Oak blades



P2586-8130K
shown with Classic Walnut blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	6,036 cubic feet per minute
Electricity Use	84 watts (excludes lights)
DOE Weighted CFM/W	96 CFM/W



Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Reversible plywood blades
- White opal shatterproof shade
- Remote control with batteries is included

SIZE

60" dia., 17-1/8" ht
80" lead wires.

LAMP

17w LED Module,
3000K, 90 CRI,
1400 lumens, dimmable.




Featuring Glandon, Debut and Glayse
Image: Richmond American Homes



1

3

Live An Open Life



A neutral color palette adds to the airiness of an open floor plan.

1

Use a ceiling fan with a light kit to provide both light and cooling power in the living area.

2

Make an open-concept space an entertainer's paradise with a kitchen that flows into the living areas.

3

Choose lighting as a single focal point for each of the areas to create room-like settings.

Greer

FINISHES

- Gilded Iron - 71
- Antique Nickel - 81

P2584-81
shown with Classic Walnut blades

This five-blade 54" Greer ceiling fan complements either industrial or farmhouse decor. It comes with a wire meshed shade light kit that uses two vintage LED lamps (included). Remote control is also included. Greer can be hung on a flat or sloped ceiling due to its dual mount system.


Industrial Design

Dual Mount System

Wire Mesh Shade

Greer

P2584-71 Gilded Iron



Driftwood

Toasted Oak

P2584-81 Antique Nickel



Driftwood

Classic Walnut



P2584-71
shown with Toasted Oak blades



P2584-81
shown with Driftwood blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	4,794 cubic feet per minute
Electricity Use	65 watts (excludes lights)
DOE Weighted CFM/W	82 CFM/W



Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-45°)
- AC Motor
- Reversible plywood blades
- Wire basket shade light kit
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 wall control

SIZE

54" dia., 21-5/8" ht
80" lead wires.

LAMP

Two medium base vintage lamps, each 5.5w max included, dimmable.

Fixtures shown with
V6.55T19DLED922/JA8 vintage lamps.



Chapin

FINISHES

- Antique Nickel - 081
- Oil Rubbed Bronze - 108
- Graphite - 143

P250022-108
shown with Distressed Walnut blades

The Chapin Collection effortlessly unites a spacious room, creating an atmosphere that's both relaxing and reviving. Antique nickel, Graphite, or oil rubbed bronze finishes complement each other with four plywood blades and a dual mount canopy for a design destined to provide a truly relaxing experience.



Dual Mount System

Relaxed Style

Plywood Blades

Chapin



P250022-081
shown with Driftwood blades

P250022-081 Antique Nickel



Driftwood

Classic Walnut

P250022-108 Oil Rubbed Bronze




Distressed Walnut

American Walnut



P250022-108
shown with American Walnut blades

P250022-143 Graphite



Graphite

Gray Weathered Wood



P250022-143
shown with Grey Weathered Wood blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	6,543 cubic feet per minute
Electricity Use	81 watts (excludes lights)
DOE Weighted CFM/W	87 CFM/W



Three-Speed Remote Control Included
Three-speed fan operation

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Reversible plywood blades
- Compatible with universal light kits
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

SIZE

54" dia., 14-1/2" ht.
80" lead wires.



Bedwin

FINISHES

- Antique Nickel - 081
- Galvanized - 141
- Graphite - 143

P250024-081
shown with Driftwood blades


Recall charming, rustic lattice work with the Bedwin Collection's farmhouse-inspired ceiling fan. With three finishes to pick from and four rough hewn plywood blades circling a handsome dual mount canopy, this ceiling fan is sure to help transform any living space into a cool paradise of relaxation.

Plywood Blades

Dual Mount System

Farmhouse Inspired Design

Bedwin



P250024-081
shown with Classic Walnut blades

P250024-081 Antique Nickel



Driftwood


Classic Walnut

P250024-141 Galvanized




Driftwood

Gray Weathered Wood



P250024-141
shown with Gray Weathered Wood blades

P250024-143 Graphite



Graphite

Gray Weathered Wood



P250024-143
shown with Graphite blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	6,044 cubic feet per minute
Electricity Use	34 watts (excludes lights)
DOE Weighted CFM/W	192 CFM/W



Full Function Remote Control Included
Six-speed fan operation
Reverse direction control

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- Reversible plywood blades
- Compatible with universal light kits
- Remote control with batteries is included

SIZE

56" dia., 15-1/2" ht.
80" lead wires.



Shaffer

FINISHES

- Satin White - 28
- Forged Black - 80
- Architectural Bronze - 129

P2590-80
shown with Silver blades

The 4-blade 56" Shaffer ceiling fan blends a streamlined design with mixed metal elements and a wire mesh housing, suitable for modern and urban industrial spaces. Available in Satin White with galvanized accents, forged black with chrome accents and Architectural Bronze with brushed bronze accents. Shaffer features a dual mount system and includes a remote control with batteries.

Dual Mount System

Modern Urban Design

Mixed Metal Elements

Shaffer



P2590-28
shown with Galvanized accents
and Silver blades


P2590-28 Satin White



P2590-80 Forged Black



P2590-129 Architectural Bronze



P2590-80
shown with Chrome accents
and Black blades



P2590-129
shown with Brushed Bronze accents
and Driftwood blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	6,144 cubic feet per minute
Electricity Use	67 watts (excludes lights)
DOE Weighted CFM/W	99 CFM/W



Three-Speed Remote Control Included
Three-speed fan operation

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-18.5°)
- AC Motor
- Reversible plywood blades
- Not compatible with light kits
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

SIZE

56" dia., 16-1/4" ht.
80" lead wires.



Soar

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20
- White - 30

P2542-2030K
shown with Walnut blades

With a white opal shade and a 17W dimmable LED module, the 54" Soar ceiling fan offers energy and cost-savings benefits for a variety of living spaces. The four-blade fan comes with a remote control and is available in Brushed Nickel, Antique Bronze and white finishes. LED source features a 3000K-color temperature. Soar features a dual mount system and includes a remote control with batteries.

Dual Mount System

White Opal Shade

Dimmable LED Light

Soar



P2542-0930K
shown with Black blades

P2542-0930K Brushed Nickel



Black

P2542-2030K Antique Bronze



Walnut

P2542-3030K White



White



P2542-2030K
shown with Walnut blades



P2542-3030K
shown with White blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	4,814 cubic feet per minute
Electricity Use	65 watts (excludes lights)
DOE Weighted CFM/W	83 CFM/W



Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Non-reversible plywood blades
- White opal shatterproof lens
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

SIZE

54" dia., 15" ht.
80" lead wires.

LAMP

17w LED Module, 3000K, 90 CRI,
1400 lumens, dimmable.



Harranvale

FINISHES

- Antique Bronze - 20
- White - 30
- Graphite - 143

P2540-14330K
shown with Graphite blades

The 54" Harranvale features a design that incorporates mixed metal design details that is very popular in today's home decor. Featuring reversible blades and opal glass shade, fans are available in three finish options: Antique Bronze with brushed bronze accent; Graphite with brushed nickel accent; and White with brushed nickel accent. Harranvale features a dual mount system and includes a remote control with batteries.

Mixed Metal Design

Opal Glass Shade

Reversible Blades



Harranvale



P2540-2030K
shown with Medium Cherry blades
and Brushed Bronze accent

P2540-2030K Antique Bronze




Classic Walnut
Medium Cherry

P2540-3030K White



White
White

P2540-14330K Graphite



Graphite
American Walnut



P2540-3030K
shown with White blades
and Brushed Nickel accent



P2540-14330K
shown with American Walnut blades
and Brushed Nickel accent

ENERGY INFORMATION AT HIGH SPEED

Airflow	5,121 cubic feet per minute
Electricity Use	66 watts (excludes lights)
DOE Weighted CFM/W	87 CFM/W



Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Reversible plywood blades
- White opal glass shade
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

SIZE

54" dia., 16-3/8" ht.
80" lead wires.

LAMP

17w LED Module, 3000K, 90 CRI,
1400 lumens, dimmable.



Graceful

FINISHES

- Brushed Nickel - 09
- Polished Chrome - 15
- Antique Bronze - 20

P2544-0930K
shown with Medium Cherry blades

Refresh your living space with the crisp, clean style of the 54" Graceful fan. With a white opal glass shade and a 17W dimmable LED module, the five-blade fan comes with a remote control and is available in Brushed Nickel, polished chrome and Antique Bronze finishes. LED source offers a 3000K-color temperature, energy savings and maintenance benefits for the home.



Clean Style

Dimmable LED Light


Opal Glass Shade

Graceful



P2544-0930K
shown with Silver blades


P2544-0930K Brushed Nickel



Medium Cherry

Silver

P2544-1530K Polished Chrome



Toasted Oak

Silver

P2544-2030K Antique Bronze



Medium Cherry

American Walnut



P2544-1530K
shown with Toasted Oak blades



P2544-2030K
shown with American Walnut blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	4,454 cubic feet per minute
Electricity Use	60 watts (excludes lights)
DOE Weighted CFM/W	83 CFM/W



Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Reversible plywood blades
- White opal glass shade
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

SIZE

54" dia., 16-3/8" ht.
80" lead wires.

LAMP

17w LED Module, 3000K, 90 CRI,
1400 lumens, dimmable.



Olson

FINISHES

- Brushed Nickel - 09
- Graphite - 143

P2598-143
shown with Graphite blades

The 52" Olson ceiling fan features a generously sized etched watermark glass shade and sweeping blades highlighted with metal accents in a Brushed Nickel or Graphite finish. Two LED lamps are JA8 compliant, offering both form and function with energy and cost-savings benefits. Olson features a dual mount system and a three-speed pull chain fan switch, as well as an on/off pull chain switch to operate the light.

Metal Accents

LED Light

Watermark Glass Shade

Olson

P2598-09 Brushed Nickel



Medium Cherry

Classic Walnut

P2598-143 Graphite



Gray Weathered Wood

Graphite



P2598-09
shown with Medium Cherry blades



P2598-143
shown with Gray Weathered Wood blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	5,023 cubic feet per minute
Electricity Use	70 watts (excludes lights)
DOE Weighted CFM/W	83 CFM/W

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-18.5°)
- AC Motor
- Reversible plywood blades
- Etched watermark glass
- Three speed pull-chain switch
- Add a P2630-30 or P2630-95 wall control, P2661-01 or P2662-01 hand-held remote control

SIZE

52" dia., 21-5/16" ht.
80" lead wires.

LAMP

Two Medium base LED lamps, 3000K, 90 CRI, 800 lumens, dimmable (with added remote or wall control).



Gust

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20
- Graphite - 143

P2582-0930K
shown with Silver blades

This five-blade 54" Gust ceiling fan features a white opal glass shade that is available in a Brushed Nickel, Antique Bronze or Graphite finish. A remote control is included. Gust has a dual mount system to offer greater flexibility when installing. The 18W dimmable, 3000K LED module provides energy and cost-savings benefits to the homeowner.



Sleek Design

Dual Mount System

Dimmable LED Light

Gust

P2582-0930K Brushed Nickel



P2582-2030K Antique Bronze



P2582-14330K Graphite



P2582-0930K
Shown with Silver blades



P2582-2030K
Shown with Walnut blades



P2582-14330K
Shown with Graphite blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	5,242 cubic feet per minute
Electricity Use	65 watts (excludes lights)
DOE Weighted CFM/W	87 CFM/W



Three-Speed Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-18.5°)
- AC Motor
- Manual reverse switch
- Non-reversible plywood blades
- White opal glass shade
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

SIZE

54" dia., 16" ht.
80" lead wires.

LAMP

18w LED Module, 3000K, 90 CRI,
1400 lumens, dimmable.



Casual, Modern Charm

2





1

Craftsman style gets modern flair with clean and bright design.

1

Hang a sleek Gust fan from a paneled ceiling for Craftsman style with a modern edge.

2

Pair farmhouse-style furniture with cozy textures and neutral colors for casual comfort.

3

Break up a bright space visually with a handcrafted, dark wood door.

3

Kudos

FINISHES

- Brushed Nickel - 09
- Polished Chrome - 15
- Antique Bronze - 20

P2568-0930K
shown with American Walnut blades

This five-blade 52" Kudos ceiling fan features a clear Fresnel glass shade. Available in a Brushed Nickel, polished chrome or Antique Bronze finish and includes a remote control. The Kudos features a dual mount system to offer greater flexibility when installing. The 18W dimmable, 3000K LED module provides energy and cost-savings benefits to the homeowner.



Fresnel Glass Shade

Dual Mount System


Dimmable LED Light

Kudos



P2568-0930K
shown with Silver blades

P2568-0930K Brushed Nickel



American Walnut

Silver

P2568-1530K Polished Chrome



Medium Cherry

Black

P2568-2030K Antique Bronze



Walnut

Cherry



P2568-1530K
shown with Black blades



P2568-2030K
shown with Cherry blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	5,160 cubic feet per minute
Electricity Use	60 watts (excludes lights)
DOE Weighted CFM/W	91 CFM/W



Three-Speed Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-18.5°)
- Downrod installation only. Can not be flush mounted.
- AC Motor
- Reversible plywood blades
- Clear Fresnel glass shade
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

SIZE

52" dia., 17-5/8" ht.
80" lead wires.

LAMP

18w LED Module, 3000K, 90 CRI,
1400 lumens, dimmable.



Fresno

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20
- White - 30

P2548-2030K
shown with Cherry blades

Five-blade 60" Fresno ceiling fan features an LED light source, offering both form and function with energy and cost-savings benefits. A white opal glass shade features an 18W dimmable, 3000K LED module. A remote control with full range dimming and remote control is included.



Clean Design

Dimmable LED Light

White Opal Glass Shade

Fresno




P2548-0930K
shown with Silver blades


P2548-0930K Brushed Nickel



P2548-2030K Antique Bronze



P2548-3030K White



P2548-2030K
shown with Dark Walnut blades



P2548-3030K
shown with White blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	5,718 cubic feet per minute
Electricity Use	79 watts (excludes lights)
DOE Weighted CFM/W	80 CFM/W



Full Function Remote Control Included
Three-speed fan operation
Full-range dimming for light
Reverse direction control

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-17.5°)
- AC Motor
- Reversible plywood blades
- White opal glass shade
- Remote control with batteries is included, receiver mounted in motor.
- Remote control may be replaced with P2631-30 wall control

SIZE

60" dia., 17-1/4" ht.
80" lead wires.

LAMP

18w LED Module, 3000K, 90 CRI,
1400 lumens, dimmable.



Tempt

FINISHES

- Polished Chrome - 15
- Antique Bronze - 20
- Vintage Brass - 163

P2578-16330K
shown with Chesnut blades

This five-blade 52" Tempt ceiling fan features a clear, double prismatic glass shade that is available in a Polished chrome, Antique Bronze or Vintage Brass finish. A remote is included. Tempt features a dual mount system to offer greater flexibility when installing. The 17w dimmable, 3000K LED module provides energy and cost-savings benefits to the homeowner.



Prismatic Glass Shade

Dual Mount System

Dimmable LED Light

Tempt



P2578-1530K
shown with Medium Cherry blades

P2578-1530K Polished Chrome



Medium Cherry

Black


P2578-2030K Antique Bronze



Medium Cherry

American Walnut

P2578-16330K Vintage Brass



Dark Cherry

Chesnut



P2578-2030K
shown with American Walnut blades



P2578-16330K
shown with Dark Cherry blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	4,314 cubic feet per minute
Electricity Use	63 watts (excludes lights)
DOE Weighted CFM/W	78 CFM/W



Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Reversible plywood blades
- Clear double prismatic glass shade
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

SIZE

52" dia., 16-1/4" ht.
80" lead wires.

LAMP

17w LED Module, 3000K, 90 CRI,
1400 lumens, dimmable.



Verada

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20

P2558-0930K
shown with Medium Cherry blades

This five-blade 52" Verada ceiling fan combines a linen glass shade with a 17W LED source. Available in a Brushed Nickel or Antique Bronze finish. Verada features a dual mount system and a three-speed pull chain fan switch, as well as an on/off pull chain switch to operate the light. LED light kit features a 3000K color temperature.

Dual Mount System

LED Light

Linen Glass Shade

Verada

P2558-0930K Brushed Nickel



Medium Cherry
American Walnut

P2558-2030K Antique Bronze



Medium Cherry
American Walnut



P2558-0930K
shown with white linen glass
and American Walnut blades



P2558-2030K
shown with tea stained linen glass
and Medium Cherry blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	4,445 cubic feet per minute
Electricity Use	65 watts (excludes lights)
DOE Weighted CFM/W	79 CFM/W

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-30°)
- AC Motor
- Reversible plywood blades
- Linen glass shade
- 3 Speed pull chain switches
- Add a P2630-30 or P2630-95 wall control or P2662-01 hand-held remote control

SIZE

52" dia., 16" ht.
80" lead wires.

LAMP

17w LED Module, 3000K, 90 CRI,
1400 lumens, dimmable (with added
remote or wall control).



Billows

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20
- Forged Black - 80

P2552-09
shown with White Washed blades

With a sophisticated and traditional design, the Billows offers both form and function with two energy efficient LED lamps, featuring a 3000K color temperature. The 52" Billows ceiling fan features an LED light kit with white opal glass shade and five reversible blades. The fans are available in Brushed Nickel, Antique Bronze and Forged Black finishes.

Traditional Design

Reversible Blades

White Opal Glass Shade

Billows



P2552-09
shown with Silver blades

P2552-09 Brushed Nickel



White Washed

Silver


P2552-20 Antique Bronze



Cherry

American Walnut

P2552-80 Forged Black



Black

Toasted Oak



P2552-20
shown with American Walnut blades



P2552-80
shown with Toasted Oak blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	4,682 cubic feet per minute
Electricity Use	59 watts (excludes lights)
DOE Weighted CFM/W	92 CFM/W

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-18.5°)
- AC Motor
- Reversible plywood blades
- White opal glass shade
- Add a P2630-30 or P2630-95 wall control or P2662-01 hand-held remote control

SIZE

52" dia., 17-1/2" ht.
80" lead wires.

LAMP


Two medium base, 3000K, LED lamps included. 90 CRI, 800 lumens/lamp, dimmable (with added remote or wall control).



1

Accessorize with Style

3





2

Pops of blue and plenty of collectibles give a room personality.

1

Select a ceiling fan like Billows, whose whitewashed-finish blades accentuate the organic textures in the room.

2

Follow your style by curating your space with treasures that you love.

3

Pick a focal point like the rough stone fireplace and use its natural color palette to inform the color choices for the rest of the space.

Signature

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20
- Forged Bronze - 77
- Forged Black - 80
- Antique Nickel - 81

P2521-09WA
Shown with Dark Walnut blades

A 52" Signature 5-blade fan features reversible blades and a 30-year limited warranty. A powerful AirPro motor features a 3-speed, triple-capacitor control that can also be reversed to provide year-round comfort. The Signature fan will also accept a universal light kit.

Reversible Blades

Powerful Motor

Traditional Style

Signature




P2521-09
shown with White blades




P2521-09CH
Shown with Cherry blades

P2521-09 Brushed Nickel



P2521-09CH Brushed Nickel




P2521-09WA Brushed Nickel




P2521-20 Antique Bronze



P2521-77 Forged Bronze



P2521-80 Forged Black



P2521-81 Antique Nickel



P2521-20
Shown with P2602-20WB light kit*
with Classic Walnut blades
* Light kit sold separately.



P2521-77
Shown with Classic Walnut blades



P2521-80
Shown with Dark Cherry blades



P2521-81
Shown with Medium Oak blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	4,701 cubic feet per minute
Electricity Use	65 watts (excludes lights)
DOE Weighted CFM/W	84 CFM/W


FEATURES

- 30-year limited warranty
- 45° Canopy
- Close-to-ceiling installation
- SureConnect® System
- AC Motor
- Compatible with universal light kits
- Three speed pull-chain switch
- Add a P2630-30 or P2630-95 wall control or P2662-01 hand-held remote control

SIZE

52" dia., 14-5/8" ht. (CTC 11-9/16" ht.), 80" lead wires.

CTC INSTALLATION



Trevina II 44"

The Trevina collection features fans with a signature three-blade design. Perfect for modern or traditional interiors, each fan includes an LED light source to help extend your day into the evening as you and your family relax in your peaceful retreat.


FINISHES

- Brushed Nickel - 09
- Satin White - 28
- Black - 31


P2555-0930K Brushed Nickel



P2555-2830K Satin White



P2555-3130K Black



Detail of P2555-0930K shown with P2668-09 blank plate and Silver blades

BLANK PLATE

- P2668-09 Brushed Nickel
- P2668-28 Satin White
- P2668-31 Black



P2668-09



P2668-28



P2668-31



ENERGY INFORMATION AT HIGH SPEED

Airflow	4306 cubic feet per minute
Electricity Use	42 watts (excludes lights)
DOE Weighted CFM/W	122 CFM/W

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Reversible MDF blades
- Removable light kit. Blank plate sold separately.
- White Opal glass
- Compatible with remote or hardwired wall controls (P2630, P2661-01, P2662-01, P2663-01, P2665 (sold separately))

SIZE

44" dia., 15-5/8" ht.
80" lead wires.

LAMP

18w LED Module,
3000K, 90 CRI,
1400 lumens, dimmable.



Wall Control Included
Four-speed fan operation
Full-range dimming for light
Includes switch plate cover

Trevina II 52"



P2553-129WB
shown with Medium Cherry blades




P2553-152WB
shown with Black blades

FINISHES

- Architectural Bronze - 129
- Painted Nickel - 152

P2553-129WB Architectural Bronze



P2553-152WB Painted Nickel



ENERGY INFORMATION AT HIGH SPEED

Airflow	5,296 cubic feet per minute
Electricity Use	56 watts (excludes lights)
DOE Weighted CFM/W	112 CFM/W

FEATURES

- Limited lifetime warranty (LED model)
- Dual Mount (flat or sloped ceiling-30°)
- AC Motor
- White opal glass
- Reversible plywood blades
- No switch included
- Compatible with remote control or hardwired wall controls (P2618-01, P2630, P2662-01 (sold separately))

SIZE

52" dia., 15-3/4" ht.
80" lead wires.

LAMP

Two 9.5w LED lamps (dimmable).



P2556-3030K
shown with White blades



P2556-2030K
shown with Medium Cherry blades




P2556-0930K
shown with Silver blades

Trevina II 52"


FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20
- White- 30

P2556-3030K White



P2556-2030K Antique Bronze



P2556-0930K Brushed Nickel



ENERGY INFORMATION AT HIGH SPEED

Airflow	4,916 cubic feet per minute
Electricity Use	62 watts (excludes lights)
DOE Weighted CFM/W	89 CFM/W

FEATURES

- Limited lifetime warranty (LED model)
- Dual Mount (flat or sloped ceiling-30°)
- AC Motor
- White opal glass
- Reversible plywood blades

SIZE

52" dia., 15-3/4" ht.
80" lead wires.

LAMP

17w LED Module, 3000K, 90 CRI, 1400 lumens, dimmable.



Wall Control Included
Four-speed fan operation
Full-range dimming for light
Includes switch plate cover



1

2

Coolly Modern





Wow family and friends with a dramatic ceiling treatment.

1

Install a ceiling fan like Trevina, whose contemporary design brings both form and function.

2

Add molding or beams to the ceiling to create a spectacular "fifth wall."

3

Choose wood floors and cabinetry as a warming element to unite an open floor plan.


Signature Plus II

Five-blade 54" Signature Plus II ceiling fan features an integrated LED light source, offering both form and function with energy and cost-savings benefits. The light kit contains a white opal shatterproof shade and is comprised of a 17W dimmable 3000K LED module.

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20
- White - 30

P2539-0930K Brushed Nickel



Driftwood

Silver

P2539-2030K Antique Bronze



Classic Walnut

Medium Cherry

P2539-3030K White



White

White



P2539-0930K
shown with Silver blades



P2539-2030K
shown with Medium Cherry blades



P2539-3030K
shown with White blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	5,331 cubic feet per minute
Electricity Use	65 watts (excludes lights)
DOE Weighted CFM/W	92 CFM/W

FEATURES

- Limited lifetime warranty
- 45° Canopy
- Downrod mount only
- AC Motor
- Reversible MDF blades
- White opal shatterproof shade
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

SIZE

54" dia., 15-1/2" ht.
80" lead wires.

LAMP

17w LED Module, 3000K, 90 CRI,
1400 lumens, dimmable.



Remote Control Included
Three-speed fan operation
Full-range dimming for light


Signature Plus



FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20
- White - 30

P2530-09 Brushed Nickel



Natural Cherry

Silver

P2530-20 Antique Bronze



Classic Walnut

Medium Cherry

P2530-30W White



White

White



ENERGY INFORMATION AT HIGH SPEED

Airflow	4,716 cubic feet per minute
Electricity Use	65 watts (excludes lights)
DOE Weighted CFM/W	84 CFM/W

FEATURES

- 30-year limited warranty
- 45° Canopy
- Downrod mount only
- AC Motor
- Compatible with universal light kits
- Three speed pull-chain switch
- Add a P2630-30 or P2630-95 wall control or P2662-01 hand-held remote control

SIZE

54" dia., 15" ht.
80" lead wires.



Edgefield

FINISHES

- Brushed Nickel - 009
- White - 030
- Architectural Bronze - 129


P250016-129
shown with Medium Cherry blades

The 52" Edgefield fan is energy efficient and lightweight. A DC motor provides ultra quiet operation and the efficiency of the latest fan technology along with the simple convenience of a four-speed pull chain switch. Edgefield features a reversible motor for year round comfort and is available in three finish options. Pair with a universal light kit for a more customized look.

Ultra Quiet

Lightweight

Energy Efficient



Edgefield



P250016-009
shown with American Walnut blades

P250016-009 Brushed Nickel



American Walnut

Cherry

P250016-030 White



White

White

P250016-129 Antique Bronze



Classic Walnut

Medium Cherry



P250016-030
shown with White blades



P250016-129
shown with Medium Cherry blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	5,741 cubic feet per minute
Electricity Use	34 watts (excludes lights)
DOE Weighted CFM/W	179 CFM/W

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-18.5°)
- DC motor
- Manual reverse switch
- MDF blades
- Compatible with universal light kits
- Three speed pull-chain switch
- Will not accept a wall or remote control

SIZE

52" dia., 14-9/16" ht.
80" lead wires



Clifton Heights

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20

P2531-09
shown with Cherry blades

52" 4-blade Clifton Heights ceiling fan features distinctive, squared reversible blades. This contemporary styled fan offers great performance and value. The Clifton Heights fan features a powerful, 3-speed motor that can be reversed to provide year-round comfort. The Clifton Heights fan will also accept a universal light kit.




3-Speed Motor

Contemporary Style


Distinctive Square Blades

Clifton Heights

P2531-09 Brushed Nickel



P2531-20 Antique Bronze



ENERGY INFORMATION AT HIGH SPEED

Airflow	4,373 cubic feet per minute
Electricity Use	55 watts (excludes lights)
DOE Weighted CFM/W	89 CFM/W

FEATURES


- 30-year limited warranty
- 45° Canopy
- Close-to-ceiling installation
- SureConnect System
- AC Motor
- Compatible with universal light kits
- Three speed pull-chain switch
- Add a P2630-30 or P2630-95 wall control or P2662-01 hand-held remote control

SIZE

52" dia., 15-3/4" ht.
(CTC 11" ht.),
80" lead wires.



CTC INSTALLATION




52" Performance

FINISHES


- Brushed Nickel - 09
- Antique Bronze - 20
- White - 30

P2503-09 Brushed Nickel




P2503-09
shown with Natural Cherry blades

P2503-20 Antique Bronze



P2503-30W
shown with White blades

P2503-30W White



P2503-20
shown with P2650-20TWB light kit*
and Medium Cherry blades
* Light kit sold separately.



P2503-20
shown with Medium Cherry blades



45° Canopy

- Standard canopy works with sloped ceilings up to 45°. (12:12 ceiling pitch)
- Outlet box mounting plate includes convenient hands-free hanger for wiring.
- Oversize, textured die-cast hanger ball reduces vibrations that can cause noise and wobble.
- Dual-mount for downrod or close-to-ceiling installation (on select fans)



SureConnect® System

- Motor screws pre-installed in blade arms to prevent them from falling out during installation.
- Special guides perfectly align blade arms to motor.
- Preinstalled rubber isolation pads prevent vibration noise.

ENERGY INFORMATION AT HIGH SPEED

Airflow	5,143 cubic feet per minute
Electricity Use	70 watts (excludes lights)
DOE Weighted CFM/W	85 CFM/W

FEATURES


- Limited lifetime warranty
- 45° Canopy
- Close-to-ceiling installation
- SureConnect® System
- AC Motor
- Compatible with universal light kits
- Three speed pull-chain switch
- Add a P2630-30 or P2630-95 wall control or P2662-01 hand-held remote control

SIZE

52" dia., 15-1/4" ht.
(CTC 10-1/2" ht.),
80" lead wires.



CTC INSTALLATION



42" Builder Fan



P2500-20
shown with Classic Walnut blades



P2500-09
shown with Cherry blades




P2500-30
shown with White blades


FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20
- White - 30


P2500-09 Brushed Nickel



P2500-20 Antique Bronze



P2500-30 White



P2500-09
shown with P2600-09WB light kit*
and with Cherry blades
*Light kit sold separately.

ENERGY INFORMATION AT HIGH SPEED

Airflow	3,053 cubic feet per minute
Electricity Use	46 watts (excludes lights)
DOE Weighted CFM/W	64 CFM/W

FEATURES


- 15-year limited warranty
- 23° Canopy
- Close-to-ceiling installation
- SureConnect® System
- AC Motor
- Compatible with universal light kits
- Three speed pull-chain switch
- Add a P2630 wall control or P2662-01 hand-held remote control

SIZE

42" dia., 12-3/8" ht.
(CTC 8-5/16" ht.),
72" lead wires.



CTC INSTALLATION



52" Builder Fan with Light Kit

FINISHES

- Brushed Nickel - 009
- White - 030
- Architectural Bronze - 129

P2599-09 Brushed Nickel



Natural Cherry

Cherry

P2599-30 White



White

White

P2599-129 Antique Bronze



Classic Walnut

Medium Cherry



P2599-09
shown with Cherry blades



P2599-30
shown with White blades



P2599-129
shown with Classic Walnut blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	4,474 cubic feet per minute
Electricity Use	65 watts (excludes lights)
DOE Weighted CFM/W	82 CFM/W

FEATURES

- 30-year limited warranty
- Dual Mount (flat or sloped ceiling-30°)
- AC Motor
- MDF/Plywood hybrid blades
- Etched white glass shade
- Three speed pull-chain switch
- Add a P2630-30 or P2630-95 wall control or P2662-01 hand-held remote control
- Two medium base, 3000K, LED lamps included. 800 lumens/lamp, non-dimmable.

SIZE

52" dia., 17-5/8" ht.
80" lead wires.

LAMP

Two medium base lamps,
3000K, LED lamps included.
800 lumens/lamp, non-dimmable.



52" Builder Fan



P2501-09
shown with Cherry blades



P2501-30W
shown with White blades



P2501-30
shown with Washed Oak blades



P2501-15
shown with Driftwood blades



P2501-20
shown with Medium Cherry blades



P2501-143
shown with Black blades

FINISHES

- Brushed Nickel - 09
- Polished Chrome - 15
- Antique Bronze - 20
- White - 30
- White - 30W
- Graphite - 143

P2501-09 Brushed Nickel




- Natural Cherry
- Cherry

P2501-15 Antique Bronze




- Black
- Driftwood

P2501-20 White



- Medium Cherry
- Classic Walnut

P2501-30 White



- White
- Washed Oak

P2501-30W White



- White
- White

2501-143 Graphite



- Graphite
- Black

ENERGY INFORMATION AT HIGH SPEED

Airflow	4,991 cubic feet per minute
Electricity Use	63 watts (excludes lights)
DOE Weighted CFM/W	98 CFM/W

FEATURES

- 30-year limited warranty
- 45° Canopy
- Close-to-ceiling installation with accessory
- SureConnect® System
- AC Motor
- Compatible with universal light kits
- Add a P2630 wall control or P2662-01 hand-held remote control

SIZE

52" dia., 13-1/2" ht.
80" lead wires.




Drift

FINISHES

- Brushed Nickel - 009
- White - 030
- Architectural Bronze - 129

P250008-009
shown with Silver blades

Enhance your home with the perfect mix of form and function with the 32" four-blade Drift fan. Ideal for smaller spaces, such as closets, mudrooms and laundry rooms, Drift features a powerful motor and a steep pitch to circulate a lot of air within a smaller space.




Powerful Motor

Compact Design


Traditional Style

Drift


P250008-009 Brushed Nickel



P250008-030 White



P250008-129 Architectural Bronze



P250008-009
shown with Driftwood blades



P250008-030
shown with Driftwood blades



P250008-129
shown with Classic Walnut blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	2,518 cubic feet per minute
Electricity Use	35 watts (excludes lights)
DOE Weighted CFM/W	88 CFM/W

FEATURES


- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-30°)
- Close-to-ceiling installation
- AC Motor
- Reversible MDF blades
- Compatible with universal light kits
- Three speed pull-chain switch
- Add a P2630-30 or P2630-95 wall control or P2662-01 hand-held remote control

SIZE

32" dia., 14-3/8" ht.
80" lead wires.



CTC INSTALLATION



Lindale

FINISHES

- Satin White - 028
- Antique Nickel - 081
- Architectural Bronze - 129

P250028-129
shown with Distressed Walnut blades

Retreat for a little rest and relaxation under the gentle airflow offered by the Lindale collection's ceiling fan. A mid-century modern style blends with a flush mount design as four rectangular plywood blades attach to the fan's vase-inspired center. Select your favorite finish from three beautiful options to customize your Lindale fan for a perfect fit in your home décor design.



Flush Mount Design

Mid-Century Modern


Plywood Blades

Lindale



P250028-028
shown with *Brushed Nickel* accents
and *Matte White* blades


P250028-028 Satin White



P250028-081 Antique Nickel



P250028-129 Architectural Bronze



P250028-081
shown with *White Barnwood* blades

LINDALE LIGHT KIT

P2669-028 Satin White

P2669-081 Antique Nickel

P2669-129 Architectural Bronze
24w LED Module, 3000K, 90 CRI,
2000 lumens, dimmable.



P2669-28



P2669-81



P2669-129



P250028-129
shown with *Matte Gold* accents,
Classic Walnut blades and
optional *P2669-129* Light Kit

ENERGY INFORMATION AT HIGH SPEED

Airflow	4,642 cubic feet per minute
Electricity Use	60 watts (excludes lights)
DOE Weighted CFM/W	87 CFM/W



Three-Speed Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited lifetime warranty
- Hugger low profile mounting
- AC Motor
- Reversible plywood blades
- Accepts P2669 light kit, sold separately.
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

SIZE

52" dia., 11-3/16" ht.
80" lead wires.



*Light kits only are JA8

Braden

FINISHES

- Brushed Nickel - 09
- Polished Chrome - 15
- Architectural Bronze - 129

P2588-1530K
shown with Black blades

This Braden 56", three-blade, hugger-style ceiling fan features clean lines and a design that complements modern interiors. A white opal glass shade contains an integrated 18W LED module, offering both form and function with energy and cost-savings benefits. Featuring a larger motor, Braden moves more air than a traditional hugger ceiling fan.




Braden




P2588-0930K
shown with Silver blades


P2588-0930K Brushed Nickel



P2588-1530K Polished Chrome



P2588-12930K Architectural Bronze



P2588-1530K
shown with American Walnut blades



P2588-12930K
shown with Medium Cherry blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	4,263 cubic feet per minute
Electricity Use	55 watts (excludes lights)
DOE Weighted CFM/W	85 CFM/W

FEATURES

- Limited lifetime warranty
- Hugger low profile mounting
- AC Motor
- Reversible plywood blades
- White opal glass shade
- Full function remote control with batteries is included
- Remote control may be replaced with P2631-30 wall control

SIZE

56" dia., 9-7/8" ht.
12" lead wires.

LAMP

18w LED Module, 3000K, 90 CRI, 1400 lumens, dimmable.



Full Function Remote Control Included
Three-speed fan operation
Full-range dimming for light
Reverse direction control



Vox Fan

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20
- White - 30

P2572-0930K
shown with Medium Cherry blades

Five-blade 52" Vox hugger-style ceiling fan features an LED light source, offering both form and function with energy and cost-savings benefits. A white opal glass shade contains a 17W dimmable, 3000K LED module. A full function remote control is included. The fan mounts close to the ceiling and is available in popular Brushed Nickel, Antique Bronze and white finishes.



Dimmable LED Light

Modern Style

White Opal Glass Shade

Vox Fan



P2572-0930K
shown with Medium Cherry blades

P2572-0930K Brushed Nickel



Medium Cherry

P2572-2030K Antique Bronze



American Walnut

P2572-3030K White



White



P2572-2030K
shown with American Walnut blades



P2572-3030K
shown with White blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	4,276 cubic feet per minute
Electricity Use	62 watts (excludes lights)
DOE Weighted CFM/W	76 CFM/W



Full Function Remote Control Included
Three-speed fan operation
Full-range dimming for light
Reverse direction control

FEATURES

- Limited Lifetime Warranty
- Hugger low profile mounting
- AC Motor
- Non-reversible plywood blades
- White opal glass shade
- Full function remote control with batteries is included
- Remote control may be replaced with P2631-30 wall control

SIZE

52" dia., 11-5/8" ht.
8" lead wires.

LAMP

17w LED Module,
3000K, 90 CRI,
1400 lumens, dimmable.



52" Hugger Fan

P2525-09 Brushed Nickel



Cherry

Natural Cherry

P2525-20 White



White

White



P2525-09
shown with P2610-09WB light kit*
and with Cherry blades

* Light kit sold separately.



P2525-30
shown with White blades



P2525-09
shown with Cherry blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	3,229 cubic feet per minute
Electricity Use	56 watts (excludes lights)
DOE Weighted CFM/W	58 CFM/W

FEATURES

- 15-year limited warranty
- Hugger low profile mounting
- AC Motor
- Compatible with universal light kits
- Cannot be used with remote control
- Add a P2630-30 or P2630-95 wall control

SIZE

52" dia., 8-1/8" ht.



42" Hugger Fan



P2524-30
shown with White blades

P2524-09 Brushed Nickel



Cherry

Natural Cherry

P2524-30 White



White

White



P2524-09
shown with P2602-09WB light kit*
and with Natural Cherry blades

* Light kit sold separately.



P2524-09
shown with Natural Cherry blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	2,639 cubic feet per minute
Electricity Use	44 watts (excludes lights)
DOE Weighted CFM/W	72 CFM/W

FEATURES

- 15-year limited warranty
- Hugger low profile mounting
- AC Motor
- Compatible with universal light kits
- Cannot be used with remote control
- Add a P2630-30 or P2630-95 wall control

SIZE

42" dia., 8-5/16" ht.





Featuring 54" Patio Fan and Maison



Outdoor Ceiling Fans

Enhance outdoor living areas



Scan with your camera on
your smartphone or visit
www.progresslighting.com/ceilingfans

Montague
P2564-8030K

Relaxed 3

1 Organic Shapes

Beach Accents 2



Dan McGinty
Product Designer




Easy, Breezy, Coastal with Dan

Bring your home right to the ocean side with beach-inspired accents, organic furnishings and an overall relaxed feel. Designers often create a relaxed and open environment with soft throw blankets, pillows, cozy rugs and cushioned furniture to complete the Coastal look. Focus on an all-white color palette for your coastal inspired home, while incorporating in soft beachy hues to complement the look.

When it comes to selecting materials for flooring, décor and furniture, seek out dark or weathered wood pieces to emulate a seaside environment nestled nicely by the shore.



Shop this style at
www.progresslighting.com/coastal



Alfresco

FINISHES

- Architectural Bronze - 129
- Blistered Iron - 171

P250034-129-WB
shown with Dark Bamboo blades

Infuse a warm, nature-inspired style to your outdoor home décor with the one-of-a-kind Alfresco collection. Five blades decorated in a leaf-like design sprout from a dual mount center that artistically harbors an LED light source. Select from an Architectural Bronze and blistered iron finish to bring your bohemian dreamland to life.

Leaf-like Decorated Blades

Nature-Inspired Design

Dimmable LED Light

Alfresco

P250034-129-WB Architectural Bronze



Dark Bamboo

P250034-171-WB Blistered Iron



Pewter



P250034-129-WB
shown with Dark Bamboo blades



P250034-171-WB
shown with Pewter blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	5,724 cubic feet per minute
Electricity Use	68 watts (excludes lights)
DOE Weighted CFM/W	90 CFM/W



Three-Speed Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- ABS blades
- Damp Location Rated
- Clear seeded glass
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

SIZE

54" dia., 19-1/4" ht.
80" lead wires.

LAMP

Two ST19 vintage LED lamps, 3000K, 90 CRI, 800 lumens, dimmable.



Rudder

FINISHES

- Matte White - 028
- Matte Black - 031
- Architectural Bronze - 129

P250040-028-30
shown with Distressed White blades

Transform any outdoor space into a cozy country abode with the charming rustic character of the Rudder collection. Four boat oar-inspired blades attach to a smooth center that features an LED light source for friendly illumination as needed. Available in a Matte White, Matte Black, or Architectural Bronze finish, Rudder is sure to fill your favorite patio or porch with a refreshing breeze wrapped in country character.



Oar-Inspired Blades

Charming Rustic Design

Dimmable LED Light

Rudder



P250040-028-30
shown with Distressed White blades

P250040-028-30 Matte White



Distressed White

P250040-031-30 Matte Black



Distressed Ebony

P250040-129-30 Architectural Bronze



Walnut



P250040-031-30
shown with Distressed Ebony blades



P250040-129-30
shown with Walnut blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	6,112 cubic feet per minute
Electricity Use	35 watts (excludes lights)
DOE Weighted CFM/W	188 CFM/W



Full Function Remote Control Included
Six-speed fan operation
Full-range dimming for light
Reverse direction control

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- ABS blades
- Damp Location Rated
- White opal glass shade
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

SIZE

56" dia., 16-1/8" ht.
80" lead wires.

LAMP

24w LED Module,
3000K, 90 CRI,
2000 lumens, dimmable.



Edisto

FINISHES

- Forged Black - 80
- Antique Nickel - 81
- Architectural Bronze - 129

P2596-8030K
shown with Charcoal Canvas blades

The Edisto 54" two-blade outdoor ceiling fan combines a sleek, contemporary style with high-quality performance. A wire frame supports canvas wrapped blades that feature UV inhibitors to protect the fabric from fading in the sunlight. Three fan speeds and a reversible switch keep individuals cool in the summer and warm in the winter. A white opal glass shade contains an 18W LED module light kit, offering energy efficient and cost savings benefits.

Canvas Wrapped Blades

Contemporary Style

White Opal Glass Shade

Edisto



P2596-8030K
shown with Charcoal Canvas blades

P2596-8030K Forged Black



Charcoal Canvas

P2596-8130K Antique Nickel



Oatmeal Canvas

P2596-12930K Architectural Bronze



Mushroom Canvas



P2596-8130K
shown with Oatmeal Canvas blades



P2596-12930K
shown with Mushroom Canvas blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	4,371 cubic feet per minute
Electricity Use	65 watts (excludes lights)
DOE Weighted CFM/W	73 CFM/W



Three-Speed Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-18.5")
- AC Motor
- Canvas wrapped blades
- Damp Location Rated
- White opal glass shade
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

SIZE

54" dia., 14-7/8" ht.
80" lead wires.

LAMP

18w LED Module,
3000K, 90 CRI,
1400 lumens, dimmable.



The Living is Easy





Kick back and relax in a room that brings the outside in.

1

Choose a fan filled with style like Edisto, whose canvas-wrapped blades offset the sleek look of its forged black finish.

2

Use rough-hewn wooden beams to punctuate walls and ceiling with rustic style.

3

Incorporate organic touches of wood and rattan for comfortable, relaxation-ready seating.

Whirl

FINISHES

- Antique Bronze - 20
- Forged Black - 80
- Antique Nickel - 81

P2574-8130K
shown with Driftwood blades

Refresh your indoor or covered outdoor living spaces with the crisp, clean style of the 60" Whirl fan. The stylish design comes in Antique Nickel, Antique Bronze and Forged Black finish options. The five-blade fan features an all weather damp location rating to accommodate a variety of settings throughout the home.

Clean Style

Minimal Design

White Frosted Glass Shade

Whirl



P2574-2030K
shown with Walnut blades

P2574-2030K Antique Bronze



Walnut

P2574-8030K Forged Black



Toasted Oak

P2574-8130K Antique Nickel



Driftwood



P2574-8030K
shown with Toasted Oak blades



P2574-8130K
shown with Driftwood blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	6,549 cubic feet per minute
Electricity Use	70 watts (excludes lights)
DOE Weighted CFM/W	106 CFM/W

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-18.5°)
- AC Motor
- ABS all weather blades
- White Frosted Glass Shade
- Three speed pull-chain switch (fan)
- On/off pull-chain switch (light)
- Damp Location Rated
- Add a P2630-30 or P2630-95 wall control or P2662-01 hand-held remote control

SIZE

60" dia., 15-7/8" ht.
80" lead wires.

LAMP

18w LED Module,
3000K, 90 CRI,
1400 lumens, dimmable (with
added remote or wall control).



Featuring Whirl

Relax All Year Long





Light-filled sunrooms offer the best of indoor-outdoor living.

1

Add a beautiful Whirl ceiling fan to move the air comfortably for ultimate relaxation.

2

Install multiple recessed fixtures to create the perfect ambiance for peaceful relaxation.

3

Accessorize with organic touches of wicker furniture topped with cozy cushions for a tranquil neutral color scheme.

Smyrna

P2576-2030K
shown with Walnut blades

FINISHES

- Antique Bronze - 20
- Forged Black - 80

This 52" Smyrna ceiling fan features an LED light source, offering both form and function with energy and cost-savings benefits. The light kit contains a clear hammered glass shade and contains a 17W dimmable 3000K LED module. Includes a wall control switch for fan speed and light operation.

Traditional Style

Dimmable LED Light

Clear Hammered Glass Shade

Smyrna

P2576-2030K Antique Bronze



Walnut

P2576-8030K Forged Black



Toasted Oak



P2576-2030K
shown with Walnut blades



P2576-8030K
shown with Toasted Oak blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	4,585 cubic feet per minute
Electricity Use	58 watts (excludes lights)
DOE Weighted CFM/W	91 CFM/W



Wall Control Included
Four-speed fan operation
Full-range dimming for light
Includes switch plate cover

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-30°)
- AC Motor
- ABS all weather blades
- Clear hammered glass shade
- Wet Location Rated

SIZE

52" dia., 19-1/2" ht.
80" lead wires.

LAMP

17w LED Module,
3000K, 90 CRI,
1400 lumens, dimmable.



Montague

FINISHES

- Antique Bronze - 20
- White - 30
- Forged Black - 80

P2564-8030K
shown with Toasted Oak blades

This five-blade 60" Montague ceiling fan features an all weather wet location rating to accommodate a variety of interior and exterior locations. The white opal glass shade contains a 18W dimmable, 3000K LED module, offering both form and function with energy and cost-savings benefits. A full function remote control is included.

Interior and Exterior Locations

Dimmable LED Light

White Opal Glass Shade

Montague



P2564-2030K
shown with Walnut blades

P2564-2030K Antique Bronze



Walnut

P2564-3030K White



White

P2564-8030K Forged Black



Toasted Oak



P2564-3030K
shown with White blades



P2564-8030K
shown with Toasted Oak blades



Scan with the camera on your smartphone for the Montague installation video.

ENERGY INFORMATION AT HIGH SPEED

Airflow	6,693 cubic feet per minute
Electricity Use	75 watts (excludes lights)
DOE Weighted CFM/W	96 CFM/W



Full Function Remote Control Included
Three-speed fan operation
Full-range dimming for light
Reverse direction control

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-18.5°)
- AC Motor
- White opal Glass Shade
- ABS all weather blades
- Wet Location Rated
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

SIZE

60" dia., 17-5/8" ht.
80" lead wires.

LAMP

18w LED Module,
3000K, 90 CRI,
1400 lumens, dimmable.



Albin

FINISHES

- Satin White- 028
- Matte Black- 031
- Architectural Bronze - 129

P250036-129-30
shown with Distressed Walnut blades

The Albin collection offers a modern take on a traditional design that will be perfectly at home in so many outdoor spaces and lifestyles. Five blades finished with a faux wood grain texture extend from a modern-style center available in an Architectural Bronze, Satin White, or Matte Black finish. An LED light source is encased in a crisp shade to illuminate a patio or porch space that will beg to be lived in an enjoyed.

Faux Wood Grain Texture

Modern Style

Dimmable LED Light

Albin




P250036-028-30
shown with Satin White blades


P250036-028-30 Satin White



P250036-031-30 Matte Black



P250036-129-30 Architectural Bronze



P250036-031-30
shown with Toasted Oak blades



P250036-129-30
shown with Distressed Walnut blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	5,740 cubic feet per minute
Electricity Use	67 watts (excludes lights)
DOE Weighted CFM/W	95 CFM/W



Three Speed Remote Control Included
Three speed fan operation
Full range dimming with light

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Plywood blades
- Damp Location Rated
- White opal glass shade
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

SIZE

54" dia., 15-5/8" ht.
80" lead wires.

LAMP

24w LED Module, 3000K,
90 CRI,
2000 lumens, dimmable.



Lakehurst

FINISHES

- Antique Bronze - 20
- White - 30
- Forged Black - 80

P2562-20
shown with Walnut blades

This five-blade 60" Lakehurst ceiling fan features an all weather wet location rating (ABS) to accommodate a variety of interior and exterior locations. The Lakehurst fan will accept a universal outdoor rated light kit. Features a dual mount system and a three-speed pull chain fan switch.

Interior and Exterior Locations

Traditional Design

Dual Mount System



Lakehurst




P2562-20 Antique Bronze



P2562-30 White



P2562-80 Forged Black



ENERGY INFORMATION AT HIGH SPEED

Airflow	6,440 cubic feet per minute
Electricity Use	71 watts (excludes lights)
DOE Weighted CFM/W	105 CFM/W

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-18.5°)
- AC Motor
- ABS all weather blades
- Compatible with universal light kits
- 3 Speed pull chain switch
- Wet Location Rated
- Add a P2630-30 or P2630-95 wall control or P2662-01 hand-held remote control

SIZE

60" dia., 15-3/4" ht.
80" lead wires.



Decorative Patio Fan

P2526-20
shown with Washed Walnut blades

FINISH

● Antique Bronze - 20

52" Indoor/Outdoor five-blade fan with all-weather ABS blades in palm-style design and a rich Antique Bronze finish. Three-speed motor offers great performance and value that can be reversed to provide year-round comfort. Antique Brass pull chain with medium oak fob complements the Washed Walnut blades. The Patio fan will also accept a universal outdoor rated light kit.

Washed Walnut Blades

Antique Bronze Finish

Palm-Style Design

Decorative Patio Fan

P2526-20 Antique Bronze



Washed Walnut



P2526-20
shown with Washed Walnut blades



P2526-20
shown with P2636-20WB light kit*
and Washed Walnut blades
* Light kit sold separately.

ENERGY INFORMATION AT HIGH SPEED

Airflow	4,150 cubic feet per minute
Electricity Use	70 watts (excludes lights)
DOE Weighted CFM/W	77 CFM/W

FEATURES


- 15-year limited warranty
- 45° Canopy
- Close-to-ceiling installation
- SureConnect® System
- AC Motor
- ABS all-weather blades
- Compatible with universal light kits
- Damp location rated
- Add a P2630-30 or P2630-95 wall control or P2662-01 hand-held remote control

SIZE

52" dia., 17-3/8" ht.
(CTC 12-3/16 ht.),
80" lead wires.



CTC INSTALLATION




54" Patio Fan

FINISH

● Antique Bronze - 20

P2533-20 Antique Bronze



P2533-20
shown with Toasted Oak blades
* Light kit sold separately.

ENERGY INFORMATION AT HIGH SPEED

Airflow 4,986 cubic feet per minute
Electricity Use 65 watts (excludes lights)
DOE Weighted CFM/W 74 CFM/W

FEATURES


- 30-year limited warranty
- 45° Canopy
- SureConnect® System
- AC Motor
- ABS all-weather blades
- Wet location rated
- Compatible with universal light kits
- Add a P2630-30 or P2630-95 wall control or P2662-01 hand-held remote control

SIZE

54" dia., 18-1/4" ht.
 (CTC 12-3/16 ht.),
 80" lead wires.



CTC INSTALLATION




52" Patio Fan

P2502-20 Antique Bronze



P2502-30 White




P2502-30
shown with White blades




P2502-80
shown with Toasted Oak blades

P2502-80 Forged Black



P2502-141 Galvanized



P2502-141
shown with Silver blades



P2502-20
shown with Oak blades

ENERGY INFORMATION AT HIGH SPEED

Airflow 4,991 cubic feet per minute
Electricity Use 64 watts (excludes lights)
DOE Weighted CFM/W 89 CFM/W

FEATURES


- 15-year limited warranty
- Dual Mount (flat or sloped ceiling-23°)
- Close-to-ceiling installation
- SureConnect® System
- Quick-Install canopy
- AC Motor
- ABS all-weather blades
- Compatible with universal light kits
- Three speed pull-chain switch
- Wet location rated
- Add a P2630-30 or P2630-95 wall control or P2662-01 hand-held remote control

SIZE

52" dia., 12-3/4" ht.
 (CTC 9-11/16 ht.),
 72" lead wires.



CTC INSTALLATION







Featuring 52" Builder Fan with P2602-30WB Light Kit
Image: Kirbor Homes and Susan Wilson Interiors

Accessories

Accessorise your living area



Scan with your camera on
your smartphone or visit
www.progresslighting.com/ceilingfans



James Thomas
Senior Product Designer

Modernly Minimalism

with James

Modern interiors showcase sleek design through the use of neutrals, a minimalism approach, and the use of glass décor and technology. Take advantage of spaces with wide windows and use glass in other details such as countertops and furniture. This creates a sleek design for interior spaces. Integrate new innovations into a home's décor by adding elements, such as voice activated

devices and remote controlled light dimmers. To accentuate a Modern color palette, stick to neutral shades, as well as an overall minimalistic design to create this look.



Shop this style at
www.progresslighting.com/modern



Indoor/Outdoor

Universal-style with quick-connect wiring.

SCHOOLHOUSE

P2601-20WB Antique Bronze

P2601-30WB White

P2601-80WB Forged Black

P2601-141WB Galvanized with opal glass.

8-1/2" dia., 7" ht.

One medium base, 3000K, LED lamp included.

800 lumens/lamp, 90 CRI.

(dimmable)

Wet Location Rated



P2601-20WB



P2601-30WB



P2601-80WB



P2601-141WB

LOW PROFILE

P2611-20WB Antique Bronze

P2611-30WB White

P2611-80WB Forged Black

with opal glass.

10-1/2" dia., 4-1/2" ht.

Two medium base, 3000K,

LED lamp included.

800 lumens/lamp, 90 CRI.

(dimmable)

Wet Location Rated



P2611-20WB



P2611-30WB



P2611-80WB

ASHMORE

P2636-20WB Antique Bronze

with frosted seeded glass.

11" dia., 8-1/4" ht.

Two medium base, 3000K,

LED lamp included.

800 lumens/lamp, 90 CRI.

(dimmable)

Wet Location Rated



P2636-20WB

All fixtures:



Torino

Universal-style light kit with quick-connect wiring.

P2645-77WB Forged Bronze with tea-stained glass.

P2645-01WB

with etched glass.

Included Finials:

-09 Brushed Nickel

-20 Antique Bronze

-80 Forged Black

12" dia., 5-3/4" ht.

Two medium base, 3000K,

LED lamps included.

800 lumens/lamp, 90 CRI.

Indoor use only. (dimnable)



P2645-77WB



P2645-01WB
shown with
-09 finial



P2645-01WB
shown with
-20 finial



P2645-01WB
shown with
-80 finial

Gather, Bravo & Joy

Universal-style light kit with quick-connect wiring.

P2650-20TWB Antique Bronze with tea-stained glass.

P2650-01WB

with etched glass.

Included Finials:

-09 Brushed Nickel

-20 Antique Bronze

11" dia., 5-1/2" ht.

Two medium base, 3000K,

LED lamps included.

800 lumens/lamp, 90 CRI.

Indoor use only. (dimnable)



P2650-20TWB



P2650-01WB
shown with
-09 finial



P2650-01WB
shown with
-20 finial

Madison

Universal-style with quick-connect wiring.

P2623-09WB Brushed Nickel

P2623-20WB Antique Bronze with etched glass.

19" dia., 8" ht.

Three medium base, 3000K,

LED lamps included.

800 lumens/lamp, 90 CRI.

Indoor use only. (dimnable)



P2623-09WB



P2623-20WB

Universal Bowl

Universal-style with quick-connect wiring.

P2612-20TWB Antique Bronze
with tea-stained glass.

P2612-01WB
with alabaster glass.

Included Finials:

- 09 Brushed Nickel
- 20 Antique Bronze
- 30 White
- 15 Polished Chrome
- 143 Graphite

10-3/4" dia., 5-1/2" ht.

Two medium base, 3000K,

LED lamps included.

800 lumens/lamp, 90 CRI.

Indoor use only. (dimnable)



P2612-20TWB




P2612-01WB
shown with
-09 finial



P2612-01WB
shown with
-15 finial



P2612-01WB
shown with
-20 finial



P2612-01WB
shown with
-30 finial



P2612-01WB
shown with
-143 finial

Wisten

Universal-style light kit with quick-connect wiring.

P2649-01WB

with etched glass.

Included Finials:

- 09 Brushed Nickel
- 20 Antique Bronze

11" dia., 6-1/4" ht.

Two medium base, 3000K,

LED lamps included.

800 lumens/lamp, 90 CRI.

Indoor use only. (dimnable)



P2649-01WB
shown with
-09 finial



P2649-01WB
shown with
-20 finial

Clifton Heights

Universal-style with quick-connect wiring.

P2654-01WB

with etched glass.

Included Finials:

- 09 Brushed Nickel
- 20 Antique Bronze

12-1/2" sq., 6-1/4" ht.

Two medium base, 3000K,

LED lamps included.

800 lumens/lamp, 90 CRI.

Indoor use only. (dimnable)



P2654-01WB
shown with
-09 finial



P2654-01WB
shown with
-20 finial

LED Light Kits

Universal-style light kits with quick connect wiring.

P2659-09 Brushed Nickel
P2659-20 Antique Bronze
P2659-30 White
 with etched white glass.
 12-1/4" dia., 4" ht.
 One 16w, 3000K
 LED module included.
 1265 source lumens,
 960 delivered lumens,
 90 CRI. Indoor use only.
 (dimnable)



P2659-09



P2659-20



P2659-30

P2660-01
 with etched alabaster glass.
 Included Finials:
 -09 Brushed Nickel
 -20 Antique Bronze
 -30 White
 11-1/4" dia., 5-3/8" ht.
 One 16w, 3000K
 LED module included.
 1241 source lumens,
 1150 delivered lumens,
 90 CRI. Indoor use only.
 (dimnable)



P2660-01
 shown with
 -09 finial



P2660-01
 shown with
 -20 finial



P2660-01
 shown with
 -30 finial

All fixtures:



Trinity

Universal-style with quick-connect wiring.

P2628-01WB
 with etched glass.
 Included Finials:
 -09 Brushed Nickel
 -20 Antique Bronze
 -30 White
 -77 Forged Bronze
 13-3/8" dia., 6-3/8" ht.
 Two medium base, 3000K,
 LED lamps included.
 800 lumens/lamp, 90 CRI.
 Indoor use only. (dimnable)



P2628-01WB
 shown with
 -09 finial



P2628-01WB
 shown with
 -20 finial



P2628-01WB
 shown with
 -30 finial



P2628-01WB
 shown with
 -77 finial



Four Light Universal

Universal-style with quick-connect wiring.

P2643-09WB Brushed Nickel

P2643-20WB Antique Bronze

P2643-30WB White
with alabaster glass.

P2643-20TWB Antique Bronze
with tea stained alabaster glass.

13-5/8" dia., 7-3/4" ht.

Four medium base, 3000K,

LED lamps included.

800 lumens/lamp, 90 CRI.

Indoor use only. (dimnable)



P2643-09WB



P2643-20WB



P2643-30WB



P2643-20TWB

Three Light Universal

Universal-style with quick-connect wiring.

P2642-09WB Brushed Nickel

P2642-30WB White

with alabaster glass.

13-5/8" dia., 7-3/4" ht.

Three medium base, 3000K,

LED lamps included.

800 lumens/lamp, 90 CRI.

Indoor use only. (dimnable)



P2642-09WB



P2642-30WB

Low Profile

Universal-style with quick-connect wiring.

P2602-09WB Brushed Nickel

P2602-15WB Polished Chrome

P2602-20WB Antique Bronze

P2602-30WB White

P2602-143WB Graphite

with white opal glass.

10-1/2" dia., 4-1/2" ht.

Two medium base, 3000K,

LED lamps included.

800 lumens/lamp, 90 CRI.

Indoor use only. (dimnable)



P2602-09WB



P2602-15WB



P2602-20WB



P2602-30WB



P2602-143WB

Four Light Alabaster

Spring clip glass attachment. For use with P2500, P2501, P2502, P2524 and P2525.

P2610-09WB Brushed Nickel
P2610-15WB Polished Chrome
P2610-20WB Antique Bronze
P2610-30WB White
P2610-143WB Graphite
with alabaster glass.
14-1/2" dia., 6-1/4" ht.
Four medium base, 3000K,
LED lamps included.
800 lumens/lamp, 90 CRI.
Indoor use only. (dimnable)



Three Light Alabaster

Spring clip glass attachment. For use with P2500, P2501, P2502, P2524 and P2525.

P2600-09WB Brushed Nickel
P2600-20WB Antique Bronze
P2600-30WB White
with alabaster glass.
15" dia., 6-5/8" ht.
Three medium base, 3000K,
LED lamps included.
800 lumens/lamp, 90 CRI.
Indoor use only. (dimnable)



Schoolhouse

Universal-style with quick-connect wiring.

P2644-09WB Brushed Nickel
P2644-30WB White
with white opal glass.
8-1/2" dia., 6-1/2" ht.
One medium base, 3000K,
LED lamp included.
800 lumens/lamp, 90 CRI.
Indoor use only. (dimnable)



Accessory Downrods


3/4" diameter; approximately 1" outside diameter.

CEILING HT. DOWNROD L.	9'-10'	10'-11'	11'-12'	12'-14'	13'-15'	14'-16'	15'-17'
Brushed Nickel	P2603-09	P2604-09	P2605-09	P2606-09	P2607-09	P2608-09	P2609-09
Polished Chrome	P2603-15	P2604-15	P2605-15	P2606-15	P2607-15	P2608-15	P2609-15
Antique Bronze	P2603-20	P2604-20	P2605-20	P2606-20	P2607-20	P2608-20	P2609-20
<i>*Use with 77, 108 and 129 finishes</i>							
Matte White	P2603-28	P2604-28	P2605-28	P2606-28	P2607-28	P2608-28	P2609-28
White	P2603-30	P2604-30	P2605-30	P2606-30	P2607-30	P2608-30	P2609-30
Matte Black	P2603-31	P2604-31	P2605-31	P2606-31	P2607-31	P2608-31	P2609-31
Forged Bronze	P2603-77	P2604-77	P2605-77	P2606-77	P2607-77	P2608-77	P2609-77
<i>*Use with 20 finish</i>							
Forged Black	P2603-80	P2604-80	P2605-80	P2606-80	P2607-80	P2608-80	P2609-80
<i>*Use with 71 finish</i>							
Antique Nickel	P2603-81	P2604-81	P2605-81	P2606-81	P2607-81	P2608-81	P2609-81
Galvanized	P2603-141	P2604-141	P2605-141	P2606-141	P2607-141	-	-
Graphite	P2603-143	P2604-143	P2605-143	P2606-143	P2607-143	P2608-143	P2609-143
Painted Nickel	P2603-152	P2604-152	P2605-152	P2606-152	P2607-152	-	-
Vintage Brass	P2603-163	P2604-163	P2605-163	P2606-163	P2607-163	-	-
Blistered Iron	P2603-171	P2604-171	P2605-171	P2606-171	P2607-171	-	-
Black Chrome	P2603-231	P2604-231	P2605-231	P2606-231	P2607-231	-	-

Downrod Selection Guide

Allow at least 7 feet (84 in.) from the floor to the bottom of the fan, with 8 or 9 feet being the ideal above-floor placement.

**Average length downrod, included with each fan.*



Remotes, Wall Controls & 45° Canopies



P2662-01
Fan/Light Remote
Universal remote operates three fan speeds and full-range dimming light control. Includes canopy receiver and wall storage bracket. Will work with LED lamps and modules. Featuring four “dip” switches and 16 code options to avoid the chance of interference from other remotes.



P2663-01
Fan/Light Remote
Universal remote with two, four or eight-hour timer option, operates three fan speeds and full-range dimming light control. Includes canopy receiver and wall storage bracket. Will work with LED lamps and modules. Featuring many code combination options to avoid the chance of interference from other remotes.



P2618-01
Fan/Light Remote
Provides fan speed and light control from convenient hand-held remote. Compatible with non-dimmable compact fluorescent lamps. For single pole applications. Receiver fits in fan canopy.



P2661-01
Universal Fan/Light Remote
Provides fan speed and full range light dimming control from a convenient hand held remote control. For single pole applications. Includes a wall plate for added storage convenience. Receiver fits in the fan canopy.



P2667-31
Wifi Fan/Light Remote
Universal Wifi remote control for AC motor fans. Control your ceiling fan or light kit via Wifi from anywhere. Pairs with Alexa, Google Home, or app on your phone or tablet. Voice control the fan with three speeds and the light with full range dimming. App control the fan with three speeds or four timer selections or full range dimming control of the light. Can be controlled with the hand held remote included with the kit.



P2665-30 White
Universal remote includes a wall mount transmitter, ideal for multi-family applications, that operates three fan speeds and full-range dimming light control. Includes canopy receiver and wall storage bracket. Will work with LED lamps and modules. Featuring four “dip” switches and 16 code options to avoid the chance of interference from other remotes.



P2631-30 White
Full-function wall control transmitter (receiver sold with ceiling fan). Use with, or in place of, hand-held remote included with fans that have a downlight. Includes switch plate cover.



P2630-95 Ivory
Four-speed fan wall control with full-range light dimmer. Fits single-gang wall box; requires two circuits. Includes switch plate cover. Not for use with multiple fans.



P2630-30 White
Four-speed fan wall control with full-range light dimmer. Fits single-gang wall box; requires two circuits. Includes switch plate cover. Not for use with multiple fans.



P2613-95 Ivory
Four-speed fan wall control. Includes switch plate cover. Not for use with multiple fans.



P2613-30 White
Four-speed fan wall control. Includes switch plate cover. Not for use with multiple fans.



P2666-09
Brushed Nickel
45° canopy*



P2666-30
White
45° canopy*




P2666-129
Architectural Bronze
45° canopy*

**This accessory is for use with the following ceiling fan models only: P2501, P2503, P2521, P2536, P2530, P2531, P2533, and P2539. Includes ceiling bracket, canopy, hanger ball, trim ring, and CTC mounting hardware.*

Cross Reference Chart

Here's where you'll find the specifications you'll need to purchase the perfect fan for your space. Search by Model Number, Name or Page Number.

Fan Diagram Reference:




Model Number	Model Name	Page	Motor (MM)	Fan Diameter	Blade Pitch	Dimensions				Motor Warranty
						A	B	C	D	
P250000	Springer	27	DC-165	60"	22°	17.38"	13.19"	8.38"	6.06"	Limited Lifetime
P250002	Farris	29	DC-125N	60"	18°-13°	15.63"	12.5"	7.5"	5.13"	Limited Lifetime
P250004	Teasley	65	188 X 15	56"	12.5°	22.44"	12.56"	10.88"	6.44"	Limited Lifetime
P250006	Loring	35	120 X 20	33"	13.5°	15.19"	9.02"	6.06"	7.73"	Limited Lifetime
P250008	Drift	121	153 X 12	32"	13°	14.38"	11.75"	9.25"	5.9"	Limited Lifetime
P250010	Royer	67	172 X 20	56"	13°	17.82"	16.39"	1.035"	5.13"	Limited Lifetime
P250012	Gulliver	33	N/A	23"	N/A	18.13"	N/A	5.75"	7.31"	Limited Lifetime
P250016	Edgefield	113	DC-125N	52"	13°	14.44"	12.5"	11.0"	5.18"	Limited Lifetime
P250022	Chapin	75	188 X 22	54"	14°	15.88"	14.45"	9.75"	5.18"	Limited Lifetime
P250024	Bedwin	77	DC-125N	54"	14°	15.44"	12.25"	8.69"	5.18"	Limited Lifetime
P250026	Arlo	51	DC153-20NS	60"	13°	18.56"	14.0"	8.25"	5.18"	Limited Lifetime
P250028	Lindale	123	153 X 18	52"	13°	11.19"	8.0"	8.25"	5.96"	Limited Lifetime
P250030	Huff	45	DC168-25NS	96"	14°	15.44"	12.0"	11.63"	6.25"	Limited Lifetime
P250032	Holland	61	DC153-10NS	60"	23°	16.63"	13.56"	8.56"	5.12"	Limited Lifetime
P250034	Alfresco	135	188 X 15	54"	13°	19.25"	11.88"	12.0"	5.94"	Limited Lifetime
P250036	Albin	151	172 X 17	54"	13°	15.63"	10.62"	11.01"	6.31"	Limited Lifetime
P250038	Bixby	53	DC125-30NS	60"	18°	17.69"	15.12"	6.93"	5.19"	Limited Lifetime
P250040	Rudder	137	DC153-10NS	56"	14°	16.01"	12.0"	9.13"	6.31"	Limited Lifetime
P2500	Builder	117	153 X 10	42"	12°	12.25"	9.65"	9.5"	5.13"	15yr Limited
P2501	Builder	119	153 X 12	52"	11°	12.71"	9.58"	11.0"	5.13"	30yr Limited
P2502	52" Patio Fan	156	153 X 17	52"	11°	12.75"	10.2"	11.75"	5.13"	15yr Limited
P2503	Performance	116	188 X 15	52"	14°	15.25"	12.56"	12.19"	6.5"	Limited Lifetime
P2521	Signature	105	153 X 18	52"	12°	14.63"	11.5"	11.75"	6.5"	30yr Limited
P2524	Hugger	129	153 X 10	42"	11°	8.31"	5.5"	10.0"	10.0"	15yr Limited
P2525	Hugger	128	153 X 13	52"	11°	8.13"	5.93"	11.06"	11.06"	15yr Limited
P2526	Deco Patio Fan	155	188 X 20	52"	12°	17.38"	14.25"	12.13"	6.5"	15yr Limited
P2530	Signature Plus	111	153 X 18	54"	12°	15.13"	10.4"	11.8"	6.5"	30yr Limited
P2531	Clifton Heights	115	153 X 18	52"	12.5°	15.75"	12.7"	7.88"	6.5"	30yr Limited
P2533	Patio Fan	156	153 X 18	54"	12°	18.75"	13.34"	11.38"	6.5"	30yr Limited
P2539	Signature Plus II	110	153 X 18	54"	12°	15.3"	11.2"	11.8"	6.5"	Limited Lifetime
P2540	Harranvale	83	153 X 20	54"	12°	16.38"	12.1"	12.63"	5.88"	Limited Lifetime
P2542	Soar	81	153 X 20	54"	12°	14.7"	11.05"	10.1"	5.88"	Limited Lifetime
P2544	Graceful	85	153 X 20	54"	12°	16.38"	11.5"	9.75"	5.88"	Limited Lifetime

Continued on following spread.

Cross Reference Chart *continued*

Fan Diagram Reference:



Model Number	Model Name	Page	Motor (MM)	Fan Diameter	Blade Pitch	Dimensions				Motor Warranty
						A	B	C	D	
P2546	Ellwood	41	212 X 25	68"	17°	16.7"	11.5"	9.63"	5.88"	Limited Lifetime
P2548	Fresno	95	188 X 25	60"	14°	17.2"	10.8"	12.75"	5.88"	Limited Lifetime
P2550	Vast	47	DC - 165	72"	14°	16.75"	13.67"	8.25"	5.13"	Limited Lifetime
P2552	Billows	101	153 X 15	52"	12°	17.5"	11.18"	9.1"	5.88"	Limited Lifetime
P2553	Trevina II	107	153 X 15	52"	12°	15.75"	10.8"	9.44"	5.88"	Limited Lifetime
P2554	Gaze	55	172 X 17	60"	12°	13.13"	10.71"	6.88"	5.13"	Limited Lifetime
P2555	Trevina II	106	153 X 12	44"	12°	15.68"	12.21"	8.38"	5.88"	Limited Lifetime
P2556	Trevina II	107	153 X 15	52"	12°	15.75"	10.8"	9.44"	5.88"	Limited Lifetime
P2558	Verada	99	153 X 18	52"	12°	16.56"	10.1"	10.19"	5.88"	Limited Lifetime
P2560	Caleb	43	212 X 25	68"	17°	18.0"	11.98"	13.75"	5.88"	Limited Lifetime
P2562	Lakehurst	153	188 X 25	60"	13.5°	15.69"	13.5"	11.25"	5.9"	Limited Lifetime
P2564	Montague	149	188 X 25	60"	13°	17.63"	12.28"	9.95"	5.9"	Limited Lifetime
P2568	Kudos	93	172 X 17	52"	13°	17.63"	13.11"	9.69"	5.95"	Limited Lifetime
P2570	Spades	57	DC188-10	56"	22°	18.13"	16.67"	8.08"	6.42"	Limited Lifetime
P2572	Vox	127	153 X 18	52"	12°	11.63"	7.13"	11.41"	9.91"	Limited Lifetime
P2574	Whirl	143	188 X 25	60"	12°	15.88"	11.93"	10.01"	5.91"	Limited Lifetime
P2576	Smyrna	147	153 X 20	52"	12°	19.44"	10.75"	11.94"	5.88"	Limited Lifetime
P2578	Tempt	97	153 X 18	52"	12°	16.19"	9.94"	10.25"	5.88"	Limited Lifetime
P2582	Gust	89	172 X 20	54"	13.5°	16.0"	13.13"	9.95"	5.91"	Limited Lifetime
P2584	Greer	73	153 X 20	54"	12°	21.56"	11.61"	7.88"	5.88"	Limited Lifetime
P2586	Glandon	69	188 X 25	60"	12°	17.06"	13.09"	9.06"	5.88"	Limited Lifetime
P2588	Braden	125	172 X 20	56"	13°	9.81"	7.23"	7.70"	7.70"	Limited Lifetime
P2590	Shaffer	79	188 X 20	56"	13.5°	16.31"	12.65"	10.16"	6.25"	Limited Lifetime
P2592	Oriole	63	172 X 20	60"	21°	14.56"	12.5"	9.17"	6.0"	Limited Lifetime
P2594	Sanford	37	N/A	23"	31.7°	17.69"	13.13"	22.81"	5.12"	Limited Lifetime
P2596	Edisto	139	172 X 17	54"	20°	14.88"	9.85"	11.01"	5.91"	Limited Lifetime
P2598	Olson	87	172 X 20	52"	13.5°	19.94"	8.75"	9.30"	6.0"	Limited Lifetime
P2599	Uni Pack	118	153 X 12	52"	11°	17.56"	9.58"	11.0"	5.13"	30yr Limited

Fan Blade Finishes



American Walnut



Charcoal Fabric




Dark Walnut




Antique Bronze



Cherry



Distressed Ebony




Architectural Bronze




Chestnut




Distressed Walnut



Black




Classic Walnut



Distressed White




Black Metallic



Dark Bamboo



Driftwood




Brushed Nickel



Dark Cherry




Galvanized



Graphite




Oak



Washed Oak



Gray Weathered Wood



Oatmeal Fabric




Washed Walnut



Medium Cherry



Pewter




White




Medium Oak




Silver



White Barnwood



Mushroom Fabric



Toasted Oak



White Metallic



Natural Cherry



Walnut



White Washed



All finish representations are part of Progress Lighting's comprehensive design and specification program. Through extensive research, these finishes have been carefully chosen to complement all Progress Lighting products, including our extensive range of materials and accessory options.

These finish representations match actual finish colors as accurately as possible, and while every effort has been made to render colors accurately, they may vary slightly from the actual product, especially hand-painted finishes due to the nature of hand craftsmanship.

Product Index

P2000

P2500.....	.26	P2544.....	.85	P2570.....	.56
P2501.....	.119	P2546.....	.40	P2572.....	.126
P2502.....	.156	P2548.....	.94	P2574.....	.142
P2503.....	.116	P2550.....	.46	P2576.....	.146
P2521.....	.105	P2552.....	.100	P2578.....	.96
P2524.....	.129	P2553.....	.107	P2582.....	.88
P2525.....	.128	P2554.....	.54	P2584.....	.72
P2526.....	.154	P2555.....	.106	P2586.....	.68
P2530.....	.111	P2556.....	.107	P2588.....	.124
P2531.....	.115	P2558.....	.98	P2590.....	.78
P2533.....	.156	P2560.....	.42	P2592.....	.62
P2539.....	.110	P2562.....	.152	P2594.....	.36
P2540.....	.82	P2564.....	.148	P2596.....	.138
P2542.....	.80	P2568.....	.92	P2598.....	.87

P25000

P2599.....	.118	P250000.....	.26	P250028.....	.122
P2613.....	.169	P250002.....	.28	P250030.....	.44
P2618.....	.169	P250004.....	.64	P250032.....	.60
P2630.....	.169	P250006.....	.34	P250034.....	.134
P2631.....	.169	P250008.....	.120	P250036.....	.150
P2661.....	.169	P250010.....	.66	P250038.....	.52
P2662.....	.169	P250012.....	.32	P250040.....	.136
P2663.....	.169	P250016.....	.112		
P2665.....	.169	P250022.....	.74		
P2666.....	.169	P250024.....	.76		
P2667.....	.169	P250026.....	.50		



Products referencing this logo meet the energy efficiency requirements for light fixtures set forth in ENERGY STAR® product specifications. Please refer to www.energystar.gov for specific product qualifications and list of certified products.



Please note indoor only (dry location) fans should only be used indoors. Even if an outdoor area or screened-in porch is covered, the motor and the blades can be affected when exposed to humidity. You can, however, “bring the outdoors inside” – as using outdoor ceiling fans are perfectly acceptable to use in interior spaces.



If you are selecting a ceiling fan for a space that is outdoors and under a roof, i.e. any covered porches; you should select either a damp rated or wet listed fan. Damp location fans may also be used indoors.



If the fan comes directly into contact with water, you'll need to ensure that the ceiling fan has a “wet” listing. Ceiling fans designed for damp or wet locations feature elements, such as moisture-resistant motors and all weather blades. Wet location fans may also be used indoors.



This marking indicates fixtures that have an integrated LED or replaceable LED module that has been tested and listed in the California Appliance Database. Check for certified lamps, fixtures or LED light engines by searching the MAEDBS database. Go to cacertappliances.energy.ca.gov



Complies with “American with Disabilities Act”



Table 150.0A defines products that do not have to meet JA8 and can be used to comply with 2016 Title 24. The most common types include:

- Pin-based linear or compact fluorescent light sources using electronic ballasts
- GU-24 sockets containing light sources other than LEDs
- Inseparable SSL luminaires that are installed outdoors



Products comply with the California Appliance Efficiency Regulations. Certified products are listed on the appliance efficiency database found at www.appliances.energy.ca.gov.



Products with this icon are Dark-Sky Friendly: they are certified by the International Dark-Sky Association to minimize glare while reducing light trespass and skyglow (they don't pollute the night sky.)



The products with this logo have passed the cUL requirements and are available for sale in Canada. These products include the additional safety features needed to comply with the regulations in Canada. Items with the icon are listed with NRCAN.



Products with this icon are compatible with our P2667-31 wi-fi control. Easily control your fan with your smart phone, tablet, voice controls or a hand-held remote. Use the Smart by Bond technology to control: on/off function of the fan and light kit, full range dimming, 3 fan speeds, breeze mode and 3 timer settings.

Warranty

For more details regarding product warranty coverage, please consult a qualified Progress Lighting distributor or visit:

www.progresslighting.com/warranty

Where to buy

To purchase Progress Lighting products from one of our authorized dealers visit:

www.progresslighting.com/where-to-buy



Equip. Educate. Excite.

These three words define the mission of Progress Lighting. Flip through our catalog, and you'll quickly see how we equip you with the education to make all your exciting design dreams come true. Not sure where to start? Whether you're browsing our catalog or visiting our website, Progress is at your service to help you envision where and how to use our products.

Experience Progress

Learn how lighting can totally transform a space. Experience Progress features beautiful room images from our builder partners, design firms, social media fans and influencers bringing the Progress Lighting story to life. Visit www.progresslighting.com/experienceprogress

Our Blog

Explore our blog for even more design inspiration, product integration and trend guidance to make your home into a haven of livable luxury. See www.progresslighting.com/blog

Be Inspired

-  @ProgressLtg
-  @ProgressLtg
-  @ProgressLighting
-  @ProgressLtg
-  Progress Lighting
-  Progress-Lighting
- [#ProgressLightingMoments](https://www.instagram.com/ProgressLightingMoments)

See Yourself Here

Every home and every family has a story that's all their own. In this issue, we introduce you to the many ways Progress Lighting can bring that story to life.



PROGRESS LIGHTING

701 Millennium Boulevard
Greenville, SC 29607

www.progresslighting.com

