



CAPTARENT LED ILLUMINATED MIRROR

The **Captarent** LED illuminated mirror provides a clean, architecturally pleasing solution for illuminating the vanity that is ideal for multi-family, hospitality, assisted living and residential applications. The indirect, backlit solution delivers soft illumination that is well-suited for facial rendering.

FOR MORE INFORMATION, VISIT
[PROGRESSCOMMERCIAL.COM](https://www.progresscommercial.com)

- ✦ Perimeter etched panels are indirectly backlit to provide soft illumination for rendering facial features.
- ✓ Mirror edges have a brushed, radius treatment for consistency in appearance.
- 📏 Available in four sizes and in three different light color temperatures.
- ADA All models are ADA compliant and simple to install.
- 📄 The housing comes with a standard antimicrobial paint finish to inhibit the growth of microbes.
- ⤴ Standard 0-10V dimming.

CAPTARENT LED ILLUMINATED MIRROR



Construction: One-piece 18ga. steel housing and powder coated brackets. 0.25" thick mirror with etched windows for backlighting. White, powder coat paint with an antimicrobial additive standard. LEDs mounted around perimeter of housing to provide indirect backlighting for enhanced uniformity.

Installation/Mounting: Surface mounted housing with four mounting points. Mirror brackets allow hanging attachment of housing. Safety screws provided to lock the mirror in place. Perimeter gasket between the housing and mirror ensures soft contact and prevents damage to mirror.

Electrical: Universal voltage, 120-277V, 50/60 Hz. 0-10V dimming standard.



Listing: cCSAus label for Damp Locations. ADA compliant. 5 Year limited warranty.

PERFORMANCE

Model #	3500K			INPUT CURRENT	
	Lumens	Wattage	LPW	120V	277V
2543	1140	25	46.7	0.205 A	0.088 A
3143	1650	36	45.7	0.304 A	0.131 A
3743	1690	36	47	0.302 A	0.130 A

DIMENSIONS

	MODEL #		
	2543	3143	3743
H1	43.0" (1092.2mm)	43.0" (1092.2mm)	43.0" (1092.2mm)
H2	34.3" (992.0mm)	34.3" (992.0mm)	34.3" (992.0mm)
W1	24.7" (627.4mm)	31.0" (787.4mm)	37.0" (939.8mm)
W2	16.0" (406.4mm)	22.3" (566.4mm)	28.3" (718.8mm)
A	1.8" (45.7mm)	1.8" (45.7mm)	1.8" (45.7mm)
B	2.5" (50.8mm)	2.5" (50.8mm)	2.5" (50.8mm)
C	40.1" (1018.5mm)	40.1" (1018.5mm)	40.1" (1018.5mm)
D	21.8" (553.7mm)	28.1" (713.7mm)	34.1" (916.9mm)
E	5.0" (127.0mm)	8.0" (203.2mm)	8.0" (203.2mm)
F	13.0" (330.2mm)	13.0" (330.2mm)	13.0" (330.2mm)



CATALOG NUMBER

EXAMPLE: PCIM1-3143-830-U-TR

PCIM1		-		-		-		U		-	
BASE	CAPACITY	CRI	COLOR TEMP	INPUT	OPTIONS						
PCIM1 Captarent Illuminated Mirror	2543 25" x 43" (nom.) 3143 31" x 43" (nom.) 3743 37" x 43" (nom.)	8 >80 9 >90 ¹	30 3000K 35 3500K 40 4000K	U Universal (120-277V)	TR Tamper-resistant hardware						

¹90 CRI - Only available with 30 CCT option