


DRAWING NO.

10036839

CATALOG NUMBER	ITEM NUMBER	L	CATALOG NUMBER	ITEM NUMBER	L
BE8N	10036706	8.00 [203]	BE34N	26000562	34.00 [864]
BE9N	10036707	9.00 [229]	BE36N	000266	36.00 [914]
BE10N	25021476	10.00 [254]	BE37N	10035936	37.00 [940]
BE12N	33265Y	12.00 [305]	BE38N	25016213	38.00 [965]
BE12D50N	332817	12.50 [318]	BE40N	001231	40.00 [1016]
BE13N	25004562	13.00 [330]	BE48N	001169	48.00 [1219]
BE14N	10036697	14.00 [356]	BE60N	10036708	60.00 [1524]
BE14D50N	25004643	14.50 [368]	BE72N	25021277	72.00 [1829]
BE15N	332838	15.00 [381]	BE120N	33206U	120.00 [3048]
BE16N	25014671	16.00 [406]	BE144N	332754	144.00 [3658]
BE18N	33292C	18.00 [457]	BE168N	50090125	168.00 [4267]
BE21N	10036700	21.00 [533]	BE216N	25021276	216.00 [5486]
BE22N	10036701	22.00 [559]	BE240N	10036709	240.00 [6096]
BE24N	33278M	24.00 [610]	BE360N	10036710	360.00 [9144]
BE26N	25016591	26.00 [660]	BE600N	10036711	600.00 [15240]
BE28N	001482	28.00 [711]	BE1200N	10036712	1200.00 [30480]
BE29N	10035937	29.00 [737]	BE2040N	25015157	2040.00 [51816]
BE30N	50099275	30.00 [762]			
BE32N	10022586	32.00 [813]			

REV.	DATE	DESCRIPTION	ECO	BY	C'K'D.
E	2/21/2019	TABLE UPDATION	50913	JL	BE



NOTES:

- APPROXIMATE AMP RATING: 340 INDOOR, 405 OUTDOOR
THIS RATING MAY VARY WITH AMBIENT CONDITIONS,
ORIENTATION OF THE BRAID AND OTHER SERVICE CONDITIONS.
- DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST
MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.
- 3) CAN BE ORDERED WITH PLATED FERRULES BY ADDING A SUFFIX AS SHOWN BELOW:

"SV" - FOR SILVER PLATING
 "TN" - FOR TIN PLATING
 "W" - FOR HOT TIN DIPPED

- 4) CAN BE ORDERED WITH UNDRILLED FERRULES BY ADDING SUFFIX "U".

- 5) ALL SIZES ARE LISTED TO UL 467 GROUNDING & BONDING EQUIPMENT STANDARDS.

- 6) ALL SIZES ARE LISTED TO CSA 22.2 NO.41 GROUNDING & BONDING EQUIPMENT STANDARDS.

- 7) BRAID SIZES MAY BE DESIGNATED BY SUFFIXES REPRESENTING VARIATIONS IN LENGTH,
QUANTITY & SIZE OF MOUNTING HOLES, PAD SIZE AND FINISH. (REF. NOTES 5) 6)

TO ORDER BURNDY PRODUCTS CALL 1-800-346-4175
 MANCHESTER, NH 03109, USA
 FOR PRODUCT INFO = <http://www.fciconnect.com>

BRAID

ITEM NO: (TABLE)

CAT NO: BE--N (TABLE)

SCALE: NTS

DRAWN BY: D.BOISVERT 01/05/04

CHECKER: J.MICHAUD 12/16/03

DSN APPVL: J.MICHAUD 12/16/03

MFG APPVL: ---

QC APPVL: J.BRODEUR 12/17/03

MKT APPVL: D.HAMILTON 12/16/03

PROD FAM: ---

PROJECT #: ---

DOCUMENT TYPE: Sales

REL LEVEL: AutoCAD

DRAWING NO

10036839

REV

E

SHEET 1 OF 1

TO ORDER BURNDY® PRODUCTS CALL
 UNITED STATES:
 1-800-346-4175 (LONDONDERRY, NH)
 CANADA:
 1-800-361-6975 (QUEBEC)
 1-800-387-6487 (ALL OTHER PROVINCES)
 FOR PRODUCT INFO: <http://www.burndy.com>