



CATALOG NO.	ITEM NUMBER	L
BE6G42	10039940	6.00 [152]
BE16G42	10038717	16.00 [406]
BE21G42	10039941	21.00 [533]
BE22D50G42	10039942	22.50 [572]
BE37D50G42	10068513	37.50 [953]

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
D	02/10/2012	REDRAW SALES DRAWING	26760	BSB	MA



NOTES:

1. APPROXIMATE AMP RATING: 340A INDOOR, 405A OUTDOOR. THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID, AND OTHER SERVICE CONDITIONS.
2. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.
3. ALL SIZES ARE LISTED TO UL 467 GROUNDING & BONDING EQUIPMENT STANDARDS.
4. ALL SIZES ARE LISTED TO CSA 22.2 NO.41 GROUNDING & BONDING EQUIPMENT STANDARDS.

TO ORDER BURNDY PRODUCTS CALL		BRAID	
UNITED STATES		ITEM NO: SEE TABLE	
1-800-346-4175 (LONDONDERRY, NH)		CAT. NO: BE--G42 (SEE TABLE)	
CANADA:		DRAWN BY: E.MARTIN 2/10/2012	
1-800-361-6975 (QUEBEC)		CHECKER: E.MARTIN 2/11/2012	
1-800-387-6487 (ALL OTHER PROVINCES)		DSN APRVL: E.MARTIN 2/11/2012	
FOR PRODUCT INFO: http://www.burndy.com		MFG APRVL: [Signature]	
		QA APRVL: C. ACKERMAN 2/24/2012	
		MKT APRVL: K. ROBICHEAU 2/13/2012	
		PROD FAM: [Signature]	
		DRAWING NO: 10039944	
		REV: D	
		SHEET 1 OF 1	