


CATALOG NUMBER	ITEM NUMBER	COPPER CONDUCTOR	DIMENSIONS IN/mm					
			O.D. ±.003	B MIN.	C ±.08	L ±.12	T REF.	NO.OF CRIMPS
YGHHA31NTN	10070180	350 kcmil (.629-.710)	1.168 [30]	2.03 [52]	1.62 [41]	4.08 [104]	.26 [7]	4
YGHHA31NTNNP	10045300							

REV	DATE	DESCRIPTION	ECO	BY	CH'K.
C	04/25/2018	NEW CATALOG ADDED	43152	RM	RG



**NOTES:**

1. MATERIAL: COPPER TUBING.
2. FINISH: ELECTRO TIN PLATED.
3. NO PENETROX™ "E"
4. DIMENSIONS IN BRACKETS [ ] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.

TO ORDER BURNDY PRODUCTS CALL		GROUNDING TERMINAL	
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: SEE TABLE	
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: SEE TABLE	
FOR PRODUCT INFO: <a href="http://www.burndy.com">http://www.burndy.com</a>		DRAWN BY: R. BOISVERT 01/04/2006	
		CHECKER: P. LAPONIUS 01/04/2006	
		DSN APRVL: J. MICHAUD 01/03/2006	
		MFG APRVL: --	
		QA APRVL: J. BRODEUD 12/22/2005	
		MKT APRVL: P. THERRIEN 12/27/2005	
		PROD FAM: CM&R COMPRESSION	
		DRAWING NO	
		10064665	
		REV	
		C	
		SHEET 1 OF 1	