


REV	DATE	DESCRIPTION	ECO	BY	C.H.K.
C	2017-11-07 00:00:00 EST	FORMAT CHANGE	47995	JP	MB



NOTES:

1. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED, AND ARE FOR REFERENCE ONLY.

2. APPROXIMATE AMP RATING: 700 INDOOR, 840 OUTDOOR
THIS MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID AND OTHER SERVICE CONDITIONS.

3 ALL SIZES LISTED TO UL 467 GROUNDING & BONDING EQUIPMENT STANDARDS.

TO ORDER BURNDY® PRODUCTS CALL UNITED STATES 1-800-346-4175 (LONDONDERRY, NH) CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES) FOR PRODUCT INFO: http://www.burndy.com		BRAID	
		ITEM NO: 10088744	CAT. NO: CB3E79G3TN
DRAWN BY: R. BOISVERT 06/13/08		CHECKER: J. PARKER 06/16/08	
DSN APPVL: J. PARKER 06/12/08		MFG APPVL: L. LEAVITT 06/12/08	
QA APPVL: J. BRODEUR 06/12/08		MKT APPVL: P. THERRIEN 06/12/08	
PROD FAM: --	SCALE: 1:1	DRAWING NO	REV
PROJECT #: --	SIZE	10089442	C
DOCUMENT TYPE: Sales	D	SHEET 1 OF 1	
REL LEVEL: Released			



REV: PEG200