


REV	DATE	DESCRIPTION	ECO	BY	C'HK.
C	2017-11-07 00:00:00 EST	FORMAT CHANGE	47995	JP	MB



NOTES:

1. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED, AND ARE FOR REFERENCE ONLY.
2. APPROXIMATE AMP RATING: 2000 A.
THIS MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID, AND OTHER SERVICE CONDITIONS.

TO ORDER BURNDY [®] PRODUCTS CALL		BRAID	
UNITED STATES: 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: 10088706	
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: CB24G72G2TN	
FOR PRODUCT INFO: http://www.burndy.com		DRAWN BY: R. BOISVERT 07/21/08	
		CHECKER: J. PARKER 07/21/08	
		DSN APPVL: J. PARKER 06/30/08	
		MFG APPVL: L. LEAVITT 06/25/08	
		QA APPVL: J. BRODEUR 07/16/08	
		MKT APPVL: P. THERRIEN 06/24/08	
		SCALE: 1:4	
		PROJ #: --	DRAWING NO
		SIZE	REV
		10089447	C
		DOCUMENT TYPE: Sales	
		REL LEVEL: Released	SHEET 1 OF 1

REV: PE0200

