

DRAWING NO.
10092722

4


3

2

1

ITEM NUMBER	CATALOG NUMBER	L
332901	BE18G97TN	18.00 [457]
332902	BE24G97TN	24.00 [607]
10110755	BE16G97TN	16.00 [406]

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
D	2017-11-07 09:36:00 EST	FORMAT CHANGE	47995	JP	MB



NOTES:
1. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED, AND ARE FOR REFERENCE ONLY.

2. APPROXIMATE AMP RATING: 340 INDOOR, 405 OUTDOOR
THIS MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID AND OTHER SERVICE CONDITIONS.

3 'UL' SYMBOL FOR INTERNAL SPECIFICATION L4219, LOCATION AND SIZE TO BE DETERMINED BY MANUFACTURING.

4 'CSA' SYMBOL PER INTERNAL SPECIFICATION L4591, LOCATION AND SIZE TO BE DETERMINED BY MANUFACTURING.

TO ORDER BURNDY® PRODUCTS CALL
UNITED STATES:
1-800-346-4175 (LONDONDERRY, NH)
CANADA:
1-800-361-6975 (QUEBEC)
1-800-387-6487 (ALL OTHER PROVINCES)
FOR PRODUCT INFO: <http://www.burndy.com>

BRAID	
ITEM NO:	(SEE TABLE)
CAT. NO:	(SEE TABLE)
DRAWN BY:	R. BOISVERT 10/27/08
CHECKER:	J. PARKER 10/28/08
DSN APPVL:	J. PARKER 09/30/08
MFG APPVL:	L. LEAVITT 09/23/08
QA APPVL:	J. BRODEUR 09/23/08
MKT APPVL:	P. THERRIEN 09/29/08
PROD FAM:	--
PROJECT #:	--
DOCUMENT TYPE:	Sales
REL LEVEL:	In Work
SCALE:	3:4
DRAWING NO	10092722
REV	D
SHEET 1 OF 1	

4

3

2

1

REV: PE0200

D

D

C

C

B

B

A

A