



- NOTES:  
 1. ALL DIMENSIONS ARE IN INCHES AND [MILLIMETERS]  
 2. BOX VOLUME: 30.3 IN<sup>3</sup> [496.5 CM<sup>3</sup>]  
 3. UL LISTED

KNOCKOUTS	
TRADE SIZE	LOCATION
1/2" KO	1- ON THE BOTTOM
3/4" TKO	4- ON THE BOTTOM, 2-ON EACH SIDE, 2 -ON EACH SIDE OF THE SPACER

LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
SPACER	STEEL	GALVANIZED
SIDES	STEEL	GALVANIZED
FASTENERS	STEEL	GALVANIZED

SYMBOL	REVISION DESCRIPTION	APP	DATE
	INITIAL RELEASE	RMV	01/10/17

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE: **4" SQ. 2-1/8" DEEP WELDED BOX**

TOLERANCE UNLESS OTHERWISE SPECIFIED  
 .XX DECIMAL ±.015  
 .XXX DECIMAL ±.005  
 ANGLE ±2°

**RACO**  
 South Bend, Indiana

DRAWN BY: RMV  
 APP. BY: N.S.  
 DATE: 01/10/17

SCALE: 1:2