



LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
SPACER	STEEL	GALVANIZED
SIDES	STEEL	GALVANIZED
BASE PLATE	STEEL	GALVANIZED
FAR SIDE SUPPORT	STEEL	GALVANIZED
FASTENERS	STEEL	GALVANIZED

- NOTES:**
- ALL DIMENSIONS ARE IN INCHES AND [MILLIMETERS]
  - BOX VOLUME: 113.3 IN<sup>3</sup> [1856.6 CM<sup>3</sup>]
  - FAR SIDE (WALL) SUPPORT INCLUDED. ADJUSTABLE FOR STEEL AND WOOD STUDS
  - 3 GREEN #10-32 GROUND STUDS INCLUDED
  - ACCEPTS #981 PARTITION, SOLD SEPARATELY
  - ACCEPTS 4" SINGLE GANG AND DOUBLE GANG MUD RINGS, NOT INCLUDED
  - AFTER REMOVING PORTION OF COVER, ACCEPTS 3-GANG DEVICE COVERS #792 (5/8" DRYWALL), #793 (3/4" DRYWALL), AND #794 (1-1/4" DRYWALL)
  - cULus LISTED

KNOCKOUTS		
TRADE SIZE	LOCATION	QTY.
(1/2"-3/4") TKO®	A,B,C,D,E	2
(3/4"-1") TKO®	A,C	1
(3/4"-1") TKO®	E	2
(1"-1 1/4") TKO®	B,D	1
(1"-1 1/4") TKO®	E	2
1", 1-1/4", 1-1/2", 2" COMBINATION KO	A,C	1

SYMBOL	INITIAL RELEASE	REVISION DESCRIPTION	DATE
	RMV		07-31-17
	APP		

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE: **DATA BOX 4 11/16" x 7 7/8" LONG x 3 1/4" DEEP**

TOLERANCE UNLESS OTHERWISE SPECIFIED  
.XX DECIMAL ±.015  
.XXX DECIMAL ±.005  
ANGLE ±2°

**RACO**  
South Bend, Indiana

DRAWN BY: RMV  
APP. BY: N.S.  
DATE: 07-31-17

SCALE: 1:3