



LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
SPACER	STEEL	GALVANIZED
SIDE	STEEL	GALVANIZED
FASTENERS	STEEL	GALVANIZED

265 CUS

	INITIAL RELEASE	J.R.	06/19/2015
SYM.	REVISION DESCRIPTION	APP	DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE:
**4-11/16" SQUARE WELDED BOX
 2-1/8" DEEP WITH RAISED
 GROUND**

DIMENSION SHEET FOR CAT. NO.
265, 8265, 8265SP

KNOCKOUTS		
TRADE SIZE	LOCATION	QTY.
1/2"	A	1
(1/2"-3/4") TKO®	A	3
1/2"	B, C, D, E	1
3/4"	B, C, D, E	1

- NOTES:
- ALL DIMENSIONS ARE IN INCHES AND [MILLIMETERS]
 - BOX VOLUME: 42 IN³ [688.2 CM³]
 - ACCEPTS ALL 4-11/16" COVERS, 707RAC & 709 PARTITIONS, ALL SOLD SEPARATELY
 - UL LISTED

TOLERANCE UNLESS OTHERWISE SPECIFIED

.XX DECIMAL ±.015
 .XXX DECIMAL ±.005
 ANGLE ±2°

RACO
 South Bend, Indiana

DRAWN BY:	J.R.	SCALE:
APP. BY:	N.S.	1:3
DATE:	06/19/2015	

SIZE:
A