


CATALOG NO.	ITEM NO.	CONDUCTOR		INSULATION COLOR	INSULATION TYPE	B	C	L	W
		WIRE SIZE	METRIC SIZE						
PTV18	30014752	22 AWG - 18 AWG	.34 MM <sup>2</sup> - .75 MM <sup>2</sup>	RED	MOLDED VINYL	.189 [5]	.414 [11]	.795 [20]	.074 [2]
PTV14	30014753	16 AWG - 14 AWG	1.50 MM <sup>2</sup>	BLUE	MOLDED VINYL	.189 [5]	.414 [11]	.795 [20]	.074 [2]
PTV10	30014754	12 AWG - 10 AWG	4.00 MM <sup>2</sup>	YELLOW	MOLDED VINYL	.268 [7]	.504 [13]	.969 [25]	.110 [3]

REV.	DATE	DESCRIPTION	ECO	BY	C'H'K.
D	2020-07-27 13:30:00 EDT	METRIC WIRE SIZE ADDED IN TABLE	53947	SS	YR



PTV18

PTV14

PTV10

NOTES:

- DIMENSIONS IN BRACKETS [ ] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETERS UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.
- CONNECTORS ARE TIN PLATED COPPER WITH VINYL INSULATION SLEEVE.

TO ORDER BURNDY® PRODUCTS CALL  
 UNITED STATES:  
 1-800-346-4175 (LONDONDERRY, NH)  
 CANADA:  
 1-800-361-6975 (QUEBEC)  
 1-800-387-6487 (ALL OTHER PROVINCES)  
 FOR PRODUCT INFO: <http://www.burndy.com>

PIN TERMINALS	
ITEM NO:	SEE TABLE
CAT. NO:	PTV-- (SEE TABLE)
DRAWN BY:	R. BOISVERT 06/24/11
CHECKER:	K. BOUTIN 04/06/11
DSN APPVL:	K. BOUTIN 04/06/11
MFG APPVL:	--
QA APPVL:	J. BRODEUR 04/06/11
MKT APPVL:	R. CAVANAUGH 04/11/11
PROD FAM:	CM&R COMPRESSION
PROJECT #:	--
DOCUMENT TYPE:	Sales
REL LEVEL:	Released



REV: PE0200