

DRAWING NO.
30015666

4


3

2

1

CATALOG NUMBER	ITEM NUMBER	L
B2D7	332107	7.00 [178]
B2D8D62	332130	8.62 [219]
B2D10	33215T	10.00 [254]
B2D12	332215	12.00 [305]
B2D14	33215V	14.00 [356]
B2D16	50084092	16.00 [406]
B2D18	33270P	18.00 [457]
B2D23U	332072	23.00 [584]
B2D24	33256J	24.00 [607]
B2D25	1760	25.00 [635]
B2D30	332519	30.00 [762]
B2D36TN	33204U	36.00 [914]
B2D80	2116	80.00 [2032]

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
B	06/22/2017 21:00:00 PM	FOCUS REQUEST FPN1706053	47013	CV	MB



NOTES:

- APPROXIMATE AMP RATING: 380 INDOOR, 455 OUTDOOR
THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID AND OTHER SERVICE CONDITIONS.
- DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.

3 CAN BE ORDERED WITH PLATED FERRULES BY ADDING SUFFIX AS SHOWN BELOW:
 "NK" - FOR NICKEL PLATING
 "SV" - FOR SILVER PLATING
 "TN" - FOR TIN PLATING
 "W" - FOR HOT TIN DIPPED

4 CAN BE ORDERED WITH UNDRILLED FERRULES BY ADDING SUFFIX "U".

5 ALL SIZES ARE LISTED TO UL 467 GROUNDING & BONDING EQUIPMENT STANDARDS.

6 ALL SIZES ARE LISTED TO CSA C22.2 NO.41 GROUNDING & BONDING EQUIPMENT STANDARDS.

7 BRAID SIZES MAY BE DESIGNATED BY SUFFIXES REPRESENTING VARIATIONS IN LENGTH, QUANTITY & SIZE OF MOUNTING HOLES, PAD SIZE AND FINISH. (REF. NOTES 5 6)

TO ORDER BURNDY® PRODUCTS CALL
 UNITED STATES:
 1-800-346-4175 (LONDONDERRY, NH)
 CANADA:
 1-800-361-6975 (QUEBEC)
 1-800-387-6487 (ALL OTHER PROVINCES)
 FOR PRODUCT INFO: <http://www.burndy.com>

BRAID	
ITEM NO:	SEE TABLE
CAT. NO:	B2D-- (TABLE)
DRAWN BY:	B.SURESH BABU 05/18/11
CHECKER:	E.MARTIN 06/15/2011
DSN APPVL:	A.PINEDA 06/23/2011
MFG APPVL:	G.ORDONEZ 06/23/2011
QA APPVL:	--
MKT APPVL:	P.THERRIEN 06/15/2011
PROD FAM:	--
PROJECT #:	FPN1706053
DOCUMENT TYPE:	Sales
REL LEVEL:	Released



SCALE:	DRAWING NO	REV
1:1	30015666	B
SHEET 1 OF 1		

4

3

2

1

REV: PE0200