


REV	DATE	DESCRIPTION	ECO	BY	C'HK.
A	03/27/2012	DRAWING RELEASED	27110	BSB	MA



NOTES:

1. APPROXIMATE AMP RATING: 530A INDOOR, 635A OUTDOOR. THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID, AND OTHER SERVICE CONDITIONS.

2. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.

3 ALL SIZES ARE LISTED TO UL 467 GROUNDING & BONDING EQUIPMENT STANDARDS.

4 SUFFIX "TN" DENOTES TIN PLATED FERRULES.

TO ORDER BURNDY® PRODUCTS CALL		BRAID	
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: 30026484	
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: B2E15G127TN	
FOR PRODUCT INFO: http://www.burndy.com		DRAWN BY: E.MARTIN 03-12-2012	
		CHECKER: E.MARTIN 03-27-2012	
		DSN APRVL: E.MARTIN 03-27-2012	
		MFG APRVL: L.LEAVITT 03-27-2012	
		QA APRVL: C.KOWALCZYK 03-27-2012	
		MKT APRVL:	
		PROD FAM: CM&R MECHANICAL	
		DRAWING NO	
		30026485	
		REV	
		A	
		SHEET 1 OF 1	