


ITEM NO.	CATALOG NO.	LENGTH (L)
50001429	BB024L5D13G56TN	5.13 [130]
50004628	BB024L72G56TN	72 [1829]

REV	DATE	DESCRIPTION	ECO	BY	CHK.
A	07/10/2012	CREATE PRODUCTION DRAWING	28081	EM	RC



NOTES:

- APPROXIMATE AMP RATING: 93A INDOOR. THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID, AND OTHER SERVICE CONDITIONS.
- DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.

$\triangleleft 3$ SUFFIX "TN" DENOTES TIN PLATED FERRULES.

TO ORDER BURNDY PRODUCTS CALL		BRAID	
UNITED STATES		ITEM NO: SEE TABLE	
1-800-346-4175 (LONDONDERRY, NH)		CAT. NO: BB024L--G56TN $\triangleleft 3$	
CANADA:		DRAWN BY: E.MARTIN 04/23/2012	
1-800-361-6975 (QUEBEC)		CHECKER: R.CRUIZ 07/25/2012	
1-800-387-6487 (ALL OTHER PROVINCES)		DSN APRVL: E.MARTIN 07/24/2012	
FOR PRODUCT INFO: http://www.burndy.com		MFG APRVL: --	
		QA APRVL: J.MEDINA 07/25/2012	
		MKT APRVL: K.ROBICHEAU 07/25/2012	
PROD FAM: MECHANICAL GROUNDING	DRAWING NO	REV	
PROJECT #: --	SIZE	50001430	A
DOCUMENT TYPE: SALES	B	SHEET 1 OF 1	
REL LEVEL: Released			