







CATALOG NUMBER	MATERIAL	MIN. TENSILE STRENGTH (LBS)	BUNDLE DIA.	FEATURE	PACKAGE	COLOR	W	L
CT50137EPRC	NYLON 6/6 STANDARD	50 LBS	1.38 [35]	1 EXTENDED PAWL RELEASABLE	100	NATURAL	.291 [7]	5.50 [140]
CT50137EPRC0	NYLON 6/6 STANDARD	50 LBS	1.38 [35]	1 EXTENDED PAWL RELEASABLE	100	UV BLACK ¹		
CT50137RC	NYLON 6/6 STANDARD	50 LBS	1.38 [35]	2 RELEASABLE TIE	100	NATURAL	.18 [5]	6.50 [165]
CT50137RC0	NYLON 6/6 STANDARD	50 LBS	1.38 [35]	2 RELEASABLE TIE	100	UV BLACK ¹		

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
A	06/30/2012	CREATE SALES DRAWING	27681	BD	MB



2 FEATURE: RELEASABLE TIE



1 FEATURE: EXTENDED PAWL RELEASABLE


NOTES:

- DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED AND ARE FOR REFERENCE ONLY.
- COLOR UV BLACK¹ IS NYLON 6/6 UV STABILIZED; UV BLACK² IS NYLON 6/6 CARBON UV STABILIZED.

TO ORDER BURNDY® PRODUCTS CALL		UNIRAP™	
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: N/A	
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: SEE TABLE	
FOR PRODUCT INFO: http://www.burndy.com		DRAWN BY: B.DURAICHAMY 6/21/2012	
		CHECKER: A.MONTMINY 8/23/2012	
		DSN APRVL: A.MONTMINY 8/23/2012	
		MFG APRVL: --	
		QA APRVL: C.KOWALCZYK 8/24/2012	
		MKT APRVL: R.CAVANAUGH 8/22/2012	
		PROD FAM: --	
		PROJECT #: --	
		SIZE	
		DRAWING NO	
		50004604	
		REV	
		A	
		SHEET 1 OF 5	

CATALOG NUMBER	MATERIAL	MIN. TENSILE STRENGTH (LBS)	BUNDLE DIA.	FEATURE	PACKAGE	COLOR	W	L
CT50175C	NYLON 6/6 STANDARD	50 LBS	1.75 [44]	--	100	NATURAL	.18 [5]	8.00 [203]
CT50175C0	NYLON 6/6 STANDARD	50 LBS	1.75 [44]	--	100	UV BLACK ¹		
CT50175C00	NYLON 6/6 STANDARD	50 LBS	1.75 [44]	--	100	UV BLACK ²		
CT50175C02	NYLON 6/6 STANDARD	50 LBS	1.75 [44]	--	100	RED		
CT50175C1	NYLON 6/6 STANDARD	50 LBS	1.75 [44]	--	100	BROWN		
CT50175C10	NYLON 6/6 STANDARD	50 LBS	1.75 [44]	--	100	WHITE		
CT50175C11	NYLON 6/6 STANDARD	50 LBS	1.75 [44]	--	100	TELCO GRAY		
CT50175C2	NYLON 6/6 STANDARD	50 LBS	1.75 [44]	--	100	RED		
CT50175C3	NYLON 6/6 STANDARD	50 LBS	1.75 [44]	--	100	ORANGE		
CT50175C4	NYLON 6/6 STANDARD	50 LBS	1.75 [44]	--	100	YELLOW		
CT50175C5	NYLON 6/6 STANDARD	50 LBS	1.75 [44]	--	100	GREEN		
CT50175C6	NYLON 6/6 STANDARD	50 LBS	1.75 [44]	--	100	BLUE		
CT50175C7	NYLON 6/6 STANDARD	50 LBS	1.75 [44]	--	100	PURPLE		
CT50175C8	NYLON 6/6 STANDARD	50 LBS	1.75 [44]	--	100	GRAY		
CT50175ID2L	NYLON 6/6 STANDARD	50 LBS	1.75 [44]	5 DOUBLE HEAD ID	50	NATURAL		
CT50175ID3L	NYLON 6/6 STANDARD	50 LBS	1.75 [44]	6 TRIPLE HEAD ID	50	NATURAL		
CT50175IDC	NYLON 6/6 STANDARD	50 LBS	1.75 [44]	4 SINGLE HEAD ID	100	NATURAL		
CT50175IDC4	NYLON 6/6 STANDARD	50 LBS	1.75 [44]	4 SINGLE HEAD ID	100	YELLOW		
CT50175M	NYLON 6/6 STANDARD	50 LBS	1.75 [44]	--	1000	NATURAL		
CT50175M0	NYLON 6/6 STANDARD	50 LBS	1.75 [44]	--	1000	UV BLACK ¹		
CT50175M00	NYLON 6/6 STANDARD	50 LBS	1.75 [44]	--	1000	UV BLACK ²		
CT50175M02	NYLON 6/6 STANDARD	50 LBS	1.75 [44]	--	1000	RED		
CT50175MH10C	NYLON 6/6 STANDARD	50 LBS	1.75 [44]	3 MOUNTING HOLE #10	100	NATURAL		
CT50175MH10C0	NYLON 6/6 STANDARD	50 LBS	1.75 [44]	3 MOUNTING HOLE #10	100	UV BLACK ¹		
CT50175MH10M	NYLON 6/6 STANDARD	50 LBS	1.75 [44]	3 MOUNTING HOLE #10	1000	NATURAL		
CT50175MH10M0	NYLON 6/6 STANDARD	50 LBS	1.75 [44]	3 MOUNTING HOLE #10	1000	UV BLACK ¹		
CT50175PMC	NYLON 6/6 STANDARD	50 LBS	1.75 [44]	PUSH MOUNT TIE	100	NATURAL		
CT50175PMC0	NYLON 6/6 STANDARD	50 LBS	1.75 [44]	PUSH MOUNT TIE	100	UV BLACK ¹		
CT50175PMM	NYLON 6/6 STANDARD	50 LBS	1.75 [44]	PUSH MOUNT TIE	1000	NATURAL		
CT50175PMM0	NYLON 6/6 STANDARD	50 LBS	1.75 [44]	PUSH MOUNT TIE	1000	UV BLACK ¹		




REV	DATE	DESCRIPTION	ECO	BY	CH'K.
A	06/30/2012	CREATE SALES DRAWING	27681	BD	MB



TO ORDER BURNDY® PRODUCTS CALL		UNIRAP™	
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: N/A	
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: SEE TABLE	
FOR PRODUCT INFO: http://www.burndy.com		DRAWN BY: B.DURAICHAMY 6/21/2012 CHECKER: A.MONTMINY 8/23/2012 DSN APRVL: A.MONTMINY 8/23/2012 MFG APRVL: -- QA APRVL: C.KOWALCZYK 8/24/2012 MKT APRVL: R.CAVANAUGH 8/22/2012	
PROJECT #: --	SIZE: D	DRAWING NO: 50004604	
REL LEVEL: Released		SHEET 2 OF 5	

CATALOG NUMBER	MATERIAL	MIN. TENSILE STRENGTH (LBS)	BUNDLE DIA.	FEATURE	PACKAGE	COLOR	W	L
CT50250EPRC	NYLON 6/6 STANDARD	50 LBS	2.50 [64]	1 EXTENDED PAWL RELEASE	100	NATURAL	.291	9.80
CT50250EPRC0	NYLON 6/6 STANDARD	50 LBS	2.50 [64]	1 EXTENDED PAWL RELEASE	100	UV BLACK ¹	[7]	[249]

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
A	06/30/2012	CREATE SALES DRAWING	27681	BD	MB

TO ORDER BURNDY® PRODUCTS CALL		UNIRAP™															
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: N/A															
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: SEE TABLE															
FOR PRODUCT INFO: http://www.burndy.com		<table border="1"> <tr> <td>DRAWN BY: B.DURAICHAMY</td> <td>6/21/2012</td> <td rowspan="5"></td> </tr> <tr> <td>CHECKER: A.MONTMINY</td> <td>8/23/2012</td> </tr> <tr> <td>DSN APRVL: A.MONTMINY</td> <td>8/23/2012</td> </tr> <tr> <td>MFG APRVL: --</td> <td>--</td> </tr> <tr> <td>QA APRVL: C.KOWALCZYK</td> <td>8/24/2012</td> </tr> <tr> <td>MKT APRVL: R.CAVANAUGH</td> <td>8/22/2012</td> <td></td> </tr> </table>		DRAWN BY: B.DURAICHAMY	6/21/2012		CHECKER: A.MONTMINY	8/23/2012	DSN APRVL: A.MONTMINY	8/23/2012	MFG APRVL: --	--	QA APRVL: C.KOWALCZYK	8/24/2012	MKT APRVL: R.CAVANAUGH	8/22/2012	
DRAWN BY: B.DURAICHAMY	6/21/2012																
CHECKER: A.MONTMINY	8/23/2012																
DSN APRVL: A.MONTMINY	8/23/2012																
MFG APRVL: --	--																
QA APRVL: C.KOWALCZYK	8/24/2012																
MKT APRVL: R.CAVANAUGH	8/22/2012																
PROJECT #: --	SIZE	DRAWING NO	REV														
DOCUMENT TYPE: SALES	D	50004604	A														
REL LEVEL: Released		SHEET 3 OF 5															

CATALOG NUMBER	MATERIAL	MIN. TENSILE STRENGTH (LBS)	BUNDLE DIA.	FEATURE	PACKAGE	COLOR	W	L
CT50300C	NYLON 6/6 STANDARD	50 LBS	3.00 [76]	--	100	NATURAL	.18 [5]	11.75 [298]
CT50300C0	NYLON 6/6 STANDARD	50 LBS	3.00 [76]	--	100	UV BLACK ¹		
CT50300C00	NYLON 6/6 STANDARD	50 LBS	3.00 [76]	--	100	UV BLACK ²		
CT50300C1	NYLON 6/6 STANDARD	50 LBS	3.00 [76]	--	100	BROWN		
CT50300C10	NYLON 6/6 STANDARD	50 LBS	3.00 [76]	--	100	WHITE		
CT50300C11	NYLON 6/6 STANDARD	50 LBS	3.00 [76]	--	100	TELCO GRAY		
CT50300C2	NYLON 6/6 STANDARD	50 LBS	3.00 [76]	--	100	RED		
CT50300C3	NYLON 6/6 STANDARD	50 LBS	3.00 [76]	--	100	ORANGE		
CT50300C4	NYLON 6/6 STANDARD	50 LBS	3.00 [76]	--	100	YELLOW		
CT50300C5	NYLON 6/6 STANDARD	50 LBS	3.00 [76]	--	100	GREEN		
CT50300C6	NYLON 6/6 STANDARD	50 LBS	3.00 [76]	--	100	BLUE		
CT50300C7	NYLON 6/6 STANDARD	50 LBS	3.00 [76]	--	100	PURPLE		
CT50300C8	NYLON 6/6 STANDARD	50 LBS	3.00 [76]	--	100	GRAY		
CT50300M	NYLON 6/6 STANDARD	50 LBS	3.00 [76]	--	1000	NATURAL		
CT50300M0	NYLON 6/6 STANDARD	50 LBS	3.00 [76]	--	1000	UV BLACK ¹		
CT50300M00	NYLON 6/6 STANDARD	50 LBS	3.00 [76]	--	1000	UV BLACK ²		
CT50300PSM	NYLON 6/6 STANDARD	50 LBS	3.00 [76]	POSITIVE STOP	1000	NATURAL		

REV	DATE	DESCRIPTION	ECO	BY	CHK.
A	06/30/2012	CREATE SALES DRAWING	27681	BD	MB

TO ORDER BURNDY® PRODUCTS CALL		UNIRAP™																	
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: N/A																	
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: SEE TABLE																	
FOR PRODUCT INFO: http://www.burndy.com		<table border="1"> <tr> <td>DRAWN BY: B.DURAICHAMY</td> <td>6/21/2012</td> </tr> <tr> <td>CHECKER: A.MONTMINY</td> <td>8/23/2012</td> </tr> <tr> <td>DSN APRVL: A.MONTMINY</td> <td>8/23/2012</td> </tr> <tr> <td>MFG APRVL: --</td> <td>--</td> </tr> <tr> <td>QA APRVL: C.KOWALCZYK</td> <td>8/24/2012</td> </tr> <tr> <td>MKT APRVL: R.CAVANAUGH</td> <td>8/22/2012</td> </tr> </table>		DRAWN BY: B.DURAICHAMY	6/21/2012	CHECKER: A.MONTMINY	8/23/2012	DSN APRVL: A.MONTMINY	8/23/2012	MFG APRVL: --	--	QA APRVL: C.KOWALCZYK	8/24/2012	MKT APRVL: R.CAVANAUGH	8/22/2012				
DRAWN BY: B.DURAICHAMY	6/21/2012																		
CHECKER: A.MONTMINY	8/23/2012																		
DSN APRVL: A.MONTMINY	8/23/2012																		
MFG APRVL: --	--																		
QA APRVL: C.KOWALCZYK	8/24/2012																		
MKT APRVL: R.CAVANAUGH	8/22/2012																		
		<table border="1"> <tr> <td>PROJECT #:</td> <td>--</td> <td>DRAWING NO</td> <td>50004604</td> </tr> <tr> <td>DOCUMENT TYPE:</td> <td>SALES</td> <td>REV</td> <td>A</td> </tr> <tr> <td>REL LEVEL:</td> <td>Released</td> <td>SIZE</td> <td>D</td> </tr> <tr> <td colspan="2"></td> <td colspan="2">SHEET 4 OF 5</td> </tr> </table>		PROJECT #:	--	DRAWING NO	50004604	DOCUMENT TYPE:	SALES	REV	A	REL LEVEL:	Released	SIZE	D			SHEET 4 OF 5	
PROJECT #:	--	DRAWING NO	50004604																
DOCUMENT TYPE:	SALES	REV	A																
REL LEVEL:	Released	SIZE	D																
		SHEET 4 OF 5																	

CATALOG NUMBER	MATERIAL	MIN. TENSILE STRENGTH (LBS)	BUNDLE DIA.	FEATURE	PACKAGE	COLOR	W	L	REV	DATE	DESCRIPTION	ECO	BY	C'H'K.			
									A	06/30/2012	CREATE SALES DRAWING	27681	BD	MB			
CT50400C	NYLON 6/6 STANDARD	50 LBS	4.00 [102]	--	100	NATURAL	.18 [5]	15.50 [394]									
CT50400C0	NYLON 6/6 STANDARD	50 LBS	4.00 [102]	--	100	UV BLACK ¹											
CT50400C00	NYLON 6/6 STANDARD	50 LBS	4.00 [102]	--	100	UV BLACK ²											
CT50400C02	NYLON 6/6 STANDARD	50 LBS	4.00 [102]	--	100	RED											
CT50400C1	NYLON 6/6 STANDARD	50 LBS	4.00 [102]	--	100	BROWN											
CT50400C10	NYLON 6/6 STANDARD	50 LBS	4.00 [102]	--	100	WHITE											
CT50400C11	NYLON 6/6 STANDARD	50 LBS	4.00 [102]	--	100	TELCO GRAY											
CT50400C2	NYLON 6/6 STANDARD	50 LBS	4.00 [102]	--	100	RED											
CT50400C3	NYLON 6/6 STANDARD	50 LBS	4.00 [102]	--	100	ORANGE											
CT50400C4	NYLON 6/6 STANDARD	50 LBS	4.00 [102]	--	100	YELLOW											
CT50400C5	NYLON 6/6 STANDARD	50 LBS	4.00 [102]	--	100	GREEN											
CT50400C6	NYLON 6/6 STANDARD	50 LBS	4.00 [102]	--	100	BLUE											
CT50400C7	NYLON 6/6 STANDARD	50 LBS	4.00 [102]	--	100	PURPLE											
CT50400C8	NYLON 6/6 STANDARD	50 LBS	4.00 [102]	--	100	GRAY											
CT50400IDC	NYLON 6/6 STANDARD	50 LBS	4.00 [102]	4 SINGLE HEAD ID	100	NATURAL											
CT50400M	NYLON 6/6 STANDARD	50 LBS	4.00 [102]	--	1000	NATURAL											
CT50400M0	NYLON 6/6 STANDARD	50 LBS	4.00 [102]	--	1000	UV BLACK ¹											
CT50400M00	NYLON 6/6 STANDARD	50 LBS	4.00 [102]	--	1000	UV BLACK ²											
CT50400M02	NYLON 6/6 STANDARD	50 LBS	4.00 [102]	--	1000	RED											
CT50400MH10C	NYLON 6/6 STANDARD	50 LBS	4.00 [102]	3 MOUNTING HOLE #10	100	NATURAL											
CT50400MH10C0	NYLON 6/6 STANDARD	50 LBS	4.00 [102]	3 MOUNTING HOLE #10	100	UV BLACK ¹											
CT50400MH10M	NYLON 6/6 STANDARD	50 LBS	4.00 [102]	3 MOUNTING HOLE #10	1000	NATURAL											
CT50400MH10M0	NYLON 6/6 STANDARD	50 LBS	4.00 [102]	3 MOUNTING HOLE #10	1000	UV BLACK ¹											
CT50400RC	NYLON 6/6 STANDARD	50 LBS	4.00 [102]	2 RELEASABLE TIE	100	NATURAL											
CT50400RC0	NYLON 6/6 STANDARD	50 LBS	4.00 [102]	2 RELEASABLE TIE	100	UV BLACK ¹											
									TO ORDER BURNDY® PRODUCTS CALL UNITED STATES 1-800-346-4175 (LONDONDERRY, NH) CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES) FOR PRODUCT INFO: http://www.burndy.com			UNIRAP™ ITEM NO: N/A CAT. NO: SEE TABLE DRAWN BY: B.DURAICHAMY 6/21/2012 CHECKER: A.MONTMINY 8/23/2012 DSN APRVL: A.MONTMINY 8/23/2012 MFG APRVL: -- QA APRVL: C.KOWALCZYK 8/24/2012 MKT APRVL: R.CAVANAUGH 8/22/2012 PROD FAM: -- PROJECT #: -- DOCUMENT TYPE: SALES REL LEVEL: Released			DRAWING NO 50004604		REV A