


ITEM NUMBER	CATALOG NO.	Length (L)
50007332	BB048L6T14	6.00 [152]
50007333	BB048L9T14	9.00 [229]
50053111	BB048L12T14	12.00 [305]
50053112	BB048L18T14	18.00 [457]
50053113	BB048L24T14	24.00 [610]
50100927	BB048L40T14	40.00 [1016]
50095611	BB048L120T14	120.00 [3048]

REV	DATE	DESCRIPTION	ECO	BY	CHK.
D	06/13/2019	ADDED PART BB048L40T14	51616	JL	BE



NOTES:

- APPROXIMATE AMP RATING: 93 A. THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID, AND OTHER SERVICE CONDITIONS.
- DIMENSIONS IN BRACKETS [ ] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.

TO ORDER BURNDY® PRODUCTS CALL  
 UNITED STATES  
 1-800-346-4175 (LONDONDERRY, NH)  
 CANADA:  
 1-800-361-6975 (QUEBEC)  
 1-800-387-6487 (ALL OTHER PROVINCES)  
 FOR PRODUCT INFO: <http://www.burndy.com>

BRAID		DRAWING NO	REV
ITEM NO: SEE TABLE		50007334	D
CAT. NO: BB048L--T14 (TABLE)			
DRAWN BY: SENTHIL	8/24/2012		
CHECKER: E.MARTIN	8/16/2012		
DSN APRVL: E.MARTIN			
MFG APRVL: L.LEAVITT	8/17/2012		
QA APRVL: C.KOWALCZYK	8/19/2012		
MKT APRVL: K.ROBICHEAU	8/17/2012		
PROD FAM: MECHANICAL GROUNDING	SIZE		
PROJECT #: FPN1906044	B		
DOCUMENT TYPE: SALES			
REL LEVEL: Released			

