



DRAWING NO. 50008621		7
CATALOG NUMBER	ITEM NUMBER	L
BB024L18G18TN	50008619	18.00 [457]
BB024L24G18TN	50008620	24.00 [610]
BB024L14G18TN	50020769	14.00 [356]

REV	DATE	DESCRIPTION	ECO	BY	C.H.K.
B	03/06/2013 00:00:00 AM	ADD PART BB024L14G18TN	30775	PM	MB



- NOTES:
- APPROXIMATE AMP. RATING: 93A. THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF BRAID, AND OTHER SERVICE CONDITIONS.
 - DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.

TO ORDER BURNDY® PRODUCTS CALL		BRAID, FLEXIBLE	
UNITED STATES		ITEM NO:	SEE TABLE
1-800-346-4175 (LONDONDERRY, NH)		CAT. NO:	SEE TABLE
CANADA:		DRAWN BY:	D DHEENA 09/06/12
1-800-387-6487 (ALL OTHER PROVINCES)		CHECKER:	R CRUZ 09/29/12
FOR PRODUCT INFO: http://www.burndy.com		DSN APPVL:	E MARTIN 09/28/12
		MFG APPVL:	-- --
		QA APPVL:	J MEDINA 10/02/12
		MKT APPVL:	K ROBICHEAU 09/28/12
		PROD FAM:	CM&R COMPRESSION
		PROJECT #:	--
		SIZE:	D
		DOCUMENT TYPE:	Sales
		REL LEVEL:	Released
		DRAWING NO:	50008621
		SCALE:	3:2
		REV:	B
		SHEET:	1 OF 1

REV: PEG200