


REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
A	05/13/2013	DRAWING UPDATED AS PER MARKUP	31616	GP	MB



- NOTES:
- APPROXIMATE AMP. RATING: 93A. THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID, AND OTHER SERVICE CONDITIONS.
  - DIMENSIONS IN BRACKETS [ ] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED AND ARE FOR REFERENCE ONLY.
- 3 SUFFIX "TN" DENOTES TINNED COPPER FERRULES.

TO ORDER BURNDY® PRODUCTS CALL		BRAID	
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: 50008706	
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: BB024L38G58TN	
FOR PRODUCT INFO: <a href="http://www.burndy.com">http://www.burndy.com</a>		DRAWN BY: SRAMESH 09/11/2012	
		CHECKER: --	
		DSN APRVL: --	
		MFG APRVL: --	
		QA APRVL: --	
		MKT APRVL: --	
		PROD FAM: MECHANICAL GROUNDING	
		DRAWING NO	
		50008707	
		REV	
		A	
		SHEET 1 OF 1	