




REV	DATE	DESCRIPTION	ECO	BY	CHK.
A	10/29/2012	RELEASE SALES DRAWINGS OF THE AFFECTED ITEMS	29186	MS	MB



NOTES:

1. APPROXIMATE AMP RATING: 190A INDOOR, 225A OUTDOOR. THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID, AND OTHER SERVICE CONDITIONS.

2. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.

3 ALL SIZES ARE LISTED TO UL 467 GROUNDING & BONDING EQUIPMENT STANDARDS.

4 ALL SIZES ARE LISTED TO CSA 22.2 NO.41 GROUNDING & BONDING EQUIPMENT STANDARDS.

TO ORDER BURNDY® PRODUCTS CALL		BRAID	
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: 50009668	
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: BD24G272TN	
FOR PRODUCT INFO: http://www.burndy.com		DRAWN BY: N.D.KANNAN 10/12/2012	
		CHECKER: T.REYNOLDS 11/29/2012	
		DSN APRVL: R.CRUIZ 11/30/2012	
		MFG APRVL: --	
		QA APRVL: J.MEDINA 11/30/2012	
		MKT APRVL: K.ROBICHEAU 11/30/2012	
		PROJ FAM: MECHANICAL GROUNDING	
		DRAWING NO	
		50009670	
		REV	
		A	
		SHEET 1 OF 1	
		REL LEVEL: Released	