




REV	DATE	DESCRIPTION	ECO	BY	C'H.K.
A	02/15/2013	CREATE SALES DRAWINGS FOR BE24G199	30512	GP	MB



NOTES:

1. APPROXIMATE AMP RATING: 340A INDOOR, 405A OUTDOOR. THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID, AND OTHER SERVICE CONDITIONS.
 2. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.
- 3> BRAID LISTED TO UL 467 GROUNDING & BONDING EQUIPMENT STANDARDS.
- 4> BRAID LISTED TO CSA 22.2 NO.41 GROUNDING & BONDING EQUIPMENT STANDARDS.

TO ORDER BURNDY® PRODUCTS CALL		BRAID	
UNITED STATES		ITEM NO: 50019237	
1-800-346-4175 (LONDONDERRY, NH)		CAT. NO: BE24G199	
CANADA:		DRAWN BY: PRASAD G 02/15/2013	
1-800-361-6975 (QUEBEC)		CHECKER: T REYNOLDS 02/19/2013	
1-800-387-6487 (ALL OTHER PROVINCES)		DSN APRVL: T REYNOLDS 02/19/2013	
FOR PRODUCT INFO: http://www.burndy.com		MFG APRVL: L LEAVIT 02/19/2013	
		QA APRVL: T WATTS 02/19/2013	
		MKT APRVL: K ROBICHEAU 02/19/2013	
PROD FAM: MECHANICAL GROUNDING	DRAWING NO	REV	
PROJECT #: --	SIZE	50019239	A
DOCUMENT TYPE: SALES	B	SHEET 1 OF 1	
REL LEVEL: Released			