



BURNDY ITEM NUMBER	BURNDY CATALOG NUMBER	"COATED" FULLY / SEMI	"COATING" MATERIAL	PACKAGE QUANTITY	CARTON QUANTITY	TENSILE STRENGTH LBS / N	BUNDLE DIA. MIN. IN [MM]	BUNDLE DIA. MAX. IN [MM]	LENGTH IN [MM]	WIDTH IN [MM]	MIN. INSTALLATION TEMPERATURE °F / °C	MIN. OPERATING TEMPERATURE °F / °C	MAX. OPERATING TEMPERATURE °F / °C	BAG LENGTH IN [MM]	BAG WIDTH IN [MM]	INSTALLATION TOOL
50017492	CTSS100100FC304C	FULLY	POLYESTER	100	10000	160 / 712	.50 [12.7]	.98 [25]	3.94 [100]	.18 [4.6]	-40 / -40	-40 / -40	239 / 115	6.69 [170]	4.33 [110]	MK9SST (HVY)
50017494	CTSS100200FC304C	FULLY	POLYESTER	100	10000	160 / 712	.50 [12.7]	1.97 [50]	7.87 [200]	.18 [4.6]	-40 / -40	-40 / -40	239 / 115	10.63 [270]	4.33 [110]	MK9SST (HVY)
50017496	CTSS100300FC304C	FULLY	POLYESTER	100	6000	160 / 712	.50 [12.7]	3.00 [76]	11.81 [300]	.18 [4.6]	-40 / -40	-40 / -40	239 / 115	14.57 [370]	4.33 [110]	MK9SST (HVY)
50066987	CTSS100350FC304C	FULLY	POLYESTER	100		160 / 712	.50 [12.7]	8.11 [206]	13.78 [350]	.18 [4.6]	-40 / -40	-40 / -40	239 / 115	16.54 [420]	4.33 [110]	MK9SST (HVY)
50017498	CTSS100400FC304C	FULLY	POLYESTER	100	4000	160 / 712	.50 [12.7]	4.02 [102]	15.75 [400]	.18 [4.6]	-40 / -40	-40 / -40	239 / 115	18.50 [470]	4.33 [110]	MK9SST (HVY)
50017500	CTSS100500FC304C	FULLY	POLYESTER	100	3000	160 / 712	.50 [12.7]	5.04 [128]	19.68 [500]	.18 [4.6]	-40 / -40	-40 / -40	239 / 115	22.44 [570]	4.33 [110]	MK9SST (HVY)
50022382	CTSS100600FC304C	FULLY	POLYESTER	100	3000	160 / 712	.50 [12.7]	6.07 [154]	23.60 [600]	.18 [4.6]	-40 / -40	-40 / -40	239 / 115	34.25 [870]	4.33 [110]	MK9SST (HVY)
50022563	CTSS100800FC304C	FULLY	POLYESTER	100	2000	160 / 712	.50 [12.7]	8.11 [206]	31.50 [800]	.18 [4.6]	-40 / -40	-40 / -40	239 / 115	43.31 [1100]	4.33 [110]	MK9SST (HVY)

FULLY COATED:



PARTIALLY COATED:



NOTES:

1. MATERIAL : STAINLESS STEEL COATED WITH POLYESTER
2. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED AND ARE FOR REFERENCE ONLY.

TO ORDER BURNDY® PRODUCTS CALL		304 STAINLESS STEEL CABLE TIES															
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: SEE TABLE															
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: SEE TABLE															
FOR PRODUCT INFO: http://www.burndy.com		<table border="1"> <tr> <td>DRAWN BY: V.KAMAL</td> <td>02/21/2013</td> <td rowspan="5"></td> </tr> <tr> <td>CHECKER: A.MONTMINY</td> <td>04/18/2013</td> </tr> <tr> <td>DSN APRVL: A.MONTMINY</td> <td>04/18/2013</td> </tr> <tr> <td>MFG APRVL: --</td> <td>--</td> </tr> <tr> <td>QA APRVL: C.KOWALCZYK</td> <td>04/18/2013</td> </tr> <tr> <td>MKT APRVL: J.SYLVIA</td> <td>04/18/2013</td> <td></td> </tr> </table>		DRAWN BY: V.KAMAL	02/21/2013		CHECKER: A.MONTMINY	04/18/2013	DSN APRVL: A.MONTMINY	04/18/2013	MFG APRVL: --	--	QA APRVL: C.KOWALCZYK	04/18/2013	MKT APRVL: J.SYLVIA	04/18/2013	
DRAWN BY: V.KAMAL	02/21/2013																
CHECKER: A.MONTMINY	04/18/2013																
DSN APRVL: A.MONTMINY	04/18/2013																
MFG APRVL: --	--																
QA APRVL: C.KOWALCZYK	04/18/2013																
MKT APRVL: J.SYLVIA	04/18/2013																
REV	DATE	DESCRIPTION	ECO	BY	C'H'K.	DRAWING NO	REV										
G	12/01/2017	CARTON QUANTITIES ADDED TO TABLE	48120	DD	PB	50020256	G										

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
G	12/01/2017	CARTON QUANTITIES ADDED TO TABLE	48120	DD	PB

PROD FAM: --	SIZE	DRAWING NO	REV
PROJECT #: --	B	50020256	G
DOCUMENT TYPE: SALES			
REL LEVEL: Released			

BURNDY ITEM NUMBER	BURNDY CATALOG NUMBER	"COATED" FULLY / SEMI	"COATING" MATERIAL	PACKAGE QUANTITY	CARTON QUANTITY	TENSILE STRENGTH LBS / N	BUNDLE DIA. MIN. IN [MM]	BUNDLE DIA. MAX. IN [MM]	LENGTH IN [MM]	WIDTH IN [MM]	MIN. INSTALLATION TEMPERATURE °F / °C	MIN. OPERATING TEMPERATURE °F / °C	MAX. OPERATING TEMPERATURE °F / °C	BAG LENGTH IN [MM]	BAG WIDTH IN [MM]	INSTALLATION TOOL
50017502	CTSS250200FC304L	FULLY	POLYESTER	50	5000	250 / 1112	.50 [12.7]	1.97 [50]	7.87 [200]	.31 [7.9]	-40 / -40	-40 / -40	239 / 115	10.63 [270]	5.90 [150]	MK9SST (HVY)
50018297	CTSS250200PC304L	SEMI	POLYESTER	50	5000	270 / 1201	.50 [12.7]	1.97 [50]	7.87 [200]	.31 [7.9]	-40 / -40	-40 / -40	239 / 115	10.63 [270]	5.90 [150]	MK9SST (HVY)
50017504	CTSS250300FC304L	FULLY	POLYESTER	50	4000	250 / 1112	.50 [12.7]	3.00 [76]	11.81 [300]	.31 [7.9]	-40 / -40	-40 / -40	239 / 115	14.57 [370]	5.90 [150]	MK9SST (HVY)
50018299	CTSS250300PC304L	SEMI	POLYESTER	50	4000	270 / 1201	.50 [12.7]	3.00 [76]	11.81 [300]	.31 [7.9]	-40 / -40	-40 / -40	239 / 115	14.57 [370]	5.90 [150]	MK9SST (HVY)
50017506	CTSS250400FC304L	FULLY	POLYESTER	50	2500	250 / 1112	.50 [12.7]	4.02 [102]	15.75 [400]	.31 [7.9]	-40 / -40	-40 / -40	239 / 115	18.50 [470]	5.90 [150]	MK9SST (HVY)
50018301	CTSS250400PC304L	SEMI	POLYESTER	50	2500	270 / 1201	.50 [12.7]	4.02 [102]	15.75 [400]	.31 [7.9]	-40 / -40	-40 / -40	239 / 115	18.50 [470]	5.90 [150]	MK9SST (HVY)
50017508	CTSS250500FC304L	FULLY	POLYESTER	50	2000	250 / 1112	.50 [12.7]	5.04 [128]	19.68 [500]	.31 [7.9]	-40 / -40	-40 / -40	239 / 115	22.44 [570]	4.72 [120]	MK9SST (HVY)
50018303	CTSS250500PC304L	SEMI	POLYESTER	50	2000	270 / 1201	.50 [12.7]	5.04 [128]	19.68 [500]	.31 [7.9]	-40 / -40	-40 / -40	239 / 115	22.44 [570]	4.72 [120]	MK9SST (HVY)
50017510	CTSS250600FC304L	FULLY	POLYESTER	50	2000	250 / 1112	.50 [12.7]	6.06 [154]	23.62 [600]	.31 [7.9]	-40 / -40	-40 / -40	239 / 115	26.38 [670]	4.72 [120]	MK9SST (HVY)
50018305	CTSS250600PC304L	SEMI	POLYESTER	50	2000	270 / 1201	.50 [12.7]	6.06 [154]	23.62 [600]	.31 [7.9]	-40 / -40	-40 / -40	239 / 115	26.38 [670]	4.72 [120]	MK9SST (HVY)
50017512	CTSS250700FC304L	FULLY	POLYESTER	50	1500	250 / 1112	.50 [12.7]	7.09 [180]	27.56 [700]	.31 [7.9]	-40 / -40	-40 / -40	239 / 115	30.31 [770]	4.72 [120]	MK9SST (HVY)
50018307	CTSS250700PC304L	SEMI	POLYESTER	50	1500	270 / 1201	.50 [12.7]	7.09 [180]	27.56 [700]	.31 [7.9]	-40 / -40	-40 / -40	239 / 115	30.31 [770]	4.72 [120]	MK9SST (HVY)
50017514	CTSS250800FC304L	FULLY	POLYESTER	50	1000	250 / 1112	.50 [12.7]	8.11 [206]	39.37 [1000]	.31 [7.9]	-40 / -40	-40 / -40	239 / 115	42.13 [1070]	4.72 [120]	MK9SST (HVY)
50018309	CTSS250800PC304L	SEMI	POLYESTER	50	1000	270 / 1201	.50 [12.7]	8.11 [206]	39.37 [1000]	.31 [7.9]	-40 / -40	-40 / -40	239 / 115	42.13 [1070]	4.72 [120]	MK9SST (HVY)

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
G	12/01/2017	CARTON QUANTITIES ADDED TO TABLE	48120	DD	PB

TO ORDER BURNDY® PRODUCTS CALL		304 STAINLESS STEEL CABLE TIES	
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: SEE TABLE	
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: SEE TABLE	
FOR PRODUCT INFO: http://www.burndy.com		DRAWN BY: V.KAMAL 02/21/2013	
		CHECKER: A.MONTMINY 04/18/2013	
		DSN APRVL: A.MONTMINY 04/18/2013	
		MFG APRVL: --	
		QA APRVL: C.KOWALCZYK 04/18/2013	
		MKT APRVL: J.SYLVIA 04/18/2013	
		PROD FAM: --	DRAWING NO
		PROJECT #: --	50020256
		DOCUMENT TYPE: SALES	REV
		REL LEVEL: Released	G
		SIZE: B	SHEET 2 OF 4


BURNDY ITEM NUMBER	BURNDY CATALOG NUMBER	"COATED" FULLY / SEMI	"COATING" MATERIAL	PACKAGE QUANTITY	CARTON QUANTITY	TENSILE STRENGTH LBS / N	BUNDLE DIA. MIN. IN [MM]	BUNDLE DIA. MAX. IN [MM]	LENGTH IN [MM]	WIDTH IN [MM]	MIN. INSTALLATION TEMPERATURE °F / °C	MIN. OPERATING TEMPERATURE °F / °C	MAX. OPERATING TEMPERATURE °F / °C	BAG LENGTH IN [MM]	BAG WIDTH IN [MM]	INSTALLATION TOOL
50017516	CTSS450200FC304L	FULLY	POLYESTER	50	2500	450 / 2002	1.00 [25.4]	1.97 [50]	7.87 [200]	.50 [12.7]	-40 / -40	-40 / -40	239 / 115	11.81 [300]	5.90 [150]	MK9SST (HVY)
50018311	CTSS450200PC304L	SEMI	POLYESTER	50	2500	450 / 2002	1.00 [25.4]	1.97 [50]	7.87 [200]	.50 [12.7]	-40 / -40	-40 / -40	239 / 115	11.81 [300]	5.90 [150]	MK9SST (HVY)
50017518	CTSS450300FC304L	FULLY	POLYESTER	50	2000	450 / 2002	1.00 [25.4]	3.00 [76]	11.81 [300]	.50 [12.7]	-40 / -40	-40 / -40	239 / 115	15.75 [400]	5.90 [150]	MK9SST (HVY)
50018313	CTSS450300PC304L	SEMI	POLYESTER	50	2000	450 / 2002	1.00 [25.4]	3.00 [76]	11.81 [300]	.50 [12.7]	-40 / -40	-40 / -40	239 / 115	15.75 [400]	5.90 [150]	MK9SST (HVY)
50017520	CTSS450400FC304L	FULLY	POLYESTER	50	1200	450 / 2002	1.00 [25.4]	4.02 [102]	15.75 [400]	.50 [12.7]	-40 / -40	-40 / -40	239 / 115	19.68 [500]	5.12 [130]	MK9SST (HVY)
50018315	CTSS450400PC304L	SEMI	POLYESTER	50	1200	450 / 2002	1.00 [25.4]	4.02 [102]	15.75 [400]	.50 [12.7]	-40 / -40	-40 / -40	239 / 115	19.68 [500]	5.12 [130]	MK9SST (HVY)
50017522	CTSS450500FC304L	FULLY	POLYESTER	50	1000	450 / 2002	1.00 [25.4]	5.04 [128]	19.68 [500]	.50 [12.7]	-40 / -40	-40 / -40	239 / 115	23.62 [600]	5.12 [130]	MK9SST (HVY)
50018317	CTSS450500PC304L	SEMI	POLYESTER	50	1000	450 / 2002	1.00 [25.4]	5.04 [128]	19.68 [500]	.50 [12.7]	-40 / -40	-40 / -40	239 / 115	23.62 [600]	5.12 [130]	MK9SST (HVY)
50017524	CTSS450600FC304L	FULLY	POLYESTER	50	1000	450 / 2002	1.00 [25.4]	6.06 [154]	23.62 [600]	.50 [12.7]	-40 / -40	-40 / -40	239 / 115	27.56 [700]	5.12 [130]	MK9SST (HVY)
50018319	CTSS450600PC304L	SEMI	POLYESTER	50	1000	450 / 2002	1.00 [25.4]	6.06 [154]	23.62 [600]	.50 [12.7]	-40 / -40	-40 / -40	239 / 115	27.56 [700]	5.12 [130]	MK9SST (HVY)
50017526	CTSS450700FC304L	FULLY	POLYESTER	50	700	450 / 2002	1.00 [25.4]	7.09 [180]	27.56 [700]	.50 [12.7]	-40 / -40	-40 / -40	239 / 115	31.49 [800]	5.12 [130]	MK9SST (HVY)
50018321	CTSS450700PC304L	SEMI	POLYESTER	50	700	450 / 2002	1.00 [25.4]	7.09 [180]	27.56 [700]	.50 [12.7]	-40 / -40	-40 / -40	239 / 115	31.49 [800]	5.12 [130]	MK9SST (HVY)
50017528	CTSS450800FC304L	FULLY	POLYESTER	50	500	450 / 2002	1.00 [25.4]	8.11 [206]	39.37 [1000]	.50 [12.7]	-40 / -40	-40 / -40	239 / 115	43.31 [1100]	4.33 [110]	MK9SST (HVY)
50018323	CTSS450800PC304L	SEMI	POLYESTER	50	500	450 / 2002	1.00 [25.4]	8.11 [206]	39.37 [1000]	.50 [12.7]	-40 / -40	-40 / -40	239 / 115	43.31 [1100]	4.33 [110]	MK9SST (HVY)

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
G	12/01/2017	CARTON QUANTITIES ADDED TO TABLE	48120	DD	PB

TO ORDER BURNDY® PRODUCTS CALL		304 STAINLESS STEEL CABLE TIES	
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: SEE TABLE	
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: SEE TABLE	
FOR PRODUCT INFO: http://www.burndy.com		DRAWN BY: V.KAMAL 02/21/2013	
		CHECKER: A.MONTMINY 04/18/2013	
		DSN APRVL: A.MONTMINY 04/18/2013	
		MFG APRVL: --	
		QA APRVL: C.KOWALCZYK 04/18/2013	
		MKT APRVL: J.SYLVIA 04/18/2013	
		PROD FAM: --	
		DRAWING NO	
		50020256	
		REV	
		G	
		DOCUMENT TYPE: SALES	
		REL LEVEL: Released	
		SHEET 3 OF 4	

BURNDY ITEM NUMBER	BURNDY CATALOG NUMBER	"COATED" FULLY / SEMI	"COATING" MATERIAL	PACKAGE QUANTITY	CARTON QUANTITY	TENSILE STRENGTH LBS / N	BUNDLE DIA. MIN. IN [MM]	BUNDLE DIA. MAX. IN [MM]	LENGTH IN [MM]	WIDTH IN [MM]	MIN. INSTALLATION TEMPERATURE °F / °C	MIN. OPERATING TEMPERATURE °F / °C	MAX. OPERATING TEMPERATURE °F / °C	BAG LENGTH IN [MM]	BAG WIDTH IN [MM]	INSTALLATION TOOL
50017530	CTSS675200FC304Q	FULLY	POLYESTER	25	1200	675 / 3003	1.00 [25.4]	1.97 [50]	7.87 [200]	.62 [15.9]	-40 / -40	-40 / -40	239 / 115	11.81 [300]	7.48 [190]	CTTSS900
50018325	CTSS675200PC304Q	SEMI	POLYESTER	25	1200	675 / 3003	1.00 [25.4]	1.97 [50]	7.87 [200]	.62 [15.9]	-40 / -40	-40 / -40	239 / 115	11.81 [300]	7.48 [190]	CTTSS900
50017532	CTSS675300FC304Q	FULLY	POLYESTER	25	1000	675 / 3003	1.00 [25.4]	3.00 [76]	11.81 [300]	.62 [15.9]	-40 / -40	-40 / -40	239 / 115	15.75 [400]	5.12 [130]	CTTSS900
50018327	CTSS675300PC304Q	SEMI	POLYESTER	25	1000	675 / 3003	1.00 [25.4]	3.00 [76]	11.81 [300]	.62 [15.9]	-40 / -40	-40 / -40	239 / 115	15.75 [400]	5.12 [130]	CTTSS900
50017534	CTSS675400FC304Q	FULLY	POLYESTER	25	800	675 / 3003	1.00 [25.4]	4.02 [102]	15.75 [400]	.62 [15.9]	-40 / -40	-40 / -40	239 / 115	19.68 [500]	5.12 [130]	CTTSS900
50018329	CTSS675400PC304Q	SEMI	POLYESTER	25	800	675 / 3003	1.00 [25.4]	4.02 [102]	15.75 [400]	.62 [15.9]	-40 / -40	-40 / -40	239 / 115	19.68 [500]	5.12 [130]	CTTSS900
50017536	CTSS675500FC304Q	FULLY	POLYESTER	25	600	675 / 3003	1.00 [25.4]	5.04 [128]	19.68 [500]	.62 [15.9]	-40 / -40	-40 / -40	239 / 115	23.62 [600]	5.12 [130]	CTTSS900
50018331	CTSS675500PC304Q	SEMI	POLYESTER	25	600	675 / 3003	1.00 [25.4]	5.04 [128]	19.68 [500]	.62 [15.9]	-40 / -40	-40 / -40	239 / 115	23.62 [600]	5.12 [130]	CTTSS900
50017538	CTSS675600FC304Q	FULLY	POLYESTER	25	500	675 / 3003	1.00 [25.4]	6.06 [154]	23.62 [600]	.62 [15.9]	-40 / -40	-40 / -40	239 / 115	27.56 [700]	5.12 [130]	CTTSS900
50018333	CTSS675600PC304Q	SEMI	POLYESTER	25	500	675 / 3003	1.00 [25.4]	6.06 [154]	23.62 [600]	.62 [15.9]	-40 / -40	-40 / -40	239 / 115	27.56 [700]	5.12 [130]	CTTSS900
50017540	CTSS675700FC304Q	FULLY	POLYESTER	25	400	675 / 3003	1.00 [25.4]	7.09 [180]	27.56 [700]	.62 [15.9]	-40 / -40	-40 / -40	239 / 115	31.49 [800]	4.33 [110]	CTTSS900
50018335	CTSS675700PC304Q	SEMI	POLYESTER	25	400	675 / 3003	1.00 [25.4]	7.09 [180]	27.56 [700]	.62 [15.9]	-40 / -40	-40 / -40	239 / 115	31.49 [800]	4.33 [110]	CTTSS900
50017542	CTSS675800FC304Q	FULLY	POLYESTER	25	300	675 / 3003	1.00 [25.4]	8.11 [206]	39.37 [1000]	.62 [15.9]	-40 / -40	-40 / -40	239 / 115	43.31 [1100]	4.33 [110]	CTTSS900
50018337	CTSS675800PC304Q	SEMI	POLYESTER	25	300	675 / 3003	1.00 [25.4]	8.11 [206]	39.37 [1000]	.62 [15.9]	-40 / -40	-40 / -40	239 / 115	43.31 [1100]	4.33 [110]	CTTSS900

TO ORDER BURNDY® PRODUCTS CALL
 UNITED STATES
 1-800-346-4175 (LONDONDERRY, NH)
 CANADA:
 1-800-361-6975 (QUEBEC)
 1-800-387-6487 (ALL OTHER PROVINCES)
 FOR PRODUCT INFO: <http://www.burndy.com>

304 STAINLESS STEEL CABLE TIES			
ITEM NO: SEE TABLE			
CAT. NO: SEE TABLE			
DRAWN BY: V.KAMAL	02/21/2013		
CHECKER: A.MONTMINY	04/18/2013		
DSN APRVL: A.MONTMINY	04/18/2013		
MFG APRVL: --			
QA APRVL: C.KOWALCZYK	04/18/2013		
MKT APRVL: J.SYLVIA	04/18/2013		
PROD FAM: --		DRAWING NO	REV
PROJECT #: --	SIZE	50020256	G
DOCUMENT TYPE: SALES	B	SHEET 4 OF 4	
REL LEVEL: Released			

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
G	12/01/2017	CARTON QUANTITIES ADDED TO TABLE	48120	DD	PB