



BURNDY ITEM NUMBER	BURNDY CATALOG NUMBER	"COATED" FULLY / SEMI	"COATING" MATERIAL	PACKAGE QUANTITY	CARTON QUANTITY	TENSILE STRENGTH LBS / N	BUNDLE DIA. MIN. IN [MM]	BUNDLE DIA. MAX. IN [MM]	LENGTH IN [MM]	WIDTH IN [MM]	MIN. INSTALLATION TEMPERATURE °F / °C	MIN. OPERATING TEMPERATURE °F / °C	MAX. OPERATING TEMPERATURE °F / °C	BAG LENGTH IN [MM]	BAG WIDTH IN [MM]	INSTALLATION TOOL
50017543	CTSS100100FC316C	FULLY	POLYESTER	100	10000	160 / 712	.50 [12.7]	.98 [25]	3.94 [100]	.18 [4.6]	-40 / -40	-40 / -40	239 / 115	6.69 [170]	4.33 [110]	MK9SST (HVY)
50017545	CTSS100200FC316C	FULLY	POLYESTER	100	10000	160 / 712	.50 [12.7]	1.97 [50]	7.87 [200]	.18 [4.6]	-40 / -40	-40 / -40	239 / 115	10.63 [270]	4.33 [110]	MK9SST (HVY)
50017547	CTSS100300FC316C	FULLY	POLYESTER	100	6000	160 / 712	.50 [12.7]	3.00 [76]	11.81 [300]	.18 [4.6]	-40 / -40	-40 / -40	239 / 115	14.57 [370]	4.33 [110]	MK9SST (HVY)
50017549	CTSS100400FC316C	FULLY	POLYESTER	100	4000	160 / 712	.50 [12.7]	4.02 [102]	15.75 [400]	.18 [4.6]	-40 / -40	-40 / -40	239 / 115	18.50 [470]	4.33 [110]	MK9SST (HVY)
50017551	CTSS100500FC316C	FULLY	POLYESTER	100	3000	160 / 712	.50 [12.7]	5.04 [128]	19.68 [500]	.18 [4.6]	-40 / -40	-40 / -40	239 / 115	22.44 [570]	4.33 [110]	MK9SST (HVY)
50022383	CTSS100600FC316C	FULLY	POLYESTER	100	3000	160 / 712	.50 [12.7]	6.07 [154]	23.60 [600]	.18 [4.6]	-40 / -40	-40 / -40	239 / 115	34.25 [870]	4.33 [110]	MK9SST (HVY)
50022384	CTSS100800FC316C	FULLY	POLYESTER	100	2000	160 / 712	.50 [12.7]	8.11 [206]	31.50 [800]	.18 [4.6]	-40 / -40	-40 / -40	239 / 115	43.31 [1100]	4.33 [110]	MK9SST (HVY)

FULLY COATED:



PARTIALLY COATED:



NOTES:

1. MATERIAL : STAINLESS STEEL COATED WITH POLYESTER
2. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED AND ARE FOR REFERENCE ONLY.

TO ORDER BURNDY® PRODUCTS CALL		316 STAINLESS STEEL CABLE TIES	
UNITED STATES		ITEM NO: SEE TABLE	
1-800-346-4175 (LONDONDERRY, NH)		CAT. NO: SEE TABLE	
CANADA:		DRAWN BY: V.KAMAL 02/21/2013	
1-800-361-6975 (QUEBEC)		CHECKER: A.MONTMINY 04/18/2013	
1-800-387-6487 (ALL OTHER PROVINCES)		DSN APRVL: A.MONTMINY 04/18/2013	
FOR PRODUCT INFO: http://www.burndy.com		MFG APRVL: --	
		QA APRVL: C.KOWALCZYK 04/18/2013	
		MKT APRVL: J.SYLVIA 04/18/2013	
		PROD FAM: --	
		DRAWING NO	
		50020258	
		REV	
		F	

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
F	12/01/2017	CARTON QUANTITIES ADDED TO TABLE	48120	DD	PB


BURNDY ITEM NUMBER	BURNDY CATALOG NUMBER	"COATED" FULLY / SEMI	"COATING" MATERIAL	PACKAGE QUANTITY	CARTON QUANTITY	TENSILE STRENGTH LBS / N	BUNDLE DIA. MIN. IN [MM]	BUNDLE DIA. MAX. IN [MM]	LENGTH IN [MM]	WIDTH IN [MM]	MIN. INSTALLATION TEMPERATURE °F / °C	MIN. OPERATING TEMPERATURE °F / °C	MAX. OPERATING TEMPERATURE °F / °C	BAG LENGTH IN [MM]	BAG WIDTH IN [MM]	INSTALLATION TOOL
50017553	CTSS250200FC316L	FULLY	POLYESTER	50	5000	250 / 1112	.50 [12.7]	1.97 [50]	7.87 [200]	.31 [7.9]	-40 / -40	-40 / -40	239 / 115	10.63 [270]	5.90 [150]	MK9SST (HVY)
50018348	CTSS250200PC316L	SEMI	POLYESTER	50	5000	270 / 1201	.50 [12.7]	1.97 [50]	7.87 [200]	.31 [7.9]	-40 / -40	-40 / -40	239 / 115	10.63 [270]	5.90 [150]	MK9SST (HVY)
50017555	CTSS250300FC316L	FULLY	POLYESTER	50	4000	250 / 1112	.50 [12.7]	3.00 [76]	11.81 [300]	.31 [7.9]	-40 / -40	-40 / -40	239 / 115	14.57 [370]	5.90 [150]	MK9SST (HVY)
50018350	CTSS250300PC316L	SEMI	POLYESTER	50	4000	270 / 1201	.50 [12.7]	3.00 [76]	11.81 [300]	.31 [7.9]	-40 / -40	-40 / -40	239 / 115	14.57 [370]	5.90 [150]	MK9SST (HVY)
50017557	CTSS250400FC316L	FULLY	POLYESTER	50	2500	250 / 1112	.50 [12.7]	4.02 [102]	15.75 [400]	.31 [7.9]	-40 / -40	-40 / -40	239 / 115	18.50 [470]	5.90 [150]	MK9SST (HVY)
50018352	CTSS250400PC316L	SEMI	POLYESTER	50	2500	270 / 1201	.50 [12.7]	4.02 [102]	15.75 [400]	.31 [7.9]	-40 / -40	-40 / -40	239 / 115	18.50 [470]	5.90 [150]	MK9SST (HVY)
50017559	CTSS250500FC316L	FULLY	POLYESTER	50	2000	250 / 1112	.50 [12.7]	5.04 [128]	19.68 [500]	.31 [7.9]	-40 / -40	-40 / -40	239 / 115	22.44 [570]	4.72 [120]	MK9SST (HVY)
50018354	CTSS250500PC316L	SEMI	POLYESTER	50	2000	270 / 1201	.50 [12.7]	5.04 [128]	19.68 [500]	.31 [7.9]	-40 / -40	-40 / -40	239 / 115	22.44 [570]	4.72 [120]	MK9SST (HVY)
50017561	CTSS250600FC316L	FULLY	POLYESTER	50	2000	250 / 1112	.50 [12.7]	6.06 [154]	23.62 [600]	.31 [7.9]	-40 / -40	-40 / -40	239 / 115	26.38 [670]	4.72 [120]	MK9SST (HVY)
50018356	CTSS250600PC316L	SEMI	POLYESTER	50	2000	270 / 1201	.50 [12.7]	6.06 [154]	23.62 [600]	.31 [7.9]	-40 / -40	-40 / -40	239 / 115	26.38 [670]	4.72 [120]	MK9SST (HVY)
50017563	CTSS250700FC316L	FULLY	POLYESTER	50	1500	250 / 1112	.50 [12.7]	7.09 [180]	27.56 [700]	.31 [7.9]	-40 / -40	-40 / -40	239 / 115	30.31 [770]	4.72 [120]	MK9SST (HVY)
50018358	CTSS250700PC316L	SEMI	POLYESTER	50	1500	270 / 1201	.50 [12.7]	7.09 [180]	27.56 [700]	.31 [7.9]	-40 / -40	-40 / -40	239 / 115	30.31 [770]	4.72 [120]	MK9SST (HVY)
50017565	CTSS250800FC316L	FULLY	POLYESTER	50	1000	250 / 1112	.50 [12.7]	8.11 [206]	39.37 [1000]	.31 [7.9]	-40 / -40	-40 / -40	239 / 115	42.13 [1070]	4.72 [120]	MK9SST (HVY)
50018360	CTSS250800PC316L	SEMI	POLYESTER	50	1000	270 / 1201	.50 [12.7]	8.11 [206]	39.37 [1000]	.31 [7.9]	-40 / -40	-40 / -40	239 / 115	42.13 [1070]	4.72 [120]	MK9SST (HVY)

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
F	12/01/2017	CARTON QUANTITIES ADDED TO TABLE	48120	DD	PB

TO ORDER BURNDY® PRODUCTS CALL		316 STAINLESS STEEL CABLE TIES	
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: SEE TABLE	
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: SEE TABLE	
FOR PRODUCT INFO: http://www.burndy.com		DRAWN BY: V.KAMAL 02/21/2013	
		CHECKER: A.MONTMINY 04/18/2013	
		DSN APRVL: A.MONTMINY 04/18/2013	
		MFG APRVL: --	
		QA APRVL: C.KOWALCZYK 04/18/2013	
		MKT APRVL: J.SYLVIA 04/18/2013	
		PROD FAM: --	
		DRAWING NO	
		50020258	
		REV	
		F	
		SHEET 2 OF 4	

BURNDY ITEM NUMBER	BURNDY CATALOG NUMBER	"COATED" FULLY / SEMI	"COATING" MATERIAL	PACKAGE QUANTITY	CARTON QUANTITY	TENSILE STRENGTH LBS / N	BUNDLE DIA. MIN. IN [MM]	BUNDLE DIA. MAX. IN [MM]	LENGTH IN [MM]	WIDTH IN [MM]	MIN. INSTALLATION TEMPERATURE °F / °C	MIN. OPERATING TEMPERATURE °F / °C	MAX. OPERATING TEMPERATURE °F / °C	BAG LENGTH IN [MM]	BAG WIDTH IN [MM]	INSTALLATION TOOL
50017567	CTSS450200FC316L	FULLY	POLYESTER	50	2500	450 / 2002	1.00 [25.4]	1.97 [50]	7.87 [200]	.50 [12.7]	-40 / -40	-40 / -40	239 / 115	11.81 [300]	5.90 [150]	MK9SST (HVY)
50018362	CTSS450200PC316L	SEMI	POLYESTER	50	2500	450 / 2002	1.00 [25.4]	1.97 [50]	7.87 [200]	.50 [12.7]	-40 / -40	-40 / -40	239 / 115	11.81 [300]	5.90 [150]	MK9SST (HVY)
50017569	CTSS450300FC316L	FULLY	POLYESTER	50	2000	450 / 2002	1.00 [25.4]	3.00 [76]	11.81 [300]	.50 [12.7]	-40 / -40	-40 / -40	239 / 115	15.75 [400]	5.90 [150]	MK9SST (HVY)
50018364	CTSS450300PC316L	SEMI	POLYESTER	50	2000	450 / 2002	1.00 [25.4]	3.00 [76]	11.81 [300]	.50 [12.7]	-40 / -40	-40 / -40	239 / 115	15.75 [400]	5.90 [150]	MK9SST (HVY)
50017571	CTSS450400FC316L	FULLY	POLYESTER	50	1200	450 / 2002	1.00 [25.4]	4.02 [102]	15.75 [400]	.50 [12.7]	-40 / -40	-40 / -40	239 / 115	19.68 [500]	5.12 [130]	MK9SST (HVY)
50018366	CTSS450400PC316L	SEMI	POLYESTER	50	1200	450 / 2002	1.00 [25.4]	4.02 [102]	15.75 [400]	.50 [12.7]	-40 / -40	-40 / -40	239 / 115	19.68 [500]	5.12 [130]	MK9SST (HVY)
50017573	CTSS450500FC316L	FULLY	POLYESTER	50	1000	450 / 2002	1.00 [25.4]	5.04 [128]	19.68 [500]	.50 [12.7]	-40 / -40	-40 / -40	239 / 115	23.62 [600]	5.12 [130]	MK9SST (HVY)
50018368	CTSS450500PC316L	SEMI	POLYESTER	50	1000	450 / 2002	1.00 [25.4]	5.04 [128]	19.68 [500]	.50 [12.7]	-40 / -40	-40 / -40	239 / 115	23.62 [600]	5.12 [130]	MK9SST (HVY)
50017575	CTSS450600FC316L	FULLY	POLYESTER	50	1000	450 / 2002	1.00 [25.4]	6.06 [154]	23.62 [600]	.50 [12.7]	-40 / -40	-40 / -40	239 / 115	27.56 [700]	5.12 [130]	MK9SST (HVY)
50018370	CTSS450600PC316L	SEMI	POLYESTER	50	1000	450 / 2002	1.00 [25.4]	6.06 [154]	23.62 [600]	.50 [12.7]	-40 / -40	-40 / -40	239 / 115	27.56 [700]	5.12 [130]	MK9SST (HVY)
50017577	CTSS450700FC316L	FULLY	POLYESTER	50	700	450 / 2002	1.00 [25.4]	7.09 [180]	27.56 [700]	.50 [12.7]	-40 / -40	-40 / -40	239 / 115	31.49 [800]	5.12 [130]	MK9SST (HVY)
50018372	CTSS450700PC316L	SEMI	POLYESTER	50	700	450 / 2002	1.00 [25.4]	7.09 [180]	27.56 [700]	.50 [12.7]	-40 / -40	-40 / -40	239 / 115	31.49 [800]	5.12 [130]	MK9SST (HVY)
50017579	CTSS450800FC316L	FULLY	POLYESTER	50	500	450 / 2002	1.00 [25.4]	8.11 [206]	39.37 [1000]	.50 [12.7]	-40 / -40	-40 / -40	239 / 115	43.31 [1100]	4.33 [110]	MK9SST (HVY)
50018374	CTSS450800PC316L	SEMI	POLYESTER	50	500	450 / 2002	1.00 [25.4]	8.11 [206]	39.37 [1000]	.50 [12.7]	-40 / -40	-40 / -40	239 / 115	43.31 [1100]	4.33 [110]	MK9SST (HVY)

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
F	12/01/2017	CARTON QUANTITIES ADDED TO TABLE	48120	DD	PB

TO ORDER BURNDY® PRODUCTS CALL		316 STAINLESS STEEL CABLE TIES													
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: SEE TABLE													
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: SEE TABLE													
FOR PRODUCT INFO: http://www.burndy.com		<table border="1"> <tr><td>DRAWN BY: V.KAMAL</td><td>02/21/2013</td></tr> <tr><td>CHECKER: A.MONTMINY</td><td>04/18/2013</td></tr> <tr><td>DSN APRVL: A.MONTMINY</td><td>04/18/2013</td></tr> <tr><td>MFG APRVL: --</td><td></td></tr> <tr><td>QA APRVL: C.KOWALCZYK</td><td>04/18/2013</td></tr> <tr><td>MKT APRVL: J.SYLVIA</td><td>04/18/2013</td></tr> </table>		DRAWN BY: V.KAMAL	02/21/2013	CHECKER: A.MONTMINY	04/18/2013	DSN APRVL: A.MONTMINY	04/18/2013	MFG APRVL: --		QA APRVL: C.KOWALCZYK	04/18/2013	MKT APRVL: J.SYLVIA	04/18/2013
DRAWN BY: V.KAMAL	02/21/2013														
CHECKER: A.MONTMINY	04/18/2013														
DSN APRVL: A.MONTMINY	04/18/2013														
MFG APRVL: --															
QA APRVL: C.KOWALCZYK	04/18/2013														
MKT APRVL: J.SYLVIA	04/18/2013														
<table border="1"> <tr><td>PROD FAM: --</td><td>DRAWING NO</td><td>REV</td></tr> <tr><td>PROJECT #: --</td><td>SIZE</td><td>50020258</td></tr> <tr><td>DOCUMENT TYPE: SALES</td><td>B</td><td>F</td></tr> <tr><td>REL LEVEL: Released</td><td></td><td>SHEET 3 OF 4</td></tr> </table>		PROD FAM: --	DRAWING NO	REV	PROJECT #: --	SIZE	50020258	DOCUMENT TYPE: SALES	B	F	REL LEVEL: Released		SHEET 3 OF 4		
PROD FAM: --	DRAWING NO	REV													
PROJECT #: --	SIZE	50020258													
DOCUMENT TYPE: SALES	B	F													
REL LEVEL: Released		SHEET 3 OF 4													

BURNDY ITEM NUMBER	BURNDY CATALOG NUMBER	"COATED" FULLY / SEMI	"COATING" MATERIAL	PACKAGE QUANTITY	CARTON QUANTITY	TENSILE STRENGTH LBS / N	BUNDLE DIA. MIN. IN [MM]	BUNDLE DIA. MAX. IN [MM]	LENGTH IN [MM]	WIDTH IN [MM]	MIN. INSTALLATION TEMPERATURE °F / °C	MIN. OPERATING TEMPERATURE °F / °C	MAX. OPERATING TEMPERATURE °F / °C	BAG LENGTH IN [MM]	BAG WIDTH IN [MM]	INSTALLATION TOOL
50017581	CTSS675200FC316Q	FULLY	POLYESTER	25	1200	675 / 3003	1.00 [25.4]	1.97 [50]	7.87 [200]	.62 [15.9]	-40 / -40	-40 / -40	239 / 115	11.81 [300]	7.48 [190]	CTTSS900
50018376	CTSS675200PC316Q	SEMI	POLYESTER	25	1200	675 / 3003	1.00 [25.4]	1.97 [50]	7.87 [200]	.62 [15.9]	-40 / -40	-40 / -40	239 / 115	11.81 [300]	7.48 [190]	CTTSS900
50017583	CTSS675300FC316Q	FULLY	POLYESTER	25	1000	675 / 3003	1.00 [25.4]	3.00 [76]	11.81 [300]	.62 [15.9]	-40 / -40	-40 / -40	239 / 115	15.75 [400]	5.12 [130]	CTTSS900
50018378	CTSS675300PC316Q	SEMI	POLYESTER	25	1000	675 / 3003	1.00 [25.4]	3.00 [76]	11.81 [300]	.62 [15.9]	-40 / -40	-40 / -40	239 / 115	15.75 [400]	5.12 [130]	CTTSS900
50017585	CTSS675400FC316Q	FULLY	POLYESTER	25	800	675 / 3003	1.00 [25.4]	4.02 [102]	15.75 [400]	.62 [15.9]	-40 / -40	-40 / -40	239 / 115	19.68 [500]	5.12 [130]	CTTSS900
50018380	CTSS675400PC316Q	SEMI	POLYESTER	25	800	675 / 3003	1.00 [25.4]	4.02 [102]	15.75 [400]	.62 [15.9]	-40 / -40	-40 / -40	239 / 115	19.68 [500]	5.12 [130]	CTTSS900
50017587	CTSS675500FC316Q	FULLY	POLYESTER	25	600	675 / 3003	1.00 [25.4]	5.04 [128]	19.68 [500]	.62 [15.9]	-40 / -40	-40 / -40	239 / 115	23.62 [600]	5.12 [130]	CTTSS900
50018382	CTSS675500PC316Q	SEMI	POLYESTER	25	600	675 / 3003	1.00 [25.4]	5.04 [128]	19.68 [500]	.62 [15.9]	-40 / -40	-40 / -40	239 / 115	23.62 [600]	5.12 [130]	CTTSS900
50017589	CTSS675600FC316Q	FULLY	POLYESTER	25	500	675 / 3003	1.00 [25.4]	6.06 [154]	23.62 [600]	.62 [15.9]	-40 / -40	-40 / -40	239 / 115	27.56 [700]	5.12 [130]	CTTSS900
50018384	CTSS675600PC316Q	SEMI	POLYESTER	25	500	675 / 3003	1.00 [25.4]	6.06 [154]	23.62 [600]	.62 [15.9]	-40 / -40	-40 / -40	239 / 115	27.56 [700]	5.12 [130]	CTTSS900
50017591	CTSS675700FC316Q	FULLY	POLYESTER	25	400	675 / 3003	1.00 [25.4]	7.09 [180]	27.56 [700]	.62 [15.9]	-40 / -40	-40 / -40	239 / 115	31.49 [800]	4.33 [110]	CTTSS900
50018386	CTSS675700PC316Q	SEMI	POLYESTER	25	400	675 / 3003	1.00 [25.4]	7.09 [180]	27.56 [700]	.62 [15.9]	-40 / -40	-40 / -40	239 / 115	31.49 [800]	4.33 [110]	CTTSS900
50017593	CTSS675800FC316Q	FULLY	POLYESTER	25	300	675 / 3003	1.00 [25.4]	8.11 [206]	39.37 [1000]	.62 [15.9]	-40 / -40	-40 / -40	239 / 115	43.31 [1100]	4.33 [110]	CTTSS900
50018388	CTSS675800PC316Q	SEMI	POLYESTER	25	300	675 / 3003	1.00 [25.4]	8.11 [206]	39.37 [1000]	.62 [15.9]	-40 / -40	-40 / -40	239 / 115	43.31 [1100]	4.33 [110]	CTTSS900

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
F	12/01/2017	CARTON QUANTITIES ADDED TO TABLE	48120	DD	PB

TO ORDER BURNDY® PRODUCTS CALL		316 STAINLESS STEEL CABLE TIES													
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: SEE TABLE													
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: SEE TABLE													
FOR PRODUCT INFO: http://www.burndy.com		<table border="1"> <tr><td>DRAWN BY: V.KAMAL</td><td>02/21/2013</td></tr> <tr><td>CHECKER: A.MONTMINY</td><td>04/18/2013</td></tr> <tr><td>DSN APRVL: A.MONTMINY</td><td>04/18/2013</td></tr> <tr><td>MFG APRVL: --</td><td></td></tr> <tr><td>QA APRVL: C.KOWALCZYK</td><td>04/18/2013</td></tr> <tr><td>MKT APRVL: J.SYLVIA</td><td>04/18/2013</td></tr> </table>		DRAWN BY: V.KAMAL	02/21/2013	CHECKER: A.MONTMINY	04/18/2013	DSN APRVL: A.MONTMINY	04/18/2013	MFG APRVL: --		QA APRVL: C.KOWALCZYK	04/18/2013	MKT APRVL: J.SYLVIA	04/18/2013
DRAWN BY: V.KAMAL	02/21/2013														
CHECKER: A.MONTMINY	04/18/2013														
DSN APRVL: A.MONTMINY	04/18/2013														
MFG APRVL: --															
QA APRVL: C.KOWALCZYK	04/18/2013														
MKT APRVL: J.SYLVIA	04/18/2013														
PROJ #: --		DRAWING NO													
DOCUMENT TYPE: SALES		50020258													
REL LEVEL: Released		SHEET 4 OF 4													
		REV													
		F													

