


REV	DATE	DESCRIPTION	ECO	BY	C'H.K.
A	04/16/2013	NEW DRAWING RELEASE	31287	DD	MB



NOTES:

- APPROXIMATE AMP RATING: 3000A. THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID, AND OTHER SERVICE CONDITIONS.
- DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.

TO ORDER BURNDY® PRODUCTS CALL		BRAID	
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: 33209V	
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: B33G18G25	
FOR PRODUCT INFO: http://www.burndy.com		DRAWN BY: D DHEENA 4/16/2013	
		CHECKER: E MARTIN 4/16/2013	
		DSN APRVL: E MARTIN 4/16/2013	
		MFG APRVL: []	
		QA APRVL: C ACKERMAN 4/26/2013	
		MKT APRVL: K ROBICHEAU 4/16/2013	
PROD FAM:	DRAWING NO:	REV:	
PROJECT #:	SIZE:	50023055	A
DOCUMENT TYPE: SALES	B	SHEET 1 OF 1	
REL LEVEL: Released			