




REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
A	05/16/2013	CREATE SALES DOCUMENT FOR ACSS EHV SPLICES (CAT.# BYNS-RHT)	31713	SP	PW



ACSS NON EHV LOOP SPLICES															
ACSS CONDUCTOR				CATALOG NUMBER	ITEM NUMBER	L In [mm]	OD In [mm]	INSTALLATION TOOLING							
NAME	Kcmil	STRANDS	DIAMETER					BURNDY HYPRESS & DIE SET		T&B DIES FOR 21940 TYPE PRESS	BURNDY DIES TO FIT ACA PRESS			ACA DIES	
								DIE INDEX	Y60B		ACA PRESS 150B	ACA PRESS H2H	ACA PRESS 100A	60 TON PRESS	100 TON PRESS
LINNET	336.4	26/7	0.720 [18]	BYNS32RHT	30010984	18.48 [469]	1.19 [30]	717	L717	96	M717	H717	MH717	--	--
ORIOLE	336.4	30/7	0.741 [19]												
IBIS	397.5	26/7	0.783 [20]	BYNS34RHT	30010986	18.56 [471]	1.30 [33]	719	L719	106	M719	H719	MH719	6020AH	10020AH
FLICKER	477	24/7	0.846 [21]	BYNS36RHT	10099343	19.08 [485]	1.41 [36]	720	L720	115	M720	H720	MH720	--	--
HAWK	477	26/7	0.858 [22]												
PARAKEET	556.5	24/7	0.914 [23]	BYNS39RHT	30010989	19.64 [499]	1.50 [38]	722	L722	125	M722	H722	MH722	6024AH	10024AH
DOVE	556.5	26/7	0.927 [24]												
PEACOCK	605	24/7	0.953 [24]	BYNS43RHT	30008800	19.74 [501]	1.61 [41]	724	L724	140	M724	H724	MH724	--	--
SQUAB	605	26/7	0.966 [25]												
ROOK	636	24/7	0.977 [25]												
GROSBEAK	636	26/7	0.991 [25]												
FLAMINGO	666.6	24/7	1.000 [25]												

NOTES:

- DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED AND ARE FOR REFERENCE ONLY.
- THE EQUIVALENT T&B DIE INDEXES ARE LISTED FOR YOUR CONVENIENCE.
- FLASH FORMED DURING CRIMPING SHOULD BE REMOVED BY FILING AND SHARP EDGES ROUNDED OFF.
- CONNECTOR IS INDIVIDUALLY PACKAGED AND SEALED IN POLY TUBE.
- MATERIAL: ALUMINUM TUBE
- INSTALLATION INSTRUCTION IS DRAWING NO. 10100461 (FORM# 10100460)
- ALUM. FILLER PLUGS ARE SUPPLIED TO SEAL CONNECTOR AFTER CRIMPING.
- PENETROX™ PENHT IS REQUIRED FOR INSTALLATION. PENETROX™ PENHT IS NOT PROVIDED WITH THE CONNECTOR AND IS PURCHASED SEPARATELY.
- INSTALLATION TOOLING IS NOT INCLUDED, AND IS PURCHASED SEPARATELY.

TO ORDER BURNDY® PRODUCTS CALL		ACSS LOOP SPLICE, NON EHV	
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: SEE TABLE CAT. NO: SEE TABLE	
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		DRAWN BY: S PANDIAN 5/16/2013 CHECKER: M MOHAN 5/16/2013 DSN APRVL: P WALTZ 5/20/2013 MFG APRVL: -- QA APRVL: C ACKERMAN 5/20/2013 MKT APRVL: B CRUTCHER 5/18/2013	
FOR PRODUCT INFO: http://www.burndy.com			
PROJECT #:	SIZE	DRAWING NO	REV
DOCUMENT TYPE: SALES	D	50025278	A
REL LEVEL: Released		SHEET 1 OF 1	