



BURNDY ITEM NUMBER	BURNDY CATALOG NUMBER	PACKAGE QUANTITY	CARTON QUANTITY	TENSILE STRENGTH LBS / N	BUNDLE DIA. MIN. IN [MM]	BUNDLE DIA. MAX. IN [MM]	LENGTH IN [MM]	WIDTH IN [MM]	MIN INSTALLATION TEMPERATURE °F / °C	MIN OPERATING TEMPERATURE °F / °C	MAX OPERATING TEMPERATURE °F / °C	BAG LENGTH IN [MM]	BAG WIDTH IN [MM]	INSTALLATION TOOL
50022944	CTSS225100304C	100	10000	225 / 1000	.50 [12.7]	.99 [25]	3.94 [100]	.18 [4.6]	-40 / -40	-40 / -40	572 / 300	6.69 [170]	4.33 [110]	CTTSS900
50022945	CTSS225200304C	100	10000	225 / 1000	.50 [12.7]	1.97 [50]	7.87 [200]	.18 [4.6]	-40 / -40	-40 / -40	572 / 300	10.63 [270]	4.33 [110]	CTTSS900
50022946	CTSS225300304C	100	7000	225 / 1000	.50 [12.7]	3.00 [76]	11.81 [300]	.18 [4.6]	-40 / -40	-40 / -40	572 / 300	14.57 [370]	4.33 [110]	CTTSS900
50022947	CTSS225400304C	100	5000	225 / 1000	.50 [12.7]	4.02 [102]	15.75 [400]	.18 [4.6]	-40 / -40	-40 / -40	572 / 300	18.50 [470]	4.33 [110]	CTTSS900
50022948	CTSS225500304C	100	4000	225 / 1000	.50 [12.7]	5.04 [128]	19.68 [500]	.18 [4.6]	-40 / -40	-40 / -40	572 / 300	22.44 [570]	4.33 [110]	CTTSS900
50022949	CTSS225600304C	100	4000	225 / 1000	.50 [12.7]	6.07 [154]	23.62 [600]	.18 [4.6]	-40 / -40	-40 / -40	572 / 300	22.44 [570]	4.33 [110]	CTTSS900

STAINLESS STEEL CABLE TIE:



NOTES:

1. MATERIAL : 304 STAINLESS STEEL.
2. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED AND ARE FOR REFERENCE ONLY.


TO ORDER BURNDY® PRODUCTS CALL		304 STAINLESS STEEL CABLE TIES															
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: SEE TABLE															
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: SEE TABLE															
FOR PRODUCT INFO: http://www.burndy.com		<table border="1"> <tr> <td>DRAWN BY: V.KAMAL</td> <td>05/22/2013</td> <td rowspan="5"></td> </tr> <tr> <td>CHECKER: A.MONTMINY</td> <td>06/27/2013</td> </tr> <tr> <td>DSN APRVL: A.MONTMINY</td> <td>06/27/2013</td> </tr> <tr> <td>MFG APRVL: --</td> <td>--</td> </tr> <tr> <td>QA APRVL: C.KOWALCZYK</td> <td>06/28/2013</td> </tr> <tr> <td>MKT APRVL: R.CAVANAUGH</td> <td>06/27/2013</td> <td></td> </tr> </table>		DRAWN BY: V.KAMAL	05/22/2013		CHECKER: A.MONTMINY	06/27/2013	DSN APRVL: A.MONTMINY	06/27/2013	MFG APRVL: --	--	QA APRVL: C.KOWALCZYK	06/28/2013	MKT APRVL: R.CAVANAUGH	06/27/2013	
DRAWN BY: V.KAMAL	05/22/2013																
CHECKER: A.MONTMINY	06/27/2013																
DSN APRVL: A.MONTMINY	06/27/2013																
MFG APRVL: --	--																
QA APRVL: C.KOWALCZYK	06/28/2013																
MKT APRVL: R.CAVANAUGH	06/27/2013																
REV	DATE	DESCRIPTION	ECO	BY	C'H'K.	PROJ #	SIZE	DRAWING NO	REV								
F	12/01/2017	CARTON QUANTITIES ADDED TO TABLE	48120	DD	PB		B	50025551	F								

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
F	12/01/2017	CARTON QUANTITIES ADDED TO TABLE	48120	DD	PB

PROJ #	SIZE	DRAWING NO	REV
	B	50025551	F
REL LEVEL: Released		SHEET 1 OF 4	




BURNDY ITEM NUMBER	BURNDY CATALOG NUMBER	PACKAGE QUANTITY	CARTON QUANTITY	TENSILE STRENGTH LBS / N	BUNDLE DIA. MIN. IN [MM]	BUNDLE DIA. MAX. IN [MM]	LENGTH IN [MM]	WIDTH IN [MM]	MIN INSTALLATION TEMPERATURE °F / °C	MIN OPERATING TEMPERATURE °F / °C	MAX OPERATING TEMPERATURE °F / °C	BAG LENGTH IN [MM]	BAG WIDTH IN [MM]	INSTALLATION TOOL
50022950	CTSS500200304L	50	5000	500 / 2200	.50 [12.7]	1.97 [50]	7.87 [200]	.31 [7.9]	-40 / -40	-40 / -40	572 / 300	10.63 [270]	5.90 [150]	CTTSS900
50022951	CTSS500300304L	50	4000	500 / 2200	.50 [12.7]	3.00 [76]	11.81 [300]	.31 [7.9]	-40 / -40	-40 / -40	572 / 300	14.57 [370]	5.90 [150]	CTTSS900
50022952	CTSS500400304L	50	2500	500 / 2200	.50 [12.7]	4.02 [102]	15.75 [400]	.31 [7.9]	-40 / -40	-40 / -40	572 / 300	18.50 [470]	5.90 [150]	CTTSS900
50022953	CTSS500500304L	50	2000	500 / 2200	.50 [12.7]	5.04 [128]	19.68 [500]	.31 [7.9]	-40 / -40	-40 / -40	572 / 300	22.44 [570]	5.90 [150]	CTTSS900
50022954	CTSS500600304L	50	2000	500 / 2200	.50 [12.7]	6.07 [154]	23.62 [600]	.31 [7.9]	-40 / -40	-40 / -40	572 / 300	26.38 [670]	5.90 [150]	CTTSS900
50022955	CTSS500700304L	50	1500	500 / 2200	.50 [12.7]	7.09 [180]	27.56 [700]	.31 [7.9]	-40 / -40	-40 / -40	572 / 300	30.31 [770]	5.90 [150]	CTTSS900
50022956	CTSS500750304L	50	1000	500 / 2200	.50 [12.7]	7.60 [193]	31.50 [800]	.31 [7.9]	-40 / -40	-40 / -40	572 / 300	34.25 [870]	5.90 [150]	CTTSS900
50022957	CTSS500800304L	50	1000	500 / 2200	.50 [12.7]	8.12 [206]	39.37 [1000]	.31 [7.9]	-40 / -40	-40 / -40	572 / 300	42.13 [1070]	5.90 [150]	CTTSS900

TO ORDER BURNDY® PRODUCTS CALL
 UNITED STATES
 1-800-346-4175 (LONDONDERRY, NH)
 CANADA:
 1-800-361-6975 (QUEBEC)
 1-800-387-6487 (ALL OTHER PROVINCES)
 FOR PRODUCT INFO: <http://www.burndy.com>

304 STAINLESS STEEL CABLE TIES			
ITEM NO: SEE TABLE			
CAT. NO: SEE TABLE			
DRAWN BY: V.KAMAL	05/22/2013		
CHECKER: A.MONTMINY	06/27/2013		
DSN APRVL: A.MONTMINY	06/27/2013		
MFG APRVL: --			
QA APRVL: C.KOWALCZYK	06/28/2013		
MKT APRVL: R.CAVANAUGH	06/27/2013		
PROD FAM: --		DRAWING NO	REV
PROJECT #: --	SIZE	50025551	F
DOCUMENT TYPE: SALES	B	SHEET 2 OF 4	
REL LEVEL: Released			


REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
F	12/01/2017	CARTON QUANTITIES ADDED TO TABLE	48120	DD	PB

BURNDY ITEM NUMBER	BURNDY CATALOG NUMBER	PACKAGE QUANTITY	CARTON QUANTITY	TENSILE STRENGTH LBS / N	BUNDLE DIA. MIN. IN [MM]	BUNDLE DIA. MAX. IN [MM]	LENGTH IN [MM]	WIDTH IN [MM]	MIN INSTALLATION TEMPERATURE °F / °C	MIN OPERATING TEMPERATURE °F / °C	MAX OPERATING TEMPERATURE °F / °C	BAG LENGTH IN [MM]	BAG WIDTH IN [MM]	INSTALLATION TOOL
50022958	CTSS700200304L	50	2500	700 / 3113	1.00 [25.4]	1.97 [50]	7.87 [200]	.50 [12.7]	-40 / -40	-40 / -40	572 / 300	11.81 [300]	7.48 [190]	CTTSS900
50022959	CTSS700300304L	50	2000	700 / 3113	1.00 [25.4]	3.00 [76]	11.81 [300]	.50 [12.7]	-40 / -40	-40 / -40	572 / 300	15.75 [400]	7.48 [190]	CTTSS900
50022960	CTSS700400304L	50	1200	700 / 3113	1.00 [25.4]	4.02 [102]	15.75 [400]	.50 [12.7]	-40 / -40	-40 / -40	572 / 300	19.68 [500]	7.48 [190]	CTTSS900
50022961	CTSS700500304L	50	1000	700 / 3113	1.00 [25.4]	5.04 [128]	19.68 [500]	.50 [12.7]	-40 / -40	-40 / -40	572 / 300	23.62 [600]	7.48 [190]	CTTSS900
50022962	CTSS700600304L	50	1000	700 / 3113	1.00 [25.4]	6.07 [154]	23.62 [600]	.50 [12.7]	-40 / -40	-40 / -40	572 / 300	27.56 [700]	7.48 [190]	CTTSS900
50022963	CTSS700700304L	50	700	700 / 3113	1.00 [25.4]	7.09 [180]	27.56 [700]	.50 [12.7]	-40 / -40	-40 / -40	572 / 300	31.50 [800]	7.48 [190]	CTTSS900
50022964	CTSS700800304L	50	500	700 / 3113	1.00 [25.4]	8.12 [206]	39.37 [1000]	.50 [12.7]	-40 / -40	-40 / -40	572 / 300	43.31 [1100]	7.48 [190]	CTTSS900

TO ORDER BURNDY® PRODUCTS CALL		304 STAINLESS STEEL CABLE TIES															
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: SEE TABLE															
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: SEE TABLE															
FOR PRODUCT INFO: http://www.burndy.com		<table border="1"> <tr> <td>DRAWN BY: V.KAMAL</td> <td>05/22/2013</td> <td rowspan="5"></td> </tr> <tr> <td>CHECKER: A.MONTMINY</td> <td>06/27/2013</td> </tr> <tr> <td>DSN APRVL: A.MONTMINY</td> <td>06/27/2013</td> </tr> <tr> <td>MFG APRVL: --</td> <td></td> </tr> <tr> <td>QA APRVL: C.KOWALCZYK</td> <td>06/28/2013</td> </tr> <tr> <td>MKT APRVL: R.CAVANAUGH</td> <td>06/27/2013</td> <td></td> </tr> </table>		DRAWN BY: V.KAMAL	05/22/2013		CHECKER: A.MONTMINY	06/27/2013	DSN APRVL: A.MONTMINY	06/27/2013	MFG APRVL: --		QA APRVL: C.KOWALCZYK	06/28/2013	MKT APRVL: R.CAVANAUGH	06/27/2013	
DRAWN BY: V.KAMAL	05/22/2013																
CHECKER: A.MONTMINY	06/27/2013																
DSN APRVL: A.MONTMINY	06/27/2013																
MFG APRVL: --																	
QA APRVL: C.KOWALCZYK	06/28/2013																
MKT APRVL: R.CAVANAUGH	06/27/2013																
REV	DATE	DESCRIPTION	ECO	BY	C'H'K.	DRAWING NO	REV										
F	12/01/2017	CARTON QUANTITIES ADDED TO TABLE	48120	DD	PB	50025551	F										
						PROJ #:	SALES										
						REL LEVEL:	Released										
						SIZE	B										
						SHEET	3 OF 4										

BURNDY ITEM NUMBER	BURNDY CATALOG NUMBER	PACKAGE QUANTITY	CARTON QUANTITY	TENSILE STRENGTH LBS / N	BUNDLE DIA. MIN. IN [MM]	BUNDLE DIA. MAX. IN [MM]	LENGTH IN [MM]	WIDTH IN [MM]	MIN INSTALLATION TEMPERATURE °F / °C	MIN OPERATING TEMPERATURE °F / °C	MAX OPERATING TEMPERATURE °F / °C	BAG LENGTH IN [MM]	BAG WIDTH IN [MM]	INSTALLATION TOOL
50022965	CTSS900200304L	50	1200	920 / 4100	1.00 [25.4]	1.97 [50]	7.87 [200]	.62 [15.9]	-40 / -40	-40 / -40	572 / 300	11.81 [300]	7.48 [190]	CTTSS900
50022966	CTSS900300304L	50	1000	920 / 4100	1.00 [25.4]	3.00 [76]	11.81 [300]	.62 [15.9]	-40 / -40	-40 / -40	572 / 300	15.75 [400]	7.48 [190]	CTTSS900
50022967	CTSS900400304L	50	800	920 / 4100	1.00 [25.4]	4.02 [102]	15.75 [400]	.62 [15.9]	-40 / -40	-40 / -40	572 / 300	19.68 [500]	7.48 [190]	CTTSS900
50022968	CTSS900500304L	50	600	920 / 4100	1.00 [25.4]	5.04 [128]	19.68 [500]	.62 [15.9]	-40 / -40	-40 / -40	572 / 300	23.62 [600]	7.48 [190]	CTTSS900
50022969	CTSS900600304L	50	500	920 / 4100	1.00 [25.4]	6.07 [154]	23.62 [600]	.62 [15.9]	-40 / -40	-40 / -40	572 / 300	27.56 [700]	7.48 [190]	CTTSS900
50022970	CTSS900700304L	50	400	920 / 4100	1.00 [25.4]	7.09 [180]	27.56 [700]	.62 [15.9]	-40 / -40	-40 / -40	572 / 300	31.50 [800]	7.48 [190]	CTTSS900
50022971	CTSS900800304L	50	300	920 / 4100	1.00 [25.4]	8.12 [206]	39.37 [1000]	.62 [15.9]	-40 / -40	-40 / -40	572 / 300	43.31 [1100]	7.48 [190]	CTTSS900

TO ORDER BURNDY® PRODUCTS CALL
 UNITED STATES
 1-800-346-4175 (LONDONDERRY, NH)
 CANADA:
 1-800-361-6975 (QUEBEC)
 1-800-387-6487 (ALL OTHER PROVINCES)
 FOR PRODUCT INFO: <http://www.burndy.com>

304 STAINLESS STEEL CABLE TIES			
ITEM NO: SEE TABLE			
CAT. NO: SEE TABLE			
DRAWN BY: V.KAMAL	05/22/2013		
CHECKER: A.MONTMINY	06/27/2013		
DSN APRVL: A.MONTMINY	06/27/2013		
MFG APRVL: --			
QA APRVL: C.KOWALCZYK	06/28/2013		
MKT APRVL: R.CAVANAUGH	06/27/2013		
PROD FAM: --		DRAWING NO	REV
PROJECT #: --	SIZE	50025551	F
DOCUMENT TYPE: SALES	B	SHEET 4 OF 4	
REL LEVEL: Released			

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
F	12/01/2017	CARTON QUANTITIES ADDED TO TABLE	48120	DD	PB