



INSPECTION PIN GAUGE DIA.			
DIE INDEX	COLOR CODE	GO	NO GO
7	BLUE	.175 [4.44]	.212 [5.38]

REV	DATE	DESCRIPTION	ECO	BY	CHK.
A	12/03/2013	SALES DRAWINGS CREATED FOR J6CNC	34011	VK	PB



**NOTES:**

- DIMENSIONS IN BRACKETS [ ] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED AND ARE FOR REFERENCE ONLY.
- CATALOG NUMBER J6CNC CONSISTS OF 1 INDENTOR DIE AND INCLUDED SCREW. TO BE USED WITH Y2CNC NEST DIE AND Y6NCP PNEUMATIC TOOL.
- FOR USE ON YA6C- & YAV6C- HYLUG™ TERMINALS AND YS6C- & YSV6C- HYLINK™ SPLICES.

TO ORDER BURNDY® PRODUCTS CALL		J DIE #6 UPPER HEAD GROOVE	
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: 26001337	CAT. NO: J6CNC
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		DRAWN BY: E.MARTIN 11/13/2013	CHECKER: P.WASON 11/15/2013
FOR PRODUCT INFO: <a href="http://www.burndy.com">http://www.burndy.com</a>		DSN APRVL: E.MARTIN 11/15/2013	MFG APRVL: --
		QA APRVL: J.BRODEUR 11/16/2013	MKT APRVL: M.RZASA 12/02/2013
PROJECT #:	SIZE	DRAWING NO	REV
DOCUMENT TYPE: SALES	B	50035236	A
REL LEVEL: Released		SHEET 1 OF 1	