


CATALOG NO.	ITEM NO.	L
BD18G80	33203K	18.00 [457]
BD36G80	50093159	36.00 [914]


REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
B	07/10/2018	UPDATED AS PER REQUEST	49460	YR	VS



NOTES:

1. APPROXIMATE AMP RATING: 190A INDOOR, 225A OUTDOOR. THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID, AND OTHER SERVICE CONDITIONS.
2. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.

- 3 LISTED TO UL 467 GROUNDING & BONDING EQUIPMENT STANDARDS.
- 4 LISTED TO CSA 22.2 NO.41 GROUNDING & BONDING EQUIPMENT STANDARDS.



TO ORDER BURNDY® PRODUCTS CALL		BRAID	
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: SEE TABLE	
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: SEE TABLE	
FOR PRODUCT INFO: http://www.burndy.com		DRAWN BY: B.SURESH BABU 7/31/2014	
		CHECKER: L.TROMBLEY 8/1/2014	
		DSN APRVL: L.TROMBLEY 8/1/2014	
		MFG APRVL: -- 8/1/2014	
		QA APRVL: C.LINDQUIST 8/4/2014	
		MKT APRVL: K.ROBICHEAU 7/31/2014	
PROD FAM: MECHANICAL GROUNDING	DRAWING NO	REV	
PROJECT #: --	SIZE	50047629	B
DOCUMENT TYPE: SALES	B	SHEET 1 OF 1	
REL LEVEL: Released			