


CAT. NO.	ITEM NUMBER	"L"
BD12NB	50047785	12.00
BD18NB	50047786	18.00
BD24NB	50047787	24.00

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
A	11/24/2014	SALES DRAWING RELEASE	38481	DK	MA



NOTES:

- APPROXIMATE AMP. RATING: 190 INDOOR, 225 OUTDOOR, THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID AND OTHER SERVICE CONDITIONS.
- DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.

3 ALL SIZES ARE LISTED TO UL 467 GROUNDING & BONDING EQUIPMENT STANDARDS.

4 ALL SIZES ARE LISTED TO CSA C22.2 NO.41 GROUNDING & BONDING EQUIPMENT STANDARDS.

TO ORDER BURNDY PRODUCTS CALL		BLACK HEAT SHRINK INSULATED BRAID	
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: SEE TABLE	
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: BD-NB (TABLE)	
FOR PRODUCT INFO: http://www.burndy.com		DRAWN BY: N.D.KANNAN 11/24/2014	
		CHECKER: L.TROMBLEY 12/18/2014	
		DSN APRVL: L.TROMBLEY 12/18/2014	
		MFG APRVL: M.STEVENS 12/17/2014	
		QA APRVL: C.LINDQUIST 12/22/2014	
		MKT APRVL: K.ROBICHEAU 12/17/2014	
PROD FAM:	DRAWING NO	REV	
PROJECT #:	SIZE	50047825	A
DOCUMENT TYPE: SALES	B	SHEET 1 OF 1	
REL LEVEL: Released			

