


DRAWING# 50049475				
ITEM NO.	CATALOG NO.	LENGTH		
		L (IN)	L (FT)	L [mm]
50047576	BB048L300	300	25.0	[7620]
50050359	BB048L600	600	50.0	[15240]
25006215	BB048L720	720	60.0	[18288]
25004012	BB048L1200	1200	100.0	[30480]
25009251	BB048L3000	3000	250.0	[76200]
50067113	BB048L12000	12000	1000.0	[304800]

REV	DATE	DESCRIPTION	ECO	BY	CHK.
C	11/20/2019	HATCHING UPDATED TO SHOW THE BRAID REALISTIC	52547	PB	RG



NOTES:

1. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED AND ARE FOR REFERENCE ONLY.
2. MATERIAL : TIN PLATED COPPER
3. APPROXIMATE AWG SIZE : #3 AWG
4. FOR OTHER BRAID SIZES, REFERENCE DRAWING #10110676.
5. AVAILABLE IN OTHER LENGTHS UPON REQUEST.
6. LONG LENGTHS MAY NOT BE ONE CONTINUOUS PIECE.

TO ORDER BURNDY® PRODUCTS CALL UNITED STATES 1-800-346-4175 (LONDONDERRY, NH) CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES) FOR PRODUCT INFO: http://www.burndy.com	BRAID		
	ITEM NO: SEE TABLE		
	CAT. NO: BB048L--(TABLE)		
	DRAWN BY: B.PARTHIBAN	09/22/2014	BURNDY
	CHECKER: L.TROMBLEY	10/07/2014	
	DSN APRVL: L.TROMBLEY	10/07/2014	
	MFG APRVL: --		
	QA APRVL: C.LINDQUIST	10/08/2014	
	MKT APRVL: K.ROBICHEAU	10/07/2014	
	PROD FAM: --		DRAWING NO
PROJECT #: --	SIZE	50049475	
DOCUMENT TYPE: SALES	B	REV	
REL LEVEL: Released		C	